

SMD Tactile Switch KLS7-TS4407

SMD Tactile Switch

SIZE: 4.2*4.5mm

Rating: 50mA 12VDC

Contact Resistance : 50mΩ Max.

Insulation Resistance: 100MΩ Min.

Dielectric Strength : AC250V(50/60Hz for 1minute)

Electrically Life: 100,000cycles

Environment temperature: -20°C-70°C

Operating Force: 180/250(±30gf)

Seal temperature:260°C-280°C

ORDER INFORMATION

KLS7-TS4407-1.5-180-B

(1) (2)

(1)-Operating Force :180~250gf

(2)-Packing: B=Bulk T=Tape

