


Datasheet

ENGLISH


RS PRO, 12 V dc, 1869 gcm, Brushed DC Geared Motor, Output Speed 906 rpm

Stock No: 420-665



Specifications:

Output Speed	906 rpm
Supply Voltage	4.5 - 15 V dc
Maximum Output Torque	1869 g.cm
DC Motor Type	Brushed
Shaft Diameter	6mm
Power Rating	19.8 W
Gearhead Type	Spur
Length	79.5mm
Width	39.3mm
Current Rating	2.81 A
Weight	278g



Operating relative humidity 20% ~ 85%
 Operating temperature range -10°C ~ +60°C

Ratio	L
16:1	28.5mm

Gearbox Housing material	Metal
Backlash at no-load	< 2°
Bearing at output	Sleeve bearings
Radial load (10mm from flange)	< 1 kgf
Shaft axial load	< 0.7 kgf
Shaft press fit force max	< 5 kgf
Radial play of shaft	< 0.05mm
Thrust play of shaft	< 0.35mm

Reduction Ratio	Rated tolerance Torque	Max momentary Tolerance Torque	Efficiency
1/16	2.0 kgf-cm Max.	6.0 kgf-cm	73%

Reduction Table RPM SUPPLY VOLTAGE	4.5v	6v	9v	12v	15v
420-665	340	453	680	906	1133

Note: Motor speeds may vary by (+) or (-) 12.5%

