

# 0 601 9H8 000 – GSR 12V-35

Material number	0 601 9H8 000	0 601 9H8 001	0 601 9H8 070
EAN	3165140953696	3165140953702	3165140953665
2 x battery GBA 12V 3.0Ah 1 600 A00 X79			✓
Cardboard box	✓		
L-BOXX 102 1 600 A00 1RP		✓	✓
Quick charger GAL 12V-40 Professional 1 600 A01 9R4			✓
Tool dimensions (height)	181 mm	181 mm	
Battery voltage	12.0 V	12.0 V	12.0 V
Drill chuck, version		10-mm keyless chuck	
Battery type		Lithium-ion	
Charging time (80%/100%) approx.			36/50 min [3.0 Ah]
Weight incl. battery			1,2 kg

## Technical data

### Technical data

Torque (soft/hard/max.)	20/35/- Nm
No-load speed (1st gear / 2nd gear)	0 – 460 / 0 – 1,750 rpm
Battery type	Lithium-ion
Chuck capacity, min./max.	10 mm
Battery voltage	12 V
Weight excl. battery	0.75 kg
Torque settings	20+1

### Drilling diameter

Max. drilling diameter in wood	32 mm
Max. drilling diameter in steel	10 mm

### Screw diameter

Max. screw diameter	8 mm
---------------------	------

### Noise/vibration information

Sound power level	73 dB(A)
Uncertainty K	3 dB



## Sales information

---

### Positioning

- The drill driver with the best performance and compactness in the 12V category

### User benefit

- Compact design enables optimum handling, especially when working overhead or in tight spaces
- Best performance-to-size ratio: 35 Nm hard torque, 0-1,750 rpm, 154-mm head length
- Brushless motor along with Electronic Motor Protection prevents overload and ensures a longer tool lifetime

