


Datasheet High Dome

RS Stock 896-2060



Dimensions: (mm)



Specifications

Connection Type:	2Pole + Earth
Voltage:	250V AC VAC / 250 VAC
Approvals:	NA
Standard:	NA
Mounting:	Screw Type
Type:	HD-Socket (HI-DOME) – Illuminated
Socket Type:	Type A
Mounting:	M3 Screw
Material For Rubber Gasket:	Nitril / Silicon
Material Body:	Nylon-6 GF
Gland Size:	PG-9
Body Colours:	Black, Grey
Contact Resistance:	20m Ohms max
Current Carrying Parts:	Copper alloy / Tin plated
Rating:	10A 110VAC, 230VAC
Terminals:	Screw-type
H.V Breakdown Test:	2 KV AC For 1 Minute
Insulation Resistance:	100 M Ohms min.