

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2137192061](#)
Status: **Active**
Overview: Micro-Lock Plus Wire-to-Board Connector System
Description: 2.00mm Pitch, Micro-Lock Plus Plug Crimp Housing, Single Row, 6 Circuits, UL 94V-0, Black

Documents:

Drawing (PDF)	Packaging Specification 2137199200-SPK-200 (PDF)
Product Specification 5055700003-PS-000 (PDF)	Datasheet (PDF)
Application Specification 5055700001-A03 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E29179

General

Product Family	Crimp Housings
Series	213719
Application	Power, Wire-to-Wire
Overview	Micro-Lock Plus Wire-to-Board Connector System
Product Name	Micro-Lock Plus
Taxonomy	Connector Housings
UPC	193264756513


Physical

Circuits (maximum)	6
Color - Resin	Black
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyamide
Net Weight	1680.280/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	5055700001-A03
Packaging Specification	2137199200-SPK-200
Product Specification	5055700003-PS-000
Sales Drawing	2137190000-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[213719 Series](#)

Mates With

[Micro-Lock Plus Receptacle Crimp Housing 505570](#)

Use With

[Micro-Lock Plus Male Crimp Terminal 213720](#)