

HUBER+SUHNER® DATA SHEET

Coaxial Panel Connector: 24_QN-50-3-2/133_N



Description

Straight panel bulkhead cable jack, flange mount

Interface standards
QN QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω	
Interface frequency max.	11 GHz	
Frequency range	DC to 2 GHz	2 to 2.5 GHz
Return loss	≥ 32 dB	≥ 30 dB

Mechanical Data

Weight 0.02 kg

Environmental Data

Operating Temperature -40 °C to 125 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	MVQ	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00009333
Catalogue drawing	DCA-00008982
Assembly instruction	DOC-0000185710
Mounting hole	ML112

Ordering Information

Single package 24_QN-50-3-2/133_NE

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions