


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	50-00540	Connector, dc plug, 5.5x2.1x23 mm, molding style, spring contacts, nickel plated, 105° C	1	
2	30-01248	Wire, 2C, 18 AWG, UL4384, 300V, 105 °C, 4.4 mm, VW-1, LSZH, XLPE	1	
3	24-00003	Overmold	1	TPE, 105 °C, black



Wiring Diagram	
50-00540	wire color
center	black with stripe
sleeve	black

Revision:	Date:	Description:	Prepared:	Notes:	Size:	Part number:
A	10/03/2018	Initial release	RoHS compliant	Function test: no open, no short circuit, no intermittent	A	10-03130
			Verified:	Low smoke, zero halogen		
			Dimensions are in millimeters.	Description:		
			Tolerances:	Cable, 1830 mm, 5.5x2.1x12 mm 50-00540 dc plug to 10 mm tinned, 18 AWG, 30-01248, LSZH		
			X: ± 0.5 mm			
			XX: ± 0.3 mm			
			XXX: ± 0.05 mm			
					Scale: 1:1	Sheet 1 of 1

TENSILITY

tel 1.541.323.3228 800 877.670.7118
 fax 1.541.323.4202 web tensility.com

