

REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------

NOTES1:

UL Standard

1. Rated voltage/current : 300V / 8A
2. Withstanding voltage : AC1600V/1Min.
3. Torque value : M2 , 1.77Lb.in
4. Wire range : 28~16AWG

IEC Standard

1. Pollution degree	2
Overvoltage category	II
Rate impulse voltage(KV)	2.5KV
Rate voltage(V)	250V
Rate current(A)	7A

2. Torque value : M2 , 0.2N·m
3. Wire range : 0.5~1.5mm²

NOTES2:

1. Dimension shall be interpreted per ASME Y14.5-2009
2. Pitch : 3.5/3.81mm, Poles : N=02~24P
3. Stripping length : 6~7mm
4. Operating temperature: -40°C~+105°C
5. Undimensioned tolerances:



Pitch range in mm		Nominal dimension range in mm						0.1/10
TO	Over TO	Over TO	Over TO	Over TO	Over TO	Over TO	0.1/10	
6	6 TO 10	10 TO 24	30 TO 30	60 TO 60	100 TO 100	150 TO 150	<	
	±0.15	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30	
							±2*	

6. RoHS Compliance

15EDGK - 3.5/3.81 - XXP - 1Y - 00A (H)

(Series No.) (Pitch) (Poles) (Color): 1.(Grey)
 2.(Blue)
 3.(Black)
 4.(Green)
 5.(Orange)
 6.(Red)
 7.(Transparent)
 8.(Yellow)
 9.(White)

(RoHS)
 00A--(Standard)






2.15
2.30

3.5
3.81

3.5x(N-1)
3.81x(N-1)


3.5x(N-1)+4.3
3.81x(N-1)+4.6

02~06P have this card point



DETACHED LISTS	PART NO.:	/			
	APPD:	/			
	CHKD:	/			
	DRFT:	/			
	NAME:		15EDGK-3.5/3.81-XXP-1Y-00A(H)		
TITLE:		CUSTOMER DRAWING	REV	DO	
DRAWING NO.:		/	SHEET	1/1	
THIRD ANGLE PROJECTION		MM (INCH)	DO NOT SCALE DRAWING	SCALE 1:1	

宁波高松电子有限公司
 NINGBO DEGSON ELECTRICAL CO., LTD



THIRD ANGLE PROJECTION

DRAWING NO.:

MM (INCH)

DO NOT SCALE DRAWING

SCALE 1:1

REV

DO

SHEET

1/1

SCALE

1:1