

Detailed Specifications

Frame Width:	150[mm]
Frame Height:	172[mm]
Frame Depth:	25[mm]
Max. Air Flow:	250[CFM]
Max. Air Flow:	7.08[m3 per min]
Max. Static Pressure:	0.65[In H2O]
Max. Static Pressure:	263.7[Pa]
Fan Speed:	3500[RPM]
Noise:	62.5[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	18[V]
Current:	2.06[A]
Input Power:	24.7[W]
Mass:	510.3[g]
Tach / Locked Rotor Output:	No
Status:	Active