

## 111.12.050 1.6 bar 2nd scale psi G1/8B

### Bourdon tube pressure gauges,model 111

Item number:

Quantity: 1 pcs.

Order code: 111.12-B-BG316P-GA-BOZ3NZ4Z-Z-ZZZZ 1SBZ2AAZAA3  
DIAL-IAC1ZZZZZZZZZ1Z- 1Z1ZZ9ZZZZ  
LABEL-S61DE-##ZZZ

Overview: 111.12.050 1.6 bar 2nd scale psi G1/8B  
Connector location: center back mount  
Case: black steel with pressure vent  
class 2.5  
narrow panel ring, SS, rolled on, with mounting bracket  
Window: plastic, clear  
Pointer: plastic, black  
single packing  
Dial: plastic, white, with stop-pin  
stop-pin at zero  
2nd scale red  
\*EN 837-1\* \*Cl.2.5\* \*WIKA\*  
Label: WIKA UK customer: RS (Label yellow) "Made in Poland"  
447 9034  
G1/8B 1.6 bar 50mm

Details: Bourdon tube pressure gauges,model 111  
Model: 111.12  
Specifications according to data sheet  
Model: 111.12 standard center back  
Nominal size: 050 mm  
Unit of outer Scale: bar  
Measuring range: gauge pressure range  
Scale range: 0...1.6 bar  
2nd Scale or Special Scale: 2nd scale psi  
Process connection: G 1/8 B  
Connector location: center back mount  
Case: black steel with pressure vent  
Mounting flange/bracket: narrow panel ring, SS, rolled on, with mounting bracket  
Window: plastic, clear  
Accuracy class: class 2.5  
Overpressure safe: standard  
Ingress protection: Standard  
Pointer: plastic, black  
Packaging: single packing  
Process connection surface area: brass  
Dial: plastic, white, with stop-pin

Date: 25/01/2024



Specifications according to data sheet: PM 01.01

Dial description:

Pressure Gauge Standard: International (standard Europe)

color for 1.scale (outside): black

color for 2.scale (inside): red RAL 3020

dial background: White

Manufacturer logo: \*WIKA\*

stop pin on dial: at zero

norm-mark on dial: \*EN 837-1\*

accuracy class on dial: \*Cl.2.5\*

description field 1 (ET1): 447 9034

description field 2 (ET2): G1/8B 1.6 bar 50mm