

MOSA M12 FEMALE 0° FIELD-WIREABLE (IDC)5-pol., 0,34-0.5mm²


Female straight

M12, 5-pole


IDC terminals

Connection cross section: 0.34...0.5 mm²

The resistance to aggressive media should be individually tested for your application.
Further details on request.

[Link to Product](#)**Illustration**

Female



Product may differ from Image

Approvals



Form

Form 12593

Technical Data

| | |
|-------------------------------|---|
| Operating voltage | max. 50 V AC/DC |
| Operating current per contact | max. 4 A |
| Connection cross section | 0.34...0.5 mm ² (conductor diameter min. 0.1 mm) |
| Sealing range (cable Ø) | 4.7...6 mm |
| Wire isolation | PVC, PP |
| Outer wire Ø | 1.2...2.0 mm |
| Protection | IP67 inserted and tightened (EN 60529) |

General data

| | |
|----------------------|-----------------|
| Temperature range | -25...+85 °C |
| Dimensions H x W x D | 49x20.5x20.5 mm |

Commercial data

| | |
|------------------------|---------------|
| country of origin | DE |
| customs tariff number | 85366990 |
| EAN | 4048879306003 |
| eClass | 27279221 |
| minimum order quantity | 1 |