

SPECIFICATION FOR APPROVAL

COMMODITY	PK CHOKE		SPEC NO.	SP-070704001
ITEM	COIL0807-0.33	Green	D	QRRD-01-02

(1) DIMENSION: (UNIT: mm)		DIM.	TOL.
	A	9.5	MAX.
	B	8.5	MAX.
	C	16.0	±3.0
	D	0.65	±0.1
	E	5.0	±0.5
	F	3.0	MAX.
	G		
	H		
	I		
	J		

(2) ELECTRICAL CHARACTERISTIC			TEST INSTRUMENTS.
INDUCTANCE	330± 10%	μH	<input checked="" type="checkbox"/> AGILENT 4294A Precision Impedance Analyzer. <input type="checkbox"/> AGILENT 4285A Precision L.C.R. Meter. <input type="checkbox"/> HP-4286A RF L.C.R. Meter.
TEST FREQUENCY	1	kHz	<input type="checkbox"/> ZENTECH 3302 Automatic Components Analyzer. <input type="checkbox"/> ZENTECH 101 L.C.R. Meter.
TEST VOLT	0.25	V	<input type="checkbox"/> WAYNE KERR 6420 Precision Impedance Analyzer. <input checked="" type="checkbox"/> ZENTECH 1320 BIAS CURRENT.
RDC	1.038 (max)	Ω	<input checked="" type="checkbox"/> ZENTECH 502AC Resistance Meter. <input type="checkbox"/> ADEX AX-1155B DC Low Ohm Meter.
Isat	0.9 (max)	A	
Irms	0.8 (max)	A	

REMARK :

1. Inductance drop = 10% typ at Isat.
2. ΔT = 40°C rise typ at Irms.

SPECIFICATION FOR APPROVAL

COMMODITY	PK CHOKE		SPEC NO.	SP-070704001
ITEM	COIL0807-0.33	Green	D	QRRD-01-02
(3) Material List				
NO	ITEM	MATERIAL	NOTE	
1	CORE	DR2W 8*7 Or other's equivalent		
2	WIRE	UEW Or other's equivalent	130°C CLASS	
3	SOLDER	100H Or other's equivalent		
4	TUBE	Heat Shrinkable tube		