

Detailed Specifications

Frame Width:	119[mm]
Frame Height:	119[mm]
Frame Depth:	32[mm]
Max. Air Flow:	111.9[CFM]
Max. Air Flow:	3.17[m ³ per min]
Max. Static Pressure:	0.33[In H ₂ O]
Max. Static Pressure:	82[Pa]
Fan Speed:	3100[RPM]
Noise:	47[dB]
Life Expectancy:	25 degree C 50,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.69[A]
Input Power:	8.3[W]
Mass:	240[g]
Tach / Locked Rotor Output:	No
Status:	Active

DC Axial Fans