

**Specifications of UT60 Series Digital Multimeters**

Specification	Range	UT60EU	UT60BT	UT60S
DC Voltage	9.999mV/99.99mV/999.9mV/ 9.999V/99.99V/999.9V	±(0.5%+3)	±(0.5%+3)	±(0.5%+3)
AC Voltage	9.999mV/99.99mV/999.9mV/ 9.999V/99.99V/999.9V	±(0.8%+3)	±(0.8%+3)	±(0.8%+3)
DC Current	999.9uA/999.9mA/9.999A/10A	±(0.8%+3)	±(0.8%+3)	±(0.8%+3)
AC Current	999.9uA/999.9mA/9.999A/10A	±(1.0%+3)	±(1.0%+3)	±(1.0%+3)
Resistance	999.9Ω/9.999kΩ/99.99kΩ/999.9kΩ/9.999MΩ/99.99MΩ	±(0.8%+2)	±(0.8%+2)	±(0.8%+2)
Capacitor	9.999nF/99.99nF/999.9nF/9.999μF/99.99μF/999.9μF/9.999mF/ 99.9mF	±(4.0%+5)	±(4.0%+5)	±(4.0%+5)
Frequency	99.99Hz~9.999MHz	±(0.1%+5)	±(0.1%+5)	±(0.1%+5)
Duty Cycle	0.1~99.9%	±(3%+5)	±(3%+5)	±(3%+5)
Temperatue	-40°C~1000°C/-40°F~1832°F	±4°C/±5°F	±4°C/±5°F	±4°C/±5°F
<b>Features</b>				
Bluetooth			√	
Display Count		9999	9999	9999
Auto Range		√	√	√
REL		√	√	√
NCV		√	√	√
Diode		√	√	√
Continuity Test		√	√	√
Acousto-optic Indication		√	√	√

(NCV/continuity/battery power)				
Low Battery Indication	≤3.6V	√	√	√
Data Hold		√	√	√
Auto Power Off	15Min	√	√	√
Operation Temperature	0°C~40°C			
Safety	CAT II 1000V/CAT III 600V			
General Characteristics				
Battery	1.5V AAA x 3			
Product Color	Red and Gray			
Product Net Weight	290g			
Product Size	169mm x 81mm x 46mm			
Standard Individual Packing	Gift Box, Manual, Thermocouple			
Standard Quantity Per Carton	20pcs			
Standard Carton Size	420mm x 320mm x 300mm			