


150 kg

Castors for Pallets Series 3360


Housing made of pressed steel, zinc-chromatised, double ball bearing swivel head, dustguard, Standard: Wheel axle with nut

Wheel: POJ
Wheel: Polypropylene, black, with small threadguards, roller bearing











Wheel: POO
Wheel: Polypropylene, black, without threadguards, plain bearing

Wheel: POR
Wheel: Polypropylene, black, without threadguards, roller bearing










3360 POO 125 P62


Swivel Castor	 mm	 mm	 mm	 mm	 mm	 mm	 mm	 kg
3360 POO 100 P62	100	36	105 x 85	80/77 x 60	9	32	128	150
3360 POR 100 P62	100	36	105 x 85	80/77 x 60	9	32	128	150
3360 POJ 108 P62	108	36	105 x 85	80/77 x 60	9	32	132	150
3360 POO 125 P62	125	40	105 x 85	80/77 x 60	9	40	155	150
3360 POR 125 P62	125	40	105 x 85	80/77 x 60	9	40	155	150



3478 POO 125 P62

Fixed Castor	 mm	 mm	 mm	 mm	 mm	 mm	 kg
3478 POO 100 P62	100	36	103 x 85	80/77 x 60	9	128	150
3478 POR 100 P62	100	36	103 x 85	80/77 x 60	9	128	150
3478 POJ 108 P62	108	36	103 x 85	80/77 x 60	9	132	150
3478 POO 125 P62	125	40	103 x 85	80/77 x 60	9	155	150
3478 POR 125 P62	125	40	103 x 85	80/77 x 60	9	155	150

Fixing Plates:



Swivel Castor P 62-105x85

Fixed Castor P62 103x85

Further Informations:
www.tente.com