

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

Firestop® Technical Datasheet 

tasker® T20 – 2x17 AWG - Flexible Loudspeaker Cable



CATEGORY Flexible Speaker Cable (See Audio Catalogue)
APPLICATIONS Loudspeakers and Electronics.

- A:** Black Soft **Flame Retardant PVC** Sheath.
Outer cable Diam. Ø 6,50 (±0,20) mm.
- B:** Core Insulation with PVC, colored one Red and one Black.
Diam. Ø 2,20 (±0,20) mm.
- C:** O.F.C. red copper formation 20x0,25 mm.
Nom. Cross section 2x17 AWG.

MARKING **tasker®** T20 2x17 AWG O.F.C. Loudspeaker Cable - FirestoP® - Made In Italy
CUSTOM This product may be custom produced also in **L.S.Z.H.** polymer, **PE**,
PRODUCTION **PUR**, with or without Metallic Armor.

Cable Properties

Conductor Resistance	18 Ω/Km
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	<input checked="" type="checkbox"/>	Indoor	Interno Edificio	INSTALLATION	<input checked="" type="checkbox"/>	Fixed	Fissa	INFORMATION	<input checked="" type="checkbox"/>	RoHS2 Compliant
Impiego	<input checked="" type="checkbox"/>	Outdoor Limited	Esterno Limitato	Posa	<input checked="" type="checkbox"/>	Restricted Mobile	Mobile Limitata	Informazioni	<input checked="" type="checkbox"/>	Ver. A / 16.05.16
		Outdoor	Esterno			Mobile	Mobile			
		Outdoor Direct Burial	Esterno Interrato			Mobile in Drag Chain	Mobile in Catena			