

## 41 - Metric offset combination wrenches





### Standards:

NF ISO 7738, ISO 7738, DIN 3113

### Description:

- Offset combination wrenches: ring offset to clear fingers or obstacles. Ideal for series of nuts.
- OGV® profile with 12-point ring for powerful tightening while protecting the nut.
- Open end head angled at 15°.
- Metric sizes: 6 to 32 mm.
- Presentation: satin chrome finish.



	A [mm]	Length L [mm]	Thickness E [mm]	Thickness E1 [mm]	Head Width B [mm]	Height H [mm]	Weight [Kg]
41.10	10.0	142.0	5.0	8.0	23.5	16.5	0.05
41.11	11.0	160.0	5.5	8.6	27.5	18.5	0.075
41.12	12.0	160.0	5.5	8.6	27.5	18.5	0.075
41.13	13.0	180.0	5.5	9.0	31.5	18.5	0.1
41.14	14.0	180.0	5.5	9.0	31.5	18.5	0.1
41.15	15.0	200.0	6.6	10.3	36.5	20.5	0.13
41.16	16.0	200.0	6.6	10.3	36.5	20.5	0.13
41.17	17.0	224.0	7.3	11.2	40.5	22.0	0.195
41.18	18.0	224.0	7.3	11.2	40.0	22.0	0.195
41.19	19.0	248.0	7.8	12.6	43.0	24.0	0.25
41.21	21.0	275.0	8.2	13.0	48.0	33.0	0.32
41.22	22.0	275.0	8.2	13.0	48.0	26.5	0.32
41.23	23.0	302.0	9.0	14.0	53.0	28.5	0.415
41.24	24.0	302.0	9.0	14.0	53.0	28.5	0.415
41.26	26.0	332.0	9.5	15.0	59.0	31.5	0.605
41.27	27.0	332.0	9.5	15.0	59.0	31.5	0.605
41.28	28.0	364.0	10.0	15.6	63.0	33.5	0.7
41.29	29.0	364.0	10.0	15.6	63.0	33.5	0.7
41.30	30.0	398.0	10.5	16.5	68.0	35.5	0.85
41.32	32.0	398.0	10.5	16.5	68.0	35.5	0.85
41.6	6.0	113.0	4.0	6.0	14.5	12.5	0.03
41.7	7.0	127.0	4.5	7.0	18.5	15.0	0.035
41.8	8.0	127.0	4.5	7.0	18.5	15.0	0.035
41.9	9.0	142.0	5.0	8.0	23.5	16.5	0.05