



207

LED Installation Permanent Beacon



- Optimised illumination
- 360° visibility
- Suitable for use in the 22 mm standard control panel/switchgear programme
- Simple connection by means of 6.3 mm spades

Life duration
up to 100,000 hrs**i** TECHNICAL SPECIFICATIONS:

Dimensions (Ø x Height):	58 mm x 69 mm (Protrusion from panel)		
Housing:	PA-GF, high impact		
Lens:	PC, transparent, Ring: PC		
Connection:	Spades 6.3 x 0.8 mm Finger-proof model according to BGV A2, when used with insulated spades		
Fixing:	Installation mounting for Ø 22.5 mm (M 22 x 1.5 mm) with anti-twist device		

W ORDER SPECIFICATIONS:

Voltage	24 V \approx	115 V \sim	230 V \sim
Current consumption	45 mA	25 mA	25 mA
red	207 100 75	207 100 67	207 100 68
green	207 200 75	207 200 67	207 200 68
yellow	207 300 75	207 300 67	207 300 68

Further colours and voltages on request.

D TECHNICAL DIAGRAMS:

see page 269

Sizes of Permanent Beacons



24 V

