

231 LED Installation Beacon

LED Permanent beacon with M 22 thread for control panel / switch gear programme. Extremely high light intensity. Modern Chip-On-Board technology. High protection rating IP 65 for indoor and outdoor applications.



TECHNICAL SPECIFICATIONS

| | |
|--|---|
| Dimensions (Diameter x Height): | 28.7 mm x 46 mm |
| Dome: | Polycarbonate, transparent |
| Fixing : | Installation mounting for Ø 22,5 mm (M 22 x 1,5 mm) |
| Housing : | ABS/PC-Blend, black |
| Operating voltage: | 24 V =, 115 V ~, 230 V ~ |
| Current consumption: | 45 mA at 24 V 15 mA at 115 V 15 mA at 230 V |
| Starting current: | < 0,5 A at 24 V |
| Life duration: | up to 100.000 h |
| Terminal element : | 2 wires, c. 115 mm long |

231 LED Installation Beacon

LED Permanent beacon with M 22 thread for control panel / switch gear programme. Extremely high light intensity. Modern Chip-On-Board technology. High protection rating IP 65 for indoor and outdoor applications.



ORDER SPECIFICATIONS

| | 24 V = | 115 V ~ | 240 V ~ |
|--------|----------|----------|----------|
| red | 23110055 | 23110067 | 23110068 |
| green | 23120055 | 23120067 | 23120068 |
| yellow | 23130055 | 23130067 | 23130068 |
| clear | 23140055 | 23140067 | 23140068 |
| blue | 23150055 | 23150067 | 23150068 |