




0682
THREADED SILENCER, MALE BSP
PARALLEL

0682

maximum working pressure	bar 12	MPa 1,2	psi 174
working temperature	°C (Celsius) From -20 to 180	F (Fahrenheit) From -4 to 356	K (Kelvin) From 253 to 453
body	stainless steel 316L		
silencer	stainless steel 316		



		C	E (mm)	F (mm)	ØG (mm)	H (mm)	(kg)
0682 00 10		G1/8	8,0	7,0	14,0	15,0	0,009
0682 00 13		G1/4	8,0	7,0	17,0	15,0	0,013
0682 00 17		G3/8	10,0	8,0	22,0	18,0	0,020
0682 00 21		G1/2	12,0	10,0	27,0	22,0	0,038
0682 00 27		G3/4	15,0	12,0	32,0	27,0	0,066
0682 00 34		G1	18,0	14,0	38,0	32,0	0,118