



Datasheet

ENGLISH

Limit Switch

RS Stock number 902-6941





Description:

Pre-wired, Double insulation, Plastic Casing IP67, 30mm width PVC Cable 4x0.75mm², 1mt length Plain plunger with fixing nuts

Z: Snap action contacts (1NO+1NC)

Specification:

	°C	Devices conform with international IEC 947-5-1 and European EN 60 947-5-1 standards UL (upon request) - IMQ
	°C	
	°C	UL (upon request) - IMQ
	°C	
	٥٥.	
	-	- 25 + 70
	°C	- 40 + 70
		All positions are authorized
ng to IEC 536)		Class II
EN 60 529)		IP 67
Degree of protection (according to UL50)		Type 1 enclosure
		("indoor use only")
		400 V (degree of pollution 3) (250 V for M12 connector)
		B 300, R 300
	Α	10 (4A for M12 connector)
< 40 °C		
	Α	10 (4A for M12 connector
24 V - 50/60 Hz	Α	10 (4A for M12 connector)
240 V - 50/60 Hz	Α	3
24 V - d.c.	Α	2.8
125 V - d.c.	Α	0.22
250 V - d.c.	Α	0.27
Cyc	les/h	3600
		0.5
	$m\Omega$	< 25
		10 Millions of operations
	240 V - 50/60 Hz 24 V - d.c. 125 V - d.c. 250 V - d.c.	EN 60 529) < 40 °C A 24 V - 50/60 Hz A 24 V - 50/60 Hz A 24 V - d.c. A 125 V - d.c. A Cycles/h mΩ

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.