MODULAR JACKS



Specifications / Design Features

• Housing Material: UL 94V-0 rated glass -filled thermoplastic

• Contact Material: Copper Alloy

Contact Plating: Selective gold plating in the contact interface

• Current Rating: 1.5 A (maximum) @ 25° C

Voltage Rating: 150 VAC (maximum)

Description

Stewart Connector single port modular jacks are designed to meet the demanding requirements of high-performance communication environments including the increasing harsh environments that mobile electronics must operate in. Available in a wide verity of height configurations, there is a Stewart single port right angle, vertical, angled jack that will provide the versatility and reliable solution for your networking or mobile applications. All of the Stewart single port modular jacks can be equipped with EPP-918A contact dressing to increase the durability of the contacts to withstand heavy insertions and extractions of the mating plugs and provide increased protection in harsh environments.

How to Order Single Port Right Angle Modular Jacks

| Part Number | Performance | Contacts | Shield | Shield Type | Orientation |
|-------------------|-------------|----------|--------|-------------|-----------------|
| SS-60300-010 | 10G | 8 | Yes | PG4 | Horizonal (90) |
| SS-60300-002 | CAT6a | 8 | Yes | PG4 | Horizontal (90) |
| SS-60300-004 | CAT6a | 8 | Yes | NF | Horizontal (90) |
| SS-60000-009 | CAT6 | 8 | Yes | NF | Horizontal (90) |
| SS-60000-010 | CAT6 | 8 | No | | Horizontal (90) |
| SS-64100-082 | Standard | 10 | Yes | NF | Horizonal (90) |
| SS-641010-NF-A115 | Standard | 10 | No | | Horizontal (90) |
| SS-6488-NF | Standard | 8 | No | | Horizontal (90) |
| SS-6488S-A-NF | Standard | 8 | Yes | NF | Horizontal (90) |
| SS-700810-NF | Standard | 8 | No | | Horizontal (90) |
| SS70100-041F | Standard | 8 | Yes | PG4 | Horizonal (90) |

Custom designs are available on request. Email **techhelp@belf.com** to submit your specific application needs. Data sheets with electrical and mechanical specifications are available at **stewartconnector.com**

Available in a wide verity of height configurations, there is a Stewart single port right angle, vertical, angled jack that will provide the versatility and reliable solution for your networking or mobile application.



MODULAR JACKS



Specifications / Design Features

• Housing Material: UL 94V-0 rated glass -filled thermoplastic

• Contact Material: Copper Alloy

• Contact Plating: Selective gold plating in the contact interface

• Current Rating: 1.5 A (maximum) @ 25° C

Voltage Rating: 150 VAC (maximum)

Description

Stewart Connector single port modular jacks are designed to meet the demanding requirements of high-performance communication environments including the increasing harsh environments that mobile electronics must operate in. Available in a wide verity of height configurations, there is a Stewart single port right angle, vertical, angled jack that will provide the versatility and reliable solution for your networking or mobile applications. All of the Stewart single port modular jacks can be equipped with EPP-918A contact dressing to increase the durability of the contacts to withstand heavy insertions and extractions of the mating plugs and provide increased protection in harsh environments.

How to Order Single Port Vertical / 45 Degree Modular Jacks

| Part Number | Performance | Contacts | Shield | Shield Type | Orientation |
|--------------------|-------------|----------|--------|-------------|----------------|
| SS-60300-014 | CAT6a | 8 | Yes | PG4 | Vertical (180) |
| SS-60300-016 | CAT6a | 8 | Yes | NF | Vertical (180) |
| SS-60300-023 | CAT6a | 8 | Yes | PG4 | Angle (45) |
| SS-60000-007 | CAT6 | 8 | No | | Vertical (180) |
| SS-60000-008 | CAT6 | 8 | Yes | NF | Vertical (180) |
| SS-60000-014 | CAT6 | 8 | No | | Angle (45) |
| SS-71100-001 | CAT5e | 8 | Yes | NF | Angle (45) |
| SS71800-027F | CAT5e | 8 | Yes | NF | Vertical (180) |
| SS-7188V-A-NF | CAT5e | 8 | No | | Vertical (180) |
| SS-650810-A-NF | Standard | 8 | No | | Vertical (180) |
| SS-650810S-A-NF-50 | Standard | 8 | Yes | NF | Vertical (180) |

Custom designs are available on request. Email **techhelp@belf.com** to submit your specific application needs. Data sheets with electrical and mechanical specifications are available at **stewartconnector.com**

Available in a wide verity of height configurations, there is a Stewart single port right angle, vertical, angled jack that will provide the versatility and reliable solution for your networking or mobile application.

+1 717.235.7512 techhelp@belf.com

stewartconnector.com

MODULAR PLUGS



Specifications / Design Features

- Electro-polished contact designs to accommodate solid and stranded conductors
- Performance levels from CAT3 thru CAT6a
- Wire management systems to improve plug assembly and performance
- Available in 4 through 10 position selectively loaded contact configurations
- Numerous keying options available on select models
- Strain relief boots with latch protection available on certain configurations

Description

With an industry leading array of part number configurations available, Stewart Connector has an RJ45 modular plug available for your application. The product family is led by next generation shielded and unshielded CAT6a plugs which have wire management systems to provide reliable patch cord assemblies required in 10GBase-T applications. If you need port density, Stewart Connector offers mod plugs with slim line boots and latch protection to work in today's highest density Gigabit Ethernet devices. In addition, Stewart offers numerous modular plugs with keying for use in proprietary communications systems where plug to jack mate-ability needs to be controlled. Designed to exceed appropriate TIA-568 and IEC 60603-7 mechanical and electrical performance specifications you can count on Stewart Connector's plug to keep your network up and running.

How to Order Modular Plugs

| Part Number | Performance | Contacts | Shield | Conductor Size | Cable Type |
|--------------------|-------------|----------|--------|---------------------------|---------------------------|
| SS-39100-030 | CAT6a | 8 | No | .033"037" (0.84mm-0.94mm) | .235" max (5.97mm max) |
| SS-39200-020 | CAT6a | 8 | Yes | .036"042" (0.91mm-1.07mm) | .220"240" (5.59mm-6.10mm) |
| SS-39100-008 | CAT6 | 8 | No | .036"042" (0.91mm-1.07mm) | .220"230" (5.59mm-5.84mm) |
| SS-39100-021 | CAT6 | 8 | No | .036"042" (0.91mm-1.07mm) | .235" max (5.97mm max) |
| SS-39200-011 | CAT6 | 8 | Yes | .036"042" (0.91mm-1.07mm) | .232"248" (5.89mm-6.30mm) |
| SS-39200-019 | CAT6 | 8 | Yes | .036"042" (0.91mm-1.07mm) | .270"295" (6.86mm-7.49mm) |
| SS-37000-007 | CAT5e | 8 | No | .036"042" (0.91mm-1.07mm) | .235" max (5.97mm max) |
| SS-37200-028 | CAT5e | 8 | Yes | .036"042" (0.91mm-1.07mm) | .235" max (5.97mm max) |
| 940-SP-301010R | Standard | 10 | No | .032"038" (0.81mm-0.97mm) | .235" max (5.97mm max) |
| 940-SP-3088R-A133 | Standard | 8 | No | .034"040" (0.86mm-1.02mm) | .235" max (5.97mm max) |
| 940-SP-360808-A161 | Standard | 8 | Yes | 032"038" (0.81mm-0.97mm) | .180"230" (4.57mm-5.84mm) |

Custom designs are available on request. Email **techhelp@belf.com** to submit your specific application needs. Data sheets with electrical and mechanical specifications are available at **stewartconnector.com**

The product family is led by next generation shielded and unshielded CAT6a plugs which have wire management systems to provide reliable patch cord assemblies required in 10GBase-T applications.

+1 717.235.7512 techhelp@belf.com