


C882/3 Series - Metallised Plastic D Hoods 45°/Top Entry



- Manufactured in ABS, nickel plated over copper.
- Unique compression insert ensures excellent strain relief and reliable screen termination.

Order Code

Series	C883	20000
C882 - 45° Entry		
C883 - Top Entry		
Size		
00000 - 9 way		
10000 - 15 way		
20000 - 25 way		
30000 - 37 way		
40000 - 50 way (Top entry only)		

- Thumbscrews are available.
Part Code:- **JLJ-10S** (4-40 UNC)
- Company logo's available.


Top Entry

Ways	Dim A	Dim B	Dim C	Dim D
9	31.3	35.5	16.3	16.3
15	39.1	38.8	16.3	16.3
25	53.1	42.0	18.0	16.3
37	69.3	46.5	23.0	16.3
50	67.2	47.1	23.9	19.1

45° Entry

Ways	Dim A	Dim B	Dim C	Dim D
9	31.3	37.2	16.3	16.3
15	39.1	40.6	16.3	16.3
25	53.1	44.1	18.0	16.3
37	69.3	45.7	22.4	16.3

C88000 Series - Zinc Die Cast D Hoods Top Entry



Order Code

Series	C88000	204
C88000 - Top entry		
C8842 - 90° entry (25 way only)		
C8852 - Flat cable entry (25 way only)		
Size		
209 - 9 way, 211 - 15 way		
204 - 25 way, 210 - 37 way		
212 - 50 way, 0000 - 25 way (C8842/C8852 only)		

Top Entry	9 & 15 way	25 way	37 & 50 way

90°	Flat Cable

- Exceeds FCC 20780 Class A and B.
- Die cast zinc shell, zinc plated
- Unique compression insert ensures excellent strain relief and reliable screen termination.
- Thumbscrews are available.
Part Code:- **JLJ-10S** (4-40UNC).
- Company logo's available.

Ways	Dim A	Dim B	Dim C	Dim D
9	31.1	37.2	15.7	15.7
15	39.1	40.6	15.7	15.7
25	53.1	39.1	17.5	15.7
37	66.6	45.7	21.9	18.5
50	66.6	45.7	21.9	18.5
90°	53.1	43.6	18.0	16.3
Flat Cable	55.5	45.7	17.5	17.5