

non-metallic accessories

LOCKNUTS, CONDUIT CLIPS, PLASTIC THREAD CONVERTERS, END CAPS, SEALING WASHERS, END SLEEVES



Approvals may be limited to certain products, see approvals on page 44.

Nylon Locknuts



TO FIT THREAD
PA (NYLON) BLACK
PA (NYLON) GREY

Sealing Washers TYPE SWM



TO FIT THREAD
RUBBER FACE SEALING

Conduit Clips TYPE AC

PA (Nylon) 66
construction with integral lid



NOMINAL CONDUIT SIZE mm
PART NUMBER BLACK
PART NUMBER GREY

End Caps TYPE EC

Provide a smooth finish to prevent any damage to cables where the application is not terminated with a fitting.



NOMINAL CONDUIT SIZE mm
PART NUMBER

TO FIT THREAD	PA (NYLON) BLACK	PA (NYLON) GREY	TO FIT THREAD	RUBBER FACE SEALING	NOMINAL CONDUIT SIZE mm	PART NUMBER BLACK	PART NUMBER GREY	NOMINAL CONDUIT SIZE mm	PART NUMBER
M12	-	-	M12	-	10	ACB10	ACG10	-	-
M16	LNPB/M16	LNPG/M16	M16	SWM16	13	ACB13	ACG13	13	ECB13
M20	LNPB/M20	LNPG/M20	M20	SWM20	16	ACB16	ACG16	16	ECB16
M25	LNPB/M25	LNPG/M25	M25	SWM25	17	ACB17	ACG17	17	-
M32	LNPB/M32	LNPG/M32	M32	SWM32	21	ACB21	ACG21	21	ECB21
M40	LNPB/M40	LNPG/M40	M40	SWM40	22	ACB22	ACG22	28	ECB28
M50	LNPB/M50	LNPG/M50	M50	SWM50	28	ACB28	ACG28	34	ECB34
M63	LNPB/M63	LNPG/M63	M63	-	34	ACB34	ACG34	42	ECB42
-	-	-	M75	-	42	ACB42	ACG42	54	ECB54
PG7	LNPB/PG7	LNPG/PG7	PG7	SWPG7	54	ACB54	ACG54	-	-
PG9	LNPB/PG9	LNPG/PG9	PG9	SWPG9	-	-	-	-	-
PG11	LNPB/PG11	LNPG/PG11	PG11	SWPG11	-	-	-	-	-
PG13	LNPB/PG13	LNPG/PG13	PG13.5	SWPG13	-	-	-	-	-
PG16	LNPB/PG16	LNPG/PG16	PG16	SWPG16	-	-	-	-	-
PG21	LNPB/PG21	LNPG/PG21	PG21	SWPG21	-	-	-	-	-
PG29	LNPB/PG29	LNPG/PG29	PG29	SWPG29	-	-	-	-	-
PG36	LNPB/PG36	LNPG/PG36	PG36	SWPG36	-	-	-	-	-
PG42	LNPB/PG42	LNPG/PG42	PG42	SWPG42	-	-	-	-	-
PG48	LNPB/PG48	LNPG/PG48	PG48	SWPG48	-	-	-	-	-

Nylon Thread Convertors



EXTERNAL THREAD
M16
M20
M25

End Sleeves

For sealing cables to non-metallic conduit



NOMINAL CONDUIT SIZE mm
PART NUMBER
OLD PART NUMBER (SHOWN IN PRICE LIST)

EXTERNAL THREAD	M16	M20	M25	NOMINAL CONDUIT SIZE mm	PART NUMBER	OLD PART NUMBER (SHOWN IN PRICE LIST)
M20	P/M20-M16/R	-	-	13	ESN12	GZ9
M25	-	P/M25-M20/R	-	16	ESN16	GZ11
PG9	P/PG9-M16/TC	-	-	21	ESN20	GZ13
PG11	P/PG11-M16/TC	-	-	28	ESN28	GZ21
PG13	P/PG13-M16/TC	-	-	34	ESN32	GZ29
PG16	P/PG16-M16/TC	P/PG16-M20/TC	-	42	ESN40	GZ36
PG21	-	-	P/PG21-M25/TC	-	-	-