

ARCA 405021



Sample photo

Order symbol: ARCA 405021
Product nbr: 8120025
Description: Cabinet, PC
Remarks: Grey cover, 2-point locking, hinges on the short side

EAN: 6418074079367
EI. number:
 Finland: 3423123
 Denmark: 8212091236
 Sweden: 2500115
 Norway:

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key.
 S versions with swinghandle 3-point locking system. F versions with flange opening. Door guide included.

Dimensions:		Length	Width	Height	Rating:
mm:		400	500	210	Ingress Protection (EN 60529): IP 66
inch:		15.7	19.7	8.3	Impact Resistance (EN 62262): IK 10 +35°C /IK 08 -25°C
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:		PUR			Certificates:
Temperatures:					Fimko
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
MPS ARCA 5040		Mounting plate			
MPP ARCA 5040		Mounting plate perforated			
MPX ARCA 5040		Mounting plate			
DRS ARCA 405021		DIN rail frame set			
PMK ARCA 50		Pole mounting kit			

ARCA 500x400x210

ARCA 400x500x210

