



RoHS

**SPECIFICATION:**

- 1) RATING: 6A 250V A.C
- 2) CONTACT RESISTANCE : 200M Ohm MAX  
NOTE: DIMENSION OF THE DUMMY FUSE FOR TESTIG THE CONTACT RESISTANCE.  
DIA 5.2 X 20±0.5MM (MATERIAL : BRASS )
- 3) INSULATION RESISTANCE: 500M Ohm MIN
- 4) INSULATION WITHSTAND VOLTAGE: A.C. 50HZ 2000V FOR ONE MINUTE.
- 5) Dia 5 x 18mm & Dia 5 x 20mm
- 6) APPEARANCE: NON-ACCEPTANCE OF NOTICEABLE SCRATCHES,  
DIRTY MARK AND BREAKAGE
- 7) SOLDERING HEAT: METHOD OF TEST: JIS C0050  
SOLDERING TEMPERATURE: 350±10 C  
SOLDERING TIME: 5±1 SECONDS  
APPEARANCE IS NOT DEFORMED
- 8) MODEL PHENOLIC, BRONZE, BRASS SHEETS.

		<b>PROFUSE</b>	
		TITLE: FUSE HOLDER FOR 5X20MM FUSE	CAT NO: ZH-24-H
MATERIAL:	PA66 101	FINISH AND COLOR:	BLACK
UNIT:	SCALE:	TOLERANCE:	QTY:
DRAWN:	APPR.: 07 DEC,2007	DRG. NO.:	CHECKED: