

VELCRO® Brand

Textile Hook and Loop Tapes



WOVEN HOOKS & MUSHROOMS • WOVEN, KNITTED & NONWOVEN LOOPS



METHODS OF ATTACHMENT



Pressure sensitive adhesives
(See VELCRO® Brand Adhesives Range)




Sewing




Mechanical



Heat or solvent activated adhesives
(See VELCRO® Brand Adhesives Range)




Welding



Mold-in

FABRICATION



Slitting



Scored cut



Custom manufactured straps



Pre-cut



Mated



Complete product assembly




Die cut




Perforated


PRINTING




Flexography



Hot stamping



Pad printing



Heat transfer

PACKAGING




Rolls



Sealed bag



Bundling



Spools



Blister



Bulk



Shipping boxes



Folding boxes



Customised packaging



Labels

APPLICATIONS



APPAREL



CONSTRUCTION



MEDICAL



MILITARY &
GOVERNMENT



PACKAGING



PERSONAL
CARE



TRANSPORTATION




INDUSTRIAL



SPECIALTIES




VELCRO® Brand
Hook Tapes

WOVEN HOOK TAPES CONSIST OF MINUTE, FLEXIBLE HOOKS OR MUSHROOMS WHICH ENGAGE WITH A MATING WOVEN, KNITTED OR NONWOVEN LOOP TAPE COMPRISED OF SMALL, SOFT LOOPS OR YARNS



 **WOVEN HOOKS**

 **WOVEN MUSHROOMS**

CHARACTERISTICS	Hook 088 *	Hook MTT *****	Hook PSI *****	Hook 066 HI-AIR® *	Hook 081 Polyester *	VEL-LOC® 085 *	SUPER VEL-LOC® 083 *	SUPER VEL-LOC® Quadrilobal *
SUGGESTED MATING COMPONENTS	Loop 001	Loop MTT	Loop PSI	Loop 003 HI-AIR®	Loop 9000 Polyester	Velour 3165	Loop 001	Loop 001
BASE MATERIAL	Polyamide	Polyamide	Polyamide	Polyamide NOMEX® fibers ¹	Polyester	Polyester Polypropylene	Polyester Polypropylene	Polyester Polypropylene
CONSTRUCTION	Heavy duty hook tape	Woven edges	Woven edges	Woven edges	Woven	Mushroom hook	High density mushroom hook	Agressive "arrow head" mushroom hook
 CYCLE LIFE	High	High	High	Medium	Medium	Low	Low	Low
 PEEL STRENGTH (AVERAGE)	2 N/cm	1.1 N/cm ***	**	0.9 N/cm ****	0.9 N/cm ****	2 N/cm	7 N/cm	24 N/cm
 SHEAR STRENGTH (AVERAGE)	10.3 N/cm ²	8 N/cm ² ***	**	-	5.5 N/cm ² ****	20 N/cm ²	70 N/cm ²	115 N/cm ²
BREAKING STRENGTH (MINIMUM)	210 N/cm	-	**	-	-	220 N/cm	350 N/cm	Min. 300 N/cm
STANDARD COLOURS	20 colours	Black, white	Black, white, nato green, navy blue, royal blue, coyote, sable (desert)	Natural	Black, white, camouflage green	10 colours	Black, white, beige, grey	Black, white
STANDARD WIDTHS (mm)	16,20,25 30,38,50 100,107 150	16, 20, 25, 30, 38, 50, 105	16, 20, 25, 30, 38, 50, 105	25.4mm (1") 50.8mm (2")	25.4mm (1") 50.8mm (2") 101.6mm (4")	16, 20, 25, 30, 38, 50, 100, 125, 160, 190	16, 20, 30, 50, 100	Max. 111
STANDARD PUT-UPS	25m rolls	25m rolls	25m rolls	45.72m (50 yd) rolls	45.72m (50 yd) rolls	25m rolls	25m rolls	25m rolls
	Consumer boxes					Consumer boxes		
	Spools					Spools		




* Available with Fire Resistance Treatment or F.R.T (meets FAR 25853 (vertical test 12 sec.) and FMVSS302).
 ** Meets military requirements established by the French Army standard (Brochure GP/EM/TC 5508).
 *** Minimum value reference to 25mm tape for other widths please request information.
 **** Minimum value reference.
 ***** Infrared treatments available upon request.

VELCRO® Brand
Loop Tapes

A DIVERSITY OF WOVEN, KNITTED OR NONWOVEN LOOP TAPES ARE AVAILABLE TO MEET DIFFERENT PERFORMANCE CHARACTERISTICS WHEN COMBINED WITH WOVEN OR PLASTIC HOOK TAPES



 **WOVEN LOOPS**

CHARACTERISTICS	Loop 001*	Loop Pre-shrunk	Loop 002	Loop PSI*****	Loop MTT*****	Loop 003 HI-AIR®*	Loop 9000 Polyester*	VELSTRETCH®
SUGGESTED MATING COMPONENTS	Hook 088	Hook 088	Hook PSI	Hook PSI	Hook MTT	Hook 066 HI-AIR®	Hook 081 Polyester	Hook 065
BASE MATERIAL	Polyamide	Polyamide	Polyester Polyamide	Polyamide	Polyamide	Polyamide NOMEX® fibers ¹	Polyester	Polyamide Elastane
CONSTRUCTION	Napped finish	Napped pre-shrunk	Unnapped finish Woven edges	Unnapped finish Woven edges	Unnapped finish Woven edges	Unnapped finish Woven edges	Unnapped finish	Woven elastic
 CYCLE LIFE	High	High	High	High	High	Medium	Medium	Medium
 PEEL STRENGTH (AVERAGE)	2 N/cm	2 N/cm	0.9 N/cm	**	1.1 N/cm ***	0.9 N/cm ****	0.9 N/cm ****	-
 SHEAR STRENGTH (AVERAGE)	10.3 N/cm ²	10.3 N/cm ²	12 N/cm ²	**	8 N/cm ² ***	-	5.5 N/cm ² ****	3.1 N/cm ² ****
BREAKING STRENGTH (MINIMUM)	210 N/cm	210 N/cm	-	**	-	-	-	315 N/cm
STANDARD COLOURS	20 colours	White	Royal blue, white, grey, red, green, yellow	Black, white, nato green, navy blue, royal blue, coyote, sable (desert)	Black, white	Natural	Black, white, camouflage green	Black, white, beige, navy blue, raw
STANDARD WIDTHS (mm)	16, 20, 25, 30, 38, 50, 100, 107, 150	20, 100	105	16, 20, 25, 30, 38, 50, 105	16, 20, 25, 30, 38, 50, 105	25.4mm (1") 50.8mm (2")	25.4mm (1") 50.8mm (2") 101.6mm (4")	15.88mm (5/8") 19.01mm (3/4") 25.4mm (1") 38.1mm (1-1/2") 50.8mm (2")
STANDARD PUT-UPS	25m rolls Consumer boxes Spools	25m rolls	100m rolls	25m rolls	25m rolls	45.72m (50 yd) rolls	45.72m (50 yd) rolls	36.58m (40 yd) rolls

¹ NOMEX® is a reg. tm of E.I. du Pont de Nemours and Company.

TYPES OF CLOSURES



Woven hook & woven loop



Woven mushroom & knitted loop



Plastic hook & nonwoven loop

KNITTED LOOPS

NONWOVEN LOOPS

Velour 401		Velour 3165 standard		Velour 3894 light		Velour 3969		Velour 3200		FNL 264	FNL 403
Hook 088		VEL-LOC® 085		VEL-LOC® 085		VEL-LOC® 085		VEL-LOC® 085		Hook 819	Hook 847
Polyamide		Polyamide		Polyamide		Polyamide		Polyester		Polypropylene Polyester	Polypropylene
Wrap knit Napped finish High pile		Wrap knit Napped finish Low pile		Wrap knit Napped finish Low pile		Wrap knit Napped finish Low pile		Wrap knit Light weight Ideal for disposable products		Nonwoven	Nonwoven
Medium		Low		Low		Low		Low		Low	Low
1.8 N/cm		1.5 N/cm		1 N/cm		0.8 N/cm		2 N/cm		1.6 N/cm	1.7 N/cm
3 N/cm ²		16 N/cm ²		15 N/cm ²		13 N/cm ²		15 N/cm ²		12.1 N/cm ²	8.1 N/cm ²
80 N/cm		55 N/cm		65 N/cm		65 N/cm		25 N/cm		-	-
Black, white, raw, grey		10 colours		Black, white, beige, grey		Black, white		White		White	White
16, 20, 25, 30, 38, 50, 100, 125	1500	16, 20, 25, 30, 38, 50, 100, 125	1400	16, 20, 25, 30, 38, 50, 100, 125	1400	16, 20, 25, 30, 38, 50, 100, 125	1400	20, 25, 30, 40, 50, 70, 100	1500	101.6mm (4") 3,048mm (120")	101.6mm (4") 3,048mm (120")
25m rolls	25m rolls	25m rolls	51m rolls	25m rolls	51m rolls	25m rolls	51m rolls	50m rolls	51m rolls	3,600m rolls	3,600m rolls

NOTE: All data in this catalog is for reference only. Please contact us for more information.



Velcro Companies is a technology-driven, global organization providing fastening solutions that solve problems in simple, elegant and surprising ways for businesses and consumers around the world. We have a heritage of innovation spanning more than 60 years and own over 400 active patents and numerous trademarks, including the VELCRO® trademark, which is registered throughout the world. We develop and deliver solutions for customers through an integrated production and service system that includes manufacturing locations in the United States, Belgium, Canada, Mexico, Uruguay, Spain and China and sales offices around the world.

To buy genuine VELCRO® Brand products and to find out more about our company, visit Velcro.com



GLOBAL OFFICES

Global Corporate Headquarters

Velcro USA Inc.
95 Sundial Avenue
Manchester, NH 03103
USA
Tel: (+1) 800 225 0180
marketing@velcro.com
Velcro.com

NAM

USA

Velcro USA Inc.
Tel: (+1) 800 225 0180
marketing@velcro.com
Velcro.com

Canada

Velcro Canada Inc.
Tel: (+1) 800 683 5276
canada@velcro.com
Velcro.com

LATAM

Mexico

Velcro de México, S.A. de C.V.

Tlalnepantla de Baz,
Edo. de México
Tel: (+52) 55 5005 3300
infovdmex@velcro.com
Velcrodemexico.com

León, Gto
Tel: (+52) 477 980 0630
infovdmex@velcro.com
Velcrodemexico.com

Brazil

Velcro Brasil Importação,
Exportação e Comércio de
Sistemas de Fixação Ltda.

Campo Bom, RS
Tel: (+55) 51 3599 1483
infovbra@velcro.com
Velcro.com.br

Sumaré, SP
Tel: (+55) 11 3197 2588
infovbra@velcro.com
Velcro.com.br

Uruguay

Velcro Industrial
del Uruguay S.A.
Tel: (+598) 2288 0008
infovurg@velcro.com
Velcro.com

EMEA

Spain

Velcro Europe S.A.
Tel: (+34) 93 758 32 98
infovesa@velcro.com
Velcro.es

Germany

Velcro GmbH

Freiberg am Neckar
Tel: (+49) 7141 991 19-0
infovgmbh@velcro.com
Velcro.de

Gronau
Tel: (+49) 2562 96 45-0
infovgmbh@velcro.com
Velcro.de

France

Velcro Industries France S.A.S.
Tel: (+33) 1 34 38 78 88
infovif@velcro.com
Velcro.fr

Belgium

Alfatex N.V.
Tel: (+32) 9 386 12 18
infofbe@velcro.com
Velcro.be

Italy

Velcro Italia, S.R.L.
Tel: (+39) 039 62 70 01
infoveit@velcro.com
Velcro.it

UK

Velcro Ltd.
Tel: (+44) 1606 738 806
infov ltd@velcro.com
Velcro.co.uk

Poland

Velcro Poland Sp. z o.o.
Tel: (+48) 71 798 57 89
infovpl@velcro.com
Velcro.pl

APAC

Australia

Velcro Australia Pty. Ltd.
Tel: (+61) 3 9703 2466
infovaus@velcro.com
Velcro.com.au

China

Velcro China Fastening
Systems Company Limited
Tel: (+86) 512 8164 5888
infovch@velcro.com
Velcro.com.cn

Hong Kong

Velcro Hong Kong Ltd.
Tel: (+852) 2570 3698
infovhk@velcro.com
Velcro.com.hk

Vietnam

Velcro Vietnam Company Limited
Tel: (+84) 274 2222 497
infovvn@velcro.com
Velcro.com

VELCRO COMPANIES AROUND THE WORLD

