

# GRM1557U1A182JA01#

“#” indicates a package specification code.



< List of part numbers with package codes >

GRM1557U1A182JA01J

GRM1557U1A182JA01W

GRM1557U1A182JA01D

## Appearance & Shape



## References

Packaging	Specifications	Standard Packing Quantity
J	330mm Paper Tape	50000
W	180mm Paper Tape (W8P1)	20000
D	180mm Paper Tape	10000

Mass (typ.)	
1 piece	1.6mg
φ180mm Reel	118g

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GRM1557U1A182JA01#

“#” indicates a package specification code.



## Specifications

Length	1.0±0.05mm
Width	0.5±0.05mm
Thickness	0.5±0.05mm
Capacitance	1800pF ±5%
Distance between external terminals g	0.3mm min.
External terminal size e	0.15 to 0.35mm
Operating Temperature Range	-55°C to 125°C
Rated Voltage	10Vdc
Size code in inch(mm)	0402 (1005M)
TC	-750±120ppm/°C
Temperature characteristics (complied standard)	U2J(EIA)
Temperature range of temperature characteristics	25°C to 85°C

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GRM1557U1A182JA01#


“#” indicates a package specification code.

## Characteristic Data


The charts below may show another part number which shares its characteristics.




■ GRM1557U1A182JA01 |Z| DCOV, 25degC



■ GRM1557U1A182JA01 R DCOV, 25degC



■ GRM1557U1A182JA01 C-DC bias capchange, 25.0degC, AC1V




■ GRM1557U1A182JA01 C-AC Voltage capchange, DCOV, 25.0d

**Attention**


- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GRM1557U1A182JA01#

“#” indicates a package specification code.



■ GRM1557U1A182JA01 C-Temp. capchange, DCOV, AC1Vrms



■ GRM1557U1A182JA01 S21 DCOV, 25degC

**Attention**

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.