



## -1. Wrenches

### -1.1. ADJUSTABLE WRENCHES

- Standards: ISO 6787, DIN 3117, BS 6333, ASME B107.8M – 1996
- High performance alloy steel
- Head angle 15° for the 31 model provides better accessibility
- Head angle 22.5° for the 86 and 87 models provides better accessibility
- Left going screw
- Phosphated. Precision-hardened and anti-corrosion treated
- IP: Industrial pack

### 80 series

31/86/87

			A mm	B mm	C mm	D mm	
31	7314150004942	5	205	32	5.5	13.5	270
31 IP	7314150004959	50	205	32	5.5	13.5	270
31 R US	7314150114665	5	205	32	5.5	13.5	270
86	7314150005376	1	614	63	27.5	29.0	3165
87	7314150005406	1	770	85	31.0	33.0	5700

