

stay connected

SVS valve form A 18mm field-wireable Replaced Art.-No. 3129020

Form A (18 mm) $24\,\text{V AC/DC with LED and Z-diode} \\ PG\,9$

Image



Vicarious picture

Form	
	29021
Technical Data	
Operating voltage	24 V AC ±20 % / DC ±25 %
Operating current per contact	max. 4 A
Switch off peak	max. 55 V
Max. power (W)	max. 100 W(VA)
Connection cross section	4 mm² single core, with ferrule end 1.5 mm²
Sealing range (cable diameter)	68 mm
Locking of ports	M3 (recommended torque 0.4 Nm)
Compression gland	PG 9; (PG11, NPT 1/2" on request)
Protection	IP65 inserted and tightened (EN 60529), with gland
Temperature range	-20+60 °C
Commercial data	
Net weight	30
Weight unit	Gram
Basic unit	рс.
Customs tariff number	85369010
Unit (piece)	1
Minimum order quantity (piece)	1
Comments	


Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.




stay connected


Contact layout



Circuit diagram



Dimension drawing



Height: 41 mm