

JST

Hand crimping tool
Type: JUCS-6.3

Features

Parallel action
operation

Ratchet release

Easy readjustment
of load

Contact locator with
insulation-stop

Precisely ground
profiles

Ergonomic soft grips
colour: green

Fully recyclable

Applicable terminal:
LTD-1.0T-250N Profile 1
LTD-2.5T-250N Profile 2


Cross section range:
Profile 1: 0.5-1.0mm²
Profile 2: 1.0-2.5mm²

Crimp heights:
Profile 1: 1.5mm +0.1/-0.05
Profile 2: 1.82mm +0.1/-0.05

Operating instructions see overleaf

OPERATING INSRUCTIONS


1. INSERT CONTACT
-IMPORTANT-
Lightly push contacts
against stop whilst
inserting the wire
to ensure correct
terminal location.



2. CLOSE THE JAWS
ONTO THE TERMINAL.

3. INSERT WIRE INTO
THE CONTACT.

4. SQUEEZE HANDLES
UNTIL AUTOMATIC
RATCHET RELEASES.



5. TAKE CARE WHEN
YOU REMOVE THE
CONTACT FROM
THE DIE.

