

## ROUND TYPE LED BULB, VOLTAGE 12V TO 85V AC/DC, BASE TYPE E27, WARM WHITE



**SEEIT**  
Leds lighting

Power Supply  
Tension d'alimentation

12V       DC  
 24V       AC  
 12V to 85V       AC/DC

**Ne pas utiliser sur le secteur 230Vac !  
Please don't use in 230Vac !**

### AMP0031 / AMP0032 / AMP0033 / AMP0034

#### Introduction:

This range of LED light bulb equipped with E27 base type (diameter 27mm) works with DC or AC power supply of low voltage in 12Vdc or 24Vdc and until 85V maximum. This range of LED light bulb doesn't work in 110Vac or 230Vac! Those LED light bulb are the ideal solution to illuminate your exteriors, exterior gate, water tower (moisture environment), isolated cottage, garden shelter, garden terrace, garage access, technical area, or to operate with a photovoltaic installation. Round in shape, with a 120° light reflecting dome, these bulbs will fit perfectly in your living space for optimum lighting and a color temperature of 3000°K. Several lighting powers consumption are available: 3W (240 lm), 6W (480 lm), 9W (720 lm) and 12W (960 lm) for a low consumption combined with high luminosity. Those LED light bulbs do not emit UV or IR radiation. The lighting is instantaneous and the power stable even for long-time use. Manufactured with a high-quality base in aluminium material covered with insulating plastic for optimum heat dissipation and an extended lifetime of up to 40000 hours.

#### Hardware & Electrical specifications:

Reference	AMP0031	AMP0032	AMP0033	AMP0034
Power	3W	6W	9W	12W
Luminous	240 lm	480 lm	720 lm	960 lm
T° of color	3000 °K	3000°K	3000 °K	3000 °K
Color	Warm White	Warm White	Warm White	Warm White
Voltage min	12V AC/DC	12V AC/DC	12V AC/DC	12V AC/DC
Voltage max	85V AC/DC	85V AC/DC	85V AC/DC	85V AC/DC
Current	80 mA	210 mA	280 mA	370 mA
Technology	Epistar LED SMD	Epistar LED SMD	Epistar LED SMD	Epistar LED SMD
Beam angle	120°	120°	120°	120°
Lifetime max	40.000 h	40.000 h	40.000 h	40.000 h
Bulb style	Round	Round	Round	Round
Base type	E27	E27	E27	E27
Height	90 mm	115 mm	120 mm	130 mm
Diameter	50 mm	60 mm	65 mm	70 mm
Material	Plastic / Alu	Plastic / Alu	Plastic / Alu	Plastic / Alu
Certification	CE / RoHS	CE / RoHS	CE / RoHS	CE / RoHS



#### Item include:

1 LED light bulb.  
 Dimensions package 3W/6W : 50 x 50 x 90 mm. Weight : 30g.  
 Dimensions package 9W/12W : 60 x 60 x 105 mm. Weight : 35g.

