

**UNIVERSAL PROGRAMMER, 48 PINS ZIF SOCKET, USB PORT  
FOR PROMs, EPROMs, EEPROMs, NANDs, FLASHs, PLDs, MICROCONTROLLERS**

**Support over 20.000 devices**



# TOPMAX-III



## Introduction:

The TOPMAX-III is the new version of the universal programmer TOPMAX. It allows you to program memory with a speed up to 2.5 Mb/second thanks to its connection on USB 2.0 port, and its integrated processor allows it to load files directly in its memory. It permits programming of the most recent devices, including PROMs, EPROMs, EEPROMs, Flash Memory, FPGAs, PALs, GALs, EPLDs and microcontrollers. Its ZIF socket is equipped with 48 pins entirely and independently parametrizable enabling it to program all the 6 to 48-pin devices without having to add any supplementary adapter. It also automatically detects defective device pins. Sockets can be added if the chip to be programmed is not in a DIP package, such as PLCC, LCC, TSOP, PSOP, SOP, QFP, TQFP,  $\mu$ BGA, FBGA, etc... TOPMAX-III's software can handle over 20,000 device references and can also be used with 8 programmers simultaneously for production programming. Moreover, an « Auto function » key has been added to the programmer to immediately start programming a device. The TOPMAX-III supports devices in 1.8V / 2.0V / 2.5V / 2.7V / 3.0V / 3.3V / 5.0V. An IEEE-1149.1 compliant JTAG connector is also provided with this universal programmer. Works with MaxLoader software for Windows Win7/Win8/Win10/Win11 (32/64bits).

## Features:

Accept standard file formats (POF and JEDEC, INTEL (Extended) HEX, Motorola S-Records, Tekhex, Straight Hex, Hex-Space, Extended TekHex. Manages 16 and 32 bit word split (Set Programming).  
Test TTL/CMOS logic ICs and Dynamic/Static Random Access Memory devices.  
Automatically identifies the manufacturer and type of E(E)PROMs, auto identifies TTL/CMOS logic IC.  
Device insertion test and poor pin contact check.  
Support low-voltage devices down to 1,8V.  
Production mode function with "Start" button on the box of the programmer.  
Device operations : Read, Blank Check, Program, Verify, Checksum, Data compare, Security. Option bit program.  
Universal adapters DIP, PLCC, QFP, TSOP, PSOP, SOIC, SSOP, SDIP, etc...  
Run under Windows Windows 7 / Windows8 / Windows10 / Windows11 (32bits and 64bits).

## Hardware & Electrical specifications:

Dimensions product : 140 x 207 x 42mm. Weight : 1030g  
Dimensions package : 235 x 145 x 105mm. Weight : 1680g  
Power supply : CEE connector AC 100V à 240V, 50Hz/60Hz.  
Interface : USB1.0 / 2.0 / 3.0 port.  
Support : ZIF48 pin-drivers, (support 8 pins to 48 pins DIP package).

## Item includes :

Programmer with 48 pins ZIF socket.  
Power cord, (input power 110V-240Vac 50Hz-60Hz).  
USB-B to USB-A cable.  
Software on CD.  
User manual in English and French.



**Products informations : [www.seeit.fr](http://www.seeit.fr)**

↓ **Devices list programmed below** ↓



**DEVICES LIST TOPMAX-III**

(Universal programmer with ZIF48 pins drivers)

Push "CTRL + F" keys to find a component

Universal programmer TopMax-III  
 Total devices : 20303  
 Version : 6.2i

Manufacturers	Devices	Packages	Adapters
ADESTO	AT25DF011	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ADESTO	AT25DF011	TSSOP8	PA8TSS8D
ADESTO	AT25DF011	USON8	PA8SON8D(2x3)
ADESTO	AT25DF021	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ADESTO	AT25DF021	UDFN8	PA8SON8D(6x5)
ADESTO	AT25DF021A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ADESTO	AT25DF021A	TSSOP8	PA8TSS8D
ADESTO	AT25DF021A	UDFN8	PA8SON8D(6x5)
ADESTO	AT25DF021A	USON8	PA8SON8D(2x3)
ADESTO	AT25DF041A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ADESTO	AT25DF041A	SOIC8	PA20SO20D-EO-210
ADESTO	AT25DF041A	UDFN8	PA8SON8D(6x5)
ADESTO	AT25DF041B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ADESTO	AT25DF041B	TSSOP8	PA8TSS8D
ADESTO	AT25DF041B	UDFN8	PA8SON8D(6x5)
ADESTO	AT25DF041B	USON8	PA8SON8D(2x3)
ADESTO	AT25DF081	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ADESTO	AT25DF081	SOIC8	PA20SO20D-EO-210
ADESTO	AT25DF081	UDFN8	PA8SON8D(6x5)
ADESTO	AT25DF081A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ADESTO	AT25DF081A	SOIC8	PA20SO20D-EO-210
ADESTO	AT25DF081A	UDFN8	PA8SON8D(6x5)
ADESTO	AT25DF161	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ADESTO	AT25DF161	SOIC8	PA20SO20D-EO-210
ADESTO	AT25DF161	UDFN8	PA8SON8D(6x5)
ADESTO	AT25DF256	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ADESTO	AT25DF256	TSSOP8	PA8TSS8D
ADESTO	AT25DF256	USON8	PA8SON8D(2x3)
ADESTO	AT25DF321A	SOIC8	PA20SO20D-EO-210
ADESTO	AT25DF321A	UDFN8	PA8SON8D(6x5)
ADESTO	AT25DF512C	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ADESTO	AT25DF512C	TSSOP8	PA8TSS8D
ADESTO	AT25DF512C	USON8	PA8SON8D(2x3)
ADESTO	AT25DF641	SOIC16	PA28SO28D-EO-300
ADESTO	AT25DF641	VDFN8	PA8SON8DA(8x6)
ADESTO	AT25DF641A	SOIC8	PA20SO20D-EO-210
ADESTO	AT25DF641A	UDFN8	PA8SON8D(6x5)
ADESTO	AT25DN011	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ADESTO	AT25DN011	TSSOP8	PA8TSS8D
ADESTO	AT25DN011	USON8	PA8SON8D(2x3)
ADESTO	AT25DN256	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ADESTO	AT25DN256	TSSOP8	PA8TSS8D
ADESTO	AT25DN256	USON8	PA8SON8D(2x3)
ADESTO	AT25DN512C	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ADESTO	AT25DN512C	TSSOP8	PA8TSS8D
ADESTO	AT25DN512C	USON8	PA8SON8D(2x3)
ADESTO	AT26DF081A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ADESTO	AT26DF081A	SOIC8	PA20SO20D-EO-210
ADESTO	AT45DB041E	SOIC8	PA16SO16D-EO-150
ADESTO	AT45DB041E	SOIC8	PA20SO20D-EO-210
ADESTO	AT45DB641E	SOIC8	PA20SO20D-EO-210
ADESTO	AT45DB641E	UDFN8	PA8SON8D(6x5)
Ali	M6759	PLCC44	PA44-48U
ALLIANCE	AS29F010	DIP32	
ALLIANCE	AS29F010	PLCC32	PA32PL32D
ALLIANCE	AS29F010	TSOP32	PA32TS20/PA32TS32D-20
ALLIANCE	AS29F040	DIP32	
ALLIANCE	AS29F040	PLCC32	PA32PL32D
ALLIANCE	AS29F040	TSOP32	PA32TS20/PA32TS32D-20
ALLIANCE	AS29F200B	SOP44	PA44SO44D
ALLIANCE	AS29F200B	TSOP48	PA48TS48D
ALLIANCE	AS29F200T	SOP44	PA44SO44D
ALLIANCE	AS29F200T	TSOP48	PA48TS48D

ALLIANCE	AS29LV400B	SOP44	PA44SO44D
ALLIANCE	AS29LV400B	TSOP48	PA48TS48D
ALLIANCE	AS29LV400T	SOP44	PA44SO44D
ALLIANCE	AS29LV400T	TSOP48	PA48TS48D
ALLIANCE	AS29LV800B	SOP44	PA44SO44D
ALLIANCE	AS29LV800B	TSOP48	PA48TS48D
ALLIANCE	AS29LV800T	SOP44	PA44SO44D
ALLIANCE	AS29LV800T	TSOP48	PA48TS48D
ALTERA	EP1800	PLCC68	PA-EP1800
ALTERA	EP1810	PLCC68	PA-EP1800
ALTERA	EP1830	PLCC68	PA-EP1800
ALTERA	EP310	DIP20	
ALTERA	EP310	PLCC20	PA20LC20D[Dead Bug]
ALTERA	EP310I	DIP20	
ALTERA	EP310I	PLCC20	PA20LC20D[Dead Bug]
ALTERA	EP312	DIP24	
ALTERA	EP312	PLCC28	PA28PL24D7P6-YA
ALTERA	EP320	DIP20	
ALTERA	EP320	PLCC20	PA20LC20D[Dead Bug]
ALTERA	EP320I	DIP20	
ALTERA	EP320I	PLCC20	PA20LC20D[Dead Bug]
ALTERA	EP330	DIP20	
ALTERA	EP330	PLCC20	PA20LC20D[Dead Bug]
ALTERA	EP330I	DIP20	
ALTERA	EP330I	PLCC20	PA20LC20D[Dead Bug]
ALTERA	EP600	DIP24	
ALTERA	EP600	PLCC28	PA28PL24D7P6-YA
ALTERA	EP600	SOIC24	PA28SO28D-EO-300
ALTERA	EP600I	DIP24	
ALTERA	EP600I	PLCC28	PA28PL24D7P6-YA
ALTERA	EP600I	SOIC24	PA28SO28D-EO-300
ALTERA	EP610	DIP24	
ALTERA	EP610	PLCC28	PA28PL24D7P6-YA
ALTERA	EP610	SOIC24	PA28SO28D-EO-300
ALTERA	EP610I	DIP24	
ALTERA	EP610I	PLCC28	PA28PL24D7P6-YA
ALTERA	EP610I	SOIC24	PA28SO28D-EO-300
ALTERA	EP900	DIP40	
ALTERA	EP900	PLCC44	PA44-48U
ALTERA	EP900	PLCC44	PA900-44
ALTERA	EP900I	DIP40	
ALTERA	EP900I	PLCC44	PA44-48U
ALTERA	EP900I	PLCC44	PA900-44
ALTERA	EP910	DIP40	
ALTERA	EP910	PLCC44	PA44-48U
ALTERA	EP910	PLCC44	PA900-44
ALTERA	EP910A	DIP40	
ALTERA	EP910A	PLCC44	PA44-48U
ALTERA	EP910A	PLCC44	PA900-44
ALTERA	EP910I	DIP40	
ALTERA	EP910I	PLCC44	PA44-48U
ALTERA	EP910I	PLCC44	PA900-44
ALTERA	EPC1	DIP8	
ALTERA	EPC1	PLCC20	PA20LC20D[Dead Bug]
ALTERA	EPC1064	DIP8	
ALTERA	EPC1213	DIP8	
ALTERA	EPC1441	DIP8	
ALTERA	EPC1441	PLCC20	PA20LC20D[Dead Bug]
ALTERA	EPC1441	TQFP32	PA32TQ32D-YC
ALTERA	EPC2	PLCC20	PA20LC20D[Dead Bug]
ALTERA	EPC2	TQFP32	PA32TQ32D
ALTERA	EPM3032A	PLCC44	PA44-48U
ALTERA	EPM3032A	TQFP44	PA44QF44D
ALTERA	EPM3064A	PLCC44	PA44-48U
ALTERA	EPM3064A	TQFP100	PA100TQ48D
ALTERA	EPM3064A	TQFP44	PA44QF44D
ALTERA	EPM3064A	TQFP100	PA100TQ48D
ALTERA	EPM3128A	TQFP100	PA100QF48DF
ALTERA	EPM570	TQFP100	PA100QF48DF
ALTERA	EPM7032	PLCC44	PA44-48U
ALTERA	EPM7032AE	PLCC44	PA44-48U
ALTERA	EPM7032AE	TQFP44	PA44VQ44D
ALTERA	EPM7032AEas7032	PLCC44	PA44-48U
ALTERA	EPM7032AEas7032	TQFP44	PA44VQ44D

ALTERA	EPM7032AEas7032S	PLCC44	PA44-48U
ALTERA	EPM7032AEas7032S	TQFP44	PA44VQ44D
ALTERA	EPM7032S	PLCC44	PA44-48U
ALTERA	EPM7032S	TQFP44	PA44VQ44D
ALTERA	EPM7032Sas7032	PLCC44	PA44-48U
ALTERA	EPM7032Sas7032	TQFP44	PA44VQ44D
ALTERA	EPM7032V	PLCC44	PA44-48U
ALTERA	EPM7064	PLCC44	PA44-40F
ALTERA	EPM7064	PLCC44	PA44-48U
ALTERA	EPM7064	PLCC68	PA68-40A
ALTERA	EPM7064	PLCC68	PA7064/96-68LC
ALTERA	EPM7064	PLCC84	PA7064/96-84LC
ALTERA	EPM7064	PLCC84	PA84-40A
ALTERA	EPM7064AE	PLCC44	PA44-48U
ALTERA	EPM7064AE	TQFP44	PA44QF44D
ALTERA	EPM7064AEas7064	PLCC44	PA44-48U
ALTERA	EPM7064AEas7064	TQFP44	PA44QF44D
ALTERA	EPM7064AEas7064S	PLCC44	PA44-48U
ALTERA	EPM7064AEas7064S	TQFP44	PA44QF44D
ALTERA	EPM7064S	PLCC44	PA44-48U
ALTERA	EPM7064S	PLCC68	PA7064/96-68LC
ALTERA	EPM7064S	PLCC84	PA7064/96-84LC
ALTERA	EPM7064S	TQFP100	PA100TQ48DB
ALTERA	EPM7064S	TQFP44	PA44QF44D
ALTERA	EPM7064Sas7064	PLCC44	PA44-48U
ALTERA	EPM7064Sas7064	PLCC68	PA7064/96-68LC
ALTERA	EPM7064Sas7064	PLCC84	PA7064/96-84LC
ALTERA	EPM7064Sas7064	TQFP44	PA44QF44D
ALTERA	EPM7096	PLCC68	PA68-40B
ALTERA	EPM7096	PLCC68	PA7064/96-68LC
ALTERA	EPM7096	PLCC84	PA7064/96-84LC
ALTERA	EPM7096	PLCC84	PA84-40B
ALTERA	EPM7128E	PLCC84	HA7128/E-84LC
ALTERA	EPM7128E	PLCC84	PA7128/E-84LC
ALTERA	EPM7128S	PLCC84	HA7128/E-84LC
ALTERA	EPM7128S	PLCC84	PA7128/E-84LC
ALTERA	EPM7128S	PLCC84	PA84PL48DE-YC
ALTERA	EPM7128S	TQFP100	PA100TQ48DA
ALTERA	EPM7128Sas7128	PLCC84	HA7128/E-84LC
ALTERA	EPM7128Sas7128	PLCC84	PA7128/E-84LC
ALTERA	EPM7128Sas7128	TQFP100	PA100TQ48DA
AMD	8751H	DIP40	
AMD	8753H	DIP40	
AMD	87C51	DIP40	
AMD	87C521	DIP40	
AMD	87C521T2	DIP40	
AMD	87C541	DIP40	
AMD	Am27128	DIP28	
AMD	Am27128	PLCC32	PA32PL28D-YA
AMD	Am27128A	DIP28	
AMD	Am27128A	PLCC32	PA32PL28D-YA
AMD	Am2716	DIP24	
AMD	Am2716B	DIP24	
AMD	Am27256	DIP28	
AMD	Am27256	PLCC32	PA32PL28D-YA
AMD	Am2732	DIP24	
AMD	Am2732A	DIP24	
AMD	Am2732B	DIP24	
AMD	Am27512	DIP28	
AMD	Am27512	PLCC32	PA32PL28D-YA
AMD	Am2764	DIP28	
AMD	Am2764	PLCC32	PA32PL28D-YA
AMD	Am2764A	DIP28	
AMD	Am2764A	PLCC32	PA32PL28D-YA
AMD	Am27C010	DIP32	
AMD	Am27C010	PLCC32	PA32PL32D
AMD	Am27C020	DIP32	
AMD	Am27C020	PLCC32	PA32PL32D
AMD	Am27C040	DIP32	
AMD	Am27C040	PLCC32	PA32PL32D
AMD	Am27C1024	DIP40	
AMD	Am27C1024	PLCC44	PA44-48U
AMD	Am27C128	DIP28	

AMD	Am27C128	PLCC32	PA32PL28D-YA
AMD	Am27C2048	DIP40	
AMD	Am27C2048	PLCC44	PA44-48U
AMD	Am27C256	DIP28	
AMD	Am27C256	PLCC32	PA32PL28D-YA
AMD	Am27C400	DIP40	
AMD	Am27C4096	DIP40	
AMD	Am27C4096	PLCC44	PA44-48U
AMD	Am27C512	DIP28	
AMD	Am27C512	PLCC32	PA32PL28D-YA
AMD	Am27C64	DIP28	
AMD	Am27C64	PLCC32	PA32PL28D-YA
AMD	Am27C800	DIP42	
AMD	Am27C800	PLCC44	PA44-48U
AMD	Am27H010	DIP32	
AMD	Am27H010	PLCC32	PA32PL32D
AMD	Am27H256	DIP28	
AMD	Am27H256	PLCC32	PA32PL28D-YA
AMD	Am27HB010	DIP32	
AMD	Am27HB010	PLCC32	PA32PL32D
AMD	Am27LV010	PLCC32	PA32PL32D
AMD	Am27LV010	TSOP32	PA32TS20/PA32TS32D-20
AMD	Am27LV010B	DIP32	
AMD	Am27LV010B	PLCC32	PA32PL32D
AMD	Am27LV010B	TSOP32	PA32TS20/PA32TS32D-20
AMD	Am27LV020	DIP32	
AMD	Am27LV020	PLCC32	PA32PL32D
AMD	Am27LV020	TSOP32	PA32TS20/PA32TS32D-20
AMD	Am27LV020B	DIP32	
AMD	Am27LV020B	PLCC32	PA32PL32D
AMD	Am27LV020B	TSOP32	PA32TS20/PA32TS32D-20
AMD	Am2817A	DIP28	
AMD	Am2864A	DIP28	
AMD	Am2864AE	DIP28	
AMD	Am2864B	DIP28	
AMD	Am2864BE	DIP28	
AMD	Am28F010	DIP32	
AMD	Am28F010	PLCC32	PA32PL32D
AMD	Am28F010	TSOP32	PA32TS20/PA32TS32D-20
AMD	Am28F010A	DIP32	
AMD	Am28F010A	PLCC32	PA32PL32D
AMD	Am28F010A	TSOP32	PA32TS20/PA32TS32D-20
AMD	Am28F020	DIP32	
AMD	Am28F020	PLCC32	PA32PL32D
AMD	Am28F020	TSOP32	PA32TS20/PA32TS32D-20
AMD	Am28F020A	DIP32	
AMD	Am28F020A	PLCC32	PA32PL32D
AMD	Am28F020A	TSOP32	PA32TS20/PA32TS32D-20
AMD	Am28F256	DIP32	
AMD	Am28F256	PLCC32	PA32PL32D
AMD	Am28F256	TSOP32	PA32TS20/PA32TS32D-20
AMD	Am28F256A	DIP32	
AMD	Am28F256A	PLCC32	PA32PL32D
AMD	Am28F256A	TSOP32	PA32TS20/PA32TS32D-20
AMD	Am28F512	DIP32	
AMD	Am28F512	PLCC32	PA32PL32D
AMD	Am28F512	TSOP32	PA32TS20/PA32TS32D-20
AMD	Am28F512A	DIP32	
AMD	Am28F512A	PLCC32	PA32PL32D
AMD	Am28F512A	TSOP32	PA32TS20/PA32TS32D-20
AMD	Am29BL802CB	SSOP56	PA56SS48DA
AMD	Am29DL162CB	TSOP48	PA48TS48D
AMD	Am29DL162CT	TSOP48	PA48TS48D
AMD	Am29DL162DB	BGA48	HA48BGA48DAO
AMD	Am29DL162DT	BGA48	HA48BGA48DAO
AMD	Am29DL163CB	TSOP48	PA48TS48D
AMD	Am29DL163CT	TSOP48	PA48TS48D
AMD	Am29DL164DB	TSOP48	PA48TS48D
AMD	Am29DL164DT	TSOP48	PA48TS48D
AMD	Am29DL316CB	TSOP40	PA40TS40D
AMD	Am29DL316CT	TSOP40	PA40TS40D
AMD	Am29DL322CB	TSOP48	PA48TS48D
AMD	Am29DL322CT	TSOP48	PA48TS48D

AMD	Am29DL322DB	TSOP48	PA48TS48D
AMD	Am29DL322DT	TSOP48	PA48TS48D
AMD	Am29DL323CB	TSOP48	PA48TS48D
AMD	Am29DL323CT	TSOP48	PA48TS48D
AMD	Am29DL323DB	TSOP48	PA48TS48D
AMD	Am29DL323DT	TSOP48	PA48TS48D
AMD	Am29DL323GB	TSOP48	PA48TS48D
AMD	Am29DL323GT	TSOP48	PA48TS48D
AMD	Am29DL324DB	TSOP48	PA48TS48D
AMD	Am29DL324DT	TSOP48	PA48TS48D
AMD	Am29DL400BB	SOP44	PA44SO44D
AMD	Am29DL400BB	TSOP48	PA48TS48D
AMD	Am29DL400BT	SOP44	PA44SO44D
AMD	Am29DL400BT	TSOP48	PA48TS48D
AMD	Am29DL640D	TSOP48	PA48TS48D
AMD	Am29DL640G	TSOP48	PA48TS48D
AMD	Am29DL800BB	SOP44	PA44SO44D
AMD	Am29DL800BB	TSOP48	PA48TS48D
AMD	Am29DL800BT	BGA48	HA48BG48DAP
AMD	Am29DL800BT	SOP44	PA44SO44D
AMD	Am29DL800BT	TSOP48	PA48TS48D
AMD	Am29F002B	DIP32	
AMD	Am29F002B	PLCC32	PA32PL32D
AMD	Am29F002B	TSOP32	PA32TS32D
AMD	Am29F002BB	DIP32	
AMD	Am29F002BB	PLCC32	PA32PL32D
AMD	Am29F002BB	TSOP32	PA32TS32D
AMD	Am29F002BT	DIP32	
AMD	Am29F002BT	PLCC32	PA32PL32D
AMD	Am29F002BT	TSOP32	PA32TS32D
AMD	Am29F002NB	DIP32	
AMD	Am29F002NB	PLCC32	PA32PL32D
AMD	Am29F002NB	TSOP32	PA32TS32D
AMD	Am29F002NBB	DIP32	
AMD	Am29F002NBB	PLCC32	PA32PL32D
AMD	Am29F002NBB	TSOP32	PA32TS32D
AMD	Am29F002NBT	DIP32	
AMD	Am29F002NBT	PLCC32	PA32PL32D
AMD	Am29F002NBT	TSOP32	PA32TS32D
AMD	Am29F002NT	DIP32	
AMD	Am29F002NT	PLCC32	PA32PL32D
AMD	Am29F002NT	TSOP32	PA32TS32D
AMD	Am29F002T	DIP32	
AMD	Am29F002T	PLCC32	PA32PL32D
AMD	Am29F002T	TSOP32	PA32TS32D
AMD	Am29F004BB	DIP32	
AMD	Am29F004BB	PLCC32	PA32PL32D
AMD	Am29F004BB	TSOP32	PA32TS32D
AMD	Am29F004BT	DIP32	
AMD	Am29F004BT	PLCC32	PA32PL32D
AMD	Am29F004BT	TSOP32	PA32TS32D
AMD	Am29F010	DIP32	
AMD	Am29F010	PLCC32	PA32PL32D
AMD	Am29F010	TSOP32	PA32TS32D
AMD	Am29F010A	DIP32	
AMD	Am29F010A	PLCC32	PA32PL32D
AMD	Am29F010A	TSOP32	PA32TS32D
AMD	Am29F010B	DIP32	
AMD	Am29F010B	PLCC32	PA32PL32D
AMD	Am29F010B	TSOP32	PA32TS32D
AMD	Am29F016	SOP44	PA44SO44D
AMD	Am29F016	TSOP48	PA48TS48D
AMD	Am29F016B	SOP44	PA44SO44D
AMD	Am29F016B	TSOP40	PA40TS40D
AMD	Am29F016B	TSOP48	PA48TS48D
AMD	Am29F016D	SOP44	PA44SO44D
AMD	Am29F016D	TSOP40	PA40TS40D
AMD	Am29F016D	TSOP48	PA48TS48D
AMD	Am29F017B	TSOP40	PA40TS40D
AMD	Am29F017B	TSOP48	PA48TS48D
AMD	Am29F017D	TSOP40	PA40TS40D
AMD	Am29F017D	TSOP48	PA48TS48D
AMD	Am29F032B	DIP40	R.F.53432101

AMD	Am29F032B	SOP44	PA44SO44D
AMD	Am29F032B	TSOP40	PA40TS40D
AMD	Am29F040	DIP32	
AMD	Am29F040	PLCC32	PA32PL32D
AMD	Am29F040	TSOP32	PA32TS32D
AMD	Am29F040B	DIP32	
AMD	Am29F040B	PLCC32	PA32PL32D
AMD	Am29F040B	TSOP32	PA32TS32D
AMD	Am29F080	SOP44	PA44SO44D
AMD	Am29F080	TSOP40	PA40TS40D
AMD	Am29F080B	SOP44	PA44SO44D
AMD	Am29F080B	TSOP40	PA40TS40D
AMD	Am29F100B	SOP44	PA44SO44D
AMD	Am29F100B	TSOP48	PA48TS48D
AMD	Am29F100T	SOP44	PA44SO44D
AMD	Am29F100T	TSOP48	PA48TS48D
AMD	Am29F160DB	TSOP48	PA48TS48D
AMD	Am29F160DT	TSOP48	PA48TS48D
AMD	Am29F200AB	SOP44	PA44SO44D
AMD	Am29F200AB	TSOP48	PA48TS48D
AMD	Am29F200AT	SOP44	PA44SO44D
AMD	Am29F200AT	TSOP48	PA48TS48D
AMD	Am29F200B	SOP44	PA44SO44D
AMD	Am29F200B	TSOP48	PA48TS48D
AMD	Am29F200BB	SOP44	PA44SO44D
AMD	Am29F200BB	TSOP48	PA48TS48D
AMD	Am29F200BT	SOP44	PA44SO44D
AMD	Am29F200BT	TSOP48	PA48TS48D
AMD	Am29F200T	SOP44	PA44SO44D
AMD	Am29F200T	TSOP48	PA48TS48D
AMD	Am29F400AB	SOP44	PA44SO44D
AMD	Am29F400AB	TSOP48	PA48TS48D
AMD	Am29F400AT	SOP44	PA44SO44D
AMD	Am29F400AT	TSOP48	PA48TS48D
AMD	Am29F400B	SOP44	PA44SO44D
AMD	Am29F400B	TSOP48	PA48TS48D
AMD	Am29F400BB	SOP44	PA44SO44D
AMD	Am29F400BB	TSOP48	PA48TS48D
AMD	Am29F400BT	SOP44	PA44SO44D
AMD	Am29F400BT	TSOP48	PA48TS48D
AMD	Am29F400T	SOP44	PA44SO44D
AMD	Am29F400T	TSOP48	PA48TS48D
AMD	Am29F800AB	SOP44	PA44SO44D
AMD	Am29F800AB	TSOP48	PA48TS48D
AMD	Am29F800AT	SOP44	PA44SO44D
AMD	Am29F800AT	TSOP48	PA48TS48D
AMD	Am29F800B	SOP44	PA44SO44D
AMD	Am29F800B	TSOP48	PA48TS48D
AMD	Am29F800BB	SOP44	PA44SO44D
AMD	Am29F800BB	TSOP48	PA48TS48D
AMD	Am29F800BT	SOP44	PA44SO44D
AMD	Am29F800BT	TSOP48	PA48TS48D
AMD	Am29F800T	SOP44	PA44SO44D
AMD	Am29F800T	TSOP48	PA48TS48D
AMD	Am29LV001BB	DIP32	
AMD	Am29LV001BB	PLCC32	PA32PL32D
AMD	Am29LV001BB	TSOP32	PA32TS20/PA32TS32D-20
AMD	Am29LV001BT	DIP32	
AMD	Am29LV001BT	PLCC32	PA32PL32D
AMD	Am29LV001BT	TSOP32	PA32TS20/PA32TS32D-20
AMD	Am29LV002B	TSOP40	PA40TS40D
AMD	Am29LV002BB	TSOP40	PA40TS40D
AMD	Am29LV002BT	TSOP40	PA40TS40D
AMD	Am29LV002T	TSOP40	PA40TS40D
AMD	Am29LV004B	TSOP40	PA40TS40D
AMD	Am29LV004BB	TSOP40	PA40TS40D
AMD	Am29LV004BT	TSOP40	PA40TS40D
AMD	Am29LV004T	TSOP40	PA40TS40D
AMD	Am29LV008B	TSOP40	PA40TS40D
AMD	Am29LV008BB	TSOP40	PA40TS40D
AMD	Am29LV008BT	TSOP40	PA40TS40D
AMD	Am29LV008T	TSOP40	PA40TS40D
AMD	Am29LV010B	DIP32	

AMD	Am29LV010B	PLCC32	PA32PL32D
AMD	Am29LV010B	TSOP32	PA32TS20/PA32TS32D-20
AMD	Am29LV017B	TSOP40	PA40TS40D
AMD	Am29LV017D	TSOP40	PA40TS40D
AMD	Am29LV033C	TSOP40	PA40TS40D
AMD	Am29LV040B	DIP32	
AMD	Am29LV040B	PLCC32	PA32PL32D
AMD	Am29LV040B	TSOP32	PA32TS20/PA32TS32D-20
AMD	Am29LV065D	TSOP48	PA48TS48D
AMD	Am29LV081	TSOP40	PA40TS40D
AMD	Am29LV081B	TSOP40	PA40TS40D
AMD	Am29LV116BB	TSOP40	PA40TS40D
AMD	Am29LV116BT	TSOP40	PA40TS40D
AMD	Am29LV116DB	TSOP40	PA40TS40D
AMD	Am29LV116DT	TSOP40	PA40TS40D
AMD	Am29LV128MH	TSOP56	PA56TS48DB
AMD	Am29LV128ML	TSOP56	PA56TS48DB
AMD	Am29LV160BB	SOP44	PA44SO44D
AMD	Am29LV160BB	TSOP48	PA48TS48D
AMD	Am29LV160BT	SOP44	PA44SO44D
AMD	Am29LV160BT	TSOP48	PA48TS48D
AMD	Am29LV160DB	SOP44	PA44SO44D
AMD	Am29LV160DB	TSOP48	PA48TS48D
AMD	Am29LV160DT	SOP44	PA44SO44D
AMD	Am29LV160DT	TSOP48	PA48TS48D
AMD	Am29LV160MB	TSOP48	PA48TS48D1
AMD	Am29LV160MT	TSOP48	PA48TS48D1
AMD	Am29LV200B	SOP44	PA44SO44D
AMD	Am29LV200B	TSOP48	PA48TS48D
AMD	Am29LV200BB	SOP44	PA44SO44D
AMD	Am29LV200BB	TSOP48	PA48TS48D
AMD	Am29LV200BT	SOP44	PA44SO44D
AMD	Am29LV200BT	TSOP48	PA48TS48D
AMD	Am29LV200T	SOP44	PA44SO44D
AMD	Am29LV200T	TSOP48	PA48TS48D
AMD	Am29LV256MH	TSOP56	PA56TS48DC
AMD	Am29LV256ML	BGA64	PA64BG48DAD
AMD	Am29LV256ML	TSOP56	PA56TS48DC
AMD	Am29LV320DB	TSOP48	PA48TS48D
AMD	Am29LV320DT	TSOP48	PA48TS48D
AMD	Am29LV320MB	TSOP48	PA48TS48D1
AMD	Am29LV320MT	TSOP48	PA48TS48D1
AMD	Am29LV400B	SOP44	PA44SO44D
AMD	Am29LV400B	TSOP48	PA48TS48D
AMD	Am29LV400BB	BGA48	HA48BG48DAI
AMD	Am29LV400BB	BGA48	PA48BG48DW
AMD	Am29LV400BB	SOP44	PA44SO44D
AMD	Am29LV400BB	TSOP48	PA48TS48D
AMD	Am29LV400BT	BGA48	HA48BG48DAI
AMD	Am29LV400BT	BGA48	PA48BG48DW
AMD	Am29LV400BT	SOP44	PA44SO44D
AMD	Am29LV400BT	TSOP48	PA48TS48D
AMD	Am29LV400T	SOP44	PA44SO44D
AMD	Am29LV400T	TSOP48	PA48TS48D
AMD	Am29LV640DUxxPC	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
AMD	Am29LV640MB	TSOP48	PA48TS48D
AMD	Am29LV640MH	TSOP56	PA56TS48DC
AMD	Am29LV640ML	TSOP56	PA56TS48DC
AMD	Am29LV640MT	TSOP48	PA48TS48D
AMD	Am29LV641DH	TSOP48	PA48TS48D
AMD	Am29LV641DL	TSOP48	PA48TS48D
AMD	Am29LV641MH	TSOP48	PA48TS48D
AMD	Am29LV641ML	TSOP48	PA48TS48D
AMD	Am29LV800B	SOP44	PA44SO44D
AMD	Am29LV800B	TSOP48	PA48TS48D
AMD	Am29LV800BB	BGA48	HA48BG48DAP
AMD	Am29LV800BB	SOP44	PA44SO44D
AMD	Am29LV800BB	TSOP48	PA48TS48D
AMD	Am29LV800BT	BGA48	HA48BG48DAP
AMD	Am29LV800BT	SOP44	PA44SO44D
AMD	Am29LV800BT	TSOP48	PA48TS48D
AMD	Am29LV800DB	BGA48	HA48BG48DAP
AMD	Am29LV800DB	SOP44	PA44SO44D



AMD	Am29LV800DB	TSOP48	PA48TS48D
AMD	Am29LV800DT	BGA48	HA48BG48DAP
AMD	Am29LV800DT	SOP44	PA44SO44D
AMD	Am29LV800DT	TSOP48	PA48TS48D
AMD	Am29LV800T	SOP44	PA44SO44D
AMD	Am29LV800T	TSOP48	PA48TS48D
AMD	Am29PL160CB	SOP44	PA44SO44D
AMD	Am29PL160CB	TSOP48	PA48TS48D
AMD	Am29PL160CT	SOP44	PA44SO44D
AMD	Am29PL160CT	TSOP48	PA48TS48D
AMD	Am29SL160BB	TSOP48	PA48TS48D
AMD	Am29SL160BT	TSOP48	PA48TS48D
AMD	Am29SL160CB	TSOP48	PA48TS48D
AMD	Am29SL160CT	TSOP48	PA48TS48D
AMD	Am29SL800CB	BGA48	HA48BG48DBC
AMD	Am29SL800CB	TSOP48	PA48TS48D
AMD	Am29SL800CT	BGA48	HA48BG48DBC
AMD	Am29SL800CT	TSOP48	PA48TS48D
AMD	Am29SL800DB	BGA48	HA48BG48DBC
AMD	Am29SL800DB	TSOP48	PA48TS48D
AMD	Am29SL800DT	BGA48	HA48BG48DBC
AMD	Am29SL800DT	TSOP48	PA48TS48D
AMD	Am42DL64OAG	BGA73	PA73BGA48DC-YO-8X11.6
AMD	Am45DL6408G	BGA73	PA73BGA48DC-YO-8X11.6
AMD	Am49DL640BG	BGA73	PA73BGA48DC-YO-8X11.6
AMD	Am50DL128BG	BGA73	PA73BGA48DC-YO-8X11.6
AMD	Am50DL128CG	BGA88	PA88BG48DB-WO-11.6X8
AMD	Am50DL128CH	BGA88	PA88BG48DB-WO-11.6X8
AMD	Am50DL9608BG	BGA73	PA73BGA48DC-YO-8X11.6
AMD	Am50PDL193BH	BGA73	PA73BG48DG
AMD	Am50PDL193CH	BGA73	PA73BG48DG
AMD	MACH110	PLCC44	PA44-48U
AMD	MACH110	PLCC44	PA-MACH1
AMD	MACH111	PLCC44	PA44-48U
AMD	MACH111	PLCC44	PA-MACH1
AMD	MACH111SP	PLCC44	PA44-48U
AMD	MACH111SP	PLCC44	PA-MACH1
AMD	MACH120	PLCC68	PA-MACH4
AMD	MACH130	PLCC84	PA-MACH2
AMD	MACH131	PLCC84	PA-MACH2
AMD	MACH210	PLCC44	PA44-48U
AMD	MACH210	PLCC44	PA-MACH1
AMD	MACH211	PLCC44	PA44-48U
AMD	MACH211	PLCC44	PA-MACH1
AMD	MACH211SP	PLCC44	PA44-48U
AMD	MACH211SP	PLCC44	PA-MACH1
AMD	MACH215	PLCC44	PA44-48U
AMD	MACH215	PLCC44	PA-MACH1
AMD	MACH220	PLCC68	PA-MACH4
AMD	MACH230	PLCC84	PA-MACH2
AMD	MACH231-20JC/1	PLCC84	PA-MACH2
AMD	MACH231-7	PLCC84	PA-MACH2
AMD	MACH435	PLCC84	PA-MACH2
AMD	MACHLV210	PLCC44	PA44-48U
AMD	MACHLV210	PLCC44	PA-MACH1
AMD	PALC16L8Q	DIP20	
AMD	PALC16L8Q	PLCC20	PA20LC20D[Dead Bug]
AMD	PALC16L8Z	DIP20	
AMD	PALC16L8Z	PLCC20	PA20LC20D[Dead Bug]
AMD	PALC16R4Q	DIP20	
AMD	PALC16R4Q	PLCC20	PA20LC20D[Dead Bug]
AMD	PALC16R4Z	DIP20	
AMD	PALC16R4Z	PLCC20	PA20LC20D[Dead Bug]
AMD	PALC16R6Q	DIP20	
AMD	PALC16R6Q	PLCC20	PA20LC20D[Dead Bug]
AMD	PALC16R6Z	DIP20	
AMD	PALC16R6Z	PLCC20	PA20LC20D[Dead Bug]
AMD	PALC16R8Q	DIP20	
AMD	PALC16R8Q	PLCC20	PA20LC20D[Dead Bug]
AMD	PALC16R8Z	DIP20	
AMD	PALC16R8Z	PLCC20	PA20LC20D[Dead Bug]
AMD	PALC20L8Z	DIP24	
AMD	PALC20L8Z	PLCC28	PA28PL24D2P6-YA

AMD	PALC20R4Z	DIP24	
AMD	PALC20R4Z	PLCC28	PA28PL24D2P6-YA
AMD	PALC20R6Z	DIP24	
AMD	PALC20R6Z	PLCC28	PA28PL24D2P6-YA
AMD	PALC20R8Z	DIP24	
AMD	PALC20R8Z	PLCC28	PA28PL24D2P6-YA
AMD	PALCE16V8H	DIP20	
AMD	PALCE16V8H	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8H	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has10H8	DIP20	
AMD	PALCE16V8Has10H8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has10H8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has10L8	DIP20	
AMD	PALCE16V8Has10L8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has10L8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has10P8	DIP20	
AMD	PALCE16V8Has10P8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has10P8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has12H6	DIP20	
AMD	PALCE16V8Has12H6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has12H6	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has12L6	DIP20	
AMD	PALCE16V8Has12L6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has12L6	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has12P6	DIP20	
AMD	PALCE16V8Has12P6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has12P6	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has14H4	DIP20	
AMD	PALCE16V8Has14H4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has14H4	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has14L4	DIP20	
AMD	PALCE16V8Has14L4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has14L4	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has14P4	DIP20	
AMD	PALCE16V8Has14P4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has14P4	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has16H2	DIP20	
AMD	PALCE16V8Has16H2	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16H2	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has16H8	DIP20	
AMD	PALCE16V8Has16H8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16H8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has16L2	DIP20	
AMD	PALCE16V8Has16L2	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16L2	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has16L8	DIP20	
AMD	PALCE16V8Has16L8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16L8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has16P2	DIP20	
AMD	PALCE16V8Has16P2	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16P2	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has16P8	DIP20	
AMD	PALCE16V8Has16P8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16P8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has16R4	DIP20	
AMD	PALCE16V8Has16R4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16R4	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has16R6	DIP20	
AMD	PALCE16V8Has16R6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16R6	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has16R8	DIP20	
AMD	PALCE16V8Has16R8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16R8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has16RP4	DIP20	
AMD	PALCE16V8Has16RP4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16RP4	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has16RP6	DIP20	
AMD	PALCE16V8Has16RP6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16RP6	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Has16RP8	DIP20	
AMD	PALCE16V8Has16RP8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Has16RP8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Q	DIP20	

AMD	PALCE16V8Q	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Q	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas10H8	DIP20	
AMD	PALCE16V8Qas10H8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas10H8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas10L8	DIP20	
AMD	PALCE16V8Qas10L8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas10L8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas10P8	DIP20	
AMD	PALCE16V8Qas10P8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas10P8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas12H6	DIP20	
AMD	PALCE16V8Qas12H6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas12H6	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas12L6	DIP20	
AMD	PALCE16V8Qas12L6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas12L6	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas12P6	DIP20	
AMD	PALCE16V8Qas12P6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas12P6	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas14H4	DIP20	
AMD	PALCE16V8Qas14H4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas14H4	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas14L4	DIP20	
AMD	PALCE16V8Qas14L4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas14L4	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas14P4	DIP20	
AMD	PALCE16V8Qas14P4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas14P4	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16H2	DIP20	
AMD	PALCE16V8Qas16H2	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16H2	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16H8	DIP20	
AMD	PALCE16V8Qas16H8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16H8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16L2	DIP20	
AMD	PALCE16V8Qas16L2	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16L2	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16L8	DIP20	
AMD	PALCE16V8Qas16L8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16L8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16P2	DIP20	
AMD	PALCE16V8Qas16P2	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16P2	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16P8	DIP20	
AMD	PALCE16V8Qas16P8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16P8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16R4	DIP20	
AMD	PALCE16V8Qas16R4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16R4	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16R6	DIP20	
AMD	PALCE16V8Qas16R6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16R6	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16R8	DIP20	
AMD	PALCE16V8Qas16R8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16R8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16RP4	DIP20	
AMD	PALCE16V8Qas16RP4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16RP4	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16RP6	DIP20	
AMD	PALCE16V8Qas16RP6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16RP6	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Qas16RP8	DIP20	
AMD	PALCE16V8Qas16RP8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Qas16RP8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Z	DIP20	
AMD	PALCE16V8Z	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Z	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas10H8	DIP20	
AMD	PALCE16V8Zas10H8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas10H8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas10L8	DIP20	
AMD	PALCE16V8Zas10L8	PLCC20	PA20LC20D[Dead Bug]

AMD	PALCE16V8Zas10L8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas10P8	DIP20	
AMD	PALCE16V8Zas10P8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas10P8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas12H6	DIP20	
AMD	PALCE16V8Zas12H6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas12H6	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas12L6	DIP20	
AMD	PALCE16V8Zas12L6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas12L6	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas12P6	DIP20	
AMD	PALCE16V8Zas12P6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas12P6	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas14H4	DIP20	
AMD	PALCE16V8Zas14H4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas14H4	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas14L4	DIP20	
AMD	PALCE16V8Zas14L4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas14L4	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas14P4	DIP20	
AMD	PALCE16V8Zas14P4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas14P4	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16H2	DIP20	
AMD	PALCE16V8Zas16H2	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16H2	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16H8	DIP20	
AMD	PALCE16V8Zas16H8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16H8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16L2	DIP20	
AMD	PALCE16V8Zas16L2	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16L2	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16L8	DIP20	
AMD	PALCE16V8Zas16L8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16L8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16P2	DIP20	
AMD	PALCE16V8Zas16P2	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16P2	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16P8	DIP20	
AMD	PALCE16V8Zas16P8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16P8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16R4	DIP20	
AMD	PALCE16V8Zas16R4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16R4	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16R6	DIP20	
AMD	PALCE16V8Zas16R6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16R6	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16R8	DIP20	
AMD	PALCE16V8Zas16R8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16R8	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16RP4	DIP20	
AMD	PALCE16V8Zas16RP4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16RP4	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16RP6	DIP20	
AMD	PALCE16V8Zas16RP6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16RP6	SOIC20	PA20SO20D-EO-210
AMD	PALCE16V8Zas16RP8	DIP20	
AMD	PALCE16V8Zas16RP8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALCE16V8Zas16RP8	SOIC20	PA20SO20D-EO-210
AMD	PALCE20RA10H	DIP24	
AMD	PALCE20RA10H	PLCC28	PA28PL28D
AMD	PALCE20RA10Q	DIP24	
AMD	PALCE20RA10Q	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4	DIP24	
AMD	PALCE20V8H-10/4	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as14H8	DIP24	
AMD	PALCE20V8H-10/4as14H8	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as14L8	DIP24	
AMD	PALCE20V8H-10/4as14L8	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as14P8	DIP24	
AMD	PALCE20V8H-10/4as14P8	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as16H6	DIP24	
AMD	PALCE20V8H-10/4as16H6	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as16L6	DIP24	

AMD	PALCE20V8H-10/4as16L6	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as16P6	DIP24	
AMD	PALCE20V8H-10/4as16P6	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as18H4	DIP24	
AMD	PALCE20V8H-10/4as18H4	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as18L4	DIP24	
AMD	PALCE20V8H-10/4as18L4	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as18P4	DIP24	
AMD	PALCE20V8H-10/4as18P4	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as20H2	DIP24	
AMD	PALCE20V8H-10/4as20H2	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as20H8	DIP24	
AMD	PALCE20V8H-10/4as20H8	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as20L2	DIP24	
AMD	PALCE20V8H-10/4as20L2	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as20L8	DIP24	
AMD	PALCE20V8H-10/4as20L8	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as20P2	DIP24	
AMD	PALCE20V8H-10/4as20P2	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as20P8	DIP24	
AMD	PALCE20V8H-10/4as20P8	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as20R4	DIP24	
AMD	PALCE20V8H-10/4as20R4	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as20R6	DIP24	
AMD	PALCE20V8H-10/4as20R6	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as20R8	DIP24	
AMD	PALCE20V8H-10/4as20R8	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as20RP4	DIP24	
AMD	PALCE20V8H-10/4as20RP4	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as20RP6	DIP24	
AMD	PALCE20V8H-10/4as20RP6	PLCC28	PA28PL28D
AMD	PALCE20V8H-10/4as20RP8	DIP24	
AMD	PALCE20V8H-10/4as20RP8	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4	DIP24	
AMD	PALCE20V8H-15/4	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as14H8	DIP24	
AMD	PALCE20V8H-15/4as14H8	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as14L8	DIP24	
AMD	PALCE20V8H-15/4as14L8	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as14P8	DIP24	
AMD	PALCE20V8H-15/4as14P8	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as16H6	DIP24	
AMD	PALCE20V8H-15/4as16H6	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as16L6	DIP24	
AMD	PALCE20V8H-15/4as16L6	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as16P6	DIP24	
AMD	PALCE20V8H-15/4as16P6	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as18H4	DIP24	
AMD	PALCE20V8H-15/4as18H4	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as18L4	DIP24	
AMD	PALCE20V8H-15/4as18L4	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as18P4	DIP24	
AMD	PALCE20V8H-15/4as18P4	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as20H2	DIP24	
AMD	PALCE20V8H-15/4as20H2	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as20H8	DIP24	
AMD	PALCE20V8H-15/4as20H8	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as20L2	DIP24	
AMD	PALCE20V8H-15/4as20L2	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as20L8	DIP24	
AMD	PALCE20V8H-15/4as20L8	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as20P2	DIP24	
AMD	PALCE20V8H-15/4as20P2	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as20P8	DIP24	
AMD	PALCE20V8H-15/4as20P8	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as20R4	DIP24	
AMD	PALCE20V8H-15/4as20R4	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as20R6	DIP24	
AMD	PALCE20V8H-15/4as20R6	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as20R8	DIP24	
AMD	PALCE20V8H-15/4as20R8	PLCC28	PA28PL28D
AMD	PALCE20V8H-15/4as20RP4	DIP24	
AMD	PALCE20V8H-15/4as20RP4	PLCC28	PA28PL28D

AMD	PALCE20V8H-15/4as20RP6	DIP24	PA28PL28D
AMD	PALCE20V8H-15/4as20RP6	PLCC28	
AMD	PALCE20V8H-15/4as20RP8	DIP24	PA28PL28D
AMD	PALCE20V8H-15/4as20RP8	PLCC28	
AMD	PALCE20V8H-25	DIP24	PA28PL28D
AMD	PALCE20V8H-25	PLCC28	
AMD	PALCE20V8H-25/4	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4	PLCC28	
AMD	PALCE20V8H-25/4as14H8	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as14H8	PLCC28	
AMD	PALCE20V8H-25/4as14L8	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as14L8	PLCC28	
AMD	PALCE20V8H-25/4as14P8	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as14P8	PLCC28	
AMD	PALCE20V8H-25/4as16H6	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as16H6	PLCC28	
AMD	PALCE20V8H-25/4as16L6	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as16L6	PLCC28	
AMD	PALCE20V8H-25/4as16P6	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as16P6	PLCC28	
AMD	PALCE20V8H-25/4as18H4	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as18H4	PLCC28	
AMD	PALCE20V8H-25/4as18L4	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as18L4	PLCC28	
AMD	PALCE20V8H-25/4as18P4	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as18P4	PLCC28	
AMD	PALCE20V8H-25/4as20H2	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as20H2	PLCC28	
AMD	PALCE20V8H-25/4as20H8	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as20H8	PLCC28	
AMD	PALCE20V8H-25/4as20L2	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as20L2	PLCC28	
AMD	PALCE20V8H-25/4as20L8	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as20L8	PLCC28	
AMD	PALCE20V8H-25/4as20P2	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as20P2	PLCC28	
AMD	PALCE20V8H-25/4as20P8	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as20P8	PLCC28	
AMD	PALCE20V8H-25/4as20R4	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as20R4	PLCC28	
AMD	PALCE20V8H-25/4as20R6	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as20R6	PLCC28	
AMD	PALCE20V8H-25/4as20R8	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as20R8	PLCC28	
AMD	PALCE20V8H-25/4as20RP4	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as20RP4	PLCC28	
AMD	PALCE20V8H-25/4as20RP6	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as20RP6	PLCC28	
AMD	PALCE20V8H-25/4as20RP8	DIP24	PA28PL28D
AMD	PALCE20V8H-25/4as20RP8	PLCC28	
AMD	PALCE20V8H-25as14H8	DIP24	PA28PL28D
AMD	PALCE20V8H-25as14H8	PLCC28	
AMD	PALCE20V8H-25as14L8	DIP24	PA28PL28D
AMD	PALCE20V8H-25as14L8	PLCC28	
AMD	PALCE20V8H-25as14P8	DIP24	PA28PL28D
AMD	PALCE20V8H-25as14P8	PLCC28	
AMD	PALCE20V8H-25as16H6	DIP24	PA28PL28D
AMD	PALCE20V8H-25as16H6	PLCC28	
AMD	PALCE20V8H-25as16L6	DIP24	PA28PL28D
AMD	PALCE20V8H-25as16L6	PLCC28	
AMD	PALCE20V8H-25as16P6	DIP24	PA28PL28D
AMD	PALCE20V8H-25as16P6	PLCC28	
AMD	PALCE20V8H-25as18H4	DIP24	PA28PL28D
AMD	PALCE20V8H-25as18H4	PLCC28	
AMD	PALCE20V8H-25as18L4	DIP24	PA28PL28D
AMD	PALCE20V8H-25as18L4	PLCC28	
AMD	PALCE20V8H-25as18P4	DIP24	PA28PL28D
AMD	PALCE20V8H-25as18P4	PLCC28	
AMD	PALCE20V8H-25as20H2	DIP24	PA28PL28D
AMD	PALCE20V8H-25as20H2	PLCC28	
AMD	PALCE20V8H-25as20H8	DIP24	PA28PL28D
AMD	PALCE20V8H-25as20H8	PLCC28	
AMD	PALCE20V8H-25as20L2	DIP24	PA28PL28D

AMD	PALCE20V8H-25as20L2	PLCC28	PA28PL28D
AMD	PALCE20V8H-25as20L8	DIP24	
AMD	PALCE20V8H-25as20L8	PLCC28	PA28PL28D
AMD	PALCE20V8H-25as20P2	DIP24	
AMD	PALCE20V8H-25as20P2	PLCC28	PA28PL28D
AMD	PALCE20V8H-25as20P8	DIP24	
AMD	PALCE20V8H-25as20P8	PLCC28	PA28PL28D
AMD	PALCE20V8H-25as20R4	DIP24	
AMD	PALCE20V8H-25as20R4	PLCC28	PA28PL28D
AMD	PALCE20V8H-25as20R6	DIP24	
AMD	PALCE20V8H-25as20R6	PLCC28	PA28PL28D
AMD	PALCE20V8H-25as20R8	DIP24	
AMD	PALCE20V8H-25as20R8	PLCC28	PA28PL28D
AMD	PALCE20V8H-25as20RP4	DIP24	
AMD	PALCE20V8H-25as20RP4	PLCC28	PA28PL28D
AMD	PALCE20V8H-25as20RP6	DIP24	
AMD	PALCE20V8H-25as20RP6	PLCC28	PA28PL28D
AMD	PALCE20V8H-25as20RP8	DIP24	
AMD	PALCE20V8H-25as20RP8	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4	DIP24	
AMD	PALCE20V8Q-15/4	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as14H8	DIP24	
AMD	PALCE20V8Q-15/4as14H8	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as14L8	DIP24	
AMD	PALCE20V8Q-15/4as14L8	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as14P8	DIP24	
AMD	PALCE20V8Q-15/4as14P8	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as16H6	DIP24	
AMD	PALCE20V8Q-15/4as16H6	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as16L6	DIP24	
AMD	PALCE20V8Q-15/4as16L6	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as16P6	DIP24	
AMD	PALCE20V8Q-15/4as16P6	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as18H4	DIP24	
AMD	PALCE20V8Q-15/4as18H4	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as18L4	DIP24	
AMD	PALCE20V8Q-15/4as18L4	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as18P4	DIP24	
AMD	PALCE20V8Q-15/4as18P4	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as20H2	DIP24	
AMD	PALCE20V8Q-15/4as20H2	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as20H8	DIP24	
AMD	PALCE20V8Q-15/4as20H8	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as20L2	DIP24	
AMD	PALCE20V8Q-15/4as20L2	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as20L8	DIP24	
AMD	PALCE20V8Q-15/4as20L8	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as20P2	DIP24	
AMD	PALCE20V8Q-15/4as20P2	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as20P8	DIP24	
AMD	PALCE20V8Q-15/4as20P8	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as20R4	DIP24	
AMD	PALCE20V8Q-15/4as20R4	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as20R6	DIP24	
AMD	PALCE20V8Q-15/4as20R6	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as20R8	DIP24	
AMD	PALCE20V8Q-15/4as20R8	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as20RP4	DIP24	
AMD	PALCE20V8Q-15/4as20RP4	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as20RP6	DIP24	
AMD	PALCE20V8Q-15/4as20RP6	PLCC28	PA28PL28D
AMD	PALCE20V8Q-15/4as20RP8	DIP24	
AMD	PALCE20V8Q-15/4as20RP8	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4	DIP24	
AMD	PALCE20V8Q-25/4	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as14H8	DIP24	
AMD	PALCE20V8Q-25/4as14H8	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as14L8	DIP24	
AMD	PALCE20V8Q-25/4as14L8	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as14P8	DIP24	
AMD	PALCE20V8Q-25/4as14P8	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as16H6	DIP24	
AMD	PALCE20V8Q-25/4as16H6	PLCC28	PA28PL28D

AMD	PALCE20V8Q-25/4as16L6	DIP24	
AMD	PALCE20V8Q-25/4as16L6	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as16P6	DIP24	
AMD	PALCE20V8Q-25/4as16P6	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as18H4	DIP24	
AMD	PALCE20V8Q-25/4as18H4	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as18L4	DIP24	
AMD	PALCE20V8Q-25/4as18L4	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as18P4	DIP24	
AMD	PALCE20V8Q-25/4as18P4	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as20H2	DIP24	
AMD	PALCE20V8Q-25/4as20H2	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as20H8	DIP24	
AMD	PALCE20V8Q-25/4as20H8	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as20L2	DIP24	
AMD	PALCE20V8Q-25/4as20L2	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as20L8	DIP24	
AMD	PALCE20V8Q-25/4as20L8	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as20P2	DIP24	
AMD	PALCE20V8Q-25/4as20P2	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as20P8	DIP24	
AMD	PALCE20V8Q-25/4as20P8	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as20R4	DIP24	
AMD	PALCE20V8Q-25/4as20R4	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as20R6	DIP24	
AMD	PALCE20V8Q-25/4as20R6	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as20R8	DIP24	
AMD	PALCE20V8Q-25/4as20R8	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as20RP4	DIP24	
AMD	PALCE20V8Q-25/4as20RP4	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as20RP6	DIP24	
AMD	PALCE20V8Q-25/4as20RP6	PLCC28	PA28PL28D
AMD	PALCE20V8Q-25/4as20RP8	DIP24	
AMD	PALCE20V8Q-25/4as20RP8	PLCC28	PA28PL28D
AMD	PALCE22V10H	DIP24	
AMD	PALCE22V10H	PLCC28	PA28PL28D
AMD	PALCE22V10Q	DIP24	
AMD	PALCE22V10Q	PLCC28	PA28PL28D
AMD	PALCE22V10Z	DIP24	
AMD	PALCE22V10Z	PLCC28	PA28PL28D
AMD	PALCE26V12H	DIP28	
AMD	PALCE26V12H	PLCC28	PA28PL28D
AMD	PALCE26V12H/4	DIP28	
AMD	PALCE26V12H/4	PLCC28	PA28PL28D
AMD	PALCE26V12H/4-10	DIP28	
AMD	PALCE26V12H/4-10	PLCC28	PA28PL28D
AMD	PALCE29M16H	DIP24	
AMD	PALCE29M16H	PLCC28	PA28PL28D
AMD	PALCE29MA16H	DIP24	
AMD	PALCE29MA16H	PLCC28	PA28PL28D
AMD	PALCE610H	DIP24	
AMD	PALCE610H	PLCC28	PA28PL28D
AMD	PALLV16V8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as10H8	DIP20	
AMD	PALLV16V8as10H8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as10H8	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as10L8	DIP20	
AMD	PALLV16V8as10L8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as10L8	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as10P8	DIP20	
AMD	PALLV16V8as10P8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as10P8	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as12H6	DIP20	
AMD	PALLV16V8as12H6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as12H6	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as12L6	DIP20	
AMD	PALLV16V8as12L6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as12L6	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as12P6	DIP20	
AMD	PALLV16V8as12P6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as12P6	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as14H4	DIP20	



AMD	PALLV16V8as14H4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as14H4	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as14L4	DIP20	
AMD	PALLV16V8as14L4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as14L4	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as14P4	DIP20	
AMD	PALLV16V8as14P4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as14P4	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as16H2	DIP20	
AMD	PALLV16V8as16H2	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16H2	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as16H8	DIP20	
AMD	PALLV16V8as16H8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16H8	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as16L2	DIP20	
AMD	PALLV16V8as16L2	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16L2	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as16L8	DIP20	
AMD	PALLV16V8as16L8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16L8	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as16P2	DIP20	
AMD	PALLV16V8as16P2	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16P2	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as16P8	DIP20	
AMD	PALLV16V8as16P8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16P8	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as16R4	DIP20	
AMD	PALLV16V8as16R4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16R4	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as16R6	DIP20	
AMD	PALLV16V8as16R6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16R6	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as16R8	DIP20	
AMD	PALLV16V8as16R8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16R8	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as16RP4	DIP20	
AMD	PALLV16V8as16RP4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16RP4	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as16RP6	DIP20	
AMD	PALLV16V8as16RP6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16RP6	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8as16RP8	DIP20	
AMD	PALLV16V8as16RP8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8as16RP8	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Z	DIP20	
AMD	PALLV16V8Z	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Z	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas10H8	DIP20	
AMD	PALLV16V8Zas10H8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas10H8	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas10L8	DIP20	
AMD	PALLV16V8Zas10L8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas10L8	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas10P8	DIP20	
AMD	PALLV16V8Zas10P8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas10P8	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas12H6	DIP20	
AMD	PALLV16V8Zas12H6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas12H6	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas12L6	DIP20	
AMD	PALLV16V8Zas12L6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas12L6	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas12P6	DIP20	
AMD	PALLV16V8Zas12P6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas12P6	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas14H4	DIP20	
AMD	PALLV16V8Zas14H4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas14H4	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas14L4	DIP20	
AMD	PALLV16V8Zas14L4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas14L4	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas14P4	DIP20	
AMD	PALLV16V8Zas14P4	PLCC20	PA20LC20D[Dead Bug]

AMD	PALLV16V8Zas14P4	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16H2	DIP20	
AMD	PALLV16V8Zas16H2	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16H2	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16H8	DIP20	
AMD	PALLV16V8Zas16H8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16H8	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16L2	DIP20	
AMD	PALLV16V8Zas16L2	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16L2	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16L8	DIP20	
AMD	PALLV16V8Zas16L8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16L8	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16P2	DIP20	
AMD	PALLV16V8Zas16P2	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16P2	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16P8	DIP20	
AMD	PALLV16V8Zas16P8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16P8	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16R4	DIP20	
AMD	PALLV16V8Zas16R4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16R4	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16R6	DIP20	
AMD	PALLV16V8Zas16R6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16R6	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16R8	DIP20	
AMD	PALLV16V8Zas16R8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16R8	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16RP4	DIP20	
AMD	PALLV16V8Zas16RP4	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16RP4	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16RP6	DIP20	
AMD	PALLV16V8Zas16RP6	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16RP6	SOIC20	PA20SO20D-EO-210
AMD	PALLV16V8Zas16RP8	DIP20	
AMD	PALLV16V8Zas16RP8	PLCC20	PA20LC20D[Dead Bug]
AMD	PALLV16V8Zas16RP8	SOIC20	PA20SO20D-EO-210
AMD	PALLV22V10	DIP24	
AMD	PALLV22V10	PLCC28	PA28PL28D
AMD	PALLV22V10Z	DIP24	
AMD	PALLV22V10Z	PLCC28	PA28PL28D
AMI	N04C1633E3BM	BGA66	HA66BG48DD
AMI	N04C1633E3BM(SecSi)	BGA66	HA66BG48DD
AMI	N04C1633E6AM2	BGA66	HA66BG48DD
AMI	N04C1633E6AM2(SecSi)	BGA66	HA66BG48DD
AMI	PEEL18CV8	DIP20	
AMI	PEEL18CV8	PLCC20	PA20LC20D[Dead Bug]
AMI	PEEL18CV8	SOIC20	PA28SO28D-EO-300
AMI	PEEL18CV8	TSSOP20	PA24TSS24D
AMI	PEEL22CV10	DIP24	
AMI	PEEL22CV10	PLCC28	PA28PL28D
AMI	PEEL22CV10	SOIC24	PA28SO28D-EO-300
AMI	PEEL22CV10A	DIP24	
AMI	PEEL22CV10A	PLCC28	PA28PL28D
AMI	PEEL22CV10A	SOIC24	PA28SO28D-EO-300
AMI	PEEL22CV10A	TSSOP24	PA24TSS24D
AMI	PEEL22CV10A+	DIP24	
AMI	PEEL22CV10A+	PLCC28	PA28PL28D
AMI	PEEL22CV10A+	SOIC24	PA28SO28D-EO-300
AMI	PEEL22CV10A+	TSSOP24	PA24TSS24D
AMI	PEEL22CV10A++	DIP24	
AMI	PEEL22CV10A++	PLCC28	PA28PL28D
AMI	PEEL22CV10A++	SOIC24	PA28SO28D-EO-300
AMI	PEEL22CV10A++	TSSOP24	PA24TSS24D
AMI	PEEL22CV10AZ+	DIP24	
AMI	PEEL22CV10AZ+	PLCC28	PA28PL28D
AMI	PEEL22CV10AZ+	SOIC24	PA28SO28D-EO-300
AMI	PEEL22CV10AZ+	TSSOP24	PA24TSS24D
AMI	PEEL22CV10Z	DIP24	
AMI	PEEL22CV10Z	PLCC28	PA28PL28D
AMI	PEEL22CV10Z	SOIC24	PA28SO28D-EO-300
AMIC	A25L010	DIP8	
AMIC	A25L010A	DIP8	

AMIC	A25L010AO	SOP8	PA16SO16D-EO-150
AMIC	A25L010AQ1	USON8	HBP8USON48DB(2x3)
AMIC	A25L010AV	TSSOP8	PA8TSS8D
AMIC	A25L010M	SOP8	PA20SO20D-EO-210
AMIC	A25L010O	SOP8	PA16SO16D-EO-150
AMIC	A25L010Q1	USON8	HBP8USON48DB(2x3)
AMIC	A25L010Q4	WSON8	PA8SON8D(6x5)
AMIC	A25L010V	TSSOP8	PA8TSS8D
AMIC	A25L016	DIP8	
AMIC	A25L016M	SOP8	PA20SO20D-EO-210
AMIC	A25L016N	SOP16	PA28SO28D-EO-300
AMIC	A25L016O	SOP8	PA16SO16D-EO-150
AMIC	A25L016Q4	WSON8	PA8SON8D(6x5)
AMIC	A25L020	DIP8	
AMIC	A25L020C	DIP8	
AMIC	A25L020CM	SOP8	PA20SO20D-EO-210
AMIC	A25L020CO	SOP8	PA16SO16D-EO-150
AMIC	A25L020CQ1	USON8	HBP8USON48DB(2x3)
AMIC	A25L020CQ4	WSON8	PA8SON8D(6x5)
AMIC	A25L020CV	TSSOP8	PA8TSS8D
AMIC	A25L020M	SOP8	PA20SO20D-EO-210
AMIC	A25L020O	SOP8	PA16SO16D-EO-150
AMIC	A25L020Q1	USON8	HBP8USON48DB(2x3)
AMIC	A25L020Q4	WSON8	PA8SON8D(6x5)
AMIC	A25L020V	TSSOP8	PA8TSS8D
AMIC	A25L032	DIP8	
AMIC	A25L032M	SOP8	PA20SO20D-EO-210
AMIC	A25L032Q4	WSON8	PA8SON8D(6x5)
AMIC	A25L040	DIP8	
AMIC	A25L040A	DIP8	
AMIC	A25L040AM	SOP8	PA20SO20D-EO-210
AMIC	A25L040AO	SOP8	PA16SO16D-EO-150
AMIC	A25L040AQ1	USON8	HBP8USON48DB(2x3)
AMIC	A25L040AQ4	WSON8	PA8SON8D(6x5)
AMIC	A25L040AV	TSSOP8	PA8TSS8D
AMIC	A25L040M	SOP8	PA20SO20D-EO-210
AMIC	A25L040O	SOP8	PA16SO16D-EO-150
AMIC	A25L05PT	DIP8	
AMIC	A25L05PTM	SOP8	PA20SO20D-EO-210
AMIC	A25L05PTO	SOP8	PA16SO16D-EO-150
AMIC	A25L05PTQ	QFN8	PA8SON8D(6x5)
AMIC	A25L05PU	DIP8	
AMIC	A25L05PUM	SOP8	PA20SO20D-EO-210
AMIC	A25L05PUO	SOP8	PA16SO16D-EO-150
AMIC	A25L05PUQ	QFN8	PA8SON8D(6x5)
AMIC	A25L080	DIP8	
AMIC	A25L080M	SOP8	PA20SO20D-EO-210
AMIC	A25L080O	SOP8	PA16SO16D-EO-150
AMIC	A25L080Q4	WSON8	PA8SON8D(6x5)
AMIC	A25L10PT	DIP8	
AMIC	A25L10PTM	SOP8	PA20SO20D-EO-210
AMIC	A25L10PTO	SOP8	PA16SO16D-EO-150
AMIC	A25L10PTQ	QFN8	PA8SON8D(6x5)
AMIC	A25L10PU	DIP8	
AMIC	A25L10PUM	SOP8	PA20SO20D-EO-210
AMIC	A25L10PUO	SOP8	PA16SO16D-EO-150
AMIC	A25L10PUQ	QFN8	PA8SON8D(6x5)
AMIC	A25L16PTM	SOP8	PA20SO20D-EO-210
AMIC	A25L16PTN	SOP16	PA28SO28D-EO-300
AMIC	A25L16PTQ	QFN8	PA8SON8D(6x5)
AMIC	A25L16PUM	SOP8	PA20SO20D-EO-210
AMIC	A25L16PUN	SOP16	PA28SO28D-EO-300
AMIC	A25L16PUQ	QFN8	PA8SON8D(6x5)
AMIC	A25L20PT	DIP8	
AMIC	A25L20PTM	SOP8	PA20SO20D-EO-210
AMIC	A25L20PTO	SOP8	PA16SO16D-EO-150
AMIC	A25L20PTQ	QFN8	PA8SON8D(6x5)
AMIC	A25L20PU	DIP8	
AMIC	A25L20PUM	SOP8	PA20SO20D-EO-210
AMIC	A25L20PUO	SOP8	PA16SO16D-EO-150
AMIC	A25L20PUQ	QFN8	PA8SON8D(6x5)
AMIC	A25L40PT	DIP8	
AMIC	A25L40PTM	SOP8	PA20SO20D-EO-210

AMIC	A25L40PTN	SOP16	PA28SO28D-EO-300
AMIC	A25L40PTO	SOP8	PA16SO16D-EO-150
AMIC	A25L40PTQ	QFN8	PA8SON8D(6x5)
AMIC	A25L40PU	DIP8	
AMIC	A25L40PUM	SOP8	PA20SO20D-EO-210
AMIC	A25L40PUN	SOP16	PA28SO28D-EO-300
AMIC	A25L40PUO	SOP8	PA16SO16D-EO-150
AMIC	A25L40PUQ	QFN8	PA8SON8D(6x5)
AMIC	A25L512	DIP8	
AMIC	A25L512A	DIP8	
AMIC	A25L512AM	SOP8	PA20SO20D-EO-210
AMIC	A25L512AO	SOP8	PA16SO16D-EO-150
AMIC	A25L512AQ1	USON8	HBP8USON48DB(2x3)
AMIC	A25L512AQ4	WSON8	PA8SON8D(6x5)
AMIC	A25L512AV	TSSOP8	PA8TSS8D
AMIC	A25L512M	SOP8	PA20SO20D-EO-210
AMIC	A25L512O	SOP8	PA16SO16D-EO-150
AMIC	A25L512Q1	USON8	HBP8USON48DB(2x3)
AMIC	A25L512Q4	WSON8	PA8SON8D(6x5)
AMIC	A25L512V	TSSOP8	PA8TSS8D
AMIC	A25L80P	DIP8	
AMIC	A25L80PM	SOP8	PA20SO20D-EO-210
AMIC	A25L80PN	SOP16	PA28SO28D-EO-300
AMIC	A25L80PO	SOP8	PA16SO16D-EO-150
AMIC	A25L80PQ	QFN8	PA8SON8D(6x5)
AMIC	A25LM010	DIP8	
AMIC	A25LM010O	SOP8	PA16SO16D-EO-150
AMIC	A25LM010Q1	USON8	HBP8USON48DB(2x3)
AMIC	A25LMQ64	DIP8	
AMIC	A25LMQ64G	BGA24	HA24BG48D
AMIC	A25LMQ64M	SOP8	PA20SO20D-EO-210
AMIC	A25LMQ64M-FE	SOP8	PA20SO20D-EO-210
AMIC	A25LMQ64Q4	WSON8	PA8SON8D(6x5)
AMIC	A25LQ080	DIP8	
AMIC	A25LQ080M	SOP8	PA20SO20D-EO-210
AMIC	A25LQ080O	SOP8	PA16SO16D-EO-150
AMIC	A25LQ080Q4	WSON8	PA8SON8D(6x5)
AMIC	A25LQ16	DIP8	
AMIC	A25LQ16M	SOP8	PA20SO20D-EO-210
AMIC	A25LQ16O	SOP8	PA16SO16D-EO-150
AMIC	A25LQ16Q4	WSON8	PA8SON8D(6x5)
AMIC	A25LQ32A	DIP8	
AMIC	A25LQ32AM	SOP8	PA20SO20D-EO-210
AMIC	A25LQ32AQ4	WSON8	PA8SON8D(6x5)
AMIC	A25LQ64	DIP8	
AMIC	A25LQ64G	BGA24	HA24BG48D
AMIC	A25LQ64M	SOP8	PA20SO20D-EO-210
AMIC	A25LQ64M-FE	SOP8	PA20SO20D-EO-210
AMIC	A25LQ64N	SOP16	PA28SO28D-EO-300
AMIC	A25LQ64Q4	WSON8	PA8SON8D(6x5)
AMIC	A25LS512A	DIP8	
AMIC	A25LS512AM	SOP8	PA20SO20D-EO-210
AMIC	A25LS512AO	SOP8	PA16SO16D-EO-150
AMIC	A25LS512AQ1	USON8	HBP8USON48DB(2x3)
AMIC	A25LS512AQ4	WSON8	PA8SON8D(6x5)
AMIC	A25LS512AV	TSSOP8	PA8TSS8D
AMIC	A25P010	DIP8	
AMIC	A25P010O	SOP8	PA16SO16D-EO-150
AMIC	A25P010Q1	USON8	HBP8USON48DB(2x3)
AMIC	A25P010V	TSSOP8	PA8TSS8D
AMIC	A25P020	DIP8	
AMIC	A25P020M	SOP8	PA20SO20D-EO-210
AMIC	A25P020O	SOP8	PA16SO16D-EO-150
AMIC	A25P020Q1	USON8	HBP8USON48DB(2x3)
AMIC	A25P020Q4	WSON8	PA8SON8D(6x5)
AMIC	A25P040	DIP8	
AMIC	A25P040M	SOP8	PA20SO20D-EO-210
AMIC	A25P040O	SOP8	PA16SO16D-EO-150
AMIC	A25P040Q1	USON8	HBP8USON48DB(2x3)
AMIC	A25P040Q4	WSON8	PA8SON8D(6x5)
AMIC	A25P512	DIP8	
AMIC	A25P512M	SOP8	PA20SO20D-EO-210
AMIC	A25P512O	SOP8	PA16SO16D-EO-150

AMIC	A25P512Q1	USON8	HBP8USON48DB(2x3)
AMIC	A25P512Q4	WSON8	PA8SON8D(6x5)
AMIC	A25P512V	TSSOP8	PA8TSS8D
AMIC	A27020	DIP32	
AMIC	A27020	PLCC32	PA32PL32D
AMIC	A27020	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A27020L	DIP32	
AMIC	A27020L	PLCC32	PA32PL32D
AMIC	A27020L	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A276308A	DIP28	
AMIC	A276308AL	PLCC32	PA32PL28D-YA
AMIC	A290011AULU	PLCC32	PA32PL32D
AMIC	A290011T	DIP32	
AMIC	A290011T	PLCC32	PA32PL32D
AMIC	A290011T	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A290011U	DIP32	
AMIC	A290011U	PLCC32	PA32PL32D
AMIC	A290011U	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A29001T	DIP32	
AMIC	A29001T	PLCC32	PA32PL32D
AMIC	A29001T	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A29001U	DIP32	
AMIC	A29001U	PLCC32	PA32PL32D
AMIC	A29001U	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A290021T	DIP32	
AMIC	A290021T	PLCC32	PA32PL32D
AMIC	A290021T	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A290021U	DIP32	
AMIC	A290021U	PLCC32	PA32PL32D
AMIC	A290021U	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A29002T	DIP32	
AMIC	A29002T	PLCC32	PA32PL32D
AMIC	A29002T	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A29002U	DIP32	
AMIC	A29002U	PLCC32	PA32PL32D
AMIC	A29002U	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A29010	DIP32	
AMIC	A29010A	DIP32	
AMIC	A29010L	PLCC32	PA32PL32D
AMIC	A29010V	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A29040	DIP32	
AMIC	A29040A	DIP32	
AMIC	A29040AL	PLCC32	PA32PL32D
AMIC	A29040AV	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A29040B	DIP32	
AMIC	A29040BL	PLCC32	PA32PL32D
AMIC	A29040BV	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A29040CL	PLCC32	PA32PL32D
AMIC	A29040L	PLCC32	PA32PL32D
AMIC	A29040V	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A29160ATV	TSOP48	PA48TS48D
AMIC	A29160AUV	TSOP48	PA48TS48D
AMIC	A29160TV	TSOP48	PA48TS48D1
AMIC	A29160UV	TSOP48	PA48TS48D1
AMIC	A29400T	TSOP48	PA48TS48D
AMIC	A29400U	TSOP48	PA48TS48D
AMIC	A29512	DIP32	
AMIC	A29512A	DIP32	
AMIC	A29512A	PLCC32	PA32PL32D
AMIC	A29512A	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A29512L	PLCC32	PA32PL32D
AMIC	A29512V	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A29800ATV	TSOP48	PA48TS48D
AMIC	A29800TM	SOP44	PA44SO44D
AMIC	A29800TV	TSOP48	PA48TS48D
AMIC	A29800UM	SOP44	PA44SO44D
AMIC	A29800UV	TSOP48	PA48TS48D
AMIC	A29801AUV	TSOP48	PA48TS48D
AMIC	A29DL162TV	TSOP48	PA48TS48D1
AMIC	A29DL162UV	TSOP48	PA48TS48D1
AMIC	A29DL163TV	TSOP48	PA48TS48D1
AMIC	A29DL163UV	TSOP48	PA48TS48D1
AMIC	A29DL164TV	TSOP48	PA48TS48D1

AMIC	A29DL164UV	TSOP48	PA48TS48D1
AMIC	A29DL320FTV	TSOP48	PA48TS48D1
AMIC	A29DL320FUV	TSOP48	PA48TS48D1
AMIC	A29DL322TV	TSOP48	PA48TS48D1
AMIC	A29DL322UV	TSOP48	PA48TS48D1
AMIC	A29DL323TV	TSOP48	PA48TS48D1
AMIC	A29DL323UV	TSOP48	PA48TS48D1
AMIC	A29DL324TV	TSOP48	PA48TS48D1
AMIC	A29DL324UV	TSOP48	PA48TS48D1
AMIC	A29L004TL	PLCC32	PA32PL32D
AMIC	A29L004TV	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A29L004TW	TSOP40	PA40TS40D
AMIC	A29L004TX	TSOP32	PA32TS32D
AMIC	A29L004UL	PLCC32	PA32PL32D
AMIC	A29L004UV	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A29L004UW	TSOP40	PA40TS40D
AMIC	A29L004UX	TSOP32	PA32TS32D
AMIC	A29L008AUV	TSOP40	PA40TS40D
AMIC	A29L008TV	TSOP40	PA40TS40D
AMIC	A29L008UV	TSOP40	PA40TS40D
AMIC	A29L040L	PLCC32	PA32PL32D
AMIC	A29L040V	TSOP32	PA32TS20/PA32TS32D-20
AMIC	A29L040X	TSOP32	PA32TS32D
AMIC	A29L160ATM	SOP44	PA44SO44D
AMIC	A29L160ATV	TSOP48	PA48TS48D1
AMIC	A29L160AUM	SOP44	PA44SO44D
AMIC	A29L160AUV	TSOP48	PA48TS48D1
AMIC	A29L160BTM	SOP44	PA44SO44D
AMIC	A29L160BTV	TSOP48	PA48TS48D1
AMIC	A29L160BUM	SOP44	PA44SO44D
AMIC	A29L160BUV	TSOP48	PA48TS48D1
AMIC	A29L160FTV	TSOP48	PA48TS48D
AMIC	A29L160FUV	TSOP48	PA48TS48D
AMIC	A29L160HTM	SOP44	PA44SO44D
AMIC	A29L160HTV	TSOP48	PA48TS48D
AMIC	A29L160HUM	SOP44	PA44SO44D
AMIC	A29L160HUV	TSOP48	PA48TS48D
AMIC	A29L160TM	SOP44	PA44SO44D
AMIC	A29L160TV	TSOP48	PA48TS48D
AMIC	A29L160UM	SOP44	PA44SO44D
AMIC	A29L160UV	TSOP48	PA48TS48D
AMIC	A29L320ATV	TSOP48	PA48TS48D1
AMIC	A29L320AUV	TSOP48	PA48TS48D1
AMIC	A29L400ATM	SOP44	PA44SO44D
AMIC	A29L400ATV	TSOP48	PA48TS48D
AMIC	A29L400AUM	SOP44	PA44SO44D
AMIC	A29L400AUV	TSOP48	PA48TS48D
AMIC	A29L400TM	SOP44	PA44SO44D
AMIC	A29L400TV	TSOP48	PA48TS48D
AMIC	A29L400UM	SOP44	PA44SO44D
AMIC	A29L400UV	TSOP48	PA48TS48D
AMIC	A29L800ATM	SOP44	PA44SO44D
AMIC	A29L800ATV	TSOP48	PA48TS48D
AMIC	A29L800AUM	SOP44	PA44SO44D
AMIC	A29L800AUV	TSOP48	PA48TS48D
AMIC	A29L800HTM	SOP44	PA44SO44D
AMIC	A29L800HTV	TSOP48	PA48TS48D
AMIC	A29L800HUM	SOP44	PA44SO44D
AMIC	A29L800HUV	TSOP48	PA48TS48D
AMIC	A29L800MV	TSOP48	PA48TS48D
AMIC	A29L800TM	SOP44	PA44SO44D
AMIC	A29L800TV	TSOP48	PA48TS48D
AMIC	A29L800UM	SOP44	PA44SO44D
AMIC	A29L801TV	TSOP48	PA48TS48D1
AMIC	A29L801UV	TSOP48	PA48TS48D1
AMIC	A49LF004MTL	PLCC32	PA32PL32D
AMIC	A49LF004TL	PLCC32	PA32PL32D
AMIC	A49LF040ATL	PLCC32	PA32PL32D
AMIC	A49LF040ATL	TSOP32	PA32TS32D
AMIC	A49LF040TL	PLCC32	PA32PL32D
AMIC	A50FW040MTL	PLCC32	PA32PL32D
AMIC	A50FW040TL	PLCC32	PA32PL32D
AMIC	A50LPW040TL	PLCC32	PA32PL32D

ANACHIP	AM24LC02	DIP8	
ANACHIP	AM24LC02	SOIC8	PA8SO8D-EO-150
ANACHIP	AM24LC02	TSSOP8	PA8TSS8D
ANACHIP	AM24LC04	DIP8	
ANACHIP	AM24LC04	SOIC8	PA8SO8D-EO-150
ANACHIP	AM24LC04	TSSOP8	PA8TSS8D
ANACHIP	AM24LC08	DIP8	
ANACHIP	AM24LC08	SOIC8	PA8SO8D-EO-150
ANACHIP	AM24LC16	DIP8	
ANACHIP	AM24LC16	SOIC8	PA8SO8D-EO-150
ANACHIP	AM24LC21	DIP8	
ANACHIP	AM24LC21	SOIC8	PA8SO8D-EO-150
ANACHIP	AM24LC21B	DIP8	
ANACHIP	AM24LC21B	SOIC8	PA8SO8D-EO-150
ANACHIP	PEEL16CV8	DIP20	
ANACHIP	PEEL16CV8	PLCC20	PA20LC20D[Dead Bug]
ANACHIP	PEEL16CV8	SOIC20	PA28SO28D-EO-300
ANACHIP	PEEL16CV8	TSSOP20	PA24TSS24D
ANACHIP	PEEL18CV8	DIP20	
ANACHIP	PEEL18CV8	PLCC20	PA20LC20D[Dead Bug]
ANACHIP	PEEL18CV8	SOIC20	PA28SO28D-EO-300
ANACHIP	PEEL18CV8	TSSOP20	PA24TSS24D
ANACHIP	PEEL18CV8Z	DIP20	
ANACHIP	PEEL18CV8Z	PLCC20	PA20LC20D[Dead Bug]
ANACHIP	PEEL18CV8Z	SOIC20	PA28SO28D-EO-300
ANACHIP	PEEL18CV8Z	TSSOP20	PA24TSS24D
ANACHIP	PEEL18LV8Z	DIP20	
ANACHIP	PEEL18LV8Z	PLCC20	PA20LC20D[Dead Bug]
ANACHIP	PEEL18LV8Z	SOIC20	PA28SO28D-EO-300
ANACHIP	PEEL18LV8Z	TSSOP20	PA24TSS24D
ANACHIP	PEEL22CV10	DIP24	
ANACHIP	PEEL22CV10	PLCC28	PA28PL28D
ANACHIP	PEEL22CV10	SOIC24	PA28SO28D-EO-300
ANACHIP	PEEL22CV10	TSSOP24	PA24TSS24D
ANACHIP	PEEL22CV10A	DIP24	
ANACHIP	PEEL22CV10A	PLCC28	PA28PL28D
ANACHIP	PEEL22CV10A	SOIC24	PA28SO28D-EO-300
ANACHIP	PEEL22CV10A	TSSOP24	PA24TSS24D
ANACHIP	PEEL22CV10A+	DIP24	
ANACHIP	PEEL22CV10A+	PLCC28	PA28PL28D
ANACHIP	PEEL22CV10A+	SOIC24	PA28SO28D-EO-300
ANACHIP	PEEL22CV10A+	TSSOP24	PA24TSS24D
ANACHIP	PEEL22CV10A++	DIP24	
ANACHIP	PEEL22CV10A++	PLCC28	PA28PL28D
ANACHIP	PEEL22CV10A++	SOIC24	PA28SO28D-EO-300
ANACHIP	PEEL22CV10A++	TSSOP24	PA24TSS24D
ANACHIP	PEEL22CV10AZ	DIP24	
ANACHIP	PEEL22CV10AZ	PLCC28	PA28PL28D
ANACHIP	PEEL22CV10AZ	SOIC24	PA28SO28D-EO-300
ANACHIP	PEEL22CV10AZ	TSSOP24	PA24TSS24D
ANACHIP	PEEL22CV10AZ+	DIP24	
ANACHIP	PEEL22CV10AZ+	PLCC28	PA28PL28D
ANACHIP	PEEL22CV10AZ+	SOIC24	PA28SO28D-EO-300
ANACHIP	PEEL22CV10AZ+	TSSOP24	PA24TSS24D
ANACHIP	PEEL22CV10AZ++	DIP24	
ANACHIP	PEEL22CV10AZ++	PLCC28	PA28PL28D
ANACHIP	PEEL22CV10AZ++	SOIC24	PA28SO28D-EO-300
ANACHIP	PEEL22CV10AZ++	TSSOP24	PA24TSS24D
ANACHIP	PEEL22CV10Z	DIP24	
ANACHIP	PEEL22CV10Z	PLCC28	PA28PL28D
ANACHIP	PEEL22CV10Z	SOIC24	PA28SO28D-EO-300
ANACHIP	PEEL22CV10Z	TSSOP24	PA24TSS24D
APLUS FLASH TECH	24BC01	DIP8	
APLUS FLASH TECH	24BC01	SOIC8	PA8SO8D-EO-150
APLUS FLASH TECH	24BC01	TSSOP8	PA24TSS24D
APLUS FLASH TECH	24BC01	TSSOP8	PA8TSS8D
APLUS FLASH TECH	24BC02	DIP8	
APLUS FLASH TECH	24BC02	SOIC8	PA8SO8D-EO-150
APLUS FLASH TECH	24BC02	TSSOP8	PA24TSS24D
APLUS FLASH TECH	24BC02	TSSOP8	PA8TSS8D
APLUS FLASH TECH	24BC04	DIP8	
APLUS FLASH TECH	24BC04	SOIC8	PA8SO8D-EO-150
APLUS FLASH TECH	24BC04	TSSOP8	PA24TSS24D

APLUS FLASH TECH	24BC04	TSSOP8	PA8TSS8D
APLUS FLASH TECH	24BC08	DIP8	
APLUS FLASH TECH	24BC08	SOIC8	PA8SO8D-EO-150
APLUS FLASH TECH	24BC08	TSSOP8	PA24TSS24D
APLUS FLASH TECH	24BC08	TSSOP8	PA8TSS8D
APLUS FLASH TECH	24BC16	DIP8	
APLUS FLASH TECH	24BC16	SOIC8	PA8SO8D-EO-150
APLUS FLASH TECH	24BC16	TSSOP8	PA24TSS24D
APLUS FLASH TECH	24BC16	TSSOP8	PA8TSS8D
APLUS FLASH TECH	24BC32	DIP8	
APLUS FLASH TECH	24BC32	SOIC8	PA8SO8D-EO-150
APLUS FLASH TECH	24BC32	TSSOP8	PA24TSS24D
APLUS FLASH TECH	24BC32	TSSOP8	PA8TSS8D
APLUS FLASH TECH	24BC64	DIP8	
APLUS FLASH TECH	24BC64	SOIC8	PA8SO8D-EO-150
APLUS FLASH TECH	24BC64	TSSOP8	PA24TSS24D
APLUS FLASH TECH	24BC64	TSSOP8	PA8TSS8D
ASAHI KASEI(AKM)	AK6002A	SOIC8	PA8SO8D-EO-150
ASAHI KASEI(AKM)	AK6002A	TSSOP8	PA24TSS24D
ASAHI KASEI(AKM)	AK6002A	TSSOP8	PA8TSS8D
ASAHI KASEI(AKM)	AK6003A	TSSOP8	PA24TSS24D
ASAHI KASEI(AKM)	AK6003A	TSSOP8	PA8TSS8D
ASAHI KASEI(AKM)	AK6004A	SOIC8	PA8SO8D-EO-150
ASAHI KASEI(AKM)	AK6004A	SSOP8	PA8SS8D
ASAHI KASEI(AKM)	AK6008A	SOIC8	PA8SO8D-EO-150
ASAHI KASEI(AKM)	AK6010A	SOIC8	PA8SO8D-EO-150
ASAHI KASEI(AKM)	AK6012A	SOIC8	PA8SO8D-EO-150
ASAHI KASEI(AKM)	AK93C10AF	SOIC8	PA16SO16D-EO-150
ASAHI KASEI(AKM)	AK93C85AM	SSOP8	PA8TSS-OT
ASAHI KASEI(AKM)	AK93C95AF	SOIC8	PA16SO16D-EO-150
ATC	AM24LC02	DIP8	
ATC	AM24LC02	SOIC8	PA8SO8D-EO-150
ATC	AM24LC02	TSSOP8	PA24TSS24D
ATC	AM24LC02	TSSOP8	PA8TSS8D
ATC	AM24LC04	DIP8	
ATC	AM24LC04	SOIC8	PA8SO8D-EO-150
ATC	AM24LC04	TSSOP8	PA24TSS24D
ATC	AM24LC04	TSSOP8	PA8TSS8D
ATC	AM24LC08	DIP8	
ATC	AM24LC08	SOIC8	PA8SO8D-EO-150
ATC	AM24LC16	DIP8	
ATC	AM24LC16	SOIC8	PA8SO8D-EO-150
ATC	AM24LC21	DIP8	
ATC	AM24LC21	SOIC8	PA8SO8D-EO-150
ATC	AM24LC21B	DIP8	
ATC	AM24LC21B	SOIC8	PA8SO8D-EO-150
ATMEL	AT17C002	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17C002	PLCC44	PA44-48U
ATMEL	AT17C002	QFP44	PA44QF44D
ATMEL	AT17C002A	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17C002A	PLCC44	PA44-48U
ATMEL	AT17C002A	QFP44	PA44QF44D
ATMEL	AT17C010	DIP8	
ATMEL	AT17C010	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17C010A	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17C020	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17C020A	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17C040	PLCC44	PA44-48U
ATMEL	AT17C040	QFP44	PA44QF44D
ATMEL	AT17C040A	PLCC44	PA44-48U
ATMEL	AT17C040A	QFP44	PA44QF44D
ATMEL	AT17C128	DIP8	
ATMEL	AT17C128	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17C128A	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17C256	DIP8	
ATMEL	AT17C256	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17C256A	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17C512	DIP8	
ATMEL	AT17C512	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17C512A	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17C65	DIP8	
ATMEL	AT17C65	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17C65	SOIC20	PA28SO28D-EO-300



ATMEL	AT17C65A	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17F040	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17F040A	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17F080	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17F080	PLCC44	PA44-48U
ATMEL	AT17F080	QFP44	PA44QF44D
ATMEL	AT17F080A	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17LV002	LAP8	PA8SON8DB
ATMEL	AT17LV002	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17LV002	PLCC44	PA44-48U
ATMEL	AT17LV002	QFP44	PA44QF44D
ATMEL	AT17LV002	SOIC20	PA28SO28D-EO-300
ATMEL	AT17LV002A	LAP8	PA8SON8DB
ATMEL	AT17LV002A	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17LV002A	PLCC44	PA44-48U
ATMEL	AT17LV002A	QFP44	PA44QF44D
ATMEL	AT17LV010	DIP8	
ATMEL	AT17LV010	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17LV010	SOIC20	PA28SO28D-EO-300
ATMEL	AT17LV010A	DIP8	
ATMEL	AT17LV010A	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17LV020	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17LV020A	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17LV040	PLCC44	PA44-48U
ATMEL	AT17LV040	QFP44	PA44QF44D
ATMEL	AT17LV040A	PLCC44	PA44-48U
ATMEL	AT17LV040A	QFP44	PA44QF44D
ATMEL	AT17LV128	DIP8	
ATMEL	AT17LV128	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17LV128	SOIC20	PA28SO28D-EO-300
ATMEL	AT17LV128A	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17LV256	DIP8	
ATMEL	AT17LV256	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17LV256	SOIC20	PA28SO28D-EO-300
ATMEL	AT17LV256A	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17LV512	DIP8	
ATMEL	AT17LV512	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17LV512	SOIC20	PA28SO28D-EO-300
ATMEL	AT17LV512A	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17LV65	DIP8	
ATMEL	AT17LV65	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17LV65	SOIC20	PA28SO28D-EO-300
ATMEL	AT17LV65A	PLCC20	PA20LC20D[Dead Bug]
ATMEL	AT17N002	LAP8	PA8LAP8D-EO-230
ATMEL	AT17N002	QFP44	PA44QF44D
ATMEL	AT17N002	SOIC20	PA28SO28D-EO-300
ATMEL	AT17N010	DIP8	
ATMEL	AT17N010	LAP8	PA8LAP8D-EO-230
ATMEL	AT17N010	SOIC20	PA28SO28D-EO-300
ATMEL	AT17N040	QFP44	PA44QF44D
ATMEL	AT17N256	DIP8	
ATMEL	AT17N256	SOIC20	PA28SO28D-EO-300
ATMEL	AT17N256	SOIC8	PA16SO16D-EO-150
ATMEL	AT17N512	DIP8	
ATMEL	AT17N512	LAP8	PA8LAP8D-EO-230
ATMEL	AT17N512	SOIC20	PA28SO28D-EO-300
ATMEL	AT22LV10	DIP24	
ATMEL	AT22LV10	PLCC28	PA28PL24D2P6-YA
ATMEL	AT22LV10	SOIC24	PA28SO28D-EO-300
ATMEL	AT22LV10L	DIP24	
ATMEL	AT22LV10L	PLCC28	PA28PL24D2P6-YA
ATMEL	AT22LV10L	SOIC24	PA28SO28D-EO-300
ATMEL	AT22V10	DIP24	
ATMEL	AT22V10	PLCC28	PA28PL24D2P6-YA
ATMEL	AT22V10	SOIC24	PA28SO28D-EO-300
ATMEL	AT22V10B	DIP24	
ATMEL	AT22V10B	PLCC28	PA28PL24D2P6-YA
ATMEL	AT22V10B	SOIC24	PA28SO28D-EO-300
ATMEL	AT22V10BL	DIP24	
ATMEL	AT22V10BL	PLCC28	PA28PL24D2P6-YA
ATMEL	AT22V10BL	SOIC24	PA28SO28D-EO-300
ATMEL	AT22V10L	DIP24	
ATMEL	AT22V10L	PLCC28	PA28PL24D2P6-YA

ATMEL	AT22V10L	SOIC24	PA28SO28D-EO-300
ATMEL	AT24C01	DIP8	
ATMEL	AT24C01	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C01	TSSOP8	PA24TSS24D
ATMEL	AT24C01	TSSOP8	PA8TSS8D
ATMEL	AT24C01A	dBGA8	PA8DBGA8D
ATMEL	AT24C01A	DIP8	
ATMEL	AT24C01A	MAP8	PA8MAP8
ATMEL	AT24C01A	SCM8	PA5SOT5D
ATMEL	AT24C01A	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C01A	TSSOP8	PA24TSS24D
ATMEL	AT24C01A	TSSOP8	PA8TSS8D
ATMEL	AT24C01ASC-E	SCM8	PA8SCM8D
ATMEL	AT24C01ASC-G	SCM8	PA8SCM8D
ATMEL	AT24C01ASC-H	SCM8	PA8SCM8D
ATMEL	AT24C01ASC-P	SCM8	PA8SCM8D
ATMEL	AT24C01ASC-W	SCM8	PA8SCM8D
ATMEL	AT24C02	dBGA8	PA8DBGA8D
ATMEL	AT24C02	DIP8	
ATMEL	AT24C02	MAP8	PA8MAP8
ATMEL	AT24C02	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C02	SOT23-5	PA5SOT5D
ATMEL	AT24C02	TSSOP8	PA24TSS24D
ATMEL	AT24C02	TSSOP8	PA8TSS8D
ATMEL	AT24C02A	DIP8	
ATMEL	AT24C02A	MAP8	PA8MAP8
ATMEL	AT24C02A	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C02A	TSSOP8	PA24TSS24D
ATMEL	AT24C02A	TSSOP8	PA8TSS8D
ATMEL	AT24C02SC-E	SCM8	PA8SCM8D
ATMEL	AT24C02SC-P	SCM8	PA8SCM8D
ATMEL	AT24C02SC-W	SCM8	PA8SCM8D
ATMEL	AT24C04	dBGA8	PA8DBGA8D
ATMEL	AT24C04	DIP8	
ATMEL	AT24C04	MAP8	PA8MAP8
ATMEL	AT24C04	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C04	SOT23-5	PA5SOT5D
ATMEL	AT24C04	TSSOP8	PA24TSS24D
ATMEL	AT24C04	TSSOP8	PA8TSS8D
ATMEL	AT24C04A	DIP8	
ATMEL	AT24C04A	MAP8	PA8MAP8
ATMEL	AT24C04A	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C04A	TSSOP8	PA24TSS24D
ATMEL	AT24C04A	TSSOP8	PA8TSS8D
ATMEL	AT24C04SC-E	SCM8	PA8SCM8D
ATMEL	AT24C04SC-P	SCM8	PA8SCM8D
ATMEL	AT24C04SC-W	SCM8	PA8SCM8D
ATMEL	AT24C08	dBGA8	PA8DBGA8D
ATMEL	AT24C08	DIP8	
ATMEL	AT24C08	MAP8	PA8MAP8
ATMEL	AT24C08	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C08	SOT23-5	PA5SOT5D
ATMEL	AT24C08	TSSOP8	PA24TSS24D
ATMEL	AT24C08	TSSOP8	PA8TSS8D
ATMEL	AT24C08A	DIP8	
ATMEL	AT24C08A	MAP8	PA8MAP8
ATMEL	AT24C08A	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C08A	TSSOP8	PA24TSS24D
ATMEL	AT24C08A	TSSOP8	PA8TSS8D
ATMEL	AT24C08SC-E	SCM8	PA8SCM8D
ATMEL	AT24C08SC-P	SCM8	PA8SCM8D
ATMEL	AT24C08SC-W	SCM8	PA8SCM8D
ATMEL	AT24C1024	dBGA8	PA8DBGA8D
ATMEL	AT24C1024	DIP8	
ATMEL	AT24C1024	LAP8	PA8LAP8D-EO-230
ATMEL	AT24C1024	LAP8	PA8LAP8D-EO-300
ATMEL	AT24C1024	LAP8	PA8MAP8
ATMEL	AT24C1024	SOIC8	PA16SO16D-EO-150
ATMEL	AT24C1024W	SOIC8	PA20SO20D-EO-210
ATMEL	AT24C128	DIP8	
ATMEL	AT24C128	TSSOP8	PA24TSS24D
ATMEL	AT24C128-1.8V	dBGA8	PA8DBGA8D
ATMEL	AT24C128-1.8V	SOIC8	PA8SO8D-EO-150

ATMEL	AT24C128-1.8V	TSSOP14	PA28TSS28D-EO
ATMEL	AT24C128-5V	dBGA8	PA8DBGA8D
ATMEL	AT24C128-5V	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C128-5V	TSSOP14	PA28TSS28D-EO
ATMEL	AT24C16	dBGA8	PA8DBGA8D
ATMEL	AT24C16	DIP8	
ATMEL	AT24C16	MAP8	PA8MAP8
ATMEL	AT24C16	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C16	SOT23-5	PA5SOT5D
ATMEL	AT24C16	TSSOP8	PA24TSS24D
ATMEL	AT24C16	TSSOP8	PA8TSS8D
ATMEL	AT24C164	DIP8	
ATMEL	AT24C164	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C16A	DIP8	
ATMEL	AT24C16A	MAP8	PA8MAP8
ATMEL	AT24C16A	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C16A	TSSOP8	PA24TSS24D
ATMEL	AT24C16A	TSSOP8	PA8TSS8D
ATMEL	AT24C16C-PUM	DIP8	
ATMEL	AT24C16C-SSHMT	SOIC8	PA16SO16D-EO-150
ATMEL	AT24C16D-SSHMT	SOIC8	PA16SO16D-EO-150
ATMEL	AT24C16SC-E	SCM8	PA8SCM8D
ATMEL	AT24C16SC-P	SCM8	PA8SCM8D
ATMEL	AT24C16SC-W	SCM8	PA8SCM8D
ATMEL	AT24C256	DIP8	
ATMEL	AT24C256	TSSOP8	PA24TSS24D
ATMEL	AT24C256-1.8V	dBGA8	PA8DBGA8D
ATMEL	AT24C256-1.8V	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C256-1.8V	TSSOP14	PA28TSS28D-EO
ATMEL	AT24C256-5V	dBGA8	PA8DBGA8D
ATMEL	AT24C256-5V	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C256-5V	TSSOP14	PA28TSS28D-EO
ATMEL	AT24C256B	DIP8	
ATMEL	AT24C256B	TSSOP8	PA24TSS24D
ATMEL	AT24C256BN	SOIC8	PA16SO16D-EO-150
ATMEL	AT24C256C-X	TSSOP8	PA24TSS24D
ATMEL	AT24C256N	SOIC8	PA16SO16D-EO-150
ATMEL	AT24C32	DIP8	
ATMEL	AT24C32	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C32	TSSOP8	PA24TSS24D
ATMEL	AT24C32	TSSOP8	PA8TSS8D
ATMEL	AT24C32A	DIP8	
ATMEL	AT24C32A	MAP8	PA8MAP8
ATMEL	AT24C32A	SOIC8	PA16SO16D-EO-150
ATMEL	AT24C32A	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C32A	TSSOP8	PA24TSS24D
ATMEL	AT24C32A	TSSOP8	PA8TSS8D
ATMEL	AT24C32B	DIP8	
ATMEL	AT24C32B	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C32B	TSSOP8	PA24TSS24D
ATMEL	AT24C32B	TSSOP8	PA8TSS8D
ATMEL	AT24C512	DIP8	
ATMEL	AT24C512	TSSOP8	PA24TSS24D
ATMEL	AT24C512-1.8V	dBGA8	PA8DBGA8D
ATMEL	AT24C512-1.8V	LAP8	PA8LAP8D-EO-230
ATMEL	AT24C512-1.8V	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C512-5V	dBGA8	PA8DBGA8D
ATMEL	AT24C512-5V	LAP8	PA8LAP8D-EO-230
ATMEL	AT24C512-5V	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C64	DIP8	
ATMEL	AT24C64	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C64	TSSOP8	PA24TSS24D
ATMEL	AT24C64	TSSOP8	PA8TSS8D
ATMEL	AT24C64A	DIP8	
ATMEL	AT24C64A	MAP8	PA8MAP8
ATMEL	AT24C64A	SOIC8	PA16SO16D-EO-150
ATMEL	AT24C64A	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C64A	TSSOP8	PA24TSS24D
ATMEL	AT24C64A	TSSOP8	PA8TSS8D
ATMEL	AT24C64B	DIP8	
ATMEL	AT24C64B	SOIC8	PA8SO8D-EO-150
ATMEL	AT24C64B	TSSOP8	PA24TSS24D
ATMEL	AT24C64B	TSSOP8	PA8TSS8D

ATMEL	AT24C64D-X	TSSOP8	PA24TSS24D
ATMEL	AT24CM01	SOIC8	PA16SO16D-EO-150
ATMEL	AT24CS128	DIP8	
ATMEL	AT24CS128-1.8V	SOIC8	PA16SO16D-EO-150
ATMEL	AT24CS128-1.8V	SOIC8	PA8SO8D-EO-150
ATMEL	AT24CS128-2.7:5V	SOIC8	PA16SO16D-EO-150
ATMEL	AT24CS128-2.7:5V	SOIC8	PA8SO8D-EO-150
ATMEL	AT24CS256	DIP8	
ATMEL	AT24CS256-1.8V	SOIC8	PA16SO16D-EO-150
ATMEL	AT24CS256-1.8V	SOIC8	PA8SO8D-EO-150
ATMEL	AT24CS256-2.7:5V	SOIC8	PA16SO16D-EO-150
ATMEL	AT24CS256-2.7:5V	SOIC8	PA8SO8D-EO-150
ATMEL	AT24HC02C	SOIC8	PA16SO16D-EO-150
ATMEL	AT24RF08CN	SOIC8	PA16SO16D-EO-150
ATMEL	AT24RF08CT	TSSOP14	PA24TSS24D
ATMEL	AT25010	DIP8	
ATMEL	AT25010	SOIC8	PA16SO16D-EO-150
ATMEL	AT25010A	DIP8	
ATMEL	AT25010A	MAP8	PA8MAP8
ATMEL	AT25010A	SOIC8	PA16SO16D-EO-150
ATMEL	AT25010A	TSSOP8	PA24TSS24D
ATMEL	AT25020	DIP8	
ATMEL	AT25020	SOIC8	PA16SO16D-EO-150
ATMEL	AT25020A	DIP8	
ATMEL	AT25020A	MAP8	PA8MAP8
ATMEL	AT25020A	SOIC8	PA16SO16D-EO-150
ATMEL	AT25020A	TSSOP8	PA24TSS24D
ATMEL	AT25040	DIP8	
ATMEL	AT25040	SOIC8	PA16SO16D-EO-150
ATMEL	AT25040A	DIP8	
ATMEL	AT25040A	MAP8	PA8MAP8
ATMEL	AT25040A	SOIC8	PA16SO16D-EO-150
ATMEL	AT25040A	TSSOP8	PA24TSS24D
ATMEL	AT25080	DIP8	
ATMEL	AT25080	SOIC8	PA16SO16D-EO-150
ATMEL	AT25080	TSSOP14	PA14TSS14D
ATMEL	AT25080	TSSOP20	PA20TSS20D
ATMEL	AT25080(1.8)	DIP8	
ATMEL	AT25080(1.8)	SOIC8	PA16SO16D-EO-150
ATMEL	AT25080(1.8)	TSSOP14	PA14TSS14D
ATMEL	AT25080(1.8)	TSSOP20	PA20TSS20D
ATMEL	AT25080A	DIP8	
ATMEL	AT25080A	MAP8	PA8MAP8
ATMEL	AT25080A	SOIC8	PA16SO16D-EO-150
ATMEL	AT25080A	TSSOP8	PA24TSS24D
ATMEL	AT25128	DIP8	
ATMEL	AT25128	LAP8	PA8MAP8
ATMEL	AT25128	SOIC16	PA16SO16D-1
ATMEL	AT25128	SOIC8	PA16SO16D-EO-150
ATMEL	AT25128	TSSOP14	PA14TSS14D
ATMEL	AT25128	TSSOP20	PA20TSS20D
ATMEL	AT25128(1.8)	DIP8	
ATMEL	AT25128(1.8)	LAP8	PA8MAP8
ATMEL	AT25128(1.8)	SOIC16	PA16SO16D-1
ATMEL	AT25128(1.8)	SOIC8	PA16SO16D-EO-150
ATMEL	AT25128(1.8)	TSSOP14	PA14TSS14D
ATMEL	AT25128(1.8)	TSSOP20	PA20TSS20D
ATMEL	AT25128A	BGA8	HA8BG48D
ATMEL	AT25128A	DIP8	
ATMEL	AT25128A	MAP8	PA8MAP8
ATMEL	AT25128A	SOIC8	PA16SO16D-EO-150
ATMEL	AT25128A	TSSOP8	PA24TSS24D
ATMEL	AT25160	DIP8	
ATMEL	AT25160	SOIC8	PA16SO16D-EO-150
ATMEL	AT25160	TSSOP14	PA14TSS14D
ATMEL	AT25160	TSSOP20	PA20TSS20D
ATMEL	AT25160(1.8)	DIP8	
ATMEL	AT25160(1.8)	SOIC8	PA16SO16D-EO-150
ATMEL	AT25160(1.8)	TSSOP14	PA14TSS14D
ATMEL	AT25160(1.8)	TSSOP20	PA20TSS20D
ATMEL	AT25160A	DIP8	
ATMEL	AT25160A	MAP8	PA8MAP8
ATMEL	AT25160A	SOIC8	PA16SO16D-EO-150

ATMEL	AT25160A	TSSOP8	PA24TSS24D
ATMEL	AT25256	DIP8	
ATMEL	AT25256	LAP8	PA8MAP8
ATMEL	AT25256	SOIC16	PA16SO16D-1
ATMEL	AT25256	SOIC8	PA16SO16D-EO-150
ATMEL	AT25256	TSSOP14	PA14TSS14D
ATMEL	AT25256	TSSOP20	PA20TSS20D
ATMEL	AT25256(1.8)	DIP8	
ATMEL	AT25256(1.8)	LAP8	PA8MAP8
ATMEL	AT25256(1.8)	SOIC16	PA16SO16D-1
ATMEL	AT25256(1.8)	SOIC8	PA16SO16D-EO-150
ATMEL	AT25256(1.8)	TSSOP14	PA14TSS14D
ATMEL	AT25256(1.8)	TSSOP20	PA20TSS20D
ATMEL	AT25256A	BGA8	HA8BG48D
ATMEL	AT25256A	DIP8	
ATMEL	AT25256A	MAP8	PA8MAP8
ATMEL	AT25256A	SOIC8	PA16SO16D-EO-150
ATMEL	AT25256A	TSSOP8	PA24TSS24D
ATMEL	AT25320	DIP8	
ATMEL	AT25320	SOIC8	PA16SO16D-EO-150
ATMEL	AT25320	TSSOP14	PA14TSS14D
ATMEL	AT25320	TSSOP20	PA20TSS20D
ATMEL	AT25320(1.8)	DIP8	
ATMEL	AT25320(1.8)	SOIC8	PA16SO16D-EO-150
ATMEL	AT25320(1.8)	TSSOP14	PA14TSS14D
ATMEL	AT25320(1.8)	TSSOP20	PA20TSS20D
ATMEL	AT25320A	DIP8	
ATMEL	AT25320A	MAP8	PA8MAP8
ATMEL	AT25320A	SOIC8	PA16SO16D-EO-150
ATMEL	AT25320A	TSSOP8	PA24TSS24D
ATMEL	AT25320A(QF4A512)	LQFP32	HA32LQ48DA
ATMEL	AT25640	DIP8	
ATMEL	AT25640	SOIC8	PA16SO16D-EO-150
ATMEL	AT25640	TSSOP14	PA14TSS14D
ATMEL	AT25640	TSSOP20	PA20TSS20D
ATMEL	AT25640(1.8)	DIP8	
ATMEL	AT25640(1.8)	SOIC8	PA16SO16D-EO-150
ATMEL	AT25640(1.8)	TSSOP14	PA14TSS14D
ATMEL	AT25640(1.8)	TSSOP20	PA20TSS20D
ATMEL	AT25640A	DIP8	
ATMEL	AT25640A	MAP8	PA8MAP8
ATMEL	AT25640A	SOIC8	PA16SO16D-EO-150
ATMEL	AT25640A	TSSOP8	PA24TSS24D
ATMEL	AT25DF021	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ATMEL	AT25DF021	UDFN8	PA8SON8D(6x5)
ATMEL	AT25DF041A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ATMEL	AT25DF041A	SOIC8	PA20SO20D-EO-210
ATMEL	AT25DF041A	UDFN8	PA8SON8D(6x5)
ATMEL	AT25DF081	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ATMEL	AT25DF081	SOIC8	PA20SO20D-EO-210
ATMEL	AT25DF081	UDFN8	PA8SON8D(6x5)
ATMEL	AT25DF081A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ATMEL	AT25DF081A	SOIC8	PA20SO20D-EO-210
ATMEL	AT25DF081A	UDFN8	PA8SON8D(6x5)
ATMEL	AT25DF161	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ATMEL	AT25DF161	SOIC8	PA20SO20D-EO-210
ATMEL	AT25DF161	UDFN8	PA8SON8D(6x5)
ATMEL	AT25DF321	SOIC16	PA28SO28D-EO-300
ATMEL	AT25DF321	SOIC8	PA20SO20D-EO-210
ATMEL	AT25DF321A	SOIC8	PA20SO20D-EO-210
ATMEL	AT25DF321A	UDFN8	PA8SON8D(6x5)
ATMEL	AT25DF641	SOIC16	PA28SO28D-EO-300
ATMEL	AT25DF641	VDFN8	PA8SON8DA(8x6)
ATMEL	AT25DF641A	SOIC8	PA20SO20D-EO-210
ATMEL	AT25DF641A	UDFN8	PA8SON8D(6x5)
ATMEL	AT25F1024	DIP8	
ATMEL	AT25F1024	QFN8	PA8SON8D(6x5)
ATMEL	AT25F1024	SOIC8	PA16SO16D-EO-150
ATMEL	AT25F2048	SOIC8	PA16SO16D-EO-150
ATMEL	AT25F4096	SOIC8	PA20SO20D-EO-210
ATMEL	AT25F512	QFN8	PA8SON8D(6x5)
ATMEL	AT25F512	SOIC8	PA16SO16D-EO-150
ATMEL	AT25F512A	QFN8	PA8SON8D(6x5)

ATMEL	AT25F512A	SOIC8	PA16SO16D-EO-150
ATMEL	AT25F512B	QFN8	PA8SON8D(6x5)
ATMEL	AT25F512B	SOIC8	PA16SO16D-EO-150
ATMEL	AT25FS010	SOIC8	PA16SO16D-EO-150
ATMEL	AT25FS040	SOIC8	PA16SO16D-EO-150
ATMEL	AT25HP256	DIP8	
ATMEL	AT25HP256	LAP8	PA8MAP8
ATMEL	AT25HP256	SOIC8	PA16SO16D-EO-150
ATMEL	AT25HP256(1.8)	DIP8	
ATMEL	AT25HP256(1.8)	LAP8	PA8MAP8
ATMEL	AT25HP256(1.8)	SOIC8	PA16SO16D-EO-150
ATMEL	AT25HP512	DIP8	
ATMEL	AT25HP512	LAP8	PA8MAP8
ATMEL	AT25HP512	SOIC8	PA16SO16D-EO-150
ATMEL	AT25HP512(1.8)	DIP8	
ATMEL	AT25HP512(1.8)	LAP8	PA8MAP8
ATMEL	AT25HP512(1.8)	SOIC8	PA16SO16D-EO-150
ATMEL	AT25P1024	LAP8	PA8MAP8
ATMEL	AT25P1024	SOIC20	PA28SO28D-EO-300
ATMEL	AT25P1024(1.8)	LAP8	PA8MAP8
ATMEL	AT25P1024(1.8)	SOIC20	PA28SO28D-EO-300
ATMEL	AT26DF081	MLF8	PA8SON8D(6x5)
ATMEL	AT26DF081	SOIC8	PA20SO20D-EO-210
ATMEL	AT26DF081A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ATMEL	AT26DF081A	SOIC8	PA20SO20D-EO-210
ATMEL	AT26DF161	SOIC8	PA20SO20D-EO-210
ATMEL	AT26DF161A	MLF8	PA8SON8D(6x5)
ATMEL	AT26DF161A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ATMEL	AT26DF161A	SOIC8	PA20SO20D-EO-210
ATMEL	AT26DF321	SOIC16	PA28SO28D-EO-300
ATMEL	AT26DF321	SOIC8	PA20SO20D-EO-210
ATMEL	AT26F004	MLF8	PA8SON8D(6x5)
ATMEL	AT26F004	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ATMEL	AT26F004	SOIC8	PA20SO20D-EO-210
ATMEL	AT27BV010	DIP32	
ATMEL	AT27BV010	PLCC32	PA32PL32D
ATMEL	AT27BV010	sTSOP32	PA32TS32D
ATMEL	AT27BV010	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT27BV020	DIP32	
ATMEL	AT27BV020	PLCC32	PA32PL32D
ATMEL	AT27BV020	sTSOP32	PA32TS32D
ATMEL	AT27BV020	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT27BV040	DIP32	
ATMEL	AT27BV1024	DIP40	
ATMEL	AT27BV1024	PLCC44	PA44-48U
ATMEL	AT27BV1024	TSOP40	PA40TS40D
ATMEL	AT27BV256	DIP28	
ATMEL	AT27BV256	PLCC32	PA32PL28D-YA
ATMEL	AT27BV256	SOIC28	PA28SO28D-EO-300
ATMEL	AT27BV256	TSOP28	PA28TS28D-EO
ATMEL	AT27BV4096	DIP40	
ATMEL	AT27BV4096	PLCC44	PA44-48U
ATMEL	AT27BV4096	TSOP40	PA40TS40D
ATMEL	AT27BV512	DIP28	
ATMEL	AT27BV512	PLCC32	PA32PL28D-YA
ATMEL	AT27BV512	SOIC28	PA28SO28D-EO-300
ATMEL	AT27BV512	TSOP28	PA28TS28D-EO
ATMEL	AT27BV800	PLCC44	PA44-48U
ATMEL	AT27BV800	SOP44	PA44SO44D
ATMEL	AT27C010	DIP32	
ATMEL	AT27C010	PLCC32	PA32PL32D
ATMEL	AT27C010	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT27C010L	DIP32	
ATMEL	AT27C010L	PLCC32	PA32PL32D
ATMEL	AT27C010L	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT27C020	DIP32	
ATMEL	AT27C020	PLCC32	PA32PL32D
ATMEL	AT27C020	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT27C040	DIP32	
ATMEL	AT27C040	PLCC32	PA32PL32D
ATMEL	AT27C040	SOIC32	PA32SO32D-EO-450
ATMEL	AT27C040	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT27C080	DIP32	

ATMEL	AT27C080	PLCC32	PA32PL32D
ATMEL	AT27C080	SOIC32	PA32SO32D-EO-450
ATMEL	AT27C080	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT27C1024	DIP40	
ATMEL	AT27C1024	PLCC44	PA44-48U
ATMEL	AT27C1024	TSOP40	PA40TS40D
ATMEL	AT27C1024L	DIP40	
ATMEL	AT27C1024L	PLCC44	PA44-48U
ATMEL	AT27C1024L	TSOP40	PA40TS40D
ATMEL	AT27C128	DIP28	
ATMEL	AT27C128	PLCC32	PA32PL28D-YA
ATMEL	AT27C2048	DIP40	
ATMEL	AT27C2048	PLCC44	PA44-48U
ATMEL	AT27C2048	TSOP40	PA40TS40D
ATMEL	AT27C256	DIP28	
ATMEL	AT27C256	PLCC32	PA32PL28D-YA
ATMEL	AT27C256R	DIP28	
ATMEL	AT27C256R	PLCC32	PA32PL28D-YA
ATMEL	AT27C256R	SOIC28	PA28SO28DB-EC-350
ATMEL	AT27C256R	TSOP28	PA28TS28D-EO
ATMEL	AT27C400	DIP40	
ATMEL	AT27C400	SOP40	PA40SO40D-EO-450
ATMEL	AT27C400	TSOP48	PA48TS48D
ATMEL	AT27C4096	DIP40	
ATMEL	AT27C4096	PLCC44	PA44-48U
ATMEL	AT27C4096	TSOP40	PA40TS40D
ATMEL	AT27C512	DIP28	
ATMEL	AT27C512	PLCC32	PA32PL28D-YA
ATMEL	AT27C512	SOIC28	PA28SO28D-EO-300
ATMEL	AT27C512	TSOP28	PA28TS28D-EO
ATMEL	AT27C512R	DIP28	
ATMEL	AT27C512R	PLCC32	PA32PL28D-YA
ATMEL	AT27C512R	SOIC28	PA28SO28D-EO-300
ATMEL	AT27C512R	TSOP28	PA28TS28D-EO
ATMEL	AT27C513	DIP28	
ATMEL	AT27C513R	DIP28	
ATMEL	AT27C516	DIP40	
ATMEL	AT27C516	PLCC44	PA44-48U
ATMEL	AT27C516	TSOP40	PA40TS40D
ATMEL	AT27C520	SOIC20	PA28SO-08(C)
ATMEL	AT27C520	TSOP20	PA24TSS24D
ATMEL	AT27C64	DIP28	
ATMEL	AT27C64	PLCC32	PA32PL28D-YA
ATMEL	AT27C800	DIP42	
ATMEL	AT27C800	PLCC44	PA44-48U
ATMEL	AT27C800	SOP44	PA44SO44D
ATMEL	AT27C8192	DIP42	
ATMEL	AT27C8192	SOP44	PA44SO44D
ATMEL	AT27HC1024	DIP40	
ATMEL	AT27HC1024	PLCC44	PA44-48U
ATMEL	AT27HC256	DIP28	
ATMEL	AT27HC256	PLCC32	PA32PL28D-YA
ATMEL	AT27HC256R	DIP28	
ATMEL	AT27HC256R	PLCC32	PA32PL28D-YA
ATMEL	AT27HC64	DIP28	
ATMEL	AT27HC64	PLCC32	PA32PL28D-YA
ATMEL	AT27HC64L	DIP28	
ATMEL	AT27HC64L	PLCC32	PA32PL28D-YA
ATMEL	AT27LV010	DIP32	
ATMEL	AT27LV010	PLCC32	PA32PL32D
ATMEL	AT27LV010	sTSOP32	PA32TS32D
ATMEL	AT27LV010	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT27LV010A	DIP32	
ATMEL	AT27LV010A	PLCC32	PA32PL32D
ATMEL	AT27LV010A	sTSOP32	PA32TS32D
ATMEL	AT27LV010A	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT27LV010AL	DIP32	
ATMEL	AT27LV010AL	PLCC32	PA32PL32D
ATMEL	AT27LV010AL	sTSOP32	PA32TS32D
ATMEL	AT27LV010AL	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT27LV020	DIP32	
ATMEL	AT27LV020	PLCC32	PA32PL32D
ATMEL	AT27LV020	sTSOP32	PA32TS32D

ATMEL	AT27LV020	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT27LV020A	DIP32	
ATMEL	AT27LV020A	PLCC32	PA32PL32D
ATMEL	AT27LV020A	sTSOP32	PA32TS32D
ATMEL	AT27LV020A	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT27LV040	DIP32	
ATMEL	AT27LV040	PLCC32	PA32PL32D
ATMEL	AT27LV040	sTSOP32	PA32TS32D
ATMEL	AT27LV040	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT27LV040A	DIP32	
ATMEL	AT27LV040A	PLCC32	PA32PL32D
ATMEL	AT27LV040A	sTSOP32	PA32TS32D
ATMEL	AT27LV040A	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT27LV080	DIP32	
ATMEL	AT27LV080	PLCC32	PA32PL32D
ATMEL	AT27LV080	SOIC32	PA32SO32D-EO-450
ATMEL	AT27LV080	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT27LV1024	DIP40	
ATMEL	AT27LV1024	PLCC44	PA44-48U
ATMEL	AT27LV1024	TSOP40	PA40TS40D
ATMEL	AT27LV256A	DIP28	
ATMEL	AT27LV256A/R	PLCC32	PA32PL28D-YA
ATMEL	AT27LV256A/R	SOIC28	PA28SO28D-EO-300
ATMEL	AT27LV256A/R	TSOP28	PA28TS28D-EO
ATMEL	AT27LV256R	DIP28	
ATMEL	AT27LV4096	DIP40	
ATMEL	AT27LV4096	PLCC44	PA44-48U
ATMEL	AT27LV4096	TSOP40	PA40TS40D
ATMEL	AT27LV512A	DIP28	
ATMEL	AT27LV512A	PLCC32	PA32PL28D-YA
ATMEL	AT27LV512A	SOIC28	PA28SO28D-EO-300
ATMEL	AT27LV512A	TSOP28	PA28TS28D-EO
ATMEL	AT27LV512R	DIP28	
ATMEL	AT27LV512R	PLCC32	PA32PL28D-YA
ATMEL	AT27LV512R	SOIC28	PA28SO28D-EO-300
ATMEL	AT27LV512R	TSOP28	PA28TS28D-EO
ATMEL	AT27LV520	SOIC20	PA28SO-08(C)
ATMEL	AT27LV520	TSOP20	PA24TSS24D
ATMEL	AT27RW1024	PLCC44	PA44-48U
ATMEL	AT28BV16	DIP24	
ATMEL	AT28BV16	PLCC32	PA32PL32D
ATMEL	AT28BV16	SOIC24	PA28SO28D-EO-300
ATMEL	AT28BV16	TSOP28	PA28TS28D-EO
ATMEL	AT28BV256	DIP28	
ATMEL	AT28BV256	PLCC32	PA32PL28D-YA
ATMEL	AT28BV256	SOIC28	PA28SO28D-EO-300
ATMEL	AT28BV256	TSOP28	PA28TS28D-EO
ATMEL	AT28BV64	DIP28	
ATMEL	AT28BV64	PLCC32	PA32PL28D-YA
ATMEL	AT28BV64	SOIC28	PA28SO28D-EO-300
ATMEL	AT28BV64	TSOP28	PA28TS28D-EO
ATMEL	AT28BV64B	DIP28	
ATMEL	AT28BV64B	PLCC32	PA32PL28D-YA
ATMEL	AT28BV64B	SOIC28	PA28SO28D-EO-300
ATMEL	AT28BV64B	TSOP28	PA28TS28D-EO
ATMEL	AT28C010	DIP32	
ATMEL	AT28C010	PLCC32	PA32PL32D
ATMEL	AT28C010	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT28C010E	DIP32	
ATMEL	AT28C010E	PLCC32	PA32PL32D
ATMEL	AT28C010E	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT28C020	DIP32	
ATMEL	AT28C040	DIP32	
ATMEL	AT28C1024	DIP40	
ATMEL	AT28C1024	PLCC44	PA44-48U
ATMEL	AT28C16	DIP24	
ATMEL	AT28C16	PLCC32	PA32PL24D
ATMEL	AT28C16	SOIC24	PA28SO28D-EO-300
ATMEL	AT28C16	TSOP28	PA28TS28D-EO
ATMEL	AT28C16E	DIP24	
ATMEL	AT28C16E	PLCC32	PA32PL24D
ATMEL	AT28C16E	SOIC24	PA28SO28D-EO-300
ATMEL	AT28C16E	TSOP28	PA28TS28D-EO



ATMEL	AT28C17	DIP28	PA32PL28D-YA
ATMEL	AT28C17	PLCC32	PA28SO28D-EO-300
ATMEL	AT28C17	SOIC24	PA28TS28D-EO
ATMEL	AT28C17	TSOP28	PA28TS28D-EO
ATMEL	AT28C17E	DIP28	
ATMEL	AT28C17E	PLCC32	PA32PL28D-YA
ATMEL	AT28C17E	SOIC24	PA28SO28D-EO-300
ATMEL	AT28C17E	TSOP28	PA28TS28D-EO
ATMEL	AT28C256	DIP28	
ATMEL	AT28C256	PLCC32	PA32PL28D-YA
ATMEL	AT28C256	SOIC28	PA28SO28D-EO-300
ATMEL	AT28C256	TSOP28	PA28TS28D-EO
ATMEL	AT28C256E	DIP28	
ATMEL	AT28C256E	PLCC32	PA32PL28D-YA
ATMEL	AT28C256E	SOIC28	PA28SO28D-EO-300
ATMEL	AT28C256E	TSOP28	PA28TS28D-EO
ATMEL	AT28C256F	DIP28	
ATMEL	AT28C256F	PLCC32	PA32PL28D-YA
ATMEL	AT28C256F	SOIC28	PA28SO28D-EO-300
ATMEL	AT28C256F	TSOP28	PA28TS28D-EO
ATMEL	AT28C64	DIP28	
ATMEL	AT28C64	PLCC32	PA32PL28D-YA
ATMEL	AT28C64	SOIC24	PA28SO28D-EO-300
ATMEL	AT28C64	TSOP28	PA28TS28D-EO
ATMEL	AT28C64B	DIP28	
ATMEL	AT28C64B	PLCC32	PA32PL28D-YA
ATMEL	AT28C64B	SOIC24	PA28SO28D-EO-300
ATMEL	AT28C64B	TSOP28	PA28TS28D-EO
ATMEL	AT28C64E	DIP28	
ATMEL	AT28C64E	PLCC32	PA32PL28D-YA
ATMEL	AT28C64E	SOIC24	PA28SO28D-EO-300
ATMEL	AT28C64E	TSOP28	PA28TS28D-EO
ATMEL	AT28C64X	DIP28	
ATMEL	AT28C64X	PLCC32	PA32PL28D-YA
ATMEL	AT28C64X	SOIC24	PA28SO28D-EO-300
ATMEL	AT28C64X	TSOP28	PA28TS28D-EO
ATMEL	AT28HC16	DIP24	
ATMEL	AT28HC16L	DIP24	
ATMEL	AT28HC256	DIP28	
ATMEL	AT28HC256	PLCC32	PA32PL28D-YA
ATMEL	AT28HC256	SOIC28	PA28SO28D-EO-300
ATMEL	AT28HC256	TSOP28	PA28TS28D-EO
ATMEL	AT28HC256E	DIP28	
ATMEL	AT28HC256E	PLCC32	PA32PL28D-YA
ATMEL	AT28HC256E	SOIC28	PA28SO28D-EO-300
ATMEL	AT28HC256E	TSOP28	PA28TS28D-EO
ATMEL	AT28HC256E-normalWrite	DIP28	
ATMEL	AT28HC256F	DIP28	
ATMEL	AT28HC256F	PLCC32	PA32PL28D-YA
ATMEL	AT28HC256F	SOIC28	PA28SO28D-EO-300
ATMEL	AT28HC256F	TSOP28	PA28TS28D-EO
ATMEL	AT28HC256N	PLCC32	PA32PL28D-YA
ATMEL	AT28HC64	DIP28	
ATMEL	AT28HC64	PLCC32	PA32PL28D-YA
ATMEL	AT28HC64	SOIC24	PA28SO28D-EO-300
ATMEL	AT28HC64	TSOP28	PA28TS28D-EO
ATMEL	AT28HC64B	DIP28	
ATMEL	AT28HC64B	PLCC32	PA32PL28D-YA
ATMEL	AT28HC64B	SOIC24	PA28SO28D-EO-300
ATMEL	AT28HC64B	TSOP28	PA28TS28D-EO
ATMEL	AT28LV010	DIP32	
ATMEL	AT28LV010	PLCC32	PA32PL32D
ATMEL	AT28LV010	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT28LV256	DIP28	
ATMEL	AT28LV256	PLCC32	PA32PL28D-YA
ATMEL	AT28LV256	SOIC28	PA28SO28D-EO-300
ATMEL	AT28LV256	TSOP28	PA28TS28D-EO
ATMEL	AT28LV64	DIP28	
ATMEL	AT28LV64	PLCC32	PA32PL28D-YA
ATMEL	AT28LV64	SOIC24	PA28SO28D-EO-300
ATMEL	AT28LV64	TSOP28	PA28TS28D-EO
ATMEL	AT28LV64B	DIP28	
ATMEL	AT28LV64B	PLCC32	PA32PL28D-YA

ATMEL	AT28LV64B	SOIC24	PA28SO28D-EO-300
ATMEL	AT28LV64B	TSOP28	PA28TS28D-EO
ATMEL	AT28MC010	DIP32	
ATMEL	AT28MC040	DIP32	
ATMEL	AT28PC64	DIP28	
ATMEL	AT28PC64	PLCC32	PA32PL28D-YA
ATMEL	AT28PC64	SOIC24	PA28SO28D-EO-300
ATMEL	AT28PC64	TSOP28	PA28TS28D-EO
ATMEL	AT28PC64E	DIP28	
ATMEL	AT29BV010A	DIP32	
ATMEL	AT29BV010A	PLCC32	PA32PL32D
ATMEL	AT29BV010A	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT29BV020	DIP32	
ATMEL	AT29BV020	PLCC32	PA32PL32D
ATMEL	AT29BV020	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT29BV040A	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT29BV1024	DIP40	
ATMEL	AT29BV1024	PLCC44	PA44-48U
ATMEL	AT29BV256	DIP28	
ATMEL	AT29C010	DIP32	
ATMEL	AT29C010	PLCC32	PA32PL32D
ATMEL	AT29C010	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT29C010A	DIP32	
ATMEL	AT29C010A	PLCC32	PA32PL32D
ATMEL	AT29C010A	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT29C020	DIP32	
ATMEL	AT29C020	PLCC32	PA32PL32D
ATMEL	AT29C020	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT29C040	DIP32	
ATMEL	AT29C040	PLCC32	PA32PL32D
ATMEL	AT29C040	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT29C040A	DIP32	
ATMEL	AT29C040A	PLCC32	PA32PL32D
ATMEL	AT29C040A	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT29C1024	DIP40	
ATMEL	AT29C1024	PLCC44	PA44-48U
ATMEL	AT29C1024	TSOP48	PA48TS48D
ATMEL	AT29C256	DIP28	
ATMEL	AT29C256	PLCC32	PA32PL28D-YA
ATMEL	AT29C257	DIP32	
ATMEL	AT29C257	PLCC32	PA32PL32D
ATMEL	AT29C512	DIP32	
ATMEL	AT29C512	PLCC32	PA32PL32D
ATMEL	AT29C512	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT29LV010	DIP32	
ATMEL	AT29LV010	PLCC32	PA32PL32D
ATMEL	AT29LV010	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT29LV010A	DIP32	
ATMEL	AT29LV010A	PLCC32	PA32PL32D
ATMEL	AT29LV010A	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT29LV020	DIP32	
ATMEL	AT29LV020	PLCC32	PA32PL32D
ATMEL	AT29LV020	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT29LV040A	DIP32	
ATMEL	AT29LV040A	PLCC32	PA32PL32D
ATMEL	AT29LV040A	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT29LV1024	DIP40	
ATMEL	AT29LV1024	PLCC44	PA44-48U
ATMEL	AT29LV1024	TSOP48	PA48TS48D
ATMEL	AT29LV256	DIP28	
ATMEL	AT29LV256	PLCC32	PA32PL28D-YA
ATMEL	AT29LV512	DIP32	
ATMEL	AT29LV512	PLCC32	PA32PL32D
ATMEL	AT29LV512	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT30TSE004A	DFN8	PA8QFN8D(2x3)
ATMEL	AT32C16	DIP40	
ATMEL	AT34C02	DIP8	
ATMEL	AT34C02	SOIC8	PA8SO8D-EO-150
ATMEL	AT34C02	TSSOP8	PA24TSS24D
ATMEL	AT34C02	TSSOP8	PA8TSS8D
ATMEL	AT34C02	TSSOP8	PA8TSS-OT
ATMEL	AT34C02B	SOIC8	PA8SO8D-EO-150
ATMEL	AT34C02B	TSSOP8	PA24TSS24D

ATMEL	AT34C02B	TSSOP8	PA8TSS8D
ATMEL	AT34C02C	SOIC8	PA8SO8D-EO-150
ATMEL	AT34C02C	TSSOP8	PA24TSS24D
ATMEL	AT34C02C	TSSOP8	PA8TSS8D
ATMEL	AT45D011	PLCC32	PA32PL32D
ATMEL	AT45D011	SOP8	PA20SO20D-EO-210
ATMEL	AT45D021	PLCC32	PA32PL32D
ATMEL	AT45D021	SOP28	PA28SO28DB-EC-350
ATMEL	AT45D021	TSOP28	PA28TS28D-EO
ATMEL	AT45D041	PLCC32	PA32PL32D
ATMEL	AT45D041	SOP28	PA28SO28DB-EC-350
ATMEL	AT45D041	TSOP28	PA28TS28D-EO
ATMEL	AT45D081	SOP28	PA28SO28DB-EC-350
ATMEL	AT45D081	TSOP32	PA48TS48D
ATMEL	AT45D161	PLCC32	PA32PL32D
ATMEL	AT45D161	SOP28	PA28SO28DB-EC-350
ATMEL	AT45D161	TSOP28	PA28TS28D-EO
ATMEL	AT45DB011	PLCC32	PA32PL32D
ATMEL	AT45DB011	SOP8	PA20SO20D-EO-210
ATMEL	AT45DB011B	PLCC32	PA32PL32D
ATMEL	AT45DB011B	SOP8	PA20SO20D-EO-210
ATMEL	AT45DB011B	TSSOP14	PA24TSS24D
ATMEL	AT45DB011D	CASON8	PA8SON8D(6x5)
ATMEL	AT45DB011D	SOIC8	PA16SO16D-EO-150
ATMEL	AT45DB011D	SOIC8	PA20SO20D-EO-210
ATMEL	AT45DB021	PLCC32	PA32PL32D
ATMEL	AT45DB021	SOP28	PA28SO28DB-EC-350
ATMEL	AT45DB021	TSOP28	PA28TS28D-EO
ATMEL	AT45DB021B	SOIC8	PA20SO20D-EO-210
ATMEL	AT45DB021B	SOP28	PA28SO28DB-EC-350
ATMEL	AT45DB021B	TSOP28	PA28TS28D-EO
ATMEL	AT45DB021D	SOIC8	PA16SO16D-EO-150
ATMEL	AT45DB021D	SOIC8	PA20SO20D-EO-210
ATMEL	AT45DB041	PLCC32	PA32PL32D
ATMEL	AT45DB041	SOP28	PA28SO28DB-EC-350
ATMEL	AT45DB041	TSOP28	PA28TS28D-EO
ATMEL	AT45DB041B	CASON8	PA8SON20D
ATMEL	AT45DB041B	SOP28	PA28SO28DB-EC-350
ATMEL	AT45DB041B	SOP8	PA20SO20D-EO-210
ATMEL	AT45DB041B	TSOP28	PA28TS28D-EO
ATMEL	AT45DB041D	SOIC8	PA16SO16D-EO-150
ATMEL	AT45DB041D	SOIC8	PA20SO20D-EO-210
ATMEL	AT45DB081	SOP28	PA28SO28DB-EC-350
ATMEL	AT45DB081	TSOP32	PA48TS48D
ATMEL	AT45DB081B	CASON8	PA8SON20D
ATMEL	AT45DB081B	TSOP28	PA28TS28D-EO
ATMEL	AT45DB081B	TSOP32	PA48TS48D
ATMEL	AT45DB081D	MLF8	PA8SON8D(6x5)
ATMEL	AT45DB081D	SOP8	PA20SO20D-EO-210
ATMEL	AT45DB161	PLCC32	PA32PL32D
ATMEL	AT45DB161	SOP28	PA28SO28DB-EC-350
ATMEL	AT45DB161	TSOP28	PA28TS28D-EO
ATMEL	AT45DB161B	CASON8	PA8SON20D
ATMEL	AT45DB161B	SOP28	PA28SO28DB-EC-350
ATMEL	AT45DB161B	TSOP28	PA28TS28D-EO
ATMEL	AT45DB161D	SOIC8	PA20SO20D-EO-210
ATMEL	AT45DB161D	TSOP28	PA28TS28D-EO
ATMEL	AT45DB161E	SOIC8	PA16SO16D-EO-150
ATMEL	AT45DB161E	SOIC8	PA20SO20D-EO-210
ATMEL	AT45DB161E	UDFN8	PA8SON8D(6x5)
ATMEL	AT45DB321	SOP28	PA28SO28DB-EC-350
ATMEL	AT45DB321	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT45DB321	TSOP32	PA48TS48D
ATMEL	AT45DB321B	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT45DB321C	TSOP28	PA28TS28D-EO
ATMEL	AT45DB321D	SOIC8	PA20SO20D-EO-210
ATMEL	AT45DB321D	TSOP28	PA28TS28D-EO
ATMEL	AT45DB641E	SOIC8	PA20SO20D-EO-210
ATMEL	AT45DB641E	UDFN8	PA8SON8D(6x5)
ATMEL	AT45DB642	TSOP40	PA40TS40D
ATMEL	AT45DB642D	CASON8	HA8SON48DB
ATMEL	AT45DB642D	TSOP28	PA28TS28D-EO
ATMEL	AT45DCB002	SOP28	PAAT02-04A

ATMEL	AT45DCB004	SOP28	PAAT02-04A
ATMEL	AT45DCB008	SOP28	PAAT02-04A
ATMEL	AT49BV001	DIP32	
ATMEL	AT49BV001	PLCC32	PA32PL32D
ATMEL	AT49BV001	SSOP32	PA32TS32D
ATMEL	AT49BV001	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV001A	PLCC32	PA32PL32D
ATMEL	AT49BV001A	SSOP32	PA32TS32D
ATMEL	AT49BV001A	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV001AN	PLCC32	PA32PL32D
ATMEL	AT49BV001AN	SSOP32	PA32TS32D
ATMEL	AT49BV001AN	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV001ANT	PLCC32	PA32PL32D
ATMEL	AT49BV001ANT	SSOP32	PA32TS32D
ATMEL	AT49BV001ANT	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV001AT	PLCC32	PA32PL32D
ATMEL	AT49BV001AT	SSOP32	PA32TS32D
ATMEL	AT49BV001AT	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV001N	DIP32	
ATMEL	AT49BV001N	PLCC32	PA32PL32D
ATMEL	AT49BV001N	SSOP32	PA32TS32D
ATMEL	AT49BV001N	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV001NT	DIP32	
ATMEL	AT49BV001NT	PLCC32	PA32PL32D
ATMEL	AT49BV001NT	SSOP32	PA32TS32D
ATMEL	AT49BV001NT	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV001T	DIP32	
ATMEL	AT49BV001T	PLCC32	PA32PL32D
ATMEL	AT49BV001T	SSOP32	PA32TS32D
ATMEL	AT49BV001T	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV002	DIP32	
ATMEL	AT49BV002	PLCC32	PA32PL32D
ATMEL	AT49BV002	SSOP32	PA32TS32D
ATMEL	AT49BV002	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV002A	DIP32	
ATMEL	AT49BV002A	PLCC32	PA32PL32D
ATMEL	AT49BV002A	SSOP32	PA32TS32D
ATMEL	AT49BV002A	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV002AN	DIP32	
ATMEL	AT49BV002AN	PLCC32	PA32PL32D
ATMEL	AT49BV002AN	SSOP32	PA32TS32D
ATMEL	AT49BV002AN	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV002ANT	DIP32	
ATMEL	AT49BV002ANT	PLCC32	PA32PL32D
ATMEL	AT49BV002ANT	SSOP32	PA32TS32D
ATMEL	AT49BV002ANT	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV002AT	DIP32	
ATMEL	AT49BV002AT	PLCC32	PA32PL32D
ATMEL	AT49BV002AT	SSOP32	PA32TS32D
ATMEL	AT49BV002AT	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV002N	DIP32	
ATMEL	AT49BV002N	PLCC32	PA32PL32D
ATMEL	AT49BV002N	SSOP32	PA32TS32D
ATMEL	AT49BV002N	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV002NT	DIP32	
ATMEL	AT49BV002NT	PLCC32	PA32PL32D
ATMEL	AT49BV002NT	SSOP32	PA32TS32D
ATMEL	AT49BV002NT	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV002T	DIP32	
ATMEL	AT49BV002T	PLCC32	PA32PL32D
ATMEL	AT49BV002T	SSOP32	PA32TS32D
ATMEL	AT49BV002T	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV008A	TSOP40	PA40TS40D
ATMEL	AT49BV008AT	TSOP40	PA40TS40D
ATMEL	AT49BV010	DIP32	
ATMEL	AT49BV010	PLCC32	PA32PL32D
ATMEL	AT49BV010	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV020	DIP32	
ATMEL	AT49BV020	PLCC32	PA32PL32D
ATMEL	AT49BV020	SSOP32	PA32TS32D
ATMEL	AT49BV020	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV040	DIP32	
ATMEL	AT49BV040	PLCC32	PA32PL32D

ATMEL	AT49BV040	SSOP32	PA32TS32D
ATMEL	AT49BV040	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV040A	PLCC32	PA32PL32D
ATMEL	AT49BV040A	SSOP32	PA32TS32D
ATMEL	AT49BV040A	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV040B	PLCC32	PA32PL32D
ATMEL	AT49BV040T	DIP32	
ATMEL	AT49BV040T	PLCC32	PA32PL32D
ATMEL	AT49BV040T	SSOP32	PA32TS32D
ATMEL	AT49BV040T	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV080	SOP44	PA44SO44D
ATMEL	AT49BV080	TSOP40	PA40TS40D
ATMEL	AT49BV080T	SOP44	PA44SO44D
ATMEL	AT49BV080T	TSOP40	PA40TS40D
ATMEL	AT49BV1024A	TSOP40	PA44SO44D
ATMEL	AT49BV160	TSOP48	PA48TS48D
ATMEL	AT49BV1604	TSOP48	PA48TS48D
ATMEL	AT49BV1604A	TSOP48	PA48TS48D
ATMEL	AT49BV1604AT	TSOP48	PA48TS48D
ATMEL	AT49BV1604T	TSOP48	PA48TS48D
ATMEL	AT49BV160C	TSOP48	PA48TS48D
ATMEL	AT49BV160C	TSOP48	PA48TS48D
ATMEL	AT49BV160CT	TSOP48	PA48TS48D
ATMEL	AT49BV160CT	TSOP48	PA48TS48D
ATMEL	AT49BV160T	TSOP48	PA48TS48D
ATMEL	AT49BV161	TSOP48	PA48TS48D
ATMEL	AT49BV1614	TSOP48	PA48TS48D
ATMEL	AT49BV1614A	TSOP48	PA48TS48D
ATMEL	AT49BV1614AT	TSOP48	PA48TS48D
ATMEL	AT49BV1614T	TSOP48	PA48TS48D
ATMEL	AT49BV1618	TSOP48	PA48TS48D
ATMEL	AT49BV1618T	TSOP48	PA48TS48D
ATMEL	AT49BV161T	TSOP48	PA48TS48D
ATMEL	AT49BV162A	TSOP48	PA48TS48D
ATMEL	AT49BV162AT	TSOP48	PA48TS48D
ATMEL	AT49BV163A	TSOP48	PA48TS48D
ATMEL	AT49BV2048	SOP44	PA44SO44D
ATMEL	AT49BV2048	TSOP48	PA48TS48D
ATMEL	AT49BV2048A	SOP44	PA44SO44D
ATMEL	AT49BV2048A	TSOP48	PA48TS48D
ATMEL	AT49BV320	TSOP48	PA48TS48D
ATMEL	AT49BV320A	TSOP48	PA48TS48D
ATMEL	AT49BV320AT	TSOP48	PA48TS48D
ATMEL	AT49BV320C	TSOP48	PA48TS48D
ATMEL	AT49BV320CT	TSOP48	PA48TS48D
ATMEL	AT49BV320D	TSOP48	PA48TS48D
ATMEL	AT49BV320DT	TSOP48	PA48TS48D
ATMEL	AT49BV320T	TSOP48	PA48TS48D
ATMEL	AT49BV321	TSOP48	PA48TS48D
ATMEL	AT49BV321T	TSOP48	PA48TS48D
ATMEL	AT49BV322A	BGA48	HA48BG48DAR
ATMEL	AT49BV322A	TSOP48	PA48TS48D
ATMEL	AT49BV322AT	BGA48	HA48BG48DAR
ATMEL	AT49BV322AT	TSOP48	PA48TS48D
ATMEL	AT49BV322D	TSOP48	PA48TS48D
ATMEL	AT49BV322DT	TSOP48	PA48TS48D
ATMEL	AT49BV4096	SOP44	PA44SO44D
ATMEL	AT49BV4096	TSOP48	PA48TS48D
ATMEL	AT49BV4096A	SOP44	PA44SO44D
ATMEL	AT49BV4096A	TSOP48	PA48TS48D
ATMEL	AT49BV4096AT	SOP44	PA44SO44D
ATMEL	AT49BV4096AT	TSOP48	PA48TS48D
ATMEL	AT49BV512	DIP32	
ATMEL	AT49BV512	PLCC32	PA32PL32D
ATMEL	AT49BV512	SSOP32	PA32TS32D
ATMEL	AT49BV512	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49BV6416	TSOP48	PA48TS48D
ATMEL	AT49BV6416T	TSOP48	PA48TS48D
ATMEL	AT49BV8004	TSOP48	PA48TS48D
ATMEL	AT49BV8004T	TSOP48	PA48TS48D
ATMEL	AT49BV8011	TSOP48	PA48TS48D
ATMEL	AT49BV8011T	TSOP48	PA48TS48D
ATMEL	AT49BV802A	TSOP48	PA48TS48D

ATMEL	AT49BV802AT	TSOP48	PA48TS48D
ATMEL	AT49BV8192	SOP44	PA44SO44D
ATMEL	AT49BV8192	TSOP48	PA48TS48D
ATMEL	AT49BV8192A	TSOP48	PA48TS48D
ATMEL	AT49BV8192AT	TSOP48	PA48TS48D
ATMEL	AT49BV8192T	SOP44	PA44SO44D
ATMEL	AT49BV8192T	TSOP48	PA48TS48D
ATMEL	AT49F001	DIP32	
ATMEL	AT49F001	PLCC32	PA32PL32D
ATMEL	AT49F001	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F001A	PLCC32	PA32PL32D
ATMEL	AT49F001A	PLCC32	PA32PL32D
ATMEL	AT49F001A	SSOP32	PA32TS32D
ATMEL	AT49F001A	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F001AN	PLCC32	PA32PL32D
ATMEL	AT49F001AN	PLCC32	PA32PL32D
ATMEL	AT49F001AN	SSOP32	PA32TS32D
ATMEL	AT49F001AN	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F001ANT	PLCC32	PA32PL32D
ATMEL	AT49F001ANT	SSOP32	PA32TS32D
ATMEL	AT49F001ANT	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F001AT	PLCC32	PA32PL32D
ATMEL	AT49F001AT	SSOP32	PA32TS32D
ATMEL	AT49F001AT	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F001N	DIP32	
ATMEL	AT49F001N	PLCC32	PA32PL32D
ATMEL	AT49F001N	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F001NT	DIP32	
ATMEL	AT49F001NT	PLCC32	PA32PL32D
ATMEL	AT49F001NT	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F001T	DIP32	
ATMEL	AT49F001T	PLCC32	PA32PL32D
ATMEL	AT49F001T	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F002	DIP32	
ATMEL	AT49F002	PLCC32	PA32PL32D
ATMEL	AT49F002	SSOP32	PA32TS32D
ATMEL	AT49F002	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F002A	DIP32	
ATMEL	AT49F002A	PLCC32	PA32PL32D
ATMEL	AT49F002A	SSOP32	PA32TS32D
ATMEL	AT49F002A	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F002AN	DIP32	
ATMEL	AT49F002AN	PLCC32	PA32PL32D
ATMEL	AT49F002AN	SSOP32	PA32TS32D
ATMEL	AT49F002AN	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F002ANT	DIP32	
ATMEL	AT49F002ANT	PLCC32	PA32PL32D
ATMEL	AT49F002ANT	SSOP32	PA32TS32D
ATMEL	AT49F002ANT	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F002AT	DIP32	
ATMEL	AT49F002AT	PLCC32	PA32PL32D
ATMEL	AT49F002AT	SSOP32	PA32TS32D
ATMEL	AT49F002AT	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F002N	DIP32	
ATMEL	AT49F002N	PLCC32	PA32PL32D
ATMEL	AT49F002N	SSOP32	PA32TS32D
ATMEL	AT49F002N	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F002NT	DIP32	
ATMEL	AT49F002NT	PLCC32	PA32PL32D
ATMEL	AT49F002NT	SSOP32	PA32TS32D
ATMEL	AT49F002NT	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F002T	DIP32	
ATMEL	AT49F002T	PLCC32	PA32PL32D
ATMEL	AT49F002T	SSOP32	PA32TS32D
ATMEL	AT49F002T	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F010	DIP32	
ATMEL	AT49F010	PLCC32	PA32PL32D
ATMEL	AT49F010	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F020	DIP32	
ATMEL	AT49F020	PLCC32	PA32PL32D
ATMEL	AT49F020	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F040	DIP32	
ATMEL	AT49F040	PLCC32	PA32PL32D

ATMEL	AT49F040	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F040A	DIP32	
ATMEL	AT49F040A	PLCC32	PA32PL32D
ATMEL	AT49F040A	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F040B	PLCC32	PA32PL32D
ATMEL	AT49F040B	SSOP32	PA32TS32D
ATMEL	AT49F040B	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F040T	DIP32	
ATMEL	AT49F040T	PLCC32	PA32PL32D
ATMEL	AT49F040T	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F080	TSOP40	PA40TS40D
ATMEL	AT49F080T	TSOP40	PA40TS40D
ATMEL	AT49F1024	PLCC44	PA44-48U
ATMEL	AT49F1024	TSOP40	PA40TS14-OT
ATMEL	AT49F1024	TSOP40	PA40TS40D
ATMEL	AT49F1024A	TSOP40	PA40TS40D
ATMEL	AT49F1025	PLCC44	PA44-48U
ATMEL	AT49F1025	SOP40	PA44SO44D
ATMEL	AT49F1604	TSOP48	PA48TS48D
ATMEL	AT49F1604T	TSOP48	PA48TS48D
ATMEL	AT49F1614	TSOP48	PA48TS48D
ATMEL	AT49F1614T	TSOP48	PA48TS48D
ATMEL	AT49F1618	TSOP48	PA48TS48D
ATMEL	AT49F1618T	TSOP48	PA48TS48D
ATMEL	AT49F2048	SOP44	PA44SO44D
ATMEL	AT49F2048	TSOP48	PA48TS48D
ATMEL	AT49F2048A	SOP44	PA44SO44D
ATMEL	AT49F2048A	TSOP48	PA48TS48D
ATMEL	AT49F4096	SOP44	PA44SO44D
ATMEL	AT49F4096	TSOP48	PA48TS48D
ATMEL	AT49F4096A	SOP44	PA44SO44D
ATMEL	AT49F4096A	TSOP48	PA48TS48D
ATMEL	AT49F4096AT	SOP44	PA44SO44D
ATMEL	AT49F4096AT	TSOP48	PA48TS48D
ATMEL	AT49F512	DIP32	
ATMEL	AT49F512	PLCC32	PA32PL32D
ATMEL	AT49F512	SSOP32	PA32TS32D
ATMEL	AT49F512	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49F8004	TSOP48	PA48TS48D
ATMEL	AT49F8004T	TSOP48	PA48TS48D
ATMEL	AT49F8011	TSOP48	PA48TS48D
ATMEL	AT49F8011T	TSOP48	PA48TS48D
ATMEL	AT49F8192	SOP44	PA44SO44D
ATMEL	AT49F8192	TSOP48	PA48TS48D
ATMEL	AT49F8192A	SOP44	PA44SO44D
ATMEL	AT49F8192A	TSOP48	PA48TS48D
ATMEL	AT49F8192AT	SOP44	PA44SO44D
ATMEL	AT49F8192AT	TSOP48	PA48TS48D
ATMEL	AT49F8192T	SOP44	PA44SO44D
ATMEL	AT49F8192T	TSOP48	PA48TS48D
ATMEL	AT49HBV010	PLCC32	PA32PL32D
ATMEL	AT49HBV010	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49HF010	DIP32	
ATMEL	AT49HF010	PLCC32	PA32PL32D
ATMEL	AT49HF010	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49HLV010	PLCC32	PA32PL32D
ATMEL	AT49HLV010	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49LH002-xxJC	PLCC32	PA32PL32D
ATMEL	AT49LH002-xxTC	TSOP40	PA40TS40D
ATMEL	AT49LH004-xxJC	PLCC32	PA32PL32D
ATMEL	AT49LH004-xxJC	PLCC32	PA32PL32D
ATMEL	AT49LH004-xxTC	TSOP40	PA40TS40D
ATMEL	AT49LL040	PLCC32	PA32PL32D
ATMEL	AT49LV001	DIP32	
ATMEL	AT49LV001	PLCC32	PA32PL32D
ATMEL	AT49LV001	SSOP32	PA32TS32D
ATMEL	AT49LV001	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV001N	DIP32	
ATMEL	AT49LV001N	PLCC32	PA32PL32D
ATMEL	AT49LV001N	SSOP32	PA32TS32D
ATMEL	AT49LV001N	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV001NT	DIP32	
ATMEL	AT49LV001NT	PLCC32	PA32PL32D

ATMEL	AT49LV001NT	SSOP32	PA32TS32D
ATMEL	AT49LV001NT	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV001T	DIP32	
ATMEL	AT49LV001T	PLCC32	PA32PL32D
ATMEL	AT49LV001T	SSOP32	PA32TS32D
ATMEL	AT49LV001T	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV002	DIP32	
ATMEL	AT49LV002	PLCC32	PA32PL32D
ATMEL	AT49LV002	SSOP32	PA32TS32D
ATMEL	AT49LV002	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV002N	DIP32	
ATMEL	AT49LV002N	PLCC32	PA32PL32D
ATMEL	AT49LV002N	SSOP32	PA32TS32D
ATMEL	AT49LV002N	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV002NT	DIP32	
ATMEL	AT49LV002NT	PLCC32	PA32PL32D
ATMEL	AT49LV002NT	SSOP32	PA32TS32D
ATMEL	AT49LV002NT	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV002T	DIP32	
ATMEL	AT49LV002T	PLCC32	PA32PL32D
ATMEL	AT49LV002T	SSOP32	PA32TS32D
ATMEL	AT49LV002T	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV010	DIP32	
ATMEL	AT49LV010	PLCC32	PA32PL32D
ATMEL	AT49LV010	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV020	DIP32	
ATMEL	AT49LV020	PLCC32	PA32PL32D
ATMEL	AT49LV020	SSOP32	PA32TS32D
ATMEL	AT49LV020	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV040	DIP32	
ATMEL	AT49LV040	PLCC32	PA32PL32D
ATMEL	AT49LV040	SSOP32	PA32TS32D
ATMEL	AT49LV040	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV040T	DIP32	
ATMEL	AT49LV040T	PLCC32	PA32PL32D
ATMEL	AT49LV040T	TSOP32	PA32TS20/PA32TS32D-20
ATMEL	AT49LV080	SOP44	PA44SO44D
ATMEL	AT49LV080	TSOP40	PA40TS40D
ATMEL	AT49LV080T	SOP44	PA44SO44D
ATMEL	AT49LV080T	TSOP40	PA40TS40D
ATMEL	AT49LV1025	PLCC44	PA44-48U
ATMEL	AT49LV1614	TSOP48	PA48TS48D
ATMEL	AT49LV1614A	TSOP48	PA48TS48D
ATMEL	AT49LV1614AT	TSOP48	PA48TS48D
ATMEL	AT49LV1614T	TSOP48	PA48TS48D
ATMEL	AT49LV2048	SOP44	PA44SO44D
ATMEL	AT49LV2048	TSOP48	PA48TS48D
ATMEL	AT49LV4096A	SOP44	PA44SO44D
ATMEL	AT49LV4096A	TSOP48	PA48TS48D
ATMEL	AT49LV8192A	TSOP48	PA48TS48D
ATMEL	AT49LW040	PLCC32	PA32PL32D
ATMEL	AT49LW040	TSOP40	PA40TS40D
ATMEL	AT49LW080	PLCC32	PA32PL32D
ATMEL	AT49LW080	TSOP40	PA40TS40D
ATMEL	AT49SV322A	TSOP48	HA48TS48DJ
ATMEL	AT49SV322AT	TSOP48	HA48TS48DJ
ATMEL	AT49SV322D	TSOP48	HA48TS48DJ
ATMEL	AT49SV322DT	TSOP48	HA48TS48DJ
ATMEL	AT49SV802A	BGA48	HA48BG48DAY
ATMEL	AT49SV802A	TSOP48	HA48TS48DJ
ATMEL	AT49SV802AT	BGA48	HA48BG48DAY
ATMEL	AT49SV802AT	TSOP48	HA48TS48DJ
ATMEL	AT59C11	DIP8	
ATMEL	AT59C13	DIP8	
ATMEL	AT59C22	DIP8	
ATMEL	AT87F51	DIP40	
ATMEL	AT87F51	PLCC44	PA44-48U
ATMEL	AT87F51RC	DIP40	
ATMEL	AT87F51RC	PLCC44	PA44-48U
ATMEL	AT87F52	DIP40	
ATMEL	AT87F52	PLCC44	PA44-48U
ATMEL	AT87F55	DIP40	
ATMEL	AT87F55	PLCC44	PA44-48U



ATMEL	AT87F55WD	DIP40	
ATMEL	AT87F55WD	PLCC44	PA44-48U
ATMEL	AT89C1051	DIP20	
ATMEL	AT89C1051	SOP20	PA28SO28D-EO-300
ATMEL	AT89C1051U	DIP20	
ATMEL	AT89C1051U	SOP20	PA28SO28D-EO-300
ATMEL	AT89C2051	DIP20	
ATMEL	AT89C2051	SOP20	PA28SO28D-EO-300
ATMEL	AT89C2051X2	DIP20	
ATMEL	AT89C2051X2	SOP20	PA28SO28D-EO-300
ATMEL	AT89C4051	DIP20	
ATMEL	AT89C4051	SOP20	PA28SO28D-EO-300
ATMEL	AT89C51	DIP40	
ATMEL	AT89C51	PLCC44	PA44-48U
ATMEL	AT89C5115	PLCC28	PA28PL28D
ATMEL	AT89C5115	QFP32	PA32TQ32D
ATMEL	AT89C5115	SOP24	PA28SO28D-EO-300
ATMEL	AT89C5115	SOP28	PA28SO28D-EO-300
ATMEL	AT89C51AC3	PLCC44	PA44-48U
ATMEL	AT89C51AC3	TQFP44	PA44QF44D
ATMEL	AT89C51CC01	PLCC44	PA44-48U
ATMEL	AT89C51CC01	TQFP44	PA44TQ44D-EO
ATMEL	AT89C51CC03	PLCC44	PA44-48U
ATMEL	AT89C51CC03	TQFP44	PA44QF44D
ATMEL	AT89C51ED2	DIP40	
ATMEL	AT89C51ED2	PLCC44	PA44-48U
ATMEL	AT89C51ED2	PLCC68	PA68PL40DG
ATMEL	AT89C51ED2	QFP44	PA44QF44D
ATMEL	AT89C51ED2	VQFP64	PA64VQ40D
ATMEL	AT89C51IB2-xL_3V	PLCC44	PA44-48U
ATMEL	AT89C51IB2-xL_3V	QFP44	PA44QF44D
ATMEL	AT89C51IB2-xM_5V	PLCC44	PA44-48U
ATMEL	AT89C51IB2-xM_5V	QFP44	PA44QF44D
ATMEL	AT89C51IC2-xL_3V	PLCC44	PA44-48U
ATMEL	AT89C51IC2-xL_3V	QFP44	PA44QF44D
ATMEL	AT89C51IC2-xM_5V	PLCC44	PA44-48U
ATMEL	AT89C51IC2-xM_5V	QFP44	PA44QF44D
ATMEL	AT89C51ID2	PLCC44	PA44-48U
ATMEL	AT89C51ID2	PLCC68	PA68PL40DG
ATMEL	AT89C51ID2	QFP44	PA44QF44D
ATMEL	AT89C51ID2	VQFP64	PA64VQ40D
ATMEL	AT89C51RB2-xL_3V	DIP40	
ATMEL	AT89C51RB2-xL_3V	PLCC44	PA44-48U
ATMEL	AT89C51RB2-xL_3V	QFP44	PA44QF44D
ATMEL	AT89C51RB2-xM_5V	DIP40	
ATMEL	AT89C51RB2-xM_5V	PLCC44	PA44-48U
ATMEL	AT89C51RB2-xM_5V	QFP44	PA44QF44D
ATMEL	AT89C51RC	DIP40	
ATMEL	AT89C51RC	PLCC44	PA44-48U
ATMEL	AT89C51RC2-xL_3V	DIP40	
ATMEL	AT89C51RC2-xL_3V	PLCC44	PA44-48U
ATMEL	AT89C51RC2-xL_3V	QFP44	PA44QF44D
ATMEL	AT89C51RC2-xM_5V	DIP40	
ATMEL	AT89C51RC2-xM_5V	PLCC44	PA44-48U
ATMEL	AT89C51RC2-xM_5V	QFP44	PA44QF44D
ATMEL	AT89C51RD2	DIP40	
ATMEL	AT89C51RD2	PLCC44	PA44-48U
ATMEL	AT89C51RD2	PLCC68	PA68PL40DG
ATMEL	AT89C51RD2	QFP44	PA44QF44D
ATMEL	AT89C51RD2	VQFP64	PA64VQ40D
ATMEL	AT89C51RD2-xM	PLCC44	PA44-48U
ATMEL	AT89C52	DIP40	
ATMEL	AT89C52	PLCC44	PA44-48U
ATMEL	AT89C55	DIP40	
ATMEL	AT89C55	PLCC44	PA44-48U
ATMEL	AT89C55WD	DIP40	
ATMEL	AT89C55WD	PLCC44	PA44-48U
ATMEL	AT89LP2052	DIP20	
ATMEL	AT89LP2052	SOP20	PA28SO28D-EO-300
ATMEL	AT89LP2052	TSSOP20	PA24TSS24D
ATMEL	AT89LP4052	DIP20	
ATMEL	AT89LP4052	SOP20	PA28SO28D-EO-300
ATMEL	AT89LP4052	TSSOP20	PA24TSS24D

ATMEL	AT89LP51	DIP40	
ATMEL	AT89LP51	PLCC44	PA44-48U
ATMEL	AT89LP51	QFP44	PA44VQ44D/PA44TQ44D
ATMEL	AT89LP51ED2-20AAU	LQFP44	PA44VQ44D-EC
ATMEL	AT89LP51ED2-20JU	PLCC44	PA44PL48D
ATMEL	AT89LP51ED2-20PU	DIP40	
ATMEL	AT89LP51ID2-20AAU	LQFP44	PA44VQ44D-EC
ATMEL	AT89LP51RB2-20AU	TQFP44	PA44VQ44D-EC
ATMEL	AT89LP51RB2-20JU	PLCC44	PA44PL48D
ATMEL	AT89LP51RB2-20PU	DIP40	
ATMEL	AT89LP51RC2-20JU	PLCC44	PA44PL48D
ATMEL	AT89LP51RC2-20PU	DIP40	
ATMEL	AT89LP51RD2-20AU	TQFP44	PA44VQ44D-EC
ATMEL	AT89LP51RD2-20JU	PLCC44	PA44PL48D
ATMEL	AT89LP51RD2-20PU	DIP40	
ATMEL	AT89LP52	DIP40	
ATMEL	AT89LP52	PLCC44	PA44-48U
ATMEL	AT89LP52	QFP44	PA44VQ44D/PA44TQ44D
ATMEL	AT89LS51	DIP40	
ATMEL	AT89LS51	PLCC44	PA44-48U
ATMEL	AT89LS51	TQFP44	PA44VQ44D
ATMEL	AT89LS52	DIP40	
ATMEL	AT89LS52	PLCC44	PA44-48U
ATMEL	AT89LS52	TQFP44	PA44VQ44D
ATMEL	AT89LS8252	DIP40	
ATMEL	AT89LS8252	PLCC44	PA44-48U
ATMEL	AT89LS8252	TQFP44	PA44VQ44D
ATMEL	AT89LV51	DIP40	
ATMEL	AT89LV51	PLCC44	PA44-48U
ATMEL	AT89LV51	TQFP44	PA44VQ44D
ATMEL	AT89LV52	DIP40	
ATMEL	AT89LV52	PLCC44	PA44-48U
ATMEL	AT89LV52	TQFP44	PA44VQ44D
ATMEL	AT89LV55	TQFP44	PA44VQ44D
ATMEL	AT89S2051	DIP20	
ATMEL	AT89S2051	SOP20	PA28SO28D-EO-300
ATMEL	AT89S2051	TSSOP20	PA24TSS24D
ATMEL	AT89S4051	DIP20	
ATMEL	AT89S4051	SOP20	PA28SO28D-EO-300
ATMEL	AT89S4051	TSSOP20	PA24TSS24D
ATMEL	AT89S51	DIP40	
ATMEL	AT89S51	PLCC44	PA44-48U
ATMEL	AT89S51	TQFP44	PA44VQ44D
ATMEL	AT89S52	DIP40	
ATMEL	AT89S52	PLCC44	PA44-48U
ATMEL	AT89S52	TQFP44	PA44VQ44D
ATMEL	AT89S53	DIP40	
ATMEL	AT89S53	PLCC44	PA44-48U
ATMEL	AT89S53	TQFP44	PA44VQ44D
ATMEL	AT89S8252	DIP40	
ATMEL	AT89S8252	PLCC44	PA44-48U
ATMEL	AT89S8252	TQFP44	PA44VQ44D
ATMEL	AT89S8253	DIP40	
ATMEL	AT89S8253	PLCC44	PA44-48U
ATMEL	AT89S8253	QFP44	PA44QF44D
ATMEL	AT90CAN128	TQFP64	PA64QF48DD
ATMEL	AT90CAN32	TQFP64	PA64QF48DD
ATMEL	AT90CAN64	TQFP64	PA64QF48DD
ATMEL	AT90LS2323	DIP8	
ATMEL	AT90LS2333	DIP28	
ATMEL	AT90LS2343	DIP8	
ATMEL	AT90LS4433	DIP28	
ATMEL	AT90LS4434	DIP40	
ATMEL	AT90LS4434	PLCC44	PA44-48U
ATMEL	AT90LS8535	DIP40	
ATMEL	AT90LS8535	PLCC44	PA44-48U
ATMEL	AT90PWM2	SOIC24	PA28SO28D-EO-300
ATMEL	AT90PWM2B	SOIC24	PA28SO28D-EO-300
ATMEL	AT90S1200	DIP20	
ATMEL	AT90S1200	SOIC20	PA28SO28D-EO-300
ATMEL	AT90S1200	SSOP20	PA28SS28D
ATMEL	AT90S1200A	DIP20	
ATMEL	AT90S1200A	SOIC20	PA28SO28D-EO-300

ATMEL	AT90S1200A	SSOP20	PA28SS28D
ATMEL	AT90S2313	DIP20	
ATMEL	AT90S2323	DIP8	
ATMEL	AT90S2333	DIP28	
ATMEL	AT90S2343	DIP8	
ATMEL	AT90S4414	DIP40	
ATMEL	AT90S4414	PLCC44	PA44-48U
ATMEL	AT90S4433	DIP28	
ATMEL	AT90S4434	DIP40	
ATMEL	AT90S4434	PLCC44	PA44-48U
ATMEL	AT90S8515	DIP40	
ATMEL	AT90S8515	PLCC44	PA44-48U
ATMEL	AT90S8535	DIP40	
ATMEL	AT90S8535	PLCC44	PA44-48U
ATMEL	AT90USB1287	TQFP64	PA64QF48DD
ATMEL	AT90USB647	TQFP64	PA64QF48DD
ATMEL	AT91SAM7S128	QFP64	PA64QF48DC
ATMEL	AT91SAM7S256	QFP64	PA64QF48DC
ATMEL	AT91SAM7S64	QFP64	PA64QF48DC
ATMEL	AT93C46	DIP8	
ATMEL	AT93C46	SOIC8	PA16SO16D-EO-150
ATMEL	AT93C46	TSSOP8	PA8TSS-OT
ATMEL	AT93C46A	DIP8	
ATMEL	AT93C46A	SOIC8	PA16SO16D-EO-150
ATMEL	AT93C46A	TSSOP8	PA8TSS-OT
ATMEL	AT93C46R	SOIC8	PA8SO8D-EO-150
ATMEL	AT93C56	DIP8	
ATMEL	AT93C56	SOIC8	PA16SO16D-EO-150
ATMEL	AT93C56	TSSOP8	PA8TSS-OT
ATMEL	AT93C56A	DIP8	
ATMEL	AT93C56A	SOIC8	PA16SO16D-EO-150
ATMEL	AT93C56A	TSSOP8	PA8TSS-OT
ATMEL	AT93C56R	SOIC8	PA8SO8D-EO-150
ATMEL	AT93C57	DIP8	
ATMEL	AT93C57	SOIC8	PA16SO16D-EO-150
ATMEL	AT93C66	DIP8	
ATMEL	AT93C66	SOIC8	PA16SO16D-EO-150
ATMEL	AT93C66	TSSOP8	PA8TSS-OT
ATMEL	AT93C66A	DIP8	
ATMEL	AT93C66A	SOIC8	PA16SO16D-EO-150
ATMEL	AT93C66A	TSSOP8	PA8TSS-OT
ATMEL	AT93C66B-XHM	TSSOP8	PA8TSS8D
ATMEL	AT93C66R	SOIC8	PA8SO8D-EO-150
ATMEL	AT93C86	DIP8	
ATMEL	AT93C86	SOIC8	PA16SO16D-EO-150
ATMEL	AT93C86	TSSOP8	PA8TSS-OT
ATMEL	AT93C86A	DIP8	
ATMEL	AT93C86A	SOIC8	PA16SO16D-EO-150
ATMEL	AT93C86A	TSSOP8	PA8TSS-OT
ATMEL	ATF1500	PLCC44	PA44-48U
ATMEL	ATF1500	QFP44	PA44QF44D
ATMEL	ATF1500A	PLCC44	PA44-48U
ATMEL	ATF1500A	QFP44	PA44QF44D
ATMEL	ATF1500ABV	PLCC44	PA44-48U
ATMEL	ATF1500ABV	QFP44	PA44QF44D
ATMEL	ATF1500AL	PLCC44	PA44-48U
ATMEL	ATF1500AL	QFP44	PA44QF44D
ATMEL	ATF1502AS	PLCC44	PA44-48U
ATMEL	ATF1502AS	QFP44	PA44QF44D
ATMEL	ATF1502ASL	PLCC44	PA44-48U
ATMEL	ATF1502ASL	QFP44	PA44QF44D
ATMEL	ATF1502ASV	PLCC44	PA44-48U
ATMEL	ATF1502ASV	QFP44	PA44QF44D
ATMEL	ATF1502BE-A44	QFP44	PA44QF44D
ATMEL	ATF1504AS	PLCC44	PA44-48U
ATMEL	ATF1504AS	PLCC68	PA150X-68LC
ATMEL	ATF1504AS	PLCC84	PA150X-84LC
ATMEL	ATF1504ASV	PLCC44	PA44-48U
ATMEL	ATF1504ASV	PLCC68	PA150X-68LC
ATMEL	ATF1504ASV	PLCC84	PA150X-84LC
ATMEL	ATF1504BE-A100	TQFP100	PA100TQ48DE
ATMEL	ATF1504BE-A44	QFP44	PA44QF44D
ATMEL	ATF1508AS	PLCC84	PA150X-84LC

ATMEL	ATF1508AS	TQFP100	PA100TQ48D
ATMEL	ATF1508ASV	PLCC84	PA150X-84LC
ATMEL	ATF16LV8C	DIP20	
ATMEL	ATF16LV8C	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8C	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8C	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas10H8	DIP20	
ATMEL	ATF16LV8Cas10H8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas10H8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas10H8	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas10L8	DIP20	
ATMEL	ATF16LV8Cas10L8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas10L8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas10L8	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas10P8	DIP20	
ATMEL	ATF16LV8Cas10P8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas10P8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas10P8	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas12H6	DIP20	
ATMEL	ATF16LV8Cas12H6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas12H6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas12H6	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas12L6	DIP20	
ATMEL	ATF16LV8Cas12L6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas12L6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas12L6	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas12P6	DIP20	
ATMEL	ATF16LV8Cas12P6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas12P6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas12P6	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas14H4	DIP20	
ATMEL	ATF16LV8Cas14H4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas14H4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas14H4	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas14L4	DIP20	
ATMEL	ATF16LV8Cas14L4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas14L4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas14L4	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas14P4	DIP20	
ATMEL	ATF16LV8Cas14P4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas14P4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas14P4	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas16H2	DIP20	
ATMEL	ATF16LV8Cas16H2	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16H2	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16H2	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas16H8	DIP20	
ATMEL	ATF16LV8Cas16H8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16H8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16H8	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas16L2	DIP20	
ATMEL	ATF16LV8Cas16L2	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16L2	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16L2	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas16L8	DIP20	
ATMEL	ATF16LV8Cas16L8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16L8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16L8	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas16P2	DIP20	
ATMEL	ATF16LV8Cas16P2	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16P2	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16P2	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas16P8	DIP20	
ATMEL	ATF16LV8Cas16P8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16P8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16P8	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas16R4	DIP20	
ATMEL	ATF16LV8Cas16R4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16R4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16R4	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas16R6	DIP20	
ATMEL	ATF16LV8Cas16R6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16R6	SOIC20	PA20SO20D-EO-210

ATMEL	ATF16LV8Cas16R6	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas16R8	DIP20	
ATMEL	ATF16LV8Cas16R8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16R8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16R8	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas16RP4	DIP20	
ATMEL	ATF16LV8Cas16RP4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16RP4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16RP4	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas16RP6	DIP20	
ATMEL	ATF16LV8Cas16RP6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16RP6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16RP6	TSSOP20	PA24TSS24D
ATMEL	ATF16LV8Cas16RP8	DIP20	
ATMEL	ATF16LV8Cas16RP8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16LV8Cas16RP8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16LV8Cas16RP8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8B	DIP20	
ATMEL	ATF16V8B	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8B	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8B	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas10H8	DIP20	
ATMEL	ATF16V8Bas10H8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas10H8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas10H8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas10L8	DIP20	
ATMEL	ATF16V8Bas10L8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas10L8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas10L8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas10P8	DIP20	
ATMEL	ATF16V8Bas10P8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas10P8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas10P8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas12H6	DIP20	
ATMEL	ATF16V8Bas12H6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas12H6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas12H6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas12L6	DIP20	
ATMEL	ATF16V8Bas12L6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas12L6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas12L6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas12P6	DIP20	
ATMEL	ATF16V8Bas12P6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas12P6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas12P6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas14H4	DIP20	
ATMEL	ATF16V8Bas14H4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas14H4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas14H4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas14L4	DIP20	
ATMEL	ATF16V8Bas14L4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas14L4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas14L4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas14P4	DIP20	
ATMEL	ATF16V8Bas14P4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas14P4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas14P4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas16H2	DIP20	
ATMEL	ATF16V8Bas16H2	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16H2	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16H2	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas16H8	DIP20	
ATMEL	ATF16V8Bas16H8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16H8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16H8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas16L2	DIP20	
ATMEL	ATF16V8Bas16L2	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16L2	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16L2	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas16L8	DIP20	
ATMEL	ATF16V8Bas16L8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16L8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16L8	TSSOP20	PA24TSS24D

ATMEL	ATF16V8Bas16P2	DIP20	
ATMEL	ATF16V8Bas16P2	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16P2	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16P2	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas16P8	DIP20	
ATMEL	ATF16V8Bas16P8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16P8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16P8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas16R4	DIP20	
ATMEL	ATF16V8Bas16R4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16R4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16R4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas16R6	DIP20	
ATMEL	ATF16V8Bas16R6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16R6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16R6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas16R8	DIP20	
ATMEL	ATF16V8Bas16R8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16R8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16R8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas16RP4	DIP20	
ATMEL	ATF16V8Bas16RP4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16RP4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16RP4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas16RP6	DIP20	
ATMEL	ATF16V8Bas16RP6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16RP6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16RP6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Bas16RP8	DIP20	
ATMEL	ATF16V8Bas16RP8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Bas16RP8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Bas16RP8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQ	DIP20	
ATMEL	ATF16V8BQ	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQ	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQ	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas10H8	DIP20	
ATMEL	ATF16V8BQas10H8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas10H8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas10H8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas10L8	DIP20	
ATMEL	ATF16V8BQas10L8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas10L8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas10L8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas10P8	DIP20	
ATMEL	ATF16V8BQas10P8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas10P8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas10P8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas12H6	DIP20	
ATMEL	ATF16V8BQas12H6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas12H6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas12H6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas12L6	DIP20	
ATMEL	ATF16V8BQas12L6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas12L6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas12L6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas12P6	DIP20	
ATMEL	ATF16V8BQas12P6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas12P6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas12P6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas14H4	DIP20	
ATMEL	ATF16V8BQas14H4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas14H4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas14H4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas14L4	DIP20	
ATMEL	ATF16V8BQas14L4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas14L4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas14L4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas14P4	DIP20	
ATMEL	ATF16V8BQas14P4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas14P4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas14P4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas16H2	DIP20	

ATMEL	ATF16V8BQas16H2	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16H2	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16H2	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas16H8	DIP20	
ATMEL	ATF16V8BQas16H8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16H8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16H8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas16L2	DIP20	
ATMEL	ATF16V8BQas16L2	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16L2	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16L2	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas16L8	DIP20	
ATMEL	ATF16V8BQas16L8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16L8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16L8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas16P2	DIP20	
ATMEL	ATF16V8BQas16P2	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16P2	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16P2	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas16P8	DIP20	
ATMEL	ATF16V8BQas16P8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16P8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16P8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas16R4	DIP20	
ATMEL	ATF16V8BQas16R4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16R4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16R4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas16R6	DIP20	
ATMEL	ATF16V8BQas16R6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16R6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16R6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas16R8	DIP20	
ATMEL	ATF16V8BQas16R8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16R8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16R8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas16RP4	DIP20	
ATMEL	ATF16V8BQas16RP4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16RP4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16RP4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas16RP6	DIP20	
ATMEL	ATF16V8BQas16RP6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16RP6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16RP6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQas16RP8	DIP20	
ATMEL	ATF16V8BQas16RP8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQas16RP8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQas16RP8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQL	DIP20	
ATMEL	ATF16V8BQL	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQL	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQL	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas10H8	DIP20	
ATMEL	ATF16V8BQLas10H8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas10H8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas10H8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas10L8	DIP20	
ATMEL	ATF16V8BQLas10L8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas10L8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas10L8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas10P8	DIP20	
ATMEL	ATF16V8BQLas10P8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas10P8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas10P8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas12H6	DIP20	
ATMEL	ATF16V8BQLas12H6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas12H6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas12H6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas12L6	DIP20	
ATMEL	ATF16V8BQLas12L6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas12L6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas12L6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas12P6	DIP20	
ATMEL	ATF16V8BQLas12P6	PLCC20	PA20LC20D[Dead Bug]

ATMEL	ATF16V8BQLas12P6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas12P6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas14H4	DIP20	
ATMEL	ATF16V8BQLas14H4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas14H4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas14H4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas14L4	DIP20	
ATMEL	ATF16V8BQLas14L4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas14L4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas14L4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas14P4	DIP20	
ATMEL	ATF16V8BQLas14P4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas14P4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas14P4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas16H2	DIP20	
ATMEL	ATF16V8BQLas16H2	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16H2	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16H2	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas16H8	DIP20	
ATMEL	ATF16V8BQLas16H8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16H8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16H8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas16L2	DIP20	
ATMEL	ATF16V8BQLas16L2	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16L2	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16L2	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas16L8	DIP20	
ATMEL	ATF16V8BQLas16L8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16L8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16L8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas16P2	DIP20	
ATMEL	ATF16V8BQLas16P2	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16P2	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16P2	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas16P8	DIP20	
ATMEL	ATF16V8BQLas16P8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16P8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16P8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas16R4	DIP20	
ATMEL	ATF16V8BQLas16R4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16R4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16R4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas16R6	DIP20	
ATMEL	ATF16V8BQLas16R6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16R6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16R6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas16R8	DIP20	
ATMEL	ATF16V8BQLas16R8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16R8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16R8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas16RP4	DIP20	
ATMEL	ATF16V8BQLas16RP4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16RP4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16RP4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas16RP6	DIP20	
ATMEL	ATF16V8BQLas16RP6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16RP6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16RP6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8BQLas16RP8	DIP20	
ATMEL	ATF16V8BQLas16RP8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8BQLas16RP8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8BQLas16RP8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8C	DIP20	
ATMEL	ATF16V8C	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8C	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8C	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas10H8	DIP20	
ATMEL	ATF16V8Cas10H8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas10H8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas10H8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas10L8	DIP20	
ATMEL	ATF16V8Cas10L8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas10L8	SOIC20	PA20SO20D-EO-210



ATMEL	ATF16V8Cas10L8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas10P8	DIP20	
ATMEL	ATF16V8Cas10P8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas10P8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas10P8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas12H6	DIP20	
ATMEL	ATF16V8Cas12H6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas12H6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas12H6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas12L6	DIP20	
ATMEL	ATF16V8Cas12L6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas12L6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas12L6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas12P6	DIP20	
ATMEL	ATF16V8Cas12P6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas12P6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas12P6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas14H4	DIP20	
ATMEL	ATF16V8Cas14H4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas14H4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas14H4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas14L4	DIP20	
ATMEL	ATF16V8Cas14L4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas14L4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas14L4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas14P4	DIP20	
ATMEL	ATF16V8Cas14P4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas14P4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas14P4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas16H2	DIP20	
ATMEL	ATF16V8Cas16H2	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16H2	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16H2	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas16H8	DIP20	
ATMEL	ATF16V8Cas16H8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16H8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16H8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas16L2	DIP20	
ATMEL	ATF16V8Cas16L2	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16L2	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16L2	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas16L8	DIP20	
ATMEL	ATF16V8Cas16L8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16L8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16L8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas16P2	DIP20	
ATMEL	ATF16V8Cas16P2	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16P2	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16P2	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas16P8	DIP20	
ATMEL	ATF16V8Cas16P8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16P8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16P8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas16R4	DIP20	
ATMEL	ATF16V8Cas16R4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16R4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16R4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas16R6	DIP20	
ATMEL	ATF16V8Cas16R6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16R6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16R6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas16R8	DIP20	
ATMEL	ATF16V8Cas16R8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16R8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16R8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas16RP4	DIP20	
ATMEL	ATF16V8Cas16RP4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16RP4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16RP4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8Cas16RP6	DIP20	
ATMEL	ATF16V8Cas16RP6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16RP6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16RP6	TSSOP20	PA24TSS24D

ATMEL	ATF16V8Cas16RP8	DIP20	
ATMEL	ATF16V8Cas16RP8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8Cas16RP8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8Cas16RP8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZ	DIP20	
ATMEL	ATF16V8CZ	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZ	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZ	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas10H8	DIP20	
ATMEL	ATF16V8CZas10H8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas10H8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas10H8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas10L8	DIP20	
ATMEL	ATF16V8CZas10L8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas10L8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas10L8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas10P8	DIP20	
ATMEL	ATF16V8CZas10P8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas10P8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas10P8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas12H6	DIP20	
ATMEL	ATF16V8CZas12H6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas12H6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas12H6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas12L6	DIP20	
ATMEL	ATF16V8CZas12L6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas12L6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas12L6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas12P6	DIP20	
ATMEL	ATF16V8CZas12P6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas12P6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas12P6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas14H4	DIP20	
ATMEL	ATF16V8CZas14H4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas14H4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas14H4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas14L4	DIP20	
ATMEL	ATF16V8CZas14L4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas14L4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas14L4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas14P4	DIP20	
ATMEL	ATF16V8CZas14P4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas14P4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas14P4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas16H2	DIP20	
ATMEL	ATF16V8CZas16H2	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16H2	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16H2	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas16H8	DIP20	
ATMEL	ATF16V8CZas16H8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16H8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16H8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas16L2	DIP20	
ATMEL	ATF16V8CZas16L2	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16L2	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16L2	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas16L8	DIP20	
ATMEL	ATF16V8CZas16L8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16L8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16L8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas16P2	DIP20	
ATMEL	ATF16V8CZas16P2	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16P2	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16P2	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas16P8	DIP20	
ATMEL	ATF16V8CZas16P8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16P8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16P8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas16R4	DIP20	
ATMEL	ATF16V8CZas16R4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16R4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16R4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas16R6	DIP20	

ATMEL	ATF16V8CZas16R6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16R6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16R6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas16R8	DIP20	
ATMEL	ATF16V8CZas16R8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16R8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16R8	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas16RP4	DIP20	
ATMEL	ATF16V8CZas16RP4	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16RP4	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16RP4	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas16RP6	DIP20	
ATMEL	ATF16V8CZas16RP6	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16RP6	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16RP6	TSSOP20	PA24TSS24D
ATMEL	ATF16V8CZas16RP8	DIP20	
ATMEL	ATF16V8CZas16RP8	PLCC20	PA20LC20D[Dead Bug]
ATMEL	ATF16V8CZas16RP8	SOIC20	PA20SO20D-EO-210
ATMEL	ATF16V8CZas16RP8	TSSOP20	PA24TSS24D
ATMEL	ATF20V8B	DIP24	
ATMEL	ATF20V8B	PLCC28	PA28PL28D
ATMEL	ATF20V8B	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8B	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas14H8	DIP24	
ATMEL	ATF20V8Bas14H8	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas14H8	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas14H8	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas14L8	DIP24	
ATMEL	ATF20V8Bas14L8	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas14L8	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas14L8	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas14P8	DIP24	
ATMEL	ATF20V8Bas14P8	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas14P8	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas14P8	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas16H6	DIP24	
ATMEL	ATF20V8Bas16H6	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas16H6	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas16H6	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas16L6	DIP24	
ATMEL	ATF20V8Bas16L6	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas16L6	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas16L6	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas16P6	DIP24	
ATMEL	ATF20V8Bas16P6	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas16P6	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas16P6	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas18H4	DIP24	
ATMEL	ATF20V8Bas18H4	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas18H4	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas18H4	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas18L4	DIP24	
ATMEL	ATF20V8Bas18L4	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas18L4	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas18L4	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas18P4	DIP24	
ATMEL	ATF20V8Bas18P4	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas18P4	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas18P4	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas20H2	DIP24	
ATMEL	ATF20V8Bas20H2	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas20H2	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20H2	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas20H8	DIP24	
ATMEL	ATF20V8Bas20H8	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas20H8	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20H8	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas20L2	DIP24	
ATMEL	ATF20V8Bas20L2	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas20L2	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20L2	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas20L8	DIP24	
ATMEL	ATF20V8Bas20L8	PLCC28	PA28PL28D

ATMEL	ATF20V8Bas20L8	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20L8	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas20P2	DIP24	
ATMEL	ATF20V8Bas20P2	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas20P2	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20P2	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas20P8	DIP24	
ATMEL	ATF20V8Bas20P8	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas20P8	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20P8	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas20R4	DIP24	
ATMEL	ATF20V8Bas20R4	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas20R4	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20R4	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas20R6	DIP24	
ATMEL	ATF20V8Bas20R6	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas20R6	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20R6	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas20R8	DIP24	
ATMEL	ATF20V8Bas20R8	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas20R8	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20R8	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas20RP4	DIP24	
ATMEL	ATF20V8Bas20RP4	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas20RP4	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20RP4	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas20RP6	DIP24	
ATMEL	ATF20V8Bas20RP6	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas20RP6	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20RP6	TSSOP24	PA24TSS24D
ATMEL	ATF20V8Bas20RP8	DIP24	
ATMEL	ATF20V8Bas20RP8	PLCC28	PA28PL28D
ATMEL	ATF20V8Bas20RP8	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8Bas20RP8	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BL	DIP24	
ATMEL	ATF20V8BL	PLCC28	PA28PL28D
ATMEL	ATF20V8BL	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BL	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas14H8	DIP24	
ATMEL	ATF20V8BLas14H8	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas14H8	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas14H8	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas14L8	DIP24	
ATMEL	ATF20V8BLas14L8	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas14L8	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas14L8	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas14P8	DIP24	
ATMEL	ATF20V8BLas14P8	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas14P8	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas14P8	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas16H6	DIP24	
ATMEL	ATF20V8BLas16H6	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas16H6	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas16H6	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas16L6	DIP24	
ATMEL	ATF20V8BLas16L6	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas16L6	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas16L6	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas16P6	DIP24	
ATMEL	ATF20V8BLas16P6	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas16P6	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas16P6	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas18H4	DIP24	
ATMEL	ATF20V8BLas18H4	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas18H4	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas18H4	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas18L4	DIP24	
ATMEL	ATF20V8BLas18L4	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas18L4	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas18L4	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas18P4	DIP24	
ATMEL	ATF20V8BLas18P4	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas18P4	SOIC24	PA28SO28D-EO-300

ATMEL	ATF20V8BLas18P4	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas20H2	DIP24	
ATMEL	ATF20V8BLas20H2	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas20H2	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20H2	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas20H8	DIP24	
ATMEL	ATF20V8BLas20H8	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas20H8	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20H8	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas20L2	DIP24	
ATMEL	ATF20V8BLas20L2	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas20L2	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20L2	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas20L8	DIP24	
ATMEL	ATF20V8BLas20L8	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas20L8	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20L8	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas20P2	DIP24	
ATMEL	ATF20V8BLas20P2	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas20P2	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20P2	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas20P8	DIP24	
ATMEL	ATF20V8BLas20P8	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas20P8	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20P8	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas20R4	DIP24	
ATMEL	ATF20V8BLas20R4	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas20R4	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20R4	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas20R6	DIP24	
ATMEL	ATF20V8BLas20R6	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas20R6	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20R6	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas20R8	DIP24	
ATMEL	ATF20V8BLas20R8	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas20R8	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20R8	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas20RP4	DIP24	
ATMEL	ATF20V8BLas20RP4	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas20RP4	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20RP4	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas20RP6	DIP24	
ATMEL	ATF20V8BLas20RP6	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas20RP6	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20RP6	TSSOP24	PA24TSS24D
ATMEL	ATF20V8BLas20RP8	DIP24	
ATMEL	ATF20V8BLas20RP8	PLCC28	PA28PL28D
ATMEL	ATF20V8BLas20RP8	SOIC24	PA28SO28D-EO-300
ATMEL	ATF20V8BLas20RP8	TSSOP24	PA24TSS24D
ATMEL	ATF22LV10C	DIP24	
ATMEL	ATF22LV10C	PLCC28	PA28PL28D
ATMEL	ATF22LV10C(UES)	DIP24	
ATMEL	ATF22LV10C(UES)	PLCC28	PA28PL28D
ATMEL	ATF22LV10CEXT	DIP24	
ATMEL	ATF22LV10CEXT	PLCC28	PA28PL28D
ATMEL	ATF22LV10CQZ	DIP24	
ATMEL	ATF22LV10CQZ	PLCC28	PA28PL28D
ATMEL	ATF22LV10CQZ(UES)	DIP24	
ATMEL	ATF22LV10CQZ(UES)	PLCC28	PA28PL28D
ATMEL	ATF22LV10CZ	DIP24	
ATMEL	ATF22LV10CZ	PLCC28	PA28PL28D
ATMEL	ATF22LV10CZ(UES)	DIP24	
ATMEL	ATF22LV10CZ(UES)	PLCC28	PA28PL28D
ATMEL	ATF22V10B	DIP24	
ATMEL	ATF22V10B	PLCC28	PA28PL28D
ATMEL	ATF22V10BL	DIP24	
ATMEL	ATF22V10BL	PLCC28	PA28PL28D
ATMEL	ATF22V10C	DIP24	
ATMEL	ATF22V10C	PLCC28	PA28PL28D
ATMEL	ATF22V10C(UES)	DIP24	
ATMEL	ATF22V10C(UES)	PLCC28	PA28PL28D
ATMEL	ATF22V10CEXT	DIP24	
ATMEL	ATF22V10CEXT	PLCC28	PA28PL28D

ATMEL	ATF22V10CQZ	DIP24	
ATMEL	ATF22V10CQZ	PLCC28	PA28PL28D
ATMEL	ATF22V10CQZ(UES)	DIP24	
ATMEL	ATF22V10CQZ(UES)	PLCC28	PA28PL28D
ATMEL	ATF22V10CZ	DIP24	
ATMEL	ATF22V10CZ	PLCC28	PA28PL28D
ATMEL	ATF22V10CZ(UES)	DIP24	
ATMEL	ATF22V10CZ(UES)	PLCC28	PA28PL28D
ATMEL	ATF2500C	DIP40	
ATMEL	ATF2500C	PLCC44	PA44-48U
ATMEL	ATF2500C	TQFP44	PA44QF44D
ATMEL	ATF2500C(V2500)	DIP40	
ATMEL	ATF2500C(V2500)	PLCC44	PA44-48U
ATMEL	ATF2500C(V2500)	TQFP44	PA44QF44D
ATMEL	ATF2500C(V2500B)	DIP40	
ATMEL	ATF2500C(V2500B)	PLCC44	PA44-48U
ATMEL	ATF2500C(V2500B)	TQFP44	PA44QF44D
ATMEL	ATF2500CL	DIP40	
ATMEL	ATF2500CL	PLCC44	PA44-48U
ATMEL	ATF2500CL	TQFP44	PA44QF44D
ATMEL	ATF2500CL(V2500)	DIP40	
ATMEL	ATF2500CL(V2500)	PLCC44	PA44-48U
ATMEL	ATF2500CL(V2500)	TQFP44	PA44QF44D
ATMEL	ATF2500CL(V2500B)	DIP40	
ATMEL	ATF2500CL(V2500B)	PLCC44	PA44-48U
ATMEL	ATF2500CL(V2500B)	TQFP44	PA44QF44D
ATMEL	ATF2500CQ	DIP40	
ATMEL	ATF2500CQ	PLCC44	PA44-48U
ATMEL	ATF2500CQ	TQFP44	PA44QF44D
ATMEL	ATF2500CQ(V2500B)	DIP40	
ATMEL	ATF2500CQ(V2500B)	PLCC44	PA44-48U
ATMEL	ATF2500CQ(V2500B)	TQFP44	PA44QF44D
ATMEL	ATF2500CQL	DIP40	
ATMEL	ATF2500CQL	PLCC44	PA44-48U
ATMEL	ATF2500CQL	TQFP44	PA44QF44D
ATMEL	ATF2500CQL(V2500B)	DIP40	
ATMEL	ATF2500CQL(V2500B)	PLCC44	PA44-48U
ATMEL	ATF2500CQL(V2500B)	TQFP44	PA44QF44D
ATMEL	ATF750C	DIP24	
ATMEL	ATF750C	PLCC28	PA28PL28D
ATMEL	ATF750C	SOIC24	PA28SO28D-EO-300
ATMEL	ATF750C	TSSOP24	PA24TSS24D
ATMEL	ATF750C(V750)	DIP24	
ATMEL	ATF750C(V750)	PLCC28	PA28PL28D
ATMEL	ATF750C(V750)	SOIC24	PA28SO28D-EO-300
ATMEL	ATF750C(V750)	TSSOP24	PA24TSS24D
ATMEL	ATF750C(V750B)	DIP24	
ATMEL	ATF750C(V750B)	PLCC28	PA28PL28D
ATMEL	ATF750C(V750B)	SOIC24	PA28SO28D-EO-300
ATMEL	ATF750C(V750B)	TSSOP24	PA24TSS24D
ATMEL	ATF750CEXT	DIP24	
ATMEL	ATF750CEXT	PLCC28	PA28PL28D
ATMEL	ATF750CEXT	SOIC24	PA28SO28D-EO-300
ATMEL	ATF750CEXT	TSSOP24	PA24TSS24D
ATMEL	ATF750CL	DIP24	
ATMEL	ATF750CL	PLCC28	PA28PL28D
ATMEL	ATF750CL	SOIC24	PA28SO28D-EO-300
ATMEL	ATF750CL	TSSOP24	PA24TSS24D
ATMEL	ATF750CL(V750)	DIP24	
ATMEL	ATF750CL(V750)	PLCC28	PA28PL28D
ATMEL	ATF750CL(V750)	SOIC24	PA28SO28D-EO-300
ATMEL	ATF750CL(V750)	TSSOP24	PA24TSS24D
ATMEL	ATF750CL(V750B)	DIP24	
ATMEL	ATF750CL(V750B)	PLCC28	PA28PL28D
ATMEL	ATF750CL(V750B)	SOIC24	PA28SO28D-EO-300
ATMEL	ATF750CL(V750B)	TSSOP24	PA24TSS24D
ATMEL	ATF750LVC	DIP24	
ATMEL	ATF750LVC	PLCC28	PA28PL28D
ATMEL	ATF750LVC	SOIC24	PA28SO28D-EO-300
ATMEL	ATF750LVC	TSSOP24	PA24TSS24D
ATMEL	ATF750LVC(V750)	DIP24	
ATMEL	ATF750LVC(V750)	PLCC28	PA28PL28D
ATMEL	ATF750LVC(V750)	SOIC24	PA28SO28D-EO-300

ATMEL	ATF750LVC(V750)	TSSOP24	PA24TSS24D
ATMEL	ATF750LVC(V750B)	DIP24	
ATMEL	ATF750LVC(V750B)	PLCC28	PA28PL28D
ATMEL	ATF750LVC(V750B)	SOIC24	PA28SO28D-EO-300
ATMEL	ATF750LVC(V750B)	TSSOP24	PA24TSS24D
ATMEL	ATF750LVCEXT	DIP24	
ATMEL	ATF750LVCEXT	PLCC28	PA28PL28D
ATMEL	ATF750LVCEXT	SOIC24	PA28SO28D-EO-300
ATMEL	ATF750LVCEXT	TSSOP24	PA24TSS24D
ATMEL	ATF750LVCL	DIP24	
ATMEL	ATF750LVCL	PLCC28	PA28PL28D
ATMEL	ATF750LVCL	SOIC24	PA28SO28D-EO-300
ATMEL	ATF750LVCL	TSSOP24	PA24TSS24D
ATMEL	ATF750LVCL(V750)	DIP24	
ATMEL	ATF750LVCL(V750)	PLCC28	PA28PL28D
ATMEL	ATF750LVCL(V750)	SOIC24	PA28SO28D-EO-300
ATMEL	ATF750LVCL(V750)	TSSOP24	PA24TSS24D
ATMEL	ATF750LVCL(V750B)	DIP24	
ATMEL	ATF750LVCL(V750B)	PLCC28	PA28PL28D
ATMEL	ATF750LVCL(V750B)	SOIC24	PA28SO28D-EO-300
ATMEL	ATF750LVCL(V750B)	TSSOP24	PA24TSS24D
ATMEL	ATMEGA128	TQFP64	PA64QF48DD
ATMEL	ATMEGA128L	TQFP64	PA64QF48DD
ATMEL	ATMEGA16	DIP40	
ATMEL	ATMEGA16	QFP44	PA44QF44D
ATMEL	ATMEGA161	DIP40	
ATMEL	ATMEGA161	PLCC44	PA44-48U
ATMEL	ATMEGA161	QFP44	PA44QF44D
ATMEL	ATMEGA161L	DIP40	
ATMEL	ATMEGA161L	PLCC44	PA44-48U
ATMEL	ATMEGA161L	QFP44	PA44QF44D
ATMEL	ATMEGA162	DIP40	
ATMEL	ATMEGA162	QFP44	PA44QF44D
ATMEL	ATMEGA162V	DIP40	
ATMEL	ATMEGA162V	QFP44	PA44QF44D
ATMEL	ATMEGA163	DIP40	
ATMEL	ATMEGA163	QFP44	PA44QF44D
ATMEL	ATMEGA163L	DIP40	
ATMEL	ATMEGA163L	QFP44	PA44QF44D
ATMEL	ATMEGA164P	QFP44	PA44VQ44D
ATMEL	ATmega168	DIP28	
ATMEL	ATmega168	TQFP32	PA32TQ32D
ATMEL	ATmega168	TQFP32	PA32TQ32DA
ATMEL	ATmega168A	DIP28	
ATMEL	ATmega168A	TQFP32	PA32TQ32D
ATMEL	ATmega168A	TQFP32	PA32TQ32DA
ATMEL	ATmega168P	DIP28	
ATMEL	ATmega168P	TQFP32	PA32TQ32D
ATMEL	ATmega168P	TQFP32	PA32TQ32DA
ATMEL	ATmega168PA	DIP28	
ATMEL	ATmega168PA	TQFP32	PA32TQ32D
ATMEL	ATmega168PA	TQFP32	PA32TQ32DA
ATMEL	ATmega168PB	DIP28	
ATMEL	ATmega168PB	TQFP32	PA32TQ32D
ATMEL	ATmega168PB	TQFP32	PA32TQ32DA
ATMEL	ATmega168PV	DIP28	
ATMEL	ATmega168PV	TQFP32	PA32TQ32D
ATMEL	ATmega168PV	TQFP32	PA32TQ32DA
ATMEL	ATmega168V	DIP28	
ATMEL	ATmega168V	TQFP32	PA32TQ32D
ATMEL	ATmega168V	TQFP32	PA32TQ32DA
ATMEL	ATMEGA16A	DIP40	
ATMEL	ATMEGA16A	QFP44	PA44QF44D
ATMEL	ATMEGA16L	DIP40	
ATMEL	ATMEGA16L	QFP44	PA44QF44D
ATMEL	ATMEGA16M1-15MZ	QFN32	PA32MLF32DD
ATMEL	ATMEGA16M1-MU	QFN32	PA32MLF32DD
ATMEL	ATMEGA16U2	TQFP32	PA32TQ32D-YC
ATMEL	ATMEGA32	DIP40	
ATMEL	ATMEGA32	MLF44	PA44ML44D
ATMEL	ATMEGA32	QFP44	PA44QF44D
ATMEL	ATMEGA324P	MLF44	PA44ML44D
ATMEL	ATMEGA324P	QFP44	PA44VQ44D

ATMEL	ATmega328P	DIP28	
ATMEL	ATmega328P	TQFP32	PA32TQ32D
ATMEL	ATmega328P	TQFP32	PA32TQ32DA
ATMEL	ATMEGA32C1	TQFP32	PA32TQ32D
ATMEL	ATMEGA32L	DIP40	
ATMEL	ATMEGA32L	MLF44	PA44ML44D
ATMEL	ATMEGA32L	QFP44	PA44QF44D
ATMEL	ATmega48	DIP28	
ATMEL	ATmega48	TQFP32	PA32TQ32D
ATMEL	ATmega48	TQFP32	PA32TQ32DA
ATMEL	ATmega48A	DIP28	
ATMEL	ATmega48A	TQFP32	PA32TQ32D
ATMEL	ATmega48A	TQFP32	PA32TQ32DA
ATMEL	ATmega48P	DIP28	
ATMEL	ATmega48P	TQFP32	PA32TQ32D
ATMEL	ATmega48P	TQFP32	PA32TQ32DA
ATMEL	ATmega48PA	DIP28	
ATMEL	ATmega48PA	TQFP32	PA32TQ32D
ATMEL	ATmega48PA	TQFP32	PA32TQ32DA
ATMEL	ATmega48PB	DIP28	
ATMEL	ATmega48PB	TQFP32	PA32TQ32D
ATMEL	ATmega48PB	TQFP32	PA32TQ32DA
ATMEL	ATmega48PV	DIP28	
ATMEL	ATmega48PV	TQFP32	PA32TQ32D
ATMEL	ATmega48PV	TQFP32	PA32TQ32DA
ATMEL	ATmega48V	DIP28	
ATMEL	ATmega48V	TQFP32	PA32TQ32D
ATMEL	ATmega48V	TQFP32	PA32TQ32DA
ATMEL	ATMEGA64	TQFP64	PA64QF48DD
ATMEL	ATMEGA644P	QFP44	PA44VQ44D
ATMEL	ATMEGA64L	TQFP64	PA64QF48DD
ATMEL	ATmega8	DIP28	
ATMEL	ATmega8	TQFP32	PA32TQ32D
ATMEL	ATmega8	TQFP32	PA32TQ32DA
ATMEL	ATMEGA8515	DIP40	
ATMEL	ATMEGA8515	PLCC44	PA44-48U
ATMEL	ATMEGA8515	QFP44	PA44QF44D
ATMEL	ATMEGA8515L	DIP40	
ATMEL	ATMEGA8515L	PLCC44	PA44-48U
ATMEL	ATMEGA8515L	QFP44	PA44QF44D
ATMEL	ATMEGA8535	DIP40	
ATMEL	ATMEGA8535	PLCC44	PA44-48U
ATMEL	ATMEGA8535	QFP44	PA44QF44D
ATMEL	ATMEGA8535L	DIP40	
ATMEL	ATMEGA8535L	PLCC44	PA44-48U
ATMEL	ATMEGA8535L	QFP44	PA44QF44D
ATMEL	ATmega88	DIP28	
ATMEL	ATmega88	TQFP32	PA32TQ32D
ATMEL	ATmega88	TQFP32	PA32TQ32DA
ATMEL	ATmega88A	DIP28	
ATMEL	ATmega88A	TQFP32	PA32TQ32D
ATMEL	ATmega88A	TQFP32	PA32TQ32DA
ATMEL	ATmega88P	DIP28	
ATMEL	ATmega88P	TQFP32	PA32TQ32D
ATMEL	ATmega88P	TQFP32	PA32TQ32DA
ATMEL	ATmega88PA	DIP28	
ATMEL	ATmega88PA	TQFP32	PA32TQ32D
ATMEL	ATmega88PA	TQFP32	PA32TQ32DA
ATMEL	ATmega88PB	DIP28	
ATMEL	ATmega88PB	TQFP32	PA32TQ32D
ATMEL	ATmega88PB	TQFP32	PA32TQ32DA
ATMEL	ATmega88PV	DIP28	
ATMEL	ATmega88PV	TQFP32	PA32TQ32D
ATMEL	ATmega88PV	TQFP32	PA32TQ32DA
ATMEL	ATmega88V	DIP28	
ATMEL	ATmega88V	TQFP32	PA32TQ32D
ATMEL	ATmega88V	TQFP32	PA32TQ32DA
ATMEL	ATmega8A	DIP28	
ATMEL	ATmega8A	TQFP32	PA32TQ32D
ATMEL	ATmega8A	TQFP32	PA32TQ32DA
ATMEL	ATmega8L	DIP28	
ATMEL	ATmega8L	TQFP32	PA32TQ32D
ATMEL	ATmega8L	TQFP32	PA32TQ32DA



ATMEL	ATTINY10	DIP8	
ATMEL	ATTINY10	SOIC8	PA20SO20D-EO-210
ATMEL	ATTINY10L	DIP8	
ATMEL	ATTINY10L	SOIC8	PA20SO20D-EO-210
ATMEL	ATTINY11	DIP8	
ATMEL	ATTINY11	SOIC8	PA20SO20D-EO-210
ATMEL	ATTINY11L	DIP8	
ATMEL	ATTINY11L	SOIC8	PA20SO20D-EO-210
ATMEL	ATTINY12	DIP8	
ATMEL	ATTINY12	SOIC8	PA20SO20D-EO-210
ATMEL	ATTINY12L	DIP8	
ATMEL	ATTINY12L	SOIC8	PA20SO20D-EO-210
ATMEL	ATTINY13	DIP8	
ATMEL	ATTINY13	SOIC8	PA16SO16D-EO-150
ATMEL	ATTINY13	SOIC8	PA20SO20D-EO-210
ATMEL	ATTINY13V	DIP8	
ATMEL	ATTINY13V	SOIC8	PA16SO16D-EO-150
ATMEL	ATTINY13V	SOIC8	PA20SO20D-EO-210
ATMEL	ATTINY15L	DIP8	
ATMEL	ATTINY15L	SOIC8	PA20SO20D-EO-210
ATMEL	ATTINY22	DIP8	
ATMEL	ATTINY22	SOIC8	PA20SO20D-EO-210
ATMEL	ATTINY22L	DIP8	
ATMEL	ATTINY22L	SOIC8	PA20SO20D-EO-210
ATMEL	ATTINY2313	DIP20	
ATMEL	ATTINY2313	SOIC20	PA28SO28D-EO-300
ATMEL	ATTINY2313V	DIP20	
ATMEL	ATTINY2313V	SOIC20	PA28SO28D-EO-300
ATMEL	ATTINY24	DIP14	
ATMEL	ATTINY24	SOIC14	PA16SO16D-EO-150
ATMEL	ATTINY24V	DIP14	
ATMEL	ATTINY24V	SOIC14	PA16SO16D-EO-150
ATMEL	ATTINY25	DIP8	
ATMEL	ATTINY25	SOIC8	PA20SO20D-EO-210
ATMEL	ATTINY25V	DIP8	
ATMEL	ATTINY25V	SOIC8	PA20SO20D-EO-210
ATMEL	ATTINY26	DIP20	
ATMEL	ATTINY26	MLF32	PA32QFN28D
ATMEL	ATTINY26	SOIC20	PA28SO28D-EO-300
ATMEL	ATTINY261	DIP20	
ATMEL	ATTINY261	SOIC20	PA28SO28D-EO-300
ATMEL	ATTINY261V	DIP20	
ATMEL	ATTINY261V	SOIC20	PA28SO28D-EO-300
ATMEL	ATTINY26L	DIP20	
ATMEL	ATTINY26L	MLF32	PA32QFN28D
ATMEL	ATTINY26L	SOIC20	PA28SO28D-EO-300
ATMEL	ATTINY28L	DIP28	
ATMEL	ATTINY28L	QFP32	PA32TQ32D-YC
ATMEL	ATTINY28V	DIP28	
ATMEL	ATTINY28V	QFP32	PA32TQ32D-YC
ATMEL	ATTINY44	DIP14	
ATMEL	ATTINY44	SOIC14	PA16SO16D-EO-150
ATMEL	ATTINY44V	DIP14	
ATMEL	ATTINY44V	SOIC14	PA16SO16D-EO-150
ATMEL	ATTINY45	DIP8	
ATMEL	ATTINY45	SOIC8	PA20SO20D-EO-210
ATMEL	ATTINY45V	DIP8	
ATMEL	ATTINY45V	SOIC8	PA20SO20D-EO-210
ATMEL	ATTINY461	DIP20	
ATMEL	ATTINY461	SOIC20	PA28SO28D-EO-300
ATMEL	ATTINY461V	DIP20	
ATMEL	ATTINY461V	SOIC20	PA28SO28D-EO-300
ATMEL	ATTINY828-AU	TQFP32	PA32TQ32D-YC
ATMEL	ATTINY84	DIP14	
ATMEL	ATTINY84V	DIP14	
ATMEL	ATTINY85	DIP8	
ATMEL	ATTINY85	SOIC8	PA20SO20D-EO-210
ATMEL	ATTINY85V	DIP8	
ATMEL	ATTINY85V	SOIC8	PA20SO20D-EO-210
ATMEL	ATTINY861	DIP20	
ATMEL	ATTINY861	SOIC20	PA28SO28D-EO-300
ATMEL	ATTINY861V	DIP20	
ATMEL	ATTINY861V	SOIC20	PA28SO28D-EO-300

ATMEL	ATV2500	DIP40	
ATMEL	ATV2500	PLCC44	PA44-48U
ATMEL	ATV2500B	DIP40	
ATMEL	ATV2500B	PLCC44	PA44-48U
ATMEL	ATV2500BL	DIP40	
ATMEL	ATV2500BL	PLCC44	PA44-48U
ATMEL	ATV2500BQ	DIP40	
ATMEL	ATV2500BQ	PLCC44	PA44-48U
ATMEL	ATV2500BQL	DIP40	
ATMEL	ATV2500BQL	PLCC44	PA44-48U
ATMEL	ATV2500H	DIP40	
ATMEL	ATV2500H	PLCC44	PA44-48U
ATMEL	ATV2500L	DIP40	
ATMEL	ATV2500L	PLCC44	PA44-48U
ATMEL	ATV750	DIP24	
ATMEL	ATV750	PLCC28	PA28PL24D2P6-YA
ATMEL	ATV750B	DIP24	
ATMEL	ATV750B	PLCC28	PA28PL24D2P6-YA
ATMEL	ATV750BL	DIP24	
ATMEL	ATV750BL	PLCC28	PA28PL24D2P6-YA
ATMEL	ATV750BQ	DIP24	
ATMEL	ATV750BQ	PLCC28	PA28PL24D2P6-YA
ATMEL	ATV750BQL	DIP24	
ATMEL	ATV750BQL	PLCC28	PA28PL24D2P6-YA
ATMEL	ATV750L	DIP24	
ATMEL	ATV750L	PLCC28	PA28PL24D2P6-YA
ATMEL	T89C51CC01	PLCC44	PA44-48U
ATMEL	T89C51CC01	TQFP44	PA44TQ44D-EO
AUSTIN-SEMICONDUCTOR	SMJ27C040	DIP32	
BENCHMARQ	BQ4011	EDIP28	
BENCHMARQ	BQ4011Y	EDIP28	
BENCHMARQ	BQ4013	EDIP32	
BENCHMARQ	BQ4013Y	EDIP32	
BMT	BM29LV160B	TSOP48	PA48TS48D
BMT	BM29LV160T	TSOP48	PA48TS48D
BRIGHT	BM29F040	DIP32	
BRIGHT	BM29F040	PLCC32	PA32PL32D
BRIGHT	BM29F040	TSOP32	PA32TS20/PA32TS32D-20
BRIGHT	BM29F400B	SOP44	PA44SO44D
BRIGHT	BM29F400B	TSOP48	PA48TS48D
BRIGHT	BM29F400T	SOP44	PA44SO44D
BRIGHT	BM29F400T	TSOP48	PA48TS48D
CATALYST	CAT24AC128	DIP8	
CATALYST	CAT24AC128-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24AC128-K	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24AC128-L	DIP8	
CATALYST	CAT24AC128-U14	TSSOP14	PA28TSS28D-EO
CATALYST	CAT24AC128-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24AC128-X	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24AC128-Y14	TSSOP14	PA28TSS28D-EO
CATALYST	CAT24C00	DIP8	
CATALYST	CAT24C00-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C00-L	DIP8	
CATALYST	CAT24C00-TB	SOT23-5	PA5SOT5D
CATALYST	CAT24C00-TP	SOT23-5	PA5SOT5D
CATALYST	CAT24C00-U	TSSOP8	PA24TSS24D
CATALYST	CAT24C00-U	TSSOP8	PA8TSS8D
CATALYST	CAT24C00-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C00-Y	TSSOP8	PA24TSS24D
CATALYST	CAT24C00-Y	TSSOP8	PA8TSS8D
CATALYST	CAT24C01	DIP8	
CATALYST	CAT24C01B	DIP8	
CATALYST	CAT24C01B-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C01B-L	DIP8	
CATALYST	CAT24C01B-R	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24C01B-U	TSSOP8	PA24TSS24D
CATALYST	CAT24C01B-U	TSSOP8	PA8TSS8D
CATALYST	CAT24C01B-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C01B-Y	TSSOP8	PA24TSS24D
CATALYST	CAT24C01B-Y	TSSOP8	PA8TSS8D
CATALYST	CAT24C01B-Z	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24C01-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C01-J14	SOIC14	PA16SO16D-EO-150

CATALYST	CAT24C01-U	TSSOP8	PA24TSS24D
CATALYST	CAT24C01-U	TSSOP8	PA8TSS8D
CATALYST	CAT24C02	DIP8	
CATALYST	CAT24C021	DIP8	
CATALYST	CAT24C021-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C022	DIP8	
CATALYST	CAT24C022-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C023	DIP8	
CATALYST	CAT24C023-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C02-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C02-J14	SOIC14	PA16SO16D-EO-150
CATALYST	CAT24C02-U	TSSOP8	PA24TSS24D
CATALYST	CAT24C02-U	TSSOP8	PA8TSS8D
CATALYST	CAT24C04	DIP8	
CATALYST	CAT24C041	DIP8	
CATALYST	CAT24C041-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C042	DIP8	
CATALYST	CAT24C042-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C043	DIP8	
CATALYST	CAT24C043-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C04-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C04-J14	SOIC14	PA16SO16D-EO-150
CATALYST	CAT24C04-U	TSSOP8	PA24TSS24D
CATALYST	CAT24C04-U	TSSOP8	PA8TSS8D
CATALYST	CAT24C08	DIP8	
CATALYST	CAT24C081	DIP8	
CATALYST	CAT24C081-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C082	DIP8	
CATALYST	CAT24C082-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C083	DIP8	
CATALYST	CAT24C083-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C08-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C08-J14	SOIC14	PA16SO16D-EO-150
CATALYST	CAT24C08-U	TSSOP8	PA24TSS24D
CATALYST	CAT24C08-U	TSSOP8	PA8TSS8D
CATALYST	CAT24C16	DIP8	
CATALYST	CAT24C161	DIP8	
CATALYST	CAT24C161-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C162	DIP8	
CATALYST	CAT24C162-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C163	DIP8	
CATALYST	CAT24C163-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C16-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C16-J14	SOIC14	PA16SO16D-EO-150
CATALYST	CAT24C16-U	TSSOP8	PA24TSS24D
CATALYST	CAT24C16-U	TSSOP8	PA8TSS8D
CATALYST	CAT24C21B	DIP8	
CATALYST	CAT24C21B-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C21B-L	DIP8	
CATALYST	CAT24C21B-R	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24C21B-U	TSSOP8	PA24TSS24D
CATALYST	CAT24C21B-U	TSSOP8	PA8TSS8D
CATALYST	CAT24C21B-U	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C21B-Y	TSSOP8	PA24TSS24D
CATALYST	CAT24C21B-Y	TSSOP8	PA8TSS8D
CATALYST	CAT24C21B-Z	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24C256	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT24C256	SOP8	PA20SO20D-EO-210
CATALYST	CAT24C256	TSSOP8	PA8TSS8D
CATALYST	CAT24C256	USON8	PA8SON8D(2x3)
CATALYST	CAT24C321	DIP8	
CATALYST	CAT24C321-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C322	DIP8	
CATALYST	CAT24C322-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C323	DIP8	
CATALYST	CAT24C323-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C32-L	DIP8	
CATALYST	CAT24C32-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C32-Y	TSSOP8	PA24TSS24D
CATALYST	CAT24C32-Y	TSSOP8	PA8TSS8D
CATALYST	CAT24C641	DIP8	
CATALYST	CAT24C641-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C642	DIP8	

CATALYST	CAT24C642-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C643	DIP8	
CATALYST	CAT24C643-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C64-L	DIP8	
CATALYST	CAT24C64-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24C64-Y	TSSOP8	PA24TSS24D
CATALYST	CAT24C64-Y	TSSOP8	PA8TSS8D
CATALYST	CAT24FC01	DIP8	
CATALYST	CAT24FC01-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24FC01-L	DIP8	
CATALYST	CAT24FC01-R	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24FC01-U	TSSOP8	PA24TSS24D
CATALYST	CAT24FC01-U	TSSOP8	PA8TSS8D
CATALYST	CAT24FC01-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24FC01-Y	TSSOP8	PA24TSS24D
CATALYST	CAT24FC01-Y	TSSOP8	PA8TSS8D
CATALYST	CAT24FC01-Z	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24FC02	DIP8	
CATALYST	CAT24FC02-GL	DIP8	
CATALYST	CAT24FC02-GW	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24FC02-GY	TSSOP8	PA24TSS24D
CATALYST	CAT24FC02-GY	TSSOP8	PA8TSS8D
CATALYST	CAT24FC02-GZ	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24FC02-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24FC02-L	DIP8	
CATALYST	CAT24FC02-R	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24FC02-U	TSSOP8	PA24TSS24D
CATALYST	CAT24FC02-U	TSSOP8	PA8TSS8D
CATALYST	CAT24FC02-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24FC02-Y	TSSOP8	PA24TSS24D
CATALYST	CAT24FC02-Y	TSSOP8	PA8TSS8D
CATALYST	CAT24FC02-Z	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24FC16	DIP8	
CATALYST	CAT24FC16-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24FC16-L	DIP8	
CATALYST	CAT24FC16-R	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24FC16-RD4	TDFN8	PA8TDFN8D
CATALYST	CAT24FC16-U	TSSOP8	PA24TSS24D
CATALYST	CAT24FC16-U	TSSOP8	PA8TSS8D
CATALYST	CAT24FC16-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24FC16-Y	TSSOP8	PA24TSS24D
CATALYST	CAT24FC16-Y	TSSOP8	PA8TSS8D
CATALYST	CAT24FC16-Z	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24FC16-ZD4	TDFN8	PA8TDFN8D
CATALYST	CAT24FC17	DIP8	
CATALYST	CAT24FC17-GD4	TDFN8	PA8TDFN8D
CATALYST	CAT24FC17-GL	DIP8	
CATALYST	CAT24FC17-GW	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24FC17-GY	TSSOP8	PA24TSS24D
CATALYST	CAT24FC17-GY	TSSOP8	PA8TSS8D
CATALYST	CAT24FC17-GZ	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24FC17-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24FC17-L	DIP8	
CATALYST	CAT24FC17-R	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24FC17-RD4	TDFN8	PA8TDFN8D
CATALYST	CAT24FC17-U	TSSOP8	PA24TSS24D
CATALYST	CAT24FC17-U	TSSOP8	PA8TSS8D
CATALYST	CAT24FC17-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24FC17-Y	TSSOP8	PA24TSS24D
CATALYST	CAT24FC17-Y	TSSOP8	PA8TSS8D
CATALYST	CAT24FC17-Z	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24FC17-ZD4	TDFN8	PA8TDFN8D
CATALYST	CAT24FC256	DIP8	
CATALYST	CAT24FC256	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT24FC256	SOP8	PA20SO20D-EO-210
CATALYST	CAT24FC32	DIP8	
CATALYST	CAT24FC32A	DIP8	
CATALYST	CAT24FC32A-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24FC32A-K	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24FC32A-L	DIP8	
CATALYST	CAT24FC32A-U	TSSOP8	PA24TSS24D
CATALYST	CAT24FC32A-U	TSSOP8	PA8TSS8D
CATALYST	CAT24FC32A-W	SOIC8	PA8SO8D-EO-150

CATALYST	CAT24FC32A-X	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24FC32A-Y	TSSOP8	PA24TSS24D
CATALYST	CAT24FC32A-Y	TSSOP8	PA8TSS8D
CATALYST	CAT24FC32-GL	DIP8	
CATALYST	CAT24FC32-GW	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24FC32-GX	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24FC32-GY	TSSOP8	PA24TSS24D
CATALYST	CAT24FC32-GY	TSSOP8	PA8TSS8D
CATALYST	CAT24FC32-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24FC32-K	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24FC32-L	DIP8	
CATALYST	CAT24FC32-RD2	TDFN8	PA8TDFN8D
CATALYST	CAT24FC32-U	TSSOP8	PA24TSS24D
CATALYST	CAT24FC32-U	TSSOP8	PA8TSS8D
CATALYST	CAT24FC32-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24FC32-X	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24FC32-Y	TSSOP8	PA24TSS24D
CATALYST	CAT24FC32-Y	TSSOP8	PA8TSS8D
CATALYST	CAT24FC32-ZD2	TDFN8	PA8TDFN8D
CATALYST	CAT24FC64	DIP8	
CATALYST	CAT24FC64-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24FC64-K	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24FC64-L	DIP8	
CATALYST	CAT24FC64-RD2	TDFN8	PA8TDFN8D
CATALYST	CAT24FC64-U	TSSOP8	PA24TSS24D
CATALYST	CAT24FC64-U	TSSOP8	PA8TSS8D
CATALYST	CAT24FC64-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24FC64-X	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24FC64-Y	TSSOP8	PA24TSS24D
CATALYST	CAT24FC64-Y	TSSOP8	PA8TSS8D
CATALYST	CAT24FC64-ZD2	TDFN8	PA8TDFN8D
CATALYST	CAT24WC01	DIP8	
CATALYST	CAT24WC01-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC01-L	DIP8	
CATALYST	CAT24WC01-R	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24WC01-U	TSSOP8	PA24TSS24D
CATALYST	CAT24WC01-U	TSSOP8	PA8TSS8D
CATALYST	CAT24WC01-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC01-Y	TSSOP8	PA24TSS24D
CATALYST	CAT24WC01-Y	TSSOP8	PA8TSS8D
CATALYST	CAT24WC01-Z	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24WC02	DIP8	
CATALYST	CAT24WC02-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC02-L	DIP8	
CATALYST	CAT24WC02-R	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24WC02-U	TSSOP8	PA24TSS24D
CATALYST	CAT24WC02-U	TSSOP8	PA8TSS8D
CATALYST	CAT24WC02-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC02-Y	TSSOP8	PA24TSS24D
CATALYST	CAT24WC02-Y	TSSOP8	PA8TSS8D
CATALYST	CAT24WC02-Z	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24WC03	DIP8	
CATALYST	CAT24WC03-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC03-U	TSSOP8	PA24TSS24D
CATALYST	CAT24WC03-U	TSSOP8	PA8TSS8D
CATALYST	CAT24WC04	DIP8	
CATALYST	CAT24WC04-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC04-L	DIP8	
CATALYST	CAT24WC04-R	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24WC04-U	TSSOP8	PA24TSS24D
CATALYST	CAT24WC04-U	TSSOP8	PA8TSS8D
CATALYST	CAT24WC04-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC04-Y	TSSOP8	PA24TSS24D
CATALYST	CAT24WC04-Y	TSSOP8	PA8TSS8D
CATALYST	CAT24WC04-Z	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24WC05	DIP8	
CATALYST	CAT24WC05-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC08	DIP8	
CATALYST	CAT24WC08-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC08-L	DIP8	
CATALYST	CAT24WC08-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC09	DIP8	
CATALYST	CAT24WC09-J	SOIC8	PA8SO8D-EO-150

CATALYST	CAT24WC128	DIP8	
CATALYST	CAT24WC128-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC128-K	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24WC128-U14	TSSOP14	PA28TSS28D-EO
CATALYST	CAT24WC129	DIP8	
CATALYST	CAT24WC129-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC129-K	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24WC16	DIP8	
CATALYST	CAT24WC164	DIP8	
CATALYST	CAT24WC164-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC164-L	DIP8	
CATALYST	CAT24WC164-R	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24WC164-U	TSSOP8	PA24TSS24D
CATALYST	CAT24WC164-U	TSSOP8	PA8TSS8D
CATALYST	CAT24WC164-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC164-Y	TSSOP8	PA24TSS24D
CATALYST	CAT24WC164-Y	TSSOP8	PA8TSS8D
CATALYST	CAT24WC164-Z	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT24WC16-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC16-P	DIP8	
CATALYST	CAT24WC16-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC17	DIP8	
CATALYST	CAT24WC17-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC256	DIP8	
CATALYST	CAT24WC256	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT24WC256	SOP8	PA20SO20D-EO-210
CATALYST	CAT24WC257	DIP8	
CATALYST	CAT24WC257-K	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24WC32	DIP8	
CATALYST	CAT24WC32-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC32-K	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24WC32-L	DIP8	
CATALYST	CAT24WC32-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC32-X	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24WC33	DIP8	
CATALYST	CAT24WC33-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC33-K	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24WC33-L	DIP8	
CATALYST	CAT24WC33-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC33-X	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24WC64	DIP8	
CATALYST	CAT24WC64-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC64-K	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24WC64-L	DIP8	
CATALYST	CAT24WC64-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC64-X	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24WC65	DIP8	
CATALYST	CAT24WC65-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC65-K	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24WC65-L	DIP8	
CATALYST	CAT24WC65-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC65-X	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24WC66	DIP8	
CATALYST	CAT24WC66-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT24WC66-K	SOIC8	PA16SO16D-EO-150
CATALYST	CAT24WC66-L	DIP8	
CATALYST	CAT24WC66-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT25010	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25010	TSSOP8	PA8TSS8D
CATALYST	CAT25010	USON8	PA8SON8D(2x3)
CATALYST	CAT25020	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25020	TSSOP8	PA8TSS8D
CATALYST	CAT25020	USON8	PA8SON8D(2x3)
CATALYST	CAT25040	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25040	TSSOP8	PA8TSS8D
CATALYST	CAT25040	USON8	PA8SON8D(2x3)
CATALYST	CAT25080	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25080	TSSOP8	PA8TSS8D
CATALYST	CAT25080	USON8	PA8SON8D(2x3)
CATALYST	CAT25128	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25128	SOIC8	PA20SO20D-EO-210
CATALYST	CAT25128	TSSOP8	PA8TSS8D
CATALYST	CAT25128	USON8	PA8SON8D(2x3)

CATALYST	CAT25160	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25160	TSSOP8	PA8TSS8D
CATALYST	CAT25160	USON8	PA8SON8D(2x3)
CATALYST	CAT25256	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25256	SOIC8	PA20SO20D-EO-210
CATALYST	CAT25256	TSSOP8	PA8TSS8D
CATALYST	CAT25256	USON8	PA8SON8D(2x3)
CATALYST	CAT25320	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25320	TSSOP8	PA8TSS8D
CATALYST	CAT25640	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25640	TSSOP8	PA8TSS8D
CATALYST	CAT25640	USON8	PA8SON8D(2x3)
CATALYST	CAT25C01	DIP8	
CATALYST	CAT25C01	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT25C01	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25C01	TSSOP14	PA14TSS14D
CATALYST	CAT25C01	TSSOP8	PA8TSS8D
CATALYST	CAT25C02	DIP8	
CATALYST	CAT25C02	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT25C02	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25C02	TSSOP14	PA14TSS14D
CATALYST	CAT25C02	TSSOP8	PA8TSS8D
CATALYST	CAT25C03	DIP8	
CATALYST	CAT25C03	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT25C03	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25C03	TSSOP14	PA14TSS14D
CATALYST	CAT25C03	TSSOP8	PA8TSS8D
CATALYST	CAT25C04	DIP8	
CATALYST	CAT25C04	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25C04	TSSOP14	PA14TSS14D
CATALYST	CAT25C04	TSSOP8	PA8TSS8D
CATALYST	CAT25C05	DIP8	
CATALYST	CAT25C05	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25C05	TSSOP14	PA14TSS14D
CATALYST	CAT25C05	TSSOP8	PA8TSS8D
CATALYST	CAT25C08	DIP8	
CATALYST	CAT25C08	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25C08	TSSOP14	PA14TSS14D
CATALYST	CAT25C08	TSSOP8	PA8TSS8D
CATALYST	CAT25C09	DIP8	
CATALYST	CAT25C09	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25C09	TSSOP14	PA14TSS14D
CATALYST	CAT25C09	TSSOP8	PA8TSS8D
CATALYST	CAT25C11	DIP8	
CATALYST	CAT25C11	MSOP8	PA8MSOP8D/PA8SS8D-120
CATALYST	CAT25C11	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25C11	TSSOP14	PA14TSS14D
CATALYST	CAT25C11	TSSOP8	PA8TSS8D
CATALYST	CAT25C128	DIP8	
CATALYST	CAT25C128	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25C128	TSSOP14	PA14TSS14D
CATALYST	CAT25C128	TSSOP20	PA20TSS20D
CATALYST	CAT25C16	DIP8	
CATALYST	CAT25C16	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25C16	TSSOP14	PA14TSS14D
CATALYST	CAT25C16	TSSOP8	PA8TSS8D
CATALYST	CAT25C17	DIP8	
CATALYST	CAT25C17	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25C17	TSSOP14	PA14TSS14D
CATALYST	CAT25C17	TSSOP8	PA8TSS8D
CATALYST	CAT25C256	DIP8	
CATALYST	CAT25C256	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25C256	TSSOP20	PA20TSS20D
CATALYST	CAT25C32	DIP8	
CATALYST	CAT25C32	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25C32	TSSOP14	PA14TSS14D
CATALYST	CAT25C32	TSSOP20	PA20TSS20D
CATALYST	CAT25C64	DIP8	
CATALYST	CAT25C64	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CATALYST	CAT25C64	TSSOP14	PA14TSS14D
CATALYST	CAT25C64	TSSOP20	PA20TSS20D
CATALYST	CAT27010	DIP32	
CATALYST	CAT27010	PLCC32	PA32PL32D

CATALYST	CAT27010	TSOP32	PA32TS20/PA32TS32D-20
CATALYST	CAT27128A	DIP28	
CATALYST	CAT27128A	PLCC32	PA32PL28D-YA
CATALYST	CAT27256	DIP28	
CATALYST	CAT27512	DIP28	
CATALYST	CAT27512	PLCC32	PA32PL28D-YA
CATALYST	CAT2764A	DIP28	
CATALYST	CAT27C210	DIP40	
CATALYST	CAT27C210	PLCC44	PA44-48U
CATALYST	CAT27HC256	DIP28	
CATALYST	CAT27HC256	PLCC32	PA32PL28D-YA
CATALYST	CAT27HC256L	DIP28	
CATALYST	CAT27HC256L	PLCC32	PA32PL28D-YA
CATALYST	CAT28C16A	DIP24	
CATALYST	CAT28C16A	PLCC32	PA32PL32D
CATALYST	CAT28C16A	SOIC24	PA28SO28D-EO-300
CATALYST	CAT28C17A	DIP28	
CATALYST	CAT28C17A	PLCC32	PA32PL28D-YA
CATALYST	CAT28C17A	SOIC24	PA28SO28D-EO-300
CATALYST	CAT28C256	DIP28	
CATALYST	CAT28C256	PLCC32	PA32PL28D-YA
CATALYST	CAT28C256	TSOP28	PA28TS28D-EO
CATALYST	CAT28C512	DIP32	
CATALYST	CAT28C512	PLCC32	PA32PL32D
CATALYST	CAT28C512	TSOP32	PA32TS20/PA32TS32D-20
CATALYST	CAT28C513	PLCC32	PA32PL32D
CATALYST	CAT28C64A	DIP28	
CATALYST	CAT28C64A	PLCC32	PA32PL28D-YA
CATALYST	CAT28C64A	SOIC28	PA28SO28D-EO-300
CATALYST	CAT28C64B	DIP28	
CATALYST	CAT28C64B	PLCC32	PA32PL28D-YA
CATALYST	CAT28C64B	SOIC28	PA28SO28D-EO-300
CATALYST	CAT28C64B	TSOP28	PA28TS28D-EO
CATALYST	CAT28C65A	DIP28	
CATALYST	CAT28C65A	PLCC32	PA32PL28D-YA
CATALYST	CAT28C65A	SOIC28	PA28SO28D-EO-300
CATALYST	CAT28C65B	DIP28	
CATALYST	CAT28C65B	PLCC32	PA32PL28D-YA
CATALYST	CAT28C65B	TSOP28	PA28TS28D-EO
CATALYST	CAT28C65BJ	SOIC28	PA28SO28D-EO-300
CATALYST	CAT28F001B	DIP32	
CATALYST	CAT28F001B	PLCC32	PA32PL32D
CATALYST	CAT28F001B	TSOP32	PA32TS20/PA32TS32D-20
CATALYST	CAT28F001T	DIP32	
CATALYST	CAT28F001T	PLCC32	PA32PL32D
CATALYST	CAT28F001T	TSOP32	PA32TS20/PA32TS32D-20
CATALYST	CAT28F010	DIP32	
CATALYST	CAT28F010	PLCC32	PA32PL32D
CATALYST	CAT28F010	TSOP32	PA32TS20/PA32TS32D-20
CATALYST	CAT28F020	DIP32	
CATALYST	CAT28F020	PLCC32	PA32PL32D
CATALYST	CAT28F020	TSOP32	PA32TS20/PA32TS32D-20
CATALYST	CAT28F512	DIP32	
CATALYST	CAT28F512	PLCC32	PA32PL32D
CATALYST	CAT28F512	TSOP32	PA32TS20/PA32TS32D-20
CATALYST	CAT28LV256	DIP28	
CATALYST	CAT28LV256	PLCC32	PA32PL28D-YA
CATALYST	CAT28LV256	TSOP28	PA28TS28D-EO
CATALYST	CAT28LV64	DIP28	
CATALYST	CAT28LV64	PLCC32	PA32PL28D-YA
CATALYST	CAT28LV64	SOIC28	PA28SO28D-EO-300
CATALYST	CAT28LV64	TSOP28	PA28TS28D-EO
CATALYST	CAT28LV65	DIP28	
CATALYST	CAT28LV65	PLCC32	PA32PL28D-YA
CATALYST	CAT28LV65	SOIC28	PA28SO28D-EO-300
CATALYST	CAT28LV65	TSOP28	PA28TS28D-EO
CATALYST	CAT33C101	DIP8	
CATALYST	CAT33C104	DIP8	
CATALYST	CAT33C116	DIP8	
CATALYST	CAT33C116I	DIP8	
CATALYST	CAT33C204	DIP8	
CATALYST	CAT34C02-VP2	TDFN8	PA8TDFN8D
CATALYST	CAT34C02-Y	TSSOP8	PA24TSS24D



CATALYST	CAT34C02-Y	TSSOP8	PA8TSS8D
CATALYST	CAT34FC02	DIP8	
CATALYST	CAT34FC02-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT34FC02-L	DIP8	
CATALYST	CAT34FC02-RD7	TDFN8	PA8TDFN8D
CATALYST	CAT34FC02-U	TSSOP8	PA24TSS24D
CATALYST	CAT34FC02-U	TSSOP8	PA8TSS8D
CATALYST	CAT34FC02-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT34FC02-Y	TSSOP8	PA24TSS24D
CATALYST	CAT34FC02-Y	TSSOP8	PA8TSS8D
CATALYST	CAT34FC02-ZD7	TDFN8	PA8TDFN8D
CATALYST	CAT34RC02	DIP8	
CATALYST	CAT34RC02-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT34RC02-L	DIP8	
CATALYST	CAT34RC02-SP2	TDFN8	PA8TDFN8D
CATALYST	CAT34RC02-U	TSSOP8	PA24TSS24D
CATALYST	CAT34RC02-U	TSSOP8	PA8TSS8D
CATALYST	CAT34RC02-VP2	TDFN8	PA8TDFN8D
CATALYST	CAT34RC02-W	SOIC8	PA8SO8D-EO-150
CATALYST	CAT34RC02-Y	TSSOP8	PA24TSS24D
CATALYST	CAT34RC02-Y	TSSOP8	PA8TSS8D
CATALYST	CAT34WC02-VP2	TDFN8	PA8TDFN8D
CATALYST	CAT34WC02-Y	TSSOP8	PA24TSS24D
CATALYST	CAT34WC02-Y	TSSOP8	PA8TSS8D
CATALYST	CAT35C102	DIP8	
CATALYST	CAT35C104	DIP8	
CATALYST	CAT35C116	DIP8	
CATALYST	CAT35C116I	DIP8	
CATALYST	CAT35C202	DIP8	
CATALYST	CAT35C204	DIP8	
CATALYST	CAT59C11	DIP8	
CATALYST	CAT93C46	DIP8	
CATALYST	CAT93C46	SOIC8	PA16SO16D-EO-150
CATALYST	CAT93C46	TSSOP8	PA8TSS-OT
CATALYST	CAT93C46A	DIP8	
CATALYST	CAT93C46A	SOIC8	PA16SO16D-EO-150
CATALYST	CAT93C46A-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT93C46-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT93C56	DIP8	
CATALYST	CAT93C56	SOIC8	PA16SO16D-EO-150
CATALYST	CAT93C56	TSSOP8	PA8TSS-OT
CATALYST	CAT93C56-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT93C57	DIP8	
CATALYST	CAT93C57	SOIC8	PA16SO16D-EO-150
CATALYST	CAT93C57	TSSOP8	PA8TSS-OT
CATALYST	CAT93C57-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT93C66	DIP8	
CATALYST	CAT93C66	SOIC8	PA16SO16D-EO-150
CATALYST	CAT93C66	TSSOP8	PA8TSS-OT
CATALYST	CAT93C66A	DIP8	
CATALYST	CAT93C66A	SOIC8	PA16SO16D-EO-150
CATALYST	CAT93C66A	TSSOP8	PA8TSS-OT
CATALYST	CAT93C66A-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT93C66-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT93C86	DIP8	
CATALYST	CAT93C86	SOIC8	PA16SO16D-EO-150
CATALYST	CAT93C86	TSSOP8	PA8TSS-OT
CATALYST	CAT93C86A	DIP8	
CATALYST	CAT93C86A	SOIC8	PA16SO16D-EO-150
CATALYST	CAT93C86A	TSSOP8	PA8TSS-OT
CATALYST	CAT93C86A-J	SOIC8	PA8SO8D-EO-150
CATALYST	CAT93C86-J	SOIC8	PA8SO8D-EO-150
CERAMATE	24LC02	DIP8	
CERAMATE	24LC02	SOIC8	PA8SO8D-EO-150
CERAMATE	24LC02	TSSOP8	PA24TSS24D
CERAMATE	24LC02	TSSOP8	PA8TSS8D
CERAMATE	24LC08	DIP8	
CERAMATE	24LC08	SOIC8	PA8SO8D-EO-150
CERAMATE	24LC08	TSSOP8	PA24TSS24D
CERAMATE	24LC08	TSSOP8	PA8TSS8D
CERAMATE	24LC16	DIP8	
CERAMATE	24LC16	SOIC8	PA8SO8D-EO-150
CERAMATE	24LC16	TSSOP8	PA24TSS24D

CERAMATE	24LC16	TSSOP8	PA8TSS8D
CERAMATE	24LLC02	DIP8	
CERAMATE	24LLC02	SOIC8	PA8SO8D-EO-150
CERAMATE	24LLC02	TSSOP8	PA24TSS24D
CERAMATE	24LLC02	TSSOP8	PA8TSS8D
CERAMATE	24LLC08	DIP8	
CERAMATE	24LLC08	SOIC8	PA8SO8D-EO-150
CERAMATE	24LLC08	TSSOP8	PA24TSS24D
CERAMATE	24LLC08	TSSOP8	PA8TSS8D
CERAMATE	24LLC16	DIP8	
CERAMATE	24LLC16	SOIC8	PA8SO8D-EO-150
CERAMATE	24LLC16	TSSOP8	PA24TSS24D
CERAMATE	24LLC16	TSSOP8	PA8TSS8D
Chingis	Pm25LD010	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LD010	TSSOP8	PA8TSS8D
Chingis	Pm25LD010	VVSOP8	PA16SO16D-EO-150
Chingis	Pm25LD010	WSOP8	PA8SON8D(6x5)
Chingis	Pm25LD010C	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LD010C	TSSOP8	PA8TSS8D
Chingis	Pm25LD010C	WSOP8	PA8SON8D(6x5)
Chingis	Pm25LD020	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LD020	TSSOP8	PA8TSS8D
Chingis	Pm25LD020	VVSOP8	PA16SO16D-EO-150
Chingis	Pm25LD020	WSOP8	PA8SON8D(6x5)
Chingis	Pm25LD020C	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LD020C	TSSOP8	PA8TSS8D
Chingis	Pm25LD020C	WSOP8	PA8SON8D(6x5)
Chingis	Pm25LD040	DIP8	
Chingis	Pm25LD040	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LD040	SOIC8	PA20SO20D-EO-210
Chingis	Pm25LD040	VVSOP8	PA16SO16D-EO-150
Chingis	Pm25LD040	WSOP8	PA8SON8D(6x5)
Chingis	Pm25LD040C	DIP8	
Chingis	Pm25LD040C	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LD040C	SOIC8	PA20SO20D-EO-210
Chingis	Pm25LD040C	WSOP8	PA8SON8D(6x5)
Chingis	Pm25LD256C	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LD256C	TSSOP8	PA8TSS8D
Chingis	Pm25LD512	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LD512	TSSOP8	PA8TSS8D
Chingis	Pm25LD512	VVSOP8	PA16SO16D-EO-150
Chingis	Pm25LD512	WSOP8	PA8SON8D(6x5)
Chingis	Pm25LD512C	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LD512C	TSSOP8	PA8TSS8D
Chingis	Pm25LD512C	WSOP8	PA8SON8D(6x5)
Chingis	Pm25LQ010B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LQ010B	SOIC8	PA20SO20D-EO-210
Chingis	Pm25LQ010B	TSSOP8	PA8TSS8D
Chingis	Pm25LQ010B	USOP8	PA8SON8D(2x3)
Chingis	Pm25LQ010B	VVSOP8	PA16SO16D-EO-150
Chingis	Pm25LQ010B	WSOP8	PA8SON8D(6x5)
Chingis	Pm25LQ016	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LQ016	SOIC8	PA20SO20D-EO-210
Chingis	Pm25LQ016	VVSOP8	PA16SO16D-EO-150
Chingis	Pm25LQ016	WSOP8	PA8SON8D(6x5)
Chingis	Pm25LQ016	WSOP8	PA8SON8DA(8x6)
Chingis	Pm25LQ020	DIP8	
Chingis	Pm25LQ020	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LQ020	SOIC8	PA20SO20D-EO-210
Chingis	Pm25LQ020	VVSOP8	PA16SO16D-EO-150
Chingis	Pm25LQ020	WSOP8	PA8SON8D(6x5)
Chingis	Pm25LQ020B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LQ020B	SOIC8	PA20SO20D-EO-210
Chingis	Pm25LQ020B	TSSOP8	PA8TSS8D
Chingis	Pm25LQ020B	USOP8	PA8SON8D(2x3)
Chingis	Pm25LQ020B	VVSOP8	PA16SO16D-EO-150
Chingis	Pm25LQ020B	WSOP8	PA8SON8D(6x5)
Chingis	Pm25LQ032C	DIP8	
Chingis	Pm25LQ032C	SOIC16	PA28SO28D-EO-300
Chingis	Pm25LQ032C	SOIC8	PA20SO20D-EO-210
Chingis	Pm25LQ032C	VSOP8	PA20SO20D-EO-210
Chingis	Pm25LQ032C	WSOP8	PA8SON8D(6x5)
Chingis	Pm25LQ040	DIP8	

Chingis	Pm25LQ040	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LQ040	SOIC8	PA20SO20D-EO-210
Chingis	Pm25LQ040	VVSOP8	PA16SO16D-EO-150
Chingis	Pm25LQ040	WSON8	PA8SON8D(6x5)
Chingis	Pm25LQ040B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LQ040B	SOIC8	PA20SO20D-EO-210
Chingis	Pm25LQ040B	TSSOP8	PA8TSS8D
Chingis	Pm25LQ040B	USON8	PA8SON8D(2x3)
Chingis	Pm25LQ040B	VVSOP8	PA16SO16D-EO-150
Chingis	Pm25LQ040B	WSON8	PA8SON8D(6x5)
Chingis	Pm25LQ512B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LQ512B	SOIC8	PA20SO20D-EO-210
Chingis	Pm25LQ512B	TSSOP8	PA8TSS8D
Chingis	Pm25LQ512B	USON8	PA8SON8D(2x3)
Chingis	Pm25LQ512B	VVSOP8	PA16SO16D-EO-150
Chingis	Pm25LQ512B	WSON8	PA8SON8D(6x5)
Chingis	Pm25LV010	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LV010	WSON8	PA8SON8D(6x5)
Chingis	Pm25LV010A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LV010A	WSON8	PA8SON8D(6x5)
Chingis	Pm25LV016B	SOIC8	PA20SO20D-EO-210
Chingis	Pm25LV016B	WSON8	PA8SON8D(6x5)
Chingis	Pm25LV020	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LV020	WSON8	PA8SON8D(6x5)
Chingis	Pm25LV040	DIP8	
Chingis	Pm25LV040	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LV040	SOIC8	PA20SO20D-EO-210
Chingis	Pm25LV040	WSON8	PA8SON8D(6x5)
Chingis	Pm25LV080B	SOIC8	PA20SO20D-EO-210
Chingis	Pm25LV080B	WSON8	PA8SON8D(6x5)
Chingis	Pm25LV512	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LV512	WSON8	PA8SON8D(6x5)
Chingis	Pm25LV512A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25LV512A	TSSOP8	PA8TSS8D
Chingis	Pm25LV512A	WSON8	PA8SON8D(6x5)
Chingis	Pm25WD020	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25WD020	VVSOP8	PA16SO16D-EO-150
Chingis	Pm25WD020	WSON8	PA8SON8D(6x5)
Chingis	Pm25WD040	DIP8	
Chingis	Pm25WD040	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
Chingis	Pm25WD040	SOIC8	PA20SO20D-EO-210
Chingis	Pm25WD040	VVSOP8	PA16SO16D-EO-150
Chingis	Pm25WD040	WSON8	PA8SON8D(6x5)
CYPRESS	CY27C010	DIP32	
CYPRESS	CY27C010	PLCC32	PA32PL32D
CYPRESS	CY27C010	TSOP32	PA32TS20/PA32TS32D-20
CYPRESS	CY27C020	DIP32	
CYPRESS	CY27C020	PLCC32	PA32PL32D
CYPRESS	CY27C020	TSOP32	PA32TS20/PA32TS32D-20
CYPRESS	CY27C040	DIP32	
CYPRESS	CY27C040	PLCC32	PA32PL32D
CYPRESS	CY27C040	TSOP32	PA32TS20/PA32TS32D-20
CYPRESS	CY27C128	DIP28	
CYPRESS	CY27C256	DIP28	
CYPRESS	CY27C256	PLCC32	PA32PL28D-YA
CYPRESS	CY27C256	TSOP28	PA28TS28D-EO
CYPRESS	CY27C256A	DIP28	
CYPRESS	CY27C256A	PLCC32	PA32PL28D-YA
CYPRESS	CY27C256A	TSOP28	PA28TS28D-EO
CYPRESS	CY27C512	DIP28	
CYPRESS	CY27C512	PLCC32	PA32PL28D-YA
CYPRESS	CY27C512	TSOP28	PA28TS28D-EO
CYPRESS	CY27H010	DIP32	
CYPRESS	CY27H010	PLCC32	PA32PL32D
CYPRESS	CY27H010	TSOP32	PA32TS20/PA32TS32D-20
CYPRESS	CY27H256	DIP28	
CYPRESS	CY27H256	PLCC32	PA32PL28D-YA
CYPRESS	CY27H512	DIP20	
CYPRESS	CY27H512	PLCC32	PA32PL28D-YA
CYPRESS	CY27H512	TSOP28	PA28TS28D-EO
CYPRESS	CY37032	PLCC44	PA44-48U
CYPRESS	CY37032	TQFP44	PA44QF44D
CYPRESS	CY37032V	PLCC44	PA44-48U

CYPRESS	CY37032V	TQFP44	PA44QF44D
CYPRESS	CY37064	PLCC44	PA44-48U
CYPRESS	CY37064	TQFP44	PA44QF44D
CYPRESS	CY37064V	PLCC44	PA44-48U
CYPRESS	CY37064V	TQFP44	PA44QF44D
CYPRESS	CY7C225	DIP24	
CYPRESS	CY7C225	PLCC28	PA28PL28D
CYPRESS	CY7C225A	DIP24	
CYPRESS	CY7C225A	PLCC28	PA28PL28D
CYPRESS	CY7C235	DIP24	
CYPRESS	CY7C235	PLCC28	PA28PL28D
CYPRESS	CY7C235A	DIP24	
CYPRESS	CY7C235A	PLCC28	PA28PL28D
CYPRESS	CY7C245	DIP24	
CYPRESS	CY7C245	PLCC28	PA28PL28D
CYPRESS	CY7C245A	DIP24	
CYPRESS	CY7C245A	PLCC28	PA28PL28D
CYPRESS	CY7C251	DIP28	
CYPRESS	CY7C254	DIP28	
CYPRESS	CY7C261	DIP24	
CYPRESS	CY7C261	PLCC28	PA28PL28D
CYPRESS	CY7C263	DIP24	
CYPRESS	CY7C263	PLCC28	PA28PL28D
CYPRESS	CY7C264	DIP24	
CYPRESS	CY7C264	PLCC28	PA28PL28D
CYPRESS	CY7C265	DIP28	
CYPRESS	CY7C265	PLCC28	PA28PL28D
CYPRESS	CY7C266	DIP28	
CYPRESS	CY7C266	PLCC32	PA32PL32D
CYPRESS	CY7C268	DIP32	
CYPRESS	CY7C269	DIP28	
CYPRESS	CY7C270	PLCC44	PA44-48U
CYPRESS	CY7C271	DIP28	
CYPRESS	CY7C271	PLCC32	PA32PL32D
CYPRESS	CY7C271A	DIP28	
CYPRESS	CY7C271A	PLCC32	PA32PL32D
CYPRESS	CY7C274	DIP28	
CYPRESS	CY7C274	PLCC32	PA32PL32D
CYPRESS	CY7C274A	DIP28	
CYPRESS	CY7C274A	PLCC32	PA32PL32D
CYPRESS	CY7C276	PLCC44	PA44-48U
CYPRESS	CY7C277	DIP28	
CYPRESS	CY7C279	DIP28	
CYPRESS	CY7C281	DIP24	
CYPRESS	CY7C281	PLCC28	PA28PL28D
CYPRESS	CY7C281A	DIP24	
CYPRESS	CY7C281A	PLCC28	PA28PL28D
CYPRESS	CY7C282	DIP24	
CYPRESS	CY7C282	PLCC28	PA28PL28D
CYPRESS	CY7C282A	DIP24	
CYPRESS	CY7C282A	PLCC28	PA28PL28D
CYPRESS	CY7C285	DIP28	
CYPRESS	CY7C286	DIP28	
CYPRESS	CY7C287	DIP28	
CYPRESS	CY7C289	DIP32	
CYPRESS	CY7C291	DIP24	
CYPRESS	CY7C291	PLCC28	PA28PL28D
CYPRESS	CY7C291A	DIP24	
CYPRESS	CY7C291A	PLCC28	PA28PL28D
CYPRESS	CY7C292	DIP24	
CYPRESS	CY7C292	PLCC28	PA28PL28D
CYPRESS	CY7C292A	DIP24	
CYPRESS	CY7C292A	PLCC28	PA28PL28D
CYPRESS	CY7C293A	DIP24	
CYPRESS	CY7C293A	PLCC28	PA28PL28D
CYPRESS	CY7C63000A	DIP20	
CYPRESS	CY7C63000A	SOIC20	PA28SO28D-EO-300
CYPRESS	CY7C63001A	DIP20	
CYPRESS	CY7C63001A	SOIC20	PA28SO28D-EO-300
CYPRESS	CY7C63100A	DIP24	
CYPRESS	CY7C63100A	SOIC24	PA28SO28D-EO-300
CYPRESS	CY7C63101A	DIP24	
CYPRESS	CY7C63101A	SOIC24	PA28SO28D-EO-300

CYPRESS	CY7C63221A	DIP16	PA28SO28D-EO-300
CYPRESS	CY7C63231A	DIP18	
CYPRESS	CY7C63231A	SOIC18	PA28SO28D-EO-300
CYPRESS	CY7C63310	SOIC16	PA16SO16D-EO-150
CYPRESS	CY7C63411	DIP40	
CYPRESS	CY7C63411	DIP48	
CYPRESS	CY7C63412	DIP40	
CYPRESS	CY7C63412	DIP48	
CYPRESS	CY7C63413	DIP40	
CYPRESS	CY7C63413	DIP48	
CYPRESS	CY7C63511	DIP48	
CYPRESS	CY7C63512	DIP48	
CYPRESS	CY7C63513	DIP48	
CYPRESS	CY7C63612	SOIC24	PA28SO28D-EO-300
CYPRESS	CY7C63613	SOIC24	PA28SO28D-EO-300
CYPRESS	CY7C63801	DIP16	
CYPRESS	CY7C63801	SOIC16	PA16SO16D-EO-150
CYPRESS	CY7C63803	SOIC16	PA16SO16D-EO-150
CYPRESS	CY7C63813	DIP16	
CYPRESS	CY7C63813	SOIC16	PA16SO16D-EO-150
CYPRESS	CY7C63823	DIP24	
CYPRESS	CY7C63823	SOIC24	PA28SO28D-EO-300
CYPRESS	CY7C63913	DIP40	
CYPRESS	CY8C21123	DIP8	
CYPRESS	CY8C21223	SOIC16	PA16SO16D-EO-150
CYPRESS	CY8C21234	SOIC16	PA16SO16D-EO-150
CYPRESS	CY8C21312	SSOP20	PA28SS28D
CYPRESS	CY8C21323	SSOP20	PA28SS28D
CYPRESS	CY8C21334	SSOP20	PA28SS28D
CYPRESS	CY8C21512	SSOP28	PA28SS28D
CYPRESS	CY8C21534	SSOP28	PA28SS28D
CYPRESS	CY8C23433	SSOP28	PA28SS28D
CYPRESS	CY8C24123A	DIP8	
CYPRESS	CY8C24123A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
CYPRESS	CY8C24223A	SOIC20	PA28SO28D-EO-300
CYPRESS	CY8C24223A	SSOP20	PA28SS28D
CYPRESS	CY8C24423A	DIP28	
CYPRESS	CY8C24423A	SOIC28	PA28SO28D-EO-300
CYPRESS	CY8C24423A	SSOP28	PA28SS28D
CYPRESS	CY8C27143	DIP8	
CYPRESS	CY8C27243	SOIC20	PA28SO28D-EO-300
CYPRESS	CY8C27243	SSOP20	PA28SS28D
CYPRESS	CY8C27443	DIP28	
CYPRESS	CY8C27443	SOIC28	PA28SO28D-EO-300
CYPRESS	CY8C27443	SSOP28	PA28SS28D
CYPRESS	CY8C27543	TQFP44	PA44VQ44D/PA44TQ44D
CYPRESS	FM1608B	DIP28	
CYPRESS	FM1608B	SOIC28	PA28SO28D-EO-300
CYPRESS	FM1808	DIP28	
CYPRESS	FM1808	SOIC28	PA28SO28D-EO-300
CYPRESS	PALC16L8	DIP20	
CYPRESS	PALC16L8	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALC16R4	DIP20	
CYPRESS	PALC16R4	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALC16R6	DIP20	
CYPRESS	PALC16R6	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALC16R8	DIP20	
CYPRESS	PALC16R8	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALC22V10	DIP24	
CYPRESS	PALC22V10	PLCC28	PA28PL24D2P6-YA
CYPRESS	PALC22V10B	DIP24	
CYPRESS	PALC22V10B	PLCC28	PA28PL24D2P6-YA
CYPRESS	PALC22V10D	DIP24	
CYPRESS	PALC22V10D	PLCC28	PA28PL28D
CYPRESS	PALC22V10L	DIP24	
CYPRESS	PALC22V10L	PLCC28	PA28PL24D2P6-YA
CYPRESS	PALCE16V8	DIP20	
CYPRESS	PALCE16V8	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as10H8	DIP20	
CYPRESS	PALCE16V8as10H8	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as10H8	PLCC20	PA20LC20D[Dead Bug]



CYPRESS	PALCE16V8as16RP6	DIP20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16RP6	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16RP6	PLCC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8as16RP6	SOIC20	
CYPRESS	PALCE16V8as16RP8	DIP20	
CYPRESS	PALCE16V8as16RP8	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16RP8	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8as16RP8	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8L	DIP20	
CYPRESS	PALCE16V8L	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8L	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8L	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las10H8	DIP20	
CYPRESS	PALCE16V8Las10H8	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las10H8	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las10H8	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las10L8	DIP20	
CYPRESS	PALCE16V8Las10L8	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las10L8	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las10L8	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las10P8	DIP20	
CYPRESS	PALCE16V8Las10P8	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las10P8	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las10P8	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las12H6	DIP20	
CYPRESS	PALCE16V8Las12H6	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las12H6	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las12H6	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las12L6	DIP20	
CYPRESS	PALCE16V8Las12L6	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las12L6	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las12L6	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las12P6	DIP20	
CYPRESS	PALCE16V8Las12P6	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las12P6	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las12P6	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las14H4	DIP20	
CYPRESS	PALCE16V8Las14H4	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las14H4	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las14H4	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las14L4	DIP20	
CYPRESS	PALCE16V8Las14L4	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las14L4	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las14L4	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las14P4	DIP20	
CYPRESS	PALCE16V8Las14P4	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las14P4	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las14P4	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16H2	DIP20	
CYPRESS	PALCE16V8Las16H2	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16H2	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16H2	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16H8	DIP20	
CYPRESS	PALCE16V8Las16H8	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16H8	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16H8	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16L2	DIP20	
CYPRESS	PALCE16V8Las16L2	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16L2	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16L2	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16L8	DIP20	
CYPRESS	PALCE16V8Las16L8	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16L8	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16L8	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16P2	DIP20	
CYPRESS	PALCE16V8Las16P2	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16P2	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16P2	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16P8	DIP20	
CYPRESS	PALCE16V8Las16P8	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16P8	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16P8	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16R4	DIP20	

CYPRESS	PALCE16V8Las16R4	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16R4	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16R4	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16R6	DIP20	
CYPRESS	PALCE16V8Las16R6	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16R6	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16R6	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16R8	DIP20	
CYPRESS	PALCE16V8Las16R8	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16R8	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16R8	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16RP4	DIP20	
CYPRESS	PALCE16V8Las16RP4	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16RP4	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16RP4	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16RP6	DIP20	
CYPRESS	PALCE16V8Las16RP6	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16RP6	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16RP6	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE16V8Las16RP8	DIP20	
CYPRESS	PALCE16V8Las16RP8	LCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16RP8	PLCC20	PA20LC20D[Dead Bug]
CYPRESS	PALCE16V8Las16RP8	SOIC20	PA20SO20D-EO-210
CYPRESS	PALCE20V8	DIP24	
CYPRESS	PALCE20V8	LCC28	PA28PL28D
CYPRESS	PALCE20V8	PLCC28	PA28PL28D
CYPRESS	PALCE20V8	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as14H8	DIP24	
CYPRESS	PALCE20V8as14H8	LCC28	PA28PL28D
CYPRESS	PALCE20V8as14H8	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as14H8	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as14L8	DIP24	
CYPRESS	PALCE20V8as14L8	LCC28	PA28PL28D
CYPRESS	PALCE20V8as14L8	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as14L8	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as14P8	DIP24	
CYPRESS	PALCE20V8as14P8	LCC28	PA28PL28D
CYPRESS	PALCE20V8as14P8	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as14P8	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as16H6	DIP24	
CYPRESS	PALCE20V8as16H6	LCC28	PA28PL28D
CYPRESS	PALCE20V8as16H6	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as16H6	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as16L6	DIP24	
CYPRESS	PALCE20V8as16L6	LCC28	PA28PL28D
CYPRESS	PALCE20V8as16L6	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as16L6	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as16P6	DIP24	
CYPRESS	PALCE20V8as16P6	LCC28	PA28PL28D
CYPRESS	PALCE20V8as16P6	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as16P6	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as18H4	DIP24	
CYPRESS	PALCE20V8as18H4	LCC28	PA28PL28D
CYPRESS	PALCE20V8as18H4	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as18H4	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as18L4	DIP24	
CYPRESS	PALCE20V8as18L4	LCC28	PA28PL28D
CYPRESS	PALCE20V8as18L4	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as18L4	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as18P4	DIP24	
CYPRESS	PALCE20V8as18P4	LCC28	PA28PL28D
CYPRESS	PALCE20V8as18P4	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as18P4	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20H2	DIP24	
CYPRESS	PALCE20V8as20H2	LCC28	PA28PL28D
CYPRESS	PALCE20V8as20H2	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as20H2	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20H8	DIP24	
CYPRESS	PALCE20V8as20H8	LCC28	PA28PL28D
CYPRESS	PALCE20V8as20H8	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as20H8	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20L2	DIP24	
CYPRESS	PALCE20V8as20L2	LCC28	PA28PL28D



CYPRESS	PALCE20V8as20L2	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as20L2	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20L8	DIP24	
CYPRESS	PALCE20V8as20L8	LCC28	PA28PL28D
CYPRESS	PALCE20V8as20L8	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as20L8	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20P2	DIP24	
CYPRESS	PALCE20V8as20P2	LCC28	PA28PL28D
CYPRESS	PALCE20V8as20P2	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as20P2	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20P8	DIP24	
CYPRESS	PALCE20V8as20P8	LCC28	PA28PL28D
CYPRESS	PALCE20V8as20P8	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as20P8	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20R4	DIP24	
CYPRESS	PALCE20V8as20R4	LCC28	PA28PL28D
CYPRESS	PALCE20V8as20R4	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as20R4	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20R6	DIP24	
CYPRESS	PALCE20V8as20R6	LCC28	PA28PL28D
CYPRESS	PALCE20V8as20R6	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as20R6	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20R8	DIP24	
CYPRESS	PALCE20V8as20R8	LCC28	PA28PL28D
CYPRESS	PALCE20V8as20R8	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as20R8	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20RP4	DIP24	
CYPRESS	PALCE20V8as20RP4	LCC28	PA28PL28D
CYPRESS	PALCE20V8as20RP4	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as20RP4	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20RP6	DIP24	
CYPRESS	PALCE20V8as20RP6	LCC28	PA28PL28D
CYPRESS	PALCE20V8as20RP6	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as20RP6	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8as20RP8	DIP24	
CYPRESS	PALCE20V8as20RP8	LCC28	PA28PL28D
CYPRESS	PALCE20V8as20RP8	PLCC28	PA28PL28D
CYPRESS	PALCE20V8as20RP8	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8L	DIP24	
CYPRESS	PALCE20V8L	LCC28	PA28PL28D
CYPRESS	PALCE20V8L	PLCC28	PA28PL28D
CYPRESS	PALCE20V8L	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las14H8	DIP24	
CYPRESS	PALCE20V8Las14H8	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las14H8	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las14H8	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las14L8	DIP24	
CYPRESS	PALCE20V8Las14L8	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las14L8	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las14L8	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las14P8	DIP24	
CYPRESS	PALCE20V8Las14P8	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las14P8	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las14P8	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las16H6	DIP24	
CYPRESS	PALCE20V8Las16H6	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las16H6	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las16H6	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las16L6	DIP24	
CYPRESS	PALCE20V8Las16L6	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las16L6	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las16L6	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las16P6	DIP24	
CYPRESS	PALCE20V8Las16P6	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las16P6	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las16P6	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las18H4	DIP24	
CYPRESS	PALCE20V8Las18H4	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las18H4	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las18H4	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las18L4	DIP24	
CYPRESS	PALCE20V8Las18L4	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las18L4	PLCC28	PA28PL28D

CYPRESS	PALCE20V8Las18L4	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las18P4	DIP24	
CYPRESS	PALCE20V8Las18P4	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las18P4	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las18P4	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20H2	DIP24	
CYPRESS	PALCE20V8Las20H2	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las20H2	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las20H2	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20H8	DIP24	
CYPRESS	PALCE20V8Las20H8	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las20H8	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las20H8	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20L2	DIP24	
CYPRESS	PALCE20V8Las20L2	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las20L2	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las20L2	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20L8	DIP24	
CYPRESS	PALCE20V8Las20L8	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las20L8	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las20L8	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20P2	DIP24	
CYPRESS	PALCE20V8Las20P2	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las20P2	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las20P2	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20P8	DIP24	
CYPRESS	PALCE20V8Las20P8	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las20P8	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las20P8	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20R4	DIP24	
CYPRESS	PALCE20V8Las20R4	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las20R4	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las20R4	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20R6	DIP24	
CYPRESS	PALCE20V8Las20R6	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las20R6	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las20R6	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20R8	DIP24	
CYPRESS	PALCE20V8Las20R8	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las20R8	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las20R8	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20RP4	DIP24	
CYPRESS	PALCE20V8Las20RP4	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las20RP4	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las20RP4	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20RP6	DIP24	
CYPRESS	PALCE20V8Las20RP6	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las20RP6	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las20RP6	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE20V8Las20RP8	DIP24	
CYPRESS	PALCE20V8Las20RP8	LCC28	PA28PL28D
CYPRESS	PALCE20V8Las20RP8	PLCC28	PA28PL28D
CYPRESS	PALCE20V8Las20RP8	SOP24	PA28SO28D-EO-300
CYPRESS	PALCE22V10	DIP24	
CYPRESS	PALCE22V10	PLCC28	PA28PL28D
CYPRESS	PLDC20G10	DIP24	
CYPRESS	PLDC20G10	PLCC28	PA28PL24D2P6-YA
CYPRESS	PLDC20G10B	DIP24	
CYPRESS	PLDC20G10B	PLCC28	PA28PL24D2P6-YA
CYPRESS	PLDC20RA10	DIP24	
CYPRESS	PLDC20RA10	PLCC28	PA28PL24D2P6-YA
CYPRESS	S25FL001D	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CYPRESS	S25FL001D	WSON8	PA8SON8D(6x5)
CYPRESS	S25FL002D	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CYPRESS	S25FL002D	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL002D	WSON8	PA8SON8D(6x5)
CYPRESS	S25FL004A	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL004A	WSON8	PA8SON8D(6x5)
CYPRESS	S25FL004D	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL004D	WSON8	PA8SON8D(6x5)
CYPRESS	S25FL004K	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CYPRESS	S25FL004K	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL004K(Quad_IO)	SOP8	PA16SO16D-EO-150/PA8SO8D-150

CYPRESS	S25FL004K(Quad_IO)	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL008A	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL008A	WSON8	PA8SON8D(6x5)
CYPRESS	S25FL008K	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CYPRESS	S25FL008K	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL008K(Quad_IO)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CYPRESS	S25FL008K(Quad_IO)	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL016A	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL016A	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL016A	WSON8	PA8SON8DA(8x6)
CYPRESS	S25FL016K	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CYPRESS	S25FL016K	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL016K(Quad_IO)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CYPRESS	S25FL016K(Quad_IO)	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL032A	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL032K	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL032K(Quad_IO)	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL032P	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL032P	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL032P	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25FL032P	WSON8	PA8SON8D(6x5)
CYPRESS	S25FL032P	WSON8	PA8SON8DA(8x6)
CYPRESS	S25FL032P(Quad_IO)	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL032P(Quad_IO)	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL032P(Quad_IO)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25FL032P(Quad_IO)	WSON8	PA8SON8D(6x5)
CYPRESS	S25FL032P(Quad_IO)	WSON8	PA8SON8DA(8x6)
CYPRESS	S25FL040Axxxxx00	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CYPRESS	S25FL040Axxxxx00	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL040Axxxxx00	WSON8	PA8SON8D(6x5)
CYPRESS	S25FL040Axxxxx01	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CYPRESS	S25FL040Axxxxx01	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL040Axxxxx01	WSON8	PA8SON8D(6x5)
CYPRESS	S25FL040Axxxxx02	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CYPRESS	S25FL040Axxxxx02	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL040Axxxxx02	WSON8	PA8SON8D(6x5)
CYPRESS	S25FL064A	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL064K	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL064K	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL064K(Quad_IO)	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL064K(Quad_IO)	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL064P	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL064P	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25FL064P	WSON8	PA8SON8DA(8x6)
CYPRESS	S25FL064P(Quad_IO)	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL064P(Quad_IO)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25FL064P(Quad_IO)	WSON8	PA8SON8DA(8x6)
CYPRESS	S25FL116K	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL116K	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CYPRESS	S25FL116K	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL116K	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25FL116K	WSON8	PA8SON8D(6x5)
CYPRESS	S25FL127S	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL127S	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL127S	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25FL127S	WSON8	PA8SON8D(6x5)
CYPRESS	S25FL127S(Quad_IO)	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL127S(Quad_IO)	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL127S(Quad_IO)	WSON8	PA8SON8D(6x5)
CYPRESS	S25FL128K	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL128K(Quad_IO)	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL128P	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL128P	WSON8	PA8SON8DA(8x6)
CYPRESS	S25FL128S	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL128S	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25FL128S	WSON8	PA8SON8DA(8x6)
CYPRESS	S25FL128S(Quad_IO)	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL128S(Quad_IO)	WSON8	PA8SON8DA(8x6)
CYPRESS	S25FL129P	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL129P	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25FL129P	WSON8	PA8SON8DA(8x6)
CYPRESS	S25FL129P(Quad_IO)	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL129P(Quad_IO)	TFBGA24	PA24BG24D(6x8mm)5x5

CYPRESS	S25FL129P(Quad_IO)	WSON8	PA8SON8DA(8x6)
CYPRESS	S25FL132K	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL132K	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CYPRESS	S25FL132K	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL132K	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25FL132K	WSON8	PA8SON8D(6x5)
CYPRESS	S25FL164K	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL164K	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CYPRESS	S25FL164K	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL164K	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25FL164K	WSON8	PA8SON8D(6x5)
CYPRESS	S25FL204K	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CYPRESS	S25FL204K	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL208K	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CYPRESS	S25FL208K	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL216K	SOP8	PA16SO16D-EO-150/PA8SO8D-150
CYPRESS	S25FL216K	SOP8	PA20SO20D-EO-210
CYPRESS	S25FL256S	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL256S	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25FL256S	WSON8	PA8SON8DA(8x6)
CYPRESS	S25FL256S(Quad_IO)	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL256S(Quad_IO)	WSON8	PA8SON8DA(8x6)
CYPRESS	S25FL512S	SOP16	PA28SO28D-EO-300
CYPRESS	S25FL512S	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25FL512S(Quad_IO)	SOP16	PA28SO28D-EO-300
CYPRESS	S25HL01GT	SOP16	PA28SO28D-EO-300
CYPRESS	S25HL01GT	TFBGA24	PA24BG24D(8x8mm)5x5
CYPRESS	S25HL01GT(QPI)	SOP16	PA28SO28D-EO-300
CYPRESS	S25HL01GT(QPI)	TFBGA24	PA24BG24D(8x8mm)5x5
CYPRESS	S25HL256T	SOP16	PA28SO28D-EO-300
CYPRESS	S25HL256T	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25HL256T	WSON8	PA8SON8DA(8x6)
CYPRESS	S25HL256T(QPI)	SOP16	PA28SO28D-EO-300
CYPRESS	S25HL256T(QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25HL256T(QPI)	WSON8	PA8SON8DA(8x6)
CYPRESS	S25HL512T	SOP16	PA28SO28D-EO-300
CYPRESS	S25HL512T	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25HL512T(QPI)	WSON8	PA8SON8DA(8x6)
CYPRESS	S25HL512T(QPI)	SOP16	PA28SO28D-EO-300
CYPRESS	S25HL512T(QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25HL512T(QPI)	WSON8	PA8SON8DA(8x6)
CYPRESS	S25HS01GT	SOP16	PA28SO28D-EO-300
CYPRESS	S25HS01GT(QPI)	SOP16	PA28SO28D-EO-300
CYPRESS	S25HS256T	SOP16	PA28SO28D-EO-300
CYPRESS	S25HS256T	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25HS256T	WSON8	PA8SON8DA(8x6)
CYPRESS	S25HS256T(QPI)	SOP16	PA28SO28D-EO-300
CYPRESS	S25HS256T(QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25HS256T(QPI)	WSON8	PA8SON8DA(8x6)
CYPRESS	S25HS512T	SOP16	PA28SO28D-EO-300
CYPRESS	S25HS512T	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S25HS512T	WSON8	PA8SON8DA(8x6)
CYPRESS	S25HS512T(QPI)	SOP16	PA28SO28D-EO-300
CYPRESS	S25HS512T(QPI)	WSON8	PA8SON8DA(8x6)
CYPRESS	S26HL01GTxxBxx00x(HyperBus)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S26HL01GTxxBxx01x(SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S26HL256TxxBxx00x(HyperBus)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S26HL256TxxBxx01x(SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S26HL512TxxBxx00x(HyperBus)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S26HL512TxxBxx01x(SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S26HS01GTxxBxx00x(HyperBus)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S26HS01GTxxBxx01x(SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S26HS256TxxBxx00x(HyperBus)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S26HS256TxxBxx01x(SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S26HS512TxxBxx00x(HyperBus)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S26HS512TxxBxx01x(SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S28HL01GT (Octal I/O / DDR)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S28HL01GT (Octal I/O / SDR)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S28HL01GT (SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S28HL256T (Octal I/O / DDR)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S28HL256T (Octal I/O / SDR)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S28HL256T (SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S28HL512T (Octal I/O / DDR)	TFBGA24	PA24BG24D(6x8mm)5x5

CYPRESS	S28HL512T (Octal I/O / SDR)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S28HL512T (SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S28HS01GT (Octal I/O / DDR)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S28HS01GT (Octal I/O / SDR)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S28HS01GT (SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S28HS256T (Octal I/O / DDR)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S28HS256T (Octal I/O / SDR)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S28HS256T (SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S28HS512T (Octal I/O / DDR)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S28HS512T (Octal I/O / SDR)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S28HS512T (SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
CYPRESS	S29JL032J-01	TSOP48	PA48TS48D1
CYPRESS	S29JL032J-02	TSOP48	PA48TS48D1
CYPRESS	S29JL032J-21	TSOP48	PA48TS48D1
CYPRESS	S29JL032J-22	TSOP48	PA48TS48D1
CYPRESS	S29JL032J-31	TSOP48	PA48TS48D1
CYPRESS	S29JL032J-32	TSOP48	PA48TS48D1
CYPRESS	S29JL032J-41	TSOP48	PA48TS48D1
CYPRESS	S29JL032J-42	TSOP48	PA48TS48D1
CYROD	CRD89C51RD	PLCC44	PA44-48U
DALLAS	DS1086	SOP8	PA16SO16D-EO-150
DALLAS	DS1220AB	EDIP24	
DALLAS	DS1220AD	EDIP24	
DALLAS	DS1220Y	EDIP24	
DALLAS	DS1225AB	EDIP28	
DALLAS	DS1225AD	EDIP28	
DALLAS	DS1225Y	EDIP28	
DALLAS	DS1230AB	EDIP28	
DALLAS	DS1230Y	EDIP28	
DALLAS	DS1235AB	EDIP28	
DALLAS	DS1235YW	EDIP28	
DALLAS	DS1243Y	EDIP28	
DALLAS	DS1244W	EDIP28	
DALLAS	DS1244WP	EDIP28	
DALLAS	DS1244Y	EDIP28	
DALLAS	DS1245AB	EDIP32	
DALLAS	DS1245Y	EDIP32	
DALLAS	DS1248Y	EDIP32	
DALLAS	DS1250AB	EDIP32	
DALLAS	DS1250Y	EDIP32	
DALLAS	DS1286	EDIP28	
DALLAS	DS12887	EDIP24	
DALLAS	DS12C887	EDIP24	
DALLAS	DS1386(32K)	EDIP32	
DALLAS	DS1386(8K)	EDIP32	
DALLAS	DS1486	EDIP32	
DALLAS	DS1624	DIP8	
DALLAS	DS1624S	SOIC8	PA20SO20D-EO-210
DALLAS	DS1642	EDIP24	
DALLAS	DS1643	EDIP28	
DALLAS	DS1643Y	EDIP28	
DALLAS	DS1644	EDIP28	
DALLAS	DS1645AB	EDIP32	
DALLAS	DS1645Y	EDIP32	
DALLAS	DS1650AB	EDIP32	
DALLAS	DS1650Y	EDIP32	
DALLAS	DS1658AB	DIP40	
DALLAS	DS1658Y	DIP40	
DALLAS	DS1746	EDIP32	
DALLAS	DS1746W	EDIP32	
DALLAS	DS2431	TO-92.3	
DALLAS	DS2433	PR-35.3	
DALLAS	DS2433	SOIC8	PA20SO20D-EO-210
DALLAS	DS24B33	TO-92.3	
DALLAS	DS28E07	TO-92.3	
DALLAS	DS28EC20	TO-92.3	
DALLAS	DS5000/T-32	DIP40	
DALLAS	DS5000/T-8	DIP40	
DALLAS	DS87C520	DIP40	
DALLAS	DS87C520	PLCC44	PA44-48U
DALLAS	DS87C530	PLCC52	PA52PL40DD
DALLAS	DS87C530	PLCC52	PA530-52
DALLAS	DS89C420	DIP40	

DALLAS	DS89C420	PLCC44	PA44-48U
DALLAS	DS89C420REVB4	DIP40	
DALLAS	DS89C420REVB4	PLCC44	PA44-48U
DALLAS	DS89C420REVB4	TQFP44	PA44QF44D
DALLAS	DS89C430	DIP40	
DALLAS	DS89C430	PLCC44	PA44-48U
DALLAS	DS89C430	TQFP44	PA44QF44D
DALLAS	DS89C440	DIP40	
DALLAS	DS89C440	PLCC44	PA44-48U
DALLAS	DS89C440	TQFP44	PA44QF44D
DALLAS	DS89C450	DIP40	
DALLAS	DS89C450	PLCC44	PA44-48U
DALLAS	DS89C450	TQFP44	PA44QF44D
DENSE PAC	DPV27C101	DIP32	
DENSE PAC	DPV27C256	DIP28	
DENSE PAC	DPV27C512	DIP28	
DENSE PAC	DPV27C512	PLCC32	PA32PL28D-YA
EFST	F49B002UA	DIP32	
EFST	F49B002UA	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN25B10	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25B10	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25B10T	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25B10T	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25B16	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25B16	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25B16	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25B16T	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25B16T	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25B16T	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25B20	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25B20	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25B20T	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25B20T	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25B32	DIP8	
Eon Silicon Solution	Inc. EN25B32	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25B32	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25B32	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25B32T	DIP8	
Eon Silicon Solution	Inc. EN25B32T	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25B32T	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25B32T	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25B40	DIP8	
Eon Silicon Solution	Inc. EN25B40	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25B40	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25B40	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25B40T	DIP8	
Eon Silicon Solution	Inc. EN25B40T	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25B40T	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25B40T	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25B64	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25B64T	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25B80	DIP8	
Eon Silicon Solution	Inc. EN25B80	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25B80	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25B80T	DIP8	
Eon Silicon Solution	Inc. EN25B80T	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25B80T	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25E40(2A)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25E40(2A)	USON8	PA8SON8D(2x3)
Eon Silicon Solution	Inc. EN25F10	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25F10	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25F10A(2NF)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25F10A(2NF)	USON8	PA8SON8D(2x3)
Eon Silicon Solution	Inc. EN25F10A(2NF)	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25F10A(2NF)	VSOP8	PA16SO16D-EO-150
Eon Silicon Solution	Inc. EN25F16	DIP8	
Eon Silicon Solution	Inc. EN25F16	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25F16	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25F16	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25F20	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25F20	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25F20A	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25F20A	USON8	PA8SON8D(2x3)

Eon Silicon Solution	Inc. EN25F20A	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25F20A	VSOP8	PA16SO16D-EO-150
Eon Silicon Solution	Inc. EN25F32	DIP8	
Eon Silicon Solution	Inc. EN25F32	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25F32	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25F32	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25F40	DIP8	
Eon Silicon Solution	Inc. EN25F40	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25F40	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25F40	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25F80	DIP8	
Eon Silicon Solution	Inc. EN25F80	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25F80	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25F80A	DIP8	
Eon Silicon Solution	Inc. EN25F80A	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25F80A	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25LF05	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25LF05	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25LF10	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25LF10	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25P05	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25P05	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25P10	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25P10	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25P16	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25P16	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25P16	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25P20	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25P20	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25P32	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25P32	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25P32	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25P40	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25P40	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25P40	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25P64	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25P80	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25P80	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25Q128	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25Q128	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25Q128	VDFN8	PA8SON8DA(8x6)
Eon Silicon Solution	Inc. EN25Q16	DIP8	
Eon Silicon Solution	Inc. EN25Q16	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25Q16	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25Q16	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25Q16A	DIP8	
Eon Silicon Solution	Inc. EN25Q16A	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25Q16A	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25Q16A	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25Q32	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25Q32	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25Q32A	DIP8	
Eon Silicon Solution	Inc. EN25Q32A	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25Q32A	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25Q32A	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25Q32B	DIP8	
Eon Silicon Solution	Inc. EN25Q32B	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25Q32B	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25Q32B	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25Q32C	DIP8	
Eon Silicon Solution	Inc. EN25Q32C	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25Q32C	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25Q32C	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25Q40	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25Q40	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25Q40A	DIP8	
Eon Silicon Solution	Inc. EN25Q40A	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25Q40A	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25Q40A	USON8	PA8SON8D(2x3)
Eon Silicon Solution	Inc. EN25Q40A	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25Q40A	VSOP8	PA16SO16D-EO-150
Eon Silicon Solution	Inc. EN25Q64	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25Q64	SOP8	PA20SO20D-EO-210

Eon Silicon Solution	Inc. EN25Q64	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25Q64	VDFN8	PA8SON8DA(8x6)
Eon Silicon Solution	Inc. EN25Q80A	DIP8	
Eon Silicon Solution	Inc. EN25Q80A	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25Q80A	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25Q80A	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25Q80B	DIP8	
Eon Silicon Solution	Inc. EN25Q80B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25Q80B	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25Q80B	USON8	PA8SON8D(2x3)
Eon Silicon Solution	Inc. EN25Q80B	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25Q80B	VSOP8	PA16SO16D-EO-150
Eon Silicon Solution	Inc. EN25Q80B (Dual I/O)	DIP8	
Eon Silicon Solution	Inc. EN25Q80B (Dual I/O)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25Q80B (Dual I/O)	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25Q80B (Dual I/O)	USON8	PA8SON8D(2x3)
Eon Silicon Solution	Inc. EN25Q80B (Dual I/O)	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25Q80B (Dual I/O)	VSOP8	PA16SO16D-EO-150
Eon Silicon Solution	Inc. EN25Q80B(2C)	DIP8	
Eon Silicon Solution	Inc. EN25Q80B(2C)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25Q80B(2C)	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25Q80B(2C)	USON8	PA8SON8D(2x3)
Eon Silicon Solution	Inc. EN25Q80B(2C)	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25Q80B(2C) (Dual I/O)	DIP8	
Eon Silicon Solution	Inc. EN25Q80B(2C) (Dual I/O)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25Q80B(2C) (Dual I/O)	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25Q80B(2C) (Dual I/O)	USON8	PA8SON8D(2x3)
Eon Silicon Solution	Inc. EN25Q80B(2C) (Dual I/O)	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25Q80C(2A)	DIP8	
Eon Silicon Solution	Inc. EN25Q80C(2A)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25Q80C(2A)	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25Q80C(2A)	USON8	PA8SON8D(2x3)
Eon Silicon Solution	Inc. EN25Q80C(2A)	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25Q80C(2A)	VSOP8	PA16SO16D-EO-150
Eon Silicon Solution	Inc. EN25QA32A	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25QA32B(2B)	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25QA32B(2C)	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25QA64A	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25QH128	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25QH128	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25QH128	VDFN8	PA8SON8DA(8x6)
Eon Silicon Solution	Inc. EN25QH128A(2T)	DIP8	
Eon Silicon Solution	Inc. EN25QH128A(2T)	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25QH128A(2T)	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25QH128A(2T)	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25QH128A(2T)	VDFN8	PA8SON8DA(8x6)
Eon Silicon Solution	Inc. EN25QH16	DIP8	
Eon Silicon Solution	Inc. EN25QH16	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25QH16	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25QH16	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25QH16A	DIP8	
Eon Silicon Solution	Inc. EN25QH16A	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25QH16A	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25QH16A	USON8	PA8SON8D(4x3)
Eon Silicon Solution	Inc. EN25QH16A	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25QH16A	VSOP8	PA16SO16D-EO-150
Eon Silicon Solution	Inc. EN25QH256	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25QH256	VDFN8	PA8SON8DA(8x6)
Eon Silicon Solution	Inc. EN25QH256 (QPI)	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25QH256 (QPI)	VDFN8	PA8SON8DA(8x6)
Eon Silicon Solution	Inc. EN25QH32	DIP8	
Eon Silicon Solution	Inc. EN25QH32	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25QH32	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25QH32	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25QH32	VDFN8	PA8SON8DA(8x6)
Eon Silicon Solution	Inc. EN25QH32A	DIP8	
Eon Silicon Solution	Inc. EN25QH32A	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25QH32A	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25QH32A	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25QH32B(2C)	DIP8	
Eon Silicon Solution	Inc. EN25QH32B(2C)	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25QH32B(2C)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25QH32B(2C)	SOP8	PA20SO20D-EO-210





Eon Silicon Solution	Inc. EN25S64A	VSOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25S64A(2SC)	DIP8	
Eon Silicon Solution	Inc. EN25S64A(2SC)	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25S64A(2SC)	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25S64A(2SC)	VSOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25S80	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25S80	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25S80	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25S80A	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25S80A	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25S80A	USON8	PA8SON8D(4x3)
Eon Silicon Solution	Inc. EN25S80A	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25S80A	VSOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25S80B(2S)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
Eon Silicon Solution	Inc. EN25S80B(2S)	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25S80B(2S)	USON8	PA8SON8D(2x3)
Eon Silicon Solution	Inc. EN25S80B(2S)	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25S80B(2S)	VSOP8	PA16SO16D-EO-150
Eon Silicon Solution	Inc. EN25SX128A(2P)	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25SX128A(2P)	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25SX128A(2P)	USON8	PA8SON8D(4x3)
Eon Silicon Solution	Inc. EN25SX128A(2P)	WSON8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN25SX128A(2P)	WSON8	PA8SON8DA(8x6)
Eon Silicon Solution	Inc. EN25T16	DIP8	
Eon Silicon Solution	Inc. EN25T16	SOP16	PA28SO28D-EO-300
Eon Silicon Solution	Inc. EN25T16	SOP8	PA20SO20D-EO-210
Eon Silicon Solution	Inc. EN25T16	VDFN8	PA8SON8D(6x5)
Eon Silicon Solution	Inc. EN27C010	DIP32	
Eon Silicon Solution	Inc. EN27C010	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN27C010	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN27C020	DIP32	
Eon Silicon Solution	Inc. EN27C020	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN27C020	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN27C512	DIP28	
Eon Silicon Solution	Inc. EN27C512	PLCC32	PA32PL28D-YA
Eon Silicon Solution	Inc. EN27C512	TSOP28	PA28TS28D-EO
Eon Silicon Solution	Inc. EN27LV010	DIP32	
Eon Silicon Solution	Inc. EN27LV010	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN27LV010	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN27LV010B	DIP32	
Eon Silicon Solution	Inc. EN27LV010B	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN27LV010B	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN27LV020	DIP32	
Eon Silicon Solution	Inc. EN27LV020	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN27LV020	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN27LV020B	DIP32	
Eon Silicon Solution	Inc. EN27LV020B	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN27LV020B	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN27LV512	DIP28	
Eon Silicon Solution	Inc. EN27LV512	PLCC32	PA32PL28D-YA
Eon Silicon Solution	Inc. EN27LV512	TSOP28	PA28TS28D-EO
Eon Silicon Solution	Inc. EN27LV512B	DIP28	
Eon Silicon Solution	Inc. EN27LV512B	PLCC32	PA32PL28D-YA
Eon Silicon Solution	Inc. EN27LV512B	TSOP28	PA28TS28D-EO
Eon Silicon Solution	Inc. EN29F002AB	DIP32	
Eon Silicon Solution	Inc. EN29F002AB	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN29F002AB	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN29F002ANB	DIP32	
Eon Silicon Solution	Inc. EN29F002ANB	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN29F002ANB	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN29F002ANT	DIP32	
Eon Silicon Solution	Inc. EN29F002ANT	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN29F002ANT	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN29F002AT	DIP32	
Eon Silicon Solution	Inc. EN29F002AT	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN29F002AT	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN29F002B	DIP32	
Eon Silicon Solution	Inc. EN29F002B	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN29F002B	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN29F002NB	DIP32	
Eon Silicon Solution	Inc. EN29F002NB	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN29F002NB	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN29F002NT	DIP32	

Eon Silicon Solution	Inc. EN29F002NT	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN29F002NT	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN29F002T	DIP32	
Eon Silicon Solution	Inc. EN29F002T	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN29F002T	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN29F010	DIP32	
Eon Silicon Solution	Inc. EN29F010	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN29F010	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN29F040	DIP32	
Eon Silicon Solution	Inc. EN29F040	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN29F040	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN29F040A	DIP32	
Eon Silicon Solution	Inc. EN29F040A	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN29F040A	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN29F512	DIP32	
Eon Silicon Solution	Inc. EN29F512	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN29F512	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN29F800B	TSOP48	PA48TS48D
Eon Silicon Solution	Inc. EN29F800T	TSOP48	PA48TS48D
Eon Silicon Solution	Inc. EN29GL128H	TSOP56	HA56TS48DI
Eon Silicon Solution	Inc. EN29GL128H	TSOP56	PA56TS48DB
Eon Silicon Solution	Inc. EN29GL128H	TSOP56	PA56TS48DC
Eon Silicon Solution	Inc. EN29GL128H	TSOP56	PA56TS48DD
Eon Silicon Solution	Inc. EN29GL128L	TSOP56	HA56TS48DI
Eon Silicon Solution	Inc. EN29GL128L	TSOP56	PA56TS48DB
Eon Silicon Solution	Inc. EN29GL128L	TSOP56	PA56TS48DC
Eon Silicon Solution	Inc. EN29GL128L	TSOP56	PA56TS48DD
Eon Silicon Solution	Inc. EN29LV010	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN29LV010	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN29LV040	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN29LV040	sTSOP32	PA32TS32D
Eon Silicon Solution	Inc. EN29LV040	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN29LV040A	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN29LV040A	sTSOP32	PA32TS32D
Eon Silicon Solution	Inc. EN29LV040A	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN29LV040J	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN29LV040J	sTSOP32	PA32TS32D
Eon Silicon Solution	Inc. EN29LV040J	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN29LV160AB	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV160AT	BGA48	PA48BG48DAI
Eon Silicon Solution	Inc. EN29LV160AT	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV160BB	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV160BB-70BIP	BGA48	HA48BG48DAI
Eon Silicon Solution	Inc. EN29LV160BB-70TIP	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV160BB-B	BGA48	HA48BG48DAI
Eon Silicon Solution	Inc. EN29LV160BT	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV160BT-70BIP	BGA48	HA48BG48DAI
Eon Silicon Solution	Inc. EN29LV160BT-70TIP	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV160BT-B	BGA48	HA48BG48DAI
Eon Silicon Solution	Inc. EN29LV320AB	BGA48	HA48BG48DAI
Eon Silicon Solution	Inc. EN29LV320AB	BGA48	PA48BG48DW
Eon Silicon Solution	Inc. EN29LV320AB	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV320AT	BGA48	PA48BG48DAI
Eon Silicon Solution	Inc. EN29LV320AT	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV320B	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV320BB	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV320BB-B	BGA48	HA48BG48DAI
Eon Silicon Solution	Inc. EN29LV320BT	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV320BT-B	BGA48	HA48BG48DAI
Eon Silicon Solution	Inc. EN29LV320T	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV400AB	TSOP48	PA48TS48D
Eon Silicon Solution	Inc. EN29LV400AT	TSOP48	PA48TS48D
Eon Silicon Solution	Inc. EN29LV400B	TSOP48	PA48TS48D
Eon Silicon Solution	Inc. EN29LV400JB	TSOP48	PA48TS48D
Eon Silicon Solution	Inc. EN29LV400JT	TSOP48	PA48TS48D
Eon Silicon Solution	Inc. EN29LV400T	TSOP48	PA48TS48D
Eon Silicon Solution	Inc. EN29LV512	PLCC32	PA32PL32D
Eon Silicon Solution	Inc. EN29LV512	TSOP32	PA32TS20/PA32TS32D-20
Eon Silicon Solution	Inc. EN29LV640B	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV640H	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV640L	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV640T	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV641H	TSOP48	PA48TS48D

Eon Silicon Solution	Inc. EN29LV641L	TSOP48	PA48TS48D
Eon Silicon Solution	Inc. EN29LV800AB	TSOP48	PA48TS48D
Eon Silicon Solution	Inc. EN29LV800AT	TSOP48	PA48TS48D
Eon Silicon Solution	Inc. EN29LV800B	TSOP48	PA48TS48D
Eon Silicon Solution	Inc. EN29LV800BB	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV800BT	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV800CB-70TIP	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV800CB-B	BGA48	HA48BG48DAI
Eon Silicon Solution	Inc. EN29LV800CB-T	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV800CT-70TIP	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV800CT-B	BGA48	HA48BG48DAI
Eon Silicon Solution	Inc. EN29LV800CT-T	TSOP48	PA48TS48D1
Eon Silicon Solution	Inc. EN29LV800JB	TSOP48	PA48TS48D
Eon Silicon Solution	Inc. EN29LV800JT	TSOP48	PA48TS48D
Eon Silicon Solution	Inc. EN29LV800T	TSOP48	PA48TS48D
Eon Silicon Solution	Inc. EN29SL400B	TSOP48	HA48TS48DJ
Eon Silicon Solution	Inc. EN29SL400T	TSOP48	HA48TS48DJ
Eon Silicon Solution	Inc. EN29SL800B	TSOP48	HA48TS48DJ
Eon Silicon Solution	Inc. EN29SL800T	TSOP48	HA48TS48DJ
Eon Silicon Solution	Inc. EN39LV010	PLCC32	PA32PL32D
ESMT	EN25F10A(2NF)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ESMT	EN25F10A(2NF)	USON8	PA8SON8D(2x3)
ESMT	EN25F10A(2NF)	VDFN8	PA8SON8D(6x5)
ESMT	EN25F10A(2NF)	VSOP8	PA16SO16D-EO-150
ESMT	EN25F20A	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ESMT	EN25F20A	USON8	PA8SON8D(2x3)
ESMT	EN25F20A	VDFN8	PA8SON8D(6x5)
ESMT	EN25F20A	VSOP8	PA16SO16D-EO-150
ESMT	EN25Q40A	DIP8	
ESMT	EN25Q40A	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ESMT	EN25Q40A	SOP8	PA20SO20D-EO-210
ESMT	EN25Q40A	USON8	PA8SON8D(2x3)
ESMT	EN25Q40A	VDFN8	PA8SON8D(6x5)
ESMT	EN25Q40A	VSOP8	PA16SO16D-EO-150
ESMT	EN25Q80B	DIP8	
ESMT	EN25Q80B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ESMT	EN25Q80B	SOP8	PA20SO20D-EO-210
ESMT	EN25Q80B	USON8	PA8SON8D(2x3)
ESMT	EN25Q80B	VDFN8	PA8SON8D(6x5)
ESMT	EN25Q80B	VSOP8	PA16SO16D-EO-150
ESMT	EN25Q80B (Dual I/O)	DIP8	
ESMT	EN25Q80B (Dual I/O)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ESMT	EN25Q80B (Dual I/O)	SOP8	PA20SO20D-EO-210
ESMT	EN25Q80B (Dual I/O)	USON8	PA8SON8D(2x3)
ESMT	EN25Q80B (Dual I/O)	VDFN8	PA8SON8D(6x5)
ESMT	EN25Q80B (Dual I/O)	VSOP8	PA16SO16D-EO-150
ESMT	EN25Q80B(2C)	DIP8	
ESMT	EN25Q80B(2C)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ESMT	EN25Q80B(2C)	SOP8	PA20SO20D-EO-210
ESMT	EN25Q80B(2C)	USON8	PA8SON8D(2x3)
ESMT	EN25Q80B(2C)	VDFN8	PA8SON8D(6x5)
ESMT	EN25Q80B(2C) (Dual I/O)	DIP8	
ESMT	EN25Q80B(2C) (Dual I/O)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ESMT	EN25Q80B(2C) (Dual I/O)	SOP8	PA20SO20D-EO-210
ESMT	EN25Q80B(2C) (Dual I/O)	USON8	PA8SON8D(2x3)
ESMT	EN25Q80B(2C) (Dual I/O)	VDFN8	PA8SON8D(6x5)
ESMT	EN25Q80C(2A)	DIP8	
ESMT	EN25Q80C(2A)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ESMT	EN25Q80C(2A)	SOP8	PA20SO20D-EO-210
ESMT	EN25Q80C(2A)	USON8	PA8SON8D(2x3)
ESMT	EN25Q80C(2A)	VDFN8	PA8SON8D(6x5)
ESMT	EN25Q80C(2A)	VSOP8	PA16SO16D-EO-150
ESMT	EN25QA32B(2B)	SOP8	PA20SO20D-EO-210
ESMT	EN25QA32B(2C)	SOP8	PA20SO20D-EO-210
ESMT	EN25QA64A	SOP8	PA20SO20D-EO-210
ESMT	EN25QH128A(2T)	DIP8	
ESMT	EN25QH128A(2T)	SOP16	PA28SO28D-EO-300
ESMT	EN25QH128A(2T)	SOP8	PA20SO20D-EO-210
ESMT	EN25QH128A(2T)	VDFN8	PA8SON8D(6x5)
ESMT	EN25QH128A(2T)	VDFN8	PA8SON8DA(8x6)
ESMT	EN25QH256	SOP16	PA28SO28D-EO-300
ESMT	EN25QH256	VDFN8	PA8SON8DA(8x6)
ESMT	EN25QH32B(2C)	DIP8	

ESMT	EN25QH32B(2C)	SOP16	PA28SO28D-EO-300
ESMT	EN25QH32B(2C)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ESMT	EN25QH32B(2C)	SOP8	PA20SO20D-EO-210
ESMT	EN25QH32B(2C)	VDFN8	PA8SON8D(6x5)
ESMT	EN25QH64A	DIP8	
ESMT	EN25QH64A	SOP16	PA28SO28D-EO-300
ESMT	EN25QH64A	SOP8	PA20SO20D-EO-210
ESMT	EN25QH64A	USON8	PA8SON8D(4x3)
ESMT	EN25QH64A	VDFN8	PA8SON8D(6x5)
ESMT	EN25QH64A	VDFN8	PA8SON8DA(8x6)
ESMT	EN25QX128A(2V)	SOP16	PA28SO28D-EO-300
ESMT	EN25QX128A(2V)	SOP8	PA20SO20D-EO-210
ESMT	EN25QX128A(2V)	WSON8	PA8SON8D(6x5)
ESMT	EN25QX128A(2V)	WSON8	PA8SON8DA(8x6)
ESMT	EN25QX128A(2V) (QPI)	SOP16	PA28SO28D-EO-300
ESMT	EN25QX128A(2V) (QPI)	SOP8	PA20SO20D-EO-210
ESMT	EN25QX128A(2V) (QPI)	WSON8	PA8SON8D(6x5)
ESMT	EN25QX128A(2V) (QPI)	WSON8	PA8SON8DA(8x6)
ESMT	EN25QX64A(2C)	SOP16	PA28SO28D-EO-300
ESMT	EN25QX64A(2C)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ESMT	EN25QX64A(2C)	SOP8	PA20SO20D-EO-210
ESMT	EN25QX64A(2C)	USON8	PA8SON8D(4x3)
ESMT	EN25QX64A(2C)	WSON8	PA8SON8D(6x5)
ESMT	EN25QX64A(2C)	WSON8	PA8SON8DA(8x6)
ESMT	EN25QX64A(2C) (QPI)	SOP16	PA28SO28D-EO-300
ESMT	EN25QX64A(2C) (QPI)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ESMT	EN25QX64A(2C) (QPI)	SOP8	PA20SO20D-EO-210
ESMT	EN25QX64A(2C) (QPI)	USON8	PA8SON8D(4x3)
ESMT	EN25QX64A(2C) (QPI)	WSON8	PA8SON8D(6x5)
ESMT	EN25QX64A(2C) (QPI)	WSON8	PA8SON8DA(8x6)
ESMT	EN25S10A	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ESMT	EN25S10A	USON8	PA8SON8D(2x3)
ESMT	EN25S10A	VSOP8	PA16SO16D-EO-150
ESMT	EN25S16B(2S)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ESMT	EN25S16B(2S)	SOP8	PA20SO20D-EO-210
ESMT	EN25S16B(2S)	USON8	PA8SON8D(2x3)
ESMT	EN25S16B(2S)	USON8	PA8SON8D(4x3)
ESMT	EN25S16B(2S)	VDFN8	PA8SON8D(6x5)
ESMT	EN25S16B(2S)	VSOP8	PA16SO16D-EO-150
ESMT	EN25S20A	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ESMT	EN25S20A	USON8	PA8SON8D(2x3)
ESMT	EN25S20A	VDFN8	PA8SON8D(6x5)
ESMT	EN25S20A	VSOP8	PA16SO16D-EO-150
ESMT	EN25S32A(2S)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ESMT	EN25S32A(2S)	SOP8	PA20SO20D-EO-210
ESMT	EN25S32A(2S)	USON8	PA8SON8D(4x3)
ESMT	EN25S32A(2S)	VDFN8	PA8SON8D(6x5)
ESMT	EN25S32A(2S)	VSOP8	PA20SO20D-EO-210
ESMT	EN25S40A	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ESMT	EN25S40A	USON8	PA8SON8D(2x3)
ESMT	EN25S40A	VDFN8	PA8SON8D(6x5)
ESMT	EN25S40A	VSOP8	PA16SO16D-EO-150
ESMT	EN25S64A	DIP8	
ESMT	EN25S64A	SOP8	PA20SO20D-EO-210
ESMT	EN25S64A	VDFN8	PA8SON8D(6x5)
ESMT	EN25S64A	VSOP8	PA20SO20D-EO-210
ESMT	EN25S80B(2S)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ESMT	EN25S80B(2S)	SOP8	PA20SO20D-EO-210
ESMT	EN25S80B(2S)	USON8	PA8SON8D(2x3)
ESMT	EN25S80B(2S)	VDFN8	PA8SON8D(6x5)
ESMT	EN25S80B(2S)	VSOP8	PA16SO16D-EO-150
ESMT	EN25SX128A(2P)	SOP16	PA28SO28D-EO-300
ESMT	EN25SX128A(2P)	SOP8	PA20SO20D-EO-210
ESMT	EN25SX128A(2P)	USON8	PA8SON8D(4x3)
ESMT	EN25SX128A(2P)	WSON8	PA8SON8D(6x5)
ESMT	EN25SX128A(2P)	WSON8	PA8SON8DA(8x6)
EXCELSEMI	ES29LV160DB	SOP44	PA44SO44D
EXCELSEMI	ES29LV160DB	TSOP48	PA48TS48D1
EXCELSEMI	ES29LV160DT	SOP44	PA44SO44D
EXCELSEMI	ES29LV160DT	TSOP48	PA48TS48D1
EXCELSEMI	ES29LV160EB	SOP44	PA44SO44D
EXCELSEMI	ES29LV160EB	TSOP48	PA48TS48D1
EXCELSEMI	ES29LV160ET	SOP44	PA44SO44D

EXCELSEMI	ES29LV160ET	TSOP48	PA48TS48D1
EXCELSEMI	ES29LV160FB	BGA48	HA48BG48DBC
EXCELSEMI	ES29LV160FB	TSOP48	PA48TS48D1
EXCELSEMI	ES29LV160FT	BGA48	HA48BG48DBC
EXCELSEMI	ES29LV160FT	TSOP48	PA48TS48D1
EXCELSEMI	ES29LV320DB	BGA48	HA48BG48DBC
EXCELSEMI	ES29LV320DB	TSOP48	PA48TS48D1
EXCELSEMI	ES29LV320DT	BGA48	HA48BG48DBC
EXCELSEMI	ES29LV320DT	TSOP48	PA48TS48D1
EXCELSEMI	ES29LV320EB	TSOP48	PA48TS48D1
EXCELSEMI	ES29LV320ET	TSOP48	PA48TS48D1
EXCELSEMI	ES29LV400DB	BGA48	HA48BG48DBC
EXCELSEMI	ES29LV400DB	TSOP48	PA48TS48D1
EXCELSEMI	ES29LV400DT	BGA48	HA48BG48DBC
EXCELSEMI	ES29LV400DT	TSOP48	PA48TS48D1
EXCELSEMI	ES29LV400EB	BGA48	HA48BG48DBC
EXCELSEMI	ES29LV400EB	TSOP48	PA48TS48D1
EXCELSEMI	ES29LV400ET	BGA48	HA48BG48DBC
EXCELSEMI	ES29LV400ET	TSOP48	PA48TS48D1
EXCELSEMI	ES29LV800DB	BGA48	HA48BG48DBC
EXCELSEMI	ES29LV800DB	SOP44	PA44SO44D
EXCELSEMI	ES29LV800DB	TSOP48	PA48TS48D1
EXCELSEMI	ES29LV800DT	BGA48	HA48BG48DBC
EXCELSEMI	ES29LV800DT	SOP44	PA44SO44D
EXCELSEMI	ES29LV800DT	TSOP48	PA48TS48D1
EXCELSEMI	ES29LV800EB	BGA48	HA48BG48DBC
EXCELSEMI	ES29LV800EB	TSOP48	PA48TS48D1
EXCELSEMI	ES29LV800ET	BGA48	HA48BG48DBC
EXCELSEMI	ES29LV800ET	TSOP48	PA48TS48D1
EXEL	XL2816A	DIP24	
EXEL	XL2816A	PLCC32	PA32PL32D
EXEL	XL2816A	SOIC28	PA28SO28D-EO-300
EXEL	XL2817A	DIP28	
EXEL	XL2864A	DIP28	
EXEL	XL2864A	PLCC32	PA32PL28D-YA
EXEL	XL2864A	SOIC28	PA28SO28D-EO-300
EXEL	XL2865A	DIP28	
EXEL	XL2865A	PLCC32	PA32PL28D-YA
EXEL	XL28C16A	DIP24	
EXEL	XL28C16A	PLCC32	PA32PL32D
EXEL	XL28C16A	SOIC28	PA28SO28D-EO-300
EXEL	XL28C256	DIP28	
EXEL	XL28C256	PLCC32	PA32PL28D-YA
EXEL	XL28C64	DIP28	
EXEL	XL28C64	PLCC32	PA32PL28D-YA
EXEL	XL28C64	SOIC28	PA28SO28D-EO-300
EXEL	XL28C64B	DIP28	
EXEL	XL28C64B	PLCC32	PA32PL28D-YA
EXEL	XL28C64B	SOIC28	PA28SO28D-EO-300
EXEL	XL28C65A	DIP28	
EXEL	XL28C65A	PLCC32	PA32PL32D
EXEL	XL28C65A	SOIC28	PA28SO28D-EO-300
EXEL	XL93C06	DIP8	
EXEL	XL93C06	SOIC8	PA16SO16D-EO-150
EXEL	XL93C46	DIP8	
EXEL	XL93C46	SOIC8	PA16SO16D-EO-150
EXEL	XL93C46A	DIP8	
EXEL	XL93C46A	SOIC8	PA16SO16D-EO-150
EXEL	XL93C56	DIP8	
EXEL	XL93C56	SOIC8	PA16SO16D-EO-150
EXEL	XL93C56A	DIP8	
EXEL	XL93C56A	SOIC8	PA16SO16D-EO-150
EXEL	XL93C66	DIP8	
EXEL	XL93C66	SOIC8	PA16SO16D-EO-150
EXEL	XL93C66A	DIP8	
EXEL	XL93C66A	SOIC8	PA16SO16D-EO-150
EXEL	XL93CS46	DIP8	
EXEL	XL93LC46	DIP8	
EXEL	XL93LC46	SOIC8	PA16SO16D-EO-150
EXEL	XL93LC56	DIP8	
EXEL	XL93LC56	SOIC8	PA16SO16D-EO-150
EXEL	XL93LC66	DIP8	
EXEL	XL93LC66	SOIC8	PA16SO16D-EO-150

EXEL	XL93LL46		DIP8	
EXEL	XL93LL56		DIP8	
EXEL	XL93LL66		DIP8	
EXEL	XLE2816A		DIP24	
EXEL	XLE2816A		PLCC32	PA32PL32D
EXEL	XLE2816A		SOIC28	PA28SO28D-EO-300
EXEL	XLE2864A		DIP28	
EXEL	XLE2864A		PLCC32	PA32PL28D-YA
EXEL	XLE2864A		SOIC28	PA28SO28D-EO-300
EXEL	XLE2865A		DIP28	
EXEL	XLE2865A		PLCC32	PA32PL28D-YA
EXEL	XLE28C16A		DIP24	
EXEL	XLE28C16A		PLCC32	PA32PL32D
EXEL	XLE28C16A		SOIC28	PA28SO28D-EO-300
EXEL	XLE28C256		DIP28	
EXEL	XLE28C256		PLCC32	PA32PL28D-YA
EXEL	XLE28C64		DIP28	
EXEL	XLE28C64		PLCC32	PA32PL28D-YA
EXEL	XLE28C64		SOIC28	PA28SO28D-EO-300
EXEL	XLE28C64B		DIP28	
EXEL	XLE28C64B		PLCC32	PA32PL28D-YA
EXEL	XLE28C64B		SOIC28	PA28SO28D-EO-300
EXEL	XLE28C65A		DIP28	
EXEL	XLE28C65A		PLCC32	PA32PL28D-YA
EXEL	XLE28C65A		SOIC28	PA28SO28D-EO-300
EXEL	XLE93C46		DIP8	
EXEL	XLE93C56		DIP8	
EXEL	XLE93C66		DIP8	
EXEL	XLE93CS46		DIP8	
EXEL	XLM2817A		DIP28	
EXEL	XLM28C65A		DIP28	
EXEL	XLM28C65A		PLCC32	PA32PL28D-YA
EXEL	XLM28C65A		SOIC28	PA28SO28D-EO-300
EXEL	XLS2804A		DIP24	
EXEL	XLS2816A		DIP24	
EXEL	XLS2816A		PLCC32	PA32PL32D
EXEL	XLS2816A		SOIC28	PA28SO28D-EO-300
EXEL	XLS2817A		DIP28	
EXEL	XLS2864A		DIP28	
EXEL	XLS2864A		PLCC32	PA32PL28D-YA
EXEL	XLS2864A		SOIC28	PA28SO28D-EO-300
EXEL	XLS2865A		DIP28	
EXEL	XLS2865A		PLCC32	PA32PL28D-YA
EXEL	XLS28C16A		DIP24	
EXEL	XLS28C16A		PLCC32	PA32PL32D
EXEL	XLS28C16A		SOIC28	PA28SO28D-EO-300
EXEL	XLS28C256		DIP28	
EXEL	XLS28C256		PLCC32	PA32PL28D-YA
EXEL	XLS28C64		DIP28	
EXEL	XLS28C64		PLCC32	PA32PL28D-YA
EXEL	XLS28C64		SOIC28	PA28SO28D-EO-300
EXEL	XLS28C64B		DIP28	
EXEL	XLS28C64B		PLCC32	PA32PL28D-YA
EXEL	XLS28C64B		SOIC28	PA28SO28D-EO-300
EXEL	XLS28C65A		DIP28	
EXEL	XLS28C65A		PLCC32	PA32PL28D-YA
EXEL	XLS28C65A		SOIC28	PA28SO28D-EO-300
EXEL	XLS93C46		DIP8	
EXEL	XLS93C46		SOIC8	PA16SO16D-EO-150
EXEL	XLS93C56		DIP8	
EXEL	XLS93C56		SOIC8	PA16SO16D-EO-150
EXEL	XLS93C66		DIP8	
EXEL	XLS93C66		SOIC8	PA16SO16D-EO-150
EXEL	XLS93CS46		DIP8	
EXEL	XLS93LC46		DIP8	
EXEL	XLS93LC56		DIP8	
EXEL	XLS93LC66		DIP8	
FAIRCHILD		93427	DIP16	
FAIRCHILD		93436	DIP16	
FAIRCHILD	ACE1101		DIP8	
FAIRCHILD	ACE1202		DIP8	
FAIRCHILD	F2716		DIP24	
FAIRCHILD	F2732		DIP24	

FAIRCHILD	FM24C02UF-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C02UF-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	FM24C02UF-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C02UF-N	DIP8	
FAIRCHILD	FM24C02U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C02U-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	FM24C02U-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C02U-N	DIP8	
FAIRCHILD	FM24C03UF-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C03UF-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	FM24C03UF-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C03UF-N	DIP8	
FAIRCHILD	FM24C03U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C03U-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	FM24C03U-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C03U-N	DIP8	
FAIRCHILD	FM24C04UF-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C04UF-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	FM24C04UF-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C04UF-N	DIP8	
FAIRCHILD	FM24C04U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C04U-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	FM24C04U-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C04U-N	DIP8	
FAIRCHILD	FM24C05UF-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C05UF-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	FM24C05UF-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C05UF-N	DIP8	
FAIRCHILD	FM24C05U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C05U-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	FM24C05U-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C05U-N	DIP8	
FAIRCHILD	FM24C08UF-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C08UF-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	FM24C08UF-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C08UF-N	DIP8	
FAIRCHILD	FM24C08U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C08U-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	FM24C08U-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C08U-N	DIP8	
FAIRCHILD	FM24C09UF-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C09UF-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	FM24C09UF-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C09UF-N	DIP8	
FAIRCHILD	FM24C09U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C09U-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	FM24C09U-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C09U-N	DIP8	
FAIRCHILD	FM24C128F-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C128F-MT8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C128F-N	DIP8	
FAIRCHILD	FM24C128-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C128-MT8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C128-N	DIP8	
FAIRCHILD	FM24C16UF-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C16UF-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	FM24C16UF-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C16UF-N	DIP8	
FAIRCHILD	FM24C16U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C16U-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	FM24C16U-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C16U-N	DIP8	
FAIRCHILD	FM24C17UF-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C17UF-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	FM24C17UF-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C17UF-N	DIP8	
FAIRCHILD	FM24C17U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C17U-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	FM24C17U-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C17U-N	DIP8	
FAIRCHILD	FM24C32UF-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C32UF-N	DIP8	
FAIRCHILD	FM24C32U-M8	SOIC8	PA8SO8D-EO-150



FAIRCHILD	FM24C32U-N	DIP8	PA8SO8D-EO-150
FAIRCHILD	FM24C64F-M8	SOIC8	PA24TSS24D
FAIRCHILD	FM24C64F-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C64F-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C64F-N	DIP8	
FAIRCHILD	FM24C64-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM24C64-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	FM24C64-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	FM24C64-N	DIP8	
FAIRCHILD	FM27C010	DIP32	
FAIRCHILD	FM27C010	PLCC32	PA32PL32D
FAIRCHILD	FM27C040	DIP32	
FAIRCHILD	FM27C040	PLCC32	PA32PL32D
FAIRCHILD	FM27C040Q	DIP32	
FAIRCHILD	FM27C256	DIP28	
FAIRCHILD	FM27C256	PLCC32	PA32PL28D-YA
FAIRCHILD	FM27C512	DIP28	
FAIRCHILD	FM27C512	PLCC32	PA32PL28D-YA
FAIRCHILD	FM27LV010	DIP32	
FAIRCHILD	FM27LV010	PLCC32	PA32PL32D
FAIRCHILD	FM34C02U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	FM34C02U-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	FM34C02U-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C02UF-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C02UF-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM24C02UF-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C02UF-N	DIP8	
FAIRCHILD	NM24C02U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C02U-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM24C02U-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C02U-N	DIP8	
FAIRCHILD	NM24C03UF-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C03UF-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM24C03UF-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C03UF-N	DIP8	
FAIRCHILD	NM24C03U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C03U-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM24C03U-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C03U-N	DIP8	
FAIRCHILD	NM24C04UF-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C04UF-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM24C04UF-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C04UF-N	DIP8	
FAIRCHILD	NM24C04U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C04U-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM24C04U-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C04U-N	DIP8	
FAIRCHILD	NM24C05UF-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C05UF-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM24C05UF-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C05UF-N	DIP8	
FAIRCHILD	NM24C05U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C05U-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM24C05U-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C05U-N	DIP8	
FAIRCHILD	NM24C08UF-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C08UF-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM24C08UF-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C08UF-N	DIP8	
FAIRCHILD	NM24C08U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C08U-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM24C08U-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C08U-N	DIP8	
FAIRCHILD	NM24C09UF-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C09UF-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM24C09UF-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C09UF-N	DIP8	
FAIRCHILD	NM24C09U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C09U-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM24C09U-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C09U-N	DIP8	
FAIRCHILD	NM24C128F-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C128F-MT8	SOIC8	PA8SO8D-EO-150

FAIRCHILD	NM24C128F-N	DIP8	
FAIRCHILD	NM24C128-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C128-MT8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C128-N	DIP8	
FAIRCHILD	NM24C16UF-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C16UF-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM24C16UF-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C16UF-N	DIP8	
FAIRCHILD	NM24C16U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C16U-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM24C16U-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C16U-N	DIP8	
FAIRCHILD	NM24C17UF-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C17UF-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM24C17UF-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C17UF-N	DIP8	
FAIRCHILD	NM24C17U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C17U-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM24C17U-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C17U-N	DIP8	
FAIRCHILD	NM24C32UF-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C32UF-N	DIP8	
FAIRCHILD	NM24C32U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C32U-N	DIP8	
FAIRCHILD	NM24C64F-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C64F-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM24C64F-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C64F-N	DIP8	
FAIRCHILD	NM24C64-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM24C64-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM24C64-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM24C64-N	DIP8	
FAIRCHILD	NM27C010	DIP32	
FAIRCHILD	NM27C010	PLCC32	PA32PL32D
FAIRCHILD	NM27C010	TSOP32	PA32TS20/PA32TS32D-20
FAIRCHILD	NM27C020	DIP32	
FAIRCHILD	NM27C020	PLCC32	PA32PL32D
FAIRCHILD	NM27C020	TSOP32	PA32TS20/PA32TS32D-20
FAIRCHILD	NM27C040	DIP32	
FAIRCHILD	NM27C040	PLCC32	PA32PL32D
FAIRCHILD	NM27C128	DIP28	
FAIRCHILD	NM27C128	PLCC32	PA32PL28D-YA
FAIRCHILD	NM27C210	DIP40	
FAIRCHILD	NM27C210	PLCC44	PA44-48U
FAIRCHILD	NM27C240	DIP40	
FAIRCHILD	NM27C240	PLCC44	PA44-48U
FAIRCHILD	NM27C256	DIP28	
FAIRCHILD	NM27C256	PLCC32	PA32PL28D-YA
FAIRCHILD	NM27C256B	DIP28	
FAIRCHILD	NM27C256B	PLCC32	PA32PL28D-YA
FAIRCHILD	NM27C512	DIP28	
FAIRCHILD	NM27C512	PLCC32	PA32PL28D-YA
FAIRCHILD	NM27LC256	DIP28	
FAIRCHILD	NM27LC256	PLCC32	PA32PL28D-YA
FAIRCHILD	NM27LC512	DIP28	
FAIRCHILD	NM27LC512	PLCC32	PA32PL28D-YA
FAIRCHILD	NM27LV010	DIP32	
FAIRCHILD	NM27LV010	PLCC32	PA32PL32D
FAIRCHILD	NM27LV010	TSOP32	PA32TS20/PA32TS32D-20
FAIRCHILD	NM27LV010B	DIP32	
FAIRCHILD	NM27LV010B	PLCC32	PA32PL32D
FAIRCHILD	NM27LV010B	TSOP32	PA32TS20/PA32TS32D-20
FAIRCHILD	NM27LV210	PLCC44	PA44-48U
FAIRCHILD	NM27LV512	DIP28	
FAIRCHILD	NM27LV512	PLCC32	PA32PL28D-YA
FAIRCHILD	NM27P040	DIP32	
FAIRCHILD	NM27P040	PLCC32	PA32PL32D
FAIRCHILD	NM27P512	DIP28	
FAIRCHILD	NM27P512	PLCC32	PA32PL28D-YA
FAIRCHILD	NM34C02U-M8	SOIC8	PA8SO8D-EO-150
FAIRCHILD	NM34C02U-MT8	TSSOP8	PA24TSS24D
FAIRCHILD	NM34C02U-MT8	TSSOP8	PA8TSS8D
FAIRCHILD	NM93C06	DIP8	

FAIRCHILD	NM93C06	SOIC8	PA16SO16D-EO-150
FAIRCHILD	NM93C06	TSSOP8	PA8TSS-OT
FAIRCHILD	NM93C46	DIP8	
FAIRCHILD	NM93C46	SOIC8	PA16SO16D-EO-150
FAIRCHILD	NM93C46	TSSOP8	PA8TSS-OT
FAIRCHILD	NM93C56	DIP8	
FAIRCHILD	NM93C56	SOIC8	PA16SO16D-EO-150
FAIRCHILD	NM93C56	TSSOP8	PA8TSS-OT
FAIRCHILD	NM93C66	DIP8	
FAIRCHILD	NM93C66	SOIC8	PA16SO16D-EO-150
FAIRCHILD	NM93C66	TSSOP8	PA8TSS-OT
FAIRCHILD	NM93C86	DIP8	
FAIRCHILD	NM93C86	SOIC8	PA16SO16D-EO-150
FAIRCHILD	NM93C86	TSSOP8	PA8TSS-OT
FAIRCHILD	NM93CS06	DIP8	
FAIRCHILD	NM93CS06	SOIC8	PA16SO16D-EO-150
FAIRCHILD	NM93CS06	TSSOP8	PA8TSS-OT
FAIRCHILD	NM93CS46	DIP8	
FAIRCHILD	NM93CS46	SOIC8	PA16SO16D-EO-150
FAIRCHILD	NM93CS46	TSSOP8	PA8TSS-OT
FAIRCHILD	NM93CS56	DIP8	
FAIRCHILD	NM93CS56	SOIC8	PA16SO16D-EO-150
FAIRCHILD	NM93CS56	TSSOP8	PA8TSS-OT
FAIRCHILD	NM93CS66	DIP8	
FAIRCHILD	NM93CS66	SOIC8	PA16SO16D-EO-150
FAIRCHILD	NM93CS66	TSSOP8	PA8TSS-OT
FAIRCHILD	NMC27C64	DIP28	
FAIRCHILD	NMC27LC64	DIP28	
FREESCALE	MC68HC705JJ7	SOIC20	PA28SO28D-EO-300
FREESCALE	MC705P6ACDWE	SOIC28	PA28SO28D-EO-300
FREESCALE	MC705P6ACPE	DIP28	
FREESCALE	MC9S08GT16ACFB	QFP44	PA44QF44D
FREESCALE	MC9S08GT16CFB	QFP44	PA44QF44D
FREESCALE	MC9S08GT32ACFB	QFP44	PA44QF44D
FREESCALE	MC9S08GT32CFB	QFP44	PA44QF44D
FREESCALE	MC9S08GT8ACFB	QFP44	PA44QF44D
FREESCALE	MC9S08QA2	SOIC8	PA8SO8D-EO-150
FREESCALE	MC9S08SH4	SSOP20	PA20TSS20D
FUJITSU	MB84VD23280FA	BGA65	PA65BGA48DA
FUJITSU	MB84VD23381FJ	BGA65	PA65BGA48DA
FUJITSU	MB84VD23381HJ	BGA56	PA56BG48DG
FUJITSU	MB84VF5F5F4J2	BGA107	PA107BG48DA
FUJITSU	MB84VF5F5F5J2	BGA107	PA107BG48DA
FUJITSU	MB8541P	DIP8	
FUJITSU	MB85RS4MT	SOP8	PA20SO20D-EO-210
FUJITSU	MB89P625	DIP64	64SD-28DP-8L
FUJITSU	MB89P625	DIP64	HA64ZF48D
FUJITSU	MBL8742H	DIP40	
FUJITSU	MBM27128	DIP28	
FUJITSU	MBM27128	PLCC32	PA32PL28D-YA
FUJITSU	MBM2716	DIP24	
FUJITSU	MBM2716H	DIP24	
FUJITSU	MBM27256	DIP28	
FUJITSU	MBM27256	PLCC32	PA32PL28D-YA
FUJITSU	MBM2732	DIP24	
FUJITSU	MBM2732A	DIP24	
FUJITSU	MBM2764	DIP28	
FUJITSU	MBM27C1000	DIP32	
FUJITSU	MBM27C1001	DIP32	
FUJITSU	MBM27C1001A	DIP32	
FUJITSU	MBM27C1024	DIP40	
FUJITSU	MBM27C1024	PLCC44	PA44-48U
FUJITSU	MBM27C128	DIP28	
FUJITSU	MBM27C128P	DIP28	
FUJITSU	MBM27C128P	PLCC32	PA32PL28D-YA
FUJITSU	MBM27C2048	DIP40	
FUJITSU	MBM27C2048	PLCC44	PA44-48U
FUJITSU	MBM27C256	DIP28	
FUJITSU	MBM27C256	PLCC32	PA32PL28D-YA
FUJITSU	MBM27C256A	DIP28	
FUJITSU	MBM27C256A	PLCC32	PA32PL28D-YA
FUJITSU	MBM27C256A-##-W	DIP28	
FUJITSU	MBM27C256AP	DIP28	

FUJITSU	MBM27C256AP	PLCC32	PA32PL28D-YA
FUJITSU	MBM27C256AP	SOIC28	PA28SO28D-EO-300
FUJITSU	MBM27C256H	DIP28	
FUJITSU	MBM27C256H	PLCC32	PA32PL28D-YA
FUJITSU	MBM27C4001	DIP32	
FUJITSU	MBM27C4096	DIP40	
FUJITSU	MBM27C4096	PLCC44	PA44-48U
FUJITSU	MBM27C512	DIP28	
FUJITSU	MBM27C512	PLCC32	PA32PL28D-YA
FUJITSU	MBM27C512P	DIP28	
FUJITSU	MBM27C512P	PLCC32	PA32PL28D-YA
FUJITSU	MBM27C64	DIP28	
FUJITSU	MBM28C256	DIP28	
FUJITSU	MBM28C64	DIP28	
FUJITSU	MBM28C65	DIP28	
FUJITSU	MBM28F010	DIP32	
FUJITSU	MBM28F010	PLCC32	PA32PL32D
FUJITSU	MBM28F010	TSOP32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29DL161BD	BGA48	PA48BG48DAH
FUJITSU	MBM29DL161TD	BGA48	PA48BG48DAH
FUJITSU	MBM29DL162CB	TSOP48	PA48TS48D
FUJITSU	MBM29DL162CT	TSOP48	PA48TS48D
FUJITSU	MBM29DL163CB	TSOP48	PA48TS48D
FUJITSU	MBM29DL163CT	TSOP48	PA48TS48D
FUJITSU	MBM29DL316CB	TSOP48	PA48TS48D
FUJITSU	MBM29DL316CT	TSOP40	PA40TS40D
FUJITSU	MBM29DL316CT	TSOP40	PA40TS40D
FUJITSU	MBM29DL322BE	TSOP48	PA48TS48D
FUJITSU	MBM29DL322CB	TSOP48	PA48TS48D
FUJITSU	MBM29DL322CT	TSOP48	PA48TS48D
FUJITSU	MBM29DL322TE	TSOP48	PA48TS48D
FUJITSU	MBM29DL323CB	TSOP48	PA48TS48D
FUJITSU	MBM29DL323CT	TSOP48	PA48TS48D
FUJITSU	MBM29DL32BF	TSOP48	PA48TS48D
FUJITSU	MBM29DL32TF	TSOP48	PA48TS48D
FUJITSU	MBM29DL34BF	TSOP48	PA48TS48D
FUJITSU	MBM29DL34TF	TSOP48	PA48TS48D
FUJITSU	MBM29DL400BB	SOP44	PA44SO44D
FUJITSU	MBM29DL400BB	TSOP48	PA48TS48D
FUJITSU	MBM29DL400BC	BGA48	HA48BG48DBC
FUJITSU	MBM29DL400BC	TSOP48	PA48TS48D
FUJITSU	MBM29DL400BT	SOP44	PA44SO44D
FUJITSU	MBM29DL400BT	TSOP48	PA48TS48D
FUJITSU	MBM29DL400TC	BGA48	HA48BG48DBC
FUJITSU	MBM29DL400TC	TSOP48	PA48TS48D
FUJITSU	MBM29DL800BA	BGA48	HA48BG48DBC
FUJITSU	MBM29DL800BA	TSOP48	PA48TS48D
FUJITSU	MBM29DL800BB	SOP44	PA44SO44D
FUJITSU	MBM29DL800BB	TSOP48	PA48TS48D
FUJITSU	MBM29DL800BT	SOP44	PA44SO44D
FUJITSU	MBM29DL800BT	TSOP48	PA48TS48D
FUJITSU	MBM29DL800TA	BGA48	HA48BG48DBC
FUJITSU	MBM29DL800TA	TSOP48	PA48TS48D
FUJITSU	MBM29F002B	DIP32	
FUJITSU	MBM29F002B	PLCC32	PA32PL32D
FUJITSU	MBM29F002B	TSOP32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29F002BC	PLCC32	PA32PL32D
FUJITSU	MBM29F002BC	TSOP32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29F002SB	TSOP40	PA40TS40D
FUJITSU	MBM29F002ST	TSOP40	PA40TS40D
FUJITSU	MBM29F002T	DIP32	
FUJITSU	MBM29F002T	PLCC32	PA32PL32D
FUJITSU	MBM29F002T	TSOP32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29F002TC	PLCC32	PA32PL32D
FUJITSU	MBM29F002TC	TSOP32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29F004BC	PLCC32	PA32PL32D
FUJITSU	MBM29F004BC	TSOP32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29F004TC	PLCC32	PA32PL32D
FUJITSU	MBM29F004TC	TSOP32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29F016	TSOP48	PA48TS48D
FUJITSU	MBM29F016A	TSOP48	PA48TS48D
FUJITSU	MBM29F017A	TSOP48	PA48TS48D
FUJITSU	MBM29F033C	TSOP40	PA40TS40D
FUJITSU	MBM29F040	DIP32	

FUJITSU	MBM29F040A	PLCC32	PA32PL32D
FUJITSU	MBM29F040A	TSOP32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29F040B	DIP32	
FUJITSU	MBM29F040C	DIP32	
FUJITSU	MBM29F040C	PLCC32	PA32PL32D
FUJITSU	MBM29F040C	TSOP32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29F080	SOP44	PA44SO44D
FUJITSU	MBM29F080	TSOP40	PA40TS40D
FUJITSU	MBM29F080	TSOP48	PA48TS48D
FUJITSU	MBM29F080A	SOP44	PA44SO44D
FUJITSU	MBM29F080A	TSOP40	PA40TS40D
FUJITSU	MBM29F080A	TSOP48	PA48TS48D
FUJITSU	MBM29F160BE	TSOP48	PA48TS48D
FUJITSU	MBM29F160TE	TSOP48	PA48TS48D
FUJITSU	MBM29F200BA	SOP44	PA44SO44D
FUJITSU	MBM29F200BA	TSOP48	PA48TS48D
FUJITSU	MBM29F200BB	SOP44	PA44SO44D
FUJITSU	MBM29F200BB	TSOP48	PA48TS48D
FUJITSU	MBM29F200BC	SOP44	PA44SO44D
FUJITSU	MBM29F200BC	TSOP48	PA48TS48D
FUJITSU	MBM29F200BT	SOP44	PA44SO44D
FUJITSU	MBM29F200BT	TSOP48	PA48TS48D
FUJITSU	MBM29F200TA	SOP44	PA44SO44D
FUJITSU	MBM29F200TA	TSOP48	PA48TS48D
FUJITSU	MBM29F200TC	SOP44	PA44SO44D
FUJITSU	MBM29F200TC	TSOP48	PA48TS48D
FUJITSU	MBM29F400BA	SOP44	PA44SO44D
FUJITSU	MBM29F400BA	TSOP48	PA48TS48D
FUJITSU	MBM29F400BB	SOP44	PA44SO44D
FUJITSU	MBM29F400BB	TSOP48	PA48TS48D
FUJITSU	MBM29F400BC	SOP44	PA44SO44D
FUJITSU	MBM29F400BC	TSOP48	PA48TS48D
FUJITSU	MBM29F400BT	SOP44	PA44SO44D
FUJITSU	MBM29F400BT	TSOP48	PA48TS48D
FUJITSU	MBM29F400TA	SOP44	PA44SO44D
FUJITSU	MBM29F400TA	TSOP48	PA48TS48D
FUJITSU	MBM29F400TC	SOP44	PA44SO44D
FUJITSU	MBM29F400TC	TSOP48	PA48TS48D
FUJITSU	MBM29F800B	TSOP48	PA48TS48D
FUJITSU	MBM29F800BA	SOP44	PA44SO44D
FUJITSU	MBM29F800BA	TSOP48	PA48TS48D
FUJITSU	MBM29F800T	TSOP48	PA48TS48D
FUJITSU	MBM29F800TA	SOP44	PA44SO44D
FUJITSU	MBM29F800TA	TSOP48	PA48TS48D
FUJITSU	MBM29LV001BC	PLCC32	PA32PL32D
FUJITSU	MBM29LV001BC	TSOP32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29LV001TC	PLCC32	PA32PL32D
FUJITSU	MBM29LV001TC	TSOP32	PA32TS20/PA32TS32D-20
FUJITSU	MBM29LV002B	TSOP40	PA40TS40D
FUJITSU	MBM29LV002BC	TSOP40	PA40TS40D
FUJITSU	MBM29LV002T	TSOP40	PA40TS40D
FUJITSU	MBM29LV002TC	TSOP40	PA40TS40D
FUJITSU	MBM29LV004B	TSOP40	PA40TS40D
FUJITSU	MBM29LV004BC	TSOP40	PA40TS40D
FUJITSU	MBM29LV004T	TSOP40	PA40TS40D
FUJITSU	MBM29LV004TC	TSOP40	PA40TS40D
FUJITSU	MBM29LV008B	TSOP40	PA40TS40D
FUJITSU	MBM29LV008BA	TSOP40	PA40TS40D
FUJITSU	MBM29LV008BB	TSOP40	PA40TS40D
FUJITSU	MBM29LV008BT	TSOP40	PA40TS40D
FUJITSU	MBM29LV008T	TSOP40	PA40TS40D
FUJITSU	MBM29LV008TA	TSOP40	PA40TS40D
FUJITSU	MBM29LV080	TSOP40	PA40TS40D
FUJITSU	MBM29LV080A	TSOP40	PA40TS40D
FUJITSU	MBM29LV160B	TSOP48	PA48TS48D
FUJITSU	MBM29LV160BB	SOP44	PA44SO44D
FUJITSU	MBM29LV160BB	TSOP48	PA48TS48D
FUJITSU	MBM29LV160BE	BGA48	PA48BG48DAG
FUJITSU	MBM29LV160BE	TSOP48	PA48TS48D
FUJITSU	MBM29LV160BT	SOP44	PA44SO44D
FUJITSU	MBM29LV160BT	TSOP48	PA48TS48D
FUJITSU	MBM29LV160DB	SOP44	PA44SO44D
FUJITSU	MBM29LV160DB	TSOP48	PA48TS48D

FUJITSU	MBM29LV160DT	SOP44	PA44SO44D
FUJITSU	MBM29LV160DT	TSOP48	PA48TS48D
FUJITSU	MBM29LV160T	TSOP48	PA48TS48D
FUJITSU	MBM29LV160TE	BGA48	PA48BG48DAG
FUJITSU	MBM29LV160TE	TSOP48	PA48TS48D
FUJITSU	MBM29LV200BB	SOP44	PA44SO44D
FUJITSU	MBM29LV200BB	TSOP48	PA48TS48D
FUJITSU	MBM29LV200BC	SOP44	PA44SO44D
FUJITSU	MBM29LV200BC	TSOP48	PA48TS48D
FUJITSU	MBM29LV200BT	SOP44	PA44SO44D
FUJITSU	MBM29LV200BT	TSOP48	PA48TS48D
FUJITSU	MBM29LV200TC	SOP44	PA44SO44D
FUJITSU	MBM29LV200TC	TSOP48	PA48TS48D
FUJITSU	MBM29LV320BE	TSOP48	PA48TS48D
FUJITSU	MBM29LV320TE	TSOP48	PA48TS48D
FUJITSU	MBM29LV400B	SOP44	PA44SO44D
FUJITSU	MBM29LV400B	TSOP48	PA48TS48D
FUJITSU	MBM29LV400BB	SOP44	PA44SO44D
FUJITSU	MBM29LV400BB	TSOP48	PA48TS48D
FUJITSU	MBM29LV400BC	BGA48	HA48BG48DBC
FUJITSU	MBM29LV400BC	SOP44	PA44SO44D
FUJITSU	MBM29LV400BC	TSOP48	PA48TS48D
FUJITSU	MBM29LV400BT	SOP44	PA44SO44D
FUJITSU	MBM29LV400BT	TSOP48	PA48TS48D
FUJITSU	MBM29LV400T	SOP44	PA44SO44D
FUJITSU	MBM29LV400T	TSOP48	PA48TS48D
FUJITSU	MBM29LV400TC	BGA48	HA48BG48DBC
FUJITSU	MBM29LV400TC	SOP44	PA44SO44D
FUJITSU	MBM29LV400TC	TSOP48	PA48TS48D
FUJITSU	MBM29LV650UE	TSOP48	PA48TS48D
FUJITSU	MBM29LV651UE	TSOP48	PA48TS48D
FUJITSU	MBM29LV652UE	BGA63	HA63BG48DAB
FUJITSU	MBM29LV800BA	BGA48	HA48BG48DBC
FUJITSU	MBM29LV800BA	SOP44	PA44SO44D
FUJITSU	MBM29LV800BA	TSOP48	PA48TS48D
FUJITSU	MBM29LV800BB	SOP44	PA44SO44D
FUJITSU	MBM29LV800BB	TSOP48	PA48TS48D
FUJITSU	MBM29LV800BE	TSOP48	PA48TS48D
FUJITSU	MBM29LV800BT	SOP44	PA44SO44D
FUJITSU	MBM29LV800BT	TSOP48	PA48TS48D
FUJITSU	MBM29LV800TA	BGA48	HA48BG48DBC
FUJITSU	MBM29LV800TA	SOP44	PA44SO44D
FUJITSU	MBM29LV800TA	TSOP48	PA48TS48D
FUJITSU	MBM29LV800TE	TSOP48	PA48TS48D
FUJITSU	MBM29PL160BD	SOP44	PA44SO44D
FUJITSU	MBM29PL160CB	SOP44	PA44SO44D
FUJITSU	MBM29PL160CB	TSOP48	PA48TS48D
FUJITSU	MBM29PL160CT	SOP44	PA44SO44D
FUJITSU	MBM29PL160CT	TSOP48	PA48TS48D
FUJITSU	MBM29PL160TD	TSOP48	PA48TS48D
FUJITSU	MBM29PL32BM	TSOP48	PA48TS48D
FUJITSU	MBM29PL32TM	TSOP48	PA48TS48D
FUJITSU	MBM29SL160CB	TSOP48	PA48TS48D
FUJITSU	MBM29SL160CT	TSOP48	PA48TS48D
FUJITSU	MBM29SL800BD	BGA48	HA48BG48DBC
FUJITSU	MBM29SL800BD	TSOP48	PA48TS48D
FUJITSU	MBM29SL800BE	TSOP48	PA48TS48D
FUJITSU	MBM29SL800CB	TSOP48	PA48TS48D
FUJITSU	MBM29SL800CT	TSOP48	PA48TS48D
FUJITSU	MBM29SL800TD	BGA48	HA48BG48DBC
FUJITSU	MBM29SL800TD	TSOP48	PA48TS48D
FUJITSU	MBM29SL800TE	TSOP48	PA48TS48D
FUJITSU	MSP55LV128	SOP44	PA44SO44D
FUJITSU	MSP55LV256	SOP44	PA44SO44D
GENCORE	GC87C520A0	DIP40	
GENCORE	GC87C520A0	PLCC44	PA44-48U
GENCORE	GC87C520A0	VQFP44	PA44VQ44D
GENERAL INSTRUMENT		DIP28	
GENERAL INSTRUMENT	27C128	DIP28	
GENERAL INSTRUMENT	27C128	PLCC32	PA32PL28D-YA
GENERAL INSTRUMENT	27C256	DIP28	
GENERAL INSTRUMENT	27C256	PLCC32	PA32PL28D-YA
GENERAL INSTRUMENT	27C512	DIP28	

GENERAL INSTRUMENT	27C512	PLCC32	PA32PL28D-YA
GENERAL INSTRUMENT	27C64	DIP28	
GENERAL INSTRUMENT	27HC64	DIP28	
GENERAL INSTRUMENT	27HC64L	PLCC32	PA32PL28D-YA
GENERAL INSTRUMENT	28C04	DIP24	
GENERAL INSTRUMENT	28C04F	DIP24	
GENERAL INSTRUMENT	28C16	DIP24	
GENERAL INSTRUMENT	28C17	DIP28	
GENERAL INSTRUMENT	28C17F	DIP28	
GENERAL INSTRUMENT	28C64	DIP28	
GENERAL INSTRUMENT	28C64A	DIP28	
GENERAL INSTRUMENT	28C64AX	DIP28	
GENERIC ALGORITHM	27128<21V>	DIP28	
GENERIC ALGORITHM	27128A<12.5V>	DIP28	
GENERIC ALGORITHM	2716<25V>	DIP24	
GENERIC ALGORITHM	27256<12.5V>	DIP28	
GENERIC ALGORITHM	2732<25V>	DIP24	
GENERIC ALGORITHM	2732A<21V>	DIP24	
GENERIC ALGORITHM	2732B<12.5V>	DIP24	
GENERIC ALGORITHM	27512<12.5V>	DIP28	
GENERIC ALGORITHM	27512<12.5V>	PLCC32	PA32PL28D-YA
GENERIC ALGORITHM	2764<21V>	DIP28	
GENERIC ALGORITHM	2764A<12.5V>	DIP28	
GENERIC ALGORITHM	27C128<12.5V>	DIP28	
GENERIC ALGORITHM	27C128<21V>	DIP28	
GENERIC ALGORITHM	27C16<25V>	DIP24	
GENERIC ALGORITHM	27C256<12.5V>	DIP28	
GENERIC ALGORITHM	27C32<25V>	DIP24	
GENERIC ALGORITHM	27C512<12.5V>	DIP28	
GENERIC ALGORITHM	27C512<12.5V>	PLCC32	PA32PL28D-YA
GENERIC ALGORITHM	27C64<12.5V>	DIP28	
GENERIC ALGORITHM	27C64<21V>	DIP28	
GENERIC RAM	41000(1M*1)	DIP18	
GENERIC RAM	41256(256K*1)	DIP16	
GENERIC RAM	41416(16K*4)	DIP18	
GENERIC RAM	414256(256K*4)	DIP20	
GENERIC RAM	41464(64K*4)	DIP18	
GENERIC RAM	4164(64K*1)	DIP16	
GENERIC RAM	44000(4M*1)	DIP20	
GENERIC RAM	6116(3.3V)	DIP24	
GENERIC RAM	6116(5V)	DIP24	
GENERIC RAM	61256(3.3V)	DIP28	
GENERIC RAM	61256(5V)	DIP28	
GENERIC RAM	6164(3.3V)	DIP28	
GENERIC RAM	6164(5V)	DIP28	
GENERIC RAM	621000(3.3V)	DIP32	
GENERIC RAM	621000(5V)	DIP32	
GENERIC RAM	624000(3.3V)	DIP32	
GENERIC RAM	624000(5V)	DIP32	
GigaDevice	GD25B127D	DIP8	
GigaDevice	GD25B127D	SOP16	PA28SO28D-EO-300
GigaDevice	GD25B127D	SOP8	PA20SO20D-EO-210
GigaDevice	GD25B127D	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25B127D	WSON8	PA8SON8D(6x5)
GigaDevice	GD25B127D	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25B127D (Dual)	DIP8	
GigaDevice	GD25B127D (Dual)	SOP16	PA28SO28D-EO-300
GigaDevice	GD25B127D (Dual)	SOP8	PA20SO20D-EO-210
GigaDevice	GD25B127D (Dual)	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25B127D (Dual)	WSON8	PA8SON8D(6x5)
GigaDevice	GD25B127D (Dual)	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25B127D (Quad)	DIP8	
GigaDevice	GD25B127D (Quad)	SOP16	PA28SO28D-EO-300
GigaDevice	GD25B127D (Quad)	SOP8	PA20SO20D-EO-210
GigaDevice	GD25B127D (Quad)	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25B127D (Quad)	WSON8	PA8SON8D(6x5)
GigaDevice	GD25B127D (Quad)	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25B128C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25B128C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25B128E	SOP16	PA28SO28D-EO-300
GigaDevice	GD25B128E	SOP8	PA20SO20D-EO-210
GigaDevice	GD25B128E	TFBGA24	PA24BG24D(6x8mm)5x5
GigaDevice	GD25B128E	WSON8	PA8SON8D(6x5)

GigaDevice	GD25B128E	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25B16C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25B16C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25B256D	SOP16	PA28SO28D-EO-300
GigaDevice	GD25B256D	TFBGA24	PA24BG24D(6x8mm)5x5
GigaDevice	GD25B256D	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25B32C	DIP8	
GigaDevice	GD25B32C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25B32C	USON8	PA8SON8D(4x3)
GigaDevice	GD25B32C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25B64C	DIP8	
GigaDevice	GD25B64C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25B64C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25B64C	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25B64C (Dual)	DIP8	
GigaDevice	GD25B64C (Dual)	SOP8	PA20SO20D-EO-210
GigaDevice	GD25B64C (Dual)	WSON8	PA8SON8D(6x5)
GigaDevice	GD25B64C (Dual)	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25B64C (Quad)	DIP8	
GigaDevice	GD25B64C (Quad)	SOP8	PA20SO20D-EO-210
GigaDevice	GD25B64C (Quad)	WSON8	PA8SON8D(6x5)
GigaDevice	GD25B64C (Quad)	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25D05B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25D05B	TSSOP8	PA8TSS8D
GigaDevice	GD25D05B	USON8	PA8SON8D(2x3)
GigaDevice	GD25D05C	DIP8	
GigaDevice	GD25D05C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25D05C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25D05C	TSSOP8	PA8TSS8D
GigaDevice	GD25D05C	USON8	PA8SON8D(2x3)
GigaDevice	GD25D10B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25D10B	TSSOP8	PA8TSS8D
GigaDevice	GD25D10B	USON8	PA8SON8D(2x3)
GigaDevice	GD25D10C	DIP8	
GigaDevice	GD25D10C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25D10C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25D10C	TSSOP8	PA8TSS8D
GigaDevice	GD25D10C	USON8	PA8SON8D(2x3)
GigaDevice	GD25D20C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25D20C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25D20C	TSSOP8	PA8TSS8D
GigaDevice	GD25D20C	USON8	PA8SON8D(2x3)
GigaDevice	GD25D40C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25D40C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25D40C	TSSOP8	PA8TSS8D
GigaDevice	GD25D40C	USON8	PA8SON8D(2x3)
GigaDevice	GD25D80C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25D80C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25D80C	TSSOP8	PA8TSS8D
GigaDevice	GD25D80C	USON8	PA8SON8D(2x3)
GigaDevice	GD25LB128D	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LB128D	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LB128D	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LB64C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LB64C	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LB64C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LD20C	DIP8	
GigaDevice	GD25LD20C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25LD20C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LD20C	TSSOP8	PA8TSS8D
GigaDevice	GD25LD20C	USON8	PA8SON8D(2x3)
GigaDevice	GD25LD20C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LD40C	DIP8	
GigaDevice	GD25LD40C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25LD40C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LD40C	TSSOP8	PA8TSS8D
GigaDevice	GD25LD40C	USON8	PA8SON8D(2x3)
GigaDevice	GD25LD40C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ05B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25LQ05B	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ05B	TSSOP8	PA8TSS8D
GigaDevice	GD25LQ05B	USON8	PA8SON8D(2x3)
GigaDevice	GD25LQ05B	USON8	PA8SON8D(4x3)



GigaDevice	GD25LQ05B	VSOP8	PA16SO16D-EO-150
GigaDevice	GD25LQ05B	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ05B	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ05C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25LQ05C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ05C	TSSOP8	PA8TSS8D
GigaDevice	GD25LQ05C	USON8	PA8SON8D(2x3)
GigaDevice	GD25LQ05C	USON8	PA8SON8D(4x3)
GigaDevice	GD25LQ05C	VSOP8	PA16SO16D-EO-150
GigaDevice	GD25LQ05C	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ05C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ10B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25LQ10B	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ10B	TSSOP8	PA8TSS8D
GigaDevice	GD25LQ10B	USON8	PA8SON8D(2x3)
GigaDevice	GD25LQ10B	USON8	PA8SON8D(4x3)
GigaDevice	GD25LQ10B	VSOP8	PA16SO16D-EO-150
GigaDevice	GD25LQ10B	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ10B	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ10C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25LQ10C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ10C	TSSOP8	PA8TSS8D
GigaDevice	GD25LQ10C	USON8	PA8SON8D(2x3)
GigaDevice	GD25LQ10C	USON8	PA8SON8D(4x3)
GigaDevice	GD25LQ10C	VSOP8	PA16SO16D-EO-150
GigaDevice	GD25LQ10C	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ10C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ128C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ128C	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ128C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ128C	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25LQ128D	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ128D	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ128D	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ128D	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25LQ16	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25LQ16	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ16	USON8	PA8SON8D(4x3)
GigaDevice	GD25LQ16	VSOP8	PA16SO16D-EO-150
GigaDevice	GD25LQ16	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ16	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ16C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25LQ16C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ16C	USON8	PA8SON8D(4x3)
GigaDevice	GD25LQ16C	VSOP8	PA16SO16D-EO-150
GigaDevice	GD25LQ16C	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ16C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ20B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25LQ20B	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ20B	TSSOP8	PA8TSS8D
GigaDevice	GD25LQ20B	USON8	PA8SON8D(2x3)
GigaDevice	GD25LQ20B	USON8	PA8SON8D(4x3)
GigaDevice	GD25LQ20B	VSOP8	PA16SO16D-EO-150
GigaDevice	GD25LQ20B	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ20B	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ20C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25LQ20C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ20C	TSSOP8	PA8TSS8D
GigaDevice	GD25LQ20C	USON8	PA8SON8D(2x3)
GigaDevice	GD25LQ20C	USON8	PA8SON8D(4x3)
GigaDevice	GD25LQ20C	VSOP8	PA16SO16D-EO-150
GigaDevice	GD25LQ20C	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ20C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ256C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ256C	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25LQ256D	SOP16	PA28SO28D-EO-300
GigaDevice	GD25LQ256D	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ256D	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25LQ256D	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ32C	USON8	PA8SON8D(2x3)
GigaDevice	GD25LQ32C	USON8	PA8SON8D(4x3)
GigaDevice	GD25LQ32C	VSOP8	PA16SO16D-EO-150
GigaDevice	GD25LQ32C	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ32C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ32D	SOP8	PA20SO20D-EO-210

GigaDevice	GD25LQ32D	USON8	PA8SON8D(4x3)
GigaDevice	GD25LQ32D	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ32D	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ40	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25LQ40	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ40	TSSOP8	PA8TSS8D
GigaDevice	GD25LQ40	USON8	PA8SON8D(4x3)
GigaDevice	GD25LQ40	VSOP8	PA16SO16D-EO-150
GigaDevice	GD25LQ40	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ40	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ40B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25LQ40B	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ40B	TSSOP8	PA8TSS8D
GigaDevice	GD25LQ40B	USON8	PA8SON8D(2x3)
GigaDevice	GD25LQ40B	USON8	PA8SON8D(4x3)
GigaDevice	GD25LQ40B	VSOP8	PA16SO16D-EO-150
GigaDevice	GD25LQ40B	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ40B	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ40C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25LQ40C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ40C	TSSOP8	PA8TSS8D
GigaDevice	GD25LQ40C	USON8	PA8SON8D(2x3)
GigaDevice	GD25LQ40C	USON8	PA8SON8D(4x3)
GigaDevice	GD25LQ40C	VSOP8	PA16SO16D-EO-150
GigaDevice	GD25LQ40C	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ40C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ64C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ64C	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ64C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ80	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25LQ80	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ80	USON8	PA8SON8D(4x3)
GigaDevice	GD25LQ80	VSOP8	PA16SO16D-EO-150
GigaDevice	GD25LQ80	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ80	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ80B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25LQ80B	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ80B	TSSOP8	PA8TSS8D
GigaDevice	GD25LQ80B	USON8	PA8SON8D(2x3)
GigaDevice	GD25LQ80B	USON8	PA8SON8D(4x3)
GigaDevice	GD25LQ80B	VSOP8	PA16SO16D-EO-150
GigaDevice	GD25LQ80B	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ80B	WSON8	PA8SON8D(6x5)
GigaDevice	GD25LQ80C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25LQ80C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ80C	USON8	PA8SON8D(2x3)
GigaDevice	GD25LQ80C	USON8	PA8SON8D(4x3)
GigaDevice	GD25LQ80C	VSOP8	PA16SO16D-EO-150
GigaDevice	GD25LQ80C	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25LQ80C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25Q10	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q10	USON8	PA8SON8D(2x3)
GigaDevice	GD25Q10	WSON8	PA8SON8D(6x5)
GigaDevice	GD25Q127C	DIP8	
GigaDevice	GD25Q127C	SOP16	PA28SO28D-EO-300
GigaDevice	GD25Q127C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q127C	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25Q127C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25Q127C	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25Q128B	SOP16	PA28SO28D-EO-300
GigaDevice	GD25Q128B	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25Q128C	DIP8	
GigaDevice	GD25Q128C	SOP16	PA28SO28D-EO-300
GigaDevice	GD25Q128C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q128C	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25Q128C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25Q128C	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25Q128E	SOP16	PA28SO28D-EO-300
GigaDevice	GD25Q128E	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q128E	TFBGA24	PA24BG24D(6x8mm)5x5
GigaDevice	GD25Q128E	WSON8	PA8SON8D(6x5)
GigaDevice	GD25Q128E	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25Q16	DIP8	

GigaDevice	GD25Q16	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q16B	DIP8	
GigaDevice	GD25Q16B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q16B	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q16B	WSON8	PA8SON8D(6x5)
GigaDevice	GD25Q16C	DIP8	
GigaDevice	GD25Q16C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q16C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q16C	USON8	PA8SON8D(2x3)
GigaDevice	GD25Q16C	USON8	PA8SON8D(4x3)
GigaDevice	GD25Q16C	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25Q16C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25Q16E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q16E	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q16E	USON8	PA8SON8D(2x3)
GigaDevice	GD25Q16E	USON8	PA8SON8D(4x3)
GigaDevice	GD25Q16E	WSON8	PA8SON8D(6x5)
GigaDevice	GD25Q20	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q20	USON8	PA8SON8D(2x3)
GigaDevice	GD25Q20	WSON8	PA8SON8D(6x5)
GigaDevice	GD25Q20B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q20B	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q20B	TSSOP8	PA8TSS8D
GigaDevice	GD25Q20B	USON8	PA8SON8D(2x3)
GigaDevice	GD25Q21B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q21B	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q21B	TSSOP8	PA8TSS8D
GigaDevice	GD25Q21B	USON8	PA8SON8D(2x3)
GigaDevice	GD25Q256C	SOP16	PA28SO28D-EO-300
GigaDevice	GD25Q256C	TFBGA24	PA24BG24D(6x8mm)5x5
GigaDevice	GD25Q256C	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25Q256D	SOP16	PA28SO28D-EO-300
GigaDevice	GD25Q256D	TFBGA24	PA24BG24D(6x8mm)5x5
GigaDevice	GD25Q256D	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25Q32	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q32	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q32B	DIP8	
GigaDevice	GD25Q32B	SOP16	PA28SO28D-EO-300
GigaDevice	GD25Q32B	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q32B	TFBGA24	PA24BG24D(6x8mm)5x5
GigaDevice	GD25Q32B	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25Q32B	WSON8	PA8SON8D(6x5)
GigaDevice	GD25Q32C	DIP8	
GigaDevice	GD25Q32C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q32C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q32C	TFBGA24	PA24BG24D(6x8mm)5x5
GigaDevice	GD25Q32C	USON8	PA8SON8D(4x3)
GigaDevice	GD25Q32C	VSOP8	PA20SO20D-EO-210
GigaDevice	GD25Q32C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25Q32E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q32E	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q32E	TFBGA24	PA24BG24D(6x8mm)5x5
GigaDevice	GD25Q32E	USON8	PA8SON8D(2x3)
GigaDevice	GD25Q32E	USON8	PA8SON8D(4x3)
GigaDevice	GD25Q32E	WSON8	PA8SON8D(6x5)
GigaDevice	GD25Q40	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q40	USON8	PA8SON8D(2x3)
GigaDevice	GD25Q40	WSON8	PA8SON8D(6x5)
GigaDevice	GD25Q40B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q40B	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q40B	TSSOP8	PA8TSS8D
GigaDevice	GD25Q40B	USON8	PA8SON8D(2x3)
GigaDevice	GD25Q40C	DIP8	
GigaDevice	GD25Q40C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q40C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q40C	TSSOP8	PA8TSS8D
GigaDevice	GD25Q40C	USON8	PA8SON8D(2x3)
GigaDevice	GD25Q40C	USON8	PA8SON8D(4x3)
GigaDevice	GD25Q41B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q41B	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q41B	TSSOP8	PA8TSS8D
GigaDevice	GD25Q41B	USON8	PA8SON8D(2x3)
GigaDevice	GD25Q41B	WSON8	PA8SON8D(6x5)

GigaDevice	GD25Q512	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q512	USON8	PA8SON8D(2x3)
GigaDevice	GD25Q512	WSON8	PA8SON8D(6x5)
GigaDevice	GD25Q512MC	SOP16	PA28SO28D-EO-300
GigaDevice	GD25Q512MC	TFBGA24	PA24BG24D(6x8mm)5x5
GigaDevice	GD25Q512MC	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25Q64B	DIP8	
GigaDevice	GD25Q64B	SOP16	PA28SO28D-EO-300
GigaDevice	GD25Q64B	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q64B	WSON8	PA8SON8D(6x5)
GigaDevice	GD25Q64C	DIP8	
GigaDevice	GD25Q64C	SOP16	PA28SO28D-EO-300
GigaDevice	GD25Q64C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q64C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25Q64C	WSON8	PA8SON8DA(8x6)
GigaDevice	GD25Q64E	SOP16	PA28SO28D-EO-300
GigaDevice	GD25Q64E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q64E	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q64E	TFBGA24	PA24BG24D(6x8mm)5x5
GigaDevice	GD25Q64E	USON8	PA8SON8D(4x3)
GigaDevice	GD25Q64E	WSON8	PA8SON8D(6x5)
GigaDevice	GD25Q80	DIP8	
GigaDevice	GD25Q80	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q80	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q80B	DIP8	
GigaDevice	GD25Q80B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q80B	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q80B	USON8	PA8SON8D(2x3)
GigaDevice	GD25Q80B	VSOP8	PA16SO16D-EO-150
GigaDevice	GD25Q80C	DIP8	
GigaDevice	GD25Q80C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q80C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q80C	USON8	PA8SON8D(2x3)
GigaDevice	GD25Q80C	USON8	PA8SON8D(4x3)
GigaDevice	GD25Q80C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25Q80C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25Q80E	SOP8	PA20SO20D-EO-210
GigaDevice	GD25Q80E	USON8	PA8SON8D(2x3)
GigaDevice	GD25Q80E	USON8	PA8SON8D(4x3)
GigaDevice	GD25Q80E	WSON8	PA8SON8D(6x5)
GigaDevice	GD25VQ16C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25VQ16C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25VQ16C	TFBGA24	PA24BG24D(6x8mm)5x5
GigaDevice	GD25VQ16C	USON8	PA8SON8D(2x3)
GigaDevice	GD25VQ16C	USON8	PA8SON8D(4x3)
GigaDevice	GD25VQ16C	WSON8	PA8SON8D(6x5)
GigaDevice	GD25VQ21B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25VQ21B	SOP8	PA20SO20D-EO-210
GigaDevice	GD25VQ21B	TSSOP8	PA8TSS8D
GigaDevice	GD25VQ21B	USON8	PA8SON8D(2x3)
GigaDevice	GD25VQ21B	VSOP8	PA16SO16D-EO-150
GigaDevice	GD25VQ41B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25VQ41B	SOP8	PA20SO20D-EO-210
GigaDevice	GD25VQ41B	TSSOP8	PA8TSS8D
GigaDevice	GD25VQ41B	USON8	PA8SON8D(2x3)
GigaDevice	GD25VQ41B	VSOP8	PA16SO16D-EO-150
GigaDevice	GD25WD20C	DIP8	
GigaDevice	GD25WD20C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25WD20C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25WD20C	TSSOP8	PA8TSS8D
GigaDevice	GD25WD20C	USON8	PA8SON8D(2x3)
GigaDevice	GD25WD40C	DIP8	
GigaDevice	GD25WD40C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25WD40C	SOP8	PA20SO20D-EO-210
GigaDevice	GD25WD40C	TSSOP8	PA8TSS8D
GigaDevice	GD25WD40C	USON8	PA8SON8D(2x3)
GigaDevice	GD25WQ16E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25WQ16E	SOP8	PA20SO20D-EO-210
GigaDevice	GD25WQ16E	USON8	PA8SON8D(2x3)
GigaDevice	GD25WQ32E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25WQ32E	SOP8	PA20SO20D-EO-210
GigaDevice	GD25WQ32E	USON8	PA8SON8D(2x3)
GigaDevice	GD25WQ32E	USON8	PA8SON8D(4x3)

GigaDevice	GD25WQ64E	SOP8	PA20SQ20D-EO-210
GigaDevice	GD25WQ64E	TFBGA24	PA24BG24D(6x8mm)5x5
GigaDevice	GD25WQ64E	USON8	PA8SON8D(4x3)
GigaDevice	GD25WQ64E	WSON8	PA8SON8D(6x5)
GigaDevice	GD25WQ80E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
GigaDevice	GD25WQ80E	SOP8	PA20SQ20D-EO-210
GigaDevice	GD25WQ80E	USON8	PA8SON8D(2x3)
GOULD	PEEL153	DIP20	
GOULD	PEEL173	DIP24	
GOULD	PEEL18CV8	DIP20	
GOULD	PEEL18CV8	PLCC20	PA20LC20D[Dead Bug]
GOULD	PEEL18CV8	SOIC20	PA28SO28D-EO-300
GOULD	PEEL18CV8	TSSOP20	PA24TSS24D
GOULD	PEEL20CG10	DIP24	
GOULD	PEEL22CV10	DIP24	
GOULD	PEEL22CV10	DIP24	
GOULD	PEEL22CV10	PLCC28	PA28PL28D
GOULD	PEEL22CV10	SOIC24	PA28SO28D-EO-300
GOULD	PEEL22CV10	TSSOP24	PA24TSS24D
GOULD	PEEL22CV10A	DIP24	
GOULD	PEEL22CV10A	PLCC28	PA28PL28D
GOULD	PEEL22CV10A	SOIC24	PA28SO28D-EO-300
GOULD	PEEL22CV10A	TSSOP24	PA24TSS24D
GOULD	PEEL22CV10A+	DIP24	
GOULD	PEEL22CV10A+	PLCC28	PA28PL28D
GOULD	PEEL22CV10A+	SOIC24	PA28SO28D-EO-300
GOULD	PEEL22CV10A+	TSSOP24	PA24TSS24D
GOULD	PEEL22CV10A++	DIP24	
GOULD	PEEL22CV10A++	PLCC28	PA28PL28D
GOULD	PEEL22CV10A++	SOIC24	PA28SO28D-EO-300
GOULD	PEEL22CV10A++	TSSOP24	PA24TSS24D
GOULD	PEEL22CV10AZ+	DIP24	
GOULD	PEEL22CV10AZ+	PLCC28	PA28PL28D
GOULD	PEEL22CV10AZ+	SOIC24	PA28SO28D-EO-300
GOULD	PEEL22CV10AZ+	TSSOP24	PA24TSS24D
GOULD	PEEL22CV10AZ++	DIP24	
GOULD	PEEL22CV10AZ++	PLCC28	PA28PL28D
GOULD	PEEL22CV10AZ++	SOIC24	PA28SO28D-EO-300
GOULD	PEEL22CV10AZ++	TSSOP24	PA24TSS24D
GOULD	PEEL22CV10Z	DIP24	
GOULD	PEEL22CV10Z	PLCC28	PA28PL28D
GOULD	PEEL22CV10Z	SOIC24	PA28SO28D-EO-300
GOULD	PEEL22CV10Z	TSSOP24	PA24TSS24D
GOULD	PEEL253	DIP20	
GOULD	PEEL273	DIP24	
GOULD	PEEL273	DIP32	
GREENLIANT	GLS27SF010	PLCC32	PA32PL32D
GREENLIANT	GLS27SF010	DIP32	
GREENLIANT	GLS27SF020	PLCC32	PA32PL32D
GREENLIANT	GLS27SF020	PLCC32	PA32PL28D-YA
GREENLIANT	GLS27SF512	DIP32	
GREENLIANT	GLS29EE010	PLCC32	PA32PL32D
GREENLIANT	GLS29EE010	TSOP32	PA32TS32D
GREENLIANT	GLS29EE512	PLCC32	PA32PL32D
GREENWICH	GR12882	EDIP32	
GREENWICH	GR12883	EDIP32	
GREENWICH	GR27128	DIP28	
GREENWICH	GR27256	DIP28	
GREENWICH	GR27512	DIP28	
GREENWICH	GR2764	DIP28	
GREENWICH	GR281	EDIP24	
GREENWICH	GR3281	EDIP28	
GREENWICH	GR881	EDIP28	
HARRIS	HM-7648	DIP20	
HARRIS	HM-7649	DIP20	
HITACHI	H8/532	PLCC84	PA84PL40DD
HITACHI	H8/534	PLCC84	PA84PL40DD
HITACHI	H8/534(S)	PLCC84	PA84PL40DD
HITACHI	H8/536	PLCC84	PA84PL40DD
HITACHI	H8/536(S)	PLCC84	PA84PL40DD
HITACHI	HD6473228P(H8/322)	SDIP64	mcp AD372
HITACHI	HD6473238P(H8/323)	SDIP64	mcp AD372
HITACHI	HD6473258P(H8/325)	SDIP64	mcp AD372

HITACHI	HD64F2238	DIP40	PAH8SBGA112
HITACHI	HN27128A	DIP28	
HITACHI	HN27128AG	DIP28	
HITACHI	HN27128AP	DIP28	
HITACHI	HN27256	DIP28	
HITACHI	HN27256G	DIP28	
HITACHI	HN27256P	DIP28	
HITACHI	HN27512	DIP28	
HITACHI	HN27512G	DIP28	
HITACHI	HN27512P	DIP28	
HITACHI	HN2764	DIP28	
HITACHI	HN2764AG	DIP28	
HITACHI	HN27C101AG	DIP32	
HITACHI	HN27C101AP	DIP32	
HITACHI	HN27C101G	DIP32	
HITACHI	HN27C101G	SOP32	PA32SO32D-EO-450
HITACHI	HN27C101GP	SOP32	PA32SO32D-EO-450
HITACHI	HN27C101P	DIP32	
HITACHI	HN27C1024HG	DIP40	
HITACHI	HN27C1024HG	PLCC44	PA44-48U
HITACHI	HN27C256	DIP28	
HITACHI	HN27C256A	PLCC32	PA32PL28D-YA
HITACHI	HN27C256A	SOIC28	PA28SO28D-EO-300
HITACHI	HN27C256AG	DIP28	
HITACHI	HN27C256G	DIP28	
HITACHI	HN27C256H	PLCC32	PA32PL28D-YA
HITACHI	HN27C256H	SOIC28	PA28SO28D-EO-300
HITACHI	HN27C256HG	DIP28	
HITACHI	HN27C301G	DIP32	
HITACHI	HN27C301P	DIP32	
HITACHI	HN27C4000G	DIP40	
HITACHI	HN27C4001G	DIP32	
HITACHI	HN27C4096	DIP40	
HITACHI	HN27C4096	PLCC44	PA44-48U
HITACHI	HN27C4096AHCC	PLCC44	PA44-48U
HITACHI	HN27C4096AHG	DIP40	
HITACHI	HN27C4096G	DIP40	
HITACHI	HN27C4096G	PLCC44	PA44-48U
HITACHI	HN27C4096HCC	PLCC44	PA44-48U
HITACHI	HN27C4096HG	DIP40	
HITACHI	HN27C512AG	DIP28	
HITACHI	HN27C64	DIP28	
HITACHI	HN27C64G	DIP28	
HITACHI	HN28F101	DIP32	
HITACHI	HN28F101	PLCC32	PA32PL32D
HITACHI	HN462716	DIP24	
HITACHI	HN462716G	DIP24	
HITACHI	HN462732	DIP24	
HITACHI	HN462732G	DIP24	
HITACHI	HN48016P	DIP24	
HITACHI	HN4827128G	DIP28	
HITACHI	HN4827128P	DIP28	
HITACHI	HN482732A	DIP24	
HITACHI	HN482732AG	DIP24	
HITACHI	HN482764G	DIP28	
HITACHI	HN482764P	DIP28	
HITACHI	HN58064	DIP28	
HITACHI	HN58C1001	DIP32	
HITACHI	HN58C1001	SOP32	PA32PS-32D-450
HITACHI	HN58C256P(Page)	DIP28	
HITACHI	HN58C256P(Single)	DIP28	
HITACHI	HN58C65P	DIP28	
HOLTEK	HT27C010	DIP32	
HOLTEK	HT27C010	PLCC32	PA32PL32D
HOLTEK	HT27C010	SOP32	PA32SO32D-EO-450
HOLTEK	HT27C020	DIP32	
HOLTEK	HT27C020	PLCC32	PA32PL32D
HOLTEK	HT27C020	SOP32	PA32SO32D-EO-450
HOLTEK	HT27C040	DIP32	
HOLTEK	HT27C040	PLCC32	PA32PL32D
HOLTEK	HT27C040	SOP32	PA32SO32D-EO-450
HOLTEK	HT27C512	DIP28	
HOLTEK	HT27C512	PLCC32	PA32PL28D-YA

HOLTEK	HT27LC010	DIP32	
HOLTEK	HT27LC010	PLCC32	PA32PL32D
HOLTEK	HT27LC010	SOP32	PA32SO32D-EO-450
HOLTEK	HT27LC010	TSOP32	PA32TS20/PA32TS32D-20
HOLTEK	HT27LC020	DIP32	
HOLTEK	HT27LC020	PLCC32	PA32PL32D
HOLTEK	HT27LC020	SOP32	PA32SO32D-EO-450
HOLTEK	HT27LC020	TSOP32	PA32TS20/PA32TS32D-20
HOLTEK	HT27LC040	DIP32	
HOLTEK	HT27LC040	PLCC32	PA32PL32D
HOLTEK	HT27LC040	SOP32	PA32SO32D-EO-450
HOLTEK	HT27LC040	TSOP32	PA32TS20/PA32TS32D-20
HOLTEK	HT27LC512	DIP28	
HOLTEK	HT27LC512	PLCC32	PA32PL28D-YA
HOLTEK	HT93C46	DIP8	
HOLTEK	HT93C46	SOIC8	PA16SO16D-EO-150
HOLTEK	HT93C56	DIP8	
HOLTEK	HT93C56	SOIC8	PA16SO16D-EO-150
HOLTEK	HT93C66	DIP8	
HOLTEK	HT93C66	SOIC8	PA16SO16D-EO-150
HOLTEK	HT93LC46	DIP8	
HOLTEK	HT93LC46	SOIC8	PA16SO16D-EO-150
HOLTEK	HT93LC46	TSSOP8	PA8TSS-OT
HOLTEK	HT93LC56	DIP8	
HOLTEK	HT93LC56	SOIC8	PA16SO16D-EO-150
HOLTEK	HT93LC66	DIP8	
HOLTEK	HT93LC66	SOIC8	PA16SO16D-EO-150
HOLTEK	HT93LC66	TSSOP8	PA8TSS-OT
HOLTEK	HT93LC86	DIP8	
HOLTEK	HT93LC86	SOIC8	PA16SO16D-EO-150
HOLTEK	HT93LC86	TSSOP8	PA8TSS-OT
HYNIX	GMS34004TK	DIP16	
HYNIX	GMS34004TM	DIP16	
HYNIX	GMS34112TK	DIP20	
HYNIX	GMS34112TM	DIP20	
HYNIX	GMS34140TK	DIP24	
HYNIX	GMS34140TM	DIP24	
HYNIX	GMS77C1000	DIP18	
HYNIX	GMS77C1001	DIP18	
HYNIX	GMS81004T	DIP20	
HYNIX	GMS81004T	DIP24	
HYNIX	GMS81004T	DIP28	
HYNIX	GMS81008T	DIP20	
HYNIX	GMS81008T	DIP24	
HYNIX	GMS81008T	DIP28	
HYNIX	GMS81016T	DIP20	
HYNIX	GMS81016T	DIP24	
HYNIX	GMS81016T	DIP28	
HYNIX	GMS81024T	DIP20	
HYNIX	GMS81024T	DIP24	
HYNIX	GMS81024T	DIP28	
HYNIX	GMS81032T	DIP20	
HYNIX	GMS81032T	DIP24	
HYNIX	GMS81032T	DIP28	
HYNIX	GMS87C1102	DIP16	
HYNIX	GMS87C1202	DIP20	
HYNIX	GMS97C1051	DIP20	
HYNIX	GMS97C2051	DIP20	
HYNIX	GMS97C51	DIP40	
HYNIX	GMS97C51	PLCC44	PA44-48U
HYNIX	GMS97C52	DIP40	
HYNIX	GMS97C52	PLCC44	PA44-48U
HYNIX	GMS97C54	DIP40	
HYNIX	GMS97C54	PLCC44	PA44-48U
HYNIX	GMS97C54	QFP44	PA44QF44D
HYNIX	GMS97C56	DIP40	
HYNIX	GMS97C56	PLCC44	PA44-48U
HYNIX	GMS97C58	DIP40	
HYNIX	GMS97C58	PLCC44	PA44-48U
HYNIX	GMS97L51	DIP40	
HYNIX	GMS97L51	PLCC44	PA44-48U
HYNIX	GMS97L52	DIP40	
HYNIX	GMS97L52	PLCC44	PA44-48U

HYNIX	GMS99C58	DIP40	
HYNIX	GMS99C58	PLCC44	PA44-48U
HYNIX	HMS77C2000	DIP8	
HYNIX	HMS77C2001	DIP8	
HYNIX	HMS97C8032	QFP80	PA97C8032
HYNIX	HMS99C51S	DIP40	
HYNIX	HMS99C52	DIP40	
HYNIX	HMS99C52S	DIP40	
HYNIX	HMS99C54S	DIP40	
HYNIX	HMS99C56S	DIP40	
HYNIX	HMS99C58S	DIP40	
HYNIX	HY2764	DIP28	
HYNIX	HY27C64A	DIP28	
HYNIX	HY27UF081G2M	TSOP48	PA48TS48D
HYNIX	HY27UF082G2M	TSOP48	PA48TS48D
HYNIX	HY27UF084G2M	TSOP48	PA48TS48D
HYNIX	HY27US08121A	BGA63	HA63BG48DN
HYNIX	HY27US08121A	TSOP48	PA48TS48D
HYNIX	HY27US08281A	TSOP48	PA48TS48D
HYNIX	HY27US08561A	BGA63	HA63BG48DN
HYNIX	HY27US08561A	TSOP48	PA48TS48D
HYNIX	HY29DL162BT	TSOP48	PA48TS48D
HYNIX	HY29DL162TT	TSOP48	PA48TS48D
HYNIX	HY29DL163BT	TSOP48	PA48TS48D
HYNIX	HY29DL163TT	TSOP48	PA48TS48D
HYNIX	HY29DS162BT	TSOP48	PA48TS48D
HYNIX	HY29DS162TT	TSOP48	PA48TS48D
HYNIX	HY29DS163BT	TSOP48	PA48TS48D
HYNIX	HY29DS163TT	TSOP48	PA48TS48D
HYNIX	HY29F002B	DIP32	
HYNIX	HY29F002B	PLCC32	PA32PL32D
HYNIX	HY29F002B	TSOP32	PA32TS20/PA32TS32D-20
HYNIX	HY29F002CT	PLCC32	PA32PL32D
HYNIX	HY29F002T	DIP32	
HYNIX	HY29F002T	PLCC32	PA32PL32D
HYNIX	HY29F002T	TSOP32	PA32TS20/PA32TS32D-20
HYNIX	HY29F002TT	TSOP32	PA32TS20/PA32TS32D-20
HYNIX	HY29F040	DIP32	
HYNIX	HY29F040	PLCC32	PA32PL32D
HYNIX	HY29F040	TSOP32	PA32TS20/PA32TS32D-20
HYNIX	HY29F040A	DIP32	
HYNIX	HY29F040A	PLCC32	PA32PL32D
HYNIX	HY29F040A	TSOP32	PA32TS20/PA32TS32D-20
HYNIX	HY29F080T	SOP44	PA44SO44D
HYNIX	HY29F080T	TSOP40	PA40TS40D
HYNIX	HY29F400BG	SOP44	PA44SO44D
HYNIX	HY29F400BT	TSOP48	PA48TS48D
HYNIX	HY29F400TG	SOP44	PA44SO44D
HYNIX	HY29F400TT	TSOP48	PA48TS48D
HYNIX	HY29F800BG	SOP44	PA44SO44D
HYNIX	HY29F800BT	TSOP48	PA48TS48D
HYNIX	HY29F800TG	SOP44	PA44SO44D
HYNIX	HY29F800TT	TSOP48	PA48TS48D
HYNIX	HY29LV160BT	TSOP48	PA48TS48D
HYNIX	HY29LV160TT	TSOP48	PA48TS48D
HYNIX	HY29LV320BT	TSOP48	PA48TS48D
HYNIX	HY29LV320TT	TSOP48	PA48TS48D
HYNIX	HY29LV400BT	SOP44	PA44SO44D
HYNIX	HY29LV400BT	TSOP48	PA48TS48D
HYNIX	HY29LV400TT	SOP44	PA44SO44D
HYNIX	HY29LV400TT	TSOP48	PA48TS48D
HYNIX	HY29LV800BT	SOP44	PA44SO44D
HYNIX	HY29LV800BT	TSOP48	PA48TS48D
HYNIX	HY29LV800TT	SOP44	PA44SO44D
HYNIX	HY29LV800TT	TSOP48	PA48TS48D
HYNIX	HY91U3204AD	BGA72	PA72BGA48D-B11
HYNIX	HY91U3208AD	BGA72	PA72BGA48D-B11
HYNIX	HY93C46	DIP8	
HYNIX	HY96U1604M	BGA69	PA69BGA48DH
HYNIX	HYG0UEG0MF2	BGA107	HA107BGA48DH
HYNIX	PEEL18CV8	DIP20	
HYNIX	PEEL18CV8	PLCC20	PA20LC20D[Dead Bug]
HYNIX	PEEL18CV8	SOIC20	PA28SO28D-EO-300



HYNIX	PEEL18CV8	TSSOP20	PA24TSS24D
ICE	ICE25P05	DIP8	
ICE	ICE25P05	SOIC8	PA16SO16D-EO-150
ICE	ICE27C010	DIP32	
ICE	ICE27C010	PLCC32	PA32PL32D
ICE	ICE27C010	TSOP32	PA32TS20/PA32TS32D-20
ICE	ICE27C512	DIP28	
ICE	ICE27C512	PLCC32	PA32PL28D-YA
ICE	ICE27C512	TSOP28	PA28TS28D-EO
ICE	ICE27LC010	DIP32	
ICE	ICE27LC010	PLCC32	PA32PL32D
ICE	ICE27LC010	TSOP32	PA32TS20/PA32TS32D-20
ICE	ICE27IC512	DIP28	
ICE	ICE27IC512	PLCC32	PA32PL28D-YA
ICE	ICE27IC512	TSOP28	PA28TS28D-EO
ICSI	IS89C52A	DIP40	
ICSI	IS89C52A	PLCC44	PA44-48U
ICSI	IS89C54	DIP40	
ICSI	IS89C54	PLCC44	PA44-48U
ICSI	IS89C58	DIP40	
ICSI	IS89C58	PLCC44	PA44-48U
ICSI	IS89C64	DIP40	
ICSI	IS89C64	PLCC44	PA44-48U
ICT	27CX010	DIP32	
ICT	93C46	DIP8	
ICT	93C46	SOIC8	PA16SO16D-EO-150
ICT	93C46A	DIP8	
ICT	93C46A	SOIC8	PA16SO16D-EO-150
ICT	93C56	DIP8	
ICT	93C56	SOIC8	PA16SO16D-EO-150
ICT	93C56A	DIP8	
ICT	93C56A	SOIC8	PA16SO16D-EO-150
ICT	93C66	DIP8	
ICT	93C66	SOIC8	PA16SO16D-EO-150
ICT	93C66A	DIP8	
ICT	93C66A	SOIC8	PA16SO16D-EO-150
ICT	93CX46	DIP8	
ICT	93CX46	SOIC8	PA16SO16D-EO-150
ICT	93CX56	DIP8	
ICT	93CX56	SOIC8	PA16SO16D-EO-150
ICT	93CX66	DIP8	
ICT	93CX66	SOIC8	PA16SO16D-EO-150
ICT	PA7024J	PLCC28	PA28PL28D
ICT	PA7024P	DIP24	
ICT	PA7128P	DIP28	
ICT	PA7140J	PLCC44	PA44-48U
ICT	PA7140P	DIP40	
ICT	PA7536J	PLCC28	PA28PL28D
ICT	PA7536P	DIP28	
ICT	PA7536S	SOIC28	PA28SQ28D-EO-300
ICT	PA7540J	PLCC28	PA28PL28D
ICT	PA7540P	DIP24	
ICT	PA7572J	PLCC44	PA44-48U
ICT	PA7572P	DIP40	
ICT	PA7572Q	TQFP44	PA44QF44D
ICT	PEEL153	DIP20	
ICT	PEEL16CV8	DIP20	
ICT	PEEL16CV8	PLCC20	PA20LC20D[Dead Bug]
ICT	PEEL16CV8	SOIC20	PA28SQ28D-EO-300
ICT	PEEL16CV8	TSSOP20	PA20SS-P54
ICT	PEEL173	DIP24	
ICT	PEEL18CV8	DIP20	
ICT	PEEL18CV8	PLCC20	PA20LC20D[Dead Bug]
ICT	PEEL18CV8	SOIC20	PA28SQ28D-EO-300
ICT	PEEL18CV8	TSSOP20	PA24TSS24D
ICT	PEEL18CV8Z	DIP20	
ICT	PEEL18CV8Z	PLCC20	PA20LC20D[Dead Bug]
ICT	PEEL18CV8Z	SOIC20	PA28SQ28D-EO-300
ICT	PEEL18CV8Z	TSSOP20	PA24TSS24D
ICT	PEEL18LV8Z	DIP20	
ICT	PEEL18LV8Z	PLCC20	PA20LC20D[Dead Bug]
ICT	PEEL18LV8Z	SOIC20	PA28SQ28D-EO-300
ICT	PEEL18LV8Z	TSSOP20	PA24TSS24D

ICT	PEEL20CG10	DIP24	
ICT	PEEL20CG10A	DIP24	
ICT	PEEL22CV10	DIP24	
ICT	PEEL22CV10	PLCC28	PA28PL28D
ICT	PEEL22CV10	SOIC24	PA28SO28D-EO-300
ICT	PEEL22CV10	TSSOP24	PA24TSS24D
ICT	PEEL22CV10A	DIP24	
ICT	PEEL22CV10A	PLCC28	PA28PL28D
ICT	PEEL22CV10A	SOIC24	PA28SO28D-EO-300
ICT	PEEL22CV10A	TSSOP24	PA24TSS24D
ICT	PEEL22CV10A+	DIP24	
ICT	PEEL22CV10A+	PLCC28	PA28PL28D
ICT	PEEL22CV10A+	SOIC24	PA28SO28D-EO-300
ICT	PEEL22CV10A+	TSSOP24	PA24TSS24D
ICT	PEEL22CV10A++	DIP24	
ICT	PEEL22CV10A++	PLCC28	PA28PL28D
ICT	PEEL22CV10A++	SOIC24	PA28SO28D-EO-300
ICT	PEEL22CV10A++	TSSOP24	PA24TSS24D
ICT	PEEL22CV10AZ	DIP24	
ICT	PEEL22CV10AZ	PLCC28	PA28PL28D
ICT	PEEL22CV10AZ	SOIC24	PA28SO28D-EO-300
ICT	PEEL22CV10AZ	TSSOP24	PA24TSS24D
ICT	PEEL22CV10AZ+	DIP24	
ICT	PEEL22CV10AZ+	PLCC28	PA28PL28D
ICT	PEEL22CV10AZ+	SOIC24	PA28SO28D-EO-300
ICT	PEEL22CV10AZ+	TSSOP24	PA24TSS24D
ICT	PEEL22CV10AZ++	DIP24	
ICT	PEEL22CV10AZ++	PLCC28	PA28PL28D
ICT	PEEL22CV10AZ++	SOIC24	PA28SO28D-EO-300
ICT	PEEL22CV10AZ++	TSSOP24	PA24TSS24D
ICT	PEEL22CV10Z	DIP24	
ICT	PEEL22CV10Z	PLCC28	PA28PL28D
ICT	PEEL22CV10Z	SOIC24	PA28SO28D-EO-300
ICT	PEEL22CV10Z	TSSOP24	PA24TSS24D
ICT	PEEL253	DIP20	
ICT	PEEL273	DIP24	
IDT	TSE2004G	DFN8	PA8QFN8D(2x3)
IMT	IM29F001B	DIP32	
IMT	IM29F001B	PLCC32	PA32PL32D
IMT	IM29F001B	TSOP32	PA32TS20/PA32TS32D-20
IMT	IM29F001T	DIP32	
IMT	IM29F001T	PLCC32	PA32PL32D
IMT	IM29F001T	TSOP32	PA32TS20/PA32TS32D-20
IMT	IM29F002B	DIP32	
IMT	IM29F002B	PLCC32	PA32PL32D
IMT	IM29F002B	TSOP32	PA32TS20/PA32TS32D-20
IMT	IM29F002T	DIP32	
IMT	IM29F002T	PLCC32	PA32PL32D
IMT	IM29F002T	TSOP32	PA32TS20/PA32TS32D-20
IMT	IM29F004B	DIP32	
IMT	IM29F004B	PLCC32	PA32PL32D
IMT	IM29F004B	TSOP32	PA32TS20/PA32TS32D-20
IMT	IM29F004T	DIP32	
IMT	IM29F004T	PLCC32	PA32PL32D
IMT	IM29F004T	TSOP32	PA32TS20/PA32TS32D-20
IMT	IM29LV004B	DIP32	
IMT	IM29LV004B	PLCC32	PA32PL32D
IMT	IM29LV004B	TSOP32	PA32TS20/PA32TS32D-20
IMT	IM29LV004T	DIP32	
IMT	IM29LV004T	PLCC32	PA32PL32D
IMT	IM29LV004T	TSOP32	PA32TS20/PA32TS32D-20
INTEL		27010	DIP32
INTEL		27010	PLCC32
INTEL		27010	TSOP32
INTEL		27011	DIP28
INTEL		27128	DIP28
INTEL	27128A		DIP28
INTEL	27128B		DIP28
INTEL		2716	DIP24
INTEL		27210	DIP40
INTEL		27210	PLCC44
INTEL		27256	DIP28
INTEL		2732	DIP24
			PA44-48U

INTEL	2732A		DIP24	
INTEL		27512	DIP28	
INTEL	27512J		DIP28	
INTEL		2764	DIP28	
INTEL	2764A		DIP28	
INTEL	27C010		DIP32	
INTEL	27C010		PLCC32	PA32PL32D
INTEL	27C010		TSOP32	PA32TS20/PA32TS32D-20
INTEL	27C010A		DIP32	
INTEL	27C010A		PLCC32	PA32PL32D
INTEL	27C010A		TSOP32	PA32TS20/PA32TS32D-20
INTEL	27C011		DIP28	
INTEL	27C020		DIP32	
INTEL	27C020		PLCC32	PA32PL32D
INTEL	27C020		TSOP32	PA32TS20/PA32TS32D-20
INTEL	27C040		DIP32	
INTEL	27C040		PLCC32	PA32PL32D
INTEL	27C100		DIP32	
INTEL	27C128		DIP28	
INTEL	27C128		PLCC32	PA32PL28D-YA
INTEL	27C210		DIP40	
INTEL	27C210		PLCC44	PA44-48U
INTEL	27C220		DIP40	
INTEL	27C220		PLCC44	PA44-48U
INTEL	27C240		DIP40	
INTEL	27C240		PLCC44	PA44-48U
INTEL	27C256		DIP28	
INTEL	27C256		PLCC32	PA32PL28D-YA
INTEL	27C400		DIP40	
INTEL	27C512		DIP28	
INTEL	27C512		PLCC32	PA32PL28D-YA
INTEL	27C513		DIP28	
INTEL	27C64		DIP28	
INTEL	27C64		PLCC32	PA32PL28D-YA
INTEL	2816A		DIP24	
INTEL	2817A		DIP28	
INTEL		2864	DIP28	
INTEL	2864A		DIP28	
INTEL	28F256-###P1C2		DIP32	
INTEL	28F256-###P2C2		DIP32	
INTEL	28F256A		DIP32	
INTEL	28F512		DIP32	
INTEL	5C031		DIP20	
INTEL	5C031		PLCC20	PA20LC20D[Dead Bug]
INTEL	5C032		DIP20	
INTEL	5C032		PLCC20	PA20LC20D[Dead Bug]
INTEL	5C060		DIP24	
INTEL	5C060		PLCC28	PA28PL24D2P6-YA
INTEL	5C090		DIP40	
INTEL	5C090		PLCC44	PA44-48U
INTEL	5C090		PLCC44	PA900-44
INTEL	5C180		PLCC68	PA-EP1800
INTEL	8741A		DIP40	
INTEL	8741AH		DIP40	
INTEL		8742	DIP40	
INTEL	8742AH		DIP40	
INTEL		8748	DIP40	
INTEL	8748H		DIP40	
INTEL	8749H		DIP40	
INTEL	8751BH		DIP40	
INTEL	8751H(10ms)		DIP40	
INTEL	8751H(50ms)		DIP40	
INTEL	8752BH		DIP40	
INTEL	8755A		DIP40	
INTEL	87C196CA		PLCC68	PA68-40E
INTEL	87C196JQ		PLCC52	PA52-40C
INTEL	87C196JR		PLCC52	PA52-40C
INTEL	87C196JT		PLCC52	PA52-40C
INTEL	87C196JV		PLCC52	PA52-40C
INTEL	87C196KB		PLCC68	PA68-40D
INTEL	87C196KC		PLCC68	PA68-40D
INTEL	87C196KD		PLCC68	PA68-40D
INTEL	87C196KQ		PLCC68	PA68-40C

INTEL	87C196KR	PLCC68	PA68-40C
INTEL	87C196KS	PLCC68	PA68-40C
INTEL	87C196KT	PLCC68	PA68-40C
INTEL	87C196MC	PLCC84	PA84-40C
INTEL	87C196MD	PLCC84	PA84-40C
INTEL	87C196MH	PLCC84	PA84-40C
INTEL	87C251SB	DIP40	
INTEL	87C251SB	PLCC44	PA44-48U
INTEL	87C42	DIP40	
INTEL	87C51	DIP40	
INTEL	87C51	PLCC44	PA44-48U
INTEL	87C511	DIP40	
INTEL	87C511	PLCC44	PA44-48U
INTEL	87C511	QFP44	PA44QF44D
INTEL	87C51FA	DIP40	
INTEL	87C51FA	PLCC44	PA44-48U
INTEL	87C51FA	QFP44	PA44QF44D
INTEL	87C51FB	DIP40	
INTEL	87C51FB	PLCC44	PA44-48U
INTEL	87C51FB	QFP44	PA44QF44D
INTEL	87C51FC	DIP40	
INTEL	87C51FC	PLCC44	PA44-48U
INTEL	87C51FC	QFP44	PA44QF44D
INTEL	87C51RA	DIP40	
INTEL	87C51RA	PLCC44	PA44-48U
INTEL	87C51RB	DIP40	
INTEL	87C51RB	PLCC44	PA44-48U
INTEL	87C51RC	DIP40	
INTEL	87C51RC	PLCC44	PA44-48U
INTEL	87C52	DIP40	
INTEL	87C52	PLCC44	PA44-48U
INTEL	87C521	DIP40	
INTEL	87C521	PLCC44	PA44-48U
INTEL	87C54	DIP40	
INTEL	87C54	PLCC44	PA44-48U
INTEL	87C64	DIP28	
INTEL	87L51FA	PLCC44	PA44-48U
INTEL	87L51FB	PLCC44	PA44-48U
INTEL	87L51FC	PLCC44	PA44-48U
INTEL	AB28F200B5B	SOP44	PA44SO44D
INTEL	AB28F200B5T	SOP44	PA44SO44D
INTEL	AB28F200BRB	SOP44	PA44SO44D
INTEL	AB28F200BRT	SOP44	PA44SO44D
INTEL	AB28F200BXB	SOP44	PA44SO44D
INTEL	AB28F200BXT	SOP44	PA44SO44D
INTEL	AB28F400BRB	SOP44	PA44SO44D
INTEL	AB28F400BRT	SOP44	PA44SO44D
INTEL	DA28F320J5	SSOP56	PA56SS48DB/CIC-56SS-48D-B6-TI
INTEL	DA28F320J5A	SSOP56	PA56SS48DB/CIC-56SS-48D-B6-TI
INTEL	DA28F640J5	SSOP56	PA56SS48DB/CIC-56SS-48D-B6-TI
INTEL	DD28F032SA	TSOP56	PA56TS48DK
INTEL	DT28F160F3-B	SSOP56	CIC-56SS-48D-C6-TI
INTEL	DT28F160F3-T	SSOP56	CIC-56SS-48D-C6-TI
INTEL	DT28F160S3	SSOP56	PA56SS48DB/CIC-56SS-48D-B6-TI
INTEL	DT28F320S3	SSOP56	PA56SS48DB/CIC-56SS-48D-B6-TI
INTEL	DT28F320S5	SSOP56	PA56SS48DB/CIC-56SS-48D-B6-TI
INTEL	DT28F800F3-B	SSOP56	CIC-56SS-48D-C6-TI
INTEL	DT28F800F3-T	SSOP56	CIC-56SS-48D-C6-TI
INTEL	E28F002BC-T	TSOP40	PA40TS40D
INTEL	E28F002BV/E-B	TSOP40	PA40TS40D
INTEL	E28F002BV/E-T	TSOP40	PA40TS40D
INTEL	E28F002BX/L-B	TSOP40	PA40TS40D
INTEL	E28F002BX/L-T	TSOP40	PA40TS40D
INTEL	E28F004B3-B	TSOP40	PA40TS40D
INTEL	E28F004B3-T	TSOP40	PA40TS40D
INTEL	E28F004B5-B	TSOP40	PA40TS40D
INTEL	E28F004B5-T	TSOP40	PA40TS40D
INTEL	E28F004BE-B	TSOP40	PA40TS40D
INTEL	E28F004BE-T	TSOP40	PA40TS40D
INTEL	E28F004BV-B	TSOP40	PA40TS40D
INTEL	E28F004BV-T	TSOP40	PA40TS40D
INTEL	E28F004BX/L-B	TSOP40	PA40TS40D
INTEL	E28F004BX/L-T	TSOP40	PA40TS40D

INTEL	E28F004S3	TSOP40	PA40TS40D
INTEL	E28F004S5	TSOP40	PA40TS40D
INTEL	E28F008B3-B	TSOP40	PA40TS40D
INTEL	E28F008B3-T	TSOP40	PA40TS40D
INTEL	E28F008BE-B	TSOP40	PA40TS40D
INTEL	E28F008BE-T	TSOP40	PA40TS40D
INTEL	E28F008BV-B	TSOP40	PA40TS40D
INTEL	E28F008BV-T	TSOP40	PA40TS40D
INTEL	E28F008C3-B	TSOP40	PA40TS40D
INTEL	E28F008C3-T	TSOP40	PA40TS40D
INTEL	E28F008S3	TSOP40	PA40TS40D
INTEL	E28F008S5	TSOP40	PA40TS40D
INTEL	E28F008SA	TSOP40	PA40TS40D
INTEL	E28F016B3-B	TSOP40	PA40TS40D
INTEL	E28F016B3-T	TSOP40	PA40TS40D
INTEL	E28F016C3-B	TSOP40	PA40TS40D
INTEL	E28F016C3-T	TSOP40	PA40TS40D
INTEL	E28F016S3	TSOP40	PA40TS40D
INTEL	E28F016S5	TSOP40	PA40TS40D
INTEL	E28F016SA	TSOP56	PA56TS48DK
INTEL	E28F128J3A	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	E28F128J3C	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	E28F160B3-B	TSOP48	PA48TS48D
INTEL	E28F160B3-T	TSOP48	PA48TS48D
INTEL	E28F160C2-BA	TSOP48	PA48TS48D
INTEL	E28F160C2-TA	TSOP48	PA48TS48D
INTEL	E28F160C3-B	TSOP48	PA48TS48D
INTEL	E28F160C3-T	TSOP48	PA48TS48D
INTEL	E28F160S3	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	E28F160S5	SSOP56	PA56SS48DB/CIC-56SS-48D-B6-TI
INTEL	E28F160S5	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	E28F200BV-B80	TSOP56	HA56TS48DAB
INTEL	E28F200BV-T60	TSOP56	HA56TS48DAB
INTEL	E28F200BX-B60	TSOP56	HA56TS48DAB
INTEL	E28F320B3-B	TSOP48	PA48TS48D
INTEL	E28F320B3-T	TSOP48	PA48TS48D
INTEL	E28F320C3-B	TSOP48	PA48TS48D
INTEL	E28F320C3-T	TSOP48	PA48TS48D
INTEL	E28F320J3A	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	E28F320J5	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	E28F400B3-B	TSOP48	PA48TS48D
INTEL	E28F400B3-T	TSOP48	PA48TS48D
INTEL	E28F400B5-B	TSOP48	PA48TS48D
INTEL	E28F400B5-T	TSOP48	PA48TS48D
INTEL	E28F400C3-B	TSOP48	PA48TS48D
INTEL	E28F400C3-T	TSOP48	PA48TS48D
INTEL	E28F640J3A	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	E28F640J3C	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	E28F640J5	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	E28F800B3-B	TSOP48	PA48TS48D
INTEL	E28F800B3-T	TSOP48	PA48TS48D
INTEL	E28F800B5-B	TSOP48	PA48TS48D
INTEL	E28F800B5-T	TSOP48	PA48TS48D
INTEL	E28F800C2-BA	TSOP48	PA48TS48D
INTEL	E28F800C2-TA	TSOP48	PA48TS48D
INTEL	E28F800C3-B	TSOP48	PA48TS48D
INTEL	E28F800C3-T	TSOP48	PA48TS48D
INTEL	E28F800CV-B	TSOP48	PA48TS48D
INTEL	E28F800CV-T	TSOP48	PA48TS48D
INTEL	E82802AB	TSOP40	PA40TS40D
INTEL	E82802AC	TSOP40	PA40TS40D
INTEL	G28F320J5	BGA48	CIC-56uBGA-48D-A6-YAM
INTEL	G28F640J5	BGA48	CIC-56uBGA-48D-A6-YAM
INTEL	GE28F3204W30-B	BGA56	PA56BGA48D-TO
INTEL	GE28F3204W30-T	BGA56	PA56BGA48D-TO
INTEL	GE28F3208W30-B	BGA56	PA56BGA48D-TO
INTEL	GE28F3208W30-T	BGA56	PA56BGA48D-TO
INTEL	GE28F320W30-B	BGA56	PA56BGA48D-TO
INTEL	GE28F320W30-T	BGA56	PA56BGA48D-TO
INTEL	GE28F6408W18-B	BGA56	PA56BGA48DE
INTEL	GE28F6408W18-T	BGA56	PA56BGA48DE
INTEL	GE28F6408W30-B	BGA56	PA56BGA48D-TO
INTEL	GE28F6408W30-T	BGA56	PA56BGA48D-TO

INTEL	GT28F004B3-B	BGA48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F004B3-T	BGA48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F008B3-B	BGA48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F008B3-T	BGA48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F008C3-B	BGA48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F008C3-T	BGA48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F016B3-B	BGA48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F016B3-T	BGA48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F016C3-B	BGA48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F016C3-T	BGA48	CIC-48uBGA-40D-B6-TI
INTEL	GT28F160B3-B	BGA48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F160B3-T	BGA48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F160C2-BA	BGA48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F160C2-TA	BGA48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F160C3-B	BGA48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F160C3-T	BGA48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F160F3-B	BGA56	CIC-56uBGA-48D-B6-TI
INTEL	GT28F160F3-T	BGA56	CIC-56uBGA-48D-B6-TI
INTEL	GT28F320B3-B	BGA48	CIC-48uBGA-48D-A6-TI
INTEL	GT28F320B3-T	BGA48	CIC-48uBGA-48D-A6-TI
INTEL	GT28F320C3-B	BGA48	CIC-48uBGA-48D-A6-TI
INTEL	GT28F320C3-T	BGA48	CIC-48uBGA-48D-A6-TI
INTEL	GT28F400B3-B	BGA48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F400B3-T	BGA48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F400C3-B	BGA48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F400C3-T	BGA48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F800B3-B	BGA48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F800B3-T	BGA48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F800C2-BA	BGA48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F800C2-TA	BGA48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F800C3-B	BGA48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F800C3-T	BGA48	CIC-48uBGA-44D-A6-YAM
INTEL	GT28F800F3-B	BGA56	CIC-56uBGA-48D-B6-TI
INTEL	GT28F800F3-T	BGA56	CIC-56uBGA-48D-B6-TI
INTEL	I2716	DIP24	
INTEL	ID2716	DIP24	
INTEL	JS28F128J3C	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	JS28F128J3D	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	JS28F128J3F	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	JS28F128P30B	TSOP56	HA56TS48DJ
INTEL	JS28F128P30T	TSOP56	HA56TS48DJ
INTEL	JS28F128P33B	TSOP56	HA56TS48DF
INTEL	JS28F128P33T	TSOP56	HA56TS48DF
INTEL	JS28F256P30B	TSOP56	HA56TS48DJ
INTEL	JS28F256P30T	TSOP56	HA56TS48DJ
INTEL	JS28F256P33B	TSOP56	HA56TS48DF
INTEL	JS28F256P33T	TSOP56	HA56TS48DF
INTEL	JS28F256P3G	TSOP56	PA56TS48DC
INTEL	JS28F320J3C	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	JS28F320J3D	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	JS28F320J3F	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	JS28F640J3C	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	JS28F640J3D	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	JS28F640J3F	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	JS28F640P30B	TSOP56	HA56TS48DJ
INTEL	JS28F640P30T	TSOP56	HA56TS48DJ
INTEL	JS28F640P33B	TSOP56	HA56TS48DF
INTEL	JS28F640P33T	TSOP56	HA56TS48DF
INTEL	M2716	DIP24	
INTEL	N28F001BX-B	PLCC32	PA32PL32D
INTEL	N28F001BX-T	PLCC32	PA32PL32D
INTEL	N28F010	PLCC32	PA32PL32D
INTEL	N28F020	PLCC32	PA32PL32D
INTEL	N82802AB	PLCC32	PA32PL32D
INTEL	N82802AC	PLCC32	PA32PL32D
INTEL	P27128A	DIP28	
INTEL	P27128B	DIP28	
INTEL	P27256	DIP28	
INTEL	P27512	DIP28	
INTEL	P2764A	DIP28	
INTEL	P27C128	DIP28	
INTEL	P27C256	DIP28	
INTEL	P27C256	PLCC32	PA32PL28D-YA

INTEL	P27C64	DIP28	
INTEL	P28F001BX-B	DIP32	
INTEL	P28F001BX-T	DIP32	
INTEL	P28F010	DIP32	
INTEL	P28F020	DIP32	
INTEL	PA28F004S3	SOP44	PA44SO44D
INTEL	PA28F004S5	SOP44	PA44SO44D
INTEL	PA28F008S3	SOP44	PA44SO44D
INTEL	PA28F008S5	SOP44	PA44SO44D
INTEL	PA28F008SA	SOP44	PA44SO44D
INTEL	PA28F008SA-L	SOP44	PA44SO44D
INTEL	PA28F200B5-B	SOP44	PA44SO44D
INTEL	PA28F200B5-T	SOP44	PA44SO44D
INTEL	PA28F200BV/E-B	SOP44	PA44SO44D
INTEL	PA28F200BV/E-T	SOP44	PA44SO44D
INTEL	PA28F200BX/L-B	SOP44	PA44SO44D
INTEL	PA28F200BX/L-T	SOP44	PA44SO44D
INTEL	PA28F400B5-B	SOP44	PA44SO44D
INTEL	PA28F400B5-T	SOP44	PA44SO44D
INTEL	PA28F400BV/E-B	SOP44	PA44SO44D
INTEL	PA28F400BV/E-T	SOP44	PA44SO44D
INTEL	PA28F400BX/L-B	SOP44	PA44SO44D
INTEL	PA28F400BX/L-T	SOP44	PA44SO44D
INTEL	PA28F800B5-B	SOP44	PA44SO44D
INTEL	PC28F256P33B	EBGA64	HA64BG48DM
INTEL	PC28F256P33T	EBGA64	HA64BG48DM
INTEL	RC28F128J3A	EBGA64	PA64BGA48D/HA64BGA48D
INTEL	RC28F128J3C	EBGA64	PA64BGA48D/HA64BGA48D
INTEL	RC28F128J3D	EBGA64	PA64BGA48D/HA64BGA48D
INTEL	RC28F128K18	EBGA64	HA64BG48DN
INTEL	RC28F128K3	EBGA64	PA64BGA48DA
INTEL	RC28F128P30B	EBGA64	PA64BGA48DI/HA64BGA48DI
INTEL	RC28F128P30T	EBGA64	PA64BGA48DI/HA64BGA48DI
INTEL	RC28F256J3C	EBGA64	HA64BG48D-ES
INTEL	RC28F256K18	EBGA64	PA64BGA48DA
INTEL	RC28F256K3	EBGA64	PA64BGA48DA
INTEL	RC28F256P30B	EBGA64	PA64BGA48DI/HA64BGA48DI
INTEL	RC28F256P30T	EBGA64	PA64BGA48DI/HA64BGA48DI
INTEL	RC28F256P33B	EBGA64	HA64BG48DM
INTEL	RC28F256P33T	EBGA64	HA64BG48DM
INTEL	RC28F320J3A	EBGA64	PA64BGA48D/HA64BGA48D
INTEL	RC28F320J3C	EBGA64	PA64BGA48D/HA64BGA48D
INTEL	RC28F320J3D	EBGA64	PA64BGA48D/HA64BGA48D
INTEL	RC28F640J3A	EBGA64	PA64BGA48D/HA64BGA48D
INTEL	RC28F640J3C	EBGA64	PA64BGA48D/HA64BGA48D
INTEL	RC28F640J3D	EBGA64	PA64BGA48D/HA64BGA48D
INTEL	RC28F640K3	EBGA64	PA64BGA48DA
INTEL	RC28F640P30B	EBGA64	PA64BGA48DI/HA64BGA48DI
INTEL	RC28F640P30T	EBGA64	PA64BGA48DI/HA64BGA48DI
INTEL	RD28F128J3AM	BGA80	PA80BGA48D-A
INTEL	RD28F1602C3-B	BGA72	PA72BGA48D-B
INTEL	RD28F1602C3-T	BGA72	PA72BGA48D-B
INTEL	RD28F1604C3-B	BGA72	PA72BGA48D-B
INTEL	RD28F1604C3-T	BGA72	PA72BGA48D-B
INTEL	RD28F192SJ3AM	BGA80	PA80BGA48D-A
INTEL	RD28F256SJ3AM	BGA80	PA80BGA48D-A
INTEL	RD28F3202C3-B	BGA72	PA72BGA48D-B
INTEL	RD28F3202C3-T	BGA72	PA72BGA48D-B
INTEL	RD28F3204C3-B	BGA72	PA72BGA48D-B
INTEL	RD28F3204C3-T	BGA72	PA72BGA48D-B
INTEL	RD28F3208W30-B	BGA80	PA80BGA48D
INTEL	RD28F3208W30-T	BGA80	PA80BGA48D
INTEL	RD28F320W30-B	BGA80	PA80BGA48D
INTEL	RD28F320W30-T	BGA80	PA80BGA48D
INTEL	RD28F6408W30-B	BGA80	PA80BGA48D
INTEL	RD28F6408W30-T	BGA80	PA80BGA48D
INTEL	RD28F640W30-B	BGA80	PA80BGA48D
INTEL	RD28F640W30-T	BGA80	PA80BGA48D
INTEL	RD38F1010C0ZBL0	BGA66	PA66BGA48DB
INTEL	RD38F1010C0ZTL0	BGA66	PA66BGA48DB
INTEL	RD38F1020C0ZBL0	BGA66	PA66BGA48DB
INTEL	RD38F1020C0ZTL0	BGA66	PA66BGA48DB
INTEL	RD38F1030W0ZBQ0	BGA88	PA88BGA48DA-YO-8X10

INTEL	RD38F2030W0ZBQ1	BGA88	PA88BGA48DA-YO-8X10
INTEL	RD38F2040W0YBQ0	BGA88	HA88BGA48DA7
INTEL	RD38F2040W0ZBQ0	BGA88	PA88BGA48DA-YO-8X10
INTEL	RD38F2230WWZBQ0	BGA88	PA88BGA48DA-YO-8X10
INTEL	RD38F2240WWZBQ0	BGA88	PA88BGA48DA-YO-8X10
INTEL	RD38F2240WWZDQ0	BGA88	PA88BGA48DA-YO-8X10
INTEL	RD38F3040L0ZBQ0	BGA88	PA88BGA48DA-YO-8X10
INTEL	RD38F3040L0ZTQ0	BGA88	PA88BGA48DA-YO-8X10
INTEL	RD38F3350LLZDQ0	BGA88	PA88BGA48DA-YO-8X10
INTEL	RD38F3350WWZDQ1	BGA88	PA88BGA48DA-YO-8X10
INTEL	TD8755A	DIP40	
INTEL	TE28F128J3C	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	TE28F128J3D	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	TE28F128P30B	TSOP56	HA56TS48DJ
INTEL	TE28F128P30T	TSOP56	HA56TS48DJ
INTEL	TE28F128P33B	TSOP56	HA56TS48DF
INTEL	TE28F128P33T	TSOP56	HA56TS48DF
INTEL	TE28F256P30B	TSOP56	HA56TS48DJ
INTEL	TE28F256P30T	TSOP56	HA56TS48DJ
INTEL	TE28F256P33B	TSOP56	HA56TS48DF
INTEL	TE28F256P33T	TSOP56	HA56TS48DF
INTEL	TE28F320J3C	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	TE28F320J3D	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	TE28F640C3-B	TSOP48	PA48TS48D
INTEL	TE28F640C3-T	TSOP48	PA48TS48D
INTEL	TE28F640J3C	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	TE28F640J3D	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
INTEL	TE28F640P30B	TSOP56	HA56TS48DJ
INTEL	TE28F640P30T	TSOP56	HA56TS48DJ
INTEL	TE28F640P33B	TSOP56	HA56TS48DF
INTEL	TE28F640P33T	TSOP56	HA56TS48DF
ISSI	IS24C64A	TSSOP8	PA24TSS24D
ISSI	IS24C64A	TSSOP8	PA8TSS8D
ISSI	IS25CD010	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25CD010	TSSOP8	PA8TSS8D
ISSI	IS25CD010	WSO8	PA8SON8D(6x5)
ISSI	IS25CD025	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25CD025	TSSOP8	PA8TSS8D
ISSI	IS25CD512	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25CD512	TSSOP8	PA8TSS8D
ISSI	IS25CD512	USO8	PA8SON8D(2x3)
ISSI	IS25CD512	WSO8	PA8SON8D(6x5)
ISSI	IS25CQ032	SOIC16	PA28SO28D-EO-300
ISSI	IS25CQ032	SOIC8	PA20SO20D-EO-210
ISSI	IS25CQ032	VSOP8	PA20SO20D-EO-210
ISSI	IS25CQ032	WSO8	PA8SON8D(6x5)
ISSI	IS25CQ032	WSO8	PA8SON8DA(8x6)
ISSI	IS25LD020	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LD020	TSSOP8	PA8TSS8D
ISSI	IS25LD020	USO8	PA8SON8D(2x3)
ISSI	IS25LD020	VVSOP8	PA16SO16D-EO-150
ISSI	IS25LD020	WSO8	PA8SON8D(6x5)
ISSI	IS25LD040	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LD040	SOIC8	PA20SO20D-EO-210
ISSI	IS25LD040	VVSOP8	PA16SO16D-EO-150
ISSI	IS25LD040	WSO8	PA8SON8D(6x5)
ISSI	IS25LP016D	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP016D	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LP016D	SOIC8	PA20SO20D-EO-210
ISSI	IS25LP016D	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP016D	USO8	PA8SON8D(2x3)
ISSI	IS25LP016D	USO8	PA8SON8D(4x3)
ISSI	IS25LP016D	VVSOP8	PA16SO16D-EO-150
ISSI	IS25LP016D	WSO8	PA8SON8D(6x5)
ISSI	IS25LP016D	WSO8	PA8SON8DA(8x6)
ISSI	IS25LP032	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP032	SOIC8	PA20SO20D-EO-210
ISSI	IS25LP032	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP032	WSO8	PA8SON8D(6x5)
ISSI	IS25LP032	WSO8	PA8SON8DA(8x6)
ISSI	IS25LP032(QPI)	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP032(QPI)	SOIC8	PA20SO20D-EO-210
ISSI	IS25LP032(QPI)	TFBGA24	PA24BG24D(6x8mm)5x5



ISSI	IS25LP032(QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25LP032(QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP032A	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP032A	SOIC8	PA20SO20D-EO-210
ISSI	IS25LP032A	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP032A	VSOP8	PA20SO20D-EO-210
ISSI	IS25LP032A	WSON8	PA8SON8D(6x5)
ISSI	IS25LP032A	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP032A(QPI)	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP032A(QPI)	SOIC8	PA20SO20D-EO-210
ISSI	IS25LP032A(QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP032A(QPI)	VSOP8	PA20SO20D-EO-210
ISSI	IS25LP032A(QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25LP032A(QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP032D	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP032D	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LP032D	SOIC8	PA20SO20D-EO-210
ISSI	IS25LP032D	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP032D	USON8	PA8SON8D(4x3)
ISSI	IS25LP032D	WSON8	PA8SON8D(6x5)
ISSI	IS25LP032D	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP064	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP064	SOIC8	PA20SO20D-EO-210
ISSI	IS25LP064	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP064	WSON8	PA8SON8D(6x5)
ISSI	IS25LP064	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP064(QPI)	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP064(QPI)	SOIC8	PA20SO20D-EO-210
ISSI	IS25LP064(QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP064(QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25LP064(QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP064A	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP064A	SOIC8	PA20SO20D-EO-210
ISSI	IS25LP064A	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP064A	VSOP8	PA20SO20D-EO-210
ISSI	IS25LP064A	WSON8	PA8SON8D(6x5)
ISSI	IS25LP064A	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP064A(QPI)	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP064A(QPI)	SOIC8	PA20SO20D-EO-210
ISSI	IS25LP064A(QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP064A(QPI)	VSOP8	PA20SO20D-EO-210
ISSI	IS25LP064A(QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25LP064A(QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP064D	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP064D	SOIC8	PA20SO20D-EO-210
ISSI	IS25LP064D	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP064D	WSON8	PA8SON8D(6x5)
ISSI	IS25LP064D	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP080D	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LP080D	SOIC8	PA20SO20D-EO-210
ISSI	IS25LP080D	USON8	PA8SON8D(2x3)
ISSI	IS25LP080D	VVSOP8	PA16SO16D-EO-150
ISSI	IS25LP080D	WSON8	PA8SON8D(6x5)
ISSI	IS25LP080D(QPI)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LP080D(QPI)	SOIC8	PA20SO20D-EO-210
ISSI	IS25LP080D(QPI)	USON8	PA8SON8D(2x3)
ISSI	IS25LP080D(QPI)	VVSOP8	PA16SO16D-EO-150
ISSI	IS25LP080D(QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25LP128	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP128	SOIC8	PA20SO20D-EO-210
ISSI	IS25LP128	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP128	WSON8	PA8SON8D(6x5)
ISSI	IS25LP128	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP128(QPI)	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP128(QPI)	SOIC8	PA20SO20D-EO-210
ISSI	IS25LP128(QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP128(QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25LP128(QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP128F	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP128F	SOIC8	PA20SO20D-EO-210
ISSI	IS25LP128F	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP128F	WSON8	PA8SON8D(6x5)
ISSI	IS25LP128F	WSON8	PA8SON8DA(8x6)

ISSI	IS25LP128F (QPI)	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP128F (QPI)	SOIC8	PA20SO20D-EO-210
ISSI	IS25LP128F (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP128F (QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25LP128F (QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP256D	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP256D	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP256D	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP256D (QPI)	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP256D (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP256D (QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP256E	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP256E	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP256E	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP256E (QPI)	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP256E (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP256E (QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP512M	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP512M	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP512M	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP512M (QPI)	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP512M (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP512M (QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP512MG	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP512MG	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP512MG	WSON8	PA8SON8DA(8x6)
ISSI	IS25LP512MG (QPI)	SOIC16	PA28SO28D-EO-300
ISSI	IS25LP512MG (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LP512MG (QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25LQ010A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LQ010A	TSSOP8	PA8TSS8D
ISSI	IS25LQ010B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LQ010B	SOIC8	PA20SO20D-EO-210
ISSI	IS25LQ010B	TSSOP8	PA8TSS8D
ISSI	IS25LQ010B	USON8	PA8SON8D(2x3)
ISSI	IS25LQ010B	VVSOP8	PA16SO16D-EO-150
ISSI	IS25LQ010B	WSON8	PA8SON8D(6x5)
ISSI	IS25LQ016	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LQ016	SOIC8	PA20SO20D-EO-210
ISSI	IS25LQ016	VVSOP8	PA16SO16D-EO-150
ISSI	IS25LQ016	WSON8	PA8SON8D(6x5)
ISSI	IS25LQ016	WSON8	PA8SON8DA(8x6)
ISSI	IS25LQ016B	SOIC16	PA28SO28D-EO-300
ISSI	IS25LQ016B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LQ016B	SOIC8	PA20SO20D-EO-210
ISSI	IS25LQ016B	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LQ016B	USON8	PA8SON8D(4x3)
ISSI	IS25LQ016B	VSOP8	PA20SO20D-EO-210
ISSI	IS25LQ016B	WSON8	PA8SON8D(6x5)
ISSI	IS25LQ016B	WSON8	PA8SON8DA(8x6)
ISSI	IS25LQ020A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LQ020A	TSSOP8	PA8TSS8D
ISSI	IS25LQ020A	VVSOP8	PA16SO16D-EO-150
ISSI	IS25LQ020B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LQ020B	SOIC8	PA20SO20D-EO-210
ISSI	IS25LQ020B	TSSOP8	PA8TSS8D
ISSI	IS25LQ020B	USON8	PA8SON8D(2x3)
ISSI	IS25LQ020B	VVSOP8	PA16SO16D-EO-150
ISSI	IS25LQ020B	WSON8	PA8SON8D(6x5)
ISSI	IS25LQ025B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LQ025B	SOIC8	PA20SO20D-EO-210
ISSI	IS25LQ025B	TSSOP8	PA8TSS8D
ISSI	IS25LQ025B	USON8	PA8SON8D(2x3)
ISSI	IS25LQ025B	VVSOP8	PA16SO16D-EO-150
ISSI	IS25LQ025B	WSON8	PA8SON8D(6x5)
ISSI	IS25LQ032B	SOIC16	PA28SO28D-EO-300
ISSI	IS25LQ032B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LQ032B	SOIC8	PA20SO20D-EO-210
ISSI	IS25LQ032B	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LQ032B	USON8	PA8SON8D(4x3)
ISSI	IS25LQ032B	VSOP8	PA20SO20D-EO-210
ISSI	IS25LQ032B	WSON8	PA8SON8D(6x5)
ISSI	IS25LQ032B	WSON8	PA8SON8DA(8x6)

ISSI	IS25LQ040B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LQ040B	SOIC8	PA20SO20D-EO-210
ISSI	IS25LQ040B	TSSOP8	PA8TSS8D
ISSI	IS25LQ040B	USON8	PA8SON8D(2x3)
ISSI	IS25LQ040B	VVSOP8	PA16SO16D-EO-150
ISSI	IS25LQ040B	WSON8	PA8SON8D(6x5)
ISSI	IS25LQ080	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LQ080	SOIC8	PA20SO20D-EO-210
ISSI	IS25LQ080	VVSOP8	PA16SO16D-EO-150
ISSI	IS25LQ080	WSON8	PA8SON8D(6x5)
ISSI	IS25LQ080B	SOIC16	PA28SO28D-EO-300
ISSI	IS25LQ080B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LQ080B	SOIC8	PA20SO20D-EO-210
ISSI	IS25LQ080B	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25LQ080B	USON8	PA8SON8D(4x3)
ISSI	IS25LQ080B	VSOP8	PA20SO20D-EO-210
ISSI	IS25LQ080B	WSON8	PA8SON8D(6x5)
ISSI	IS25LQ080B	WSON8	PA8SON8DA(8x6)
ISSI	IS25LQ512A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LQ512A	TSSOP8	PA8TSS8D
ISSI	IS25LQ512B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25LQ512B	SOIC8	PA20SO20D-EO-210
ISSI	IS25LQ512B	TSSOP8	PA8TSS8D
ISSI	IS25LQ512B	USON8	PA8SON8D(2x3)
ISSI	IS25LQ512B	VVSOP8	PA16SO16D-EO-150
ISSI	IS25LQ512B	WSON8	PA8SON8D(6x5)
ISSI	IS25WP016	SOIC16	PA28SO28D-EO-300
ISSI	IS25WP016	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WP016	SOIC8	PA20SO20D-EO-210
ISSI	IS25WP016	TSSOP8	PA8TSS8D
ISSI	IS25WP016	USON8	PA8SON8D(2x3)
ISSI	IS25WP016	USON8	PA8SON8D(4x3)
ISSI	IS25WP016	VSOP8	PA20SO20D-EO-210
ISSI	IS25WP016	VVSOP8	PA16SO16D-EO-150
ISSI	IS25WP016	WSON8	PA8SON8D(6x5)
ISSI	IS25WP016 (QPI)	SOIC16	PA28SO28D-EO-300
ISSI	IS25WP016 (QPI)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WP016 (QPI)	SOIC8	PA20SO20D-EO-210
ISSI	IS25WP016 (QPI)	TSSOP8	PA8TSS8D
ISSI	IS25WP016 (QPI)	USON8	PA8SON8D(2x3)
ISSI	IS25WP016 (QPI)	USON8	PA8SON8D(4x3)
ISSI	IS25WP016 (QPI)	VSOP8	PA20SO20D-EO-210
ISSI	IS25WP016 (QPI)	VVSOP8	PA16SO16D-EO-150
ISSI	IS25WP016 (QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25WP016D	SOIC16	PA28SO28D-EO-300
ISSI	IS25WP016D	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WP016D	SOIC8	PA20SO20D-EO-210
ISSI	IS25WP016D	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP016D	USON8	PA8SON8D(2x3)
ISSI	IS25WP016D	USON8	PA8SON8D(4x3)
ISSI	IS25WP016D	VVSOP8	PA16SO16D-EO-150
ISSI	IS25WP016D	WSON8	PA8SON8D(6x5)
ISSI	IS25WP016D	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP016D (QPI)	SOIC16	PA28SO28D-EO-300
ISSI	IS25WP016D (QPI)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WP016D (QPI)	SOIC8	PA20SO20D-EO-210
ISSI	IS25WP016D (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP016D (QPI)	USON8	PA8SON8D(2x3)
ISSI	IS25WP016D (QPI)	USON8	PA8SON8D(4x3)
ISSI	IS25WP016D (QPI)	VVSOP8	PA16SO16D-EO-150
ISSI	IS25WP016D (QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25WP016D (QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP020	SOIC16	PA28SO28D-EO-300
ISSI	IS25WP020	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WP020	SOIC8	PA20SO20D-EO-210
ISSI	IS25WP020	TSSOP8	PA8TSS8D
ISSI	IS25WP020	USON8	PA8SON8D(2x3)
ISSI	IS25WP020	USON8	PA8SON8D(4x3)
ISSI	IS25WP020	VSOP8	PA20SO20D-EO-210
ISSI	IS25WP020	VVSOP8	PA16SO16D-EO-150
ISSI	IS25WP020	WSON8	PA8SON8D(6x5)
ISSI	IS25WP020 (QPI)	SOIC16	PA28SO28D-EO-300
ISSI	IS25WP020 (QPI)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150

ISSI	IS25WP020 (QPI)	SOIC8	PA20SQ20D-EO-210
ISSI	IS25WP020 (QPI)	TSSOP8	PA8TSS8D
ISSI	IS25WP020 (QPI)	USON8	PA8SON8D(2x3)
ISSI	IS25WP020 (QPI)	USON8	PA8SON8D(4x3)
ISSI	IS25WP020 (QPI)	VSOP8	PA20SQ20D-EO-210
ISSI	IS25WP020 (QPI)	VVSOP8	PA16SO16D-EO-150
ISSI	IS25WP020 (QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25WP020D	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WP020D	SOIC8	PA20SQ20D-EO-210
ISSI	IS25WP020D	USON8	PA8SON8D(2x3)
ISSI	IS25WP020D	VVSOP8	PA16SO16D-EO-150
ISSI	IS25WP020D	WSON8	PA8SON8D(6x5)
ISSI	IS25WP020D(QPI)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WP020D(QPI)	SOIC8	PA20SQ20D-EO-210
ISSI	IS25WP020D(QPI)	USON8	PA8SON8D(2x3)
ISSI	IS25WP020D(QPI)	VVSOP8	PA16SO16D-EO-150
ISSI	IS25WP020D(QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25WP032	SOIC16	PA28SQ28D-EO-300
ISSI	IS25WP032	SOIC8	PA20SQ20D-EO-210
ISSI	IS25WP032	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP032	VSOP8	PA20SQ20D-EO-210
ISSI	IS25WP032	WSON8	PA8SON8D(6x5)
ISSI	IS25WP032	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP032(QPI)	SOIC16	PA28SQ28D-EO-300
ISSI	IS25WP032(QPI)	SOIC8	PA20SQ20D-EO-210
ISSI	IS25WP032(QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP032(QPI)	VSOP8	PA20SQ20D-EO-210
ISSI	IS25WP032(QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25WP032(QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP032D	SOIC16	PA28SQ28D-EO-300
ISSI	IS25WP032D	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WP032D	SOIC8	PA20SQ20D-EO-210
ISSI	IS25WP032D	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP032D	USON8	PA8SON8D(4x3)
ISSI	IS25WP032D	WSON8	PA8SON8D(6x5)
ISSI	IS25WP032D	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP032D (QPI)	SOIC16	PA28SQ28D-EO-300
ISSI	IS25WP032D (QPI)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WP032D (QPI)	SOIC8	PA20SQ20D-EO-210
ISSI	IS25WP032D (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP032D (QPI)	USON8	PA8SON8D(4x3)
ISSI	IS25WP032D (QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25WP032D (QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP040	SOIC16	PA28SQ28D-EO-300
ISSI	IS25WP040	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WP040	SOIC8	PA20SQ20D-EO-210
ISSI	IS25WP040	TSSOP8	PA8TSS8D
ISSI	IS25WP040	USON8	PA8SON8D(2x3)
ISSI	IS25WP040	USON8	PA8SON8D(4x3)
ISSI	IS25WP040	VSOP8	PA20SQ20D-EO-210
ISSI	IS25WP040	VVSOP8	PA16SO16D-EO-150
ISSI	IS25WP040	WSON8	PA8SON8D(6x5)
ISSI	IS25WP040 (QPI)	SOIC16	PA28SQ28D-EO-300
ISSI	IS25WP040 (QPI)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WP040 (QPI)	SOIC8	PA20SQ20D-EO-210
ISSI	IS25WP040 (QPI)	TSSOP8	PA8TSS8D
ISSI	IS25WP040 (QPI)	USON8	PA8SON8D(2x3)
ISSI	IS25WP040 (QPI)	USON8	PA8SON8D(4x3)
ISSI	IS25WP040 (QPI)	VSOP8	PA20SQ20D-EO-210
ISSI	IS25WP040 (QPI)	VVSOP8	PA16SO16D-EO-150
ISSI	IS25WP040D	WSON8	PA8SON8D(6x5)
ISSI	IS25WP040D	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WP040D	SOIC8	PA20SQ20D-EO-210
ISSI	IS25WP040D	USON8	PA8SON8D(2x3)
ISSI	IS25WP040D	VVSOP8	PA16SO16D-EO-150
ISSI	IS25WP040D	WSON8	PA8SON8D(6x5)
ISSI	IS25WP040D(QPI)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WP040D(QPI)	SOIC8	PA20SQ20D-EO-210
ISSI	IS25WP040D(QPI)	USON8	PA8SON8D(2x3)
ISSI	IS25WP040D(QPI)	VVSOP8	PA16SO16D-EO-150
ISSI	IS25WP040D(QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25WP064	SOIC16	PA28SQ28D-EO-300
ISSI	IS25WP064	SOIC8	PA20SQ20D-EO-210

ISSI	IS25WP064	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP064	VSOP8	PA20SO20D-EO-210
ISSI	IS25WP064	WSON8	PA8SON8D(6x5)
ISSI	IS25WP064	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP064(QPI)	SOIC16	PA28SO28D-EO-300
ISSI	IS25WP064(QPI)	SOIC8	PA20SO20D-EO-210
ISSI	IS25WP064(QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP064(QPI)	VSOP8	PA20SO20D-EO-210
ISSI	IS25WP064(QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25WP064(QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP064D	SOIC16	PA28SO28D-EO-300
ISSI	IS25WP064D	SOIC8	PA20SO20D-EO-210
ISSI	IS25WP064D	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP064D	WSON8	PA8SON8D(6x5)
ISSI	IS25WP064D	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP064D (QPI)	SOIC16	PA28SO28D-EO-300
ISSI	IS25WP064D (QPI)	SOIC8	PA20SO20D-EO-210
ISSI	IS25WP064D (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP064D (QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25WP064D (QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP080	SOIC16	PA28SO28D-EO-300
ISSI	IS25WP080	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WP080	SOIC8	PA20SO20D-EO-210
ISSI	IS25WP080	TSSOP8	PA8TSS8D
ISSI	IS25WP080	USON8	PA8SON8D(2x3)
ISSI	IS25WP080	USON8	PA8SON8D(4x3)
ISSI	IS25WP080	VSOP8	PA20SO20D-EO-210
ISSI	IS25WP080	VVSOP8	PA16SO16D-EO-150
ISSI	IS25WP080	WSON8	PA8SON8D(6x5)
ISSI	IS25WP080 (QPI)	SOIC16	PA28SO28D-EO-300
ISSI	IS25WP080 (QPI)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WP080 (QPI)	SOIC8	PA20SO20D-EO-210
ISSI	IS25WP080 (QPI)	TSSOP8	PA8TSS8D
ISSI	IS25WP080 (QPI)	USON8	PA8SON8D(2x3)
ISSI	IS25WP080 (QPI)	USON8	PA8SON8D(4x3)
ISSI	IS25WP080 (QPI)	VSOP8	PA20SO20D-EO-210
ISSI	IS25WP080 (QPI)	VVSOP8	PA16SO16D-EO-150
ISSI	IS25WP080 (QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25WP080D	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WP080D	SOIC8	PA20SO20D-EO-210
ISSI	IS25WP080D	USON8	PA8SON8D(2x3)
ISSI	IS25WP080D	VVSOP8	PA16SO16D-EO-150
ISSI	IS25WP080D	WSON8	PA8SON8D(6x5)
ISSI	IS25WP080D(QPI)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WP080D(QPI)	SOIC8	PA20SO20D-EO-210
ISSI	IS25WP080D(QPI)	USON8	PA8SON8D(2x3)
ISSI	IS25WP080D(QPI)	VVSOP8	PA16SO16D-EO-150
ISSI	IS25WP080D(QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25WP128	SOIC16	PA28SO28D-EO-300
ISSI	IS25WP128	SOIC8	PA20SO20D-EO-210
ISSI	IS25WP128	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP128	VSOP8	PA20SO20D-EO-210
ISSI	IS25WP128	WSON8	PA8SON8D(6x5)
ISSI	IS25WP128	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP128(QPI)	SOIC16	PA28SO28D-EO-300
ISSI	IS25WP128(QPI)	SOIC8	PA20SO20D-EO-210
ISSI	IS25WP128(QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP128(QPI)	VSOP8	PA20SO20D-EO-210
ISSI	IS25WP128(QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25WP128(QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP128F	SOIC16	PA28SO28D-EO-300
ISSI	IS25WP128F	SOIC8	PA20SO20D-EO-210
ISSI	IS25WP128F	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP128F	WSON8	PA8SON8D(6x5)
ISSI	IS25WP128F	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP128F (QPI)	SOIC16	PA28SO28D-EO-300
ISSI	IS25WP128F (QPI)	SOIC8	PA20SO20D-EO-210
ISSI	IS25WP128F (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP128F (QPI)	WSON8	PA8SON8D(6x5)
ISSI	IS25WP128F (QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP256D	SOIC16	PA28SO28D-EO-300
ISSI	IS25WP256D	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP256D	WSON8	PA8SON8DA(8x6)

ISSI	IS25WP256D (QPI)	SOIC16	PA28SQ28D-EO-300
ISSI	IS25WP256D (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP256D (QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP256E	SOIC16	PA28SQ28D-EO-300
ISSI	IS25WP256E	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP256E	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP256E (QPI)	SOIC16	PA28SQ28D-EO-300
ISSI	IS25WP256E (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP256E (QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP512M	SOIC16	PA28SQ28D-EO-300
ISSI	IS25WP512M	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP512M	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP512M (QPI)	SOIC16	PA28SQ28D-EO-300
ISSI	IS25WP512M (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP512M (QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP512MG	SOIC16	PA28SQ28D-EO-300
ISSI	IS25WP512MG	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP512MG	WSON8	PA8SON8DA(8x6)
ISSI	IS25WP512MG (QPI)	SOIC16	PA28SQ28D-EO-300
ISSI	IS25WP512MG (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
ISSI	IS25WP512MG (QPI)	WSON8	PA8SON8DA(8x6)
ISSI	IS25WQ020	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WQ020	SOIC8	PA20SQ20D-EO-210
ISSI	IS25WQ020	USON8	PA8SON8D(2x3)
ISSI	IS25WQ020	VVSOP8	PA16SO16D-EO-150
ISSI	IS25WQ020	WSON8	PA8SON8D(6x5)
ISSI	IS25WQ040	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	IS25WQ040	SOIC8	PA20SQ20D-EO-210
ISSI	IS25WQ040	USON8	PA8SON8D(2x3)
ISSI	IS25WQ040	VVSOP8	PA16SO16D-EO-150
ISSI	IS25WQ040	WSON8	PA8SON8D(6x5)
ISSI	IS27C010	DIP32	
ISSI	IS27C010	PLCC32	PA32PL32D
ISSI	IS27C010	TSOP32	PA32TS20/PA32TS32D-20
ISSI	IS27C020	DIP32	
ISSI	IS27C020	PLCC32	PA32PL32D
ISSI	IS27C020	TSOP32	PA32TS20/PA32TS32D-20
ISSI	IS27C256	DIP28	
ISSI	IS27C256	PLCC32	PA32PL28D-YA
ISSI	IS27C512	DIP28	
ISSI	IS27C512	PLCC32	PA32PL28D-YA
ISSI	IS27C512	TSOP28	PA28TS28D-EO
ISSI	IS27DV256	DIP28	
ISSI	IS27DV256	PLCC32	PA32PL28D-YA
ISSI	IS27DV256	TSOP28	PA28TS28D-EO
ISSI	IS27HC010	DIP32	
ISSI	IS27HC010	PLCC32	PA32PL32D
ISSI	IS27HC010	TSOP32	PA32TS20/PA32TS32D-20
ISSI	IS27HC020	DIP32	
ISSI	IS27HC020	PLCC32	PA32PL32D
ISSI	IS27HC020	TSOP32	PA32TS20/PA32TS32D-20
ISSI	IS27HC256	DIP28	
ISSI	IS27HC256	PLCC32	PA32PL28D-YA
ISSI	IS27HC256	TSOP28	PA28TS28D-EO
ISSI	IS27HC512	DIP28	
ISSI	IS27HC512	PLCC32	PA32PL28D-YA
ISSI	IS27HC512	TSOP28	PA28TS28D-EO
ISSI	IS27LV010	DIP32	
ISSI	IS27LV010	PLCC32	PA32PL32D
ISSI	IS27LV010	TSOP32	PA32TS20/PA32TS32D-20
ISSI	IS27LV020	DIP32	
ISSI	IS27LV020	PLCC32	PA32PL32D
ISSI	IS27LV020	TSOP32	PA32TS20/PA32TS32D-20
ISSI	IS27LV256	DIP28	
ISSI	IS27LV256	PLCC32	PA32PL28D-YA
ISSI	IS27LV256	TSOP28	PA28TS28D-EO
ISSI	IS27LV512	DIP28	
ISSI	IS27LV512	PLCC32	PA32PL28D-YA
ISSI	IS27LV512	TSOP28	PA28TS28D-EO
ISSI	IS28F010	DIP32	
ISSI	IS28F010	PLCC32	PA32PL32D
ISSI	IS28F010	TSOP32	PA32TS20/PA32TS32D-20
ISSI	IS28F020	DIP32	

ISSI	IS28F020	PLCC32	PA32PL32D
ISSI	IS28F020	TSOP32	PA32TS20/PA32TS32D-20
ISSI	IS89C51	DIP40	
ISSI	IS89C51	PLCC44	PA44-48U
ISSI	IS89C51A	DIP40	
ISSI	IS89C51A	PLCC44	PA44-48U
ISSI	IS89C52	DIP40	
ISSI	IS89C52	PLCC44	PA44-48U
ISSI	IS89C52A	DIP40	
ISSI	IS89C52A	PLCC44	PA44-48U
ISSI	IS89C54A	DIP40	
ISSI	IS89C54A	PLCC44	PA44-48U
ISSI	IS93C46	DIP8	
ISSI	IS93C46-3G	SOIC8	PA8SO8D-EO-150
ISSI	IS93C46-3GR	SOIC8	PA16SO16D-EO-150
ISSI	IS93C46-3P	DIP8	
ISSI	IS93C46A-3G	SOIC8	PA8SO8D-EO-150
ISSI	IS93C46A-3GR	SOIC8	PA16SO16D-EO-150
ISSI	IS93C46A-3P	DIP8	
ISSI	IS93C46D-2G	SOIC8	PA8SO8D-EO-150
ISSI	IS93C46D-2GR	SOIC8	PA16SO16D-EO-150
ISSI	IS93C46D-2P	DIP8	
ISSI	IS93C46D-3GR	SOIC8	PA16SO16D-EO-150
ISSI	IS93C46D-3P	DIP8	
ISSI	IS93C56	DIP8	
ISSI	IS93C56-3G	SOIC8	PA8SO8D-EO-150
ISSI	IS93C56-3GR	SOIC8	PA16SO16D-EO-150
ISSI	IS93C56-3P	DIP8	
ISSI	IS93C56A-3G	SOIC8	PA8SO8D-EO-150
ISSI	IS93C56A-3GR	SOIC8	PA16SO16D-EO-150
ISSI	IS93C56A-3P	DIP8	
ISSI	IS93C66	DIP8	
ISSI	IS93C66-3G	SOIC8	PA8SO8D-EO-150
ISSI	IS93C66-3GR	SOIC8	PA16SO16D-EO-150
ISSI	IS93C66-3P	DIP8	
ISSI	IS93C66A-3G	SOIC8	PA8SO8D-EO-150
ISSI	IS93C66A-3GR	SOIC8	PA16SO16D-EO-150
ISSI	IS93C66A-3P	DIP8	
ISSI	IS93C76A-3G	SOIC8	PA8SO8D-EO-150
ISSI	IS93C76A-3GR	SOIC8	PA16SO16D-EO-150
ISSI	IS93C76A-3P	DIP8	
ISSI	IS93C86A-3G	SOIC8	PA8SO8D-EO-150
ISSI	IS93C86A-3GR	SOIC8	PA16SO16D-EO-150
ISSI	IS93C86A-3P	DIP8	
ISSI	Pm25LD010C	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	Pm25LD010C	TSSOP8	PA8TSS8D
ISSI	Pm25LD010C	WSON8	PA8SON8D(6x5)
ISSI	Pm25LD020C	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	Pm25LD020C	TSSOP8	PA8TSS8D
ISSI	Pm25LD020C	WSON8	PA8SON8D(6x5)
ISSI	Pm25LQ010B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	Pm25LQ010B	SOIC8	PA20SQ20D-EO-210
ISSI	Pm25LQ010B	TSSOP8	PA8TSS8D
ISSI	Pm25LQ010B	USON8	PA8SON8D(2x3)
ISSI	Pm25LQ010B	VVSOP8	PA16SO16D-EO-150
ISSI	Pm25LQ010B	WSON8	PA8SON8D(6x5)
ISSI	Pm25LQ016	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	Pm25LQ016	SOIC8	PA20SQ20D-EO-210
ISSI	Pm25LQ016	VVSOP8	PA16SO16D-EO-150
ISSI	Pm25LQ016	WSON8	PA8SON8D(6x5)
ISSI	Pm25LQ016	WSON8	PA8SON8DA(8x6)
ISSI	Pm25LQ020	DIP8	
ISSI	Pm25LQ020	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	Pm25LQ020	SOIC8	PA20SQ20D-EO-210
ISSI	Pm25LQ020	VVSOP8	PA16SO16D-EO-150
ISSI	Pm25LQ020	WSON8	PA8SON8D(6x5)
ISSI	Pm25LQ020B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	Pm25LQ020B	SOIC8	PA20SQ20D-EO-210
ISSI	Pm25LQ020B	TSSOP8	PA8TSS8D
ISSI	Pm25LQ020B	USON8	PA8SON8D(2x3)
ISSI	Pm25LQ020B	VVSOP8	PA16SO16D-EO-150
ISSI	Pm25LQ020B	WSON8	PA8SON8D(6x5)
ISSI	Pm25LQ040	DIP8	

ISSI	Pm25LQ040	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	Pm25LQ040	SOIC8	PA20SO20D-EO-210
ISSI	Pm25LQ040	VVSOP8	PA16SO16D-EO-150
ISSI	Pm25LQ040	WSON8	PA8SON8D(6x5)
ISSI	Pm25LQ040B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	Pm25LQ040B	SOIC8	PA20SO20D-EO-210
ISSI	Pm25LQ040B	TSSOP8	PA8TSS8D
ISSI	Pm25LQ040B	USON8	PA8SON8D(2x3)
ISSI	Pm25LQ040B	VVSOP8	PA16SO16D-EO-150
ISSI	Pm25LQ040B	WSON8	PA8SON8D(6x5)
ISSI	Pm25LQ512B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	Pm25LQ512B	SOIC8	PA20SO20D-EO-210
ISSI	Pm25LQ512B	TSSOP8	PA8TSS8D
ISSI	Pm25LQ512B	USON8	PA8SON8D(2x3)
ISSI	Pm25LQ512B	VVSOP8	PA16SO16D-EO-150
ISSI	Pm25LQ512B	WSON8	PA8SON8D(6x5)
ISSI	Pm25WD020	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	Pm25WD020	VVSOP8	PA16SO16D-EO-150
ISSI	Pm25WD020	WSON8	PA8SON8D(6x5)
ISSI	Pm25WD040	DIP8	
ISSI	Pm25WD040	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ISSI	Pm25WD040	SOIC8	PA20SO20D-EO-210
ISSI	Pm25WD040	VVSOP8	PA16SO16D-EO-150
ISSI	Pm25WD040	WSON8	PA8SON8D(6x5)
KHIC	KH29LV320DB	TSOP48	PA48TS48D1
KHIC	KH29LV320DT	TSOP48	PA48TS48D1
LATTICE	GAL16LV8C	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas10H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas10L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas10P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas12H6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas12L6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas12P6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas14H4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas14L4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas14P4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas16H2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas16H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas16L2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas16L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas16P2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas16P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas16R4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas16R6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas16R8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas16RP4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas16RP6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Cas16RP8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8D	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das10H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das10L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das10P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das12H6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das12L6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das12P6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das14H4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das14L4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das14P4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16H2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16L2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16P2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16R4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16R6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16R8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16RP4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Das16RP6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Z	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas10H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas10L8	PLCC20	PA20LC20D[Dead Bug]



LATTICE	GAL16LV8Zas10P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas12H6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas12L6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas12P6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas14H4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas14L4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas14P4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16H2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16L2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16P2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16R4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16R6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16R8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16RP4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16RP6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16LV8Zas16RP8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8	DIP20	
LATTICE	GAL16V8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8A	DIP20	
LATTICE	GAL16V8A	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8A	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas10H8	DIP20	
LATTICE	GAL16V8Aas10H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas10H8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas10L8	DIP20	
LATTICE	GAL16V8Aas10L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas10L8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas10P8	DIP20	
LATTICE	GAL16V8Aas10P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas10P8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas12H6	DIP20	
LATTICE	GAL16V8Aas12H6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas12H6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas12L6	DIP20	
LATTICE	GAL16V8Aas12L6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas12L6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas12P6	DIP20	
LATTICE	GAL16V8Aas12P6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas12P6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas14H4	DIP20	
LATTICE	GAL16V8Aas14H4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas14H4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas14L4	DIP20	
LATTICE	GAL16V8Aas14L4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas14L4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas14P4	DIP20	
LATTICE	GAL16V8Aas14P4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas14P4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16H2	DIP20	
LATTICE	GAL16V8Aas16H2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16H2	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16H8	DIP20	
LATTICE	GAL16V8Aas16H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16H8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16L2	DIP20	
LATTICE	GAL16V8Aas16L2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16L2	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16L8	DIP20	
LATTICE	GAL16V8Aas16L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16L8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16P2	DIP20	
LATTICE	GAL16V8Aas16P2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16P2	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16P8	DIP20	
LATTICE	GAL16V8Aas16P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16P8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16R4	DIP20	
LATTICE	GAL16V8Aas16R4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16R4	SOIC20	PA20SO20D-EO-210

LATTICE	GAL16V8Aas16R6	DIP20	
LATTICE	GAL16V8Aas16R6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16R6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16R8	DIP20	
LATTICE	GAL16V8Aas16R8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16R8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16RP4	DIP20	
LATTICE	GAL16V8Aas16RP4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16RP4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16RP6	DIP20	
LATTICE	GAL16V8Aas16RP6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16RP6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Aas16RP8	DIP20	
LATTICE	GAL16V8Aas16RP8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Aas16RP8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as10H8	DIP20	
LATTICE	GAL16V8as10H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as10H8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as10L8	DIP20	
LATTICE	GAL16V8as10L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as10L8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as10P8	DIP20	
LATTICE	GAL16V8as10P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as10P8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as12H6	DIP20	
LATTICE	GAL16V8as12H6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as12H6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as12L6	DIP20	
LATTICE	GAL16V8as12L6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as12L6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as12P6	DIP20	
LATTICE	GAL16V8as12P6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as12P6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as14H4	DIP20	
LATTICE	GAL16V8as14H4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as14H4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as14L4	DIP20	
LATTICE	GAL16V8as14L4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as14L4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as14P4	DIP20	
LATTICE	GAL16V8as14P4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as14P4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as16H2	DIP20	
LATTICE	GAL16V8as16H2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16H2	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as16H8	DIP20	
LATTICE	GAL16V8as16H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16H8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as16L2	DIP20	
LATTICE	GAL16V8as16L2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16L2	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as16L8	DIP20	
LATTICE	GAL16V8as16L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16L8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as16P2	DIP20	
LATTICE	GAL16V8as16P2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16P2	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as16P8	DIP20	
LATTICE	GAL16V8as16P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16P8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as16R4	DIP20	
LATTICE	GAL16V8as16R4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16R4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as16R6	DIP20	
LATTICE	GAL16V8as16R6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16R6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as16R8	DIP20	
LATTICE	GAL16V8as16R8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16R8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as16RP4	DIP20	
LATTICE	GAL16V8as16RP4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16RP4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as16RP6	DIP20	

LATTICE	GAL16V8as16RP6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16RP6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8as16RP8	DIP20	
LATTICE	GAL16V8as16RP8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8as16RP8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8B	DIP20	
LATTICE	GAL16V8B	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8B	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas10H8	DIP20	
LATTICE	GAL16V8Bas10H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas10H8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas10L8	DIP20	
LATTICE	GAL16V8Bas10L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas10L8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas10P8	DIP20	
LATTICE	GAL16V8Bas10P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas10P8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas12H6	DIP20	
LATTICE	GAL16V8Bas12H6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas12H6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas12L6	DIP20	
LATTICE	GAL16V8Bas12L6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas12L6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas12P6	DIP20	
LATTICE	GAL16V8Bas12P6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas12P6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas14H4	DIP20	
LATTICE	GAL16V8Bas14H4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas14H4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas14L4	DIP20	
LATTICE	GAL16V8Bas14L4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas14L4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas14P4	DIP20	
LATTICE	GAL16V8Bas14P4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas14P4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16H2	DIP20	
LATTICE	GAL16V8Bas16H2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16H2	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16H8	DIP20	
LATTICE	GAL16V8Bas16H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16H8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16L2	DIP20	
LATTICE	GAL16V8Bas16L2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16L2	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16L8	DIP20	
LATTICE	GAL16V8Bas16L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16L8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16P2	DIP20	
LATTICE	GAL16V8Bas16P2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16P2	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16P8	DIP20	
LATTICE	GAL16V8Bas16P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16P8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16R4	DIP20	
LATTICE	GAL16V8Bas16R4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16R4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16R6	DIP20	
LATTICE	GAL16V8Bas16R6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16R6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16R8	DIP20	
LATTICE	GAL16V8Bas16R8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16R8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16RP4	DIP20	
LATTICE	GAL16V8Bas16RP4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16RP4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16RP6	DIP20	
LATTICE	GAL16V8Bas16RP6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16RP6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Bas16RP8	DIP20	
LATTICE	GAL16V8Bas16RP8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Bas16RP8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8C	DIP20	
LATTICE	GAL16V8C	PLCC20	PA20LC20D[Dead Bug]

LATTICE	GAL16V8C	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas10H8	DIP20	
LATTICE	GAL16V8Cas10H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas10H8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas10L8	DIP20	
LATTICE	GAL16V8Cas10L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas10L8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas10P8	DIP20	
LATTICE	GAL16V8Cas10P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas10P8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas12H6	DIP20	
LATTICE	GAL16V8Cas12H6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas12H6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas12L6	DIP20	
LATTICE	GAL16V8Cas12L6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas12L6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas12P6	DIP20	
LATTICE	GAL16V8Cas12P6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas12P6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas14H4	DIP20	
LATTICE	GAL16V8Cas14H4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas14H4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas14L4	DIP20	
LATTICE	GAL16V8Cas14L4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas14L4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas14P4	DIP20	
LATTICE	GAL16V8Cas14P4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas14P4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16H2	DIP20	
LATTICE	GAL16V8Cas16H2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16H2	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16H8	DIP20	
LATTICE	GAL16V8Cas16H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16H8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16L2	DIP20	
LATTICE	GAL16V8Cas16L2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16L2	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16L8	DIP20	
LATTICE	GAL16V8Cas16L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16L8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16P2	DIP20	
LATTICE	GAL16V8Cas16P2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16P2	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16P8	DIP20	
LATTICE	GAL16V8Cas16P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16P8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16R4	DIP20	
LATTICE	GAL16V8Cas16R4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16R4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16R6	DIP20	
LATTICE	GAL16V8Cas16R6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16R6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16R8	DIP20	
LATTICE	GAL16V8Cas16R8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16R8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16RP4	DIP20	
LATTICE	GAL16V8Cas16RP4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16RP4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16RP6	DIP20	
LATTICE	GAL16V8Cas16RP6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16RP6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Cas16RP8	DIP20	
LATTICE	GAL16V8Cas16RP8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Cas16RP8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8D	DIP20	
LATTICE	GAL16V8D	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8D	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das10H8	DIP20	
LATTICE	GAL16V8Das10H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das10H8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das10L8	DIP20	
LATTICE	GAL16V8Das10L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das10L8	SOIC20	PA20SO20D-EO-210

LATTICE	GAL16V8Das10P8	DIP20	
LATTICE	GAL16V8Das10P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das10P8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das12H6	DIP20	
LATTICE	GAL16V8Das12H6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das12H6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das12L6	DIP20	
LATTICE	GAL16V8Das12L6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das12L6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das12P6	DIP20	
LATTICE	GAL16V8Das12P6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das12P6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das14H4	DIP20	
LATTICE	GAL16V8Das14H4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das14H4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das14L4	DIP20	
LATTICE	GAL16V8Das14L4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das14L4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das14P4	DIP20	
LATTICE	GAL16V8Das14P4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das14P4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das16H2	DIP20	
LATTICE	GAL16V8Das16H2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das16H2	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das16H8	DIP20	
LATTICE	GAL16V8Das16H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das16H8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das16L2	DIP20	
LATTICE	GAL16V8Das16L2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das16L2	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das16L8	DIP20	
LATTICE	GAL16V8Das16L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das16L8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das16P2	DIP20	
LATTICE	GAL16V8Das16P2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das16P2	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das16P8	DIP20	
LATTICE	GAL16V8Das16P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das16P8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das16R4	DIP20	
LATTICE	GAL16V8Das16R4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das16R4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das16R6	DIP20	
LATTICE	GAL16V8Das16R6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das16R6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das16R8	DIP20	
LATTICE	GAL16V8Das16R8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das16R8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das16RP4	DIP20	
LATTICE	GAL16V8Das16RP4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das16RP4	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das16RP6	DIP20	
LATTICE	GAL16V8Das16RP6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das16RP6	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Das16RP8	DIP20	
LATTICE	GAL16V8Das16RP8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL16V8Das16RP8	SOIC20	PA20SO20D-EO-210
LATTICE	GAL16V8Z	DIP20	
LATTICE	GAL16VP8B	DIP20	
LATTICE	GAL16VP8B	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL18V10	DIP20	
LATTICE	GAL18V10	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL18V10B	DIP20	
LATTICE	GAL18V10B	PLCC20	PA20LC20D[Dead Bug]
LATTICE	GAL20LV8C	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8C	PLCC28	PA28PL28D
LATTICE	GAL20LV8Cas14H8	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Cas14H8	PLCC28	PA28PL28D
LATTICE	GAL20LV8Cas14L8	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Cas14L8	PLCC28	PA28PL28D
LATTICE	GAL20LV8Cas14P8	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Cas14P8	PLCC28	PA28PL28D
LATTICE	GAL20LV8Cas16H6	PLCC28	PA28PL24D2P6-YA



LATTICE	GAL20LV8Das20RP4	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Das20RP4	PLCC28	PA28PL28D
LATTICE	GAL20LV8Das20RP6	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Das20RP6	PLCC28	PA28PL28D
LATTICE	GAL20LV8Das20RP8	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Das20RP8	PLCC28	PA28PL28D
LATTICE	GAL20LV8Z	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Z	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas14H8	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas14H8	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas14L8	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas14L8	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas14P8	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas14P8	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas16H6	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas16H6	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas16L6	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas16L6	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas16P6	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas16P6	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas18H4	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas18H4	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas18L4	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas18L4	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas18P4	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas18P4	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas20H2	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20H2	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas20H8	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20H8	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas20L2	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20L2	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas20L8	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20L8	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas20P2	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20P2	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas20P8	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20P8	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas20R4	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20R4	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas20R6	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20R6	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas20R8	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20R8	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas20RP4	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20RP4	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas20RP6	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20RP6	PLCC28	PA28PL28D
LATTICE	GAL20LV8Zas20RP8	PLCC28	PA28PL24D2P6-YA
LATTICE	GAL20LV8Zas20RP8	PLCC28	PA28PL28D
LATTICE	GAL20RA10	DIP24	
LATTICE	GAL20RA10	PLCC28	PA28PL28D
LATTICE	GAL20RA10B	DIP24	
LATTICE	GAL20RA10B	PLCC28	PA28PL28D
LATTICE	GAL20V8	DIP24	
LATTICE	GAL20V8	PLCC28	PA28PL28D
LATTICE	GAL20V8A	DIP24	
LATTICE	GAL20V8A	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas14H8	DIP24	
LATTICE	GAL20V8Aas14H8	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas14L8	DIP24	
LATTICE	GAL20V8Aas14L8	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas14P8	DIP24	
LATTICE	GAL20V8Aas14P8	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas16H6	DIP24	
LATTICE	GAL20V8Aas16H6	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas16L6	DIP24	
LATTICE	GAL20V8Aas16L6	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas16P6	DIP24	
LATTICE	GAL20V8Aas16P6	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas18H4	DIP24	
LATTICE	GAL20V8Aas18H4	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas18L4	DIP24	

LATTICE	GAL20V8Aas18L4	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas18P4	DIP24	
LATTICE	GAL20V8Aas18P4	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas20H2	DIP24	
LATTICE	GAL20V8Aas20H2	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas20H8	DIP24	
LATTICE	GAL20V8Aas20H8	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas20L2	DIP24	
LATTICE	GAL20V8Aas20L2	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas20L8	DIP24	
LATTICE	GAL20V8Aas20L8	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas20P2	DIP24	
LATTICE	GAL20V8Aas20P2	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas20P8	DIP24	
LATTICE	GAL20V8Aas20P8	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas20R4	DIP24	
LATTICE	GAL20V8Aas20R4	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas20R6	DIP24	
LATTICE	GAL20V8Aas20R6	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas20R8	DIP24	
LATTICE	GAL20V8Aas20R8	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas20RP4	DIP24	
LATTICE	GAL20V8Aas20RP4	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas20RP6	DIP24	
LATTICE	GAL20V8Aas20RP6	PLCC28	PA28PL28D
LATTICE	GAL20V8Aas20RP8	DIP24	
LATTICE	GAL20V8Aas20RP8	PLCC28	PA28PL28D
LATTICE	GAL20V8as14H8	DIP24	
LATTICE	GAL20V8as14H8	PLCC28	PA28PL28D
LATTICE	GAL20V8as14L8	DIP24	
LATTICE	GAL20V8as14L8	PLCC28	PA28PL28D
LATTICE	GAL20V8as14P8	DIP24	
LATTICE	GAL20V8as14P8	PLCC28	PA28PL28D
LATTICE	GAL20V8as16H6	DIP24	
LATTICE	GAL20V8as16H6	PLCC28	PA28PL28D
LATTICE	GAL20V8as16L6	DIP24	
LATTICE	GAL20V8as16L6	PLCC28	PA28PL28D
LATTICE	GAL20V8as16P6	DIP24	
LATTICE	GAL20V8as16P6	PLCC28	PA28PL28D
LATTICE	GAL20V8as18H4	DIP24	
LATTICE	GAL20V8as18H4	PLCC28	PA28PL28D
LATTICE	GAL20V8as18L4	DIP24	
LATTICE	GAL20V8as18L4	PLCC28	PA28PL28D
LATTICE	GAL20V8as18P4	DIP24	
LATTICE	GAL20V8as18P4	PLCC28	PA28PL28D
LATTICE	GAL20V8as20H2	DIP24	
LATTICE	GAL20V8as20H2	PLCC28	PA28PL28D
LATTICE	GAL20V8as20H8	DIP24	
LATTICE	GAL20V8as20H8	PLCC28	PA28PL28D
LATTICE	GAL20V8as20L2	DIP24	
LATTICE	GAL20V8as20L2	PLCC28	PA28PL28D
LATTICE	GAL20V8as20L8	DIP24	
LATTICE	GAL20V8as20L8	PLCC28	PA28PL28D
LATTICE	GAL20V8as20P2	DIP24	
LATTICE	GAL20V8as20P2	PLCC28	PA28PL28D
LATTICE	GAL20V8as20P8	DIP24	
LATTICE	GAL20V8as20P8	PLCC28	PA28PL28D
LATTICE	GAL20V8as20R4	DIP24	
LATTICE	GAL20V8as20R4	PLCC28	PA28PL28D
LATTICE	GAL20V8as20R6	DIP24	
LATTICE	GAL20V8as20R6	PLCC28	PA28PL28D
LATTICE	GAL20V8as20R8	DIP24	
LATTICE	GAL20V8as20R8	PLCC28	PA28PL28D
LATTICE	GAL20V8as20RP4	DIP24	
LATTICE	GAL20V8as20RP4	PLCC28	PA28PL28D
LATTICE	GAL20V8as20RP6	DIP24	
LATTICE	GAL20V8as20RP6	PLCC28	PA28PL28D
LATTICE	GAL20V8as20RP8	DIP24	
LATTICE	GAL20V8as20RP8	PLCC28	PA28PL28D
LATTICE	GAL20V8B	DIP24	
LATTICE	GAL20V8B	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas14H8	DIP24	
LATTICE	GAL20V8Bas14H8	PLCC28	PA28PL28D



LATTICE	GAL20V8Bas14L8	DIP24	PA28PL28D
LATTICE	GAL20V8Bas14L8	PLCC28	
LATTICE	GAL20V8Bas14P8	DIP24	
LATTICE	GAL20V8Bas14P8	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas16H6	DIP24	
LATTICE	GAL20V8Bas16H6	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas16L6	DIP24	
LATTICE	GAL20V8Bas16L6	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas16P6	DIP24	
LATTICE	GAL20V8Bas16P6	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas18H4	DIP24	
LATTICE	GAL20V8Bas18H4	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas18L4	DIP24	
LATTICE	GAL20V8Bas18L4	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas18P4	DIP24	
LATTICE	GAL20V8Bas18P4	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas20H2	DIP24	
LATTICE	GAL20V8Bas20H2	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas20H8	DIP24	
LATTICE	GAL20V8Bas20H8	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas20L2	DIP24	
LATTICE	GAL20V8Bas20L2	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas20L8	DIP24	
LATTICE	GAL20V8Bas20L8	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas20P2	DIP24	
LATTICE	GAL20V8Bas20P2	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas20P8	DIP24	
LATTICE	GAL20V8Bas20P8	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas20R4	DIP24	
LATTICE	GAL20V8Bas20R4	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas20R6	DIP24	
LATTICE	GAL20V8Bas20R6	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas20R8	DIP24	
LATTICE	GAL20V8Bas20R8	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas20RP4	DIP24	
LATTICE	GAL20V8Bas20RP4	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas20RP6	DIP24	
LATTICE	GAL20V8Bas20RP6	PLCC28	PA28PL28D
LATTICE	GAL20V8Bas20RP8	DIP24	
LATTICE	GAL20V8Bas20RP8	PLCC28	PA28PL28D
LATTICE	GAL20V8C	DIP24	
LATTICE	GAL20V8C	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas14H8	DIP24	
LATTICE	GAL20V8Cas14H8	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas14L8	DIP24	
LATTICE	GAL20V8Cas14L8	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas14P8	DIP24	
LATTICE	GAL20V8Cas14P8	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas16H6	DIP24	
LATTICE	GAL20V8Cas16H6	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas16L6	DIP24	
LATTICE	GAL20V8Cas16L6	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas16P6	DIP24	
LATTICE	GAL20V8Cas16P6	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas18H4	DIP24	
LATTICE	GAL20V8Cas18H4	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas18L4	DIP24	
LATTICE	GAL20V8Cas18L4	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas18P4	DIP24	
LATTICE	GAL20V8Cas18P4	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas20H2	DIP24	
LATTICE	GAL20V8Cas20H2	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas20H8	DIP24	
LATTICE	GAL20V8Cas20H8	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas20L2	DIP24	
LATTICE	GAL20V8Cas20L2	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas20L8	DIP24	
LATTICE	GAL20V8Cas20L8	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas20P2	DIP24	
LATTICE	GAL20V8Cas20P2	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas20P8	DIP24	
LATTICE	GAL20V8Cas20P8	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas20R4	DIP24	

LATTICE	GAL20V8Cas20R4	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas20R6	DIP24	
LATTICE	GAL20V8Cas20R6	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas20R8	DIP24	
LATTICE	GAL20V8Cas20R8	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas20RP4	DIP24	
LATTICE	GAL20V8Cas20RP4	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas20RP6	DIP24	
LATTICE	GAL20V8Cas20RP6	PLCC28	PA28PL28D
LATTICE	GAL20V8Cas20RP8	DIP24	
LATTICE	GAL20V8Cas20RP8	PLCC28	PA28PL28D
LATTICE	GAL20V8D	DIP24	
LATTICE	GAL20V8D	PLCC28	PA28PL28D
LATTICE	GAL20V8Das14H8	DIP24	
LATTICE	GAL20V8Das14H8	PLCC28	PA28PL28D
LATTICE	GAL20V8Das14L8	DIP24	
LATTICE	GAL20V8Das14L8	PLCC28	PA28PL28D
LATTICE	GAL20V8Das14P8	DIP24	
LATTICE	GAL20V8Das14P8	PLCC28	PA28PL28D
LATTICE	GAL20V8Das16H6	DIP24	
LATTICE	GAL20V8Das16H6	PLCC28	PA28PL28D
LATTICE	GAL20V8Das16L6	DIP24	
LATTICE	GAL20V8Das16L6	PLCC28	PA28PL28D
LATTICE	GAL20V8Das16P6	DIP24	
LATTICE	GAL20V8Das16P6	PLCC28	PA28PL28D
LATTICE	GAL20V8Das18H4	DIP24	
LATTICE	GAL20V8Das18H4	PLCC28	PA28PL28D
LATTICE	GAL20V8Das18L4	DIP24	
LATTICE	GAL20V8Das18L4	PLCC28	PA28PL28D
LATTICE	GAL20V8Das18P4	DIP24	
LATTICE	GAL20V8Das18P4	PLCC28	PA28PL28D
LATTICE	GAL20V8Das20H2	DIP24	
LATTICE	GAL20V8Das20H2	PLCC28	PA28PL28D
LATTICE	GAL20V8Das20H8	DIP24	
LATTICE	GAL20V8Das20H8	PLCC28	PA28PL28D
LATTICE	GAL20V8Das20L2	DIP24	
LATTICE	GAL20V8Das20L2	PLCC28	PA28PL28D
LATTICE	GAL20V8Das20L8	DIP24	
LATTICE	GAL20V8Das20L8	PLCC28	PA28PL28D
LATTICE	GAL20V8Das20P2	DIP24	
LATTICE	GAL20V8Das20P2	PLCC28	PA28PL28D
LATTICE	GAL20V8Das20P8	DIP24	
LATTICE	GAL20V8Das20P8	PLCC28	PA28PL28D
LATTICE	GAL20V8Das20R4	DIP24	
LATTICE	GAL20V8Das20R4	PLCC28	PA28PL28D
LATTICE	GAL20V8Das20R6	DIP24	
LATTICE	GAL20V8Das20R6	PLCC28	PA28PL28D
LATTICE	GAL20V8Das20R8	DIP24	
LATTICE	GAL20V8Das20R8	PLCC28	PA28PL28D
LATTICE	GAL20V8Das20RP4	DIP24	
LATTICE	GAL20V8Das20RP4	PLCC28	PA28PL28D
LATTICE	GAL20V8Das20RP6	DIP24	
LATTICE	GAL20V8Das20RP6	PLCC28	PA28PL28D
LATTICE	GAL20V8Das20RP8	DIP24	
LATTICE	GAL20V8Das20RP8	PLCC28	PA28PL28D
LATTICE	GAL20VP8B	DIP24	
LATTICE	GAL20VP8B	PLCC28	PA28PL28D
LATTICE	GAL20XV10	DIP24	
LATTICE	GAL20XV10	PLCC28	PA28PL28D
LATTICE	GAL20XV10B	DIP24	
LATTICE	GAL20XV10B	PLCC28	PA28PL28D
LATTICE	GAL22LV10C	PLCC28	PA28PL28D
LATTICE	GAL22LV10D	PLCC28	PA28PL28D
LATTICE	GAL22LV10Z	PLCC28	PA28PL28D
LATTICE	GAL22LV10ZD	PLCC28	PA28PL28D
LATTICE	GAL22V10	DIP24	
LATTICE	GAL22V10	PLCC28	PA28PL28D
LATTICE	GAL22V10B	DIP24	
LATTICE	GAL22V10B	PLCC28	PA28PL28D
LATTICE	GAL22V10C	DIP24	
LATTICE	GAL22V10C	PLCC28	PA28PL28D
LATTICE	GAL22V10D	DIP24	
LATTICE	GAL22V10D	PLCC28	PA28PL28D

LATTICE	GAL26CLV12C	DIP28	
LATTICE	GAL26CLV12C	PLCC28	PA28PL28D
LATTICE	GAL26CLV12D	DIP28	
LATTICE	GAL26CLV12D	PLCC28	PA28PL28D
LATTICE	GAL26CLV12Z	DIP28	
LATTICE	GAL26CLV12Z	PLCC28	PA28PL28D
LATTICE	GAL26CLV12ZD	DIP28	
LATTICE	GAL26CLV12ZD	PLCC28	PA28PL28D
LATTICE	GAL26CV12	DIP28	
LATTICE	GAL26CV12	PLCC28	PA28PL28D
LATTICE	GAL26CV12B	DIP28	
LATTICE	GAL26CV12B	PLCC28	PA28PL28D
LATTICE	GAL26V12C	DIP28	
LATTICE	GAL26V12C	PLCC28	PA28PL28D
LATTICE	GAL6001	DIP24	
LATTICE	GAL6001	PLCC28	PA28PL28D
LATTICE	GAL6001B	DIP24	
LATTICE	GAL6001B	PLCC28	PA28PL28D
LATTICE	GAL6002B	DIP24	
LATTICE	GAL6002B	PLCC28	PA28PL28D
LATTICE	ispGAL22LV10	PLCC28	PA28PL28D
LATTICE	ispGAL22V10	DIP28	
LATTICE	ispGAL22V10	PLCC28	PA28PL28D
LATTICE	ispGAL22V10AB	PLCC28	PA28PL28D
LATTICE	ispGAL22V10AC	PLCC28	PA28PL28D
LATTICE	ispGAL22V10AV	PLCC28	PA28PL28D
LATTICE	ispGAL22V10B	DIP28	
LATTICE	ispGAL22V10B	PLCC28	PA28PL28D
LATTICE	ispGAL22V10C	DIP28	
LATTICE	ispGAL22V10C	PLCC28	PA28PL28D
LATTICE	ispGDS14	DIP20	
LATTICE	ispGDS14	PLCC20	PA20LC20D[Dead Bug]
LATTICE	ispGDS18	DIP24	
LATTICE	ispGDS22	DIP28	
LATTICE	ispGDS22	PLCC28	PA28PL28D
LATTICE	ispLSI1016	PLCC44	PA44-48U
LATTICE	ispLSI1016E	PLCC44	PA44-48U
LATTICE	ispLSI1016EA	PLCC44	PA44-48U
LATTICE	ispLSI1032	PLCC84	AS-84-28-02P-6YAM
LATTICE	ispLSI1032	TQFP100	PA100TQ28DA
LATTICE	ispLSI1032E	PLCC84	AS-84-28-02P-6YAM
LATTICE	ispLSI1032E	TQFP100	PA100TQ28DA
LATTICE	ispLSI2032	PLCC44	PA44-48U
LATTICE	ispLSI2032A	PLCC44	PA44-48U
LATTICE	ispLSI2032E	PLCC44	PA44-48U
LATTICE	ispLSI2032V	PLCC44	PA44-48U
LATTICE	ispLSI2032VE	PLCC44	PA44-48U
LATTICE	ispLSI2064	PLCC84	AS-84-28-02P-6YAM
LATTICE	ispLSI2064A	PLCC84	AS-84-28-02P-6YAM
LATTICE	ispLSI2192VE	BGA144	PA144BGA40DA
LATTICE	ispPAC-POWR1014	TQFP48	HA48TQ48DB
LATTICE	LC4032B	TQFP44	PA44QF44D
LATTICE	LC4032V	TQFP44	PA44QF44D
LATTICE	LC4032V	TQFP48	HA48TQ48D
LATTICE	LC4064B	TQFP100	PA100TQ28D-YC
LATTICE	LC4064B	TQFP44	PA44QF44D
LATTICE	LC4064C	TQFP100	PA100TQ28D-YC
LATTICE	LC4064V	TQFP100	PA100TQ28D-YC
LATTICE	LC4064V	TQFP44	PA44QF44D
LATTICE	LC4064V	TQFP48	HA48TQ48D
LATTICE	LC4128B	TQFP100	PA100TQ28D-YC
LATTICE	LC4128C	TQFP100	PA100TQ28D-YC
LATTICE	LC4128V	TQFP100	PA100TQ28D-YC
LATTICE	LC4128ZC	BGA132	HA132BG48D
LATTICE	LC4128ZC	TQFP100	PA100TQ28D-YC
LATTICE	M4A3-32/32	PLCC44	PA44-48U
LATTICE	M4A3-64/32	PLCC44	PA44-48U
LATTICE	M4A5-32/32	PLCC44	PA44-48U
LATTICE	M4A5-32/32	QFP48	HA48QF48DK
LATTICE	M4A5-32/32	TQFP44	PA44TQ44D-EO
LATTICE	M4A5-64/32	PLCC44	PA44-48U
LATTICE	M4A5-64/32	QFP48	HA48QF48DK
LATTICE	M4A5-64/32	TQFP44	PA44TQ44D-EO

LATTICE	MACH211	PLCC44	PA44-48U
LATTICE	MACH211	PLCC44	PA-MACH1
LATTICE	MACH211SP	PLCC44	PA44-48U
LATTICE	MACH211SP	PLCC44	PA-MACH1
LATTICE	PALCE16V8H	DIP20	
LATTICE	PALCE16V8H	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8H	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has10H8	DIP20	
LATTICE	PALCE16V8Has10H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has10H8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has10L8	DIP20	
LATTICE	PALCE16V8Has10L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has10L8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has10P8	DIP20	
LATTICE	PALCE16V8Has10P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has10P8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has12H6	DIP20	
LATTICE	PALCE16V8Has12H6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has12H6	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has12L6	DIP20	
LATTICE	PALCE16V8Has12L6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has12L6	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has12P6	DIP20	
LATTICE	PALCE16V8Has12P6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has12P6	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has14H4	DIP20	
LATTICE	PALCE16V8Has14H4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has14H4	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has14L4	DIP20	
LATTICE	PALCE16V8Has14L4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has14L4	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has14P4	DIP20	
LATTICE	PALCE16V8Has14P4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has14P4	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has16H2	DIP20	
LATTICE	PALCE16V8Has16H2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has16H2	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has16H8	DIP20	
LATTICE	PALCE16V8Has16H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has16H8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has16L2	DIP20	
LATTICE	PALCE16V8Has16L2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has16L2	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has16L8	DIP20	
LATTICE	PALCE16V8Has16L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has16L8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has16P2	DIP20	
LATTICE	PALCE16V8Has16P2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has16P2	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has16P8	DIP20	
LATTICE	PALCE16V8Has16P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has16P8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has16R4	DIP20	
LATTICE	PALCE16V8Has16R4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has16R4	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has16R6	DIP20	
LATTICE	PALCE16V8Has16R6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has16R6	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has16R8	DIP20	
LATTICE	PALCE16V8Has16R8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has16R8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has16RP4	DIP20	
LATTICE	PALCE16V8Has16RP4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has16RP4	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has16RP6	DIP20	
LATTICE	PALCE16V8Has16RP6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has16RP6	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Has16RP8	DIP20	
LATTICE	PALCE16V8Has16RP8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Has16RP8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Q	DIP20	
LATTICE	PALCE16V8Q	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Q	SOIC20	PA20SO20D-EO-210

LATTICE	PALCE16V8Qas10H8	DIP20	
LATTICE	PALCE16V8Qas10H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas10H8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas10L8	DIP20	
LATTICE	PALCE16V8Qas10L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas10L8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas10P8	DIP20	
LATTICE	PALCE16V8Qas10P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas10P8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas12H6	DIP20	
LATTICE	PALCE16V8Qas12H6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas12H6	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas12L6	DIP20	
LATTICE	PALCE16V8Qas12L6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas12L6	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas12P6	DIP20	
LATTICE	PALCE16V8Qas12P6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas12P6	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas14H4	DIP20	
LATTICE	PALCE16V8Qas14H4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas14H4	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas14L4	DIP20	
LATTICE	PALCE16V8Qas14L4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas14L4	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas14P4	DIP20	
LATTICE	PALCE16V8Qas14P4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas14P4	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16H2	DIP20	
LATTICE	PALCE16V8Qas16H2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16H2	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16H8	DIP20	
LATTICE	PALCE16V8Qas16H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16H8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16L2	DIP20	
LATTICE	PALCE16V8Qas16L2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16L2	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16L8	DIP20	
LATTICE	PALCE16V8Qas16L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16L8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16P2	DIP20	
LATTICE	PALCE16V8Qas16P2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16P2	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16P8	DIP20	
LATTICE	PALCE16V8Qas16P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16P8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16R4	DIP20	
LATTICE	PALCE16V8Qas16R4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16R4	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16R6	DIP20	
LATTICE	PALCE16V8Qas16R6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16R6	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16R8	DIP20	
LATTICE	PALCE16V8Qas16R8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16R8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16RP4	DIP20	
LATTICE	PALCE16V8Qas16RP4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16RP4	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16RP6	DIP20	
LATTICE	PALCE16V8Qas16RP6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16RP6	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Qas16RP8	DIP20	
LATTICE	PALCE16V8Qas16RP8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Qas16RP8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Z	DIP20	
LATTICE	PALCE16V8Z	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Z	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas10H8	DIP20	
LATTICE	PALCE16V8Zas10H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas10H8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas10L8	DIP20	
LATTICE	PALCE16V8Zas10L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas10L8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas10P8	DIP20	

LATTICE	PALCE16V8Zas10P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas10P8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas12H6	DIP20	
LATTICE	PALCE16V8Zas12H6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas12H6	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas12L6	DIP20	
LATTICE	PALCE16V8Zas12L6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas12L6	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas12P6	DIP20	
LATTICE	PALCE16V8Zas12P6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas12P6	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas14H4	DIP20	
LATTICE	PALCE16V8Zas14H4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas14H4	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas14L4	DIP20	
LATTICE	PALCE16V8Zas14L4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas14L4	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas14P4	DIP20	
LATTICE	PALCE16V8Zas14P4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas14P4	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16H2	DIP20	
LATTICE	PALCE16V8Zas16H2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16H2	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16H8	DIP20	
LATTICE	PALCE16V8Zas16H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16H8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16L2	DIP20	
LATTICE	PALCE16V8Zas16L2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16L2	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16L8	DIP20	
LATTICE	PALCE16V8Zas16L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16L8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16P2	DIP20	
LATTICE	PALCE16V8Zas16P2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16P2	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16P8	DIP20	
LATTICE	PALCE16V8Zas16P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16P8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16R4	DIP20	
LATTICE	PALCE16V8Zas16R4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16R4	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16R6	DIP20	
LATTICE	PALCE16V8Zas16R6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16R6	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16R8	DIP20	
LATTICE	PALCE16V8Zas16R8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16R8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16RP4	DIP20	
LATTICE	PALCE16V8Zas16RP4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16RP4	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16RP6	DIP20	
LATTICE	PALCE16V8Zas16RP6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16RP6	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE16V8Zas16RP8	DIP20	
LATTICE	PALCE16V8Zas16RP8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALCE16V8Zas16RP8	SOIC20	PA20SO20D-EO-210
LATTICE	PALCE20RA10H	DIP24	
LATTICE	PALCE20RA10H	PLCC28	PA28PL28D
LATTICE	PALCE20RA10Q	DIP24	
LATTICE	PALCE20RA10Q	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-10/4	DIP24	
LATTICE	PALCE20V8H-10/4	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-10/4as14H8	DIP24	
LATTICE	PALCE20V8H-10/4as14H8	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-10/4as14L8	DIP24	
LATTICE	PALCE20V8H-10/4as14L8	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-10/4as14P8	DIP24	
LATTICE	PALCE20V8H-10/4as14P8	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-10/4as16H6	DIP24	
LATTICE	PALCE20V8H-10/4as16H6	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-10/4as16L6	DIP24	
LATTICE	PALCE20V8H-10/4as16L6	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-10/4as16P6	DIP24	



LATTICE	PALCE20V8H-15/4as20RP8	DIP24	PA28PL28D
LATTICE	PALCE20V8H-15/4as20RP8	PLCC28	
LATTICE	PALCE20V8H-25	DIP24	
LATTICE	PALCE20V8H-25	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4	DIP24	
LATTICE	PALCE20V8H-25/4	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as14H8	DIP24	
LATTICE	PALCE20V8H-25/4as14H8	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as14L8	DIP24	
LATTICE	PALCE20V8H-25/4as14L8	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as14P8	DIP24	
LATTICE	PALCE20V8H-25/4as14P8	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as16H6	DIP24	
LATTICE	PALCE20V8H-25/4as16H6	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as16L6	DIP24	
LATTICE	PALCE20V8H-25/4as16L6	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as16P6	DIP24	
LATTICE	PALCE20V8H-25/4as16P6	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as18H4	DIP24	
LATTICE	PALCE20V8H-25/4as18H4	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as18L4	DIP24	
LATTICE	PALCE20V8H-25/4as18L4	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as18P4	DIP24	
LATTICE	PALCE20V8H-25/4as18P4	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20H2	DIP24	
LATTICE	PALCE20V8H-25/4as20H2	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20H8	DIP24	
LATTICE	PALCE20V8H-25/4as20H8	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20L2	DIP24	
LATTICE	PALCE20V8H-25/4as20L2	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20L8	DIP24	
LATTICE	PALCE20V8H-25/4as20L8	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20P2	DIP24	
LATTICE	PALCE20V8H-25/4as20P2	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20P8	DIP24	
LATTICE	PALCE20V8H-25/4as20P8	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20R4	DIP24	
LATTICE	PALCE20V8H-25/4as20R4	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20R6	DIP24	
LATTICE	PALCE20V8H-25/4as20R6	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20R8	DIP24	
LATTICE	PALCE20V8H-25/4as20R8	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20RP4	DIP24	
LATTICE	PALCE20V8H-25/4as20RP4	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20RP6	DIP24	
LATTICE	PALCE20V8H-25/4as20RP6	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25/4as20RP8	DIP24	
LATTICE	PALCE20V8H-25/4as20RP8	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as14H8	DIP24	
LATTICE	PALCE20V8H-25as14H8	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as14L8	DIP24	
LATTICE	PALCE20V8H-25as14L8	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as14P8	DIP24	
LATTICE	PALCE20V8H-25as14P8	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as16H6	DIP24	
LATTICE	PALCE20V8H-25as16H6	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as16L6	DIP24	
LATTICE	PALCE20V8H-25as16L6	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as16P6	DIP24	
LATTICE	PALCE20V8H-25as16P6	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as18H4	DIP24	
LATTICE	PALCE20V8H-25as18H4	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as18L4	DIP24	
LATTICE	PALCE20V8H-25as18L4	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as18P4	DIP24	
LATTICE	PALCE20V8H-25as18P4	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as20H2	DIP24	
LATTICE	PALCE20V8H-25as20H2	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as20H8	DIP24	
LATTICE	PALCE20V8H-25as20H8	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as20L2	DIP24	
LATTICE	PALCE20V8H-25as20L2	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as20L8	DIP24	



LATTICE	PALCE20V8H-25as20L8	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as20P2	DIP24	
LATTICE	PALCE20V8H-25as20P2	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as20P8	DIP24	
LATTICE	PALCE20V8H-25as20P8	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as20R4	DIP24	
LATTICE	PALCE20V8H-25as20R4	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as20R6	DIP24	
LATTICE	PALCE20V8H-25as20R6	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as20R8	DIP24	
LATTICE	PALCE20V8H-25as20R8	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as20RP4	DIP24	
LATTICE	PALCE20V8H-25as20RP4	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as20RP6	DIP24	
LATTICE	PALCE20V8H-25as20RP6	PLCC28	PA28PL28D
LATTICE	PALCE20V8H-25as20RP8	DIP24	
LATTICE	PALCE20V8H-25as20RP8	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4	DIP24	
LATTICE	PALCE20V8Q-15/4	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as14H8	DIP24	
LATTICE	PALCE20V8Q-15/4as14H8	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as14L8	DIP24	
LATTICE	PALCE20V8Q-15/4as14L8	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as14P8	DIP24	
LATTICE	PALCE20V8Q-15/4as14P8	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as16H6	DIP24	
LATTICE	PALCE20V8Q-15/4as16H6	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as16L6	DIP24	
LATTICE	PALCE20V8Q-15/4as16L6	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as16P6	DIP24	
LATTICE	PALCE20V8Q-15/4as16P6	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as18H4	DIP24	
LATTICE	PALCE20V8Q-15/4as18H4	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as18L4	DIP24	
LATTICE	PALCE20V8Q-15/4as18L4	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as18P4	DIP24	
LATTICE	PALCE20V8Q-15/4as18P4	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as20H2	DIP24	
LATTICE	PALCE20V8Q-15/4as20H2	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as20H8	DIP24	
LATTICE	PALCE20V8Q-15/4as20H8	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as20L2	DIP24	
LATTICE	PALCE20V8Q-15/4as20L2	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as20L8	DIP24	
LATTICE	PALCE20V8Q-15/4as20L8	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as20P2	DIP24	
LATTICE	PALCE20V8Q-15/4as20P2	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as20P8	DIP24	
LATTICE	PALCE20V8Q-15/4as20P8	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as20R4	DIP24	
LATTICE	PALCE20V8Q-15/4as20R4	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as20R6	DIP24	
LATTICE	PALCE20V8Q-15/4as20R6	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as20R8	DIP24	
LATTICE	PALCE20V8Q-15/4as20R8	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as20RP4	DIP24	
LATTICE	PALCE20V8Q-15/4as20RP4	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as20RP6	DIP24	
LATTICE	PALCE20V8Q-15/4as20RP6	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-15/4as20RP8	DIP24	
LATTICE	PALCE20V8Q-15/4as20RP8	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4	DIP24	
LATTICE	PALCE20V8Q-25/4	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as14H8	DIP24	
LATTICE	PALCE20V8Q-25/4as14H8	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as14L8	DIP24	
LATTICE	PALCE20V8Q-25/4as14L8	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as14P8	DIP24	
LATTICE	PALCE20V8Q-25/4as14P8	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as16H6	DIP24	
LATTICE	PALCE20V8Q-25/4as16H6	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as16L6	DIP24	
LATTICE	PALCE20V8Q-25/4as16L6	PLCC28	PA28PL28D

LATTICE	PALCE20V8Q-25/4as16P6	DIP24	
LATTICE	PALCE20V8Q-25/4as16P6	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as18H4	DIP24	
LATTICE	PALCE20V8Q-25/4as18H4	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as18L4	DIP24	
LATTICE	PALCE20V8Q-25/4as18L4	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as18P4	DIP24	
LATTICE	PALCE20V8Q-25/4as18P4	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as20H2	DIP24	
LATTICE	PALCE20V8Q-25/4as20H2	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as20H8	DIP24	
LATTICE	PALCE20V8Q-25/4as20H8	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as20L2	DIP24	
LATTICE	PALCE20V8Q-25/4as20L2	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as20L8	DIP24	
LATTICE	PALCE20V8Q-25/4as20L8	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as20P2	DIP24	
LATTICE	PALCE20V8Q-25/4as20P2	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as20P8	DIP24	
LATTICE	PALCE20V8Q-25/4as20P8	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as20R4	DIP24	
LATTICE	PALCE20V8Q-25/4as20R4	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as20R6	DIP24	
LATTICE	PALCE20V8Q-25/4as20R6	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as20R8	DIP24	
LATTICE	PALCE20V8Q-25/4as20R8	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as20RP4	DIP24	
LATTICE	PALCE20V8Q-25/4as20RP4	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as20RP6	DIP24	
LATTICE	PALCE20V8Q-25/4as20RP6	PLCC28	PA28PL28D
LATTICE	PALCE20V8Q-25/4as20RP8	DIP24	
LATTICE	PALCE20V8Q-25/4as20RP8	PLCC28	PA28PL28D
LATTICE	PALCE22V10H	DIP24	
LATTICE	PALCE22V10H	PLCC28	PA28PL28D
LATTICE	PALCE22V10Q	DIP24	
LATTICE	PALCE22V10Q	PLCC28	PA28PL28D
LATTICE	PALCE22V10Z	DIP24	
LATTICE	PALCE22V10Z	PLCC28	PA28PL28D
LATTICE	PALCE26V12H	DIP28	
LATTICE	PALCE26V12H	PLCC28	PA28PL28D
LATTICE	PALCE26V12H/4	DIP28	
LATTICE	PALCE26V12H/4	PLCC28	PA28PL28D
LATTICE	PALCE26V12H/4-10	DIP28	
LATTICE	PALCE26V12H/4-10	PLCC28	PA28PL28D
LATTICE	PALCE29M16H	DIP24	
LATTICE	PALCE29M16H	PLCC28	PA28PL28D
LATTICE	PALCE29MA16H	DIP24	
LATTICE	PALCE29MA16H	PLCC28	PA28PL28D
LATTICE	PALCE610H	DIP24	
LATTICE	PALCE610H	PLCC28	PA28PL28D
LATTICE	PALLV16V8	DIP20	
LATTICE	PALLV16V8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as10H8	DIP20	
LATTICE	PALLV16V8as10H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as10H8	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as10L8	DIP20	
LATTICE	PALLV16V8as10L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as10L8	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as10P8	DIP20	
LATTICE	PALLV16V8as10P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as10P8	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as12H6	DIP20	
LATTICE	PALLV16V8as12H6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as12H6	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as12L6	DIP20	
LATTICE	PALLV16V8as12L6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as12L6	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as12P6	DIP20	
LATTICE	PALLV16V8as12P6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as12P6	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as14H4	DIP20	
LATTICE	PALLV16V8as14H4	PLCC20	PA20LC20D[Dead Bug]

LATTICE	PALLV16V8as14H4	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as14L4	DIP20	
LATTICE	PALLV16V8as14L4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as14L4	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as14P4	DIP20	
LATTICE	PALLV16V8as14P4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as14P4	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16H2	DIP20	
LATTICE	PALLV16V8as16H2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16H2	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16H8	DIP20	
LATTICE	PALLV16V8as16H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16H8	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16L2	DIP20	
LATTICE	PALLV16V8as16L2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16L2	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16L8	DIP20	
LATTICE	PALLV16V8as16L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16L8	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16P2	DIP20	
LATTICE	PALLV16V8as16P2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16P2	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16P8	DIP20	
LATTICE	PALLV16V8as16P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16P8	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16R4	DIP20	
LATTICE	PALLV16V8as16R4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16R4	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16R6	DIP20	
LATTICE	PALLV16V8as16R6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16R6	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16R8	DIP20	
LATTICE	PALLV16V8as16R8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16R8	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16RP4	DIP20	
LATTICE	PALLV16V8as16RP4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16RP4	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16RP6	DIP20	
LATTICE	PALLV16V8as16RP6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16RP6	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8as16RP8	DIP20	
LATTICE	PALLV16V8as16RP8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8as16RP8	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Z	DIP20	
LATTICE	PALLV16V8Z	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Z	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas10H8	DIP20	
LATTICE	PALLV16V8Zas10H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas10H8	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas10L8	DIP20	
LATTICE	PALLV16V8Zas10L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas10L8	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas10P8	DIP20	
LATTICE	PALLV16V8Zas10P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas10P8	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas12H6	DIP20	
LATTICE	PALLV16V8Zas12H6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas12H6	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas12L6	DIP20	
LATTICE	PALLV16V8Zas12L6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas12L6	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas12P6	DIP20	
LATTICE	PALLV16V8Zas12P6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas12P6	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas14H4	DIP20	
LATTICE	PALLV16V8Zas14H4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas14H4	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas14L4	DIP20	
LATTICE	PALLV16V8Zas14L4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas14L4	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas14P4	DIP20	
LATTICE	PALLV16V8Zas14P4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas14P4	SOIC20	PA20SO20D-EO-210

LATTICE	PALLV16V8Zas16H2	DIP20	
LATTICE	PALLV16V8Zas16H2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16H2	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16H8	DIP20	
LATTICE	PALLV16V8Zas16H8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16H8	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16L2	DIP20	
LATTICE	PALLV16V8Zas16L2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16L2	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16L8	DIP20	
LATTICE	PALLV16V8Zas16L8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16L8	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16P2	DIP20	
LATTICE	PALLV16V8Zas16P2	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16P2	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16P8	DIP20	
LATTICE	PALLV16V8Zas16P8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16P8	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16R4	DIP20	
LATTICE	PALLV16V8Zas16R4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16R4	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16R6	DIP20	
LATTICE	PALLV16V8Zas16R6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16R6	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16R8	DIP20	
LATTICE	PALLV16V8Zas16R8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16R8	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16RP4	DIP20	
LATTICE	PALLV16V8Zas16RP4	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16RP4	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16RP6	DIP20	
LATTICE	PALLV16V8Zas16RP6	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16RP6	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV16V8Zas16RP8	DIP20	
LATTICE	PALLV16V8Zas16RP8	PLCC20	PA20LC20D[Dead Bug]
LATTICE	PALLV16V8Zas16RP8	SOIC20	PA20SO20D-EO-210
LATTICE	PALLV22V10	DIP24	
LATTICE	PALLV22V10	PLCC28	PA28PL28D
LATTICE	PALLV22V10Z	DIP24	
LATTICE	PALLV22V10Z	PLCC28	PA28PL28D
LINVEX TECHNOLOGY	LX59CF2010	TSOP32	PA32TS20/PA32TS32D-20
LINVEX TECHNOLOGY	LX59CF2128	TSOP32	PA32TS20/PA32TS32D-20
LINVEX TECHNOLOGY	LX59CF4010	TSOP40	PA40TS40D
LINVEX TECHNOLOGY	LX59CF4128	TSOP32	PA32TS20/PA32TS32D-20
LINVEX TECHNOLOGY	LX59CF432	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX10FMAXDPC	DIP40	
MACRONIX	MX10FMAXDQC	PLCC44	PA44-48U
MACRONIX	MX23C1000PC	DIP28	
MACRONIX	MX23C1010MC	SOP32	PA44SO44D
MACRONIX	MX23C1010PC	DIP32	
MACRONIX	MX23C1010QC	PLCC32	PA32PL32D
MACRONIX	MX23C2000MC	SOP32	PA44SO44D
MACRONIX	MX23C2000PC	DIP32	
MACRONIX	MX23C2000QC	PLCC32	PA32PL32D
MACRONIX	MX23C4000MC	SOP32	PA44SO44D
MACRONIX	MX23C4000PC	DIP32	
MACRONIX	MX23C4000QC	PLCC32	PA32PL32D
MACRONIX	MX23C8000MC	SOP32	PA44SO44D
MACRONIX	MX23C8000PC	DIP32	
MACRONIX	MX23C8000QC	PLCC32	PA32PL32D
MACRONIX	MX25L1005	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L1005	WSON8	PA8SON8D(6x5)
MACRONIX	MX25L1005A	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L1005C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L1005C	USON8	PA8SON8D(2x3)
MACRONIX	MX25L1006E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L1006E	USON8	PA8SON8D(2x3)
MACRONIX	MX25L1021E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L1025C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L1026E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L12805D	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L12805N	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L12833F	SOP16	PA28SO28D-EO-300

MACRONIX	MX25L12833F	SOP8	PA20SQ20D-EO-210
MACRONIX	MX25L12833F	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L12833F	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L12833F (QPI)	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L12833F (QPI)	SOP8	PA20SQ20D-EO-210
MACRONIX	MX25L12833F (QPI)	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L12833F (QPI)	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L12835E	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L12835E	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L12835F	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L12835F	SOP8	PA20SQ20D-EO-210
MACRONIX	MX25L12835F	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L12835F	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L12835F (QPI)	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L12835F (QPI)	SOP8	PA20SQ20D-EO-210
MACRONIX	MX25L12835F (QPI)	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L12835F (QPI)	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L12845E	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L12845E	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L12855E	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L12855F	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L12855F	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25L12855F (QPI)	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L12855F (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25L12872F	SOP8	PA20SQ20D-EO-210
MACRONIX	MX25L12872F	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L12872F (QPI)	SOP8	PA20SQ20D-EO-210
MACRONIX	MX25L12872F (QPI)	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L12873F	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L12873F	SOP8	PA20SQ20D-EO-210
MACRONIX	MX25L12873F	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L12873F (QPI)	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L12873F (QPI)	SOP8	PA20SQ20D-EO-210
MACRONIX	MX25L12873F (QPI)	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L1602M	SOP28	PA28SQ28DA-EC-330
MACRONIX	MX25L1605	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L1605A	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L1605A	SOP8	PA20SQ20D-EO-210
MACRONIX	MX25L1605A	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L1605D	DIP8	
MACRONIX	MX25L1605D	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L1605D	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L1605D	SOP8	PA20SQ20D-EO-210
MACRONIX	MX25L1605D	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L1606E	SOP8	PA20SQ20D-EO-210
MACRONIX	MX25L1635D	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L1635D	SOP8	PA20SQ20D-EO-210
MACRONIX	MX25L1635D	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L1635E	SOP8	PA20SQ20D-EO-210
MACRONIX	MX25L1673E	SOP8	PA20SQ20D-EO-210
MACRONIX	MX25L1673E	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L2005	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L2005	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L2005C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L2005C	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L2006E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L2006E	USO8	PA8SON8D(2x3)
MACRONIX	MX25L2006E	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L2025	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L2025C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L25635E	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L25635E	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L25635F	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L25635F	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L25635F (QPI)	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L25635F (QPI)	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L25655F	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L25655F	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25L25655F (QPI)	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L25655F (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25L25735E	SOP16	PA28SQ28D-EO-300
MACRONIX	MX25L25735E	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L25735F	SOP16	PA28SQ28D-EO-300

MACRONIX	MX25L25735F	WSON8	PA8SON8DA(8x6)
MACRONIX	MX25L25735F (QPI)	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L25735F (QPI)	WSON8	PA8SON8DA(8x6)
MACRONIX	MX25L3202M	SOP32	PA32SO32D-1
MACRONIX	MX25L3205	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L3205A	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L3205A	WSON8	PA8SON8DA(8x6)
MACRONIX	MX25L3205D	DIP8	
MACRONIX	MX25L3205D	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L3205D	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L3205D	WSON8	PA8SON8D(6x5)
MACRONIX	MX25L3206E	DIP8	
MACRONIX	MX25L3206E	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L3206E	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L3206E	WSON8	PA8SON8D(6x5)
MACRONIX	MX25L3233F	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L3233F	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L3233F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L3233F	USON8	PA8SON8D(4x3)
MACRONIX	MX25L3233F	WSON8	PA8SON8D(6x5)
MACRONIX	MX25L3235D	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L3235D	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L3235D	WSON8	PA8SON8D(6x5)
MACRONIX	MX25L3235E	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L3235E	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L3235E	WSON8	PA8SON8D(6x5)
MACRONIX	MX25L3237D	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L3237D	WSON8	PA8SON8D(6x5)
MACRONIX	MX25L3255D	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L3255E	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L3255E	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25L3273E	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L3273E	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L3273E	VSOP8	PA20SO20D-EO-210
MACRONIX	MX25L3273E	WSON8	PA8SON8D(6x5)
MACRONIX	MX25L3291F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L4005	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L4005	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L4005	WSON8	PA8SON8D(6x5)
MACRONIX	MX25L4005A	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L4005A	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L4005A	WSON8	PA8SON8D(6x5)
MACRONIX	MX25L4005C	DIP8	
MACRONIX	MX25L4005C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L4005C	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L4005C	WSON8	PA8SON8D(6x5)
MACRONIX	MX25L4006E	DIP8	
MACRONIX	MX25L4006E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L4006E	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L4006E	USON8	PA8SON8D(2x3)
MACRONIX	MX25L4006E	WSON8	PA8SON8D(6x5)
MACRONIX	MX25L4025A	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L4025C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L4026E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L512	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L512	USON8	PA8SON8D(2x3)
MACRONIX	MX25L5121E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L5121E	TSSOP8	PA8TSS8D
MACRONIX	MX25L5121E	USON8	PA8SON8D(2x3)
MACRONIX	MX25L51245G	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L51245G	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25L51245G	WSON8	PA8SON8DA(8x6)
MACRONIX	MX25L51245G (QPI)	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L51245G (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25L51245G (QPI)	WSON8	PA8SON8DA(8x6)
MACRONIX	MX25L51273G	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L51273G	WSON8	PA8SON8DA(8x6)
MACRONIX	MX25L51273G (QPI)	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L51273G (QPI)	WSON8	PA8SON8DA(8x6)
MACRONIX	MX25L512C	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L512C	TSSOP8	PA8TSS8D
MACRONIX	MX25L512C	USON8	PA8SON8D(2x3)
MACRONIX	MX25L6402AM	SOP28	PA28SO28DA-EC-330

MACRONIX	MX25L6402M	SOP32	PA32SO32D-1
MACRONIX	MX25L6405	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L6405D	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L6405D	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L6406E	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L6406E	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L6406E	VSOP8	PA20SO20D-EO-210
MACRONIX	MX25L6406E	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L6406E	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L6433F	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L6433F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L6433F	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L6433F	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L6435E	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L6435E	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L6435E	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L6435E	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L6436E	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L6436E	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L6436E	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L6445E	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L6445E	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L6445E	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L6446E	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L6446E	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L6446E	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25L6455E	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L6473E	SOP16	PA28SO28D-EO-300
MACRONIX	MX25L6473E	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L6473E	VSOP8	PA20SO20D-EO-210
MACRONIX	MX25L6473E	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L6473F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L6473F	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L8005	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L8005	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L8005	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L8006E	DIP8	
MACRONIX	MX25L8006E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L8006E	SOP8	PA20SO20D-EO-210
MACRONIX	MX25L8006E	WSO8	PA8SON8D(6x5)
MACRONIX	MX25L8025	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L802M	SOP28	PA28SO28DA-EC-330
MACRONIX	MX25L8035E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25L8035E	SOP8	PA20SO20D-EO-210
MACRONIX	MX25LM51245G (Octa I/O / STR )	SOP16	PA28SO28D-EO-300
MACRONIX	MX25LM51245G (Octa I/O / STR )	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25LM51245G (SPI)	SOP16	PA28SO28D-EO-300
MACRONIX	MX25LM51245G (SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25R1035F	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25R1035F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25R1035F	TSSOP8	PA8TSS8D
MACRONIX	MX25R1035F	USO8	PA8SON8D(2x3)
MACRONIX	MX25R1035FZU	USO8	HBP8USO848DB(2x3)
MACRONIX	MX25R1635F	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25R1635F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25R1635F	USO8	PA8SON8D(2x3)
MACRONIX	MX25R1635F	WSO8	PA8SON8D(6x5)
MACRONIX	MX25R1635FZU	USO8	HBP8USO848DB(2x3)
MACRONIX	MX25R2035F	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25R2035F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25R2035F	TSSOP8	PA8TSS8D
MACRONIX	MX25R2035F	USO8	PA8SON8D(2x3)
MACRONIX	MX25R2035F	WSO8	PA8SON8D(6x5)
MACRONIX	MX25R2035FZU	USO8	HBP8USO848DB(2x3)
MACRONIX	MX25R3235F	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25R3235F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25R3235F	USO8	PA8SON8D(2x3)
MACRONIX	MX25R3235F	WSO8	PA8SON8D(6x5)
MACRONIX	MX25R4035F	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25R4035F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25R4035F	USO8	PA8SON8D(2x3)
MACRONIX	MX25R4035F	WSO8	PA8SON8D(6x5)
MACRONIX	MX25R4035FZU	USO8	HBP8USO848DB(2x3)

MACRONIX	MX25R512F	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25R512F	TSSOP8	PA8TSS8D
MACRONIX	MX25R512F	USON8	PA8SON8D(2x3)
MACRONIX	MX25R512FZU	USON8	HBP8USON48DB(2x3)
MACRONIX	MX25R6435F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25R6435F	WSON8	PA8SON8D(6x5)
MACRONIX	MX25R8035F	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25R8035F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25R8035F	USON8	PA8SON8D(2x3)
MACRONIX	MX25R8035F	WSON8	PA8SON8D(6x5)
MACRONIX	MX25R8035FZU	USON8	HBP8USON48DB(2x3)
MACRONIX	MX25U1001E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25U1001E	TSSOP8	PA8TSS8D
MACRONIX	MX25U1001E	USON8	PA8SON8D(2x3)
MACRONIX	MX25U12832F	SOP16	PA28SO28D-EO-300
MACRONIX	MX25U12832F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U12832F	WSON8	PA8SON8D(6x5)
MACRONIX	MX25U12832F	WSON8	PA8SON8DA(8x6)
MACRONIX	MX25U12835F	SOP16	PA28SO28D-EO-300
MACRONIX	MX25U12835F	WSON8	PA8SON8D(6x5)
MACRONIX	MX25U12835F	WSON8	PA8SON8DA(8x6)
MACRONIX	MX25U12835F (QPI)	SOP16	PA28SO28D-EO-300
MACRONIX	MX25U12835F (QPI)	WSON8	PA8SON8D(6x5)
MACRONIX	MX25U12835F (QPI)	WSON8	PA8SON8DA(8x6)
MACRONIX	MX25U12835FM	SOIC16	HA16SO48DP(300mil 1.8V)
MACRONIX	MX25U12835FM2	SOIC8	HA8SO48DAC(210mil 1.8V)
MACRONIX	MX25U12835FZN	WSON8	HA8SON48DG(6x5 1.8V)
MACRONIX	MX25U12843G	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U12872F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U12872F	WSON8	PA8SON8D(6x5)
MACRONIX	MX25U12891F	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25U12891F (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25U12892F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U1632F	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25U1632F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U1632F	USON8	PA8SON8D(2x3)
MACRONIX	MX25U1632F (QPI)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25U1632F (QPI)	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U1632F (QPI)	USON8	PA8SON8D(2x3)
MACRONIX	MX25U1633F	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25U1633F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U1633F	USON8	PA8SON8D(2x3)
MACRONIX	MX25U1635E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25U1635E	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U1635E	WSON8	PA8SON8D(6x5)
MACRONIX	MX25U1635E (QPI)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25U1635E (QPI)	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U1635E (QPI)	WSON8	PA8SON8D(6x5)
MACRONIX	MX25U1635F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U1635F	USON8	PA8SON8D(4x3)
MACRONIX	MX25U1635F	WSON8	PA8SON8D(6x5)
MACRONIX	MX25U1635F (QPI)	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U1635F (QPI)	USON8	PA8SON8D(4x3)
MACRONIX	MX25U1635F (QPI)	WSON8	PA8SON8D(6x5)
MACRONIX	MX25U2032E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25U2032E	VSOP8	PA16SO16D-EO-150
MACRONIX	MX25U2032E	WSON8	PA8SON8D(6x5)
MACRONIX	MX25U2033E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25U2033E	USON8	PA8SON8D(4x3)
MACRONIX	MX25U2033E	VSOP8	PA16SO16D-EO-150
MACRONIX	MX25U2033E	WSON8	PA8SON8D(6x5)
MACRONIX	MX25U2035F	USON8	PA8SON8D(2x3)
MACRONIX	MX25U25635F	SOP16	PA28SO28D-EO-300
MACRONIX	MX25U25635F	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25U25635F	WSON8	PA8SON8DA(8x6)
MACRONIX	MX25U25635F (QPI)	SOP16	PA28SO28D-EO-300
MACRONIX	MX25U25635F (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25U25635F (QPI)	WSON8	PA8SON8DA(8x6)
MACRONIX	MX25U25643G	SOIC16	PA28SO28D-EO-300
MACRONIX	MX25U25643G	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U25643G	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25U25643G	WSON8	PA8SON8D(6x5)
MACRONIX	MX25U25643G	WSON8	PA8SON8DA(8x6)



MACRONIX	MX25U25643G (QPI)	SOIC16	PA28SO28D-EO-300
MACRONIX	MX25U25643G (QPI)	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U25643G (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25U25643G (QPI)	WSO8	PA8SON8D(6x5)
MACRONIX	MX25U25643G (QPI)	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25U25645G	SOP16	PA28SO28D-EO-300
MACRONIX	MX25U25645G	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25U25645G	WSO8	PA8SON8DA(8x6)
MACRONIX	MX25U3232F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U3232F	USO8	PA8SON8D(4x3)
MACRONIX	MX25U3232F	WSO8	PA8SON8D(6x5)
MACRONIX	MX25U3235F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U3235F	USO8	PA8SON8D(4x3)
MACRONIX	MX25U3235F	WSO8	PA8SON8D(6x5)
MACRONIX	MX25U3235F (QPI)	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U3235F (QPI)	USO8	PA8SON8D(4x3)
MACRONIX	MX25U3235F (QPI)	WSO8	PA8SON8D(6x5)
MACRONIX	MX25U3235FM2	SOIC8	HA8SO48DAC(210mil 1.8V)
MACRONIX	MX25U4032E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25U4032E	VSOP8	PA16SO16D-EO-150
MACRONIX	MX25U4032E	WSO8	PA8SON8D(6x5)
MACRONIX	MX25U4033E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25U4033E	USO8	PA8SON8D(4x3)
MACRONIX	MX25U4033E	WSO8	PA8SON8D(6x5)
MACRONIX	MX25U4035F	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25U4035F	USO8	PA8SON8D(2x3)
MACRONIX	MX25U5121E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25U5121E	TSSOP8	PA8TSS8D
MACRONIX	MX25U5121E	USO8	PA8SON8D(2x3)
MACRONIX	MX25U6432F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U6432F	USO8	PA8SON8D(4x3)
MACRONIX	MX25U6432F	WSO8	PA8SON8D(6x5)
MACRONIX	MX25U6435F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U6435F	USO8	PA8SON8D(4x3)
MACRONIX	MX25U6435F	WSO8	PA8SON8D(6x5)
MACRONIX	MX25U6435F (QPI)	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U6435F (QPI)	USO8	PA8SON8D(4x3)
MACRONIX	MX25U6435F (QPI)	WSO8	PA8SON8D(6x5)
MACRONIX	MX25U6435FM2	SOIC8	HA8SO48DAC(210mil 1.8V)
MACRONIX	MX25U6435FZN	WSO8	HA8SON48DG(6x5 1.8V)
MACRONIX	MX25U6472F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U8032E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25U8032E	VSOP8	PA16SO16D-EO-150
MACRONIX	MX25U8032E	WSO8	PA8SON8D(6x5)
MACRONIX	MX25U8033E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25U8033E	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U8033E	WSO8	PA8SON8D(6x5)
MACRONIX	MX25U8035E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25U8035E	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U8035E	WSO8	PA8SON8D(6x5)
MACRONIX	MX25U8035E (QPI)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25U8035E (QPI)	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U8035E (QPI)	WSO8	PA8SON8D(6x5)
MACRONIX	MX25U8035EM1	SOIC8	HA8SO48DAD(150mil 1.8V)
MACRONIX	MX25U8035EM2	SOIC8	HA8SO48DAC(210mil 1.8V)
MACRONIX	MX25U8035EZN	WSO8	HA8SON48DG(6x5 1.8V)
MACRONIX	MX25U8035F	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25U8035F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25U8035F	USO8	PA8SON8D(2x3)
MACRONIX	MX25UM25345G (Octa I/O / DTR )	SOP16	PA28SO28D-EO-300
MACRONIX	MX25UM25345G (Octa I/O / DTR )	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25UM25345G (Octa I/O / STR )	SOP16	PA28SO28D-EO-300
MACRONIX	MX25UM25345G (Octa I/O / STR )	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25UM25345G (SPI)	SOP16	PA28SO28D-EO-300
MACRONIX	MX25UM25345G (SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25UW12345G (Octa I/O / DTR )	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25UW12345G (Octa I/O / STR )	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25UW12345G (SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25UW25345G (Octa I/O / DTR )	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25UW25345G (Octa I/O / STR )	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25UW25345G (SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25UW51245G (Octa I/O / DTR )	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25UW51245G (Octa I/O / STR )	TFBGA24	PA24BG24D(6x8mm)5x5

MACRONIX	MX25UW51245G (SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25UW51345G (Octa I/O / DTR)	) TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25UW51345G (Octa I/O / STR)	) TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25UW51345G (SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25UW6345G (Octa I/O / DTR)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25UW6345G (Octa I/O / STR)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25UW6345G (SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25V1006E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25V1006E	TSSOP8	PA8TSS8D
MACRONIX	MX25V1006E	USON8	PA8SON8D(2x3)
MACRONIX	MX25V1006EZU	USON8	HBP8USON48DB(2x3)
MACRONIX	MX25V16066	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25V16066	SOP8	PA20SO20D-EO-210
MACRONIX	MX25V16066	WSON8	PA8SON8D(6x5)
MACRONIX	MX25V16066 (Dual I/O)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25V16066 (Dual I/O)	SOP8	PA20SO20D-EO-210
MACRONIX	MX25V16066 (Dual I/O)	WSON8	PA8SON8D(6x5)
MACRONIX	MX25V1606F	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25V1606F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25V1606F	USON8	PA8SON8D(2x3)
MACRONIX	MX25V1635F	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25V1635F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25V1635F	USON8	PA8SON8D(2x3)
MACRONIX	MX25V1635F	USON8	PA8SON8D(4x3)
MACRONIX	MX25V1635F	WSON8	PA8SON8D(6x5)
MACRONIX	MX25V2006E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25V2006E	WSON8	PA8SON8D(6x5)
MACRONIX	MX25V2006EZU	USON8	HBP8USON48DB(2x3)
MACRONIX	MX25V4005	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25V4005	WSON8	PA8SON8D(6x5)
MACRONIX	MX25V40066	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25V40066	SOP8	PA20SO20D-EO-210
MACRONIX	MX25V40066	USON8	PA8SON8D(2x3)
MACRONIX	MX25V40066 (Dual I/O)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25V40066 (Dual I/O)	SOP8	PA20SO20D-EO-210
MACRONIX	MX25V40066 (Dual I/O)	USON8	PA8SON8D(2x3)
MACRONIX	MX25V4035	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25V4035	WSON8	PA8SON8D(6x5)
MACRONIX	MX25V4035F	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25V4035F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25V4035F	TSSOP8	PA8TSS8D
MACRONIX	MX25V4035F	USON8	PA8SON8D(2x3)
MACRONIX	MX25V4035F	WSON8	PA8SON8D(6x5)
MACRONIX	MX25V512E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25V512E	TSSOP8	PA8TSS8D
MACRONIX	MX25V512E	USON8	PA8SON8D(2x3)
MACRONIX	MX25V512EZU	USON8	HBP8USON48DB(2x3)
MACRONIX	MX25V6433F	SOP16	PA28SO28D-EO-300
MACRONIX	MX25V6433F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25V6433F	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX25V6433F	WSON8	PA8SON8D(6x5)
MACRONIX	MX25V8005	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25V8005	WSON8	PA8SON8D(6x5)
MACRONIX	MX25V80066	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25V80066	SOP8	PA20SO20D-EO-210
MACRONIX	MX25V80066	USON8	PA8SON8D(2x3)
MACRONIX	MX25V80066	WSON8	PA8SON8D(6x5)
MACRONIX	MX25V80066 (Dual I/O)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25V80066 (Dual I/O)	SOP8	PA20SO20D-EO-210
MACRONIX	MX25V80066 (Dual I/O)	USON8	PA8SON8D(2x3)
MACRONIX	MX25V80066 (Dual I/O)	WSON8	PA8SON8D(6x5)
MACRONIX	MX25V8035	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25V8035	WSON8	PA8SON8D(6x5)
MACRONIX	MX25V8035F	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MACRONIX	MX25V8035F	SOP8	PA20SO20D-EO-210
MACRONIX	MX25V8035F	USON8	PA8SON8D(2x3)
MACRONIX	MX25V8035F	WSON8	PA8SON8D(6x5)
MACRONIX	MX26C1000A	DIP32	
MACRONIX	MX26C1000A	PLCC32	PA32PL32D
MACRONIX	MX26C1000B	DIP32	
MACRONIX	MX26C1000B	PLCC32	PA32PL32D
MACRONIX	MX26C2000B	DIP32	
MACRONIX	MX26C2000B	PLCC32	PA32PL32D

MACRONIX	MX26C512A	DIP28	
MACRONIX	MX26F128J3	EBGA64	PA64BGA48D/HA64BGA48D
MACRONIX	MX26F640J3	EBGA64	PA64BGA48D/HA64BGA48D
MACRONIX	MX26F640J3	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
MACRONIX	MX26L3220	TSOP48	PA48TS48D
MACRONIX	MX26L6419	TSOP48	PA48TS48D
MACRONIX	MX26L6420MC	SOP44	PA44SO44D
MACRONIX	MX26L6420TC	TSOP48	PA48TS48D
MACRONIX	MX26LV004BQC	PLCC32	PA32PL32D
MACRONIX	MX26LV004BTC	TSOP40	PA40TS40D
MACRONIX	MX26LV004TQC	PLCC32	PA32PL32D
MACRONIX	MX26LV004TTC	TSOP40	PA40TS40D
MACRONIX	MX26LV008BTC	TSOP40	PA40TS40D
MACRONIX	MX26LV008TTC	TSOP40	PA40TS40D
MACRONIX	MX26LV128J3	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
MACRONIX	MX26LV160ABTC	TSOP48	PA48TS48D1
MACRONIX	MX26LV160ATTC	TSOP48	PA48TS48D1
MACRONIX	MX26LV160BTC	TSOP48	PA48TS48D1
MACRONIX	MX26LV160TTC	TSOP48	PA48TS48D1
MACRONIX	MX26LV400BTC	TSOP48	PA48TS48D1
MACRONIX	MX26LV400TTC	TSOP48	PA48TS48D1
MACRONIX	MX26LV800BTC	TSOP48	PA48TS48D1
MACRONIX	MX26LV800TTC	TSOP48	PA48TS48D1
MACRONIX	MX27C1000	DIP32	
MACRONIX	MX27C1000	PLCC32	PA32PL32D
MACRONIX	MX27C1000	SOP32	PA32SO32D-EO-450
MACRONIX	MX27C1000	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX27C1000A	DIP32	
MACRONIX	MX27C1000A	PLCC32	PA32PL32D
MACRONIX	MX27C1000A	SOP32	PA32SO32D-EO-450
MACRONIX	MX27C1000A	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX27C1001	DIP32	
MACRONIX	MX27C1001	SOP32	PA32SO32D-EO-450
MACRONIX	MX27C1024	DIP40	
MACRONIX	MX27C1024	PLCC44	PA44-48U
MACRONIX	MX27C1024	SOP40	PA40SO40D-EO-450
MACRONIX	MX27C1024	TSOP40	PA40TS40D
MACRONIX	MX27C1100	DIP40	
MACRONIX	MX27C2000	DIP32	
MACRONIX	MX27C2000	PLCC32	PA32PL32D
MACRONIX	MX27C2000	SOP32	PA32SO32D-EO-450
MACRONIX	MX27C2000	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX27C2000A	DIP32	
MACRONIX	MX27C2000A	PLCC32	PA32PL32D
MACRONIX	MX27C2000A	SOP32	PA32SO32D-EO-450
MACRONIX	MX27C2000A	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX27C2048	DIP40	
MACRONIX	MX27C2048	PLCC44	PA44-48U
MACRONIX	MX27C2048	TSOP40	PA40TS40D
MACRONIX	MX27C2100	DIP40	
MACRONIX	MX27C256	DIP28	
MACRONIX	MX27C256	PLCC32	PA32PL28D-YA
MACRONIX	MX27C256	TSOP28	PA28TS28D-EO
MACRONIX	MX27C4000	DIP32	
MACRONIX	MX27C4000	PLCC32	PA32PL32D
MACRONIX	MX27C4000	SOIC32	PA32SO32D-EO-450
MACRONIX	MX27C4000	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX27C4000A	DIP32	
MACRONIX	MX27C4000A	PLCC32	PA32PL32D
MACRONIX	MX27C4000A	SOIC32	PA32SO32D-EO-450
MACRONIX	MX27C4000A	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX27C4096	DIP40	
MACRONIX	MX27C4096	PLCC44	PA44-48U
MACRONIX	MX27C4100	DIP40	
MACRONIX	MX27C4100	SOP40	PA40SO40D-EO-450
MACRONIX	MX27C4111	DIP40	
MACRONIX	MX27C4111	SOP40	PA40SO40D-EO-450
MACRONIX	MX27C512	DIP28	
MACRONIX	MX27C512	PLCC32	PA32PL28D-YA
MACRONIX	MX27C512	TSOP28	PA28TS28D-EO
MACRONIX	MX27C516	DIP40	
MACRONIX	MX27C516	PLCC44	PA44-48U
MACRONIX	MX27C516	TSOP40	PA40TS40D

MACRONIX	MX27C64	DIP28	
MACRONIX	MX27C8000	DIP32	
MACRONIX	MX27C8000	PLCC32	PA32PL32D
MACRONIX	MX27C8000	SOP32	PA32SO32D-EO-450
MACRONIX	MX27C8000	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX27C8000A	DIP32	
MACRONIX	MX27C8000A	PLCC32	PA32PL32D
MACRONIX	MX27C8000A	SOP32	PA32SO32D-EO-450
MACRONIX	MX27C8000A	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX27C8100	DIP42	
MACRONIX	MX27C8100	SOP44	PA44SO44D
MACRONIX	MX27C8111	DIP42	
MACRONIX	MX27C8111	SOP44	PA44SO44D
MACRONIX	MX27L1000	DIP32	
MACRONIX	MX27L1000	PLCC32	PA32PL32D
MACRONIX	MX27L1000	SOP32	PA32SO32D-EO-450
MACRONIX	MX27L1000	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX27L1024	DIP40	
MACRONIX	MX27L1024	PLCC44	PA44-48U
MACRONIX	MX27L1024	SOP40	PA40SO40D-EO-450
MACRONIX	MX27L1024	TSOP40	PA40TS40D
MACRONIX	MX27L2000	DIP32	
MACRONIX	MX27L2000	PLCC32	PA32PL32D
MACRONIX	MX27L2000	SOP32	PA32SO32D-EO-450
MACRONIX	MX27L2000	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX27L256	DIP28	
MACRONIX	MX27L256	PLCC32	PA32PL28D-YA
MACRONIX	MX27L256	TSOP28	PA28TS28D-EO
MACRONIX	MX27L4000	DIP32	
MACRONIX	MX27L4000	PLCC32	PA32PL32D
MACRONIX	MX27L4000	SOIC32	PA32SO32D-EO-450
MACRONIX	MX27L4000	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX27L4096	DIP40	
MACRONIX	MX27L4096	PLCC44	PA44-48U
MACRONIX	MX27L4096	TSOP40	PA40TS40D
MACRONIX	MX27L4100	DIP40	
MACRONIX	MX27L4100	SOP40	PA40SO40D-EO-450
MACRONIX	MX27L512	DIP28	
MACRONIX	MX27L512	PLCC32	PA32PL28D-YA
MACRONIX	MX27L512	TSOP28	PA28TS28D-EO
MACRONIX	MX28F1000	DIP32	
MACRONIX	MX28F1000	PLCC32	PA32PL32D
MACRONIX	MX28F160C3BTC	TSOP48	PA48TS48D
MACRONIX	MX28F160C3TTC	TSOP48	PA48TS48D
MACRONIX	MX28F2000	DIP32	
MACRONIX	MX28F2000	PLCC32	PA32PL32D
MACRONIX	MX29F001B	DIP32	
MACRONIX	MX29F001B	PLCC32	PA32PL32D
MACRONIX	MX29F001B	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F001T	DIP32	
MACRONIX	MX29F001T	PLCC32	PA32PL32D
MACRONIX	MX29F001T	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F002B	DIP32	
MACRONIX	MX29F002B	PLCC32	PA32PL32D
MACRONIX	MX29F002B	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F002NB	DIP32	
MACRONIX	MX29F002NB	PLCC32	PA32PL32D
MACRONIX	MX29F002NB	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F002NT	DIP32	
MACRONIX	MX29F002NT	PLCC32	PA32PL32D
MACRONIX	MX29F002NT	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F002T	DIP32	
MACRONIX	MX29F002T	PLCC32	PA32PL32D
MACRONIX	MX29F002T	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F004B	DIP32	
MACRONIX	MX29F004B	PLCC32	PA32PL32D
MACRONIX	MX29F004B	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F004T	DIP32	
MACRONIX	MX29F004T	PLCC32	PA32PL32D
MACRONIX	MX29F004T	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F016	SOP44	PA44SO44D
MACRONIX	MX29F016	TSOP40	PA40TS40D
MACRONIX	MX29F016	TSOP48	PA48TS48D

MACRONIX	MX29F022B	DIP32	
MACRONIX	MX29F022B	PLCC32	PA32PL32D
MACRONIX	MX29F022B	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F022NB	DIP32	
MACRONIX	MX29F022NB	PLCC32	PA32PL32D
MACRONIX	MX29F022NB	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F022NT	DIP32	
MACRONIX	MX29F022NT	PLCC32	PA32PL32D
MACRONIX	MX29F022NT	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F022T	DIP32	
MACRONIX	MX29F022T	PLCC32	PA32PL32D
MACRONIX	MX29F022T	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F040CPC	DIP32	
MACRONIX	MX29F040CQC	PLCC32	PA32PL32D
MACRONIX	MX29F040CTC	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F040PC	DIP32	
MACRONIX	MX29F040QC	PLCC32	PA32PL32D
MACRONIX	MX29F040TC	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX29F100BMC	SOP44	PA44SO44D
MACRONIX	MX29F100BTC	TSOP48	PA48TS48D
MACRONIX	MX29F100TMC	SOP44	PA44SO44D
MACRONIX	MX29F100TTC	TSOP48	PA48TS48D
MACRONIX	MX29F1610AMC(USB2.0only)	SOP44	PA44SO44D
MACRONIX	MX29F1610ATC(USB2.0only)	TSOP48	PA48TS48D
MACRONIX	MX29F1610BTC(USB2.0only)	TSOP48	PA48TS48D
MACRONIX	MX29F1610MC(USB2.0only)	SOP44	PA44SO44D
MACRONIX	MX29F1610TC(USB2.0only)	TSOP48	PA48TS48D
MACRONIX	MX29F1611MC(USB2.0only)	SOP44	PA44SO44D
MACRONIX	MX29F1611TC(USB2.0only)	TSOP48	PA48TS48D
MACRONIX	MX29F1615	DIP42	
MACRONIX	MX29F200B	SOP44	PA44SO44D
MACRONIX	MX29F200B	TSOP48	PA48TS48D
MACRONIX	MX29F200CBMI	SOP44	PA44SO44D
MACRONIX	MX29F200CBTI	TSOP48	PA48TS48D
MACRONIX	MX29F200CTMI	SOP44	PA44SO44D
MACRONIX	MX29F200CTTI	TSOP48	PA48TS48D
MACRONIX	MX29F200T	SOP44	PA44SO44D
MACRONIX	MX29F200T	TSOP48	PA48TS48D
MACRONIX	MX29F400BMC	SOP44	PA44SO44D
MACRONIX	MX29F400BTC	TSOP48	PA48TS48D
MACRONIX	MX29F400CBMC	SOP44	PA44SO44D
MACRONIX	MX29F400CBTC	TSOP48	PA48TS48D
MACRONIX	MX29F400CTMC	SOP44	PA44SO44D
MACRONIX	MX29F400CTTC	TSOP48	PA48TS48D
MACRONIX	MX29F400TMC	SOP44	PA44SO44D
MACRONIX	MX29F400TTC	TSOP48	PA48TS48D
MACRONIX	MX29F800B	SOP44	PA44SO44D
MACRONIX	MX29F800B	TSOP48	PA48TS48D
MACRONIX	MX29F800CBT	TSOP48	PA48TS48D
MACRONIX	MX29F800CTT	TSOP48	PA48TS48D
MACRONIX	MX29F800T	SOP44	PA44SO44D
MACRONIX	MX29F800T	TSOP48	PA48TS48D
MACRONIX	MX29F8100MC(USB2.0only)	SOP44	PA44SO44D
MACRONIX	MX29F8100TC(USB2.0only)	TSOP48	PA48TS48D
MACRONIX	MX29GA120EHXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GA120ELXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GA128EHXC	BGA64	NA64BG48DT
MACRONIX	MX29GA128EHXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GA128ELXC	BGA64	NA64BG48DT
MACRONIX	MX29GA128ELXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GA129EHXC	BGA64	NA64BG48DU
MACRONIX	MX29GA129ELXC	BGA64	NA64BG48DU
MACRONIX	MX29GA250EHXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GA250ELXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GA256EHXC	BGA64	NA64BG48DT
MACRONIX	MX29GA256EHXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GA256ELXC	BGA64	NA64BG48DT
MACRONIX	MX29GA256ELXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GA257EHXC	BGA64	NA64BG48DU
MACRONIX	MX29GA257ELXC	BGA64	NA64BG48DU
MACRONIX	MX29GL128EHT2	TSOP56	HA56TS48DI
MACRONIX	MX29GL128EHT2	TSOP56	PA56TS48DB
MACRONIX	MX29GL128EHT2	TSOP56	PA56TS48DC

MACRONIX	MX29GL128EHT2	TSOP56	PA56TS48DD
MACRONIX	MX29GL128EHXC	BGA64	NA64BG48DT
MACRONIX	MX29GL128EHXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GL128ELT2	TSOP56	HA56TS48DI
MACRONIX	MX29GL128ELT2	TSOP56	PA56TS48DB
MACRONIX	MX29GL128ELT2	TSOP56	PA56TS48DC
MACRONIX	MX29GL128ELT2	TSOP56	PA56TS48DD
MACRONIX	MX29GL128ELXC	BGA64	NA64BG48DT
MACRONIX	MX29GL128ELXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GL128FDT2	TSOP56	HA56TS48DI
MACRONIX	MX29GL128FDXF	BGA64	PA64BG48DR
MACRONIX	MX29GL128FDXG	BGA56	NA56BG48DU
MACRONIX	MX29GL128FHT2	TSOP56	PA56TS48DD
MACRONIX	MX29GL128FHXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GL128FHXF	BGA56	NA56BG48DU
MACRONIX	MX29GL128FHT2	TSOP56	PA56TS48DD
MACRONIX	MX29GL128FLXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GL128FLXG	BGA56	NA56BG48DU
MACRONIX	MX29GL128FUT2	TSOP56	HA56TS48DI
MACRONIX	MX29GL128FUXF	BGA64	PA64BG48DR
MACRONIX	MX29GL128FUXG	BGA56	NA56BG48DU
MACRONIX	MX29GL256EHT2	TSOP56	HA56TS48DI
MACRONIX	MX29GL256EHT2	TSOP56	PA56TS48DC
MACRONIX	MX29GL256EHT2	TSOP56	PA56TS48DD
MACRONIX	MX29GL256EHXC	BGA64	NA64BG48DT
MACRONIX	MX29GL256EHXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GL256ELT2	TSOP56	HA56TS48DI
MACRONIX	MX29GL256ELT2	TSOP56	PA56TS48DC
MACRONIX	MX29GL256ELT2	TSOP56	PA56TS48DD
MACRONIX	MX29GL256ELXC	BGA64	NA64BG48DT
MACRONIX	MX29GL256ELXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GL256FHXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GL256FHXF	BGA56	NA56BG48DU
MACRONIX	MX29GL256FLT2	TSOP56	PA56TS48DD
MACRONIX	MX29GL256FLXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GL256FLXG	BGA56	NA56BG48DU
MACRONIX	MX29GL256FUXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GL320DHXC	BGA64	NA64BG48DT
MACRONIX	MX29GL320DLXC	BGA64	NA64BG48DT
MACRONIX	MX29GL320EHT2	TSOP56	PA56TS48DB
MACRONIX	MX29GL320EHT2	TSOP56	PA56TS48DC
MACRONIX	MX29GL320EHT2	TSOP56	PA56TS48DD
MACRONIX	MX29GL320EHXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GL320ELT2	TSOP56	PA56TS48DB
MACRONIX	MX29GL320ELT2	TSOP56	PA56TS48DC
MACRONIX	MX29GL320ELT2	TSOP56	PA56TS48DD
MACRONIX	MX29GL320ELXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GL512FHT2	TSOP56	HA56TS48DI
MACRONIX	MX29GL512FHT2	TSOP56	PA56TS48DD
MACRONIX	MX29GL512FHXF	BGA64	PA64BG48DR
MACRONIX	MX29GL512FLXF	BGA64	PA64BG48DR
MACRONIX	MX29GL512GHT2	TSOP56	HA56TS48DI
MACRONIX	MX29GL512GHXF	BGA64	PA64BG48DR
MACRONIX	MX29GL512GLT2	TSOP56	HA56TS48DI
MACRONIX	MX29GL512GLXF	BGA64	PA64BG48DR
MACRONIX	MX29GL640EHT2	TSOP56	PA56TS48DB
MACRONIX	MX29GL640EHT2	TSOP56	PA56TS48DC
MACRONIX	MX29GL640EHT2	TSOP56	PA56TS48DD
MACRONIX	MX29GL640EHXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GL640ELT2	TSOP56	PA56TS48DB
MACRONIX	MX29GL640ELT2	TSOP56	PA56TS48DC
MACRONIX	MX29GL640ELT2	TSOP56	PA56TS48DD
MACRONIX	MX29GL640ELXF	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MACRONIX	MX29GL640ETTI	TSOP48	PA48TS48D1
MACRONIX	MX29L1611G	DIP42	
MACRONIX	MX29L1611MC(USB2.0only)	SOP44	PA44SO44D
MACRONIX	MX29L1611TC(USB2.0only)	TSOP48	PA48TS48D
MACRONIX	MX29L3211AMC(USB2.0only)	SOP44	PA44SO44D
MACRONIX	MX29L3211ATC(USB2.0only)	TSOP48	PA48TS48D
MACRONIX	MX29L3211MC(USB2.0only)	SOP44	PA44SO44D
MACRONIX	MX29L3211TC(USB2.0only)	TSOP48	PA48TS48D
MACRONIX	MX29L8000BTC(USB2.0only)	TSOP40	PA40TS40D
MACRONIX	MX29L8000TTC(USB2.0only)	TSOP40	PA40TS40D

MACRONIX	MX29L8100BTC(USB2.0only)	TSOP48	PA48TS48D
MACRONIX	MX29L8100TTC(USB2.0only)	TSOP48	PA48TS48D
MACRONIX	MX29LA128MBTC	TSOP56	PA56TS48DB
MACRONIX	MX29LA128MTTC	TSOP56	PA56TS48DB
MACRONIX	MX29LA320MBTC	TSOP48	PA48TS48D1
MACRONIX	MX29LA320MBXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LA320MBXBC	BGA48	PA48BG48DW
MACRONIX	MX29LA320MBXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LA320MBXEC	BGA48	PA48BG48DW
MACRONIX	MX29LA320MTTC	TSOP48	PA48TS48D1
MACRONIX	MX29LA320MTXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LA320MTXBC	BGA48	PA48BG48DW
MACRONIX	MX29LA320MTXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LA320MTXEC	BGA48	PA48BG48DW
MACRONIX	MX29LA321DHXC	BGA64	NA64BG48DU
MACRONIX	MX29LA321DLXC	BGA64	NA64BG48DU
MACRONIX	MX29LA321MBTC	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
MACRONIX	MX29LA321MLHTC	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
MACRONIX	MX29LA321MLTC	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
MACRONIX	MX29LA321MTTC	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
MACRONIX	MX29LA641DHXC	BGA64	NA64BG48DU
MACRONIX	MX29LA641DLXC	BGA64	NA64BG48DU
MACRONIX	MX29LV002BPC	DIP32	
MACRONIX	MX29LV002BQC	PLCC32	PA32PL32D
MACRONIX	MX29LV002BTC	TSOP32	PA32TS32D
MACRONIX	MX29LV002CBQC	PLCC32	PA32PL32D
MACRONIX	MX29LV002CBTC	TSOP32	PA32TS32D
MACRONIX	MX29LV002CTQC	PLCC32	PA32PL32D
MACRONIX	MX29LV002CTTC	TSOP32	PA32TS32D
MACRONIX	MX29LV002NBPC	DIP32	
MACRONIX	MX29LV002NBQC	PLCC32	PA32PL32D
MACRONIX	MX29LV002NBTC	TSOP32	PA32TS32D
MACRONIX	MX29LV002NCBQC	PLCC32	PA32PL32D
MACRONIX	MX29LV002NCBTC	TSOP32	PA32TS32D
MACRONIX	MX29LV002NCTQC	PLCC32	PA32PL32D
MACRONIX	MX29LV002NCTTC	TSOP32	PA32TS32D
MACRONIX	MX29LV002NTPC	DIP32	
MACRONIX	MX29LV002NTQC	PLCC32	PA32PL32D
MACRONIX	MX29LV002NTTC	TSOP32	PA32TS32D
MACRONIX	MX29LV002TPC	DIP32	
MACRONIX	MX29LV002TQC	PLCC32	PA32PL32D
MACRONIX	MX29LV002TTC	TSOP32	PA32TS32D
MACRONIX	MX29LV004B	DIP32	
MACRONIX	MX29LV004BTC	TSOP40	PA40TS40D
MACRONIX	MX29LV004CBQC	PLCC32	PA32PL32D
MACRONIX	MX29LV004CBTC	TSOP40	PA40TS40D
MACRONIX	MX29LV004CTQC	PLCC32	PA32PL32D
MACRONIX	MX29LV004CTTC	TSOP40	PA40TS40D
MACRONIX	MX29LV004T	DIP32	
MACRONIX	MX29LV004TTC	TSOP40	PA40TS40D
MACRONIX	MX29LV008BBTC	TSOP40	PA40TS40D
MACRONIX	MX29LV008BTC	TSOP40	PA40TS40D
MACRONIX	MX29LV008BTTC	TSOP40	PA40TS40D
MACRONIX	MX29LV008CBTC	TSOP40	PA40TS40D
MACRONIX	MX29LV008CTTC	TSOP40	PA40TS40D
MACRONIX	MX29LV008TTC	TSOP40	PA40TS40D
MACRONIX	MX29LV017A	TSOP40	PA40TS40D
MACRONIX	MX29LV017B	TSOP40	PA40TS40D
MACRONIX	MX29LV033	TSOP40	PA40TS40D
MACRONIX	MX29LV033A	TSOP40	PA40TS40D
MACRONIX	MX29LV033C	TSOP40	PA40TS40D
MACRONIX	MX29LV033M	TSOP40	PA40TS40D
MACRONIX	MX29LV033MTC	TSOP40	PA40TS40D
MACRONIX	MX29LV033TTC	TSOP40	PA40TS40D
MACRONIX	MX29LV040CQC	PLCC32	PA32PL32D
MACRONIX	MX29LV040CTC	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX29LV040QC	PLCC32	PA32PL32D
MACRONIX	MX29LV040TC	TSOP32	PA32TS20/PA32TS32D-20
MACRONIX	MX29LV065BTC	TSOP48	PA48TS48D
MACRONIX	MX29LV065MTC	TSOP48	PA48TS48D
MACRONIX	MX29LV081	TSOP40	PA40TS40D
MACRONIX	MX29LV128DBT2C	TSOP56	HA56TS48DI
MACRONIX	MX29LV128DBT2C	TSOP56	PA56TS48DB

MACRONIX	MX29LV128DBT2C	TSOP56	PA56TS48DC
MACRONIX	MX29LV128DBT2C	TSOP56	PA56TS48DD
MACRONIX	MX29LV128DBTC	TSOP48	PA48TS48D
MACRONIX	MX29LV128DTT2C	TSOP56	HA56TS48DI
MACRONIX	MX29LV128DTT2C	TSOP56	PA56TS48DB
MACRONIX	MX29LV128DTT2C	TSOP56	PA56TS48DC
MACRONIX	MX29LV128DTT2C	TSOP56	PA56TS48DD
MACRONIX	MX29LV128DTTC	TSOP48	PA48TS48D
MACRONIX	MX29LV128MBTC	TSOP56	PA56TS48DB
MACRONIX	MX29LV128MHTC	TSOP56	PA56TS48DB
MACRONIX	MX29LV128MLTC	TSOP56	PA56TS48DB
MACRONIX	MX29LV128MTTC	TSOP56	PA56TS48DB
MACRONIX	MX29LV160ABMC	SOP44	PA44SO44D1
MACRONIX	MX29LV160ABTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV160ATMC	SOP44	PA44SO44D1
MACRONIX	MX29LV160ATTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV160BBTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV160BMC	SOP44	PA44SO44D1
MACRONIX	MX29LV160BTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV160BTTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV160CBMC	SOP44	PA44SO44D1
MACRONIX	MX29LV160CBTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV160CBXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV160CBXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV160CBXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV160CBXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV160CTMC	SOP44	PA44SO44D1
MACRONIX	MX29LV160CTTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV160CTXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV160CTXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV160CTXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV160CTXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV160DB	BGA48	PA48BG48DAI
MACRONIX	MX29LV160DB	TSOP48	PA48TS48D1
MACRONIX	MX29LV160DT	BGA48	PA48BG48DAI
MACRONIX	MX29LV160DT	TSOP48	PA48TS48D1
MACRONIX	MX29LV160TMC	SOP44	PA44SO44D1
MACRONIX	MX29LV160TTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV161DBT	TSOP48	PA48TS48D1
MACRONIX	MX29LV161DTT	TSOP48	PA48TS48D1
MACRONIX	MX29LV320ABTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV320ATTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV320BTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV320BXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV320BXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV320BXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV320BXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV320CBTC	TSOP48	PA48TS48D
MACRONIX	MX29LV320CBXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV320CBXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV320CBXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV320CBXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV320CTTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV320CTXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV320CTXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV320CTXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV320CTXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV320DB	BGA48	HA48BG48DAI
MACRONIX	MX29LV320DB	BGA48	PA48BG48DW
MACRONIX	MX29LV320DB	TSOP48	PA48TS48D1
MACRONIX	MX29LV320DT	BGA48	HA48BG48DAI
MACRONIX	MX29LV320DT	BGA48	PA48BG48DW
MACRONIX	MX29LV320ODT	TSOP48	PA48TS48D1
MACRONIX	MX29LV320EB	BGA48	HA48BG48DAI
MACRONIX	MX29LV320EB	TSOP48	PA48TS48D1
MACRONIX	MX29LV320ET	BGA48	HA48BG48DAI
MACRONIX	MX29LV320ET	TSOP48	PA48TS48D1
MACRONIX	MX29LV320MBTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV320MBXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV320MBXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV320MBXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV320MBXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV320MHTC	TSOP56	PA56TS48DB



MACRONIX	MX29LV320MLTC	TSOP56	PA56TS48DB
MACRONIX	MX29LV320MTTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV320MTXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV320MTXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV320MTXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV320MTXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV320TTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV320TXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV320TXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV320TXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV320TXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV321DB	TSOP48	PA48TS48D1
MACRONIX	MX29LV321DT	TSOP48	PA48TS48D1
MACRONIX	MX29LV400BMC	SOP44	PA44SO44D1
MACRONIX	MX29LV400BTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV400BXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV400BXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV400BXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV400BXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV400CBMC	SOP44	PA44SO44D1
MACRONIX	MX29LV400CBTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV400CBXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV400CBXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV400CBXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV400CBXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV400CTMC	SOP44	PA44SO44D1
MACRONIX	MX29LV400CTTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV400CTXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV400CTXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV400CTXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV400CTXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV400TMC	SOP44	PA44SO44D1
MACRONIX	MX29LV400TTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV400TXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV400TXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV400TXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV400TXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV401B	SOP44	PA44SO44D1
MACRONIX	MX29LV401B	TSOP48	PA48TS48D1
MACRONIX	MX29LV401T	SOP44	PA44SO44D1
MACRONIX	MX29LV401T	TSOP48	PA48TS48D1
MACRONIX	MX29LV640BBTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV640BTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV640BTTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV640BUTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV640DB	BGA48	HA48BG48DAI
MACRONIX	MX29LV640DB	BGA48	PA48BG48DW
MACRONIX	MX29LV640DBTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV640DBTI	TSOP48	PA48TS48D1
MACRONIX	MX29LV640DT	BGA48	HA48BG48DAI
MACRONIX	MX29LV640DT	BGA48	PA48BG48DW
MACRONIX	MX29LV640DTTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV640DTTI	TSOP48	PA48TS48D1
MACRONIX	MX29LV640EB	BGA48	HA48BG48DAI
MACRONIX	MX29LV640EB	BGA48	PA48BG48DW
MACRONIX	MX29LV640EB	TSOP48	PA48TS48D1
MACRONIX	MX29LV640ET	BGA48	HA48BG48DAI
MACRONIX	MX29LV640ET	BGA48	PA48BG48DW
MACRONIX	MX29LV640ET	TSOP48	PA48TS48D1
MACRONIX	MX29LV640MBTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV640MHTC	TSOP56	PA56TS48DC
MACRONIX	MX29LV640MLTC	TSOP56	PA56TS48DC
MACRONIX	MX29LV640MTTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV640TTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV641MHTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV641MLTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV800ABMC	SOP44	PA44SO44D1
MACRONIX	MX29LV800ABTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV800ABXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV800ABXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV800ABXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV800ABXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV800ATMC	SOP44	PA44SO44D1

MACRONIX	MX29LV800ATTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV800ATXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV800ATXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV800ATXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV800ATXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV800BBMC	SOP44	PA44SO44D1
MACRONIX	MX29LV800BBTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV800BBTI	TSOP48	PA48TS48D1
MACRONIX	MX29LV800BBXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV800BBXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV800BBXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV800BBXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV800BMC	SOP44	PA44SO44D1
MACRONIX	MX29LV800BTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV800BTMC	SOP44	PA44SO44D1
MACRONIX	MX29LV800BTTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV800BTTI	TSOP48	PA48TS48D1
MACRONIX	MX29LV800BTXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV800BTXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV800BTXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV800BTXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV800BXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV800BXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV800BXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV800BXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV800CBMC	SOP44	PA44SO44D1
MACRONIX	MX29LV800CBTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV800CBTI	TSOP48	PA48TS48D1
MACRONIX	MX29LV800CBXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV800CBXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV800CBXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV800CBXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV800CTMC	SOP44	PA44SO44D1
MACRONIX	MX29LV800CTTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV800CTXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV800CTXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV800CTXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV800CTXEC	BGA48	PA48BG48DW
MACRONIX	MX29LV800TMC	SOP44	PA44SO44D1
MACRONIX	MX29LV800TTC	TSOP48	PA48TS48D1
MACRONIX	MX29LV800TXBC	BGA48	HA48BG48DAI
MACRONIX	MX29LV800TXBC	BGA48	PA48BG48DW
MACRONIX	MX29LV800TXEC	BGA48	HA48BG48DAI
MACRONIX	MX29LV800TXEC	BGA48	PA48BG48DW
MACRONIX	MX29SL402C-B-T	TSOP48	PA48TS48D1
MACRONIX	MX29SL402C-T-T	TSOP48	PA48TS48D1
MACRONIX	MX29SL800CBTI	TSOP48	HA48TS48DJ
MACRONIX	MX29SL800CTTI	TSOP48	HA48TS48DJ
MACRONIX	MX29SL800CTXB	BGA48	HA48BG48DAY
MACRONIX	MX30LF1G08AA	BGA63	HA63BG48DN
MACRONIX	MX30LF1G08AA	TSOP48	PA48TS48D
MACRONIX	MX30LF1G18AC	BGA63	HA63BG48DN
MACRONIX	MX30LF1G18AC	TSOP48	PA48TS48D
MACRONIX	MX30LF1GE8AB	BGA63	HA63BG48DN
MACRONIX	MX30LF1GE8AB	TSOP48	PA48TS48D
MACRONIX	MX30LF2G18AB	BGA63	HA63BG48DN
MACRONIX	MX30LF2G18AB	TSOP48	PA48TS48D
MACRONIX	MX30LF2G18AC	BGA63	HA63BG48DN
MACRONIX	MX30LF2G18AC	TSOP48	PA48TS48D
MACRONIX	MX30LF2GE8AB	BGA63	HA63BG48DN
MACRONIX	MX30LF2GE8AB	TSOP48	PA48TS48D
MACRONIX	MX30LF4G18AC	BGA63	HA63BG48DN
MACRONIX	MX30LF4G18AC	TSOP48	PA48TS48D
MACRONIX	MX30LF4GE8AB	BGA63	HA63BG48DN
MACRONIX	MX30LF4GE8AB	TSOP48	PA48TS48D
MACRONIX	MX66L1G45G	SOP16	PA28SO28D-EO-300
MACRONIX	MX66L1G45G	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX66L1G45G (QPI)	SOP16	PA28SO28D-EO-300
MACRONIX	MX66L1G45G (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX66L51235F	SOP16	PA28SO28D-EO-300
MACRONIX	MX66L51235F	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX66L51235F	WSON8	PA8SON8DA(8x6)
MACRONIX	MX66L51235F (QPI)	SOP16	PA28SO28D-EO-300

MACRONIX	MX66L51235F (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX66L51235F (QPI)	WSON8	PA8SON8DA(8x6)
MACRONIX	MX66LM1G45G (Octa I/O / DTR)	SOP16	PA28SO28D-EO-300
MACRONIX	MX66LM1G45G (Octa I/O / DTR)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX66LM1G45G (Octa I/O / STR)	SOP16	PA28SO28D-EO-300
MACRONIX	MX66LM1G45G (Octa I/O / STR)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX66LM1G45G (SPI)	SOP16	PA28SO28D-EO-300
MACRONIX	MX66LM1G45G (SPI)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX66U1G45G	SOP16	PA28SO28D-EO-300
MACRONIX	MX66U1G45G	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX66U1G45G 54	SOP16	PA28SO28D-EO-300
MACRONIX	MX66U1G45G 54	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX66U2G45G	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX66U2G45G (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX66U2G45G 54	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX66U2G45G 54 (QPI)	TFBGA24	PA24BG24D(6x8mm)5x5
MACRONIX	MX68GL1G0FHT2I	TSOP56	HA56TS48DI
MACRONIX	MX68GL1G0FHXF	BGA64	PA64BG48DR
MACRONIX	MX68GL1G0FLXF	BGA64	PA64BG48DR
MACRONIX	MX68GL1G0FUXF	BGA64	PA64BG48DR
MAXIM	DS1746	EDIP32	
MAXIM	DS1746W	EDIP32	
MAXIM	DS2431	TO-92.3	
MAXIM	DS2433	PR-35.3	
MAXIM	DS2433	SOIC8	PA20SO20D-EO-210
MAXIM	DS24B33	TO-92.3	
MAXIM	DS28E07	TO-92.3	
MAXIM	DS28EC20	TO-92.3	
MCS-LOGIC	MLC1043D	DIP24	
MCS-LOGIC	MLC1043D	SOIC24	PA28SO28D-EO-300
MEDIA REALITY TECH.	M8064	PLCC44	PA44-48U
MEGAWIN	MPC89E515AE	DIP40	
MEGAWIN	MPC89E515AF	PQFP44	PA44PQ48D
MEGAWIN	MPC89E515AP	PLCC44	PA44-48U
MEGAWIN	MPC89E51AE	DIP40	
MEGAWIN	MPC89E51AF	PQFP44	PA44PQ48D
MEGAWIN	MPC89E51AP	PLCC44	PA44-48U
MEGAWIN	MPC89E52AE	DIP40	
MEGAWIN	MPC89E52AF	PQFP44	PA44PQ48D
MEGAWIN	MPC89E52AP	PLCC44	PA44-48U
MEGAWIN	MPC89E53AE	DIP40	
MEGAWIN	MPC89E53AF	PQFP44	PA44PQ48D
MEGAWIN	MPC89E53AP	PLCC44	PA44-48U
MEGAWIN	MPC89E54AE	DIP40	
MEGAWIN	MPC89E54AF	PQFP44	PA44PQ48D
MEGAWIN	MPC89E54AP	PLCC44	PA44-48U
MEGAWIN	MPC89E58AE	DIP40	
MEGAWIN	MPC89E58AF	PQFP44	PA44PQ48D
MEGAWIN	MPC89E58AP	PLCC44	PA44-48U
MEGAWIN	MPC89L515AE	DIP40	
MEGAWIN	MPC89L515AF	PQFP44	PA44PQ48D
MEGAWIN	MPC89L515AP	PLCC44	PA44-48U
MEGAWIN	MPC89L51AE	DIP40	
MEGAWIN	MPC89L51AF	PQFP44	PA44PQ48D
MEGAWIN	MPC89L51AP	PLCC44	PA44-48U
MEGAWIN	MPC89L52AE	DIP40	
MEGAWIN	MPC89L52AF	PQFP44	PA44PQ48D
MEGAWIN	MPC89L52AP	PLCC44	PA44-48U
MEGAWIN	MPC89L53AE	DIP40	
MEGAWIN	MPC89L53AF	PQFP44	PA44PQ48D
MEGAWIN	MPC89L53AP	PLCC44	PA44-48U
MEGAWIN	MPC89L54AE	DIP40	
MEGAWIN	MPC89L54AF	PQFP44	PA44PQ48D
MEGAWIN	MPC89L54AP	PLCC44	PA44-48U
MEGAWIN	MPC89L58AE	DIP40	
MEGAWIN	MPC89L58AF	PQFP44	PA44PQ48D
MEGAWIN	MPC89L58AP	PLCC44	PA44-48U
MICROCHIP	24AA00	DIP8	
MICROCHIP	24AA00	SOIC8	PA8SO8D-EO-150
MICROCHIP	24AA00	SOT23-5	PA5SOT5D
MICROCHIP	24AA00	TSSOP8	PA8TSS8D
MICROCHIP	24AA00-I/P	DIP8	
MICROCHIP	24AA00-I/SN	SOIC8	PA8SO8D-EO-150

MICROCHIP	24AA00-I/ST	TSSOP8	PA8TSS8D
MICROCHIP	24AA01	DIP8	
MICROCHIP	24AA01	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24AA01	SOIC8	PA8SO8D-EO-150
MICROCHIP	24AA01	SOT23-5	PA5SOT5D
MICROCHIP	24AA01	TSSOP8	PA8TSS8D
MICROCHIP	24AA014	DIP8	
MICROCHIP	24AA014	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24AA014	SOIC8	PA8SO8D-EO-150
MICROCHIP	24AA014	TSSOP8	PA8TSS8D
MICROCHIP	24AA02	DIP8	
MICROCHIP	24AA02	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24AA02	SOIC8	PA8SO8D-EO-150
MICROCHIP	24AA02	SOT23-5	PA5SOT5D
MICROCHIP	24AA02	TSSOP8	PA8TSS8D
MICROCHIP	24AA024	DIP8	
MICROCHIP	24AA024	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24AA024	SOIC8	PA8SO8D-EO-150
MICROCHIP	24AA024	TSSOP8	PA8TSS8D
MICROCHIP	24AA025E64-I/SN	SOIC8	PA16SO16D-EO-150
MICROCHIP	24AA025UID	SOIC8	PA16SO16D-EO-150
MICROCHIP	24AA02UID-I/SN	SOIC8	PA16SO16D-EO-150
MICROCHIP	24AA04	DIP8	
MICROCHIP	24AA04	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24AA04	SOIC8	PA8SO8D-EO-150
MICROCHIP	24AA04	SOT23-5	PA5SOT5D
MICROCHIP	24AA04	TSSOP8	PA8TSS8D
MICROCHIP	24AA08	DIP8	
MICROCHIP	24AA08	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24AA08	SOIC8	PA8SO8D-EO-150
MICROCHIP	24AA08	SOT23-5	PA5SOT5D
MICROCHIP	24AA08	TSSOP8	PA24TSS24D
MICROCHIP	24AA08	TSSOP8	PA8TSS8D
MICROCHIP	24AA1025	DIP8	
MICROCHIP	24AA1025	SOIC8	PA20SO20D-EO-210
MICROCHIP	24AA128	DFN8	PA8SON8D(6x5)
MICROCHIP	24AA128	DIP8	
MICROCHIP	24AA128	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24AA128	SOIC8	PA16SO16D-EO-150
MICROCHIP	24AA128	SOIC8	PA8SO8D-EO-150
MICROCHIP	24AA128	TSSOP14	PA28TSS28D-EO
MICROCHIP	24AA128	TSSOP8	PA24TSS24D
MICROCHIP	24AA128	TSSOP8	PA8TSS8D
MICROCHIP	24AA16	DIP8	
MICROCHIP	24AA16	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24AA16	SOIC8	PA8SO8D-EO-150
MICROCHIP	24AA16	SOT23-5	PA5SOT5D
MICROCHIP	24AA16	TSSOP8	PA24TSS24D
MICROCHIP	24AA16	TSSOP8	PA8TSS8D
MICROCHIP	24AA164	DIP8	
MICROCHIP	24AA164	SOIC8	PA8SO8D-EO-150
MICROCHIP	24AA16-I/P	DIP8	
MICROCHIP	24AA16-I/SN	SOIC8	PA16SO16D-EO-150
MICROCHIP	24AA16-I/ST	TSSOP8	PA8TSS8D
MICROCHIP	24AA16-I-MS	MSOP8	HA8MSOP48D
MICROCHIP	24AA174	DIP8	
MICROCHIP	24AA174	SOIC8	PA8SO8D-EO-150
MICROCHIP	24AA256	DFN8	PA8SON8D(6x5)
MICROCHIP	24AA256	DIP8	
MICROCHIP	24AA256	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24AA256	SOIC8	PA16SO16D-EO-150
MICROCHIP	24AA256	SOIC8	PA8SO8D-EO-150
MICROCHIP	24AA256	TSSOP14	PA28TSS28D-EO
MICROCHIP	24AA256	TSSOP8	PA24TSS24D
MICROCHIP	24AA256	TSSOP8	PA8TSS8D
MICROCHIP	24AA32	DIP8	
MICROCHIP	24AA32	SOIC8	PA8SO8D-EO-150
MICROCHIP	24AA32A	DIP8	
MICROCHIP	24AA32A	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24AA32A	SOIC8	PA16SO16D-EO-150
MICROCHIP	24AA32A	SOIC8	PA8SO8D-EO-150
MICROCHIP	24AA32A	TSSOP8	PA24TSS24D
MICROCHIP	24AA32A	TSSOP8	PA8TSS8D

MICROCHIP	24AA32A-I/MS	MSOP8	HA8MSOP48D
MICROCHIP	24AA32A-I/P	DIP8	
MICROCHIP	24AA32A-I/SM	SOIC8	PA20SO20D-EO-210
MICROCHIP	24AA32A-I/SN	SOIC8	PA16SO16D-EO-150
MICROCHIP	24AA32A-I/ST	TSSOP8	PA8TSS8D
MICROCHIP	24AA32AX	TSSOP8	PA8RTSS8D
MICROCHIP	24AA512	DFN8	PA8SON8D(6x5)
MICROCHIP	24AA512	DIP8	
MICROCHIP	24AA512	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24AA512	SOIC8	PA16SO16D-EO-150
MICROCHIP	24AA512	SOIC8	PA8SO8D-EO-150
MICROCHIP	24AA512	TSSOP14	PA28TSS28D-EO
MICROCHIP	24AA512	TSSOP8	PA24TSS24D
MICROCHIP	24AA512	TSSOP8	PA8TSS8D
MICROCHIP	24AA515	DIP8	
MICROCHIP	24AA515	SOIC8	PA16SO16D-EO-150
MICROCHIP	24AA515	SOIC8	PA8SO8D-EO-150
MICROCHIP	24AA52	DIP8	
MICROCHIP	24AA52	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24AA52	SOIC8	PA8SO8D-EO-150
MICROCHIP	24AA52	TSSOP8	PA24TSS24D
MICROCHIP	24AA52	TSSOP8	PA8TSS8D
MICROCHIP	24AA64	DFN8	PA8QFN8D(2x3)
MICROCHIP	24AA64	DIP8	
MICROCHIP	24AA64	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24AA64	SOIC8	PA16SO16D-EO-150
MICROCHIP	24AA64	SOIC8	PA8SO8D-EO-150
MICROCHIP	24AA64	TSSOP8	PA24TSS24D
MICROCHIP	24AA64	TSSOP8	PA8TSS8D
MICROCHIP	24AA64-I/MS	MSOP8	HA8MSOP48D
MICROCHIP	24AA64-I/P	DIP8	
MICROCHIP	24AA64-I/SM	SOIC8	PA20SO20D-EO-210
MICROCHIP	24AA64-I/SN	SOIC8	PA16SO16D-EO-150
MICROCHIP	24AA64-I/ST	TSSOP8	PA8TSS8D
MICROCHIP	24AA64T-I/MNY	DFN8	PA8QFN8D(2x3)
MICROCHIP	24AA64X	TSSOP8	PA8RTSS8D
MICROCHIP	24AA65	DIP8	
MICROCHIP	24AA65	SOIC8	PA16SO16D-EO-150
MICROCHIP	24C00	DIP8	
MICROCHIP	24C00	SOIC8	PA8SO8D-EO-150
MICROCHIP	24C00	SOT23-5	PA5SOT5D
MICROCHIP	24C00	TSSOP8	PA24TSS24D
MICROCHIP	24C00	TSSOP8	PA8TSS8D
MICROCHIP	24C01A	DIP8	
MICROCHIP	24C01A	SOIC14	PA16SO16D-EO-150
MICROCHIP	24C01A	SOIC8	PA8SO8D-EO-150
MICROCHIP	24C01B	SOIC14	PA16SO16D-EO-150
MICROCHIP	24C01B	SOIC8	PA8SO8D-EO-150
MICROCHIP	24C01C	SOIC8	PA8SO8D-EO-150
MICROCHIP	24C01C	TSSOP8	PA24TSS24D
MICROCHIP	24C01C	TSSOP8	PA8TSS8D
MICROCHIP	24C02A	DIP8	
MICROCHIP	24C02A	SOIC14	PA16SO16D-EO-150
MICROCHIP	24C02A	SOIC8	PA8SO8D-EO-150
MICROCHIP	24C02B	SOIC14	PA16SO16D-EO-150
MICROCHIP	24C02B	SOIC8	PA8SO8D-EO-150
MICROCHIP	24C04A	DIP8	
MICROCHIP	24C04A	SOIC14	PA16SO16D-EO-150
MICROCHIP	24C04A	SOIC8	PA8SO8D-EO-150
MICROCHIP	24C08A	DIP8	
MICROCHIP	24C08A	SOIC14	PA16SO16D-EO-150
MICROCHIP	24C08A	SOIC8	PA8SO8D-EO-150
MICROCHIP	24C08B	DIP8	
MICROCHIP	24C08B	SOIC14	PA16SO16D-EO-150
MICROCHIP	24C08B	SOIC8	PA8SO8D-EO-150
MICROCHIP	24C128	DIP8	
MICROCHIP	24C16A	DIP8	
MICROCHIP	24C16A	SOIC14	PA16SO16D-EO-150
MICROCHIP	24C16A	SOIC8	PA8SO8D-EO-150
MICROCHIP	24C16B	DIP8	
MICROCHIP	24C16B	SOIC14	PA16SO16D-EO-150
MICROCHIP	24C16B	SOIC8	PA8SO8D-EO-150
MICROCHIP	24C256	DIP8	

MICROCHIP	24C32	DIP8	
MICROCHIP	24C32	SOIC8	PA16SO16D-EO-150
MICROCHIP	24C32	SOIC8	PA8SO8D-EO-150
MICROCHIP	24C32A	SOIC8	PA16SO16D-EO-150
MICROCHIP	24C32A	SOIC8	PA8SO8D-EO-150
MICROCHIP	24C64	DIP8	
MICROCHIP	24C65	DIP8	
MICROCHIP	24C65	SOIC8	PA16SO16D-EO-150
MICROCHIP	24C65	SOIC8	PA8SO8D-EO-150
MICROCHIP	24FC1025	DIP8	
MICROCHIP	24FC1025	SOIC8	PA20SO20D-EO-210
MICROCHIP	24FC128	DFN8	PA8SON8D(6x5)
MICROCHIP	24FC128	DIP8	
MICROCHIP	24FC128	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24FC128	SOIC8	PA16SO16D-EO-150
MICROCHIP	24FC128	SOIC8	PA8SO8D-EO-150
MICROCHIP	24FC128	TSSOP14	PA28TSS28D-EO
MICROCHIP	24FC128	TSSOP8	PA24TSS24D
MICROCHIP	24FC128	TSSOP8	PA8TSS8D
MICROCHIP	24FC16	DIP8	
MICROCHIP	24FC16	SOIC8	PA8SO8D-EO-150
MICROCHIP	24FC256	DFN8	PA8SON8D(6x5)
MICROCHIP	24FC256	DIP8	
MICROCHIP	24FC256	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24FC256	SOIC8	PA16SO16D-EO-150
MICROCHIP	24FC256	SOIC8	PA8SO8D-EO-150
MICROCHIP	24FC256	TSSOP14	PA28TSS28D-EO
MICROCHIP	24FC256	TSSOP8	PA24TSS24D
MICROCHIP	24FC256	TSSOP8	PA8TSS8D
MICROCHIP	24FC256-SM	SOIC8	PA20SO20D-EO-210
MICROCHIP	24FC32	DIP8	
MICROCHIP	24FC32	SOIC8	PA16SO16D-EO-150
MICROCHIP	24FC512	DFN8	PA8SON8D(6x5)
MICROCHIP	24FC512	DIP8	
MICROCHIP	24FC512	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24FC512	SOIC8	PA16SO16D-EO-150
MICROCHIP	24FC512	SOIC8	PA8SO8D-EO-150
MICROCHIP	24FC512	TSSOP14	PA28TSS28D-EO
MICROCHIP	24FC512	TSSOP8	PA24TSS24D
MICROCHIP	24FC512	TSSOP8	PA8TSS8D
MICROCHIP	24FC515	DIP8	
MICROCHIP	24FC515	SOIC8	PA16SO16D-EO-150
MICROCHIP	24FC515	SOIC8	PA8SO8D-EO-150
MICROCHIP	24FC64	DIP8	
MICROCHIP	24FC64	SOIC8	PA16SO16D-EO-150
MICROCHIP	24FC65	DIP8	
MICROCHIP	24FC65	SOIC8	PA16SO16D-EO-150
MICROCHIP	24LC00	DIP8	
MICROCHIP	24LC00	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC00	SOT23-5	PA5SOT5D
MICROCHIP	24LC00	TSSOP8	PA24TSS24D
MICROCHIP	24LC00	TSSOP8	PA8TSS8D
MICROCHIP	24LC00-I/P	DIP8	
MICROCHIP	24LC00-I/SN	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC014	DIP8	
MICROCHIP	24LC014	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24LC014	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC014	TSSOP8	PA24TSS24D
MICROCHIP	24LC014	TSSOP8	PA8TSS8D
MICROCHIP	24LC01B	DIP8	
MICROCHIP	24LC01B	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24LC01B	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC01B	SOT23-5	PA5SOT5D
MICROCHIP	24LC01B	TSSOP8	PA24TSS24D
MICROCHIP	24LC01B	TSSOP8	PA8TSS8D
MICROCHIP	24LC024	DIP8	
MICROCHIP	24LC024	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24LC024	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC024	TSSOP8	PA24TSS24D
MICROCHIP	24LC024	TSSOP8	PA8TSS8D
MICROCHIP	24LC025	DIP8	
MICROCHIP	24LC025	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24LC025	SOIC8	PA8SO8D-EO-150

MICROCHIP	24LC025	TSSOP8	PA24TSS24D
MICROCHIP	24LC025	TSSOP8	PA8TSS8D
MICROCHIP	24LC02B	DIP8	
MICROCHIP	24LC02B	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24LC02B	SOT23-5	PA5SOT5D
MICROCHIP	24LC02B	TSSOP8	PA24TSS24D
MICROCHIP	24LC02B	TSSOP8	PA8TSS8D
MICROCHIP	24LC04B	DIP8	
MICROCHIP	24LC04B	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24LC04B	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC04B	SOT23-5	PA5SOT5D
MICROCHIP	24LC04B	TSSOP8	PA24TSS24D
MICROCHIP	24LC04B	TSSOP8	PA8TSS8D
MICROCHIP	24LC08B	DIP8	
MICROCHIP	24LC08B	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24LC08B	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC08B	SOT23-5	PA5SOT5D
MICROCHIP	24LC08B	TSSOP8	PA24TSS24D
MICROCHIP	24LC08B	TSSOP8	PA8TSS8D
MICROCHIP	24LC08B-I/MS	MSOP8	HA8MSOP48D
MICROCHIP	24LC08B-I/P	DIP8	
MICROCHIP	24LC08B-I/SN	SOIC8	PA16SO16D-EO-150
MICROCHIP	24LC08B-I/ST	TSSOP8	PA8TSS8D
MICROCHIP	24LC09	DIP8	
MICROCHIP	24LC09	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC1025	DIP8	
MICROCHIP	24LC1025	SOIC8	PA20SO20D-EO-210
MICROCHIP	24LC128	DFN8	PA8SON8D(6x5)
MICROCHIP	24LC128	DIP8	
MICROCHIP	24LC128	SOIC8	PA20SO20D-EO-210
MICROCHIP	24LC128	TSSOP14	PA28TSS28D-EO
MICROCHIP	24LC128	TSSOP8	PA24TSS24D
MICROCHIP	24LC164	DIP8	
MICROCHIP	24LC164	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC16B	DIP8	
MICROCHIP	24LC16B	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24LC16B	SOIC14	PA16SO16D-EO-150
MICROCHIP	24LC16B	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC16B	SOT23-5	PA5SOT5D
MICROCHIP	24LC16B	TSSOP8	PA24TSS24D
MICROCHIP	24LC16B	TSSOP8	PA8TSS8D
MICROCHIP	24LC16B-I/MS	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24LC16B-I/P	DIP8	
MICROCHIP	24LC16B-I/SN	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC16B-I/ST	TSSOP8	PA8TSS8D
MICROCHIP	24LC174	DIP8	
MICROCHIP	24LC174	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC21	DIP8	
MICROCHIP	24LC21	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC211	DIP8	
MICROCHIP	24LC211	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC21A	DIP8	
MICROCHIP	24LC21A	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC21A-I/P	DIP8	
MICROCHIP	24LC21A-I/SN	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC22A	DIP8	
MICROCHIP	24LC22A	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC22A-I/P	DIP8	
MICROCHIP	24LC22A-I/SN	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC256	DFN8	PA8SON8D(6x5)
MICROCHIP	24LC256	DIP8	
MICROCHIP	24LC256	SOIC8	PA20SO20D-EO-210
MICROCHIP	24LC256	TSSOP14	PA28TSS28D-EO
MICROCHIP	24LC256	TSSOP8	PA24TSS24D
MICROCHIP	24LC32	DIP8	
MICROCHIP	24LC32	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC32A	DIP8	
MICROCHIP	24LC32A	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24LC32A	SOIC8	PA16SO16D-EO-150
MICROCHIP	24LC32A	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC32A	TSSOP8	PA24TSS24D
MICROCHIP	24LC32A	TSSOP8	PA8TSS8D
MICROCHIP	24LC32A-I/MS	MSOP8	HA8MSOP48D

MICROCHIP	24LC32A-I/P	DIP8	
MICROCHIP	24LC32A-I/SM	SOIC8	PA20SO20D-EO-210
MICROCHIP	24LC32A-I/SN	SOIC8	PA16SO16D-EO-150
MICROCHIP	24LC32A-I/ST	TSSOP8	PA8TSS8D
MICROCHIP	24LC32AX	TSSOP8	PA8RTSS8D
MICROCHIP	24LC41	DIP8	
MICROCHIP	24LC41	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC41A	DIP8	
MICROCHIP	24LC41A	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC512	DFN8	PA8SON8D(6x5)
MICROCHIP	24LC512	DIP8	
MICROCHIP	24LC512	SOIC8	PA20SO20D-EO-210
MICROCHIP	24LC512	TSSOP14	PA28TSS28D-EO
MICROCHIP	24LC512	TSSOP8	PA24TSS24D
MICROCHIP	24LC515	DIP8	
MICROCHIP	24LC515	SOIC8	PA16SO16D-EO-150
MICROCHIP	24LC515	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC64	DIP8	
MICROCHIP	24LC64	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24LC64	SOIC8	PA16SO16D-EO-150
MICROCHIP	24LC64	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LC64	TSSOP8	PA24TSS24D
MICROCHIP	24LC64	TSSOP8	PA8TSS8D
MICROCHIP	24LC64X	TSSOP8	PA8RTSS8D
MICROCHIP	24LC65	DIP8	
MICROCHIP	24LC65	SOIC8	PA16SO16D-EO-150
MICROCHIP	24LC65	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LCS21	DIP8	
MICROCHIP	24LCS21	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LCS21A	DIP8	
MICROCHIP	24LCS21A	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LCS22A	DIP8	
MICROCHIP	24LCS22A	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LCS41	DIP8	
MICROCHIP	24LCS41A	DIP8	
MICROCHIP	24LCS52	DIP8	
MICROCHIP	24LCS52	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	24LCS52	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LCS52	TSSOP8	PA24TSS24D
MICROCHIP	24LCS52	TSSOP8	PA8TSS8D
MICROCHIP	24LCS52	TSSOP8	PA8TSS-OT
MICROCHIP	24LCS61	DIP8	
MICROCHIP	24LCS61	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LCS61	TSSOP14	PA28TSS28D-EO
MICROCHIP	24LCS62	DIP8	
MICROCHIP	24LCS62	SOIC8	PA8SO8D-EO-150
MICROCHIP	24LCS62	TSSOP14	PA28TSS28D-EO
MICROCHIP	25AA02UID-I/SN	SOIC8	PA16SO16D-EO-150
MICROCHIP	25AA040	DIP8	
MICROCHIP	25AA040	SOIC8	PA16SO16D-EO-150
MICROCHIP	25AA040	TSSOP8	PA24TSS24D
MICROCHIP	25AA040	TSSOP8	PA8TSS8D
MICROCHIP	25AA080	DIP8	
MICROCHIP	25AA080	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	25AA080	SOIC8	PA16SO16D-EO-150
MICROCHIP	25AA080A	DIP8	
MICROCHIP	25AA080A	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	25AA080A	SOIC8	PA16SO16D-EO-150
MICROCHIP	25AA080A	TSSOP8	PA24TSS24D
MICROCHIP	25AA080A	TSSOP8	PA8TSS8D
MICROCHIP	25AA080B	DIP8	
MICROCHIP	25AA080B	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	25AA080B	SOIC8	PA16SO16D-EO-150
MICROCHIP	25AA080B	TSSOP8	PA24TSS24D
MICROCHIP	25AA080B	TSSOP8	PA8TSS8D
MICROCHIP	25AA1024	DFN8	PA8SON8D(6x5)
MICROCHIP	25AA1024	DIP8	
MICROCHIP	25AA1024	SOIC8	PA20SO20D-EO-210
MICROCHIP	25AA160	DIP8	
MICROCHIP	25AA160	SOIC8	PA16SO16D-EO-150
MICROCHIP	25AA160A	DIP8	
MICROCHIP	25AA160A	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	25AA160A	SOIC8	PA16SO16D-EO-150



MICROCHIP	25AA160A	TSSOP8	PA24TSS24D
MICROCHIP	25AA160A	TSSOP8	PA8TSS8D
MICROCHIP	25AA160B	DIP8	
MICROCHIP	25AA160B	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	25AA160B	SOIC8	PA16SO16D-EO-150
MICROCHIP	25AA160B	TSSOP8	PA24TSS24D
MICROCHIP	25AA160B	TSSOP8	PA8TSS8D
MICROCHIP	25AA256	DFN8	PA8SON8D(6x5)
MICROCHIP	25AA256	DIP8	
MICROCHIP	25AA256	SOIC8	PA16SO16D-EO-150
MICROCHIP	25AA256X	TSSOP8	PA24TSS24D
MICROCHIP	25AA256X	TSSOP8	PA8TSS8D
MICROCHIP	25AA320	DIP8	
MICROCHIP	25AA320	SOIC8	PA16SO16D-EO-150
MICROCHIP	25AA320X	TSSOP8	PA24TSS24D
MICROCHIP	25AA320X	TSSOP8	PA8TSS8D
MICROCHIP	25AA512	DFN8	PA8SON8D(6x5)
MICROCHIP	25AA512	DIP8	
MICROCHIP	25AA512	SOIC8	PA16SO16D-EO-150
MICROCHIP	25AA512X	TSSOP8	PA24TSS24D
MICROCHIP	25AA512X	TSSOP8	PA8TSS8D
MICROCHIP	25AA640	DIP8	
MICROCHIP	25AA640	SOIC8	PA16SO16D-EO-150
MICROCHIP	25AA640X	TSSOP8	PA24TSS24D
MICROCHIP	25AA640X	TSSOP8	PA8TSS8D
MICROCHIP	25C040	DIP8	
MICROCHIP	25C040	SOIC8	PA16SO16D-EO-150
MICROCHIP	25C040	TSSOP8	PA24TSS24D
MICROCHIP	25C040	TSSOP8	PA8TSS8D
MICROCHIP	25C080	DIP8	
MICROCHIP	25C080	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	25C080	SOIC8	PA16SO16D-EO-150
MICROCHIP	25C160	DIP8	
MICROCHIP	25C160	SOIC8	PA16SO16D-EO-150
MICROCHIP	25C320	DIP8	
MICROCHIP	25C320	SOIC8	PA16SO16D-EO-150
MICROCHIP	25C320	TSSOP14	PA14TSS14D
MICROCHIP	25C320X	TSSOP8	PA24TSS24D
MICROCHIP	25C320X	TSSOP8	PA8TSS8D
MICROCHIP	25C640	DIP8	
MICROCHIP	25C640	SOIC8	PA16SO16D-EO-150
MICROCHIP	25C640X	TSSOP8	PA24TSS24D
MICROCHIP	25C640X	TSSOP8	PA8TSS8D
MICROCHIP	25LC040	DIP8	
MICROCHIP	25LC040	SOIC8	PA16SO16D-EO-150
MICROCHIP	25LC040	TSSOP8	PA24TSS24D
MICROCHIP	25LC040	TSSOP8	PA8TSS8D
MICROCHIP	25LC080	DIP8	
MICROCHIP	25LC080	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	25LC080	SOIC8	PA16SO16D-EO-150
MICROCHIP	25LC080A	DIP8	
MICROCHIP	25LC080A	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	25LC080A	SOIC8	PA16SO16D-EO-150
MICROCHIP	25LC080A	TSSOP8	PA24TSS24D
MICROCHIP	25LC080A	TSSOP8	PA8TSS8D
MICROCHIP	25LC080B	DIP8	
MICROCHIP	25LC080B	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	25LC080B	SOIC8	PA16SO16D-EO-150
MICROCHIP	25LC080B	TSSOP8	PA24TSS24D
MICROCHIP	25LC080B	TSSOP8	PA8TSS8D
MICROCHIP	25LC1024	DFN8	PA8SON8D(6x5)
MICROCHIP	25LC1024	DIP8	
MICROCHIP	25LC1024	SOIC8	PA20SO20D-EO-210
MICROCHIP	25LC160	DIP8	
MICROCHIP	25LC160	SOIC8	PA16SO16D-EO-150
MICROCHIP	25LC160A	DIP8	
MICROCHIP	25LC160A	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	25LC160A	SOIC8	PA16SO16D-EO-150
MICROCHIP	25LC160A	TSSOP8	PA24TSS24D
MICROCHIP	25LC160A	TSSOP8	PA8TSS8D
MICROCHIP	25LC160B	DIP8	
MICROCHIP	25LC160B	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	25LC160B	SOIC8	PA16SO16D-EO-150

MICROCHIP	25LC160B		TSSOP8	PA24TSS24D
MICROCHIP	25LC160B		TSSOP8	PA8TSS8D
MICROCHIP	25LC256		DFN8	PA8SON8D(6x5)
MICROCHIP	25LC256		DIP8	
MICROCHIP	25LC256		SOIC8	PA16SO16D-EO-150
MICROCHIP	25LC256X		TSSOP8	PA24TSS24D
MICROCHIP	25LC256X		TSSOP8	PA8TSS8D
MICROCHIP	25LC320		DIP8	
MICROCHIP	25LC320		SOIC8	PA16SO16D-EO-150
MICROCHIP	25LC320		TSSOP14	PA14TSS14D
MICROCHIP	25LC320X		TSSOP8	PA24TSS24D
MICROCHIP	25LC320X		TSSOP8	PA8TSS8D
MICROCHIP	25LC512		DFN8	PA8SON8D(6x5)
MICROCHIP	25LC512		DIP8	
MICROCHIP	25LC512		SOIC8	PA16SO16D-EO-150
MICROCHIP	25LC512		SOIC8	PA20SO20D-EO-210
MICROCHIP	25LC640		DIP8	
MICROCHIP	25LC640		SOIC8	PA16SO16D-EO-150
MICROCHIP	25LC640X		TSSOP8	PA24TSS24D
MICROCHIP	25LC640X		TSSOP8	PA8TSS8D
MICROCHIP		27256	DIP28	
MICROCHIP		27256	PLCC32	PA32PL28D-YA
MICROCHIP	27C128		DIP28	
MICROCHIP	27C128		PLCC32	PA32PL28D-YA
MICROCHIP	27C128		SOIC28	PA28SO28D-EO-300
MICROCHIP	27C256		DIP28	
MICROCHIP	27C256		PLCC32	PA32PL28D-YA
MICROCHIP	27C256		SOIC28	PA28SO28D-EO-300
MICROCHIP	27C256		TSOP28	PA28TS28D-EO
MICROCHIP	27C512		DIP28	
MICROCHIP	27C512		PLCC32	PA32PL28D-YA
MICROCHIP	27C512		SOIC28	PA28SO28D-EO-300
MICROCHIP	27C512A		DIP28	
MICROCHIP	27C512A		PLCC32	PA32PL28D-YA
MICROCHIP	27C512A		SOIC28	PA28SO28D-EO-300
MICROCHIP	27C512A		TSOP28	PA28TS28D-EO
MICROCHIP	27C64		DIP28	
MICROCHIP	27C64		PLCC32	PA32PL28D-YA
MICROCHIP	27C64		SOIC28	PA28SO28D-EO-300
MICROCHIP	27HC128		DIP28	
MICROCHIP	27HC128		PLCC32	PA32PL28D-YA
MICROCHIP	27HC128		SOIC28	PA28SO28D-EO-300
MICROCHIP	27HC256		DIP28	
MICROCHIP	27HC256		PLCC32	PA32PL28D-YA
MICROCHIP	27HC256		SOIC28	PA28SO28D-EO-300
MICROCHIP	27HC256L		DIP28	
MICROCHIP	27HC256L		PLCC32	PA32PL28D-YA
MICROCHIP	27HC256L		SOIC28	PA28SO28D-EO-300
MICROCHIP	27HC64		DIP28	
MICROCHIP	27HC64		PLCC32	PA32PL28D-YA
MICROCHIP	27HC64		SOIC28	PA28SO28D-EO-300
MICROCHIP	27HC64L		DIP28	
MICROCHIP	27LV256		DIP28	
MICROCHIP	27LV256		PLCC32	PA32PL28D-YA
MICROCHIP	27LV256		SOIC28	PA28SO28D-EO-300
MICROCHIP	27LV256		TSOP28	PA28TS28D-EO
MICROCHIP	27LV512		DIP28	
MICROCHIP	27LV512		PLCC32	PA32PL28D-YA
MICROCHIP	27LV512		SOIC28	PA28SO28D-EO-300
MICROCHIP	27LV512		TSOP28	PA28TS28D-EO
MICROCHIP	27LV64		DIP28	
MICROCHIP	27LV64		PLCC32	PA32PL28D-YA
MICROCHIP	27LV64		SOIC28	PA28SO28D-EO-300
MICROCHIP	28C04		DIP24	
MICROCHIP	28C04A		DIP24	
MICROCHIP	28C04A		PLCC32	PA32PL32D
MICROCHIP	28C04AF		DIP24	
MICROCHIP	28C04AF		PLCC32	PA32PL32D
MICROCHIP	28C04F		DIP24	
MICROCHIP	28C16		DIP24	
MICROCHIP	28C16A		DIP24	
MICROCHIP	28C16A		PLCC32	PA32PL32D
MICROCHIP	28C16AF		DIP24	

MICROCHIP	28C16AF	PLCC32	PA32PL32D
MICROCHIP	28C16F	DIP24	
MICROCHIP	28C17	DIP28	
MICROCHIP	28C17A	DIP28	
MICROCHIP	28C17A	PLCC32	PA32PL28D-YA
MICROCHIP	28C17AF	DIP28	
MICROCHIP	28C17AF	PLCC32	PA32PL28D-YA
MICROCHIP	28C17F	DIP28	
MICROCHIP	28C64	DIP28	
MICROCHIP	28C64A	DIP28	
MICROCHIP	28C64AF	DIP28	
MICROCHIP	28C64AX	DIP28	
MICROCHIP	34AA04	DFN8	PA8QFN8D(2x3)
MICROCHIP	37LV128	DIP8	
MICROCHIP	37LV36	DIP8	
MICROCHIP	37LV65	DIP8	
MICROCHIP	65P542R	SOIC28	PA28SO28D-EO-300
MICROCHIP	85C72	DIP8	
MICROCHIP	85C72	SOP8	PA20SO20D-EO-210
MICROCHIP	85C82	DIP8	
MICROCHIP	85C82	SOP8	PA20SO20D-EO-210
MICROCHIP	85C92	DIP8	
MICROCHIP	85C92	SOIC14	PA16SO16D-EO-150
MICROCHIP	85C92	SOP8	PA20SO20D-EO-210
MICROCHIP	89C54	DIP40	
MICROCHIP	89C54	PLCC44	PA44-48U
MICROCHIP	89C54	QFP44	PA44QF44D
MICROCHIP	89C58	DIP40	
MICROCHIP	89C58	PLCC44	PA44-48U
MICROCHIP	89C58	QFP44	PA44QF44D
MICROCHIP	89C59	DIP40	
MICROCHIP	89C59	PLCC44	PA44-48U
MICROCHIP	89C59	QFP44	PA44QF44D
MICROCHIP	89E516RD	DIP40	
MICROCHIP	89E516RD	PLCC44	PA44-48U
MICROCHIP	89E516RD	TQFP44	PA44QF44D
MICROCHIP	89E516RD2	PLCC44	PA44-48U
MICROCHIP	89E516RD2	TQFP44	PA44QF44D
MICROCHIP	89E52RD	DIP40	
MICROCHIP	89E52RD	PLCC44	PA44-48U
MICROCHIP	89E52RD	TQFP44	PA44QF44D
MICROCHIP	89E52RD2	PLCC44	PA44-48U
MICROCHIP	89E52RD2	TQFP44	PA44QF44D
MICROCHIP	89E54RD	DIP40	
MICROCHIP	89E54RD	PLCC44	PA44-48U
MICROCHIP	89E54RD	TQFP44	PA44QF44D
MICROCHIP	89E54RD2	PLCC44	PA44-48U
MICROCHIP	89E54RD2	TQFP44	PA44QF44D
MICROCHIP	89E554RC	DIP40	
MICROCHIP	89E554RC	PLCC44	PA44-48U
MICROCHIP	89E564RD	DIP40	
MICROCHIP	89E564RD	PLCC44	PA44-48U
MICROCHIP	89E564RD	WQFN40	PA40WQ40D
MICROCHIP	89E58RD	DIP40	
MICROCHIP	89E58RD	PLCC44	PA44-48U
MICROCHIP	89E58RD	TQFP44	PA44QF44D
MICROCHIP	89E58RD2	PLCC44	PA44-48U
MICROCHIP	89E58RD2	TQFP44	PA44QF44D
MICROCHIP	89F54	DIP40	
MICROCHIP	89F54	PLCC44	PA44-48U
MICROCHIP	89F58	DIP40	
MICROCHIP	89F58	PLCC44	PA44-48U
MICROCHIP	89V516RD	DIP40	
MICROCHIP	89V516RD	PLCC44	PA44-48U
MICROCHIP	89V516RD	TQFP44	PA44QF44D
MICROCHIP	89V516RD2	PLCC44	PA44-48U
MICROCHIP	89V516RD2	TQFP44	PA44QF44D
MICROCHIP	89V52RD	DIP40	
MICROCHIP	89V52RD	PLCC44	PA44-48U
MICROCHIP	89V52RD	QFP44	PA44QF44D
MICROCHIP	89V52RD2	PLCC44	PA44-48U
MICROCHIP	89V52RD2	TQFP44	PA44QF44D
MICROCHIP	89V54RD	DIP40	

MICROCHIP	89V54RD	PLCC44	PA44-48U
MICROCHIP	89V54RD	TQFP44	PA44QF44D
MICROCHIP	89V54RD2	PLCC44	PA44-48U
MICROCHIP	89V54RD2	TQFP44	PA44QF44D
MICROCHIP	89V554RC	DIP40	
MICROCHIP	89V554RC	PLCC44	PA44-48U
MICROCHIP	89V564RD	DIP40	
MICROCHIP	89V564RD	PLCC44	PA44-48U
MICROCHIP	89V564RD	WQFN40	PA40WQ40D
MICROCHIP	89V58RD	DIP40	
MICROCHIP	89V58RD	PLCC44	PA44-48U
MICROCHIP	89V58RD	TQFP44	PA44QF44D
MICROCHIP	89V58RD2	PLCC44	PA44-48U
MICROCHIP	89V58RD2	TQFP44	PA44QF44D
MICROCHIP	93AA46	DIP8	
MICROCHIP	93AA46	SOIC8	PA16SO16D-EO-150
MICROCHIP	93AA46A	DIP8	
MICROCHIP	93AA46A	SOIC8	PA16SO16D-EO-150
MICROCHIP	93AA46A	TSSOP8	PA8TSS-OT
MICROCHIP	93AA46AX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93AA46B	DIP8	
MICROCHIP	93AA46B	SOIC8	PA16SO16D-EO-150
MICROCHIP	93AA46B	TSSOP8	PA8TSS-OT
MICROCHIP	93AA46BX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93AA46C	DIP8	
MICROCHIP	93AA46C	SOIC8	PA16SO16D-EO-150
MICROCHIP	93AA46C	TSSOP8	PA8TSS-OT
MICROCHIP	93AA46CX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93AA46X	SOIC8	PA8SO8D-EO-150
MICROCHIP	93AA56	DIP8	
MICROCHIP	93AA56	SOIC8	PA16SO16D-EO-150
MICROCHIP	93AA56A	DIP8	
MICROCHIP	93AA56A	SOIC8	PA16SO16D-EO-150
MICROCHIP	93AA56A	TSSOP8	PA8TSS-OT
MICROCHIP	93AA56AX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93AA56B	DIP8	
MICROCHIP	93AA56B	SOIC8	PA16SO16D-EO-150
MICROCHIP	93AA56B	TSSOP8	PA8TSS-OT
MICROCHIP	93AA56BX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93AA56C	DIP8	
MICROCHIP	93AA56C	SOIC8	PA16SO16D-EO-150
MICROCHIP	93AA56C	TSSOP8	PA8TSS-OT
MICROCHIP	93AA56CX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93AA56X	SOIC8	PA8SO8D-EO-150
MICROCHIP	93AA66	DIP8	
MICROCHIP	93AA66	SOIC8	PA16SO16D-EO-150
MICROCHIP	93AA66A	DIP8	
MICROCHIP	93AA66A	SOIC8	PA16SO16D-EO-150
MICROCHIP	93AA66A	TSSOP8	PA8TSS-OT
MICROCHIP	93AA66AX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93AA66B	DIP8	
MICROCHIP	93AA66B	SOIC8	PA16SO16D-EO-150
MICROCHIP	93AA66B	TSSOP8	PA8TSS-OT
MICROCHIP	93AA66BX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93AA66C	DIP8	
MICROCHIP	93AA66C	SOIC8	PA16SO16D-EO-150
MICROCHIP	93AA66C	TSSOP8	PA8TSS-OT
MICROCHIP	93AA66CX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93AA66X	SOIC8	PA8SO8D-EO-150
MICROCHIP	93AA76	DIP8	
MICROCHIP	93AA76	SOIC8	PA16SO16D-EO-150
MICROCHIP	93AA76B	DIP8	
MICROCHIP	93AA76B	SOIC8	PA16SO16D-EO-150
MICROCHIP	93AA76C	DIP8	
MICROCHIP	93AA76C	SOIC8	PA16SO16D-EO-150
MICROCHIP	93AA76C	TSSOP8	PA8TSS-OT
MICROCHIP	93AA76X	SOIC8	PA8SO8D-EO-150
MICROCHIP	93AA86	DIP8	
MICROCHIP	93AA86	SOIC8	PA16SO16D-EO-150
MICROCHIP	93AA86B	DIP8	
MICROCHIP	93AA86B	SOIC8	PA16SO16D-EO-150
MICROCHIP	93AA86C	DIP8	
MICROCHIP	93AA86C	SOIC8	PA16SO16D-EO-150

MICROCHIP	93AA86C	TSSOP8	PA8TSS-OT
MICROCHIP	93AA86X	SOIC8	PA8SO8D-EO-150
MICROCHIP	93C06	DIP8	
MICROCHIP	93C06	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C46	DIP8	
MICROCHIP	93C46	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C46A	DIP8	
MICROCHIP	93C46A	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C46A	TSSOP8	PA8TSS-OT
MICROCHIP	93C46AX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93C46B	DIP8	
MICROCHIP	93C46B	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C46B	TSSOP8	PA8TSS-OT
MICROCHIP	93C46BX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93C46C	DIP8	
MICROCHIP	93C46C	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C46C	TSSOP8	PA8TSS-OT
MICROCHIP	93C46CX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93C46X	SOIC8	PA8SO8D-EO-150
MICROCHIP	93C56	DIP8	
MICROCHIP	93C56	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C56A	DIP8	
MICROCHIP	93C56A	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C56A	TSSOP8	PA8TSS-OT
MICROCHIP	93C56AX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93C56B	DIP8	
MICROCHIP	93C56B	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C56B	TSSOP8	PA8TSS-OT
MICROCHIP	93C56BX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93C56C	DIP8	
MICROCHIP	93C56C	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C56C	TSSOP8	PA8TSS-OT
MICROCHIP	93C56CX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93C56X	SOIC8	PA8SO8D-EO-150
MICROCHIP	93C66	DIP8	
MICROCHIP	93C66	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C66A	DIP8	
MICROCHIP	93C66A	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C66A	TSSOP8	PA8TSS-OT
MICROCHIP	93C66AX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93C66B	DIP8	
MICROCHIP	93C66B	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C66B	TSSOP8	PA8TSS-OT
MICROCHIP	93C66BX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93C66C	DIP8	
MICROCHIP	93C66C	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C66C	TSSOP8	PA8TSS-OT
MICROCHIP	93C66CX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93C76	DIP8	
MICROCHIP	93C76	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C76A	DIP8	
MICROCHIP	93C76A	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C76B	DIP8	
MICROCHIP	93C76B	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C76C	DIP8	
MICROCHIP	93C76C	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C76C	TSSOP8	PA8TSS-OT
MICROCHIP	93C76C-I/MS	MSOP8	HA8MSOP48D
MICROCHIP	93C76C-I/P	DIP8	
MICROCHIP	93C76C-I/SN	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C76C-I/ST	TSSOP8	PA8TSS8D
MICROCHIP	93C86	DIP8	
MICROCHIP	93C86	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C86A	DIP8	
MICROCHIP	93C86A	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C86B	DIP8	
MICROCHIP	93C86B	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C86C	DIP8	
MICROCHIP	93C86C	SOIC8	PA16SO16D-EO-150
MICROCHIP	93C86C	TSSOP8	PA8TSS-OT
MICROCHIP	93C86C-I/MS	MSOP8	HA8MSOP48D
MICROCHIP	93C86C-I/P	DIP8	
MICROCHIP	93C86C-I/SN	SOIC8	PA16SO16D-EO-150

MICROCHIP	93C86C-I/ST	TSSOP8	PA8TSS8D
MICROCHIP	93LC46	DIP8	
MICROCHIP	93LC46	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC46A	DIP8	
MICROCHIP	93LC46A	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC46A	TSSOP8	PA8TSS-OT
MICROCHIP	93LC46AX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93LC46B	DIP8	
MICROCHIP	93LC46B	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC46B	TSSOP8	PA8TSS-OT
MICROCHIP	93LC46BX	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC46C	DIP8	
MICROCHIP	93LC46C	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC46C	TSSOP8	PA8TSS-OT
MICROCHIP	93LC46C-I/MS	MSOP8	HA8MSOP48D
MICROCHIP	93LC46C-I/P	DIP8	
MICROCHIP	93LC46C-I/SN	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC46C-I/ST	TSSOP8	PA8TSS8D
MICROCHIP	93LC46CX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93LC46X	SOIC8	PA8SO8D-EO-150
MICROCHIP	93LC56	DIP8	
MICROCHIP	93LC56	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC56A	DIP8	
MICROCHIP	93LC56A	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC56A	TSSOP8	PA8TSS-OT
MICROCHIP	93LC56A-I/MS	MSOP8	HA8MSOP48D
MICROCHIP	93LC56A-I/P	DIP8	
MICROCHIP	93LC56A-I/SN	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC56A-I/ST	TSSOP8	PA8TSS8D
MICROCHIP	93LC56AX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93LC56B	DIP8	
MICROCHIP	93LC56B	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC56B	TSSOP8	PA8TSS-OT
MICROCHIP	93LC56B-I/MS	MSOP8	HA8MSOP48D
MICROCHIP	93LC56B-I/P	DIP8	
MICROCHIP	93LC56B-I/SN	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC56B-I/ST	TSSOP8	PA8TSS8D
MICROCHIP	93LC56BX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93LC56C	DIP8	
MICROCHIP	93LC56C	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC56C	TSSOP8	PA8TSS-OT
MICROCHIP	93LC56CX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93LC56X	SOIC8	PA8SO8D-EO-150
MICROCHIP	93LC66	DIP8	
MICROCHIP	93LC66	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC66A	DIP8	
MICROCHIP	93LC66A	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC66A	TSSOP8	PA8TSS-OT
MICROCHIP	93LC66AX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93LC66B	DIP8	
MICROCHIP	93LC66B	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC66B	TSSOP8	PA8TSS-OT
MICROCHIP	93LC66BX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93LC66C	DIP8	
MICROCHIP	93LC66C	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC66C	TSSOP8	PA8TSS-OT
MICROCHIP	93LC66CX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93LC66X	SOIC8	PA8SO8D-EO-150
MICROCHIP	93LC76	DIP8	
MICROCHIP	93LC76	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC76A	DIP8	
MICROCHIP	93LC76A	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC76AX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93LC76B	DIP8	
MICROCHIP	93LC76B	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC76C	DIP8	
MICROCHIP	93LC76C	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC76C	TSSOP8	PA8TSS-OT
MICROCHIP	93LC76X	SOIC8	PA8SO8D-EO-150
MICROCHIP	93LC86	DIP8	
MICROCHIP	93LC86	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC86A	DIP8	
MICROCHIP	93LC86A	SOIC8	PA16SO16D-EO-150

MICROCHIP	93LC86AX	SOIC8	PA8SO8D-EO-150
MICROCHIP	93LC86B	DIP8	
MICROCHIP	93LC86B	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC86C	DIP8	
MICROCHIP	93LC86C	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC86C	TSSOP8	PA8TSS-OT
MICROCHIP	93LC86C-I/MS	MSOP8	HA8MSOP48D
MICROCHIP	93LC86C-I/P	DIP8	
MICROCHIP	93LC86C-I/SN	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LC86C-I/ST	TSSOP8	PA8TSS8D
MICROCHIP	93LC86X	SOIC8	PA8SO8D-EO-150
MICROCHIP	93LCS56	DIP8	
MICROCHIP	93LCS56	SOIC8	PA16SO16D-EO-150
MICROCHIP	93LCS66	DIP8	
MICROCHIP	93LCS66	SOIC8	PA16SO16D-EO-150
MICROCHIP	AT89LP51	DIP40	
MICROCHIP	AT89LP51	PLCC44	PA44-48U
MICROCHIP	AT89LP51	QFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	AT89LP52	DIP40	
MICROCHIP	AT89LP52	PLCC44	PA44-48U
MICROCHIP	AT89LP52	QFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	ATmega168	DIP28	
MICROCHIP	ATmega168	TQFP32	PA32TQ32D
MICROCHIP	ATmega168	TQFP32	PA32TQ32DA
MICROCHIP	ATmega168A	DIP28	
MICROCHIP	ATmega168A	TQFP32	PA32TQ32D
MICROCHIP	ATmega168A	TQFP32	PA32TQ32DA
MICROCHIP	ATmega168P	DIP28	
MICROCHIP	ATmega168P	TQFP32	PA32TQ32D
MICROCHIP	ATmega168P	TQFP32	PA32TQ32DA
MICROCHIP	ATmega168PA	DIP28	
MICROCHIP	ATmega168PA	TQFP32	PA32TQ32D
MICROCHIP	ATmega168PA	TQFP32	PA32TQ32DA
MICROCHIP	ATmega168PB	DIP28	
MICROCHIP	ATmega168PB	TQFP32	PA32TQ32D
MICROCHIP	ATmega168PB	TQFP32	PA32TQ32DA
MICROCHIP	ATmega168PV	DIP28	
MICROCHIP	ATmega168PV	TQFP32	PA32TQ32D
MICROCHIP	ATmega168PV	TQFP32	PA32TQ32DA
MICROCHIP	ATmega168V	DIP28	
MICROCHIP	ATmega168V	TQFP32	PA32TQ32D
MICROCHIP	ATmega168V	TQFP32	PA32TQ32DA
MICROCHIP	ATmega328P	DIP28	
MICROCHIP	ATmega328P	TQFP32	PA32TQ32D
MICROCHIP	ATmega328P	TQFP32	PA32TQ32DA
MICROCHIP	ATmega48	DIP28	
MICROCHIP	ATmega48	TQFP32	PA32TQ32D
MICROCHIP	ATmega48	TQFP32	PA32TQ32DA
MICROCHIP	ATmega48A	DIP28	
MICROCHIP	ATmega48A	TQFP32	PA32TQ32D
MICROCHIP	ATmega48A	TQFP32	PA32TQ32DA
MICROCHIP	ATmega48P	DIP28	
MICROCHIP	ATmega48P	TQFP32	PA32TQ32D
MICROCHIP	ATmega48P	TQFP32	PA32TQ32DA
MICROCHIP	ATmega48PA	DIP28	
MICROCHIP	ATmega48PA	TQFP32	PA32TQ32D
MICROCHIP	ATmega48PA	TQFP32	PA32TQ32DA
MICROCHIP	ATmega48PB	DIP28	
MICROCHIP	ATmega48PB	TQFP32	PA32TQ32D
MICROCHIP	ATmega48PB	TQFP32	PA32TQ32DA
MICROCHIP	ATmega48PV	DIP28	
MICROCHIP	ATmega48PV	TQFP32	PA32TQ32D
MICROCHIP	ATmega48PV	TQFP32	PA32TQ32DA
MICROCHIP	ATmega48V	DIP28	
MICROCHIP	ATmega48V	TQFP32	PA32TQ32D
MICROCHIP	ATmega48V	TQFP32	PA32TQ32DA
MICROCHIP	ATmega8	DIP28	
MICROCHIP	ATmega8	TQFP32	PA32TQ32D
MICROCHIP	ATmega8	TQFP32	PA32TQ32DA
MICROCHIP	ATmega88	DIP28	
MICROCHIP	ATmega88	TQFP32	PA32TQ32D
MICROCHIP	ATmega88	TQFP32	PA32TQ32DA
MICROCHIP	ATmega88A	DIP28	

MICROCHIP	ATmega88A	TQFP32	PA32TQ32D
MICROCHIP	ATmega88A	TQFP32	PA32TQ32DA
MICROCHIP	ATmega88P	DIP28	
MICROCHIP	ATmega88P	TQFP32	PA32TQ32D
MICROCHIP	ATmega88P	TQFP32	PA32TQ32DA
MICROCHIP	ATmega88PA	DIP28	
MICROCHIP	ATmega88PA	TQFP32	PA32TQ32D
MICROCHIP	ATmega88PA	TQFP32	PA32TQ32DA
MICROCHIP	ATmega88PB	DIP28	
MICROCHIP	ATmega88PB	TQFP32	PA32TQ32D
MICROCHIP	ATmega88PB	TQFP32	PA32TQ32DA
MICROCHIP	ATmega88PV	DIP28	
MICROCHIP	ATmega88PV	TQFP32	PA32TQ32D
MICROCHIP	ATmega88PV	TQFP32	PA32TQ32DA
MICROCHIP	ATmega88V	DIP28	
MICROCHIP	ATmega88V	TQFP32	PA32TQ32D
MICROCHIP	ATmega88V	TQFP32	PA32TQ32DA
MICROCHIP	ATmega8A	DIP28	
MICROCHIP	ATmega8A	TQFP32	PA32TQ32D
MICROCHIP	ATmega8A	TQFP32	PA32TQ32DA
MICROCHIP	ATmega8L	DIP28	
MICROCHIP	ATmega8L	TQFP32	PA32TQ32D
MICROCHIP	ATmega8L	TQFP32	PA32TQ32DA
MICROCHIP	dsPIC30F2010	DIP28	
MICROCHIP	dsPIC30F2010	QFN28	PA28QFN28D(6x6)
MICROCHIP	dsPIC30F2010	SOIC28	PA28SO28D-EO-300
MICROCHIP	dsPIC30F2011	DIP18	
MICROCHIP	dsPIC30F2011	QFN28	PA28QFN28D(6x6)
MICROCHIP	dsPIC30F2011	SOIC18	PA28SO28D-EO-300
MICROCHIP	dsPIC30F2012	DIP28	
MICROCHIP	dsPIC30F2012	QFN28	PA28QFN28D(6x6)
MICROCHIP	dsPIC30F2012	SOIC28	PA28SO28D-EO-300
MICROCHIP	dsPIC30F3010	DIP28	
MICROCHIP	dsPIC30F3010	QFN44	PA44QFN44D
MICROCHIP	dsPIC30F3010	SOIC28	PA28SO28D-EO-300
MICROCHIP	dsPIC30F3011	DIP40	
MICROCHIP	dsPIC30F3011	QFN44	PA44QFN44D
MICROCHIP	dsPIC30F3011	TQFP44	PA44TQ44D-EO
MICROCHIP	dsPIC30F3012	DIP18	
MICROCHIP	dsPIC30F3012	QFN44	PA44QFN44D
MICROCHIP	dsPIC30F3012	SOIC18	PA28SO28D-EO-300
MICROCHIP	dsPIC30F3013	DIP28	
MICROCHIP	dsPIC30F3013	QFN44	PA44QFN44D
MICROCHIP	dsPIC30F3013	SOIC28	PA28SO28D-EO-300
MICROCHIP	dsPIC30F3014	DIP40	
MICROCHIP	dsPIC30F3014	QFN44	PA44QFN44D
MICROCHIP	dsPIC30F3014	TQFP44	PA44TQ44D-EO
MICROCHIP	dsPIC30F4011	DIP40	
MICROCHIP	dsPIC30F4011	QFN44	PA44QFN44D
MICROCHIP	dsPIC30F4011	TQFP44	PA44TQ44D-EO
MICROCHIP	dsPIC30F4012	DIP28	
MICROCHIP	dsPIC30F4012	QFN44	PA44QFN44D
MICROCHIP	dsPIC30F4012	SOIC28	PA28SO28D-EO-300
MICROCHIP	dsPIC30F4013	DIP40	
MICROCHIP	dsPIC30F4013	QFN44	PA44QFN44D
MICROCHIP	dsPIC30F4013	TQFP44	PA44TQ44D-EO
MICROCHIP	HCS200	DIP8	
MICROCHIP	HCS200	SOIC8	PA16SO16D-EO-150
MICROCHIP	HCS201	DIP8	
MICROCHIP	HCS201	SOIC8	PA16SO16D-EO-150
MICROCHIP	HCS300	DIP8	
MICROCHIP	HCS300	SOIC8	PA16SO16D-EO-150
MICROCHIP	HCS301	DIP8	
MICROCHIP	HCS301	SOIC8	PA16SO16D-EO-150
MICROCHIP	HCS320	DIP8	
MICROCHIP	HCS320	SOIC8	PA16SO16D-EO-150
MICROCHIP	HCS360	DIP8	
MICROCHIP	HCS360	SOIC8	PA16SO16D-EO-150
MICROCHIP	HCS361	DIP8	
MICROCHIP	HCS361	SOIC8	PA16SO16D-EO-150
MICROCHIP	HCS362	DIP8	
MICROCHIP	HCS362	SOIC8	PA16SO16D-EO-150
MICROCHIP	HCS362	TSSOP8	PA8TSS-OT



MICROCHIP	HCS410	DIP8	
MICROCHIP	HCS410	SOIC8	PA16SO16D-EO-150
MICROCHIP	HCS410	TSSOP8	PA8TSS-OT
MICROCHIP	HCS412	DIP8	
MICROCHIP	HCS412	SOIC8	PA16SO16D-EO-150
MICROCHIP	MCP98244	DFN8	PA8QFN8D(2x3)
MICROCHIP	PH28EE011	DIP32	
MICROCHIP	PIC10F200	DIP8	
MICROCHIP	PIC10F200	SOT23-6	PA6SS6D-23
MICROCHIP	PIC10F202	DIP8	
MICROCHIP	PIC10F202	SOT23-6	PA6SS6D-23
MICROCHIP	PIC10F204	DIP8	
MICROCHIP	PIC10F204	SOT23-6	PA6SS6D-23
MICROCHIP	PIC10F206	DIP8	
MICROCHIP	PIC10F206	SOT23-6	PA6SS6D-23
MICROCHIP	PIC10F220	DIP8	
MICROCHIP	PIC10F220	SOT23-6	PA6SS6D-23
MICROCHIP	PIC10F222	DIP8	
MICROCHIP	PIC10F222	SOT23-6	PA6SS6D-23
MICROCHIP	PIC12C508	DIP8	
MICROCHIP	PIC12C508	SOIC8	PA20SO20D-EO-210
MICROCHIP	PIC12C508A	DIP8	
MICROCHIP	PIC12C508A	SOIC8	PA20SO20D-EO-210
MICROCHIP	PIC12C509	DIP8	
MICROCHIP	PIC12C509A	DIP8	
MICROCHIP	PIC12C509AF	DIP20	
MICROCHIP	PIC12C509AG	DIP18	
MICROCHIP	PIC12C671	DIP8	
MICROCHIP	PIC12C672	DIP8	
MICROCHIP	PIC12CE508	DIP8	
MICROCHIP	PIC12CE508A	DIP8	
MICROCHIP	PIC12CE509	DIP8	
MICROCHIP	PIC12CE509A	DIP8	
MICROCHIP	PIC12CE518	DIP8	
MICROCHIP	PIC12CE519	DIP8	
MICROCHIP	PIC12F1571	DIP8	
MICROCHIP	PIC12F1571	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	PIC12F1571	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	PIC12F1572	DIP8	
MICROCHIP	PIC12F1572	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	PIC12F1572	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	PIC12F1822-P	DIP8	
MICROCHIP	PIC12F1822-SN	SOIC8	PA8SO8D-EO-150
MICROCHIP	PIC12F508	DIP8	
MICROCHIP	PIC12F508	MSOP8	HA8MSOP48D
MICROCHIP	PIC12F508	SOIC8	PA16SO16D-EO-150
MICROCHIP	PIC12F509	DIP8	
MICROCHIP	PIC12F509	MSOP8	HA8MSOP48D
MICROCHIP	PIC12F509	SOIC8	PA16SO16D-EO-150
MICROCHIP	PIC12F510	DIP8	
MICROCHIP	PIC12F510	MSOP8	HA8MSOP48D
MICROCHIP	PIC12F510	SOIC8	PA16SO16D-EO-150
MICROCHIP	PIC12F519	DFN8	PA8QFN8D(2x3)
MICROCHIP	PIC12F519	DIP8	
MICROCHIP	PIC12F519	MSOP8	HA8MSOP48D
MICROCHIP	PIC12F519	SOIC8	PA16SO16D-EO-150
MICROCHIP	PIC12F609	DIP8	
MICROCHIP	PIC12F609	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	PIC12F609	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	PIC12F615	DIP8	
MICROCHIP	PIC12F615	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	PIC12F615	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	PIC12F617	DIP8	
MICROCHIP	PIC12F617	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	PIC12F617	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	PIC12F629	DIP8	
MICROCHIP	PIC12F629	SOIC8	PA16SO16D-EO-150
MICROCHIP	PIC12F635	DFN8	PA8SON8D(6x5)
MICROCHIP	PIC12F635	DIP8	
MICROCHIP	PIC12F635	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	PIC12F675	DIP8	
MICROCHIP	PIC12F675	SOIC8	PA16SO16D-EO-150
MICROCHIP	PIC12F683	DFN8	PA8SON8D(6x5)

MICROCHIP	PIC12F683	DIP8	
MICROCHIP	PIC12F683	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	PIC12HV609	DIP8	
MICROCHIP	PIC12HV609	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	PIC12HV609	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	PIC12HV615	DIP8	
MICROCHIP	PIC12HV615	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	PIC12HV615	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	PIC12LF1571	DIP8	
MICROCHIP	PIC12LF1571	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	PIC12LF1571	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	PIC12LF1572	DIP8	
MICROCHIP	PIC12LF1572	MSOP8	PA8MSOP8D/PA8SS8D-120
MICROCHIP	PIC12LF1572	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	PIC12LF1822	SOIC8	PA8SO8D-EO-150
MICROCHIP	PIC14000(OPT)	DIP28	
MICROCHIP	PIC14000(OPT)	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16C505	DIP14	
MICROCHIP	PIC16C52	DIP18	
MICROCHIP	PIC16C52(OTP)	DIP18	
MICROCHIP	PIC16C54	DIP18	
MICROCHIP	PIC16C54(OTP)	DIP18	
MICROCHIP	PIC16C54A	DIP18	
MICROCHIP	PIC16C54B	DIP18	
MICROCHIP	PIC16C54C	DIP18	
MICROCHIP	PIC16C55	DIP28	
MICROCHIP	PIC16C55(OTP)	DIP28	
MICROCHIP	PIC16C554	DIP18	
MICROCHIP	PIC16C556	DIP18	
MICROCHIP	PIC16C558	DIP18	
MICROCHIP	PIC16C55A	DIP28	
MICROCHIP	PIC16C55A	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16C56	DIP18	
MICROCHIP	PIC16C56(OTP)	DIP18	
MICROCHIP	PIC16C56A	DIP18	
MICROCHIP	PIC16C57	DIP28	
MICROCHIP	PIC16C57(OTP)	DIP28	
MICROCHIP	PIC16C57C	DIP28	
MICROCHIP	PIC16C58A	DIP18	
MICROCHIP	PIC16C58B	DIP18	
MICROCHIP	PIC16C61	DIP18	
MICROCHIP	PIC16C62	DIP28	
MICROCHIP	PIC16C620	DIP18	
MICROCHIP	PIC16C620A	DIP18	
MICROCHIP	PIC16C621	DIP18	
MICROCHIP	PIC16C621A	DIP18	
MICROCHIP	PIC16C622	DIP18	
MICROCHIP	PIC16C622A	DIP18	
MICROCHIP	PIC16C62A	DIP28	
MICROCHIP	PIC16C62B	DIP28	
MICROCHIP	PIC16C63	DIP28	
MICROCHIP	PIC16C63A	DIP28	
MICROCHIP	PIC16C64	DIP40	
MICROCHIP	PIC16C64	PLCC44	PA44-48U
MICROCHIP	PIC16C641	DIP28	
MICROCHIP	PIC16C642	DIP28	
MICROCHIP	PIC16C64A	DIP40	
MICROCHIP	PIC16C64A	PLCC44	PA44-48U
MICROCHIP	PIC16C65	DIP40	
MICROCHIP	PIC16C65	PLCC44	PA44-48U
MICROCHIP	PIC16C65A	DIP40	
MICROCHIP	PIC16C65A	PLCC44	PA44-48U
MICROCHIP	PIC16C65B	DIP40	
MICROCHIP	PIC16C65B	PLCC44	PA44-48U
MICROCHIP	PIC16C66	DIP28	
MICROCHIP	PIC16C661	DIP40	
MICROCHIP	PIC16C662	DIP40	
MICROCHIP	PIC16C67	DIP40	
MICROCHIP	PIC16C67	PLCC44	PA44-48U
MICROCHIP	PIC16C71	DIP18	
MICROCHIP	PIC16C710	DIP18	
MICROCHIP	PIC16C711	DIP18	
MICROCHIP	PIC16C712	DIP18	

MICROCHIP	PIC16C715	DIP18	
MICROCHIP	PIC16C716	DIP18	
MICROCHIP	PIC16C717	DIP18	
MICROCHIP	PIC16C72	DIP28	
MICROCHIP	PIC16C72A	DIP28	
MICROCHIP	PIC16C73	DIP28	
MICROCHIP	PIC16C73A	DIP28	
MICROCHIP	PIC16C73B	DIP28	
MICROCHIP	PIC16C73B	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16C74	DIP40	
MICROCHIP	PIC16C74	PLCC44	PA44-48U
MICROCHIP	PIC16C745	DIP28	
MICROCHIP	PIC16C74A	DIP40	
MICROCHIP	PIC16C74A	PLCC44	PA44-48U
MICROCHIP	PIC16C74B	DIP40	
MICROCHIP	PIC16C74B	PLCC44	PA44-48U
MICROCHIP	PIC16C76	DIP28	
MICROCHIP	PIC16C765	DIP40	
MICROCHIP	PIC16C77	DIP40	
MICROCHIP	PIC16C770	DIP20	
MICROCHIP	PIC16C771	DIP20	
MICROCHIP	PIC16C773	DIP28	
MICROCHIP	PIC16C774	DIP40	
MICROCHIP	PIC16C774	PLCC44	PA44-48U
MICROCHIP	PIC16C781	DIP20	
MICROCHIP	PIC16C782	DIP20	
MICROCHIP	PIC16C84	DIP18	
MICROCHIP	PIC16C923	PLCC68	PA756-68Z
MICROCHIP	PIC16C924	PLCC68	PA756-68Z
MICROCHIP	PIC16CE623	DIP18	
MICROCHIP	PIC16CE624	DIP18	
MICROCHIP	PIC16CE625	DIP18	
MICROCHIP	PIC16CR54A	DIP18	
MICROCHIP	PIC16CR54B	DIP18	
MICROCHIP	PIC16CR54C	DIP18	
MICROCHIP	PIC16CR56A	DIP18	
MICROCHIP	PIC16CR57B	DIP28	
MICROCHIP	PIC16CR57C	DIP28	
MICROCHIP	PIC16CR58A	DIP18	
MICROCHIP	PIC16CR58B	DIP18	
MICROCHIP	PIC16CR83	DIP18	
MICROCHIP	PIC16CR84	DIP18	
MICROCHIP	PIC16F1509	DIP20	
MICROCHIP	PIC16F1519	DIP40	
MICROCHIP	PIC16F1519	TQFP44	PA44TQ44D-EO
MICROCHIP	PIC16F1703	DIP14	
MICROCHIP	PIC16F1703	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16F1703	TSSOP14	PA24TSS24D
MICROCHIP	PIC16F1704	DIP14	
MICROCHIP	PIC16F1704	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16F1704	TSSOP14	PA24TSS24D
MICROCHIP	PIC16F1705	DIP14	
MICROCHIP	PIC16F1705	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16F1705	TSSOP14	PA24TSS24D
MICROCHIP	PIC16F1707	DIP20	
MICROCHIP	PIC16F1707	SOIC20	PA28SO28D-EO-300
MICROCHIP	PIC16F1707	SSOP20	PA28SS28D
MICROCHIP	PIC16F1708	DIP20	
MICROCHIP	PIC16F1708	SOIC20	PA28SO28D-EO-300
MICROCHIP	PIC16F1708	SSOP20	PA28SS28D
MICROCHIP	PIC16F1709	DIP20	
MICROCHIP	PIC16F1709	SOIC20	PA28SO28D-EO-300
MICROCHIP	PIC16F1709	SSOP20	PA28SS28D
MICROCHIP	PIC16F1823	DIP14	
MICROCHIP	PIC16F1823	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16F1826	DIP18	
MICROCHIP	PIC16F1826	SOIC18	PA28SO28D-EO-310
MICROCHIP	PIC16F1827	DIP18	
MICROCHIP	PIC16F1827	SOIC18	PA28SO28D-EO-310
MICROCHIP	PIC16F18313	DIP8	
MICROCHIP	PIC16F18313	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	PIC16F18323	DIP14	
MICROCHIP	PIC16F18323	SOIC14	PA16SO16D-EO-150

MICROCHIP	PIC16F18323	TSSOP14	PA24TSS24D
MICROCHIP	PIC16F18324	DIP14	
MICROCHIP	PIC16F18324	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16F18324	TSSOP14	PA24TSS24D
MICROCHIP	PIC16F18325	DIP14	
MICROCHIP	PIC16F18325	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16F18325	TSSOP14	PA24TSS24D
MICROCHIP	PIC16F18326	DIP14	
MICROCHIP	PIC16F18326	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16F18326	TSSOP14	PA24TSS24D
MICROCHIP	PIC16F18344	DIP20	
MICROCHIP	PIC16F18344	SOIC20	PA28SO28D-EO-300
MICROCHIP	PIC16F18344	SSOP20	PA28SS28D
MICROCHIP	PIC16F18345	DIP20	
MICROCHIP	PIC16F18345	SOIC20	PA28SO28D-EO-300
MICROCHIP	PIC16F18345	SSOP20	PA28SS28D
MICROCHIP	PIC16F18346	DIP20	
MICROCHIP	PIC16F18346	SOIC20	PA28SO28D-EO-300
MICROCHIP	PIC16F18346	SSOP20	PA28SS28D
MICROCHIP	PIC16F18854	DIP28	
MICROCHIP	PIC16F18854	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC16F18854	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16F18854	SSOP28	PA28SS28D
MICROCHIP	PIC16F18855	DIP28	
MICROCHIP	PIC16F18855	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC16F18855	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16F18855	SSOP28	PA28SS28D
MICROCHIP	PIC16F18856	DIP28	
MICROCHIP	PIC16F18856	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC16F18856	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16F18856	SSOP28	PA28SS28D
MICROCHIP	PIC16F18857	DIP28	
MICROCHIP	PIC16F18857	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC16F18857	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16F18857	SSOP28	PA28SS28D
MICROCHIP	PIC16F18875	DIP40	
MICROCHIP	PIC16F18875	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC16F18876	DIP40	
MICROCHIP	PIC16F18876	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC16F18877	DIP40	
MICROCHIP	PIC16F18877	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC16F1934	DIP40	
MICROCHIP	PIC16F1936	DIP28	
MICROCHIP	PIC16F1936	SOP28	PA28SO28D-EO-300
MICROCHIP	PIC16F1937	DIP40	
MICROCHIP	PIC16F505	DIP14	
MICROCHIP	PIC16F505	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16F505	TSSOP14	PA24TSS24D
MICROCHIP	PIC16F506	DIP14	
MICROCHIP	PIC16F506	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16F506	TSSOP14	PA24TSS24D
MICROCHIP	PIC16F54	DIP18	
MICROCHIP	PIC16F54	SOIC18	PA28SO28D-EO-310
MICROCHIP	PIC16F54	SSOP20	PA20SS-P54
MICROCHIP	PIC16F54	SSOP20	PA24TSS24D
MICROCHIP	PIC16F57	DIP28	
MICROCHIP	PIC16F57	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16F57	SSOP28	PA28TS28D-EO
MICROCHIP	PIC16F610	DIP14	
MICROCHIP	PIC16F610	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16F610	TSSOP14	PA24TSS24D
MICROCHIP	PIC16F616	DIP14	
MICROCHIP	PIC16F616	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16F616	TSSOP14	PA24TSS24D
MICROCHIP	PIC16F627	DIP18	
MICROCHIP	PIC16F627A	DIP18	
MICROCHIP	PIC16F627A	SOIC18	PA28SO28D-EO-300
MICROCHIP	PIC16F627A	SSOP20	PA20SS-P54
MICROCHIP	PIC16F628	DIP18	
MICROCHIP	PIC16F628A	DIP18	
MICROCHIP	PIC16F628A	SOIC18	PA28SO28D-EO-310
MICROCHIP	PIC16F628A	SSOP20	PA20SS-P54
MICROCHIP	PIC16F630	DIP14	

MICROCHIP	PIC16F631	DIP20	
MICROCHIP	PIC16F631	SOIC20	PA28SO28D-EO-300
MICROCHIP	PIC16F631	SSOP20	PA28SS28D
MICROCHIP	PIC16F636	DIP14	
MICROCHIP	PIC16F636	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16F636	TSSOP14	PA24TSS24D
MICROCHIP	PIC16F639	DIP20	
MICROCHIP	PIC16F639	SOIC20	PA28SO28D-EO-300
MICROCHIP	PIC16F639	SSOP20	PA28SS28D
MICROCHIP	PIC16F648A	DIP18	
MICROCHIP	PIC16F648A	SOIC18	PA28SO28D-EO-310
MICROCHIP	PIC16F648A	SSOP20	PA20SS-P54
MICROCHIP	PIC16F676	DIP14	
MICROCHIP	PIC16F676	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16F677	DIP20	
MICROCHIP	PIC16F677	SOIC20	PA28SO28D-EO-300
MICROCHIP	PIC16F677	SSOP20	PA28SS28D
MICROCHIP	PIC16F684	DIP14	
MICROCHIP	PIC16F684	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16F684	TSSOP14	PA24TSS24D
MICROCHIP	PIC16F685	DIP20	
MICROCHIP	PIC16F685	SOIC20	PA28SO28D-EO-300
MICROCHIP	PIC16F685	SSOP20	PA28SS28D
MICROCHIP	PIC16F688	DIP14	
MICROCHIP	PIC16F688	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16F688	TSSOP14	PA24TSS24D
MICROCHIP	PIC16F689	DIP20	
MICROCHIP	PIC16F689	SOIC20	PA28SO28D-EO-300
MICROCHIP	PIC16F689	SSOP20	PA28SS28D
MICROCHIP	PIC16F690	DIP20	
MICROCHIP	PIC16F690	SOIC20	PA28SO28D-EO-300
MICROCHIP	PIC16F690	SSOP20	PA28SS28D
MICROCHIP	PIC16F716	DIP18	
MICROCHIP	PIC16F716	SOIC18	PA28SO28D-EO-310
MICROCHIP	PIC16F716	SSOP20	PA20SS-P54
MICROCHIP	PIC16F72	DIP28	
MICROCHIP	PIC16F722	DIP28	
MICROCHIP	PIC16F73	DIP28	
MICROCHIP	PIC16F737	DIP28	
MICROCHIP	PIC16F737	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16F74	DIP40	
MICROCHIP	PIC16F74	PLCC44	PA44-48U
MICROCHIP	PIC16F74	TQFP44	PA44QF44D
MICROCHIP	PIC16F76	DIP28	
MICROCHIP	PIC16F767	DIP28	
MICROCHIP	PIC16F767	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16F77	DIP40	
MICROCHIP	PIC16F77	PLCC44	PA44-48U
MICROCHIP	PIC16F77	TQFP44	PA44QF44D
MICROCHIP	PIC16F818	DIP18	
MICROCHIP	PIC16F818	SOIC18	PA28SO28D-EO-310
MICROCHIP	PIC16F818	SSOP20	PA20SS-P54
MICROCHIP	PIC16F819	DIP18	
MICROCHIP	PIC16F819	SOIC18	PA28SO28D-EO-310
MICROCHIP	PIC16F819	SSOP20	PA20SS-P54
MICROCHIP	PIC16F83	DIP18	
MICROCHIP	PIC16F84	DIP18	
MICROCHIP	PIC16F84A	DIP18	
MICROCHIP	PIC16F87	DIP18	
MICROCHIP	PIC16F87	SOIC18	PA28SO28D-EO-310
MICROCHIP	PIC16F87	SSOP20	PA20SS-P54
MICROCHIP	PIC16F870	DIP28	
MICROCHIP	PIC16F870	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16F871	DIP40	
MICROCHIP	PIC16F871	PLCC44	PA44-48U
MICROCHIP	PIC16F871	TQFP44	PA44QF44D
MICROCHIP	PIC16F872	DIP28	
MICROCHIP	PIC16F872	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16F873	DIP28	
MICROCHIP	PIC16F873	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16F873A	DIP28	
MICROCHIP	PIC16F873A	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16F874	DIP40	

MICROCHIP	PIC16F874	PLCC44	PA44-48U
MICROCHIP	PIC16F874	TQFP44	PA44QF44D
MICROCHIP	PIC16F874A	DIP40	
MICROCHIP	PIC16F874A	PLCC44	PA44-48U
MICROCHIP	PIC16F874A	TQFP44	PA44QF44D
MICROCHIP	PIC16F876	DIP28	
MICROCHIP	PIC16F876	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16F876A	DIP28	
MICROCHIP	PIC16F876A	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16F876A	SSOP28	PA28SS28D
MICROCHIP	PIC16F877	DIP40	
MICROCHIP	PIC16F877	PLCC44	PA44-48U
MICROCHIP	PIC16F877	TQFP44	PA44QF44D
MICROCHIP	PIC16F877A	DIP40	
MICROCHIP	PIC16F877A	PLCC44	PA44-48U
MICROCHIP	PIC16F877A	TQFP44	PA44QF44D
MICROCHIP	PIC16F88	DIP18	
MICROCHIP	PIC16F88	SOIC18	PA28SO28D-EO-310
MICROCHIP	PIC16F88	SSOP20	PA20SS-P54
MICROCHIP	PIC16F882	DIP28	
MICROCHIP	PIC16F882	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC16F882	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16F882	SSOP28	PA28SS28D
MICROCHIP	PIC16F883	DIP28	
MICROCHIP	PIC16F883	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC16F883	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16F883	SSOP28	PA28SS28D
MICROCHIP	PIC16F884	DIP40	
MICROCHIP	PIC16F884	QFN44	PA44QFN44D
MICROCHIP	PIC16F884	TQFP44	PA44QF44D
MICROCHIP	PIC16F886	DIP28	
MICROCHIP	PIC16F886	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC16F886	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16F886	SSOP28	PA28SS28D
MICROCHIP	PIC16F887	DIP40	
MICROCHIP	PIC16F887	QFN44	PA44QFN44D
MICROCHIP	PIC16F887	TQFP44	PA44QF44D
MICROCHIP	PIC16HV540	DIP18	
MICROCHIP	PIC16HV610	DIP14	
MICROCHIP	PIC16HV610	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16HV610	TSSOP14	PA24TSS24D
MICROCHIP	PIC16HV616	DIP14	
MICROCHIP	PIC16HV616	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16HV616	TSSOP14	PA24TSS24D
MICROCHIP	PIC16LC62B	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16LC73A	DIP28	
MICROCHIP	PIC16LC73B	DIP28	
MICROCHIP	PIC16LC74A	DIP40	
MICROCHIP	PIC16LC74A	PLCC44	PA44-48U
MICROCHIP	PIC16LC74B	DIP40	
MICROCHIP	PIC16LC74B	PLCC44	PA44-48U
MICROCHIP	PIC16LC77	DIP40	
MICROCHIP	PIC16LC77	PLCC44	PA44-48U
MICROCHIP	PIC16LF1703	DIP14	
MICROCHIP	PIC16LF1703	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16LF1703	TSSOP14	PA24TSS24D
MICROCHIP	PIC16LF1704	DIP14	
MICROCHIP	PIC16LF1704	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16LF1704	TSSOP14	PA24TSS24D
MICROCHIP	PIC16LF1705	DIP14	
MICROCHIP	PIC16LF1705	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16LF1705	TSSOP14	PA24TSS24D
MICROCHIP	PIC16LF1707	DIP20	
MICROCHIP	PIC16LF1707	SOIC20	PA28SO28D-EO-300
MICROCHIP	PIC16LF1707	SSOP20	PA28SS28D
MICROCHIP	PIC16LF1708	DIP20	
MICROCHIP	PIC16LF1708	SOIC20	PA28SO28D-EO-300
MICROCHIP	PIC16LF1708	SSOP20	PA28SS28D
MICROCHIP	PIC16LF1709	DIP20	
MICROCHIP	PIC16LF1709	SOIC20	PA28SO28D-EO-300
MICROCHIP	PIC16LF1709	SSOP20	PA28SS28D
MICROCHIP	PIC16LF18313	DIP8	
MICROCHIP	PIC16LF18313	SOIC8	PA16SO16D-EO-150/PA8SO8D-150

MICROCHIP	PIC16LF18323	DIP14	
MICROCHIP	PIC16LF18323	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16LF18323	TSSOP14	PA24TSS24D
MICROCHIP	PIC16LF18324	DIP14	
MICROCHIP	PIC16LF18324	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16LF18324	TSSOP14	PA24TSS24D
MICROCHIP	PIC16LF18325	DIP14	
MICROCHIP	PIC16LF18325	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16LF18325	TSSOP14	PA24TSS24D
MICROCHIP	PIC16LF18326	DIP14	
MICROCHIP	PIC16LF18326	SOIC14	PA16SO16D-EO-150
MICROCHIP	PIC16LF18326	TSSOP14	PA24TSS24D
MICROCHIP	PIC16LF18344	DIP20	
MICROCHIP	PIC16LF18344	SOIC20	PA28SO28D-EO-300
MICROCHIP	PIC16LF18344	SSOP20	PA28SS28D
MICROCHIP	PIC16LF18345	DIP20	
MICROCHIP	PIC16LF18345	SOIC20	PA28SO28D-EO-300
MICROCHIP	PIC16LF18345	SSOP20	PA28SS28D
MICROCHIP	PIC16LF18346	DIP20	
MICROCHIP	PIC16LF18346	SOIC20	PA28SO28D-EO-300
MICROCHIP	PIC16LF18346	SSOP20	PA28SS28D
MICROCHIP	PIC16LF18854	DIP28	
MICROCHIP	PIC16LF18854	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC16LF18854	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16LF18854	SSOP28	PA28SS28D
MICROCHIP	PIC16LF18855	DIP28	
MICROCHIP	PIC16LF18855	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC16LF18855	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16LF18855	SSOP28	PA28SS28D
MICROCHIP	PIC16LF18856	DIP28	
MICROCHIP	PIC16LF18856	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC16LF18856	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16LF18856	SSOP28	PA28SS28D
MICROCHIP	PIC16LF18857	DIP28	
MICROCHIP	PIC16LF18857	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC16LF18857	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16LF18857	SSOP28	PA28SS28D
MICROCHIP	PIC16LF18875	DIP40	
MICROCHIP	PIC16LF18875	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC16LF18876	DIP40	
MICROCHIP	PIC16LF18876	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC16LF18877	DIP40	
MICROCHIP	PIC16LF18877	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC16LF1938-I/SO	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16LF1938-I/SS	SSOP28	PA28SS28D
MICROCHIP	PIC16LF72	DIP28	
MICROCHIP	PIC16LF873A	DIP28	
MICROCHIP	PIC16LF873A	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC16LF876A	DIP28	
MICROCHIP	PIC17C42	DIP40	
MICROCHIP	PIC17C42	PLCC44	PA44-48U
MICROCHIP	PIC17C42A	DIP40	
MICROCHIP	PIC17C42A	PLCC44	PA44-48U
MICROCHIP	PIC17C43	DIP40	
MICROCHIP	PIC17C43	PLCC44	PA44-48U
MICROCHIP	PIC17C44	DIP40	
MICROCHIP	PIC17C44	PLCC44	PA44-48U
MICROCHIP	PIC17C752	PLCC68	PA756-68Z
MICROCHIP	PIC17C756	PLCC68	PA756-68Z
MICROCHIP	PIC17C756	SDIP64	PA923-SD
MICROCHIP	PIC17C756A	PLCC68	PA756-68Z
MICROCHIP	PIC17C756A	SDIP64	PA923-SD
MICROCHIP	PIC17LC44	DIP40	
MICROCHIP	PIC17LC44	PLCC44	PA44-48U
MICROCHIP	PIC18C242	DIP28	
MICROCHIP	PIC18C252	DIP28	
MICROCHIP	PIC18C442	DIP40	
MICROCHIP	PIC18C442	PLCC44	PA44-48U
MICROCHIP	PIC18C452	DIP40	
MICROCHIP	PIC18C452	PLCC44	PA44-48U
MICROCHIP	PIC18C658	TQFP64	PA64TQ40D
MICROCHIP	PIC18F1220	DIP18	
MICROCHIP	PIC18F1220	SOIC18	PA28SO28D-EO-300

MICROCHIP	PIC18F1220	SSOP20	PA20SS-P54
MICROCHIP	PIC18F1320	DIP18	
MICROCHIP	PIC18F1320	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F1320	SOIC18	PA28SO28D-EO-300
MICROCHIP	PIC18F1320	SSOP20	PA20SS-P54
MICROCHIP	PIC18F14K22	SSOP20	PA28SS28D
MICROCHIP	PIC18F2220	DIP28	
MICROCHIP	PIC18F2220	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F2221	DIP28	
MICROCHIP	PIC18F2221	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F2221	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F2320	DIP28	
MICROCHIP	PIC18F2320	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F2321	DIP28	
MICROCHIP	PIC18F2321	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F2321	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F2331	DIP28	
MICROCHIP	PIC18F2331	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F23K20	DIP28	
MICROCHIP	PIC18F23K20	DIP40	
MICROCHIP	PIC18F23K20	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F23K20	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F23K20	SSOP28	PA28SS28D
MICROCHIP	PIC18F23K20	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18F23K22	DIP28	
MICROCHIP	PIC18F23K22	DIP40	
MICROCHIP	PIC18F23K22	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F23K22	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F23K22	SSOP28	PA28SS28D
MICROCHIP	PIC18F23K22	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18F2410	DIP28	
MICROCHIP	PIC18F2410	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F2410	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F242	DIP28	
MICROCHIP	PIC18F2420	DIP28	
MICROCHIP	PIC18F2420	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F2420	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F2423	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F2431	DIP28	
MICROCHIP	PIC18F2431	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F2450	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F2455	DIP28	
MICROCHIP	PIC18F2455	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F248	DIP28	
MICROCHIP	PIC18F2480	DIP28	
MICROCHIP	PIC18F2480	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F2480	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F24J10	DIP28	
MICROCHIP	PIC18F24J10	QFN28	AS-28-28-02ML-6
MICROCHIP	PIC18F24J10	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F24J10	SSOP28	PA28SS28D
MICROCHIP	PIC18F24K20	DIP28	
MICROCHIP	PIC18F24K20	DIP40	
MICROCHIP	PIC18F24K20	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F24K20	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F24K20	SSOP28	PA28SS28D
MICROCHIP	PIC18F24K20	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18F24K22	DIP28	
MICROCHIP	PIC18F24K22	DIP40	
MICROCHIP	PIC18F24K22	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F24K22	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F24K22	SSOP28	PA28SS28D
MICROCHIP	PIC18F24K22	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18F2510	DIP28	
MICROCHIP	PIC18F2510	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F2510	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F2515	DIP28	
MICROCHIP	PIC18F2515	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F252	DIP28	
MICROCHIP	PIC18F2520	DIP28	
MICROCHIP	PIC18F2520	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F2520	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F2525	DIP28	



MICROCHIP	PIC18F2525	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F2550	DIP28	
MICROCHIP	PIC18F2550	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F2553	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F258	DIP28	
MICROCHIP	PIC18F2580	DIP28	
MICROCHIP	PIC18F2580	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F2580	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F2585	DIP28	
MICROCHIP	PIC18F2585	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F25J10	DIP28	
MICROCHIP	PIC18F25J10	QFN28	AS-28-28-02ML-6
MICROCHIP	PIC18F25J10	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F25J10	SSOP28	PA28SS28D
MICROCHIP	PIC18F25K20	DIP28	
MICROCHIP	PIC18F25K20	DIP40	
MICROCHIP	PIC18F25K20	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F25K20	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F25K20	SSOP28	PA28SS28D
MICROCHIP	PIC18F25K20	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18F25K22	DIP28	
MICROCHIP	PIC18F25K22	DIP40	
MICROCHIP	PIC18F25K22	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F25K22	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F25K22	SSOP28	PA28SS28D
MICROCHIP	PIC18F25K22	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18F2610	DIP28	
MICROCHIP	PIC18F2610	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F2620	DIP28	
MICROCHIP	PIC18F2620	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F2680	DIP28	
MICROCHIP	PIC18F2680	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F26K20	DIP28	
MICROCHIP	PIC18F26K20	DIP40	
MICROCHIP	PIC18F26K20	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F26K20	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F26K20	SSOP28	PA28SS28D
MICROCHIP	PIC18F26K20	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18F26K22	DIP28	
MICROCHIP	PIC18F26K22	DIP40	
MICROCHIP	PIC18F26K22	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F26K22	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F26K22	SSOP28	PA28SS28D
MICROCHIP	PIC18F26K22	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18F4220	DIP40	
MICROCHIP	PIC18F4220	TQFP44	PA44QF44D
MICROCHIP	PIC18F4221	DIP40	
MICROCHIP	PIC18F4221	QFN44	PA44QFN44D
MICROCHIP	PIC18F4221	TQFP44	PA44QF44D
MICROCHIP	PIC18F4320	DIP40	
MICROCHIP	PIC18F4320	TQFP44	PA44QF44D
MICROCHIP	PIC18F4321	DIP40	
MICROCHIP	PIC18F4321	QFN44	PA44QFN44D
MICROCHIP	PIC18F4321	TQFP44	PA44QF44D
MICROCHIP	PIC18F4331	DIP40	
MICROCHIP	PIC18F4331	QFN44	PA44QFN44D
MICROCHIP	PIC18F4331	TQFP44	PA44QF44D
MICROCHIP	PIC18F43K20	DIP28	
MICROCHIP	PIC18F43K20	DIP40	
MICROCHIP	PIC18F43K20	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F43K20	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F43K20	SSOP28	PA28SS28D
MICROCHIP	PIC18F43K20	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18F43K22	DIP28	
MICROCHIP	PIC18F43K22	DIP40	
MICROCHIP	PIC18F43K22	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F43K22	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F43K22	SSOP28	PA28SS28D
MICROCHIP	PIC18F43K22	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18F4410	DIP40	
MICROCHIP	PIC18F4410	QFN44	PA44QFN44D
MICROCHIP	PIC18F4410	TQFP44	PA44QF44D
MICROCHIP	PIC18F442	DIP40	

MICROCHIP	PIC18F442	PLCC44	PA44-48U
MICROCHIP	PIC18F442	TQFP44	PA44QF44D
MICROCHIP	PIC18F4420	DIP40	
MICROCHIP	PIC18F4420	QFN44	PA44QFN44D
MICROCHIP	PIC18F4420	TQFP44	PA44QF44D
MICROCHIP	PIC18F4431	DIP40	
MICROCHIP	PIC18F4431	QFN44	PA44QFN44D
MICROCHIP	PIC18F4431	TQFP44	PA44QF44D
MICROCHIP	PIC18F4455	DIP40	
MICROCHIP	PIC18F4455	QFN44	PA44QFN44D
MICROCHIP	PIC18F4455	TQFP44	PA44QF44D
MICROCHIP	PIC18F448	DIP40	
MICROCHIP	PIC18F448	PLCC44	PA44-48U
MICROCHIP	PIC18F448	TQFP44	PA44QF44D
MICROCHIP	PIC18F4480	DIP40	
MICROCHIP	PIC18F4480	QFN44	PA44QFN44D
MICROCHIP	PIC18F4480	TQFP44	PA44QF44D
MICROCHIP	PIC18F44J10	DIP40	
MICROCHIP	PIC18F44J10	TQFP44	PA44VQ44D
MICROCHIP	PIC18F44K20	DIP28	
MICROCHIP	PIC18F44K20	DIP40	
MICROCHIP	PIC18F44K20	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F44K20	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F44K20	SSOP28	PA28SS28D
MICROCHIP	PIC18F44K20	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18F44K22	DIP28	
MICROCHIP	PIC18F44K22	DIP40	
MICROCHIP	PIC18F44K22	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F44K22	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F44K22	SSOP28	PA28SS28D
MICROCHIP	PIC18F44K22	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18F4510	DIP40	
MICROCHIP	PIC18F4510	QFN44	PA44QFN44D
MICROCHIP	PIC18F4510	TQFP44	PA44QF44D
MICROCHIP	PIC18F4515	DIP40	
MICROCHIP	PIC18F4515	QFN44	PA44QFN44D
MICROCHIP	PIC18F4515	TQFP44	PA44QF44D
MICROCHIP	PIC18F452	DIP40	
MICROCHIP	PIC18F452	PLCC44	PA44-48U
MICROCHIP	PIC18F452	TQFP44	PA44QF44D
MICROCHIP	PIC18F4520	DIP40	
MICROCHIP	PIC18F4520	QFN44	PA44QFN44D
MICROCHIP	PIC18F4520	TQFP44	PA44QF44D
MICROCHIP	PIC18F4525	DIP40	
MICROCHIP	PIC18F4525	QFN44	PA44QFN44D
MICROCHIP	PIC18F4525	TQFP44	PA44QF44D
MICROCHIP	PIC18F4550	DIP40	
MICROCHIP	PIC18F4550	QFN44	PA44QFN44D
MICROCHIP	PIC18F4550	TQFP44	PA44QF44D
MICROCHIP	PIC18F458	DIP40	
MICROCHIP	PIC18F458	PLCC44	PA44-48U
MICROCHIP	PIC18F458	TQFP44	PA44QF44D
MICROCHIP	PIC18F4580	DIP40	
MICROCHIP	PIC18F4580	QFN44	PA44QFN44D
MICROCHIP	PIC18F4580	TQFP44	PA44QF44D
MICROCHIP	PIC18F4585	DIP40	
MICROCHIP	PIC18F4585	QFN44	PA44QFN44D
MICROCHIP	PIC18F4585	TQFP44	PA44QF44D
MICROCHIP	PIC18F45J10	DIP40	
MICROCHIP	PIC18F45J10	TQFP44	PA44VQ44D
MICROCHIP	PIC18F45K20	DIP28	
MICROCHIP	PIC18F45K20	DIP40	
MICROCHIP	PIC18F45K20	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F45K20	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F45K20	SSOP28	PA28SS28D
MICROCHIP	PIC18F45K20	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18F45K22	DIP28	
MICROCHIP	PIC18F45K22	DIP40	
MICROCHIP	PIC18F45K22	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F45K22	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F45K22	SSOP28	PA28SS28D
MICROCHIP	PIC18F45K22	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18F4610	DIP40	

MICROCHIP	PIC18F4610	QFN44	PA44QFN44D
MICROCHIP	PIC18F4610	TQFP44	PA44QF44D
MICROCHIP	PIC18F4620	DIP40	
MICROCHIP	PIC18F4620	QFN44	PA44QFN44D
MICROCHIP	PIC18F4620	TQFP44	PA44QF44D
MICROCHIP	PIC18F4680	DIP40	
MICROCHIP	PIC18F4680	QFN44	PA44QFN44D
MICROCHIP	PIC18F4680	TQFP44	PA44QF44D
MICROCHIP	PIC18F4685	DIP40	
MICROCHIP	PIC18F46K20	DIP28	
MICROCHIP	PIC18F46K20	DIP40	
MICROCHIP	PIC18F46K20	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F46K20	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F46K20	SSOP28	PA28SS28D
MICROCHIP	PIC18F46K20	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18F46K22	DIP28	
MICROCHIP	PIC18F46K22	DIP40	
MICROCHIP	PIC18F46K22	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18F46K22	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18F46K22	SSOP28	PA28SS28D
MICROCHIP	PIC18F46K22	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18F6520	TQFP64	PA64TQ40D
MICROCHIP	PIC18F6522	TQFP64	PA64TQ40D
MICROCHIP	PIC18F6527	TQFP64	PA64TQ40D
MICROCHIP	PIC18F6585	PLCC68	PA68PL40DH
MICROCHIP	PIC18F6620	TQFP64	PA64TQ40D
MICROCHIP	PIC18F6627	TQFP64	PA64TQ40D
MICROCHIP	PIC18F6680	PLCC68	PA68PL40DH
MICROCHIP	PIC18F6720	TQFP64	PA64TQ40D
MICROCHIP	PIC18F6722	TQFP64	PA64TQ40D
MICROCHIP	PIC18F8410	TQFP80	PA80TQ40D
MICROCHIP	PIC18F8520	TQFP80	PA80TQ40D
MICROCHIP	PIC18F8527	TQFP80	PA80TQ40D
MICROCHIP	PIC18F8620	TQFP80	PA80TQ40D
MICROCHIP	PIC18F8622	TQFP80	PA80TQ40D
MICROCHIP	PIC18F8627	TQFP80	PA80TQ40D
MICROCHIP	PIC18F8720	TQFP80	PA80TQ40D
MICROCHIP	PIC18F8722	TQFP80	PA80TQ40D
MICROCHIP	PIC18LF2221	DIP28	
MICROCHIP	PIC18LF2221	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18LF2221	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2321	DIP28	
MICROCHIP	PIC18LF2321	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18LF2321	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF23K22	DIP28	
MICROCHIP	PIC18LF23K22	DIP40	
MICROCHIP	PIC18LF23K22	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18LF23K22	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF23K22	SSOP28	PA28SS28D
MICROCHIP	PIC18LF23K22	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18LF2410	DIP28	
MICROCHIP	PIC18LF2410	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18LF2410	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2420	DIP28	
MICROCHIP	PIC18LF2420	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18LF2420	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2455	DIP28	
MICROCHIP	PIC18LF2455	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2480	DIP28	
MICROCHIP	PIC18LF2480	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18LF2480	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF24J10	DIP28	
MICROCHIP	PIC18LF24J10	QFN28	AS-28-28-02ML-6
MICROCHIP	PIC18LF24J10	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF24J10	SSOP28	PA28SS28D
MICROCHIP	PIC18LF24K22	DIP28	
MICROCHIP	PIC18LF24K22	DIP40	
MICROCHIP	PIC18LF24K22	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18LF24K22	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF24K22	SSOP28	PA28SS28D
MICROCHIP	PIC18LF24K22	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18LF2510	DIP28	
MICROCHIP	PIC18LF2510	QFN28	PA28QFN28D(6x6)

MICROCHIP	PIC18LF2510	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2515	DIP28	
MICROCHIP	PIC18LF2515	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF252	DIP28	
MICROCHIP	PIC18LF252	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2520	DIP28	
MICROCHIP	PIC18LF2520	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18LF2520	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2525	DIP28	
MICROCHIP	PIC18LF2525	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2550	DIP28	
MICROCHIP	PIC18LF2550	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2580	DIP28	
MICROCHIP	PIC18LF2580	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18LF2580	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2585	DIP28	
MICROCHIP	PIC18LF2585	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF25J10	DIP28	
MICROCHIP	PIC18LF25J10	QFN28	AS-28-28-02ML-6
MICROCHIP	PIC18LF25J10	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF25J10	SSOP28	PA28SS28D
MICROCHIP	PIC18LF25K22	DIP28	
MICROCHIP	PIC18LF25K22	DIP40	
MICROCHIP	PIC18LF25K22	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18LF25K22	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF25K22	SSOP28	PA28SS28D
MICROCHIP	PIC18LF25K22	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18LF2610	DIP28	
MICROCHIP	PIC18LF2610	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2620	DIP28	
MICROCHIP	PIC18LF2620	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF2680	DIP28	
MICROCHIP	PIC18LF2680	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF26K22	DIP28	
MICROCHIP	PIC18LF26K22	DIP40	
MICROCHIP	PIC18LF26K22	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18LF26K22	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF26K22	SSOP28	PA28SS28D
MICROCHIP	PIC18LF26K22	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18LF4221	DIP40	
MICROCHIP	PIC18LF4221	QFN44	PA44QFN44D
MICROCHIP	PIC18LF4221	TQFP44	PA44QF44D
MICROCHIP	PIC18LF4321	DIP40	
MICROCHIP	PIC18LF4321	QFN44	PA44QFN44D
MICROCHIP	PIC18LF4321	TQFP44	PA44QF44D
MICROCHIP	PIC18LF43K22	DIP28	
MICROCHIP	PIC18LF43K22	DIP40	
MICROCHIP	PIC18LF43K22	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18LF43K22	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF43K22	SSOP28	PA28SS28D
MICROCHIP	PIC18LF43K22	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18LF4410	DIP40	
MICROCHIP	PIC18LF4410	QFN44	PA44QFN44D
MICROCHIP	PIC18LF4410	TQFP44	PA44QF44D
MICROCHIP	PIC18LF4420	DIP40	
MICROCHIP	PIC18LF4420	QFN44	PA44QFN44D
MICROCHIP	PIC18LF4420	TQFP44	PA44QF44D
MICROCHIP	PIC18LF4455	DIP40	
MICROCHIP	PIC18LF4455	QFN44	PA44QFN44D
MICROCHIP	PIC18LF4455	TQFP44	PA44QF44D
MICROCHIP	PIC18LF4480	DIP40	
MICROCHIP	PIC18LF4480	QFN44	PA44QFN44D
MICROCHIP	PIC18LF4480	TQFP44	PA44QF44D
MICROCHIP	PIC18LF44J10	DIP40	
MICROCHIP	PIC18LF44J10	TQFP44	PA44VQ44D
MICROCHIP	PIC18LF44K22	DIP28	
MICROCHIP	PIC18LF44K22	DIP40	
MICROCHIP	PIC18LF44K22	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18LF44K22	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF44K22	SSOP28	PA28SS28D
MICROCHIP	PIC18LF44K22	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18LF4510	DIP40	
MICROCHIP	PIC18LF4510	QFN44	PA44QFN44D

MICROCHIP	PIC18LF4510	TQFP44	PA44QF44D
MICROCHIP	PIC18LF4515	DIP40	
MICROCHIP	PIC18LF4515	QFN44	PA44QFN44D
MICROCHIP	PIC18LF4515	TQFP44	PA44QF44D
MICROCHIP	PIC18LF4520	DIP40	
MICROCHIP	PIC18LF4520	QFN44	PA44QFN44D
MICROCHIP	PIC18LF4520	TQFP44	PA44QF44D
MICROCHIP	PIC18LF4525	DIP40	
MICROCHIP	PIC18LF4525	QFN44	PA44QFN44D
MICROCHIP	PIC18LF4525	TQFP44	PA44QF44D
MICROCHIP	PIC18LF4550	DIP40	
MICROCHIP	PIC18LF4550	QFN44	PA44QFN44D
MICROCHIP	PIC18LF4550	TQFP44	PA44QF44D
MICROCHIP	PIC18LF4580	DIP40	
MICROCHIP	PIC18LF4580	QFN44	PA44QFN44D
MICROCHIP	PIC18LF4580	TQFP44	PA44QF44D
MICROCHIP	PIC18LF4585	DIP40	
MICROCHIP	PIC18LF4585	QFN44	PA44QFN44D
MICROCHIP	PIC18LF4585	TQFP44	PA44QF44D
MICROCHIP	PIC18LF45J10	DIP40	
MICROCHIP	PIC18LF45J10	TQFP44	PA44VQ44D
MICROCHIP	PIC18LF45K22	DIP28	
MICROCHIP	PIC18LF45K22	DIP40	
MICROCHIP	PIC18LF45K22	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18LF45K22	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF45K22	SSOP28	PA28SS28D
MICROCHIP	PIC18LF45K22	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18LF4610	DIP40	
MICROCHIP	PIC18LF4610	QFN44	PA44QFN44D
MICROCHIP	PIC18LF4610	TQFP44	PA44QF44D
MICROCHIP	PIC18LF4620	DIP40	
MICROCHIP	PIC18LF4620	QFN44	PA44QFN44D
MICROCHIP	PIC18LF4620	TQFP44	PA44QF44D
MICROCHIP	PIC18LF4680	DIP40	
MICROCHIP	PIC18LF4680	QFN44	PA44QFN44D
MICROCHIP	PIC18LF4680	TQFP44	PA44QF44D
MICROCHIP	PIC18LF46K22	DIP28	
MICROCHIP	PIC18LF46K22	DIP40	
MICROCHIP	PIC18LF46K22	QFN28	PA28QFN28D(6x6)
MICROCHIP	PIC18LF46K22	SOIC28	PA28SO28D-EO-300
MICROCHIP	PIC18LF46K22	SSOP28	PA28SS28D
MICROCHIP	PIC18LF46K22	TQFP44	PA44VQ44D/PA44TQ44D
MICROCHIP	PIC18LF6520	TQFP64	PA64TQ40D
MICROCHIP	PIC18LF6522	TQFP64	PA64TQ40D
MICROCHIP	PIC18LF6527	TQFP64	PA64TQ40D
MICROCHIP	PIC18LF6585	PLCC68	PA68PL40DH
MICROCHIP	PIC18LF6620	TQFP64	PA64TQ40D
MICROCHIP	PIC18LF6627	TQFP64	PA64TQ40D
MICROCHIP	PIC18LF6680	PLCC68	PA68PL40DH
MICROCHIP	PIC18LF6720	TQFP64	PA64TQ40D
MICROCHIP	PIC18LF6722	TQFP64	PA64TQ40D
MICROCHIP	PIC18LF8520	TQFP80	PA80TQ40D
MICROCHIP	PIC18LF8527	TQFP80	PA80TQ40D
MICROCHIP	PIC18LF8620	TQFP80	PA80TQ40D
MICROCHIP	PIC18LF8622	TQFP80	PA80TQ40D
MICROCHIP	PIC18LF8627	TQFP80	PA80TQ40D
MICROCHIP	PIC18LF8720	TQFP80	PA80TQ40D
MICROCHIP	PIC18LF8722	TQFP80	PA80TQ40D
MICROCHIP	PIC24F32KA301	SSOP20	PA28SS28D
MICROCHIP	PIC24HJ128GP206A	QFP64	PA64TQ48D
MICROCHIP	SST25LF020A	SOIC8	PA16SO16D-EO-150
MICROCHIP	SST25LF040A	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST25LF080A	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST25PF020B	SOIC8	PA16SO16D-EO-150
MICROCHIP	SST25PF020B-Q3AE	USON8	HBP8USON48DB(2x3)
MICROCHIP	SST25PF020B-QAE	WSON8	PA8SON8D(6x5)
MICROCHIP	SST25PF020B-SAE	SOIC8	PA16SO16D-EO-150
MICROCHIP	SST25PF040C-MF	WSON8	PA8SON8D(6x5)
MICROCHIP	SST25PF040C-NP	USON8	HBP8USON48DB(2x3)
MICROCHIP	SST25PF040C-SN	SOIC8	PA16SO16D-EO-150
MICROCHIP	SST25VF010	SOIC8	PA16SO16D-EO-150
MICROCHIP	SST25VF010	WSON8	PA8SON8D(6x5)
MICROCHIP	SST25VF010A	SOIC8	PA16SO16D-EO-150

MICROCHIP	SST25VF010A	WSON8	PA8SON8D(6x5)
MICROCHIP	SST25VF016B	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST25VF016B	WSON8	PA8SON8D(6x5)
MICROCHIP	SST25VF020	SOIC8	PA16SO16D-EO-150
MICROCHIP	SST25VF020	WSON8	PA8SON8D(6x5)
MICROCHIP	SST25VF020B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	SST25VF020B	USON8	PA8SON8D(2x3)
MICROCHIP	SST25VF020B	WSON8	PA8SON8D(6x5)
MICROCHIP	SST25VF032B	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST25VF032B	SOP16	PA20SO20D-EO-210
MICROCHIP	SST25VF040	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST25VF040	WSON8	PA8SON8D(6x5)
MICROCHIP	SST25VF040B	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST25VF040B	WSON8	PA8SON8D(6x5)
MICROCHIP	SST25VF064C	SOP16	PA28SO28D-EO-300
MICROCHIP	SST25VF064C-S3AE	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST25VF080B	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST25VF080B	WSON8	PA8SON8D(6x5)
MICROCHIP	SST25VF080B-PAE	DIP8	
MICROCHIP	SST25VF080B-QAE	WSON8	PA8SON8D(6x5)
MICROCHIP	SST25VF080B-S2AE	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST25VF512	SOIC8	PA16SO16D-EO-150
MICROCHIP	SST25VF512	WSON8	PA8SON8D(6x5)
MICROCHIP	SST25VF512A	SOIC8	PA16SO16D-EO-150
MICROCHIP	SST25VF512A	WSON8	PA8SON8D(6x5)
MICROCHIP	SST25WF010	SOIC8	PA16SO16D-EO-150
MICROCHIP	SST25WF020	SOIC8	PA16SO16D-EO-150
MICROCHIP	SST25WF020A	SOIC8	PA16SO16D-EO-150
MICROCHIP	SST25WF040	SOIC8	PA16SO16D-EO-150
MICROCHIP	SST25WF040	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST25WF040B	SOIC8	PA16SO16D-EO-150
MICROCHIP	SST25WF080	SOIC8	PA16SO16D-EO-150
MICROCHIP	SST25WF080	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST25WF080B	SOIC8	PA16SO16D-EO-150
MICROCHIP	SST25WF512	SOIC8	PA16SO16D-EO-150
MICROCHIP	SST26VF016	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST26VF016	WSON8	PA8SON8D(6x5)
MICROCHIP	SST26VF016B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	SST26VF016B	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST26VF016B	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26VF016B(Quad_IO)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	SST26VF016B(Quad_IO)	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST26VF016B(Quad_IO)	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26VF016BA	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	SST26VF016BA	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST26VF016BA	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26VF016BA(Quad_IO)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	SST26VF016BA(Quad_IO)	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST26VF016BA(Quad_IO)	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26VF020A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	SST26VF020A	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26VF020A(QUAD I/O)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	SST26VF020A(QUAD I/O)	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26VF032	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST26VF032	WSON8	PA8SON8D(6x5)
MICROCHIP	SST26VF032B	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST26VF032B	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26VF032B(Quad_IO)	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST26VF032B(Quad_IO)	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26VF032BA	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST26VF032BA	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26VF032BA(Quad_IO)	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST26VF032BA(Quad_IO)	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26VF040A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	SST26VF040A	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26VF040A(QUAD I/O)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	SST26VF040A(QUAD I/O)	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26VF064B	SOIC16	PA28SO28D-EO-300
MICROCHIP	SST26VF064B	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST26VF064B	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26VF064B	WDFN8	PA8SON8DA(8x6)
MICROCHIP	SST26VF064B(Quad_IO)	SOIC16	PA28SO28D-EO-300
MICROCHIP	SST26VF064B(Quad_IO)	SOIC8	PA20SO20D-EO-210

MICROCHIP	SST26VF064B(Quad_IO)	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26VF064B(Quad_IO)	WDFN8	PA8SON8DA(8x6)
MICROCHIP	SST26VF064BA	SOIC16	PA28SO28D-EO-300
MICROCHIP	SST26VF064BA	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST26VF064BA	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26VF064BA	WDFN8	PA8SON8DA(8x6)
MICROCHIP	SST26VF064BA(Quad_IO)	SOIC16	PA28SO28D-EO-300
MICROCHIP	SST26VF064BA(Quad_IO)	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST26VF064BA(Quad_IO)	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26VF064BA(Quad_IO)	WDFN8	PA8SON8DA(8x6)
MICROCHIP	SST26VF080A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	SST26VF080A	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26VF080A(QUAD I/O)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	SST26VF080A(QUAD I/O)	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26WF016B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	SST26WF016B	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26WF016BA	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	SST26WF016BA	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26WF040B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	SST26WF040B	USON8	PA8SON8D(2x3)
MICROCHIP	SST26WF040B	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26WF040BA	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	SST26WF040BA	USON8	PA8SON8D(2x3)
MICROCHIP	SST26WF040BA	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26WF064C	SOIC16	PA28SO28D-EO-300
MICROCHIP	SST26WF064C	SOIC8	PA20SO20D-EO-210
MICROCHIP	SST26WF064C	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26WF080B	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	SST26WF080B	USON8	PA8SON8D(2x3)
MICROCHIP	SST26WF080B	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST26WF080BA	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
MICROCHIP	SST26WF080BA	USON8	PA8SON8D(2x3)
MICROCHIP	SST26WF080BA	WDFN8	PA8SON8D(6x5)
MICROCHIP	SST27SF010	DIP32	
MICROCHIP	SST27SF010	PLCC32	PA32PL32D
MICROCHIP	SST27SF010	TSOP32	PA32TS20/PA32TS32D-20
MICROCHIP	SST27SF020	DIP32	
MICROCHIP	SST27SF020	PLCC32	PA32PL32D
MICROCHIP	SST27SF020	TSOP32	PA32TS20/PA32TS32D-20
MICROCHIP	SST27SF256	DIP28	
MICROCHIP	SST27SF512	DIP28	
MICROCHIP	SST27SF512	PLCC32	PA32PL28D-YA
MICROCHIP	SST27SF512	sTSOP28	PA28TS28D-EO
MICROCHIP	SST27VF010	DIP32	
MICROCHIP	SST27VF010	PLCC32	PA32PL32D
MICROCHIP	SST27VF010	TSOP32	PA32TS20/PA32TS32D-20
MICROCHIP	SST27VF020	DIP32	
MICROCHIP	SST27VF020	PLCC32	PA32PL32D
MICROCHIP	SST27VF020	TSOP32	PA32TS20/PA32TS32D-20
MICROCHIP	SST27VF256	DIP28	
MICROCHIP	SST27VF512	DIP28	
MICROCHIP	SST27VF512	PLCC32	PA32PL28D-YA
MICROCHIP	SST27VF512	sTSOP28	PA28TS28D-EO
MICROCHIP	SST28LF040	DIP32	
MICROCHIP	SST28LF040	PLCC32	PA32PL32D
MICROCHIP	SST28LF040	TSOP32	PA32TS20/PA32TS32D-20
MICROCHIP	SST28SF040	DIP32	
MICROCHIP	SST28SF040	PLCC32	PA32PL32D
MICROCHIP	SST28SF040	TSOP32	PA32TS20/PA32TS32D-20
MICROCHIP	SST28SF040A	DIP32	
MICROCHIP	SST28SF040A	PLCC32	PA32PL32D
MICROCHIP	SST28SF040A	TSOP32	PA32TS20/PA32TS32D-20
MICROCHIP	SST28VF040	DIP32	
MICROCHIP	SST28VF040	PLCC32	PA32PL32D
MICROCHIP	SST28VF040	TSOP32	PA32TS20/PA32TS32D-20
MICROCHIP	SST28VF040A	DIP32	
MICROCHIP	SST28VF040A	PLCC32	PA32PL32D
MICROCHIP	SST28VF040A	TSOP32	PA32TS20/PA32TS32D-20
MICROCHIP	SST29EE010	DIP32	
MICROCHIP	SST29EE010	PLCC32	PA32PL32D
MICROCHIP	SST29EE010	TSOP32	PA32TS32D
MICROCHIP	SST29EE010A	DIP32	
MICROCHIP	SST29EE010A	PLCC32	PA32PL32D

MICROCHIP	SST29EE010A	TSOP32	PA32TS32D
MICROCHIP	SST29EE020	DIP32	
MICROCHIP	SST29EE020	PLCC32	PA32PL32D
MICROCHIP	SST29EE020	TSOP32	PA32TS32D
MICROCHIP	SST29EE020A	DIP32	
MICROCHIP	SST29EE020A	PLCC32	PA32PL32D
MICROCHIP	SST29EE020A	TSOP32	PA32TS32D
MICROCHIP	SST29EE512	DIP32	
MICROCHIP	SST29EE512	PLCC32	PA32PL32D
MICROCHIP	SST29EE512	TSOP32	PA32TS20/PA32TS32D-20
MICROCHIP	SST29EE512A	DIP32	
MICROCHIP	SST29EE512A	PLCC32	PA32PL32D
MICROCHIP	SST29EE512A	TSOP32	PA32TS20/PA32TS32D-20
MICROCHIP	SST29LE010	DIP32	
MICROCHIP	SST29LE010	PLCC32	PA32PL32D
MICROCHIP	SST29LE010	TSOP32	PA32TS32D
MICROCHIP	SST29LE010A	DIP32	
MICROCHIP	SST29LE010A	PLCC32	PA32PL32D
MICROCHIP	SST29LE010A	TSOP32	PA32TS32D
MICROCHIP	SST29LE020	DIP32	
MICROCHIP	SST29LE020	PLCC32	PA32PL32D
MICROCHIP	SST29LE020	TSOP32	PA32TS32D
MICROCHIP	SST29LE020A	DIP32	
MICROCHIP	SST29LE020A	PLCC32	PA32PL32D
MICROCHIP	SST29LE020A	TSOP32	PA32TS32D
MICROCHIP	SST29LE512	DIP32	
MICROCHIP	SST29LE512	PLCC32	PA32PL32D
MICROCHIP	SST29LE512	TSOP32	PA32TS32D
MICROCHIP	SST29LE512A	DIP32	
MICROCHIP	SST29LE512A	PLCC32	PA32PL32D
MICROCHIP	SST29LE512A	TSOP32	PA32TS32D
MICROCHIP	SST29SF010	DIP32	
MICROCHIP	SST29SF010	PLCC32	PA32PL32D
MICROCHIP	SST29SF010	TSOP32	PA32TS32D
MICROCHIP	SST29SF020	DIP32	
MICROCHIP	SST29SF020	PLCC32	PA32PL32D
MICROCHIP	SST29SF020	TSOP32	PA32TS32D
MICROCHIP	SST29SF040	DIP32	
MICROCHIP	SST29SF040	PLCC32	PA32PL32D
MICROCHIP	SST29SF040	TSOP32	PA32TS32D
MICROCHIP	SST29SF512	DIP32	
MICROCHIP	SST29SF512	PLCC32	PA32PL32D
MICROCHIP	SST29SF512	TSOP32	PA32TS32D
MICROCHIP	SST29VE010	DIP32	
MICROCHIP	SST29VE010	PLCC32	PA32PL32D
MICROCHIP	SST29VE010	TSOP32	PA32TS32D
MICROCHIP	SST29VE010A	DIP32	
MICROCHIP	SST29VE010A	PLCC32	PA32PL32D
MICROCHIP	SST29VE010A	TSOP32	PA32TS32D
MICROCHIP	SST29VE020	DIP32	
MICROCHIP	SST29VE020	PLCC32	PA32PL32D
MICROCHIP	SST29VE020	TSOP32	PA32TS32D
MICROCHIP	SST29VE020A	DIP32	
MICROCHIP	SST29VE020A	PLCC32	PA32PL32D
MICROCHIP	SST29VE020A	TSOP32	PA32TS32D
MICROCHIP	SST29VE512	DIP32	
MICROCHIP	SST29VE512	PLCC32	PA32PL32D
MICROCHIP	SST29VE512	TSOP32	PA32TS32D
MICROCHIP	SST29VE512A	DIP32	
MICROCHIP	SST29VE512A	PLCC32	PA32PL32D
MICROCHIP	SST29VE512A	TSOP32	PA32TS32D
MICROCHIP	SST29VF010	DIP32	
MICROCHIP	SST29VF010	PLCC32	PA32PL32D
MICROCHIP	SST29VF010	TSOP32	PA32TS32D
MICROCHIP	SST29VF020	DIP32	
MICROCHIP	SST29VF020	PLCC32	PA32PL32D
MICROCHIP	SST29VF020	TSOP32	PA32TS32D
MICROCHIP	SST29VF040	DIP32	
MICROCHIP	SST29VF040	PLCC32	PA32PL32D
MICROCHIP	SST29VF040	TSOP32	PA32TS32D
MICROCHIP	SST29VF512	DIP32	
MICROCHIP	SST29VF512	PLCC32	PA32PL32D
MICROCHIP	SST29VF512	TSOP32	PA32TS32D



MICROCHIP	SST31LF021	TSOP32	PA32TS32D
MICROCHIP	SST31LF021	TSOP40	PA40TS14-OT
MICROCHIP	SST31LF021E	TSOP32	PA32TS32D
MICROCHIP	SST31LF041	TSOP40	PA40TS14-OT
MICROCHIP	SST31LF041A	TSOP32	PA32TS32D
MICROCHIP	SST32HF1622C	BGA62	PA62BGA48D
MICROCHIP	SST32HF1642	BGA62	PA62BGA48D
MICROCHIP	SST32HF1642C	BGA62	PA62BGA48D
MICROCHIP	SST32HF1682C	BGA62	PA62BGA48D
MICROCHIP	SST32HF402	BGA48	PA48BG48D
MICROCHIP	SST32HF402	BGA48	PA48BG48DAI
MICROCHIP	SST32VF201	BGA48	PA48BGA48-SST
MICROCHIP	SST34HF1621/Polling	BGA56	PA56BGA48D
MICROCHIP	SST34HF1621/Single	BGA56	PA56BGA48D
MICROCHIP	SST34HF1621/Toggle	BGA56	PA56BGA48D
MICROCHIP	SST34HF1621A	BGA62	PA62BGA48D
MICROCHIP	SST34HF1621A/Polling	BGA56	PA56BGA48D
MICROCHIP	SST34HF1621A/Toggle	BGA56	PA56BGA48D
MICROCHIP	SST34HF1621C/Polling	BGA56	PA56BGA48D-1
MICROCHIP	SST34HF1621C/Single	BGA56	PA56BGA48D-1
MICROCHIP	SST34HF1621C/Toggle	BGA56	PA56BGA48D-1
MICROCHIP	SST34HF1621S/Polling	BGA56	PA56BGA48D-1
MICROCHIP	SST34HF1621S/Toggle	BGA56	PA56BGA48D-1
MICROCHIP	SST34HF1622	BGA56	PA56BGA48D
MICROCHIP	SST34HF1622C	BGA56	PA56BGA48D
MICROCHIP	SST34HF1622C	BGA62	PA62BGA48D
MICROCHIP	SST34HF1622S	BGA56	PA56BGA48D
MICROCHIP	SST34HF1622S	BGA62	PA62BGA48D
MICROCHIP	SST34HF162G	BGA48	PA48BG48DAI
MICROCHIP	SST34HF1641	BGA56	PA56BGA48D
MICROCHIP	SST34HF1641	BGA62	PA62BGA48D
MICROCHIP	SST34HF1641A	BGA56	PA56BGA48D
MICROCHIP	SST34HF1641A	BGA62	PA62BGA48D
MICROCHIP	SST34HF1641C	BGA56	PA56BGA48D
MICROCHIP	SST34HF1641C	BGA62	PA62BGA48D
MICROCHIP	SST34HF1641D	BGA56	PA56BGA48D
MICROCHIP	SST34HF1641D	BGA62	PA62BGA48D
MICROCHIP	SST34HF1641S	BGA56	PA56BGA48D
MICROCHIP	SST34HF1641S	BGA62	PA62BGA48D
MICROCHIP	SST34HF1642	BGA56	PA56BGA48D
MICROCHIP	SST34HF1642C	BGA56	PA56BGA48D1
MICROCHIP	SST34HF1642C	BGA62	PA62BGA48D1
MICROCHIP	SST34HF1642D	BGA56	PA56BGA48D
MICROCHIP	SST34HF1642D	BGA62	PA62BGA48D
MICROCHIP	SST34HF1642S	BGA56	PA56BGA48D
MICROCHIP	SST34HF1642S	BGA62	PA62BGA48D
MICROCHIP	SST34HF164G	BGA48	PA48BG48DAI
MICROCHIP	SST34HF1681C	BGA56	PA56BGA48D
MICROCHIP	SST34HF1681C	BGA62	PA62BGA48D
MICROCHIP	SST34HF1681D	BGA56	PA56BGA48D
MICROCHIP	SST34HF1681D	BGA62	PA62BGA48D
MICROCHIP	SST34HF1681J	BGA56	PA56BGA48D-1
MICROCHIP	SST34HF1682D	BGA56	PA56BGA48D
MICROCHIP	SST34HF1682D	BGA62	PA62BGA48D
MICROCHIP	SST34HF3223A	BGA56	PA56BGA48D
MICROCHIP	SST34HF3243A	BGA56	PA56BGA48D
MICROCHIP	SST34HF3244C	BGA56	PA56BGA48D1
MICROCHIP	SST34HF3244C	BGA62	PA62BGA48D1
MICROCHIP	SST34HF3284	BGA56	PA56BGA48D1
MICROCHIP	SST34HF3284	BGA62	PA62BGA48D1
MICROCHIP	SST34HF32A4	BGA56	HA56BGA48D-2
MICROCHIP	SST34VF1621	BGA56	PA56BGA48D
MICROCHIP	SST34VF1622	BGA56	PA56BGA48D
MICROCHIP	SST34VF1641	BGA56	PA56BGA48D
MICROCHIP	SST34VF1642	BGA56	PA56BGA48D
MICROCHIP	SST36VF1601	TSOP48	PA48TS48D
MICROCHIP	SST36VF1601C	BGA48	PA48BG48DAI
MICROCHIP	SST36VF1601C	TSOP48	PA48TS48D
MICROCHIP	SST36VF1601C/PA5	BGA48	PA48BG48DAI
MICROCHIP	SST36VF1601C/PA5	TSOP48	PA48TS48D
MICROCHIP	SST36VF1601E	BGA48	PA48BG48DAI
MICROCHIP	SST36VF1601E	TSOP48	PA48TS48D
MICROCHIP	SST36VF1601G	TSOP48	PA48TS48D1

MICROCHIP	SST36VF1601H	TSOP48	PA48TS48D
MICROCHIP	SST36VF1602	TSOP48	PA48TS48D
MICROCHIP	SST36VF1602C	TSOP48	PA48TS48D
MICROCHIP	SST36VF1602E	BGA48	PA48BG48DAI
MICROCHIP	SST36VF1602E	TSOP48	PA48TS48D
MICROCHIP	SST36VF1602H	TSOP48	PA48TS48D
MICROCHIP	SST36VF3203	BGA48	PA48BG48DAI
MICROCHIP	SST36VF3203	TSOP48	PA48TS48D1
MICROCHIP	SST36VF3204	BGA48	PA48BG48DAI
MICROCHIP	SST36VF3204	TSOP48	PA48TS48D1
MICROCHIP	SST37VF010	DIP32	
MICROCHIP	SST37VF010	PLCC32	PA32PL32D
MICROCHIP	SST37VF010	TSOP32	PA32TS32D
MICROCHIP	SST37VF020	DIP32	
MICROCHIP	SST37VF020	PLCC32	PA32PL32D
MICROCHIP	SST37VF020	TSOP32	PA32TS32D
MICROCHIP	SST37VF040	DIP32	
MICROCHIP	SST37VF040	PLCC32	PA32PL32D
MICROCHIP	SST37VF040	TSOP32	PA32TS32D
MICROCHIP	SST37VF080	TSOP48	PA48TS48D
MICROCHIP	SST37VF512	DIP32	
MICROCHIP	SST37VF512	PLCC32	PA32PL32D
MICROCHIP	SST37VF512	TSOP32	PA32TS32D
MICROCHIP	SST38VF6401	BGA48	HA48BG48DAI
MICROCHIP	SST38VF6401	BGA48	PA48BG48DW
MICROCHIP	SST38VF6401	TSOP48	PA48TS48D1
MICROCHIP	SST38VF6401B	TSOP48	PA48TS48D1
MICROCHIP	SST38VF6402	BGA48	HA48BG48DAI
MICROCHIP	SST38VF6402	BGA48	PA48BG48DW
MICROCHIP	SST38VF6402	TSOP48	PA48TS48D1
MICROCHIP	SST38VF6403	BGA48	HA48BG48DAI
MICROCHIP	SST38VF6403	BGA48	PA48BG48DW
MICROCHIP	SST38VF6403	TSOP48	PA48TS48D1
MICROCHIP	SST38VF6404	BGA48	HA48BG48DAI
MICROCHIP	SST38VF6404	BGA48	PA48BG48DW
MICROCHIP	SST38VF6404	TSOP48	PA48TS48D1
MICROCHIP	SST39LF010	DIP32	
MICROCHIP	SST39LF010	PLCC32	PA32PL32D
MICROCHIP	SST39LF010	TSOP32	PA32TS32D
MICROCHIP	SST39LF010	WFBGA34	PA48WFB32D
MICROCHIP	SST39LF020	DIP32	
MICROCHIP	SST39LF020	PLCC32	PA32PL32D
MICROCHIP	SST39LF020	TSOP32	PA32TS32D
MICROCHIP	SST39LF040	DIP32	
MICROCHIP	SST39LF040	PLCC32	PA32PL32D
MICROCHIP	SST39LF040	TSOP32	PA32TS32D
MICROCHIP	SST39LF100	TSOP40	PA40TS14-OT
MICROCHIP	SST39LF200A	TSOP48	PA48TS48D1
MICROCHIP	SST39LF400A	TSOP48	PA48TS48D1
MICROCHIP	SST39LF512	DIP32	
MICROCHIP	SST39LF512	PLCC32	PA32PL32D
MICROCHIP	SST39LF512	TSOP32	PA32TS32D
MICROCHIP	SST39LF800A	BGA48	PA48BG48DAI
MICROCHIP	SST39LF800A	TSOP48	PA48TS48D1
MICROCHIP	SST39LF800A	WFBGA48	PA48WFB48D1
MICROCHIP	SST39LH010	DIP32	
MICROCHIP	SST39LH020	DIP32	
MICROCHIP	SST39LH040	DIP32	
MICROCHIP	SST39LH512	DIP32	
MICROCHIP	SST39SF010	DIP32	
MICROCHIP	SST39SF010	PLCC32	PA32PL32D
MICROCHIP	SST39SF010	TSOP32	PA32TS32D
MICROCHIP	SST39SF010A	DIP32	
MICROCHIP	SST39SF010A	PLCC32	PA32PL32D
MICROCHIP	SST39SF010A	TSOP32	PA32TS32D
MICROCHIP	SST39SF020	DIP32	
MICROCHIP	SST39SF020	PLCC32	PA32PL32D
MICROCHIP	SST39SF020	TSOP32	PA32TS32D
MICROCHIP	SST39SF020A	DIP32	
MICROCHIP	SST39SF020A	PLCC32	PA32PL32D
MICROCHIP	SST39SF020A	TSOP32	PA32TS32D
MICROCHIP	SST39SF020P	DIP32	
MICROCHIP	SST39SF020P	PLCC32	PA32PL32D

MICROCHIP	SST39SF020P	TSOP32	PA32TS32D
MICROCHIP	SST39SF040	DIP32	
MICROCHIP	SST39SF040	PLCC32	PA32PL32D
MICROCHIP	SST39SF040	TSOP32	PA32TS32D
MICROCHIP	SST39SF040P	DIP32	
MICROCHIP	SST39SF040P	PLCC32	PA32PL32D
MICROCHIP	SST39SF040P	TSOP32	PA32TS32D
MICROCHIP	SST39SF512	DIP32	
MICROCHIP	SST39SF512	PLCC32	PA32PL32D
MICROCHIP	SST39SF512	TSOP32	PA32TS32D
MICROCHIP	SST39SF512A	DIP32	
MICROCHIP	SST39SF512A	PLCC32	PA32PL32D
MICROCHIP	SST39SF512A	TSOP32	PA32TS32D
MICROCHIP	SST39VF010	BGA48	PA48BGA32DN-3O-6X8
MICROCHIP	SST39VF010	DIP32	
MICROCHIP	SST39VF010	PLCC32	PA32PL32D
MICROCHIP	SST39VF010	TSOP32	PA32TS32D
MICROCHIP	SST39VF016	TSOP40	PA40TS40D
MICROCHIP	SST39VF016Q	TSOP40	PA40TS40D
MICROCHIP	SST39VF020	DIP32	
MICROCHIP	SST39VF020	PLCC32	PA32PL32D
MICROCHIP	SST39VF020	TSOP32	PA32TS32D
MICROCHIP	SST39VF020P	BGA48	PA48BGA32DN-3O-6X8
MICROCHIP	SST39VF020P	DIP32	
MICROCHIP	SST39VF020P	PLCC32	PA32PL32D
MICROCHIP	SST39VF020P	TSOP32	PA32TS32D
MICROCHIP	SST39VF040	DIP32	
MICROCHIP	SST39VF040	PLCC32	PA32PL32D
MICROCHIP	SST39VF040	TSOP32	PA32TS32D
MICROCHIP	SST39VF040P	BGA48	PA48BGA32DN-3O-6X8
MICROCHIP	SST39VF040P	DIP32	
MICROCHIP	SST39VF040P	PLCC32	PA32PL32D
MICROCHIP	SST39VF040P	TSOP32	PA32TS32D
MICROCHIP	SST39VF080	TSOP40	PA40TS40D
MICROCHIP	SST39VF080B	TSOP48	PA48TS48D
MICROCHIP	SST39VF080Q	TSOP40	PA40TS40D
MICROCHIP	SST39VF088	TSOP48	PA48TS48D
MICROCHIP	SST39VF100	TSOP40	PA40TS14-OT
MICROCHIP	SST39VF160	TSOP48	PA48TS48D1
MICROCHIP	SST39VF160(Single)	TSOP48	PA48TS48D1
MICROCHIP	SST39VF1601	TSOP48	PA48TS48D1
MICROCHIP	SST39VF1601	WFBGA48	PA48BG48DAI
MICROCHIP	SST39VF1601C	TSOP48	PA48TS48D1
MICROCHIP	SST39VF1602	TSOP48	PA48TS48D1
MICROCHIP	SST39VF160Q	TSOP48	PA48TS48D1
MICROCHIP	SST39VF160Q(Single)	TSOP48	PA48TS48D1
MICROCHIP	SST39VF1681	TSOP48	PA48TS48D1
MICROCHIP	SST39VF1682	TSOP48	PA48TS48D1
MICROCHIP	SST39VF200A	BGA48	PA48BG48DAI
MICROCHIP	SST39VF200A	TSOP48	PA48TS48D1
MICROCHIP	SST39VF200A	WFBGA48	PA48WFB48D1
MICROCHIP	SST39VF320	TSOP48	PA48TS48D1
MICROCHIP	SST39VF3201	BGA48	PA48BG48DAI
MICROCHIP	SST39VF3201	TSOP48	PA48TS48D1
MICROCHIP	SST39VF3201B	TSOP48	PA48TS48D1
MICROCHIP	SST39VF3201C	TSOP48	PA48TS48D1
MICROCHIP	SST39VF3202	BGA48	PA48BG48DAI
MICROCHIP	SST39VF3202	TSOP48	PA48TS48D1
MICROCHIP	SST39VF400	TSOP48	PA48TS48D1
MICROCHIP	SST39VF400A	BGA48	PA48BG48DAI
MICROCHIP	SST39VF400A	TSOP48	PA48TS48D1
MICROCHIP	SST39VF400A	WFBGA48	PA48WFB48D1
MICROCHIP	SST39VF400Q	TSOP48	PA48TS48D1
MICROCHIP	SST39VF401C	TSOP48	PA48TS48D1
MICROCHIP	SST39VF512	BGA48	PA48BGA32DN-3O-6X8
MICROCHIP	SST39VF512	DIP32	
MICROCHIP	SST39VF512	PLCC32	PA32PL32D
MICROCHIP	SST39VF512	TSOP32	PA32TS32D
MICROCHIP	SST39VF640	TSOP48	PA48TS48D1
MICROCHIP	SST39VF6401	BGA48	HA48BG48DG1
MICROCHIP	SST39VF6401	TSOP48	PA48TS48D1
MICROCHIP	SST39VF6401B	BGA48	HA48BG48DG1
MICROCHIP	SST39VF6401B	TSOP48	PA48TS48D1

MICROCHIP	SST39VF6402	BGA48	HA48BG48DG1
MICROCHIP	SST39VF6402	TSOP48	PA48TS48D1
MICROCHIP	SST39VF6402B	BGA48	HA48BG48DG1
MICROCHIP	SST39VF6402B	TSOP48	PA48TS48D1
MICROCHIP	SST39VF800	TSOP48	PA48TS48D1
MICROCHIP	SST39VF800A	BGA48	PA48BG48DAI
MICROCHIP	SST39VF800A	TSOP48	PA48TS48D1
MICROCHIP	SST39VF800A	WFBGA48	PA48WFB48D1
MICROCHIP	SST39VF800Q	TSOP48	PA48TS48D1
MICROCHIP	SST39VF801C	TSOP48	PA48TS48D1
MICROCHIP	SST39WF1601	WFBGA48	HA48BG48DAI
MICROCHIP	SST39WF1601	WFBGA48	PA48BG48DW
MICROCHIP	SST39WF1602	WFBGA48	HA48BG48DAI
MICROCHIP	SST39WF1602	WFBGA48	PA48BG48DW
MICROCHIP	SST39WF400A	WFBGA48	PA48WFB48D
MICROCHIP	SST39WF400B	WFBGA48	HA48BG48DAI
MICROCHIP	SST39WF400B	WFBGA48	PA48BG48DW
MICROCHIP	SST39WF400A	WFBGA48	PA48WFB48D1
MICROCHIP	SST39WF800B	WFBGA48	PA48WFB48D1
MICROCHIP	SST45LF010	SOP8	PA16SO16D-EO-150
MICROCHIP	SST45VF010	SOP8	PA16SO16D-EO-150
MICROCHIP	SST49LF002	PLCC32	PA32PL32D
MICROCHIP	SST49LF002	TSOP32	PA32TS32D
MICROCHIP	SST49LF002A	PLCC32	PA32PL32D
MICROCHIP	SST49LF002A	TSOP32	PA32TS32D
MICROCHIP	SST49LF002A	TSOP40	PA40TS40D
MICROCHIP	SST49LF002B	PLCC32	PA32PL32D
MICROCHIP	SST49LF002B	TSOP32	PA32TS32D
MICROCHIP	SST49LF002B	TSOP40	PA40TS40D
MICROCHIP	SST49LF003A	PLCC32	PA32PL32D
MICROCHIP	SST49LF003A	TSOP32	PA32TS32D
MICROCHIP	SST49LF003A	TSOP40	PA40TS40D
MICROCHIP	SST49LF003B	PLCC32	PA32PL32D
MICROCHIP	SST49LF003B	TSOP32	PA32TS32D
MICROCHIP	SST49LF003B	TSOP40	PA40TS40D
MICROCHIP	SST49LF004	PLCC32	PA32PL32D
MICROCHIP	SST49LF004	TSOP32	PA32TS32D
MICROCHIP	SST49LF004A	PLCC32	PA32PL32D
MICROCHIP	SST49LF004A	TSOP32	PA32TS32D
MICROCHIP	SST49LF004A	TSOP40	PA40TS40D
MICROCHIP	SST49LF004B	PLCC32	PA32PL32D
MICROCHIP	SST49LF004B	TSOP32	PA32TS32D
MICROCHIP	SST49LF004B	TSOP40	PA40TS40D
MICROCHIP	SST49LF004C	PLCC32	PA32PL32D
MICROCHIP	SST49LF004C	TSOP32	PA32TS20/PA32TS32D-20
MICROCHIP	SST49LF008	PLCC32	PA32PL32D
MICROCHIP	SST49LF008	TSOP32	PA32TS32D
MICROCHIP	SST49LF008A	PLCC32	PA32PL32D
MICROCHIP	SST49LF008A	TSOP32	PA32TS32D
MICROCHIP	SST49LF008A	TSOP40	PA40TS40D
MICROCHIP	SST49LF008B	PLCC32	PA32PL32D
MICROCHIP	SST49LF008B	TSOP32	PA32TS32D
MICROCHIP	SST49LF008B	TSOP40	PA40TS40D
MICROCHIP	SST49LF008C	PLCC32	PA32PL32D
MICROCHIP	SST49LF008C	TSOP32	PA32TS20/PA32TS32D-20
MICROCHIP	SST49LF016C(AAI)	PLCC32	PA32PL32D
MICROCHIP	SST49LF016C(AAI)	TSOP32	PA32TS20/PA32TS32D-20
MICROCHIP	SST49LF016C(AAI)	TSOP32	PA32TS32D
MICROCHIP	SST49LF016C(AAI)	TSOP40	PA40TS40D
MICROCHIP	SST49LF016C(FWH)	PLCC32	PA32PL32D
MICROCHIP	SST49LF016C(FWH)	TSOP32	PA32TS20/PA32TS32D-20
MICROCHIP	SST49LF016C(FWH)	TSOP32	PA32TS32D
MICROCHIP	SST49LF016C(FWH)	TSOP40	PA40TS40D
MICROCHIP	SST49LF016C(LPC)	PLCC32	PA32PL32D
MICROCHIP	SST49LF016C(LPC)	TSOP32	PA32TS20/PA32TS32D-20
MICROCHIP	SST49LF016C(LPC)	TSOP32	PA32TS32D
MICROCHIP	SST49LF016C(LPC)	TSOP40	PA40TS40D
MICROCHIP	SST49LF020	PLCC32	PA32PL32D
MICROCHIP	SST49LF020	TSOP32	PA32TS32D
MICROCHIP	SST49LF020A	PLCC32	PA32PL32D
MICROCHIP	SST49LF020A	TSOP32	PA32TS32D
MICROCHIP	SST49LF030A	PLCC32	PA32PL32D
MICROCHIP	SST49LF040	PLCC32	PA32PL32D

MICROCHIP	SST49LF040	TSOP32	PA32TS32D
MICROCHIP	SST49LF040A	PLCC32	PA32PL32D
MICROCHIP	SST49LF040A	TSOP32	PA32TS32D
MICROCHIP	SST49LF040B	PLCC32	PA32PL32D
MICROCHIP	SST49LF040B	TSOP32	PA32TS32D
MICROCHIP	SST49LF080	PLCC32	PA32PL32D
MICROCHIP	SST49LF080	TSOP32	PA32TS32D
MICROCHIP	SST49LF080A	PLCC32	PA32PL32D
MICROCHIP	SST49LF080A	TSOP32	PA32TS32D
MICROCHIP	SST49LF160C(AAI)	PLCC32	PA32PL32D
MICROCHIP	SST49LF160C(AAI)	TSOP32	PA32TS20/PA32TS32D-20
MICROCHIP	SST49LF160C(AAI)	TSOP32	PA32TS32D
MICROCHIP	SST49LF160C(AAI)	TSOP40	PA40TS40D
MICROCHIP	SST89E58RDA	DIP40	
MICRON	M25P32-VME	WSON8	PA8SON8DA(8x6)
MICRON	M25P32-VMF	SOP16	PA28SO28D-EO-300
MICRON	M25P32-VMP	WSON8	PA8SON8D(6x5)
MICRON	M25P32-VMW	SOIC8	PA20SO20D-EO-210
MICRON	M29F160FB	TSOP48	PA48TS48D
MICRON	M29F160FT	TSOP48	PA48TS48D
MICRON	M29W256GH-N	TSOP56	HA56TS48DI
MICRON	M29W256GH-ZS	BGA64	PA64BG48DR
MICRON	M29W256GL-N	TSOP56	HA56TS48DI
MICRON	M29W256GL-ZS	BGA64	PA64BG48DR
MICRON	MT25QL01GBBxExE	SOP16	PA28SO28D-EO-300
MICRON	MT25QL01GBBxExE	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	MT25QL01GBBxExE	VDFN8	PA8SON8DA(8x6)
MICRON	MT25QL01GBBBxExE	SOP16	PA28SO28D-EO-300
MICRON	MT25QL01GBBBxExE	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	MT25QL01GBBBxExE	VDFN8	PA8SON8DA(8x6)
MICRON	MT25QL02GCBxExE	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	MT25QL02GCBxExE	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	MT25QL128ABxExE	SOP16	PA28SO28D-EO-300
MICRON	MT25QL128ABxExE	SOP8	PA20SO20D-EO-210
MICRON	MT25QL128ABxExE	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	MT25QL128ABxExE	VDFN8	PA8SON8D(6x5)
MICRON	MT25QL128ABxExE	VDFN8	PA8SON8DA(8x6)
MICRON	MT25QL128ABxExE	SOP16	PA28SO28D-EO-300
MICRON	MT25QL256ABxExE	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	MT25QL256ABxExE	VDFN8	PA8SON8D(6x5)
MICRON	MT25QL256ABxExE	VDFN8	PA8SON8DA(8x6)
MICRON	MT25QL256ABxExE	SOP16	PA28SO28D-EO-300
MICRON	MT25QL512ABxExE	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	MT25QL512ABxExE	VDFN8	PA8SON8DA(8x6)
MICRON	MT25QL512ABxExE	SOP16	PA28SO28D-EO-300
MICRON	MT25QL512ABBxExE	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	MT25QL512ABBxExE	VDFN8	PA8SON8DA(8x6)
MICRON	MT25QU01GBBxExE	SOP16	PA28SO28D-EO-300
MICRON	MT25QU01GBBxExE	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	MT25QU01GBBxExE	VDFN8	PA8SON8DA(8x6)
MICRON	MT25QU01GBBBxExE	SOP16	PA28SO28D-EO-300
MICRON	MT25QU01GBBBxExE	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	MT25QU01GBBBxExE	VDFN8	PA8SON8DA(8x6)
MICRON	MT25QU02GCBxExE	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	MT25QU02GCBxExE	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	MT25QU128ABxExE	SOP16	PA28SO28D-EO-300
MICRON	MT25QU128ABxExE	SOP8	PA20SO20D-EO-210
MICRON	MT25QU128ABxExE	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	MT25QU128ABxExE	VDFN8	PA8SON8D(6x5)
MICRON	MT25QU128ABxExE	VDFN8	PA8SON8DA(8x6)
MICRON	MT25QU256ABxExE	SOP16	PA28SO28D-EO-300
MICRON	MT25QU256ABxExE	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	MT25QU256ABxExE	VDFN8	PA8SON8D(6x5)
MICRON	MT25QU256ABxExE	VDFN8	PA8SON8DA(8x6)
MICRON	MT25QU512ABxExE	SOP16	PA28SO28D-EO-300
MICRON	MT25QU512ABxExE	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	MT25QU512ABxExE	VDFN8	PA8SON8DA(8x6)
MICRON	MT25QU512ABBxExE	SOP16	PA28SO28D-EO-300
MICRON	MT25QU512ABBxExE	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	MT25QU512ABBxExE	VDFN8	PA8SON8DA(8x6)
MICRON	MT28C128532W30D-TB	BGA88	PA88BGA48DA-YO-8X10
MICRON	MT28C128564W30D-TB	BGA88	PA88BGA48DA-YO-8X10
MICRON	MT28C64432W30A-T	BGA88	PA88BGA48DA-YO-8X10

MICRON	MT28EW01GABA1HJS	TSOP56	HA56TS48DI
MICRON	MT28EW01GABA1HPC	BGA64	PA64BG48DR
MICRON	MT28EW128ABA1HJS	TSOP56	HA56TS48DI
MICRON	MT28EW128ABA1HPC	BGA64	PA64BG48DR
MICRON	MT28EW256ABA1HJS	TSOP56	HA56TS48DI
MICRON	MT28EW256ABA1HJS	TSOP56	PA56TS48DD
MICRON	MT28EW256ABA1HPC	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
MICRON	MT28EW256ABA1HPC	BGA64	PA64BG48DR
MICRON	MT28EW512ABA1HJS	TSOP56	HA56TS48DI
MICRON	MT28EW512ABA1HPC	BGA64	PA64BG48DR
MICRON	MT28F128J3	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
MICRON	MT28F320J3	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
MICRON	MT28F640J3	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
MICRON	MT28F800B3-B	TSOP48	PA48TS48D
MICRON	MT28F800B3-T	TSOP48	PA48TS48D
MICRON	MT28F800B5-B	TSOP48	PA48TS48D
MICRON	MT28F800B5-T	TSOP48	PA48TS48D
MICRON	MT29F1G01AAADD	BGA63	NA63BG48DAA-D
MICRON	MT29F1G01AAADD(+Spare)	BGA63	NA63BG48DAA-D
MICRON	MT29F2G08AAC	TSOP48	PA48TS48D
MICRON	MT29F4G08AA	TSOP48	HA48TS48DET
MICRON	MT29F4G08ABAEA	TSOP48	HA48TS48DET
MICRON	MT29F8G08AA-size4G	TSOP48	HA48TS48DET
MICRON	N25Q008Ax1E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MICRON	N25Q008Ax1E	USON8	PA8SON8D(4x3)
MICRON	N25Q008Ax1E	VDFN8	PA8SON8D(6x5)
MICRON	N25Q00AAx1G	SOP16	PA28SO28D-EO-300
MICRON	N25Q00AAx1G	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	N25Q00AAx1G(Quad_IO)	SOP16	PA28SO28D-EO-300
MICRON	N25Q00AAx1G(Quad_IO)	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	N25Q00AAx3G	SOP16	PA28SO28D-EO-300
MICRON	N25Q00AAx3G	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	N25Q00AAx3G(Quad_IO)	SOP16	PA28SO28D-EO-300
MICRON	N25Q00AAx3G(Quad_IO)	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	N25Q016Ax1E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MICRON	N25Q016Ax1E	USON8	PA8SON8D(4x3)
MICRON	N25Q016Ax1E	VDFN8	PA8SON8D(6x5)
MICRON	N25Q032Ax1E	SOP16	PA28SO28D-EO-300
MICRON	N25Q032Ax1E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MICRON	N25Q032Ax1E	SOP8	PA20SO20D-EO-210
MICRON	N25Q032Ax1E	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	N25Q032Ax1E	USON8	PA8SON8D(4x3)
MICRON	N25Q032Ax1E	VDFN8	PA8SON8D(6x5)
MICRON	N25Q032Ax1E	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q032Ax1E(Quad_IO)	SOP16	PA28SO28D-EO-300
MICRON	N25Q032Ax1E(Quad_IO)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MICRON	N25Q032Ax1E(Quad_IO)	SOP8	PA20SO20D-EO-210
MICRON	N25Q032Ax1E(Quad_IO)	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	N25Q032Ax1E(Quad_IO)	USON8	PA8SON8D(4x3)
MICRON	N25Q032Ax1E(Quad_IO)	VDFN8	PA8SON8D(6x5)
MICRON	N25Q032Ax1E(Quad_IO)	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q032Ax3E	SOP16	PA28SO28D-EO-300
MICRON	N25Q032Ax3E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MICRON	N25Q032Ax3E	SOP8	PA20SO20D-EO-210
MICRON	N25Q032Ax3E	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	N25Q032Ax3E	USON8	PA8SON8D(4x3)
MICRON	N25Q032Ax3E	VDFN8	PA8SON8D(6x5)
MICRON	N25Q032Ax3E	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q032Ax3E(Quad_IO)	SOP16	PA28SO28D-EO-300
MICRON	N25Q032Ax3E(Quad_IO)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
MICRON	N25Q032Ax3E(Quad_IO)	SOP8	PA20SO20D-EO-210
MICRON	N25Q032Ax3E(Quad_IO)	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	N25Q032Ax3E(Quad_IO)	USON8	PA8SON8D(4x3)
MICRON	N25Q032Ax3E(Quad_IO)	VDFN8	PA8SON8D(6x5)
MICRON	N25Q032Ax3E(Quad_IO)	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q064Ax1E	SOP16	PA28SO28D-EO-300
MICRON	N25Q064Ax1E	SOP8	PA20SO20D-EO-210
MICRON	N25Q064Ax1E	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	N25Q064Ax1E	VDFN8	PA8SON8D(6x5)
MICRON	N25Q064Ax1E	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q064Ax1E(Quad_IO)	SOP16	PA28SO28D-EO-300
MICRON	N25Q064Ax1E(Quad_IO)	SOP8	PA20SO20D-EO-210
MICRON	N25Q064Ax1E(Quad_IO)	TFBGA24	PA24BG24D(6x8mm)5x5

MICRON	N25Q064Ax1E(Quad_IO)	VDFN8	PA8SON8D(6x5)
MICRON	N25Q064Ax1E(Quad_IO)	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q064Ax3E	SOP16	PA28SO28D-EO-300
MICRON	N25Q064Ax3E	SOP8	PA20SO20D-EO-210
MICRON	N25Q064Ax3E	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	N25Q064Ax3E	VDFN8	PA8SON8D(6x5)
MICRON	N25Q064Ax3E	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q064Ax3E(Quad_IO)	SOP16	PA28SO28D-EO-300
MICRON	N25Q064Ax3E(Quad_IO)	SOP8	PA20SO20D-EO-210
MICRON	N25Q064Ax3E(Quad_IO)	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	N25Q064Ax3E(Quad_IO)	VDFN8	PA8SON8D(6x5)
MICRON	N25Q064Ax3E(Quad_IO)	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q128Ax1B	SOP16	PA28SO28D-EO-300
MICRON	N25Q128Ax1B	SOP8	PA20SO20D-EO-210
MICRON	N25Q128Ax1B	VDFN8	PA8SON8D(6x5)
MICRON	N25Q128Ax1B	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q128Ax1B(Quad_IO)	SOP16	PA28SO28D-EO-300
MICRON	N25Q128Ax1B(Quad_IO)	SOP8	PA20SO20D-EO-210
MICRON	N25Q128Ax1B(Quad_IO)	VDFN8	PA8SON8D(6x5)
MICRON	N25Q128Ax1B(Quad_IO)	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q128Ax1E	SOP16	PA28SO28D-EO-300
MICRON	N25Q128Ax1E	SOP8	PA20SO20D-EO-210
MICRON	N25Q128Ax1E	VDFN8	PA8SON8D(6x5)
MICRON	N25Q128Ax1E	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q128Ax1E(Quad_IO)	SOP16	PA28SO28D-EO-300
MICRON	N25Q128Ax1E(Quad_IO)	SOP8	PA20SO20D-EO-210
MICRON	N25Q128Ax1E(Quad_IO)	VDFN8	PA8SON8D(6x5)
MICRON	N25Q128Ax1E(Quad_IO)	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q128Ax1T	SOP16	PA28SO28D-EO-300
MICRON	N25Q128Ax1T	SOP8	PA20SO20D-EO-210
MICRON	N25Q128Ax1T	VDFN8	PA8SON8D(6x5)
MICRON	N25Q128Ax1T	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q128Ax1T(Quad_IO)	SOP16	PA28SO28D-EO-300
MICRON	N25Q128Ax1T(Quad_IO)	SOP8	PA20SO20D-EO-210
MICRON	N25Q128Ax1T(Quad_IO)	VDFN8	PA8SON8D(6x5)
MICRON	N25Q128Ax1T(Quad_IO)	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q128Ax3B	SOP16	PA28SO28D-EO-300
MICRON	N25Q128Ax3B	SOP8	PA20SO20D-EO-210
MICRON	N25Q128Ax3B	VDFN8	PA8SON8D(6x5)
MICRON	N25Q128Ax3B	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q128Ax3B(Quad_IO)	SOP16	PA28SO28D-EO-300
MICRON	N25Q128Ax3B(Quad_IO)	SOP8	PA20SO20D-EO-210
MICRON	N25Q128Ax3B(Quad_IO)	VDFN8	PA8SON8D(6x5)
MICRON	N25Q128Ax3B(Quad_IO)	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q128Ax3E	SOP16	PA28SO28D-EO-300
MICRON	N25Q128Ax3E	SOP8	PA20SO20D-EO-210
MICRON	N25Q128Ax3E	VDFN8	PA8SON8D(6x5)
MICRON	N25Q128Ax3E	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q128Ax3E(Quad_IO)	SOP16	PA28SO28D-EO-300
MICRON	N25Q128Ax3E(Quad_IO)	SOP8	PA20SO20D-EO-210
MICRON	N25Q128Ax3E(Quad_IO)	VDFN8	PA8SON8D(6x5)
MICRON	N25Q128Ax3E(Quad_IO)	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q128Ax3T	SOP16	PA28SO28D-EO-300
MICRON	N25Q128Ax3T	SOP8	PA20SO20D-EO-210
MICRON	N25Q128Ax3T	VDFN8	PA8SON8D(6x5)
MICRON	N25Q128Ax3T	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q128Ax3T(Quad_IO)	SOP16	PA28SO28D-EO-300
MICRON	N25Q128Ax3T(Quad_IO)	SOP8	PA20SO20D-EO-210
MICRON	N25Q128Ax3T(Quad_IO)	VDFN8	PA8SON8D(6x5)
MICRON	N25Q128Ax3T(Quad_IO)	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q256Ax1E	SOP16	PA28SO28D-EO-300
MICRON	N25Q256Ax1E	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	N25Q256Ax1E	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q256Ax3E	SOP16	PA28SO28D-EO-300
MICRON	N25Q256Ax3E	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	N25Q256Ax3E	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q512Ax1G	SOP16	PA28SO28D-EO-300
MICRON	N25Q512Ax1G	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	N25Q512Ax1G	VDFN8	PA8SON8DA(8x6)
MICRON	N25Q512Ax3G	SOP16	PA28SO28D-EO-300
MICRON	N25Q512Ax3G	TFBGA24	PA24BG24D(6x8mm)5x5
MICRON	N25Q512Ax3G	VDFN8	PA8SON8DA(8x6)
MITSUBISHI	M37531E4	DIP32	PCA7435SP

mitsubishi	M37531E8	DIP32	PCA7435SP
mitsubishi	M5L27128K	DIP28	
mitsubishi	M5L27256K	DIP28	
mitsubishi	M5L2732	DIP24	
mitsubishi	M5L27512K	DIP28	
mitsubishi	M5L2764K	DIP28	
mitsubishi	M5M27128P	DIP28	
mitsubishi	M5M27256P	DIP28	
mitsubishi	M5M27512P	DIP28	
mitsubishi	M5M2764P	DIP28	
mitsubishi	M5M27C100K	DIP32	
mitsubishi	M5M27C100P	DIP32	
mitsubishi	M5M27C101K	DIP32	
mitsubishi	M5M27C101P	DIP32	
mitsubishi	M5M27C102K	DIP40	
mitsubishi	M5M27C102K	PLCC44	PA44-48U
mitsubishi	M5M27C102K	SOP40	PA40SO40D-EO-450
mitsubishi	M5M27C102K	TSOP40	PA40TS40D
mitsubishi	M5M27C102P	DIP40	
mitsubishi	M5M27C102P	PLCC44	PA44-48U
mitsubishi	M5M27C102P	SOP40	PA40SO40D-EO-450
mitsubishi	M5M27C102P	TSOP40	PA40TS40D
mitsubishi	M5M27C128K	DIP28	
mitsubishi	M5M27C201K	DIP32	
mitsubishi	M5M27C201K	PLCC32	PA32PL32D
mitsubishi	M5M27C202K	DIP40	
mitsubishi	M5M27C202K	PLCC44	PA44-48U
mitsubishi	M5M27C202K	SOP40	PA40SO40D-EO-450
mitsubishi	M5M27C202K	TSOP40	PA40TS40D
mitsubishi	M5M27C256AK	DIP28	
mitsubishi	M5M27C256AK	SOIC28	PA28SO28D-EO-300
mitsubishi	M5M27C256AK	TSOP28	PA28TS28D-EO
mitsubishi	M5M27C256K	DIP28	
mitsubishi	M5M27C256P	DIP28	
mitsubishi	M5M27C401K	DIP32	
mitsubishi	M5M27C401K	PLCC32	PA32PL32D
mitsubishi	M5M27C401K	TSOP32	PA32TS20/PA32TS32D-20
mitsubishi	M5M27C402K	DIP40	
mitsubishi	M5M27C512AK	DIP28	
mitsubishi	M5M27C512AP	DIP28	
mitsubishi	M5M28C64AP	DIP28	
mitsubishi	M5M28C64P	DIP28	
MOSEL VITELIC	V29C31004B	PLCC32	PA32PL32D
MOSEL VITELIC	V29C31004B	TSOP32	PA32TS20/PA32TS32D-20
MOSEL VITELIC	V29C31004T	PLCC32	PA32PL32D
MOSEL VITELIC	V29C31004T	TSOP32	PA32TS20/PA32TS32D-20
MOSEL VITELIC	V29C51000B	DIP32	
MOSEL VITELIC	V29C51000B	PLCC32	PA32PL32D
MOSEL VITELIC	V29C51000B	TSOP32	PA32TS20/PA32TS32D-20
MOSEL VITELIC	V29C51000T	DIP32	
MOSEL VITELIC	V29C51000T	PLCC32	PA32PL32D
MOSEL VITELIC	V29C51000T	TSOP32	PA32TS20/PA32TS32D-20
MOSEL VITELIC	V29C51001B	DIP32	
MOSEL VITELIC	V29C51001B	PLCC32	PA32PL32D
MOSEL VITELIC	V29C51001B	TSOP32	PA32TS20/PA32TS32D-20
MOSEL VITELIC	V29C51001T	DIP32	
MOSEL VITELIC	V29C51001T	PLCC32	PA32PL32D
MOSEL VITELIC	V29C51001T	TSOP32	PA32TS20/PA32TS32D-20
MOSEL VITELIC	V29C51002B	DIP32	
MOSEL VITELIC	V29C51002B	PLCC32	PA32PL32D
MOSEL VITELIC	V29C51002B	TSOP32	PA32TS20/PA32TS32D-20
MOSEL VITELIC	V29C51002T	DIP32	
MOSEL VITELIC	V29C51002T	PLCC32	PA32PL32D
MOSEL VITELIC	V29C51002T	TSOP32	PA32TS20/PA32TS32D-20
MOSEL VITELIC	V29C51004B	PLCC32	PA32PL32D
MOSEL VITELIC	V29C51004B	TSOP32	PA32TS20/PA32TS32D-20
MOSEL VITELIC	V29C51004T	PLCC32	PA32PL32D
MOSEL VITELIC	V29C51004T	TSOP32	PA32TS20/PA32TS32D-20
MOSTEK	ET2716	DIP24	
MOSTEK	ETC2716	DIP24	
MOSTEK	ETC2732	DIP24	
MOSTEK	MK2716	DIP24	
MOSTEK	MK2764	DIP28	



MOSTEK	MKB2716	DIP24	
MOSTEK	MKM2716	DIP24	
MOTOROLA	MC68705P3	DIP28	
MOTOROLA	MC68705P5	DIP28	
MOTOROLA	MC68705R3	DIP40	
MOTOROLA	MC68705R5	DIP40	
MOTOROLA	MC68705U3	DIP40	
MOTOROLA	MC68705U5	DIP40	
MOTOROLA	MC68711E20CFNE3	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC05B16CFN	PLCC52	PA52-48-01P-Y
MOTOROLA	MC68HC05B16CFN	PLCC52	PA52PL48DF
MOTOROLA	MC68HC05B16FN	PLCC52	PA52-48-01P-Y
MOTOROLA	MC68HC05B16FN	PLCC52	PA52PL48DF
MOTOROLA	MC68HC05B16MFN	PLCC52	PA52-48-01P-Y
MOTOROLA	MC68HC05B16MFN	PLCC52	PA52PL48DF
MOTOROLA	MC68HC05B16NCFN	PLCC52	PA52-48-01P-Y
MOTOROLA	MC68HC05B16NCFN	PLCC52	PA52PL48DF
MOTOROLA	MC68HC05B16NFN	PLCC52	PA52-48-01P-Y
MOTOROLA	MC68HC05B16NFN	PLCC52	PA52PL48DF
MOTOROLA	MC68HC05B16NMFN	PLCC52	PA52-48-01P-Y
MOTOROLA	MC68HC05B16NMFN	PLCC52	PA52PL48DF
MOTOROLA	MC68HC05B16NVFN	PLCC52	PA52-48-01P-Y
MOTOROLA	MC68HC05B16NVFN	PLCC52	PA52PL48DF
MOTOROLA	MC68HC05B16VFN	PLCC52	PA52-48-01P-Y
MOTOROLA	MC68HC05B16VFN	PLCC52	PA52PL48DF
MOTOROLA	MC68HC11A1FN	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11A1P	DIP48	
MOTOROLA	MC68HC11A8FN	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11A8P	DIP48	
MOTOROLA	MC68HC11E1FN	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E20CFN2	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E20CFN3	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E20FN3	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E20MFN2	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E20VFN2	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E9CFN2	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E9CFN3	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E9CFU2	QFP64	PA64TQ40D-HCx11E
MOTOROLA	MC68HC11E9CFU3	QFP64	PA64TQ40D-HCx11E
MOTOROLA	MC68HC11E9CMU2	QFP64	PA64TQ40D-HCx11E
MOTOROLA	MC68HC11E9CVU2	QFP64	PA64TQ40D-HCx11E
MOTOROLA	MC68HC11E9MFN2	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11E9VFN2	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC11F1FN	PLCC68	PA68-48E
MOTOROLA	MC68HC11K4CFN	PLCC84	PA84-48C
MOTOROLA	MC68HC11K4CFN2	PLCC84	PA84-48C
MOTOROLA	MC68HC11K4CFN3	PLCC84	PA84-48C
MOTOROLA	MC68HC11K4CFN4	PLCC84	PA84-48C
MOTOROLA	MC68HC11K4MFN2	PLCC84	PA84-48C
MOTOROLA	MC68HC11K4MFN3	PLCC84	PA84-48C
MOTOROLA	MC68HC11K4MFN4	PLCC84	PA84-48C
MOTOROLA	MC68HC11K4VFN2	PLCC84	PA84-48C
MOTOROLA	MC68HC11K4VFN3	PLCC84	PA84-48C
MOTOROLA	MC68HC11K4VFN4	PLCC84	PA84-48C
MOTOROLA	MC68HC11L6FN	PLCC68	PA68-48D
MOTOROLA	MC68HC11L6FU	QFP64	PA64QF48DF
MOTOROLA	MC68HC11P2FN	PLCC84	PA84-48D
MOTOROLA	MC68HC705B16CFN	PLCC52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16CFN	PLCC52	PA52PL48DF
MOTOROLA	MC68HC705B16FN	PLCC52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16FN	PLCC52	PA52PL48DF
MOTOROLA	MC68HC705B16MFN	PLCC52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16MFN	PLCC52	PA52PL48DF
MOTOROLA	MC68HC705B16NCFN	PLCC52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16NCFN	PLCC52	PA52PL48DF
MOTOROLA	MC68HC705B16NFN	PLCC52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16NFN	PLCC52	PA52PL48DF
MOTOROLA	MC68HC705B16NMFN	PLCC52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16NMFN	PLCC52	PA52PL48DF
MOTOROLA	MC68HC705B16NVFN	PLCC52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16NVFN	PLCC52	PA52PL48DF
MOTOROLA	MC68HC705B16VFN	PLCC52	PA52-48-01P-Y
MOTOROLA	MC68HC705B16VFN	PLCC52	PA52PL48DF

MOTOROLA	MC68HC705B32FN	PLCC52	PA52-48-01P-Y
MOTOROLA	MC68HC705B32FN	PLCC52	PA52PL48DF
MOTOROLA	MC68HC705C4AFN	PLCC44	PA44-48U
MOTOROLA	MC68HC705C4AP	DIP40	
MOTOROLA	MC68HC705C8AFB	QFP44	PA44QF44D
MOTOROLA	MC68HC705C8AFN	PLCC44	PA44-48U
MOTOROLA	MC68HC705C8AP	DIP40	
MOTOROLA	MC68HC705C8FN	PLCC44	PA44-48U
MOTOROLA	MC68HC705C8P	DIP40	
MOTOROLA	MC68HC705C9ACFN	PLCC44	PA44-48U
MOTOROLA	MC68HC705C9AFB	QFP44	PA44QF44D
MOTOROLA	MC68HC705C9AFN	PLCC44	PA44-48U
MOTOROLA	MC68HC705C9AP	DIP40	
MOTOROLA	MC68HC705C9FN	PLCC44	PA44-48U
MOTOROLA	MC68HC705C9P	DIP40	
MOTOROLA	MC68HC705D32AFN	PLCC44	PA44-48U
MOTOROLA	MC68HC705D32AP	DIP40	
MOTOROLA	MC68HC705D32FN	PLCC44	PA44-48U
MOTOROLA	MC68HC705D32P	DIP40	
MOTOROLA	MC68HC705D9FN	PLCC44	PA44-48U
MOTOROLA	MC68HC705D9P	DIP40	
MOTOROLA	MC68HC705J1A	DIP20	
MOTOROLA	MC68HC705J1A	SOP20	PA28SO28D-EO-300
MOTOROLA	MC68HC705JJ7	DIP20	
MOTOROLA	MC68HC705JP7	DIP28	
MOTOROLA	MC68HC705KJ1	DIP16	
MOTOROLA	MC68HC705KJ1	SOP16	PA28SO28D-EO-300
MOTOROLA	MC68HC705P6ACDW	SOIC28	PA28SO28D-EO-300
MOTOROLA	MC68HC705P6ACP	DIP28	
MOTOROLA	MC68HC705P6ADW	SOIC28	PA28SO28D-EO-300
MOTOROLA	MC68HC705P6AP	DIP28	
MOTOROLA	MC68HC705P6DW	SOIC28	PA28SO28D-EO-300
MOTOROLA	MC68HC705P6P	DIP28	
MOTOROLA	MC68HC705P9CDW	SOIC28	PA28SO28D-EO-300
MOTOROLA	MC68HC705P9CP	DIP28	
MOTOROLA	MC68HC705P9DW	SOIC28	PA28SO28D-EO-300
MOTOROLA	MC68HC705P9P	DIP28	
MOTOROLA	MC68HC705SR3	DIP40	
MOTOROLA	MC68HC705SR3	QFP44	PA44QF44D
MOTOROLA	MC68HC705SR3	SDIP42	PA42SD42D
MOTOROLA	MC68HC705X4CDW	SOP28	PA28SO28D-EO-300
MOTOROLA	MC68HC705X4DW	SOP28	PA28SO28D-EO-300
MOTOROLA	MC68HC711D3CFN	PLCC44	PA44-48U
MOTOROLA	MC68HC711D3CFNE2	PLCC44	PA44-48U
MOTOROLA	MC68HC711D3CP	DIP40	
MOTOROLA	MC68HC711D3FN	PLCC44	PA44-48U
MOTOROLA	MC68HC711D3FS	PLCC44	PA44-48U
MOTOROLA	MC68HC711D3P	DIP40	
MOTOROLA	MC68HC711D3S	DIP40	
MOTOROLA	MC68HC711E20CFN2	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711E20CFN3	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711E20FN3	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711E20MFN2	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711E20VFN2	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711E9CFN2	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711E9CFN3	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711E9CFU2	QFP64	PA64TQ40D-HCx11E
MOTOROLA	MC68HC711E9CFU3	QFP64	PA64TQ40D-HCx11E
MOTOROLA	MC68HC711E9CMU2	QFP64	PA64TQ40D-HCx11E
MOTOROLA	MC68HC711E9CVU2	QFP64	PA64TQ40D-HCx11E
MOTOROLA	MC68HC711E9MFN2	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711E9VFN2	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC711K4CFN	PLCC84	PA84-48C
MOTOROLA	MC68HC711K4CFN2	PLCC84	PA84-48C
MOTOROLA	MC68HC711K4CFN3	PLCC84	PA84-48C
MOTOROLA	MC68HC711K4CFN4	PLCC84	PA84-48C
MOTOROLA	MC68HC711K4MFN2	PLCC84	PA84-48C
MOTOROLA	MC68HC711K4MFN3	PLCC84	PA84-48C
MOTOROLA	MC68HC711K4MFN4	PLCC84	PA84-48C
MOTOROLA	MC68HC711K4VFN2	PLCC84	PA84-48C
MOTOROLA	MC68HC711K4VFN3	PLCC84	PA84-48C
MOTOROLA	MC68HC711K4VFN4	PLCC84	PA84-48C
MOTOROLA	MC68HC711KS2VFN	PLCC68	PA68-48H

MOTOROLA	MC68HC711L6FN	PLCC68	PA68-48D
MOTOROLA	MC68HC711L6FU	QFP64	PA64QF48DF
MOTOROLA	MC68HC711P2FN	PLCC84	PA84-48D
MOTOROLA	MC68HC811E2CFN	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC811E2FN	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC68HC811E2P	DIP48	
MOTOROLA	MC68HC908GP32CB	SDIP42	PA-MACH4
MOTOROLA	MC68HC908GP32CFB	TQFP44	PA44QF44D
MOTOROLA	MC68HC908GP32CP	DIP40	
MOTOROLA	MC68HC908GP32MB	SDIP42	PA-MACH4
MOTOROLA	MC68HC908GP32MFB	TQFP44	PA44QF44D
MOTOROLA	MC68HC908GP32MP	DIP40	
MOTOROLA	MC68HC908GP32VB	SDIP42	PA-MACH4
MOTOROLA	MC68HC908GP32VFB	TQFP44	PA44QF44D
MOTOROLA	MC68HC908GP32VP	DIP40	
MOTOROLA	MC68HC908GT16CB	SDIP42	PA-MACH4
MOTOROLA	MC68HC908GT16CFB	TQFP44	PA44QF44D
MOTOROLA	MC68HC908GT8CB	SDIP42	PA-MACH4
MOTOROLA	MC68HC908GT8CFB	TQFP44	PA44QF44D
MOTOROLA	MC68HC908JK1CDW	SOP20	PA28SO28D-EO-300
MOTOROLA	MC68HC908JK1CP	DIP20	
MOTOROLA	MC68HC908JK1MDW	SOP20	PA28SO28D-EO-300
MOTOROLA	MC68HC908JK1MP	DIP20	
MOTOROLA	MC68HC908JK3CDW	SOP20	PA28SO28D-EO-300
MOTOROLA	MC68HC908JK3CP	DIP20	
MOTOROLA	MC68HC908JK3MDW	SOP20	PA28SO28D-EO-300
MOTOROLA	MC68HC908JK3MP	DIP20	
MOTOROLA	MC68HC908JL3CDW	SOP28	PA28SO28D-EO-300
MOTOROLA	MC68HC908JL3CP	DIP28	
MOTOROLA	MC68HC908JL3MDW	SOP28	PA28SO28D-EO-300
MOTOROLA	MC68HC908JL3MP	DIP28	
MOTOROLA	MC68HC908LB8CDWE	SOIC20	PA28SO28D-EO-300
MOTOROLA	MC68HC908LB8CPE	DIP20	
MOTOROLA	MC68HC908LB8MDWE	SOIC20	PA28SO28D-EO-300
MOTOROLA	MC68HC908LB8MPE	DIP20	
MOTOROLA	MC68HC908LB8VDWE	SOIC20	PA28SO28D-EO-300
MOTOROLA	MC68HC908LB8VPE	DIP20	
MOTOROLA	MC68HC908QB4CDT	TSSOP16	PA24TSS24D
MOTOROLA	MC68HC908QB4CDW	SOIC16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QB4CP	DIP16	
MOTOROLA	MC68HC908QB8CDT	TSSOP16	PA24TSS24D
MOTOROLA	MC68HC908QB8CDW	SOIC16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QB8CP	DIP16	
MOTOROLA	MC68HC908QL2CDT	TSSOP16	PA24TSS24D
MOTOROLA	MC68HC908QL2CDW	SOIC16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QL2MDT	TSSOP16	PA24TSS24D
MOTOROLA	MC68HC908QL2MDW	SOIC16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QL2VDT	TSSOP16	PA24TSS24D
MOTOROLA	MC68HC908QL2VDW	SOIC16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QL3CDT	TSSOP16	PA24TSS24D
MOTOROLA	MC68HC908QL3CDW	SOIC16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QL3MDT	TSSOP16	PA24TSS24D
MOTOROLA	MC68HC908QL3MDW	SOIC16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QL3VDT	TSSOP16	PA24TSS24D
MOTOROLA	MC68HC908QL3VDW	SOIC16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QL4CDT	TSSOP16	PA24TSS24D
MOTOROLA	MC68HC908QL4CDW	SOIC16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QL4MDT	TSSOP16	PA24TSS24D
MOTOROLA	MC68HC908QL4MDW	SOIC16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QL4VDT	TSSOP16	PA24TSS24D
MOTOROLA	MC68HC908QL4VDW	SOIC16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QT1CDW	SOIC8	PA20SO20D-EO-210
MOTOROLA	MC68HC908QT1CFQ	DFN8	PA8SON8D(6x5)
MOTOROLA	MC68HC908QT1CP	DIP8	
MOTOROLA	MC68HC908QT2CDW	SOIC8	PA20SO20D-EO-210
MOTOROLA	MC68HC908QT2CFQ	DFN8	PA8SON8D(6x5)
MOTOROLA	MC68HC908QT2CP	DIP8	
MOTOROLA	MC68HC908QT4CDW	SOIC8	PA20SO20D-EO-210
MOTOROLA	MC68HC908QT4CFQ	DFN8	PA8SON8D(6x5)
MOTOROLA	MC68HC908QT4CP	DIP8	
MOTOROLA	MC68HC908QY1CDT	TSSOP16	PA24TSS24D
MOTOROLA	MC68HC908QY1CDW	SOIC16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QY1CP	DIP16	

MOTOROLA	MC68HC908QY2CDT	TSSOP16	PA24TSS24D
MOTOROLA	MC68HC908QY2CDW	SOIC16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QY2CP	DIP16	
MOTOROLA	MC68HC908QY4CDT	TSSOP16	PA24TSS24D
MOTOROLA	MC68HC908QY4CDW	SOIC16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QY4CP	DIP16	
MOTOROLA	MC68HC908QY8CDT	TSSOP16	PA24TSS24D
MOTOROLA	MC68HC908QY8CDW	SOIC16	PA28SO28D-EO-300
MOTOROLA	MC68HC908QY8CP	DIP16	
MOTOROLA	MC68HCP11A1P	DIP48	
MOTOROLA	MC68S711E9CFN2	PLCC52	PA52-48A-1/HA52PL48DB
MOTOROLA	MC9S08AC8	TQFP32	PA32TQ32D
MOTOROLA	MC9S08AW16	TQFP44	PA44QF44D
MOTOROLA	MC9S08DV32	TQFP32	PA32TQ32D
MOTOROLA	MC9S08GT16ACFB	QFP44	PA44QF44D
MOTOROLA	MC9S08GT16CFB	QFP44	PA44QF44D
MOTOROLA	MC9S08GT32ACFB	QFP44	PA44QF44D
MOTOROLA	MC9S08GT32CFB	QFP44	PA44QF44D
MOTOROLA	MC9S08GT8ACFB	QFP44	PA44QF44D
MOTOROLA	MCM2716	DIP24	
MOTOROLA	MCM2814	DIP8	
MOTOROLA	MCM68764	DIP24	
MOTOROLA	MCM68766	DIP24	
MOTOROLA	XC68HC705JP7	DIP28	
NATIONAL	COP8SAA716	DIP16	
NATIONAL	COP8SAA720	DIP20	
NATIONAL	COP8SAA728	DIP28	
NATIONAL	COP8SAB720	DIP20	
NATIONAL	COP8SAB728	DIP28	
NATIONAL	COP8SAC720	DIP20	
NATIONAL	COP8SAC728	DIP28	
NATIONAL	COP8SAC740	DIP40	
NATIONAL	COP8SAC744	PLCC44	PA44-48U
NATIONAL	COP8SGE720	DIP20	
NATIONAL	COP8SGE728	DIP28	
NATIONAL	COP8SGE740	DIP40	
NATIONAL	COP8SGE744	PLCC44	PA44-48U
NATIONAL	COP8SGR720	DIP20	
NATIONAL	COP8SGR728	DIP28	
NATIONAL	COP8SGR740	DIP40	
NATIONAL	COP8SGR744	PLCC44	PA44-48U
NATIONAL	GAL16V8	DIP20	
NATIONAL	GAL16V8	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8A	DIP20	
NATIONAL	GAL16V8A	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas10H8	DIP20	
NATIONAL	GAL16V8Aas10H8	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas10L8	DIP20	
NATIONAL	GAL16V8Aas10L8	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas10P8	DIP20	
NATIONAL	GAL16V8Aas10P8	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas12H6	DIP20	
NATIONAL	GAL16V8Aas12H6	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas12L6	DIP20	
NATIONAL	GAL16V8Aas12L6	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas12P6	DIP20	
NATIONAL	GAL16V8Aas12P6	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas14H4	DIP20	
NATIONAL	GAL16V8Aas14H4	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas14L4	DIP20	
NATIONAL	GAL16V8Aas14L4	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas14P4	DIP20	
NATIONAL	GAL16V8Aas14P4	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16H2	DIP20	
NATIONAL	GAL16V8Aas16H2	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16H8	DIP20	
NATIONAL	GAL16V8Aas16H8	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16L2	DIP20	
NATIONAL	GAL16V8Aas16L2	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16L8	DIP20	
NATIONAL	GAL16V8Aas16L8	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16P2	DIP20	
NATIONAL	GAL16V8Aas16P2	PLCC20	PA20LC20D[Dead Bug]

NATIONAL	GAL16V8Aas16P8	DIP20	
NATIONAL	GAL16V8Aas16P8	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16R4	DIP20	
NATIONAL	GAL16V8Aas16R4	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16R6	DIP20	
NATIONAL	GAL16V8Aas16R6	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16R8	DIP20	
NATIONAL	GAL16V8Aas16R8	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16RP4	DIP20	
NATIONAL	GAL16V8Aas16RP4	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16RP6	DIP20	
NATIONAL	GAL16V8Aas16RP6	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8Aas16RP8	DIP20	
NATIONAL	GAL16V8Aas16RP8	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as10H8	DIP20	
NATIONAL	GAL16V8as10H8	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as10L8	DIP20	
NATIONAL	GAL16V8as10L8	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as10P8	DIP20	
NATIONAL	GAL16V8as10P8	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as12H6	DIP20	
NATIONAL	GAL16V8as12H6	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as12L6	DIP20	
NATIONAL	GAL16V8as12L6	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as12P6	DIP20	
NATIONAL	GAL16V8as12P6	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as14H4	DIP20	
NATIONAL	GAL16V8as14H4	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as14L4	DIP20	
NATIONAL	GAL16V8as14L4	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as14P4	DIP20	
NATIONAL	GAL16V8as14P4	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16H2	DIP20	
NATIONAL	GAL16V8as16H2	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16H8	DIP20	
NATIONAL	GAL16V8as16H8	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16L2	DIP20	
NATIONAL	GAL16V8as16L2	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16L8	DIP20	
NATIONAL	GAL16V8as16L8	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16P2	DIP20	
NATIONAL	GAL16V8as16P2	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16P8	DIP20	
NATIONAL	GAL16V8as16P8	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16R4	DIP20	
NATIONAL	GAL16V8as16R4	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16R6	DIP20	
NATIONAL	GAL16V8as16R6	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16R8	DIP20	
NATIONAL	GAL16V8as16R8	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16RP4	DIP20	
NATIONAL	GAL16V8as16RP4	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16RP6	DIP20	
NATIONAL	GAL16V8as16RP6	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8as16RP8	DIP20	
NATIONAL	GAL16V8as16RP8	PLCC20	PA20LC20D[Dead Bug]
NATIONAL	GAL16V8QS	DIP20	
NATIONAL	GAL20RA10	DIP24	
NATIONAL	GAL20RA10	PLCC28	PA28PL28D
NATIONAL	GAL20V8	DIP24	
NATIONAL	GAL20V8	PLCC28	PA28PL28D
NATIONAL	GAL20V8A	DIP24	
NATIONAL	GAL20V8A	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas14H8	DIP24	
NATIONAL	GAL20V8Aas14H8	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas14L8	DIP24	
NATIONAL	GAL20V8Aas14L8	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas14P8	DIP24	
NATIONAL	GAL20V8Aas14P8	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas16H6	DIP24	
NATIONAL	GAL20V8Aas16H6	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas16L6	DIP24	
NATIONAL	GAL20V8Aas16L6	PLCC28	PA28PL28D

NATIONAL	GAL20V8Aas16P6	DIP24	
NATIONAL	GAL20V8Aas16P6	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas18H4	DIP24	
NATIONAL	GAL20V8Aas18H4	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas18L4	DIP24	
NATIONAL	GAL20V8Aas18L4	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas18P4	DIP24	
NATIONAL	GAL20V8Aas18P4	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas20H2	DIP24	
NATIONAL	GAL20V8Aas20H2	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas20H8	DIP24	
NATIONAL	GAL20V8Aas20H8	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas20L2	DIP24	
NATIONAL	GAL20V8Aas20L2	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas20L8	DIP24	
NATIONAL	GAL20V8Aas20L8	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas20P2	DIP24	
NATIONAL	GAL20V8Aas20P2	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas20P8	DIP24	
NATIONAL	GAL20V8Aas20P8	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas20R4	DIP24	
NATIONAL	GAL20V8Aas20R4	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas20R6	DIP24	
NATIONAL	GAL20V8Aas20R6	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas20R8	DIP24	
NATIONAL	GAL20V8Aas20R8	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas20RP4	DIP24	
NATIONAL	GAL20V8Aas20RP4	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas20RP6	DIP24	
NATIONAL	GAL20V8Aas20RP6	PLCC28	PA28PL28D
NATIONAL	GAL20V8Aas20RP8	DIP24	
NATIONAL	GAL20V8Aas20RP8	PLCC28	PA28PL28D
NATIONAL	GAL20V8as14H8	DIP24	
NATIONAL	GAL20V8as14H8	PLCC28	PA28PL28D
NATIONAL	GAL20V8as14L8	DIP24	
NATIONAL	GAL20V8as14L8	PLCC28	PA28PL28D
NATIONAL	GAL20V8as14P8	DIP24	
NATIONAL	GAL20V8as14P8	PLCC28	PA28PL28D
NATIONAL	GAL20V8as16H6	DIP24	
NATIONAL	GAL20V8as16H6	PLCC28	PA28PL28D
NATIONAL	GAL20V8as16L6	DIP24	
NATIONAL	GAL20V8as16L6	PLCC28	PA28PL28D
NATIONAL	GAL20V8as16P6	DIP24	
NATIONAL	GAL20V8as16P6	PLCC28	PA28PL28D
NATIONAL	GAL20V8as18H4	DIP24	
NATIONAL	GAL20V8as18H4	PLCC28	PA28PL28D
NATIONAL	GAL20V8as18L4	DIP24	
NATIONAL	GAL20V8as18L4	PLCC28	PA28PL28D
NATIONAL	GAL20V8as18P4	DIP24	
NATIONAL	GAL20V8as18P4	PLCC28	PA28PL28D
NATIONAL	GAL20V8as20H2	DIP24	
NATIONAL	GAL20V8as20H2	PLCC28	PA28PL28D
NATIONAL	GAL20V8as20H8	DIP24	
NATIONAL	GAL20V8as20H8	PLCC28	PA28PL28D
NATIONAL	GAL20V8as20L2	DIP24	
NATIONAL	GAL20V8as20L2	PLCC28	PA28PL28D
NATIONAL	GAL20V8as20L8	DIP24	
NATIONAL	GAL20V8as20L8	PLCC28	PA28PL28D
NATIONAL	GAL20V8as20P2	DIP24	
NATIONAL	GAL20V8as20P2	PLCC28	PA28PL28D
NATIONAL	GAL20V8as20P8	DIP24	
NATIONAL	GAL20V8as20P8	PLCC28	PA28PL28D
NATIONAL	GAL20V8as20R4	DIP24	
NATIONAL	GAL20V8as20R4	PLCC28	PA28PL28D
NATIONAL	GAL20V8as20R6	DIP24	
NATIONAL	GAL20V8as20R6	PLCC28	PA28PL28D
NATIONAL	GAL20V8as20R8	DIP24	
NATIONAL	GAL20V8as20R8	PLCC28	PA28PL28D
NATIONAL	GAL20V8as20RP4	DIP24	
NATIONAL	GAL20V8as20RP4	PLCC28	PA28PL28D
NATIONAL	GAL20V8as20RP6	DIP24	
NATIONAL	GAL20V8as20RP6	PLCC28	PA28PL28D
NATIONAL	GAL20V8as20RP8	DIP24	

NATIONAL	GAL20V8as20RP8	PLCC28	PA28PL28D
NATIONAL	GAL22V10	DIP24	
NATIONAL	GAL22V10	PLCC28	PA28PL28D
NATIONAL	GAL6001	DIP24	
NATIONAL	GAL6001	PLCC28	PA28PL28D
NATIONAL	MM2716	DIP24	
NATIONAL	MM2716E	DIP24	
NATIONAL	MM2716Q	DIP24	
NATIONAL	NM24C02	DIP8	
NATIONAL	NM24C04	DIP8	
NATIONAL	NM24C08	DIP8	
NATIONAL	NM24C16	DIP8	
NATIONAL	NM27C010	DIP32	
NATIONAL	NM27C010	PLCC32	PA32PL32D
NATIONAL	NM27C010	TSOP32	PA32TS20/PA32TS32D-20
NATIONAL	NM27C020	DIP32	
NATIONAL	NM27C020	PLCC32	PA32PL32D
NATIONAL	NM27C020	TSOP32	PA32TS20/PA32TS32D-20
NATIONAL	NM27C040	DIP32	
NATIONAL	NM27C040	PLCC32	PA32PL32D
NATIONAL	NM27C040Q	DIP32	
NATIONAL	NM27C040Q	PLCC32	PA32PL32D
NATIONAL	NM27C128	DIP28	
NATIONAL	NM27C128	PLCC32	PA32PL28D-YA
NATIONAL	NM27C240Q	DIP40	
NATIONAL	NM27C240Q	PLCC44	PA44-48U
NATIONAL	NM27C256	DIP28	
NATIONAL	NM27C256	PLCC32	PA32PL28D-YA
NATIONAL	NM27C512	DIP28	
NATIONAL	NM27C512	PLCC32	PA32PL28D-YA
NATIONAL	NM27C64	DIP28	
NATIONAL	NM27LC256	DIP28	
NATIONAL	NM27LC256	PLCC32	PA32PL28D-YA
NATIONAL	NM27LC512	DIP28	
NATIONAL	NM27LC512	PLCC32	PA32PL28D-YA
NATIONAL	NM27LV010	DIP32	
NATIONAL	NM27LV010	PLCC32	PA32PL32D
NATIONAL	NM27LV010	TSOP32	PA32TS20/PA32TS32D-20
NATIONAL	NM27LV010B	DIP32	
NATIONAL	NM27LV010B	PLCC32	PA32PL32D
NATIONAL	NM27LV010B	TSOP32	PA32TS20/PA32TS32D-20
NATIONAL	NM27LV512	DIP28	
NATIONAL	NM27LV512	PLCC32	PA32PL28D-YA
NATIONAL	NM27P040	DIP32	
NATIONAL	NM27P040	PLCC32	PA32PL32D
NATIONAL	NM27P512	DIP28	
NATIONAL	NM27P512	PLCC32	PA32PL28D-YA
NATIONAL	NMC2732	DIP24	
NATIONAL	NMC27C010	DIP32	
NATIONAL	NMC27C010	PLCC32	PA32PL32D
NATIONAL	NMC27C020	DIP32	
NATIONAL	NMC27C020	PLCC32	PA32PL32D
NATIONAL	NMC27C020	TSOP32	PA32TS20/PA32TS32D-20
NATIONAL	NMC27C1024	DIP40	
NATIONAL	NMC27C1024	PLCC44	PA44-48U
NATIONAL	NMC27C128B	DIP28	
NATIONAL	NMC27C128BN	DIP28	
NATIONAL	NMC27C128BQ	DIP28	
NATIONAL	NMC27C128C	DIP28	
NATIONAL	NMC27C128CQ	DIP28	
NATIONAL	NMC27C128Q	DIP28	
NATIONAL	NMC27C16	DIP24	
NATIONAL	NMC27C16B	DIP24	
NATIONAL	NMC27C16BQ	DIP24	
NATIONAL	NMC27C16H	DIP24	
NATIONAL	NMC27C16HQ	DIP24	
NATIONAL	NMC27C16Q	DIP24	
NATIONAL	NMC27C2048	DIP40	
NATIONAL	NMC27C2048	PLCC44	PA44-48U
NATIONAL	NMC27C256	DIP28	
NATIONAL	NMC27C256	PLCC32	PA32PL28D-YA
NATIONAL	NMC27C256B	DIP28	
NATIONAL	NMC27C256B	PLCC32	PA32PL28D-YA

NATIONAL	NMC27C256BN	DIP28	
NATIONAL	NMC27C256C	DIP28	
NATIONAL	NMC27C256Q	DIP28	
NATIONAL	NMC27C32	DIP24	
NATIONAL	NMC27C32B	DIP24	
NATIONAL	NMC27C32E	DIP24	
NATIONAL	NMC27C32EH	DIP24	
NATIONAL	NMC27C32H	DIP24	
NATIONAL	NMC27C32Q	DIP24	
NATIONAL	NMC27C512	DIP28	
NATIONAL	NMC27C512	PLCC32	PA32PL28D-YA
NATIONAL	NMC27C512A	DIP28	
NATIONAL	NMC27C512A	PLCC32	PA32PL28D-YA
NATIONAL	NMC27C512AN	DIP28	
NATIONAL	NMC27C512AN	PLCC32	PA32PL28D-YA
NATIONAL	NMC27C64	DIP28	
NATIONAL	NMC27C64B	DIP28	
NATIONAL	NMC27C64BN	DIP28	
NATIONAL	NMC27C64N	DIP28	
NATIONAL	NMC27C64Q	DIP28	
NATIONAL	NMC27CP128	DIP28	
NATIONAL	NMC9306	DIP8	
NATIONAL	NMC9307	DIP8	
NATIONAL	NMC9313B	DIP8	
NATIONAL	NMC9314B	DIP8	
NATIONAL	NMC9346	DIP8	
NATIONAL	NMC93C06	DIP8	
NATIONAL	NMC93C06	SOIC8	PA16SO16D-EO-150
NATIONAL	NMC93C06	TSSOP8	PA8TSS-OT
NATIONAL	NMC93C13	DIP8	
NATIONAL	NMC93C13	SOIC8	PA16SO16D-EO-150
NATIONAL	NMC93C14	DIP8	
NATIONAL	NMC93C14	SOIC8	PA16SO16D-EO-150
NATIONAL	NMC93C46	DIP8	
NATIONAL	NMC93C46	DIP8	
NATIONAL	NMC93C46	SOIC8	PA16SO16D-EO-150
NATIONAL	NMC93C46	TSSOP8	PA8TSS-OT
NATIONAL	NMC93C56	DIP8	
NATIONAL	NMC93C56	SOIC8	PA16SO16D-EO-150
NATIONAL	NMC93C56	TSSOP8	PA8TSS-OT
NATIONAL	NMC93C66	DIP8	
NATIONAL	NMC93C66	SOIC8	PA16SO16D-EO-150
NATIONAL	NMC93C66	TSSOP8	PA8TSS-OT
NATIONAL	NMC93C86	DIP8	
NATIONAL	NMC93C86	SOIC8	PA16SO16D-EO-150
NATIONAL	NMC93C86	TSSOP8	PA8TSS-OT
NATIONAL	NMC93CS06	DIP8	
NATIONAL	NMC93CS06	SOIC8	PA16SO16D-EO-150
NATIONAL	NMC93CS06	TSSOP8	PA8TSS-OT
NATIONAL	NMC93CS46	DIP8	
NATIONAL	NMC93CS46	SOIC8	PA16SO16D-EO-150
NATIONAL	NMC93CS46	TSSOP8	PA8TSS-OT
NATIONAL	NMC93CS56	DIP8	
NATIONAL	NMC93CS56	SOIC8	PA16SO16D-EO-150
NATIONAL	NMC93CS56	TSSOP8	PA8TSS-OT
NATIONAL	NMC93CS66	DIP8	
NATIONAL	NMC93CS66	SOIC8	PA16SO16D-EO-150
NATIONAL	NMC93CS66	TSSOP8	PA8TSS-OT
NEC	8749H	DIP40	
NEC	uPD27128	DIP28	
NEC	uPD2716	DIP24	
NEC	uPD27256	DIP28	
NEC	uPD2732	DIP24	
NEC	uPD2732A	DIP24	
NEC	uPD2764	DIP28	
NEC	uPD27C1000	DIP32	
NEC	uPD27C1000A	DIP32	
NEC	uPD27C1001A	DIP32	
NEC	uPD27C1001A	SOP32	PA32SO32D-EO-450
NEC	uPD27C1001D	DIP32	
NEC	uPD27C1024	DIP40	
NEC	uPD27C1024	PLCC44	PA44-48U
NEC	uPD27C1024A	DIP40	



NEC	uPD27C1024A	PLCC44	PA44-48U
NEC	uPD27C2001	DIP32	
NEC	uPD27C2001	PLCC32	PA32PL32D
NEC	uPD27C2001	SOP32	PA32SO32D-EO-450
NEC	uPD27C256	DIP28	
NEC	uPD27C256A	DIP28	
NEC	uPD27C256A	SOIC28	PA28SO28D-EO-300
NEC	uPD27C4001	DIP32	
NEC	uPD27C4096	DIP40	
NEC	uPD27C4096	PLCC44	PA44-48U
NEC	uPD27C512	DIP28	
NEC	uPD27C512	PLCC32	PA32PL28D-YA
NEC	uPD27C64	DIP28	
NEC	uPD27C8000	DIP42	
NEC	uPD27C8001	DIP32	
NEC	uPD28C64	DIP28	
NEC	uPD28C64	SOIC28	PA28SO28D-EO-300
NEC	uPD28C64C	DIP28	
NEC	uPD28C64C	SOIC28	PA28SO28D-EO-300
NEC	uPD78F0546	LQFP80	PA80QF48DC
NEC	uPD78F9234	SSOP30	PA30SS30D
NEC	uPD78P054GK	QFP80	PA80QF48DD
NEXFLASH	NX29F010	DIP32	
NEXFLASH	NX29F010	PLCC32	PA32PL32D
NEXFLASH	NX29F010	TSOP32	PA32TS20/PA32TS32D-20
NOVATEK MICROELECTRON	ICS NT68F631L	PLCC44	HA44PL48DZ4
NOVATEK MICROELECTRON	ICS NT68F632L	PLCC44	HA44PL48DZ4
NOVATEK MICROELECTRON	ICS NT68F63LA	PLCC44	HA44PL48DZ4
NOVATEK MICROELECTRON	ICS NT68F63LG	PLCC44	HA44PL48DZ4
NTE	2732A	DIP24	
NTE	NTE2716	DIP24	
NUMONYX	JS28F128M29EWH	TSOP56	PA56TS48DD
NUMONYX	JS28F128M29EWL	TSOP56	PA56TS48DD
NUMONYX	JS28F256M29EWH	TSOP56	PA56TS48DD
NUMONYX	JS28F256M29EWL	TSOP56	PA56TS48DD
NUMONYX	JS28F256P33BF	TSOP56	HA56TS48DF
NUMONYX	JS28F256P33TF	TSOP56	HA56TS48DF
NUMONYX	JS28F512M29EWH	TSOP56	PA56TS48DD
NUMONYX	JS28F512M29EWL	TSOP56	PA56TS48DD
NUMONYX	M25P128VMF	SOP16	PA28SO28D-EO-300
NUMONYX	M29F400FT	SOP44	PA44SO44D
NUMONYX	M29F400FT	TSOP48	PA48TS48D
NUMONYX	M29W256GL-ZA	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
NUMONYX	M29W256GL-ZS	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
NUMONYX	N25Q032Ax1E	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q032Ax1E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
NUMONYX	N25Q032Ax1E	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q032Ax1E	TFBGA24	PA24BG24D(6x8mm)5x5
NUMONYX	N25Q032Ax1E	USON8	PA8SON8D(4x3)
NUMONYX	N25Q032Ax1E	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q032Ax1E	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q032Ax1E(Quad_IO)	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q032Ax1E(Quad_IO)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
NUMONYX	N25Q032Ax1E(Quad_IO)	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q032Ax1E(Quad_IO)	TFBGA24	PA24BG24D(6x8mm)5x5
NUMONYX	N25Q032Ax1E(Quad_IO)	USON8	PA8SON8D(4x3)
NUMONYX	N25Q032Ax1E(Quad_IO)	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q032Ax1E(Quad_IO)	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q032Ax3E	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q032Ax3E	SOP8	PA16SO16D-EO-150/PA8SO8D-150
NUMONYX	N25Q032Ax3E	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q032Ax3E	TFBGA24	PA24BG24D(6x8mm)5x5
NUMONYX	N25Q032Ax3E	USON8	PA8SON8D(4x3)
NUMONYX	N25Q032Ax3E	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q032Ax3E	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q032Ax3E(Quad_IO)	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q032Ax3E(Quad_IO)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
NUMONYX	N25Q032Ax3E(Quad_IO)	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q032Ax3E(Quad_IO)	TFBGA24	PA24BG24D(6x8mm)5x5
NUMONYX	N25Q032Ax3E(Quad_IO)	USON8	PA8SON8D(4x3)
NUMONYX	N25Q032Ax3E(Quad_IO)	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q032Ax3E(Quad_IO)	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q032Ax3E(Quad_IO)	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q064Ax1E	SOP16	PA28SO28D-EO-300

NUMONYX	N25Q064Ax1E	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q064Ax1E	TFBGA24	PA24BG24D(6x8mm)5x5
NUMONYX	N25Q064Ax1E	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q064Ax1E	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q064Ax1E(Quad_IO)	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q064Ax1E(Quad_IO)	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q064Ax1E(Quad_IO)	TFBGA24	PA24BG24D(6x8mm)5x5
NUMONYX	N25Q064Ax1E(Quad_IO)	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q064Ax1E(Quad_IO)	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q064Ax3E	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q064Ax3E	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q064Ax3E	TFBGA24	PA24BG24D(6x8mm)5x5
NUMONYX	N25Q064Ax3E	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q064Ax3E	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q064Ax3E(Quad_IO)	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q064Ax3E(Quad_IO)	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q064Ax3E(Quad_IO)	TFBGA24	PA24BG24D(6x8mm)5x5
NUMONYX	N25Q064Ax3E(Quad_IO)	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q064Ax3E(Quad_IO)	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q128Ax1B	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q128Ax1B	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q128Ax1B	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q128Ax1B	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q128Ax1B(Quad_IO)	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q128Ax1B(Quad_IO)	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q128Ax1B(Quad_IO)	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q128Ax1B(Quad_IO)	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q128Ax1E	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q128Ax1E	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q128Ax1E	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q128Ax1E	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q128Ax1E(Quad_IO)	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q128Ax1E(Quad_IO)	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q128Ax1E(Quad_IO)	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q128Ax1E(Quad_IO)	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q128Ax1E(Quad_IO)	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q128Ax1T	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q128Ax1T	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q128Ax1T	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q128Ax1T	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q128Ax1T(Quad_IO)	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q128Ax1T(Quad_IO)	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q128Ax1T(Quad_IO)	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q128Ax1T(Quad_IO)	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q128Ax3B	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q128Ax3B	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q128Ax3B	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q128Ax3B	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q128Ax3B(Quad_IO)	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q128Ax3B(Quad_IO)	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q128Ax3B(Quad_IO)	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q128Ax3B(Quad_IO)	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q128Ax3E	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q128Ax3E	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q128Ax3E	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q128Ax3E	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q128Ax3E(Quad_IO)	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q128Ax3E(Quad_IO)	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q128Ax3E(Quad_IO)	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q128Ax3E(Quad_IO)	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q128Ax3T	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q128Ax3T	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q128Ax3T	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q128Ax3T	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q128Ax3T(Quad_IO)	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q128Ax3T(Quad_IO)	SOP8	PA20SO20D-EO-210
NUMONYX	N25Q128Ax3T(Quad_IO)	VDFN8	PA8SON8D(6x5)
NUMONYX	N25Q128Ax3T(Quad_IO)	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q256Ax1E	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q256Ax1E	TFBGA24	PA24BG24D(6x8mm)5x5
NUMONYX	N25Q256Ax1E	VDFN8	PA8SON8DA(8x6)
NUMONYX	N25Q256Ax3E	SOP16	PA28SO28D-EO-300
NUMONYX	N25Q256Ax3E	TFBGA24	PA24BG24D(6x8mm)5x5
NUMONYX	N25Q256Ax3E	VDFN8	PA8SON8DA(8x6)

NUMONYX	PC28F00AP30EFA	BGA64	HA64BG48DAF-SO
NUMONYX	PC28F00AP33TF	BGA64	HA64BG48DAA
NUMONYX	PC28F128P33BF	EBGA64	NA64BG48DO
NUMONYX	PC28F128P33TF	EBGA64	NA64BG48DO
NUMONYX	PC28F256M29EWH	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
NUMONYX	PC28F256M29EWL	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
NUMONYX	PC28F256P30BF	EBGA64	PA64BGA48DI/HA64BGA48DI
NUMONYX	PC28F256P30TF	EBGA64	PA64BGA48DI/HA64BGA48DI
NUMONYX	PC28F256P33BF	EBGA64	HA64BG48DM
NUMONYX	PC28F256P33TF	EBGA64	HA64BG48DM
NUMONYX	PC28F512P30TF	EBGA64	PA64BG48DAB
NUMONYX	RC28F128P30BF	EBGA64	PA64BGA48DI/HA64BGA48DI
NUMONYX	RC28F128P30TF	EBGA64	PA64BGA48DI/HA64BGA48DI
NUMONYX	RC28F128P33BF	EBGA64	NA64BG48DO
NUMONYX	RC28F128P33TF	EBGA64	NA64BG48DO
NUMONYX	RC28F256J3D	EBGA64	PA64BGA48D/HA64BGA48D
NUMONYX	RC28F256J3F	EBGA64	PA64BGA48D/HA64BGA48D
NUMONYX	RC28F256M29EWH	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
NUMONYX	RC28F256M29EWL	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
NUMONYX	RC28F256P30BF	EBGA64	PA64BGA48DI/HA64BGA48DI
NUMONYX	RC28F256P30TF	EBGA64	PA64BGA48DI/HA64BGA48DI
NUMONYX	RC28F256P33BF	EBGA64	HA64BG48DM
NUMONYX	RC28F256P33TF	EBGA64	HA64BG48DM
NUMONYX	TE28F256P33BF	TSOP56	HA56TS48DF
NUMONYX	TE28F256P33TF	TSOP56	HA56TS48DF
NUVOTON	W78E052D	DIP40	
NUVOTON	W78E052D(44PLCC)	PLCC44	PA44-48U
NUVOTON	W78E516DPG	PLCC44	PA44-48U
NXP	LPC2134	LQFP64	HA64QF48DH
NXP	LPC2134FBD	LQFP64	HA64QF48DH
NXP	MC9S08GT16ACFB	QFP44	PA44QF44D
NXP	MC9S08GT16CFB	QFP44	PA44QF44D
NXP	MC9S08GT32ACFB	QFP44	PA44QF44D
NXP	MC9S08GT32CFB	QFP44	PA44QF44D
NXP	MC9S08GT8ACFB	QFP44	PA44QF44D
NXP	P87C51SBAA	PLCC44	PA44-48U
NXP	P87C51SBPN	DIP40	
NXP	P87C52UBAA	PLCC44	PA44-48U
NXP	P87LPC778	TSSOP20	PA24TSS24D
NXP	P89C51RD2BA	PLCC44	PA44-48U
NXP	P89CV51RB2FA	PLCC44	PA44-48U
NXP	P89CV51RB2FBC	QFP44	PA44QF44D
NXP	P89CV51RC2FA	PLCC44	PA44-48U
NXP	P89CV51RC2FBC	QFP44	PA44QF44D
NXP	P89CV51RD2FA	PLCC44	PA44-48U
NXP	P89CV51RD2FBC	QFP44	PA44QF44D
NXP	P89V51RD2BN	DIP40	
NXP	P89V51RD2FA	PLCC44	PA44-48U
NXP	P89V51RD2FBC	TQFP44	PA44QF44D
NXP	P89V51RD2FN	DIP40	
NXP	P89V52X2FA	PLCC44	PA44-48U
NXP	P89V52X2FN	DIP40	
NXP	P89V660FA	PLCC44	PA44-48U
NXP	P89V660FBC	QFP44	PA44QF44D
NXP	P89V662FA	PLCC44	PA44-48U
NXP	P89V662FBC	QFP44	PA44QF44D
NXP	P89V664FA	PLCC44	PA44-48U
NXP	P89V664FBC	QFP44	PA44QF44D
OKI	MR27V1602D	DIP42	
OKI	MR27V1602D	SOP44	PA44SO44D
OKI	MR27V1602E	SOP44	PA44SO44D
OKI	MR27V1602F	DIP42	
OKI	MR27V1602F	SOP44	PA44SO44D
OKI	MR27V1652D	DIP42	
OKI	MR27V1652D	SOP44	PA44SO44D
OKI	MR27V1652E	DIP42	
OKI	MR27V1652E	SOP44	PA44SO44D
OKI	MR27V3202D	SOP44	PA44SO44D
OKI	MR27V3202D	TSOP48	PA48TS48D
OKI	MR27V3202E	SOP44	PA44SO44D
OKI	MR27V3202E	TSOP44	PA44TS44D
OKI	MR27V3202F	SOP44	PA44SO44D
OKI	MR27V3202F	TSOP48	PA48TS48D

OKI	MR27V3252D	SOP44	PA44SO44D
OKI	MR27V3252D	TSOP48	PA48TS48D
OKI	MR27V401D	DIP32	
OKI	MR27V401D	SOP32	PA32SO32D-EO-450
OKI	MR27V401D	TSOP32	PA32TS20/PA32TS32D-20
OKI	MR27V402D	DIP40	
OKI	MR27V402D	SOP40	PA40SO40D-EO-450
OKI	MR27V402D	TSOP44	PA44TS44D
OKI	MR27V402E	DIP40	
OKI	MR27V402E	SOP40	PA40SO40D-EO-450
OKI	MR27V402E	TSOP44	PA44TS44D
OKI	MR27V452D	DIP40	
OKI	MR27V452D	SOP40	PA40SO40D-EO-450
OKI	MR27V452D	TSOP44	PA44TS44D
OKI	MR27V6402D	SOP44	PA44SO44D
OKI	MR27V6402G	SOP44	PA44SO44D
OKI	MR27V6466F	TSOP86	PA6466R
OKI	MR27V801D	DIP32	
OKI	MR27V801D	PLCC32	PA32PL32D
OKI	MR27V801D	SOP32	PA32SO32D-EO-450
OKI	MR27V801D	TSOP32	PA32TS20/PA32TS32D-20
OKI	MR27V802D	DIP42	
OKI	MR27V802D	SOP44	PA44SO44D
OKI	MR27V802D	TSOP44	PA44TS44D
OKI	MR27V802F	SOP44	PA44SO44D
OKI	MR27V852D	DIP42	
OKI	MR27V852D	SOP44	PA44SO44D
OKI	MR27V852D	TSOP44	PA44TS44D
OKI	MR27V852E	DIP42	
OKI	MSM271000	DIP32	
OKI	MSM271000AS	DIP32	
OKI	MSM271000ZB	DIP32	
OKI	MSM271024	DIP40	
OKI	MSM271024	PLCC44	PA44-48U
OKI	MSM271024AS	DIP40	
OKI	MSM271024AS	PLCC44	PA44-48U
OKI	MSM271024ZB	DIP40	
OKI	MSM271024ZB	PLCC44	PA44-48U
OKI	MSM27128A	DIP28	
OKI	MSM27128AS	DIP28	
OKI	MSM27128AZB-RS	DIP28	
OKI	MSM2716	DIP24	
OKI	MSM2716AS	DIP24	
OKI	MSM27256	DIP28	
OKI	MSM27256AS	DIP28	
OKI	MSM27256ZB-RS	DIP28	
OKI	MSM2732	DIP24	
OKI	MSM2732A	DIP24	
OKI	MSM27512	DIP28	
OKI	MSM27512AS	DIP28	
OKI	MSM27512ZB-RS	DIP28	
OKI	MSM2764	DIP28	
OKI	MSM2764A	DIP28	
OKI	MSM2764AS	DIP28	
OKI	MSM2764AZB	DIP28	
OKI	MSM2764RS	DIP28	
OKI	MSM27C101ZB	DIP32	
OKI	MSM27C101ZB	PLCC32	PA32PL32D
OKI	MSM27C101ZB	TSOP32	PA32TS20/PA32TS32D-20
OKI	MSM27C1024	DIP40	
OKI	MSM27C1024	PLCC44	PA44-48U
OKI	MSM27C1024AS	DIP40	
OKI	MSM27C1024AS	PLCC44	PA44-48U
OKI	MSM27C128AS	DIP28	
OKI	MSM27C1602CZ	DIP42	
OKI	MSM27C1602CZ	SOP44	PA44SO44D
OKI	MSM27C1652CZ	DIP42	
OKI	MSM27C1652CZ	SOP44	PA44SO44D
OKI	MSM27C2000	DIP32	
OKI	MSM27C2048	DIP40	
OKI	MSM27C2048	PLCC44	PA44-48U
OKI	MSM27C256	DIP28	
OKI	MSM27C256	PLCC32	PA32PL28D-YA

OKI	MSM27C256H	DIP28	
OKI	MSM27C256H	PLCC32	PA32PL28D-YA
OKI	MSM27C256HQB	DIP28	
OKI	MSM27C256HQB	PLCC32	PA32PL28D-YA
OKI	MSM27C256ZB	DIP28	
OKI	MSM27C256ZB	PLCC32	PA32PL28D-YA
OKI	MSM27C3202CZ	SOP44	PA44SO44D
OKI	MSM27C3252CZ	SOP44	PA44SO44D
OKI	MSM27C401CZ	DIP32	
OKI	MSM27C401CZ	SOP32	PA32SO32D-EO-450
OKI	MSM27C401CZ	TSOP32	PA32TS20/PA32TS32D-20
OKI	MSM27C402ZB	SOP44	PA44SO44D
OKI	MSM27C452CZ	DIP40	
OKI	MSM27C452CZ	TSOP44	PA44TS44D
OKI	MSM27C64AS	DIP28	
OKI	MSM27C802CZ	DIP42	
OKI	MSM27C802CZ	SOP44	PA44SO44D
OKI	MSM27C802CZ	TSOP44	PA44TS44D
OKI	MSM27C852CZ	DIP42	
OKI	MSM27C852CZ	SOP44	PA44SO44D
OKI	MSM27C852CZ	TSOP44	PA44TS44D
OKI	MSM2816ARS	DIP24	
ON SEMICONDUCTOR	CAT24C03WI	SOIC8	PA8SO8D-EO-150
ON SEMICONDUCTOR	CAT24C256	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ON SEMICONDUCTOR	CAT24C256	SOP8	PA20SO20D-EO-210
ON SEMICONDUCTOR	CAT24C256	TSSOP8	PA8TSS8D
ON SEMICONDUCTOR	CAT24C512-L	USON8	PA8SON8D(2x3)
ON SEMICONDUCTOR	CAT24C512-L	DIP8	
ON SEMICONDUCTOR	CAT24C512-W	SOIC8	PA16SO16D-EO-150
ON SEMICONDUCTOR	CAT24C512-X	SOIC8	PA20SO20D-EO-210
ON SEMICONDUCTOR	CAT24C512-Y	TSSOP8	PA8TSS8D
ON SEMICONDUCTOR	CAT24FC256	DIP8	
ON SEMICONDUCTOR	CAT24FC256	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ON SEMICONDUCTOR	CAT24FC256	SOP8	PA20SO20D-EO-210
ON SEMICONDUCTOR	CAT24WC256	DIP8	
ON SEMICONDUCTOR	CAT24WC256	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ON SEMICONDUCTOR	CAT24WC256	SOP8	PA20SO20D-EO-210
ON SEMICONDUCTOR	CAT25010	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ON SEMICONDUCTOR	CAT25010	TSSOP8	PA8TSS8D
ON SEMICONDUCTOR	CAT25010	USON8	PA8SON8D(2x3)
ON SEMICONDUCTOR	CAT25020	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ON SEMICONDUCTOR	CAT25020	TSSOP8	PA8TSS8D
ON SEMICONDUCTOR	CAT25020	USON8	PA8SON8D(2x3)
ON SEMICONDUCTOR	CAT25040	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ON SEMICONDUCTOR	CAT25040	TSSOP8	PA8TSS8D
ON SEMICONDUCTOR	CAT25040	USON8	PA8SON8D(2x3)
ON SEMICONDUCTOR	CAT25080	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ON SEMICONDUCTOR	CAT25080	TSSOP8	PA8TSS8D
ON SEMICONDUCTOR	CAT25080	USON8	PA8SON8D(2x3)
ON SEMICONDUCTOR	CAT25128	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ON SEMICONDUCTOR	CAT25128	SOIC8	PA20SO20D-EO-210
ON SEMICONDUCTOR	CAT25128	TSSOP8	PA8TSS8D
ON SEMICONDUCTOR	CAT25128	USON8	PA8SON8D(2x3)
ON SEMICONDUCTOR	CAT25160	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ON SEMICONDUCTOR	CAT25160	TSSOP8	PA8TSS8D
ON SEMICONDUCTOR	CAT25160	USON8	PA8SON8D(2x3)
ON SEMICONDUCTOR	CAT25160	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ON SEMICONDUCTOR	CAT25256	SOIC8	PA20SO20D-EO-210
ON SEMICONDUCTOR	CAT25256	TSSOP8	PA8TSS8D
ON SEMICONDUCTOR	CAT25256	USON8	PA8SON8D(2x3)
ON SEMICONDUCTOR	CAT25320	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ON SEMICONDUCTOR	CAT25320	TSSOP8	PA8TSS8D
ON SEMICONDUCTOR	CAT25640	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
ON SEMICONDUCTOR	CAT25640	TSSOP8	PA8TSS8D
ON SEMICONDUCTOR	CAT25640	USON8	PA8SON8D(2x3)
ON SEMICONDUCTOR	CAT34TS04	DFN8	PA8QFN8D(2x3)
PARALLAX	SX28AC/DP	DIP28	
PHILIPS	27C010	DIP32	
PHILIPS	27C010	PLCC32	PA32PL32D
PHILIPS	27C010	TSOP32	PA32TS20/PA32TS32D-20
PHILIPS	27C040	DIP32	
PHILIPS	27C210	DIP40	
PHILIPS	27C210	PLCC44	PA44-48U

PHILIPS	27C240	DIP40	
PHILIPS	27C240	PLCC44	PA44-48U
PHILIPS	27C256	DIP28	
PHILIPS	27C256	PLCC32	PA32PL28D-YA
PHILIPS	27C512	DIP28	
PHILIPS	27C512	PLCC32	PA32PL28D-YA
PHILIPS	27C64A	DIP28	
PHILIPS	27C64A	PLCC32	PA32PL28D-YA
PHILIPS	P3Z22V10	DIP24	
PHILIPS	P3Z22V10	PLCC28	PA28PL28D
PHILIPS	P5Z22V10	DIP24	
PHILIPS	P5Z22V10	PLCC28	PA28PL28D
PHILIPS	P85LPC764	PLCC44	PA44-48U
PHILIPS	P87C51	DIP40	
PHILIPS	P87C51	PLCC44	PA44-48U
PHILIPS	P87C51FA	DIP40	
PHILIPS	P87C51FA	PLCC44	PA44-48U
PHILIPS	P87C51FB	DIP40	
PHILIPS	P87C51FB	PLCC44	PA44-48U
PHILIPS	P87C51FC	DIP40	
PHILIPS	P87C51FC	PLCC44	PA44-48U
PHILIPS	P87C51MA2	PLCC44	PA44-48U
PHILIPS	P87C51MB2	PLCC44	PA44-48U
PHILIPS	P87C51MC2	PLCC44	PA44-48U
PHILIPS	P87C51RA+	DIP40	
PHILIPS	P87C51RA+	PLCC44	PA44-48U
PHILIPS	P87C51RA2BA	PLCC44	PA44-48U
PHILIPS	P87C51RA2BBD	QFP44	PA44QF44D
PHILIPS	P87C51RB+	DIP40	
PHILIPS	P87C51RB+	PLCC44	PA44-48U
PHILIPS	P87C51RB2BA	PLCC44	PA44-48U
PHILIPS	P87C51RB2BBD	QFP44	PA44QF44D
PHILIPS	P87C51RB2BN	DIP40	
PHILIPS	P87C51RC+	DIP40	
PHILIPS	P87C51RC+	PLCC44	PA44-48U
PHILIPS	P87C51RC2BA	PLCC44	PA44-48U
PHILIPS	P87C51RC2BBD	QFP44	PA44QF44D
PHILIPS	P87C51RC2BN	DIP40	
PHILIPS	P87C51RD+	DIP40	
PHILIPS	P87C51RD+	PLCC44	PA44-48U
PHILIPS	P87C51RD2BA	PLCC44	PA44-48U
PHILIPS	P87C51RD2BBD	QFP44	PA44QF44D
PHILIPS	P87C51RD2BN	DIP40	
PHILIPS	P87C51X2	DIP40	
PHILIPS	P87C51X2	PLCC44	PA44-48U
PHILIPS	P87C51XAG37	PLCC44	PA44-48U
PHILIPS	P87C51XAS37	PLCC44	PA44-48U
PHILIPS	P87C52	DIP40	
PHILIPS	P87C52	PLCC44	PA44-48U
PHILIPS	P87C52	QFP44	PA44QF44D
PHILIPS	P87C52X2	DIP40	
PHILIPS	P87C52X2	PLCC44	PA44-48U
PHILIPS	P87C54	DIP40	
PHILIPS	P87C54	PLCC44	PA44-48U
PHILIPS	P87C54X2	DIP40	
PHILIPS	P87C54X2	PLCC44	PA44-48U
PHILIPS	P87C58	DIP40	
PHILIPS	P87C58	PLCC44	PA44-48U
PHILIPS	P87C58X2	DIP40	
PHILIPS	P87C58X2	PLCC44	PA44-48U
PHILIPS	P87C591	PLCC44	PA44-48U
PHILIPS	P87C654X2BBD	QFP44	PA44QF44D
PHILIPS	P87C654X2FA	PLCC44	PA44-48U
PHILIPS	P87C660X2BBD	QFP44	PA44QF44D
PHILIPS	P87C660X2FA	PLCC44	PA44-48U
PHILIPS	P87C661X2BBD	QFP44	PA44QF44D
PHILIPS	P87C661X2FA	PLCC44	PA44-48U
PHILIPS	P87LC52X2BBD	QFP44	PA44QF44D
PHILIPS	P87LC52X2FA	PLCC44	PA44-48U
PHILIPS	P87LC54X2BBD	QFP44	PA44QF44D
PHILIPS	P87LC54X2FA	PLCC44	PA44-48U
PHILIPS	P87LPC761	DIP16	
PHILIPS	P87LPC762	DIP16	

PHILIPS	P87LPC762	DIP20	
PHILIPS	P87LPC762	DIP8	
PHILIPS	P87LPC762	SOIC20	PA28SO28D-EO-300
PHILIPS	P87LPC764	DIP16	
PHILIPS	P87LPC764	DIP20	
PHILIPS	P87LPC764	DIP8	
PHILIPS	P87LPC764	SOIC20	PA28SO28D-EO-300
PHILIPS	P87LPC767	DIP20	
PHILIPS	P87LPC767	SOIC20	PA28SO28D-EO-300
PHILIPS	P87LPC768	DIP20	
PHILIPS	P87LPC768	SOIC20	PA28SO28D-EO-300
PHILIPS	P87LPC769	DIP20	
PHILIPS	P87LPC769	SOIC20	PA28SO28D-EO-300
PHILIPS	P87LPC778	TSSOP20	PA24TSS24D
PHILIPS	P89C51B	DIP40	
PHILIPS	P89C51B	PLCC44	PA44-48U
PHILIPS	P89C51RA+	DIP40	
PHILIPS	P89C51RA+	PLCC44	PA44-48U
PHILIPS	P89C51RA2BA	PLCC44	PA44-48U
PHILIPS	P89C51RA2BB	QFP44	PA44QF44D
PHILIPS	P89C51RA2BN	DIP40	
PHILIPS	P89C51RB+	DIP40	
PHILIPS	P89C51RB+	PLCC44	PA44-48U
PHILIPS	P89C51RB2BA	PLCC44	PA44-48U
PHILIPS	P89C51RB2BB	QFP44	PA44QF44D
PHILIPS	P89C51RB2BN	DIP40	
PHILIPS	P89C51RB2H	DIP40	
PHILIPS	P89C51RB2H	PLCC44	PA44-48U
PHILIPS	P89C51RC+	DIP40	
PHILIPS	P89C51RC+	PLCC44	PA44-48U
PHILIPS	P89C51RC2BA	PLCC44	PA44-48U
PHILIPS	P89C51RC2BB	QFP44	PA44QF44D
PHILIPS	P89C51RC2BN	DIP40	
PHILIPS	P89C51RC2FA	PLCC44	PA44-48U
PHILIPS	P89C51RC2FB	QFP44	PA44QF44D
PHILIPS	P89C51RC2H	DIP40	
PHILIPS	P89C51RC2H	PLCC44	PA44-48U
PHILIPS	P89C51RD+	DIP40	
PHILIPS	P89C51RD+	PLCC44	PA44-48U
PHILIPS	P89C51RD2BA	PLCC44	PA44-48U
PHILIPS	P89C51RD2BB	QFP44	PA44QF44D
PHILIPS	P89C51RD2BN	DIP40	
PHILIPS	P89C51RD2FA	PLCC44	PA44-48U
PHILIPS	P89C51RD2H	DIP40	
PHILIPS	P89C51RD2H	PLCC44	PA44-48U
PHILIPS	P89C51U	DIP40	
PHILIPS	P89C51U	PLCC44	PA44-48U
PHILIPS	P89C51X2BA	PLCC44	PA44-48U
PHILIPS	P89C51X2BBD	QFP44	PA44QF44D
PHILIPS	P89C51X2BN	DIP40	
PHILIPS	P89C51X2FA	PLCC44	PA44-48U
PHILIPS	P89C51XAG49	PLCC44	PA44-48U
PHILIPS	P89C52B	DIP40	
PHILIPS	P89C52B	PLCC44	PA44-48U
PHILIPS	P89C52U	DIP40	
PHILIPS	P89C52U	PLCC44	PA44-48U
PHILIPS	P89C52X2BA	PLCC44	PA44-48U
PHILIPS	P89C52X2BBD	QFP44	PA44QF44D
PHILIPS	P89C52X2BN	DIP40	
PHILIPS	P89C52X2FA	PLCC44	PA44-48U
PHILIPS	P89C52X2FBD	QFP44	PA44QF44D
PHILIPS	P89C52X2FN	DIP40	
PHILIPS	P89C54B	DIP40	
PHILIPS	P89C54B	PLCC44	PA44-48U
PHILIPS	P89C54U	DIP40	
PHILIPS	P89C54U	PLCC44	PA44-48U
PHILIPS	P89C54X2BA	PLCC44	PA44-48U
PHILIPS	P89C54X2BBD	QFP44	PA44QF44D
PHILIPS	P89C54X2BN	DIP40	
PHILIPS	P89C54X2FA	PLCC44	PA44-48U
PHILIPS	P89C58B	DIP40	
PHILIPS	P89C58B	PLCC44	PA44-48U
PHILIPS	P89C58U	DIP40	

PHILIPS	P89C58U	PLCC44	PA44-48U
PHILIPS	P89C58X2BA	PLCC44	PA44-48U
PHILIPS	P89C58X2BBD	QFP44	PA44QF44D
PHILIPS	P89C58X2BN	DIP40	
PHILIPS	P89C58X2FA	PLCC44	PA44-48U
PHILIPS	P89C60X2BA	PLCC44	PA44-48U
PHILIPS	P89C61X2BA	QFP44	PA44QF44D
PHILIPS	P89C61X2BN	DIP40	
PHILIPS	P89C660	DIP40	
PHILIPS	P89C660	PLCC44	PA44-48U
PHILIPS	P89C662	DIP40	
PHILIPS	P89C662	PLCC44	PA44-48U
PHILIPS	P89C664	DIP40	
PHILIPS	P89C664	PLCC44	PA44-48U
PHILIPS	P89C668	DIP40	
PHILIPS	P89C668	PLCC44	PA44-48U
PHILIPS	P89C669BBD	QFP44	PA44QF44D
PHILIPS	P89C669FA	PLCC44	PA44-48U
PHILIPS	P89CV51RB2FA	PLCC44	PA44-48U
PHILIPS	P89CV51RB2FBC	QFP44	PA44QF44D
PHILIPS	P89CV51RC2FA	PLCC44	PA44-48U
PHILIPS	P89CV51RC2FBC	QFP44	PA44QF44D
PHILIPS	P89CV51RD2FA	PLCC44	PA44-48U
PHILIPS	P89CV51RD2FBC	QFP44	PA44QF44D
PHILIPS	P89LPC901FD(ICP)	SOP8	PA16SO16D-EO-150
PHILIPS	P89LPC901FN(ICP)	DIP8	
PHILIPS	P89LPC902FD(ICP)	SOP8	PA16SO16D-EO-150
PHILIPS	P89LPC902FN(ICP)	DIP8	
PHILIPS	P89LPC903FD(ICP)	DIP8	
PHILIPS	P89LPC903FD(ICP)	SOP8	PA16SO16D-EO-150
PHILIPS	P89LPC904FD(ICP)	SOP8	PA16SO16D-EO-150
PHILIPS	P89LPC904FN(ICP)	DIP8	
PHILIPS	P89LPC906FD(ICP)	SOP8	PA16SO16D-EO-150
PHILIPS	P89LPC907FD(ICP)	SOP8	PA16SO16D-EO-150
PHILIPS	P89LPC908FD(ICP)	SOP8	PA16SO16D-EO-150
PHILIPS	P89LPC9102FTK(ICP)	CASON10	PA10SON10D
PHILIPS	P89LPC9103FTK(ICP)	CASON10	PA10SON10D
PHILIPS	P89LPC9107FDH(ICP)	TSSOP14	PA28TSS28D-EO
PHILIPS	P89LPC9107FN(ICP)	DIP14	
PHILIPS	P89LPC912FD(ICP)	TSSOP14	PA28TSS28D-EO
PHILIPS	P89LPC913FD(ICP)	TSSOP14	PA28TSS28D-EO
PHILIPS	P89LPC914FD(ICP)	TSSOP14	PA28TSS28D-EO
PHILIPS	P89LPC915FD(ICP)	TSSOP14	PA28TSS28D-EO
PHILIPS	P89LPC916FD(ICP)	TSSOP16	PA28TSS28D-EO
PHILIPS	P89LPC917FD(ICP)	TSSOP16	PA28TSS28D-EO
PHILIPS	P89LPC920FD	TSSOP20	PA28TSS28D-EO
PHILIPS	P89LPC920FD(ICP)	TSSOP20	PA28TSS28D-EO
PHILIPS	P89LPC921FD	TSSOP20	PA28TSS28D-EO
PHILIPS	P89LPC921FD(ICP)	TSSOP20	PA28TSS28D-EO
PHILIPS	P89LPC9221FD(ICP)	TSSOP20	PA28TSS28D-EO
PHILIPS	P89LPC9221FN(ICP)	DIP20	
PHILIPS	P89LPC922FD	TSSOP20	PA28TSS28D-EO
PHILIPS	P89LPC922FD(ICP)	TSSOP20	PA28TSS28D-EO
PHILIPS	P89LPC922FN	DIP20	
PHILIPS	P89LPC922FN(ICP)	DIP20	
PHILIPS	P89LPC924FD	TSSOP20	PA28TSS28D-EO
PHILIPS	P89LPC924FD(ICP)	TSSOP20	PA28TSS28D-EO
PHILIPS	P89LPC925FD	TSSOP20	PA28TSS28D-EO
PHILIPS	P89LPC925FD(ICP)	TSSOP20	PA28TSS28D-EO
PHILIPS	P89LPC925FN	DIP20	
PHILIPS	P89LPC925FN(ICP)	DIP20	
PHILIPS	P89LPC930FD	TSSOP28	PA28TSS28D-EO
PHILIPS	P89LPC930FD(ICP)	TSSOP28	PA28TSS28D-EO
PHILIPS	P89LPC931FD	TSSOP28	PA28TSS28D-EO
PHILIPS	P89LPC931FD(ICP)	TSSOP28	PA28TSS28D-EO
PHILIPS	P89LPC932A1FA	PLCC28	PA28PL28D
PHILIPS	P89LPC932A1FDH	TSSOP28	PA28TSS28D-EO
PHILIPS	P89LPC932A1FHN	QFN28	PA28QFN28D(6x6)
PHILIPS	P89LPC932BA	PLCC28	PA28PL28D
PHILIPS	P89LPC932BDB	TSSOP28	PA28TSS28D-EO
PHILIPS	P89LPC932FDH	TSSOP28	PA28TSS28D-EO
PHILIPS	P89LPC932FHN	QFN28	PA28QFN28D(6x6)
PHILIPS	P89LPC933FDH	TSSOP28	PA28TSS28D-EO



PHILIPS	P89LPC933FDH(ICP)	TSSOP28	PA28TSS28D-EO
PHILIPS	P89LPC934FDH	TSSOP28	PA28TSS28D-EO
PHILIPS	P89LPC934FDH(ICP)	TSSOP28	PA28TSS28D-EO
PHILIPS	P89LPC935FA	PLCC28	PA28PL28D
PHILIPS	P89LPC935FA(ICP)	PLCC28	PA28PL28D
PHILIPS	P89LPC935FDH	TSSOP28	PA28TSS28D-EO
PHILIPS	P89LPC935FDH(ICP)	TSSOP28	PA28TSS28D-EO
PHILIPS	P89LPC935FHN	QFN28	PA28QFN28D(6x6)
PHILIPS	P89LPC935FHN(ICP)	QFN28	PA28QFN28D(6x6)
PHILIPS	P89LPC936FDH	TSSOP28	PA28TSS28D-EO
PHILIPS	P89LPC936FDH(ICP)	TSSOP28	PA28TSS28D-EO
PHILIPS	P89LPC938FA	PLCC28	PA28PL28D
PHILIPS	P89LPC938FA(ICP)	PLCC28	PA28PL28D
PHILIPS	P89LPC938FDH	TSSOP28	PA28TSS28D-EO
PHILIPS	P89LPC938FDH(ICP)	TSSOP28	PA28TSS28D-EO
PHILIPS	P89LPC938FHN	QFN28	PA28QFN28D(6x6)
PHILIPS	P89LPC938FHN(ICP)	QFN28	PA28QFN28D(6x6)
PHILIPS	P89LV51RB2BA	PLCC44	PA44-48U
PHILIPS	P89LV51RB2BBC	TQFP44	PA44QF44D
PHILIPS	P89LV51RC2BN	DIP40	
PHILIPS	P89LV51RC2FA	PLCC44	PA44-48U
PHILIPS	P89LV51RC2FBC	TQFP44	PA44QF44D
PHILIPS	P89LV51RD2BA	PLCC44	PA44-48U
PHILIPS	P89LV51RD2BBC	TQFP44	PA44QF44D
PHILIPS	P89LV51RD2BN	DIP40	
PHILIPS	P89LV51RD2FA	PLCC44	PA44-48U
PHILIPS	P89V51RB2BA	PLCC44	PA44-48U
PHILIPS	P89V51RB2BBC	TQFP44	PA44QF44D
PHILIPS	P89V51RC2BN	DIP40	
PHILIPS	P89V51RC2FA	PLCC44	PA44-48U
PHILIPS	P89V51RC2FBC	TQFP44	PA44QF44D
PHILIPS	P89V51RD2BN	DIP40	
PHILIPS	P89V51RD2FA	PLCC44	PA44-48U
PHILIPS	P89V51RD2FBC	TQFP44	PA44QF44D
PHILIPS	P89V51RD2FN	DIP40	
PHILIPS	P89V660FA	PLCC44	PA44-48U
PHILIPS	P89V660FBC	QFP44	PA44QF44D
PHILIPS	P89V662FA	PLCC44	PA44-48U
PHILIPS	P89V662FBC	QFP44	PA44QF44D
PHILIPS	P89V664FA	PLCC44	PA44-48U
PHILIPS	P89V664FBC	QFP44	PA44QF44D
PHILIPS	PCD3755A	SOP28	PA28S-08
PHILIPS	PCF8582C	DIP8	
PHILIPS	PCF8582C	SOIC8	PA16SO16D-EO-150
PHILIPS	PCF8582D	DIP8	
PHILIPS	PCF8582D	SOIC8	PA16SO16D-EO-150
PHILIPS	PCF8582E	DIP8	
PHILIPS	PCF8582E	SOIC8	PA16SO16D-EO-150
PHILIPS	PCF8592C	DIP8	
PHILIPS	PCF8592C	SOIC8	PA16SO16D-EO-150
PHILIPS	PCF8594C	DIP8	
PHILIPS	PCF8594C	SOIC8	PA16SO16D-EO-150
PHILIPS	PCF8598C	DIP8	
PHILIPS	PCF8598C	SOIC8	PA16SO16D-EO-150
PHILIPS	PSD301	PLCC44	PA44-48U-PSD3xx
PHILIPS	PSD302	PLCC44	PA44-48U-PSD3xx
PHILIPS	PSD311	PLCC44	PA44-48U-PSD3xx
PHILIPS	PSD312	PLCC44	PA44-48U-PSD3xx
PHILIPS	PXAC37	PLCC44	PA44-48U
PHILIPS	PXAG37KBA	PLCC44	PA44-48U
PHILIPS	PXAG37KBBD	TQFP44	PA44QF44D
PHILIPS	PXAG37KFA	PLCC44	PA44-48U
PHILIPS	PXAG37KFBD	TQFP44	PA44QF44D
PHILIPS	PXAG49	PLCC44	PA44-48U
PHILIPS	PXAS37	PLCC44	PA44-48U
PHILIPS	PZ3032	PLCC44	PA44-48U
PHILIPS	PZ3032	TQFP44	PA44QF44D
PHILIPS	PZ5032	PLCC44	PA44-48U
PHILIPS	PZ5032	TQFP44	PA44QF44D
PMC	Pm25LV010	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
PMC	Pm25LV010	WSON8	PA8SON8D(6x5)
PMC	Pm25LV010A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
PMC	Pm25LV010A	WSON8	PA8SON8D(6x5)

PMC	Pm25LV020	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
PMC	Pm25LV020	WSON8	PA8SON8D(6x5)
PMC	Pm25LV040	DIP8	
PMC	Pm25LV040	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
PMC	Pm25LV040	SOIC8	PA20SO20D-EO-210
PMC	Pm25LV040	WSON8	PA8SON8D(6x5)
PMC	Pm25LV512	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
PMC	Pm25LV512	WSON8	PA8SON8D(6x5)
PMC	Pm25LV512A	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
PMC	Pm25LV512A	TSSOP8	PA8TSS8D
PMC	Pm25LV512A	WSON8	PA8SON8D(6x5)
PMC	Pm29F002B	DIP32	
PMC	Pm29F002B	PLCC32	PA32PL32D
PMC	Pm29F002T	DIP32	
PMC	Pm29F002T	PLCC32	PA32PL32D
PMC	Pm29F004B	DIP32	
PMC	Pm29F004B	PLCC32	PA32PL32D
PMC	Pm29F004B	TSOP32	PA32TS20/PA32TS32D-20
PMC	Pm29F004T	DIP32	
PMC	Pm29F004T	PLCC32	PA32PL32D
PMC	Pm29F004T	TSOP32	PA32TS20/PA32TS32D-20
PMC	Pm29LV002B	DIP32	
PMC	Pm29LV002T	DIP32	
PMC	Pm29LV104RB	PLCC32	PA32PL32D
PMC	Pm29LV104RB	TSOP32	PA32TS20/PA32TS32D-20
PMC	Pm29LV104RT	PLCC32	PA32PL32D
PMC	Pm29LV104RT	TSOP32	PA32TS20/PA32TS32D-20
PMC	Pm39F010-xxJC	PLCC32	PA32PL32D
PMC	Pm39F020-xxJC	PLCC32	PA32PL32D
PMC	Pm39F040-xxJC	PLCC32	PA32PL32D
PMC	Pm39LV010-xxJC	PLCC32	PA32PL32D
PMC	Pm39LV010-xxVC	sTSOP32	PA32TS32D
PMC	Pm39LV020-xxJC	PLCC32	PA32PL32D
PMC	Pm39LV040-xxJC	PLCC32	PA32PL32D
PMC	Pm39LV512R	DIP32	PA32PL32D
PMC	Pm39LV512-xxJC	PLCC32	PA32PL32D
PMC	Pm39LV512-xxVC	sTSOP32	PA32TS32D
PMC	Pm49FL002T-xxJC	PLCC32	PA32PL32D
PMC	Pm49FL002T-xxJV	sTSOP32	PA32TS32D
PMC	Pm49FL004T-xxJC	PLCC32	PA32PL32D
PMC	Pm49FL004T-xxJV	sTSOP32	PA32TS32D
PMC	Pm49FL008T-xxJC	PLCC32	PA32PL32D
PMC	Pm49FL008T-xxJV	sTSOP32	PA32TS32D
QUICK PULSE ALGORITHM		27010	DIP32
QUICK PULSE ALGORITHM		27040	DIP32
QUICK PULSE ALGORITHM	27128A		DIP28
QUICK PULSE ALGORITHM		27210	DIP40
QUICK PULSE ALGORITHM		27210	PLCC44
QUICK PULSE ALGORITHM		27256	DIP28
QUICK PULSE ALGORITHM		27512	DIP28
QUICK PULSE ALGORITHM	2764A		DIP28
RAMTRON	FM1608	DIP28	
RAMTRON	FM1608	SOIC28	PA28SO28D-EO-300
RAMTRON	FM1608B	DIP28	
RAMTRON	FM1608B	SOIC28	PA28SO28D-EO-300
RAMTRON	FM1808	DIP28	
RAMTRON	FM1808	SOIC28	PA28SO28D-EO-300
RAMTRON	FM18L08	DIP28	
RAMTRON	FM18L08	SOIC28	PA28SO28D-EO-300
RENESAS	HN58V65A	SOP28	PA28SO28DB-EC-350
RICOH	27C64	DIP28	
RICOH	27C64	PLCC32	PA32PL28D-YA
RICOH	RD27C256	DIP28	
RICOH	RD27C256	PLCC32	PA32PL28D-YA
RICOH	RD27C64	DIP28	
ROCKWELL	R2764	DIP28	
ROCKWELL	R2764C	DIP28	
ROCKWELL	R2764P	DIP28	
ROCKWELL	R27C64	DIP28	
ROCKWELL	R2816	DIP24	
ROHM	BR24C01A	DIP8	
ROHM	BR24C01A	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ROHM	BR24C01A	SOP8	PA16SO16D-EO-150/PA8SO8D-150

ROHM	BR24C01A	TSSOP8	PA8TSS8D
ROHM	BR24C01-DS	TSSOP8	PA24TSS24D
ROHM	BR24C01-DS	TSSOP8	PA8TSS8D
ROHM	BR24C01-DW	TSSOP8	PA24TSS24D
ROHM	BR24C01-DW	TSSOP8	PA8TSS8D
ROHM	BR24C01-MN	SOIC8	PA8SO8D-EO-150
ROHM	BR24C02	DIP8	
ROHM	BR24C02	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ROHM	BR24C02	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ROHM	BR24C02	TSSOP8	PA8TSS8D
ROHM	BR24C02AF	SOIC8	PA8SO8D-EO-150
ROHM	BR24C02AFJ	SOIC8	PA8SO8D-EO-150
ROHM	BR24C02AFJ-W	SOIC8	PA8SO8D-EO-150
ROHM	BR24C02AFV	SSOP8	PA8SS8D
ROHM	BR24C02AFV-W	SSOP8	PA8SS8D
ROHM	BR24C02AF-W	SOIC8	PA8SO8D-EO-150
ROHM	BR24C02A-W	DIP8	
ROHM	BR24C04	DIP8	
ROHM	BR24C04	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ROHM	BR24C04	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ROHM	BR24C04	TSSOP8	PA8TSS8D
ROHM	BR24C04A	DIP8	
ROHM	BR24C04A	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ROHM	BR24C04A	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ROHM	BR24C04A	TSSOP8	PA8TSS8D
ROHM	BR24C08	DIP8	
ROHM	BR24C08-DS	TSSOP8	PA24TSS24D
ROHM	BR24C08-DS	TSSOP8	PA8TSS8D
ROHM	BR24C08-DW	TSSOP8	PA24TSS24D
ROHM	BR24C08-DW	TSSOP8	PA8TSS8D
ROHM	BR24C08F	SOIC8	PA8SO8D-EO-150
ROHM	BR24C08FJ	SOIC8	PA8SO8D-EO-150
ROHM	BR24C08FV	SSOP8	PA8SS8D
ROHM	BR24C08-MN	SOIC8	PA8SO8D-EO-150
ROHM	BR24C16	DIP8	
ROHM	BR24C16-DS	TSSOP8	PA24TSS24D
ROHM	BR24C16-DS	TSSOP8	PA8TSS8D
ROHM	BR24C16-DW	TSSOP8	PA24TSS24D
ROHM	BR24C16-DW	TSSOP8	PA8TSS8D
ROHM	BR24C16F	SOIC8	PA8SO8D-EO-150
ROHM	BR24C16FJ	SOIC8	PA8SO8D-EO-150
ROHM	BR24C16FV	SSOP8	PA8SS8D
ROHM	BR24C16-MN	SOIC8	PA8SO8D-EO-150
ROHM	BR24C21FJ-W	SOIC8	PA8SO8D-EO-150
ROHM	BR24C21FV-W	SSOP8	PA8SS8D
ROHM	BR24C21F-W	SOIC8	PA8SO8D-EO-150
ROHM	BR24C21-W	DIP8	
ROHM	BR24C32-DW	TSSOP8	PA24TSS24D
ROHM	BR24C32-DW	TSSOP8	PA8TSS8D
ROHM	BR24C32-MN	SOIC8	PA8SO8D-EO-150
ROHM	BR24C64-MN	SOIC8	PA8SO8D-EO-150
ROHM	BR24E16	DIP8	
ROHM	BR24E16F	SOIC8	PA8SO8D-EO-150
ROHM	BR24E16FJ	SOIC8	PA8SO8D-EO-150
ROHM	BR24E16FV	SSOP8	PA8SS8D
ROHM	BR24G512-3A	DIP8	
ROHM	BR24L01AFJ-W	SOIC8	PA8SO8D-EO-150
ROHM	BR24L01AFVM-W	MSOP8	PA8MSOP8D/PA8SS8D-120
ROHM	BR24L01AFV-W	SSOP8	PA8SS8D
ROHM	BR24L01AF-W	SOIC8	PA8SO8D-EO-150
ROHM	BR24L01A-W	DIP8	
ROHM	BR24L02FJ-W	SOIC8	PA8SO8D-EO-150
ROHM	BR24L02FVM-W	MSOP8	PA8MSOP8D/PA8SS8D-120
ROHM	BR24L02FV-W	SSOP8	PA8SS8D
ROHM	BR24L02F-W	SOIC8	PA8SO8D-EO-150
ROHM	BR24L02-W	DIP8	
ROHM	BR24L04FJ-W	SOIC8	PA8SO8D-EO-150
ROHM	BR24L04FVM-W	MSOP8	PA8MSOP8D/PA8SS8D-120
ROHM	BR24L04FV-W	SSOP8	PA8SS8D
ROHM	BR24L04F-W	SOIC8	PA8SO8D-EO-150
ROHM	BR24L04-W	DIP8	
ROHM	BR24L08FJ-W	SOIC8	PA8SO8D-EO-150
ROHM	BR24L08FVM-W	MSOP8	PA8MSOP8D/PA8SS8D-120

ROHM	BR24L08FV-W	SSOP8	PA8SS8D
ROHM	BR24L08F-W	SOIC8	PA8SO8D-EO-150
ROHM	BR24L08-W	DIP8	
ROHM	BR24L16FJ-W	SOIC8	PA8SO8D-EO-150
ROHM	BR24L16FVM-W	MSOP8	PA8MSOP8D/PA8SS8D-120
ROHM	BR24L16FV-W	SSOP8	PA8SS8D
ROHM	BR24L16F-W	SOIC8	PA8SO8D-EO-150
ROHM	BR24L16-W	DIP8	
ROHM	BR24L32FJ-W	SOIC8	PA8SO8D-EO-150
ROHM	BR24L32FV-W	SSOP8	PA8SS8D
ROHM	BR24L32F-W	SOIC8	PA8SO8D-EO-150
ROHM	BR24L32-W	DIP8	
ROHM	BR24L64FJ-W	SOIC8	PA8SO8D-EO-150
ROHM	BR24L64F-W	SOIC8	PA8SO8D-EO-150
ROHM	BR24L64-W	DIP8	
ROHM	BR24T02	DIP8	
ROHM	BR24T02	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ROHM	BR24T02	SOP8	PA20SO20D-EO-210
ROHM	BR24T02	TSSOP8	PA8TSS8D
ROHM	BR24T02	USON8	PA8SON8D(2x3)
ROHM	BR24T128	DIP8	
ROHM	BR24T128	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ROHM	BR24T128	TSSOP8	PA8TSS8D
ROHM	BR24T128	USON8	PA8SON8D(2x3)
ROHM	BR24T64	DIP8	
ROHM	BR24T64	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ROHM	BR24T64	TSSOP8	PA8TSS8D
ROHM	BR24T64	USON8	PA8SON8D(2x3)
ROHM	BR9010	DIP8	
ROHM	BR9010F	DIP8	
ROHM	BR9010F	SOIC8	PA16SO16D-EO-150
ROHM	BR9010F	SSOP8	PA8TSS-OT
ROHM	BR9016	DIP8	
ROHM	BR9016F	DIP8	
ROHM	BR9016F	SOIC8	PA16SO16D-EO-150
ROHM	BR9016F	SSOP8	PA8TSS-OT
ROHM	BR9020	DIP8	
ROHM	BR9020	SOIC8	PA16SO16D-EO-150
ROHM	BR9020	SSOP8	PA8TSS-OT
ROHM	BR9020F	DIP8	
ROHM	BR9020F	SOIC8	PA16SO16D-EO-150
ROHM	BR9020F	SSOP8	PA8TSS-OT
ROHM	BR9040	DIP8	
ROHM	BR9040F	DIP8	
ROHM	BR9040F	SOIC8	PA16SO16D-EO-150
ROHM	BR9040F	SSOP8	PA8TSS-OT
ROHM	BR9080	DIP8	
ROHM	BR9080F	DIP8	
ROHM	BR9080F	SOIC8	PA16SO16D-EO-150
ROHM	BR9080F	SSOP8	PA8TSS-OT
ROHM	BR93LC46	DIP8	
ROHM	BR93LC46F	SOIC8	PA16SO16D-EO-150
ROHM	BR93LC46FJ	SOP8	PA16SO16D-EO-150
ROHM	BR93LC46FV	SOP8	PA24TSS24D
ROHM	BR93LC46FV	SOP8	PA8TSS8D
ROHM	BR93LC46RF	SOP8	PA8SO8D-EO-150
ROHM	BR93LC46RFJ	SOP8	PA8SO8D-EO-150
ROHM	BR93LC56	DIP8	
ROHM	BR93LC56F	SOIC8	PA16SO16D-EO-150
ROHM	BR93LC66	DIP8	
ROHM	BR93LC66F	SOIC8	PA16SO16D-EO-150
ROHM	BR93LL46	DIP8	
ROHM	BR93LL46F	SOIC8	PA16SO16D-EO-150
RUSSIAN	573RF2/5	DIP24	
RUSSIAN	573RF4-21.5	DIP28	
RUSSIAN	573RF4-23	DIP28	
RUSSIAN	57RF4-21	DIP28	
SAMSUNG	CPL16L8	DIP20	
SAMSUNG	CPL16L8	PLCC20	PA20LC20D[Dead Bug]
SAMSUNG	CPL16L8L	DIP20	
SAMSUNG	CPL16L8L	PLCC20	PA20LC20D[Dead Bug]
SAMSUNG	CPL16R4	DIP20	
SAMSUNG	CPL16R4	PLCC20	PA20LC20D[Dead Bug]

SAMSUNG	CPL16R4L	DIP20	
SAMSUNG	CPL16R4L	PLCC20	PA20LC20D[Dead Bug]
SAMSUNG	CPL16R6	DIP20	
SAMSUNG	CPL16R6	PLCC20	PA20LC20D[Dead Bug]
SAMSUNG	CPL16R6L	DIP20	
SAMSUNG	CPL16R6L	PLCC20	PA20LC20D[Dead Bug]
SAMSUNG	CPL16R8	DIP20	
SAMSUNG	CPL16R8	PLCC20	PA20LC20D[Dead Bug]
SAMSUNG	CPL16R8L	DIP20	
SAMSUNG	CPL16R8L	PLCC20	PA20LC20D[Dead Bug]
SAMSUNG	CPL20L10	DIP24	
SAMSUNG	CPL20L10	PLCC28	PA28PL24D2P6-YA
SAMSUNG	CPL20L8	DIP24	
SAMSUNG	CPL20L8	PLCC28	PA28PL24D2P6-YA
SAMSUNG	CPL20R4	DIP24	
SAMSUNG	CPL20R4	PLCC28	PA28PL24D2P6-YA
SAMSUNG	CPL20R6	DIP24	
SAMSUNG	CPL20R6	PLCC28	PA28PL24D2P6-YA
SAMSUNG	CPL20R8	DIP24	
SAMSUNG	CPL20R8	PLCC28	PA28PL24D2P6-YA
SAMSUNG	CPL22V10	DIP24	
SAMSUNG	CPL22V10	PLCC28	PA28PL24D2P6-YA
SAMSUNG	K5A3240YBA	BGA56	PA56BGA48-YO
SAMSUNG	K5A3240YBB	BGA56	PA56BGA48-YO
SAMSUNG	K5A3240YBM	BGA56	PA56BGA48-YO
SAMSUNG	K5A3240YTA	BGA56	PA56BGA48-YO
SAMSUNG	K5A3240YTB	BGA56	PA56BGA48-YO
SAMSUNG	K5A3240YTM	BGA56	PA56BGA48-YO
SAMSUNG	K5A3280YBA	BGA56	PA56BGA48-YO
SAMSUNG	K5A3280YBB	BGA56	PA56BGA48-YO
SAMSUNG	K5A3280YBC	BGA69	PA69BGA48DE
SAMSUNG	K5A3280YBM	BGA56	PA56BGA48-YO
SAMSUNG	K5A3280YTA	BGA56	PA56BGA48-YO
SAMSUNG	K5A3280YTB	BGA56	PA56BGA48-YO
SAMSUNG	K5A3280YTC	BGA69	PA69BGA48DE
SAMSUNG	K5A3280YTM	BGA56	PA56BGA48-YO
SAMSUNG	K5A3281CBM	BGA69	PA69BGA48DE
SAMSUNG	K5A3281CTM	BGA69	PA69BGA48DE
SAMSUNG	K5A3340YBA	BGA56	PA56BGA48-YO
SAMSUNG	K5A3340YBB	BGA56	PA56BGA48-YO
SAMSUNG	K5A3340YBM	BGA56	PA56BGA48-YO
SAMSUNG	K5A3340YTA	BGA56	PA56BGA48-YO
SAMSUNG	K5A3340YTB	BGA56	PA56BGA48-YO
SAMSUNG	K5A3340YTM	BGA56	PA56BGA48-YO
SAMSUNG	K5A3380YBA	BGA56	PA56BGA48-YO
SAMSUNG	K5A3380YBB	BGA56	PA56BGA48-YO
SAMSUNG	K5A3380YBM	BGA56	PA56BGA48-YO
SAMSUNG	K5A3380YTA	BGA56	PA56BGA48-YO
SAMSUNG	K5A3380YTB	BGA56	PA56BGA48-YO
SAMSUNG	K5A3380YTM	BGA56	PA56BGA48-YO
SAMSUNG	K5D3241YBA	BGA66	PA66BGA48DA-TO-8X11
SAMSUNG	K5D3241YTA	BGA66	PA66BGA48DA-TO-8X11
SAMSUNG	K5F3264YBM(NOR)	BGA69	PA69BGA48DB
SAMSUNG	K5F3264YTM(NOR)	BGA69	PA69BGA48DB
SAMSUNG	K5J6332CBM	BGA69	PA69BGA48DJ-YO-8X11.6
SAMSUNG	K5J6332CTM	BGA69	PA69BGA48DJ-YO-8X11.6
SAMSUNG	K5L2963CAM	BGA64	HA64BG48DF
SAMSUNG	K8D1616UBA-T	BGA48	PA48BGA48DA
SAMSUNG	K8D1616UBA-Y	TSOP48	PA48TS48D
SAMSUNG	K8D1616UBM-T	BGA48	PA48BGA48DA
SAMSUNG	K8D1616UBM-Y	TSOP48	PA48TS48D
SAMSUNG	K8D1616UTA-T	BGA48	PA48BGA48DA
SAMSUNG	K8D1616UTA-Y	TSOP48	PA48TS48D
SAMSUNG	K8D1616UTM-T	BGA48	PA48BGA48DA
SAMSUNG	K8D1616UTM-Y	TSOP48	PA48TS48D
SAMSUNG	K8D1716UBA-T	BGA48	PA48BGA48DA
SAMSUNG	K8D1716UBA-Y	TSOP48	PA48TS48D
SAMSUNG	K8D1716UBC-Y	TSOP48	PA48TS48D
SAMSUNG	K8D1716UTA-T	BGA48	PA48BGA48DA
SAMSUNG	K8D1716UTA-Y	TSOP48	PA48TS48D
SAMSUNG	K8D1716UTC-Y	TSOP48	PA48TS48D
SAMSUNG	K8D3216UBA-T	BGA48	PA48BGA48DA
SAMSUNG	K8D3216UBA-Y	TSOP48	PA48TS48D

SAMSUNG	K8D3216UBB-T	BGA48	PA48BGA48DA
SAMSUNG	K8D3216UBB-Y	TSOP48	PA48TS48D
SAMSUNG	K8D3216UBC-T	BGA48	PA48BG48DAD
SAMSUNG	K8D3216UBC-Y	TSOP48	PA48TS48D
SAMSUNG	K8D3216UBM-T	BGA48	PA48BGA48DA
SAMSUNG	K8D3216UBM-Y	TSOP48	PA48TS48D
SAMSUNG	K8D3216UTA-T	BGA48	PA48BGA48DA
SAMSUNG	K8D3216UTA-Y	TSOP48	PA48TS48D
SAMSUNG	K8D3216UTB-T	BGA48	PA48BGA48DA
SAMSUNG	K8D3216UTB-Y	TSOP48	PA48TS48D
SAMSUNG	K8D3216UTC-T	BGA48	PA48BG48DAD
SAMSUNG	K8D3216UTC-Y	TSOP48	PA48TS48D
SAMSUNG	K8D3216UTM-T	BGA48	PA48BGA48DA
SAMSUNG	K8D3216UTM-Y	TSOP48	PA48TS48D
SAMSUNG	K8D3316UBA-T	BGA48	PA48BGA48DA
SAMSUNG	K8D3316UBA-Y	TSOP48	PA48TS48D
SAMSUNG	K8D3316UBC-T	BGA48	PA48BG48DAD
SAMSUNG	K8D3316UBM-T	BGA48	PA48BGA48DA
SAMSUNG	K8D3316UBM-Y	TSOP48	PA48TS48D
SAMSUNG	K8D3316UTA-T	BGA48	PA48BGA48DA
SAMSUNG	K8D3316UTA-Y	TSOP48	PA48TS48D
SAMSUNG	K8D3316UTC-T	BGA48	PA48BG48DAD
SAMSUNG	K8D3316UTM-T	BGA48	PA48BGA48DA
SAMSUNG	K8D3316UTM-Y	TSOP48	PA48TS48D
SAMSUNG	K8D6316UBM-P	TSOP48	PA48TS48D
SAMSUNG	K8D6316UBM-T	BGA48	PA48BGA48DL
SAMSUNG	K8D6316UBM-Y	TSOP48	PA48TS48D
SAMSUNG	K8D6316UTM-P	TSOP48	PA48TS48D
SAMSUNG	K8D6316UTM-T	BGA48	PA48BGA48DL
SAMSUNG	K8D6316UTM-Y	TSOP48	PA48TS48D
SAMSUNG	K8P1615UQB	TSOP48	PA48TS48D
SAMSUNG	K8P2815UQB	BGA80	HA80BG48DF
SAMSUNG	K8P3215UQB	BGA48	HA48BG48DAI
SAMSUNG	K8P3215UQB	TSOP48	PA48TS48D
SAMSUNG	K8P5615UQA	TSOP56	PA56TS48DC
SAMSUNG	K8P6415UQB	BGA48	HA48BG48DAI
SAMSUNG	K8P6415UQB	TSOP48	PA48TS48D
SAMSUNG	K8Q2815UQB	TSOP56	PA56TS48DB
SAMSUNG	K9F1208U0A	TSOP48	PA48TS48D
SAMSUNG	K9F1208U0B	TSOP48	PA48TS48D
SAMSUNG	K9F1208U0C	TSOP48	PA48TS48D
SAMSUNG	K9F1208U0M	TSOP48	PA48TS48D
SAMSUNG	K9F1216U0A	BGA63	PA63BGA48DD
SAMSUNG	K9F1216U0A	TSOP48	PA48TS48D
SAMSUNG	K9F1G08U0A	TSOP48	PA48TS48D
SAMSUNG	K9F1G08U0B	TSOP48	PA48TS48D
SAMSUNG	K9F1G08U0C	TSOP48	PA48TS48D
SAMSUNG	K9F1G08U0D	TSOP48	PA48TS48D
SAMSUNG	K9F1G08U0F	TSOP48	HA48TS48DET
SAMSUNG	K9F1G08U0M	TSOP48	PA48TS48D
SAMSUNG	K9F2808U0A	TSOP48	PA48TS48D
SAMSUNG	K9F2808U0B	TSOP48	PA48TS48D
SAMSUNG	K9F2808U0C	TSOP48	PA48TS48D
SAMSUNG	K9F2808U0M	TSOP48	PA48TS48D
SAMSUNG	K9F2G08U0A	TSOP48	PA48TS48D
SAMSUNG	K9F2G08U0B	TSOP48	PA48TS48D
SAMSUNG	K9F2G08U0M	TSOP48	PA48TS48D
SAMSUNG	K9F4G08U0A	TSOP48	PA48TS48D
SAMSUNG	K9F4G08U0B	TSOP48	PA48TS48D
SAMSUNG	K9F4G08U0M	TSOP48	PA48TS48D
SAMSUNG	K9F5608U0A	TSOP48	PA48TS48D
SAMSUNG	K9F5608U0B	TSOP48	PA48TS48D
SAMSUNG	K9F5608U0C	TSOP48	PA48TS48D
SAMSUNG	K9F5608U0D	BGA63	HA63BG48DO
SAMSUNG	K9F5608U0D	TSOP48	PA48TS48D
SAMSUNG	K9F5608U0M	TSOP48	PA48TS48D
SAMSUNG	K9F5616U0B	TSOP48	PA48TS48D
SAMSUNG	K9F5616U0C	TSOP48	PA48TS48D
SAMSUNG	K9F5616U0M	TSOP48	PA48TS48D
SAMSUNG	K9K1208U0A	TSOP48	PA48TS48D
SAMSUNG	K9K1216D0C	BGA63	PA63BGA48DD
SAMSUNG	K9K1G08U0B	BGA63	HA63BG48DH
SAMSUNG	K9K1G08U0M	TSOP48	PA48TS48D

SAMSUNG	K9K4G08U0M	TSOP48	PA48TS48D
SAMSUNG	K9K8G08U0A	TSOP48	PA48TS48D
SAMSUNG	K9K8G08U0M	TSOP48	PA48TS48D
SAMSUNG	KAB01D100M	BGA80	PA80BGA48DB
SAMSUNG	KAB01D100M-A	BGA80	PA80BGA48DB-A
SAMSUNG	KAC070010M	BGA69	PA69BGA48DG-YO-8X13
SAMSUNG	KAD070300A	BGA69	PA69BGA48DJ-YO-8X11.6
SAMSUNG	KAD070300M	BGA69	PA69BGA48DJ-YO-8X11.6
SAMSUNG	KBB05A300M	BGA80	PA80BGA48DC
SAMSUNG	KBB05A500M	BGA80	PA80BGA48DD
SAMSUNG	KBE00F003A	BGA107	HA107BGA48DH
SAMSUNG	KBE00F003M	BGA107	HA107BG48DG
SAMSUNG	KBE00F005A	BGA137	HA137BG48DC
SAMSUNG	KBE00F005M	BGA137	HA137BG48DB
SAMSUNG	KBE00M005M	BGA137	HA137BG48DC
SAMSUNG	KBE00S003M	BGA107	HA107BG48DG
SAMSUNG	KBE00S005M	BGA137	HA137BGA48DE
SAMSUNG	KBE00S009M	BGA137	HA137BGA48DE
SAMSUNG	KM2816A	DIP24	
SAMSUNG	KM2816AI	DIP24	
SAMSUNG	KM2817A	DIP28	
SAMSUNG	KM2817AI	DIP28	
SAMSUNG	KM2864A	DIP28	
SAMSUNG	KM2864AH	DIP28	
SAMSUNG	KM2865A	DIP28	
SAMSUNG	KM2865AH	DIP28	
SAMSUNG	KM28C16	DIP24	
SAMSUNG	KM28C17	DIP28	
SAMSUNG	KM28C17	PLCC32	PA32PL28D-YA
SAMSUNG	KM28C256	DIP28	
SAMSUNG	KM28C256	PLCC32	PA32PL28D-YA
SAMSUNG	KM28C256A	DIP28	
SAMSUNG	KM28C256A	PLCC32	PA32PL28D-YA
SAMSUNG	KM28C64	DIP28	
SAMSUNG	KM28C64	PLCC32	PA32PL28D-YA
SAMSUNG	KM28C64A	DIP28	
SAMSUNG	KM28C64A	PLCC32	PA32PL28D-YA
SAMSUNG	KM28C65	DIP28	
SAMSUNG	KM28C65	PLCC32	PA32PL28D-YA
SAMSUNG	KM28C65A	DIP28	
SAMSUNG	KM28C65A	PLCC32	PA32PL28D-YA
SAMSUNG	KM28U160T-B	TSOP48	PA48TS48D
SAMSUNG	KM28U160T-T	TSOP48	PA48TS48D
SAMSUNG	KM28U800T-B	TSOP48	PA48TS48D
SAMSUNG	KM28U800T-T	TSOP48	PA48TS48D
SAMSUNG	KM29C010	DIP32	
SAMSUNG	KM29C010	PLCC32	PA32PL32D
SAMSUNG	KM29C010	TSOP32	PA32TS20/PA32TS32D-20
SAMSUNG	KM29W32000	TSOP44	PA44TS44D
SAMSUNG	KM5AU1620-B	BGA56	PA56FBGA48D
SAMSUNG	KM5AU1620-T	BGA56	PA56FBGA48D
SAMSUNG	KM5AU1621-B	BGA56	PA56FBGA48D
SAMSUNG	KM5AU1621-T	BGA56	PA56FBGA48D
SAMSUNG	KM5MU0820T-B	sTSOP48	PA48TS48D-A
SAMSUNG	KM5MU0820T-T	sTSOP48	PA48TS48D-A
SAMSUNG	KM5MU1620T-B	sTSOP48	PA48TS48D-A
SAMSUNG	KM5MU1620T-T	sTSOP48	PA48TS48D-A
SAMSUNG	KM93C06	DIP8	
SAMSUNG	KM93C07	DIP8	
SAMSUNG	KM93C46	DIP8	
SAMSUNG	KM93C56	DIP8	
SAMSUNG	KM93C66	DIP8	
SAMSUNG	KS24C010	DIP8	
SAMSUNG	KS24C011	DIP8	
SAMSUNG	KS24C020	DIP8	
SAMSUNG	KS24C021	DIP8	
SAMSUNG	KS24C040	DIP8	
SAMSUNG	KS24C041	DIP8	
SAMSUNG	KS24C080	DIP8	
SAMSUNG	KS24C081	DIP8	
SAMSUNG	KS24L161	DIP8	
SAMSUNG	KS24L321	DIP8	
SAMSUNG	KS24L641	DIP8	

SAMSUNG	KS57P0408	QFP44	SS-QFP44
SAMSUNG	KS57P0504	SDIP30	SS-SDIP
SAMSUNG	KS57P0504	SOP32	SS-SOP
SAMSUNG	KS57P0616	QFP44	SS-QFP44
SAMSUNG	KS57P0616	SDIP42	SS-SDIP
SAMSUNG	KS57P21208	QFP44	SS-QFP44
SAMSUNG	KS57P21208	SDIP42	SS-SDIP
SAMSUNG	KS57P21408	QFP100	SS-QFP100
SAMSUNG	KS57P21516	QFP100	SS-QFP100
SAMSUNG	KS57P21632	QFP100	SS-QFP100
SAMSUNG	KS57P21708	QFP64	SS-QFP64
SAMSUNG	KS57P21832	QFP100	SS-QFP100
SAMSUNG	KS57P2304	QFP64	SS-QFP64
SAMSUNG	KS57P2308	QFP80	SS-QFP80
SAMSUNG	KS57P2316	QFP80	SS-QFP80
SAMSUNG	KS57P2916	QFP80	SS-QFP80
SAMSUNG	KS57P3204	QFP64	SS-QFP64
SAMSUNG	KS57P4104	QFP44	SS-QFP44
SAMSUNG	KS57P4104	SDIP42	SS-SDIP
SAMSUNG	KS57P4204	SDIP30	SS-SDIP
SAMSUNG	KS57P4204	SOP28	SS-SOP
SAMSUNG	KS57P4304	QFP44	SS-QFP44
SAMSUNG	KS57P4304	SDIP42	SS-SDIP
SAMSUNG	KS57P5116	SDIP64	SS-SDIP
SAMSUNG	KS57P5208	QFP44	SS-QFP44
SAMSUNG	KS57P5208	SDIP42	SS-SDIP
SAMSUNG	KS57P5308	SDIP30	SS-SDIP
SAMSUNG	KS57P5308	SOP32	SS-SOP
SAMSUNG	KS57P5312	SDIP30	SS-SDIP
SAMSUNG	KS57P5312	SOP32	SS-SOP
SAMSUNG	KS57P5404	SDIP24	SS-SDIP
SAMSUNG	KS57P5404	SOP24	PA28SO28D-EO-300
SAMSUNG	KS57P5404	SOP24	SS-SOP
SAMSUNG	KS57P5532	SDIP64	SS-SDIP
SAMSUNG	KS57P5616	QFP100	SS-QFP100
SAMSUNG	KS86F4404	DIP8	
SAMSUNG	KS86F4504	DIP16	
SAMSUNG	KS86F4504	DIP20	
SAMSUNG	KS86F4504	SOP20	PA28SO28D-EO-300
SAMSUNG	KS86P4004	SDIP30	SS-SDIP
SAMSUNG	KS86P4004	SOP32	SS-SOP
SAMSUNG	KS86P4104	SDIP24	SS-SDIP
SAMSUNG	KS86P4104	SOP24	SS-SOP
SAMSUNG	KS86P4208	SDIP30	SS-SDIP
SAMSUNG	KS86P4208	SOP28	SS-SOP
SAMSUNG	KS86P4208	SOP32	SS-SOP
SAMSUNG	KS86P4304	DIP20	SS-DIP
SAMSUNG	KS86P6008	QFP44	SS-QFP44
SAMSUNG	KS86P6008	SDIP42	SS-SDIP
SAMSUNG	KS86P6104	DIP20	SS-DIP
SAMSUNG	KS86P6104	SOP24	SS-SOP
SAMSUNG	KS86P6408	QFP44	SS-QFP44
SAMSUNG	KS86P6408	SDIP42	SS-SDIP
SAMSUNG	KS88C8432	SDIP42	SS-SDIP
SAMSUNG	KS88P0416	DIP40	
SAMSUNG	KS88P0416	SDIP32	SS-SDIP
SAMSUNG	KS88P0416	SOP32	SS-SOP
SAMSUNG	KS88P0424	DIP40	
SAMSUNG	KS88P0424	DIP40	
SAMSUNG	KS88P0424	SDIP32	SS-SDIP
SAMSUNG	KS88P0424	SOP32	SS-SOP
SAMSUNG	KS88P0716	QFP64	SS-QFP64
SAMSUNG	KS88P0716	SDIP64	SS-SDIP
SAMSUNG	KS88P2148	QFP80	SS-QFP80
SAMSUNG	KS88P2416	QFP80	SS-QFP80
SAMSUNG	KS88P2432	QFP80	SS-QFP80
SAMSUNG	KS88P4504	QFP80	SS-QFP80
SAMSUNG	KS88P4632	QFP64	SS-QFP64
SAMSUNG	KS88P4632	SDIP64	SS-SDIP
SAMSUNG	KS88P4716	QFP44	SS-QFP44
SAMSUNG	KS88P4716	SDIP42	SS-SDIP
SAMSUNG	KS88P6116	QFP44	SS-QFP44
SAMSUNG	KS88P6232	SDIP42	SS-SDIP



SAMSUNG	KS88P8324		SDIP42	SS-SDIP
SAMSUNG	KS88P8432		SDIP42	SS-SDIP
SAMSUNG	S3P80A4		SOP24	PA28SO28D-EO-300
SAMSUNG	S3P80A5		SOP24	PA28SO28D-EO-300
SAMSUNG	S3P80A8		SOP24	PA28SO28D-EO-300
SAMSUNG	S3P80B4		SOP24	PA28SO28D-EO-300
SAMSUNG	S3P80B5		SOP24	PA28SO28D-EO-300
SAMSUNG	S3P80B8		SOP24	PA28SO28D-EO-300
SEEQ		27128	DIP28	
SEEQ		27256	DIP28	
SEEQ		2764	DIP28	
SEEQ	27C256		DIP28	
SEEQ	2804A		DIP24	
SEEQ	2816A		DIP24	
SEEQ	2816A		PLCC32	PA32PL28D-YA
SEEQ	2816AH		DIP24	
SEEQ	2816AH		PLCC32	PA32PL28D-YA
SEEQ	2817A		DIP28	
SEEQ	2817A		PLCC32	PA32PL28D-YA
SEEQ	2817AH		DIP28	
SEEQ		2864	DIP28	
SEEQ		2864	PLCC32	PA32PL28D-YA
SEEQ	2864H		DIP28	
SEEQ	2864H		PLCC32	PA32PL28D-YA
SEEQ	28C010		DIP32	
SEEQ	28C010		PLCC32	PA32PL28D-YA
SEEQ	28C256		DIP28	
SEEQ	28C256		PLCC32	PA32PL28D-YA
SEEQ	28C256A		DIP28	
SEEQ	28C256A		PLCC32	PA32PL28D-YA
SEEQ	28C256AH		DIP28	
SEEQ	28C256AH		PLCC32	PA32PL28D-YA
SEEQ	28C64		DIP28	
SEEQ	28C64A		DIP28	
SEEQ	28C65		DIP28	
SEEQ	28HC256		DIP28	
SEEQ	28HC256H		DIP28	
SEEQ	28HC64		DIP28	
SEEQ	52B13		DIP24	
SEEQ	52B13H		DIP24	
SEEQ	52B33		DIP28	
SEEQ	52B33H		DIP28	
SEEQ	E28C64		DIP28	
SEEQ	M28C010		DIP32	
SEEQ	M28C010A		DIP32	
SEEQ	M28C64		DIP28	
SEIKO	S24C01A		DIP8	
SEIKO	S24C02A		DIP8	
SEIKO	S24C04A		DIP8	
SEIKO	S24C08ADPA		DIP8	
SEIKO	S24C08AFJA		SOP8	PA16SO16D-EO-150
SEIKO	S24C16ADPA		DIP8	
SEIKO	S24C16AFJA		SOP8	PA16SO16D-EO-150
SEIKO	S24CS02A		DIP8	
SEIKO	S24CS02A		SOIC8	PA16SO16D-EO-150
SEIKO	S-2812A		DIP28	
SEIKO	S-2812A		SOP28	PA28SO28DA-EC-330
SEIKO	S-2817A		DIP28	
SEIKO	S-2817A		SOP28	PA28SO28DA-EC-330
SEIKO	S-2860B		DIP28	
SEIKO	S-2860B		SOP28	PA28SO28DA-EC-330
SEIKO	S-2864B		DIP28	
SEIKO	S-2864B		SOP28	PA28SO28DA-EC-330
SEIKO	S-29430A		DIP8	
SEIKO	S-29430A		SOIC8	PA16SO16D-EO-150
SEIKO	S-93C46ADFJ		SOIC8	PA16SO16D-EO-150
SEIKO	S-93C46ADP		DIP8	
SEIKO	S-93C46AFJ		SOIC8	PA8SO8D-EO-150
SEIKO	S-93C46AFT		TSSOP8	PA8TSS-OT
SEIKO	S-93C46BD		DIP8	
SEIKO	S-93C46BD		SOIC8	PA16SO16D-EO-150
SEIKO	S-93C46BD		TSSOP8	PA8TSS-OT
SEIKO	S-93C46BR		SOIC8	PA8SO8D-EO-150

SEIKO	S-93C56ADFJ	SOIC8	PA16SO16D-EO-150
SEIKO	S-93C56ADP	DIP8	
SEIKO	S-93C56AFJ	SOIC8	PA8SO8D-EO-150
SEIKO	S-93C56AFT	TSSOP8	PA8TSS-OT
SEIKO	S-93C56BD	DIP8	
SEIKO	S-93C56BD	SOIC8	PA16SO16D-EO-150
SEIKO	S-93C56BD	TSSOP8	PA8TSS-OT
SEIKO	S-93C56BR	SOIC8	PA8SO8D-EO-150
SEIKO	S-93C66ADFJ	SOIC8	PA16SO16D-EO-150
SEIKO	S-93C66ADP	DIP8	
SEIKO	S-93C66AFJ	SOIC8	PA8SO8D-EO-150
SEIKO	S-93C66AFT	TSSOP8	PA8TSS-OT
SEIKO	S-93C66BD	DIP8	
SEIKO	S-93C66BD	SOIC8	PA16SO16D-EO-150
SEIKO	S-93C66BD	TSSOP8	PA8TSS-OT
SEIKO	S-93C66BR	SOIC8	PA8SO8D-EO-150
SEIKO	S-93C76ADFJ	SOIC8	PA16SO16D-EO-150
SEIKO	S-93C76ADP	DIP8	
SEIKO	S-93C76AFT	TSSOP8	PA8TSS-OT
SEIKO	S-93C86BD	SOIC8	PA16SO16D-EO-150
SEIKO	S-93C86BD	TSSOP8	PA8TSS-OT
SHARP	LH28F004SUT	TSOP40	PA40TS40D
SHARP	LH28F008SAT	TSOP40	PA40TS40D
SHARP	LH28F128BFHED	TSOP48	PA48TS48D
SHARP	LH28F160B	BGA48	CIC-48uBGA-44D-A6-YAM
SHARP	LH28F160BJD-TTL	DIP42	
SHARP	LH28F160BJE	TSOP48	PA48TS48D
SHARP	LH28F160BJE	TSOP48	PA48TS48D
SHARP	LH28F160BJE-BTL	TSOP48	PA48TS48D
SHARP	LH28F160BJE-TTL	TSOP48	PA48TS48D
SHARP	LH28F160S3	SSOP56	PA56SS48DB/CIC-56SS-48D-B6-TI
SHARP	LH28F160S3	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
SHARP	LH28F160S5	SSOP56	PA56SS48DB/CIC-56SS-48D-B6-TI
SHARP	LH28F320BFHE-PBTL	TSOP48	PA48TS48D
SHARP	LH28F320BFHE-PTTL	TSOP48	PA48TS48D
SHARP	LH28F320BFN-PTTL	SOP44	PA44SO44D
SHARP	LH28F320BJE-PBTL	TSOP48	PA48TS48D
SHARP	LH28F320BJHE-PTTL	TSOP48	PA48TS48D
SHARP	LH28F400BVE-BL	TSOP48	PA48TS48D
SHARP	LH28F400BVE-TL	TSOP48	PA48TS48D
SHARP	LH28F400SUE	TSOP48	PA48TS48D
SHARP	LH28F640BFN-PTTL	SOP44	PA44SO44D
SHARP	LH28F800B	BGA48	CIC-48uBGA-44D-A6-YAM
SHARP	LH28F800BGHE	TSOP48	PA48TS48D
SHARP	LH28F800BJE	TSOP48	PA48TS48D
SHARP	LH28F800BJHE-PBTLT9	TSOP48	PA48TS48D
SHARP	LH28F800BJHE-PTTLT6	TSOP48	PA48TS48D
SHARP	LH28F800BVHE	TSOP48	PA48TS48D
SHARP	LH28F800SGE	TSOP48	PA48TS48D
SHARP	LH57128	DIP28	
SHARP	LH57256	DIP28	
SHARP	LH5764	DIP28	
SHARP	LHF00L09	BGA48	HA48BG48DBG
SHARP	LHF00L35	PLCC32	PA32PL32D
SHARP	LHF00L47	TSOP40	PA40TS40D
SHARP	LRS1311	BGA72	PA72BGA48D-A
SHARP	LRS1316A	BGA72	PA72BGA48D-C
SHARP	LRS1325A	BGA72	PA72BGA48D-A
SHARP	LRS1329	BGA72	PA72BGA48D-A
SHARP	LRS1331	BGA72	PA72BGA48D-B
SHARP	LRS1337	BGA72	PA72BGA48D-B
SHARP	LRS1342	BGA72	PA72BGA48D-B
SHARP	LRS1349	BGA72	PA72BGA48D-A
SHARP	LRS1350	BGA72	PA72BGA48D-A
SHARP	LRS1360	BGA72	PA72BGA48D-B
SHARP	LRS1370	BGA72	PA72BGA48D-B
SHARP	LRS1381A	BGA72	PA72BGA48D-B
SHARP	LRS1383	BGA72	PA72BGA48D-B
SHARP	LRS1386	BGA72	PA72BGA48D-B
SHARP	LRS1387	BGA72	PA72BGA48D-B
SHARP	LRS1805A	BGA72	PA72BGA48D-B
SHARP	LRS1806A	BGA72	PA72BGA48D-B
SHARP	LRS1815	BGA72	PA72BGA48D-B

SHARP	LRS1816	BGA72	PA72BGA48D-B
SHARP	LRS1825	BGA72	PA72BGA48D-B
SHARP	LRS1826	BGA72	PA72BGA48D-B
SHARP	LRS1828	BGA72	PA72BGA48D-BB
SHARP	LRS1850	BGA72	PA72BGA48D-B
SHARP	LRS1863	BGA72	PA72BGA48D-BC
SHARP	LRS1864	BGA72	PA72BGA48D-BC
SHARP	LRS1876	BGA72	PA72BGA48D-BC
SIEMENS	C501-1E	DIP40	
SIEMENS	C501-1E	PLCC44	PA44-48U
SIEMENS	C504-2E	QFP44	PA44Q-16
SIEMENS	C504-2E	QFP44	PA44Q-16
SIEMENS	C505A-4E	QFP44	PA44Q-16
SIEMENS	C505CA-4E	QFP44	PA44Q-16
SIEMENS	SDA2506	DIP8	
SIEMENS	SDE2506	DIP8	
SIGNETICS(PHILIPS)	27C010	DIP32	
SIGNETICS(PHILIPS)	27C010	PLCC32	PA32PL32D
SIGNETICS(PHILIPS)	27C010	TSOP32	PA32TS20/PA32TS32D-20
SIGNETICS(PHILIPS)	27C256	DIP28	
SIGNETICS(PHILIPS)	27C256	PLCC32	PA32PL28D-YA
SIGNETICS(PHILIPS)	87C51	DIP40	
SIGNETICS(PHILIPS)	87C51	PLCC44	PA44-48U
SIGNETICS(PHILIPS)	87C51FA	DIP40	
SIGNETICS(PHILIPS)	87C51FA	PLCC44	PA44-48U
SIGNETICS(PHILIPS)	87C51FB	DIP40	
SIGNETICS(PHILIPS)	87C51FB	PLCC44	PA44-48U
SIGNETICS(PHILIPS)	87C51FC	DIP40	
SIGNETICS(PHILIPS)	87C51FC	PLCC44	PA44-48U
SIGNETICS(PHILIPS)	87C52	DIP40	
SIGNETICS(PHILIPS)	87C52	PLCC44	PA44-48U
SIGNETICS(PHILIPS)	87C524	DIP40	
SIGNETICS(PHILIPS)	87C524	PLCC44	PA44-48U
SIGNETICS(PHILIPS)	87C528	DIP40	
SIGNETICS(PHILIPS)	87C528	PLCC44	PA44-48U
SIGNETICS(PHILIPS)	87C550	DIP40	
SIGNETICS(PHILIPS)	87C550	PLCC44	PA44-48U
SIGNETICS(PHILIPS)	87C552	PLCC68	PA552-68
SIGNETICS(PHILIPS)	87C554	PLCC68	PA552-68
SIGNETICS(PHILIPS)	87C575	DIP40	
SIGNETICS(PHILIPS)	87C575	PLCC44	PA44-48U
SIGNETICS(PHILIPS)	87C576	DIP40	
SIGNETICS(PHILIPS)	87C576	PLCC44	PA44-48U
SIGNETICS(PHILIPS)	87C592	DIP40	PA592-68
SIGNETICS(PHILIPS)	87C652	DIP40	
SIGNETICS(PHILIPS)	87C652	PLCC44	PA44-48U
SIGNETICS(PHILIPS)	87C654	DIP40	
SIGNETICS(PHILIPS)	87C654	PLCC44	PA44-48U
SIGNETICS(PHILIPS)	87C749	DIP28	
SIGNETICS(PHILIPS)	87C749	PLCC28	PA28PL28D
SIGNETICS(PHILIPS)	87C750	DIP24	
SIGNETICS(PHILIPS)	87C750	PLCC28	PA28PL28D
SIGNETICS(PHILIPS)	87C751	DIP24	
SIGNETICS(PHILIPS)	87C751	PLCC28	PA28PL28D
SIGNETICS(PHILIPS)	87C752	DIP28	
SIGNETICS(PHILIPS)	87C752	PLCC28	PA28PL28D
SIGNETICS(PHILIPS)	89C52	DIP40	
SIGNETICS(PHILIPS)	89C52	PLCC44	PA44-48U
SIGNETICS(PHILIPS)	89C52	TQFP44	PA44QF44D
SIGNETICS(PHILIPS)	89C536	PLCC44	PA44-48U
SIGNETICS(PHILIPS)	89C536	TQFP44	PA44QF44D
SIGNETICS(PHILIPS)	89C538	PLCC44	PA44-48U
SIGNETICS(PHILIPS)	89C538	TQFP44	PA44QF44D
SIGNETICS(PHILIPS)	89C54	DIP40	
SIGNETICS(PHILIPS)	89C54	PLCC44	PA44-48U
SIGNETICS(PHILIPS)	89C54	TQFP44	PA44QF44D
SIGNETICS(PHILIPS)	89C738	DIP40	
SIGNETICS(PHILIPS)	89C738	PLCC44	PA44-48U
SIGNETICS(PHILIPS)	89C738	TQFP44	PA44QF44D
SIGNETICS(PHILIPS)	PLC18V8Z	DIP20	
SIGNETICS(PHILIPS)	PLC18V8Z	PLCC20	PA20LC20D[Dead Bug]
SILICON7	SV5C2832UCA	BGA72	PA72BGA48DE
SILICON7	SV5C2832UCR	BGA72	PA72BGA48DE

SILICON7	SV5C2832UDR	BGA72	PA72BGA48DE
SILICON7	SV5C3238UBA	BGA72	PA72BGA48DD-TO-8X11
SILICON7	SV5C3238UTA	BGA72	PA72BGA48DD-TO-8X11
SILICON7	SV5C6416UDA	BGA72	PA72BGA48DD-TO-8X11
SILICON7	SV5D2832UDA	BGA88	PA88BGA48DA-YO-8X10
SILICON7	SV5D6416UBA	BGA88	PA88BGA48DA-YO-8X10
SILICON7	SV5D6416UTA	BGA88	PA88BGA48DA-YO-8X10
SILICON7	SV6C2832UBA	BGA72	PA72BG48DK
SILICON7	SV6C2832UTA	BGA72	PA72BG48DK
SILICON7	SV6C2864UBA	BGA72	PA72BG48DK
SILICON7	SV6C2864UTA	BGA72	PA72BG48DK
SILICON7	SV6C6416UBA	BGA72	PA72BG48DK
SILICON7	SV6C6416UTA	BGA72	PA72BG48DK
SILICON7	SV6C6432UBA	BGA72	PA72BG48DK
SILICON7	SV6C6432UTA	BGA72	PA72BG48DK
SILICONLABS	C8051F320	QFP32	PA32TQ32D
SIMTEK	STK12C68	SOP28	PA28SO28DA-EC-330
SIMTEK	STK20C04	DIP28	
SMOS	SPM27128	DIP28	
SMOS	SPM27128C	DIP28	
SMOS	SPM27C256	DIP28	
SMOS	SPM27C64	DIP28	
SMOS	SPM27C64H	DIP28	
SMOS	SPM2864C	DIP28	
SPANSION	S25FL001D	SOP8	PA16SO16D-EO-150/PA8SO8D-150
SPANSION	S25FL001D	WSON8	PA8SON8D(6x5)
SPANSION	S25FL002D	SOP8	PA16SO16D-EO-150/PA8SO8D-150
SPANSION	S25FL002D	SOP8	PA20SO20D-EO-210
SPANSION	S25FL002D	WSON8	PA8SON8D(6x5)
SPANSION	S25FL004A	SOP8	PA20SO20D-EO-210
SPANSION	S25FL004A	WSON8	PA8SON8D(6x5)
SPANSION	S25FL004D	SOP8	PA20SO20D-EO-210
SPANSION	S25FL004D	WSON8	PA8SON8D(6x5)
SPANSION	S25FL004K	SOP8	PA16SO16D-EO-150/PA8SO8D-150
SPANSION	S25FL004K	SOP8	PA20SO20D-EO-210
SPANSION	S25FL004K(Quad_IO)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
SPANSION	S25FL004K(Quad_IO)	SOP8	PA20SO20D-EO-210
SPANSION	S25FL008A	SOP8	PA20SO20D-EO-210
SPANSION	S25FL008A	WSON8	PA8SON8D(6x5)
SPANSION	S25FL008K	SOP8	PA16SO16D-EO-150/PA8SO8D-150
SPANSION	S25FL008K	SOP8	PA20SO20D-EO-210
SPANSION	S25FL008K(Quad_IO)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
SPANSION	S25FL008K(Quad_IO)	SOP8	PA20SO20D-EO-210
SPANSION	S25FL016A	SOP16	PA28SO28D-EO-300
SPANSION	S25FL016A	SOP8	PA20SO20D-EO-210
SPANSION	S25FL016A	WSON8	PA8SON8DA(8x6)
SPANSION	S25FL016K	SOP8	PA16SO16D-EO-150/PA8SO8D-150
SPANSION	S25FL016K	SOP8	PA20SO20D-EO-210
SPANSION	S25FL016K(Quad_IO)	SOP8	PA16SO16D-EO-150/PA8SO8D-150
SPANSION	S25FL016K(Quad_IO)	SOP8	PA20SO20D-EO-210
SPANSION	S25FL032A	SOP16	PA28SO28D-EO-300
SPANSION	S25FL032K	SOP8	PA20SO20D-EO-210
SPANSION	S25FL032K(Quad_IO)	SOP8	PA20SO20D-EO-210
SPANSION	S25FL032P	SOP16	PA28SO28D-EO-300
SPANSION	S25FL032P	SOP8	PA20SO20D-EO-210
SPANSION	S25FL032P	TFBGA24	PA24BG24D(6x8mm)5x5
SPANSION	S25FL032P	WSON8	PA8SON8D(6x5)
SPANSION	S25FL032P	WSON8	PA8SON8DA(8x6)
SPANSION	S25FL032P(Quad_IO)	SOP16	PA28SO28D-EO-300
SPANSION	S25FL032P(Quad_IO)	SOP8	PA20SO20D-EO-210
SPANSION	S25FL032P(Quad_IO)	TFBGA24	PA24BG24D(6x8mm)5x5
SPANSION	S25FL032P(Quad_IO)	WSON8	PA8SON8D(6x5)
SPANSION	S25FL032P(Quad_IO)	WSON8	PA8SON8DA(8x6)
SPANSION	S25FL040Axxxxx00	SOP8	PA16SO16D-EO-150/PA8SO8D-150
SPANSION	S25FL040Axxxxx00	SOP8	PA20SO20D-EO-210
SPANSION	S25FL040Axxxxx00	WSON8	PA8SON8D(6x5)
SPANSION	S25FL040Axxxxx01	SOP8	PA16SO16D-EO-150/PA8SO8D-150
SPANSION	S25FL040Axxxxx01	SOP8	PA20SO20D-EO-210
SPANSION	S25FL040Axxxxx01	WSON8	PA8SON8D(6x5)
SPANSION	S25FL040Axxxxx02	SOP8	PA16SO16D-EO-150/PA8SO8D-150
SPANSION	S25FL040Axxxxx02	SOP8	PA20SO20D-EO-210
SPANSION	S25FL040Axxxxx02	WSON8	PA8SON8D(6x5)
SPANSION	S25FL064A	SOP16	PA28SO28D-EO-300

SPANSION	S25FL064K	SOP16	PA28SO28D-EO-300
SPANSION	S25FL064K	SOP8	PA20SO20D-EO-210
SPANSION	S25FL064K(Quad_IO)	SOP16	PA28SO28D-EO-300
SPANSION	S25FL064K(Quad_IO)	SOP8	PA20SO20D-EO-210
SPANSION	S25FL064P	SOP16	PA28SO28D-EO-300
SPANSION	S25FL064P	TFBGA24	PA24BG24D(6x8mm)5x5
SPANSION	S25FL064P	WSON8	PA8SON8DA(8x6)
SPANSION	S25FL064P(Quad_IO)	SOP16	PA28SO28D-EO-300
SPANSION	S25FL064P(Quad_IO)	TFBGA24	PA24BG24D(6x8mm)5x5
SPANSION	S25FL064P(Quad_IO)	WSON8	PA8SON8DA(8x6)
SPANSION	S25FL116K	SOP16	PA28SO28D-EO-300
SPANSION	S25FL116K	SOP8	PA16SO16D-EO-150/PA8SO8D-150
SPANSION	S25FL116K	SOP8	PA20SO20D-EO-210
SPANSION	S25FL116K	TFBGA24	PA24BG24D(6x8mm)5x5
SPANSION	S25FL116K	WSON8	PA8SON8D(6x5)
SPANSION	S25FL127S	SOP16	PA28SO28D-EO-300
SPANSION	S25FL127S	SOP8	PA20SO20D-EO-210
SPANSION	S25FL127S	TFBGA24	PA24BG24D(6x8mm)5x5
SPANSION	S25FL127S	WSON8	PA8SON8D(6x5)
SPANSION	S25FL127S(Quad_IO)	SOP16	PA28SO28D-EO-300
SPANSION	S25FL127S(Quad_IO)	SOP8	PA20SO20D-EO-210
SPANSION	S25FL127S(Quad_IO)	WSON8	PA8SON8D(6x5)
SPANSION	S25FL128K	SOP16	PA28SO28D-EO-300
SPANSION	S25FL128K(Quad_IO)	SOP16	PA28SO28D-EO-300
SPANSION	S25FL128P	SOP16	PA28SO28D-EO-300
SPANSION	S25FL128P	WSON8	PA8SON8DA(8x6)
SPANSION	S25FL128S	SOP16	PA28SO28D-EO-300
SPANSION	S25FL128S	TFBGA24	PA24BG24D(6x8mm)5x5
SPANSION	S25FL128S	WSON8	PA8SON8DA(8x6)
SPANSION	S25FL128S(Quad_IO)	SOP16	PA28SO28D-EO-300
SPANSION	S25FL128S(Quad_IO)	WSON8	PA8SON8DA(8x6)
SPANSION	S25FL129P	SOP16	PA28SO28D-EO-300
SPANSION	S25FL129P	TFBGA24	PA24BG24D(6x8mm)5x5
SPANSION	S25FL129P	WSON8	PA8SON8DA(8x6)
SPANSION	S25FL129P(Quad_IO)	SOP16	PA28SO28D-EO-300
SPANSION	S25FL129P(Quad_IO)	TFBGA24	PA24BG24D(6x8mm)5x5
SPANSION	S25FL129P(Quad_IO)	WSON8	PA8SON8DA(8x6)
SPANSION	S25FL132K	SOP16	PA28SO28D-EO-300
SPANSION	S25FL132K	SOP8	PA16SO16D-EO-150/PA8SO8D-150
SPANSION	S25FL132K	SOP8	PA20SO20D-EO-210
SPANSION	S25FL132K	TFBGA24	PA24BG24D(6x8mm)5x5
SPANSION	S25FL132K	WSON8	PA8SON8D(6x5)
SPANSION	S25FL164K	SOP16	PA28SO28D-EO-300
SPANSION	S25FL164K	SOP8	PA16SO16D-EO-150/PA8SO8D-150
SPANSION	S25FL164K	SOP8	PA20SO20D-EO-210
SPANSION	S25FL164K	TFBGA24	PA24BG24D(6x8mm)5x5
SPANSION	S25FL164K	WSON8	PA8SON8D(6x5)
SPANSION	S25FL204K	SOP8	PA16SO16D-EO-150/PA8SO8D-150
SPANSION	S25FL204K	SOP8	PA20SO20D-EO-210
SPANSION	S25FL208K	SOP8	PA16SO16D-EO-150/PA8SO8D-150
SPANSION	S25FL208K	SOP8	PA20SO20D-EO-210
SPANSION	S25FL216K	SOP8	PA16SO16D-EO-150/PA8SO8D-150
SPANSION	S25FL216K	SOP8	PA20SO20D-EO-210
SPANSION	S25FL256S	SOP16	PA28SO28D-EO-300
SPANSION	S25FL256S	TFBGA24	PA24BG24D(6x8mm)5x5
SPANSION	S25FL256S	WSON8	PA8SON8DA(8x6)
SPANSION	S25FL256S(Quad_IO)	SOP16	PA28SO28D-EO-300
SPANSION	S25FL256S(Quad_IO)	WSON8	PA8SON8DA(8x6)
SPANSION	S25FL512S	SOP16	PA28SO28D-EO-300
SPANSION	S25FL512S	TFBGA24	PA24BG24D(6x8mm)5x5
SPANSION	S25FL512S(Quad_IO)	SOP16	PA28SO28D-EO-300
SPANSION	S29AL002-B-01	BGA48	HA48BG48DAI
SPANSION	S29AL002-B-01	BGA48	PA48BG48DW
SPANSION	S29AL002-B-02	BGA48	HA48BG48DAI
SPANSION	S29AL002-B-02	BGA48	PA48BG48DW
SPANSION	S29AL002-S-01	SOP44	PA44SO44D
SPANSION	S29AL002-S-02	SOP44	PA44SO44D
SPANSION	S29AL002-T-01	TSOP48	PA48TS48D
SPANSION	S29AL002-T-02	TSOP48	PA48TS48D
SPANSION	S29AL004-B-01	BGA48	HA48BG48DAI
SPANSION	S29AL004-B-01	BGA48	PA48BG48DW
SPANSION	S29AL004-B-02	BGA48	HA48BG48DAI
SPANSION	S29AL004-B-02	BGA48	PA48BG48DW

SPANSION	S29AL004-S-01	SOP44	PA44SO44D
SPANSION	S29AL004-S-02	SOP44	PA44SO44D
SPANSION	S29AL004-T-01	TSOP48	PA48TS48D
SPANSION	S29AL004-T-02	TSOP48	PA48TS48D
SPANSION	S29AL008-B-01	BGA48	HA48BG48DAI
SPANSION	S29AL008-B-01	BGA48	PA48BG48DW
SPANSION	S29AL008-B-02	BGA48	HA48BG48DAI
SPANSION	S29AL008-B-02	BGA48	PA48BG48DW
SPANSION	S29AL008D-B-01	BGA48	PA48BG48DAI
SPANSION	S29AL008D-B-02	BGA48	PA48BG48DAI
SPANSION	S29AL008D-B-R1	BGA48	PA48BG48DAI
SPANSION	S29AL008D-B-R2	BGA48	PA48BG48DAI
SPANSION	S29AL008D-M-01	SOP44	PA44SO44D
SPANSION	S29AL008D-M-02	SOP44	PA44SO44D
SPANSION	S29AL008D-M-R1	SOP44	PA44SO44D
SPANSION	S29AL008D-M-R2	SOP44	PA44SO44D
SPANSION	S29AL008D-T-01	TSOP48	PA48TS48D
SPANSION	S29AL008D-T-02	TSOP48	PA48TS48D
SPANSION	S29AL008D-T-R1	TSOP48	PA48TS48D
SPANSION	S29AL008D-T-R2	TSOP48	PA48TS48D
SPANSION	S29AL008J-B-01	BGA48	HA48BG48DAI
SPANSION	S29AL008J-B-01	BGA48	PA48BG48DW
SPANSION	S29AL008J-B-02	BGA48	HA48BG48DAI
SPANSION	S29AL008J-B-02	BGA48	PA48BG48DW
SPANSION	S29AL008J-B-03	BGA48	HA48BG48DAI
SPANSION	S29AL008J-B-03	BGA48	PA48BG48DW
SPANSION	S29AL008J-B-04	BGA48	HA48BG48DAI
SPANSION	S29AL008J-B-04	BGA48	PA48BG48DW
SPANSION	S29AL008J-T-01	TSOP48	PA48TS48D1
SPANSION	S29AL008J-T-02	TSOP48	PA48TS48D1
SPANSION	S29AL008J-T-03	TSOP48	PA48TS48D1
SPANSION	S29AL008J-T-04	TSOP48	PA48TS48D1
SPANSION	S29AL008-S-01	SOP44	PA44SO44D
SPANSION	S29AL008-S-02	SOP44	PA44SO44D
SPANSION	S29AL008-T-01	TSOP48	PA48TS48D
SPANSION	S29AL008-T-02	TSOP48	PA48TS48D
SPANSION	S29AL016DB	TSOP48	PA48TS48D
SPANSION	S29AL016D-M-02	SOP44	PA44SO44D
SPANSION	S29AL016DT	TSOP48	PA48TS48D
SPANSION	S29AL016J-B-01	BGA48	HA48BG48DAI
SPANSION	S29AL016J-B-01	BGA48	PA48BG48DW
SPANSION	S29AL016J-B-02	BGA48	HA48BG48DAI
SPANSION	S29AL016J-B-02	BGA48	PA48BG48DW
SPANSION	S29AL016J-B-03	BGA48	HA48BG48DAI
SPANSION	S29AL016J-B-03	BGA48	PA48BG48DW
SPANSION	S29AL016J-B-04	BGA48	HA48BG48DAI
SPANSION	S29AL016J-B-04	BGA48	PA48BG48DW
SPANSION	S29AL016J-T-01	TSOP48	PA48TS48D1
SPANSION	S29AL016J-T-02	TSOP48	PA48TS48D1
SPANSION	S29AL016J-T-03	TSOP48	PA48TS48D1
SPANSION	S29AL016J-T-04	TSOP48	PA48TS48D1
SPANSION	S29AL016MB	TSOP48	PA48TS48D
SPANSION	S29AL016M-T-01	TSOP48	PA48TS48D
SPANSION	S29AL016M-T-02	TSOP48	PA48TS48D
SPANSION	S29AL016M-T-R1	TSOP48	PA48TS48D
SPANSION	S29AL016M-T-R2	TSOP48	PA48TS48D
SPANSION	S29AL016-S-01	SOP44	PA44SO44D
SPANSION	S29AL016-S-02	SOP44	PA44SO44D
SPANSION	S29AL016-T-01	TSOP48	PA48TS48D
SPANSION	S29AL016-T-02	TSOP48	PA48TS48D
SPANSION	S29AL032D	TSOP40	PA40TS40D
SPANSION	S29AL032D-T-03	TSOP48	PA48TS48D1
SPANSION	S29AL032D-T-04	TSOP48	PA48TS48D1
SPANSION	S29AS008J-B-01	BGA48	HA48BG48DAI
SPANSION	S29AS008J-B-01	BGA48	PA48BG48DW
SPANSION	S29AS008J-B-02	BGA48	HA48BG48DAI
SPANSION	S29AS008J-B-02	BGA48	PA48BG48DW
SPANSION	S29AS008J-T-01	TSOP48	PA48TS48D1
SPANSION	S29AS008J-T-02	TSOP48	PA48TS48D1
SPANSION	S29AS016J-B-01	BGA48	HA48BG48DAI
SPANSION	S29AS016J-B-01	BGA48	PA48BG48DW
SPANSION	S29AS016J-B-02	BGA48	HA48BG48DAI
SPANSION	S29AS016J-B-02	BGA48	PA48BG48DW

SPANSION	S29AS016J-T-01	TSOP48	PA48TS48D1
SPANSION	S29AS016J-T-02	TSOP48	PA48TS48D1
SPANSION	S29GL016A-TF-R1	TSOP48	PA48TS48D1
SPANSION	S29GL016A-TF-R2	TSOP48	PA48TS48D1
SPANSION	S29GL01GPxxFxxS7	BGA64	PA64BG48DR
SPANSION	S29GL01GPxxFxxS8	BGA64	PA64BG48DR
SPANSION	S29GL01GPxxTxx01	TSOP56	HA56TS48DI
SPANSION	S29GL01GPxxTxx02	TSOP56	HA56TS48DI
SPANSION	S29GL01GPxxTxxR1	TSOP56	HA56TS48DI
SPANSION	S29GL01GPxxTxxV1	TSOP56	HA56TS48DI
SPANSION	S29GL01GPxxTxxV2	TSOP56	HA56TS48DI
SPANSION	S29GL01GRxxTxx01	TSOP56	HA56TS48DI
SPANSION	S29GL01GRxxTxx02	TSOP56	HA56TS48DI
SPANSION	S29GL01GS-DH-01	BGA64	NA64BG48DY
SPANSION	S29GL01GS-DH-S5	BGA64	NA64BG48DY
SPANSION	S29GL01GS-DH-S6	BGA64	NA64BG48DY
SPANSION	S29GL01GS-TF-01	TSOP56	HA56TS48DI
SPANSION	S29GL01GS-TF-02	TSOP56	HA56TS48DI
SPANSION	S29GL01GS-TF-V1	TSOP56	HA56TS48DI
SPANSION	S29GL01GS-TF-V2	TSOP56	HA56TS48DI
SPANSION	S29GL032A-FF-S1	BGA64	PA64BG48DG
SPANSION	S29GL032A-FF-S2	BGA64	PA64BG48DG
SPANSION	S29GL032A-FF-S3	BGA64	PA64BG48DH
SPANSION	S29GL032A-FF-S4	BGA64	PA64BG48DH
SPANSION	S29GL032A-TF-R1	TSOP56	PA56TS48DB
SPANSION	S29GL032A-TF-R2	TSOP56	PA56TS48DB
SPANSION	S29GL032A-TF-R3	TSOP48	PA48TS48D1
SPANSION	S29GL032A-TF-R4	TSOP48	PA48TS48D1
SPANSION	S29GL032M-FA-S1	BGA64	PA64BG48DG
SPANSION	S29GL032M-FA-S2	BGA64	PA64BG48DG
SPANSION	S29GL032M-FA-S3	BGA64	PA64BG48DH
SPANSION	S29GL032M-FA-S4	BGA64	PA64BG48DH
SPANSION	S29GL032M-FF-S1	BGA64	PA64BG48DG
SPANSION	S29GL032M-FF-S2	BGA64	PA64BG48DG
SPANSION	S29GL032M-FF-S3	BGA64	PA64BG48DH
SPANSION	S29GL032M-FF-S4	BGA64	PA64BG48DH
SPANSION	S29GL032M-R0	TSOP40	PA40TS40D
SPANSION	S29GL032M-R3	BGA48	PA48BG48DAO/DAO1
SPANSION	S29GL032M-R3	TSOP48	PA48TS48D
SPANSION	S29GL032M-R4	BGA48	PA48BG48DAO/DAO1
SPANSION	S29GL032M-R4	TSOP48	PA48TS48D
SPANSION	S29GL032M-R4(+SecSi)	TSOP48	PA48TS48D
SPANSION	S29GL032M-R5	BGA48	PA48BG48DAO/DAO1
SPANSION	S29GL032M-R5	TSOP48	PA48TS48D
SPANSION	S29GL032M-R6	BGA48	PA48BG48DAO/DAO1
SPANSION	S29GL032M-R6	TSOP48	PA48TS48D
SPANSION	S29GL032N-B-03	BGA48	HA48BG48DAI
SPANSION	S29GL032N-B-03	BGA48	PA48BG48DW
SPANSION	S29GL032N-B-04	BGA48	HA48BG48DAI
SPANSION	S29GL032N-B-04	BGA48	PA48BG48DW
SPANSION	S29GL032N-FF-01	BGA64	PA64BG48DG
SPANSION	S29GL032N-FF-02	BGA64	PA64BG48DG
SPANSION	S29GL032N-FF-03	BGA64	PA64BG48DG
SPANSION	S29GL032N-FF-04	BGA64	PA64BG48DG
SPANSION	S29GL032N-FF-S1	BGA64	PA64BG48DG
SPANSION	S29GL032N-FF-S2	BGA64	PA64BG48DG
SPANSION	S29GL032N-FF-S3	BGA64	PA64BG48DH
SPANSION	S29GL032N-FF-S4	BGA64	PA64BG48DH
SPANSION	S29GL032N-TF-01	TSOP56	PA56TS48DB
SPANSION	S29GL032N-TF-02	TSOP56	PA56TS48DB
SPANSION	S29GL032N-TF-03	TSOP48	PA48TS48D1
SPANSION	S29GL032N-TF-04	TSOP48	PA48TS48D1
SPANSION	S29GL064A-FF-S1	BGA64	PA64BG48DG
SPANSION	S29GL064A-FF-S2	BGA64	PA64BG48DG
SPANSION	S29GL064A-FF-S3	BGA64	PA64BG48DH
SPANSION	S29GL064A-FF-S4	BGA64	PA64BG48DH
SPANSION	S29GL064A-TF-R1	TSOP56	PA56TS48DB
SPANSION	S29GL064A-TF-R2	TSOP56	PA56TS48DB
SPANSION	S29GL064A-TF-R3	TSOP48	PA48TS48D1
SPANSION	S29GL064A-TF-R4	TSOP48	PA48TS48D1
SPANSION	S29GL064A-TF-R6	TSOP48	PA48TS48D1
SPANSION	S29GL064A-TF-R7	TSOP48	PA48TS48D1
SPANSION	S29GL064M-FA-S1	BGA64	PA64BG48DG

SPANSION	S29GL064M-FA-S2	BGA64	PA64BG48DG
SPANSION	S29GL064M-FA-S3	BGA64	PA64BG48DH
SPANSION	S29GL064M-FA-S4	BGA64	PA64BG48DH
SPANSION	S29GL064M-FF-S1	BGA64	PA64BG48DG
SPANSION	S29GL064M-FF-S2	BGA64	PA64BG48DG
SPANSION	S29GL064M-FF-S3	BGA64	PA64BG48DH
SPANSION	S29GL064M-FF-S4	BGA64	PA64BG48DH
SPANSION	S29GL064M-R1	TSOP56	PA56TS48DB
SPANSION	S29GL064M-R2	TSOP56	PA56TS48DB
SPANSION	S29GL064M-R3	TSOP48	PA48TS48D
SPANSION	S29GL064M-R4	TSOP48	PA48TS48D
SPANSION	S29GL064M-R6	TSOP48	PA48TS48D
SPANSION	S29GL064M-R7	TSOP48	PA48TS48D
SPANSION	S29GL064N-B-03	BGA48	HA48BG48DAI
SPANSION	S29GL064N-B-03	BGA48	PA48BG48DW
SPANSION	S29GL064N-B-04	BGA48	HA48BG48DAI
SPANSION	S29GL064N-B-04	BGA48	PA48BG48DW
SPANSION	S29GL064N-FF-01	BGA64	PA64BG48DG
SPANSION	S29GL064N-FF-01	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL064N-FF-02	BGA64	PA64BG48DG
SPANSION	S29GL064N-FF-03	BGA64	PA64BG48DG
SPANSION	S29GL064N-FF-04	BGA64	PA64BG48DG
SPANSION	S29GL064N-FF-R2	BGA64	PA64BG48DG
SPANSION	S29GL064N-FF-S1	BGA64	PA64BG48DG
SPANSION	S29GL064N-FF-S2	BGA64	PA64BG48DG
SPANSION	S29GL064N-FF-S3	BGA64	PA64BG48DH
SPANSION	S29GL064N-FF-S4	BGA64	PA64BG48DH
SPANSION	S29GL064N-TF-02	TSOP56	PA56TS48DB
SPANSION	S29GL064N-TF-03	TSOP48	PA48TS48D1
SPANSION	S29GL064N-TF-04	TSOP48	PA48TS48D1
SPANSION	S29GL064N-TF-06	TSOP48	PA48TS48D1
SPANSION	S29GL064N-TF-07	TSOP48	PA48TS48D1
SPANSION	S29GL064N-TF-R3	TSOP48	PA48TS48D1
SPANSION	S29GL064N-TF-R3(+SecSi)	TSOP48	PA48TS48D1
SPANSION	S29GL064N-TF-R4	TSOP48	PA48TS48D1
SPANSION	S29GL064N-TF-V1	TSOP56	PA56TS48DB
SPANSION	S29GL064S-BH-03	BGA48	HA48BG48DAI
SPANSION	S29GL064S-BH-04	BGA48	HA48BG48DAI
SPANSION	S29GL064S-DH-01	BGA64	NA64BG48DY
SPANSION	S29GL064S-DH-02	BGA64	NA64BG48DY
SPANSION	S29GL064S-DH-03	BGA64	NA64BG48DY
SPANSION	S29GL064S-DH-04	BGA64	NA64BG48DY
SPANSION	S29GL064S-FH-01	BGA64	PA64BG48DG
SPANSION	S29GL064S-FH-02	BGA64	PA64BG48DG
SPANSION	S29GL064S-FH-03	BGA64	PA64BG48DG
SPANSION	S29GL064S-FH-04	BGA64	PA64BG48DG
SPANSION	S29GL128M-R1	TSOP56	PA56TS48DB
SPANSION	S29GL128M-R2	TSOP56	PA56TS48DB
SPANSION	S29GL128NxxFxx01	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL128NxxFxx02	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL128NxxFxxV1	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL128NxxFxxV2	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL128NxxTxx01	TSOP56	PA56TS48DB
SPANSION	S29GL128NxxTxx02	TSOP56	PA56TS48DB
SPANSION	S29GL128NxxTxxR2	TSOP56	PA56TS48DB
SPANSION	S29GL128NxxTxxV1	TSOP56	PA56TS48DB
SPANSION	S29GL128NxxTxxV2	TSOP56	PA56TS48DB
SPANSION	S29GL128P-FF-S0	BGA64	HA64BG48DQ
SPANSION	S29GL128P-FF-S1	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL128P-FF-S2	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL128P-FF-S3	BGA64	HA64BG48DQ
SPANSION	S29GL128P-FF-S4	BGA64	HA64BG48DQ
SPANSION	S29GL128P-FF-S7	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL128P-FF-S9	BGA64	HA64BG48DQ
SPANSION	S29GL128PxxFxx01	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL128PxxFxx02	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL128PxxFxxR1	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL128PxxFxxR2	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL128PxxFxxV1	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL128PxxFxxV2	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL128PxxTxx01	TSOP56	HA56TS48DI
SPANSION	S29GL128PxxTxx02	TSOP56	HA56TS48DI
SPANSION	S29GL128PxxTxxR1	TSOP56	HA56TS48DI



SPANSION	S29GL128PxxTxxR1	TSOP56	PA56TS48DB
SPANSION	S29GL128PxxTxxR1	TSOP56	PA56TS48DC
SPANSION	S29GL128PxxTxxR1	TSOP56	PA56TS48DD
SPANSION	S29GL128PxxTxxR2	TSOP56	HA56TS48DI
SPANSION	S29GL128PxxTxxR2	TSOP56	PA56TS48DB
SPANSION	S29GL128PxxTxxR2	TSOP56	PA56TS48DC
SPANSION	S29GL128PxxTxxR2	TSOP56	PA56TS48DD
SPANSION	S29GL128PxxTxxV1	TSOP56	HA56TS48DI
SPANSION	S29GL128PxxTxxV2	TSOP56	HA56TS48DI
SPANSION	S29GL128S-GH-01	BGA56	NA56BG48DU
SPANSION	S29GL128S-GH-02	BGA56	NA56BG48DU
SPANSION	S29GL128S-TF-01	TSOP56	PA56TS48DD
SPANSION	S29GL128S-TF-02	TSOP56	PA56TS48DD
SPANSION	S29GL128S-TF-V1	TSOP56	PA56TS48DD
SPANSION	S29GL128S-TF-V2	TSOP56	PA56TS48DD
SPANSION	S29GL256M-R1	TSOP56	PA56TS48DC
SPANSION	S29GL256M-R2	TSOP56	PA56TS48DC
SPANSION	S29GL256NxxFxlIH	BGA64	HA64BG48DQ
SPANSION	S29GL256NxxFxx01	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL256NxxFxx02	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL256NxxFxxV1	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL256NxxFxxV2	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL256NxxTxx01	TSOP56	PA56TS48DC
SPANSION	S29GL256NxxTxx02	TSOP56	PA56TS48DC
SPANSION	S29GL256NxxTxxR2	TSOP56	PA56TS48DC
SPANSION	S29GL256NxxTxxV1	TSOP56	PA56TS48DC
SPANSION	S29GL256NxxTxxV2	TSOP56	PA56TS48DC
SPANSION	S29GL256P-FF-S0	BGA64	HA64BG48DQ
SPANSION	S29GL256P-FF-S1	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL256P-FF-S2	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL256P-FF-S3	BGA64	HA64BG48DQ
SPANSION	S29GL256P-FF-S4	BGA64	HA64BG48DQ
SPANSION	S29GL256P-FF-S7	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL256P-FF-S8	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL256P-FF-S9	BGA64	HA64BG48DQ
SPANSION	S29GL256PxxFxx01	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL256PxxFxx02	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL256PxxFxxV1	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL256PxxFxxV2	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL256PxxTxx01	TSOP56	HA56TS48DI
SPANSION	S29GL256PxxTxx01	TSOP56	PA56TS48DD
SPANSION	S29GL256PxxTxx02	TSOP56	HA56TS48DI
SPANSION	S29GL256PxxTxx02	TSOP56	PA56TS48DD
SPANSION	S29GL256PxxTxxR1	TSOP56	HA56TS48DI
SPANSION	S29GL256PxxTxxR1	TSOP56	PA56TS48DD
SPANSION	S29GL256PxxTxxR2	TSOP56	HA56TS48DI
SPANSION	S29GL256PxxTxxR2	TSOP56	PA56TS48DD
SPANSION	S29GL256PxxTxxV1	TSOP56	HA56TS48DI
SPANSION	S29GL256PxxTxxV1	TSOP56	PA56TS48DD
SPANSION	S29GL256PxxTxxV2	TSOP56	HA56TS48DI
SPANSION	S29GL256PxxTxxV2	TSOP56	PA56TS48DD
SPANSION	S29GL256S-DH-S6	BGA64	NA64BG48DY
SPANSION	S29GL256S-FH-S6	BGA64	PA64BG48DR
SPANSION	S29GL256S-GH-01	BGA56	NA56BG48DU
SPANSION	S29GL256S-GH-02	BGA56	NA56BG48DU
SPANSION	S29GL256S-TF-01	TSOP56	PA56TS48DD
SPANSION	S29GL256S-TF-02	TSOP56	PA56TS48DD
SPANSION	S29GL256S-TF-V1	TSOP56	PA56TS48DD
SPANSION	S29GL256S-TF-V2	TSOP56	PA56TS48DD
SPANSION	S29GL512NxxFxx01	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL512NxxFxx02	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL512NxxFxxV1	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL512NxxFxxV2	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL512NxxTxx01	TSOP56	PA56TS48DD
SPANSION	S29GL512NxxTxx02	TSOP56	PA56TS48DD
SPANSION	S29GL512NxxTxxV1	TSOP56	PA56TS48DD
SPANSION	S29GL512NxxTxxV2	TSOP56	PA56TS48DD
SPANSION	S29GL512P-FF-S1	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL512P-FF-S1	BGA64	PA64BG48DR
SPANSION	S29GL512P-FF-S2	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL512P-FF-S2	BGA64	PA64BG48DR
SPANSION	S29GL512P-FF-S7	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL512P-FF-S7	BGA64	PA64BG48DR

SPANSION	S29GL512P-FF-S8	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL512P-FF-S8	BGA64	PA64BG48DR
SPANSION	S29GL512P-TF-R1	TSOP56	HA56TS48DI
SPANSION	S29GL512P-TF-R1	TSOP56	PA56TS48DD
SPANSION	S29GL512PxxFxx01	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL512PxxFxx01	BGA64	PA64BG48DR
SPANSION	S29GL512PxxFxx02	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL512PxxFxx02	BGA64	PA64BG48DR
SPANSION	S29GL512PxxFxxV1	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL512PxxFxxV1	BGA64	PA64BG48DR
SPANSION	S29GL512PxxFxxV2	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
SPANSION	S29GL512PxxFxxV2	BGA64	PA64BG48DR
SPANSION	S29GL512PxxTxx01	TSOP56	HA56TS48DI
SPANSION	S29GL512PxxTxx02	TSOP56	HA56TS48DI
SPANSION	S29GL512PxxTxxV1	TSOP56	HA56TS48DI
SPANSION	S29GL512PxxTxxV2	TSOP56	HA56TS48DI
SPANSION	S29GL512RxxTxx01	TSOP56	HA56TS48DI
SPANSION	S29GL512RxxTxx01	TSOP56	PA56TS48DD
SPANSION	S29GL512RxxTxx02	TSOP56	HA56TS48DI
SPANSION	S29GL512RxxTxx02	TSOP56	PA56TS48DD
SPANSION	S29GL512RxxTxxR1	TSOP56	HA56TS48DI
SPANSION	S29GL512RxxTxxR1	TSOP56	PA56TS48DD
SPANSION	S29GL512S-DH-01	BGA64	NA64BG48DY
SPANSION	S29GL512S-FH-S6	BGA64	PA64BG48DR
SPANSION	S29GL512S-TF-01	TSOP56	PA56TS48DD
SPANSION	S29GL512S-TF-02	TSOP56	PA56TS48DD
SPANSION	S29GL512S-TF-V1	TSOP56	PA56TS48DD
SPANSION	S29GL512S-TF-V2	TSOP56	PA56TS48DD
SPANSION	S29JL032H-01	TSOP48	PA48TS48D1
SPANSION	S29JL032H-02	TSOP48	PA48TS48D1
SPANSION	S29JL032H-21	TSOP48	PA48TS48D1
SPANSION	S29JL032H-22	TSOP48	PA48TS48D1
SPANSION	S29JL032H-31	TSOP48	PA48TS48D1
SPANSION	S29JL032H-32	TSOP48	PA48TS48D1
SPANSION	S29JL032H-41	TSOP48	PA48TS48D1
SPANSION	S29JL032H-42	TSOP48	PA48TS48D1
SPANSION	S29JL032J-01	TSOP48	PA48TS48D1
SPANSION	S29JL032J-02	TSOP48	PA48TS48D1
SPANSION	S29JL032J-21	TSOP48	PA48TS48D1
SPANSION	S29JL032J-22	TSOP48	PA48TS48D1
SPANSION	S29JL032J-31	TSOP48	PA48TS48D1
SPANSION	S29JL032J-32	TSOP48	PA48TS48D1
SPANSION	S29JL032J-41	TSOP48	PA48TS48D1
SPANSION	S29JL032J-42	TSOP48	PA48TS48D1
SPANSION	S29JL064H	TSOP48	PA48TS48D1
SPANSION	S29PL032J12	BGA48	HA48BG48DAS
SPANSION	S34ML02G100T	TSOP48	PA48TS48D
SPANSION	S34ML04G100T	TSOP48	PA48TS48D
SPANSION	S71GL032N	BGA56	HA56BG48DH
SPANSION	S71GL064N	BGA56	HA56BG48DH
SPANSION	S71JL064HB0	BGA73	PA73BGA48DC-YO-8X11.6
SPANSION	S71JL128HB0	BGA73	PA73BGA48DC-YO-8X11.6
SPANSION	S71PL032JA0	BGA56	HA56BG48DH
SPANSION	S71PL064JA0	BGA56	HA56BG48DH
SPANSION	S71PL127NB0	BGA64	HA64BG48DF
SPANSION	S71PL127NC0	BGA64	HA64BG48DF
SPANSION	S71PL129JA0	BGA73	PA73BGA48DC-YO-8X11.6
SPANSION	S71PL129JB0	BGA64	HA64BG48DF
SPANSION	S71PL129JC0	BGA64	HA64BG48DF
SPANSION	S99PL193JC0	BGA73	PA73BG48DG
SST	65P542R	SOIC28	PA28SO28D-EO-300
SST	89C54	DIP40	
SST	89C54	PLCC44	PA44-48U
SST	89C54	QFP44	PA44QF44D
SST	89C58	DIP40	
SST	89C58	PLCC44	PA44-48U
SST	89C58	QFP44	PA44QF44D
SST	89C59	DIP40	
SST	89C59	PLCC44	PA44-48U
SST	89C59	QFP44	PA44QF44D
SST	89E516RD	DIP40	
SST	89E516RD	PLCC44	PA44-48U
SST	89E516RD	TQFP44	PA44QF44D

SST	89E516RD2	PLCC44	PA44-48U
SST	89E516RD2	TQFP44	PA44QF44D
SST	89E52RD	DIP40	
SST	89E52RD	PLCC44	PA44-48U
SST	89E52RD	TQFP44	PA44QF44D
SST	89E52RD2	PLCC44	PA44-48U
SST	89E52RD2	TQFP44	PA44QF44D
SST	89E54RD	DIP40	
SST	89E54RD	PLCC44	PA44-48U
SST	89E54RD	TQFP44	PA44QF44D
SST	89E54RD2	PLCC44	PA44-48U
SST	89E54RD2	TQFP44	PA44QF44D
SST	89E554RC	DIP40	
SST	89E554RC	PLCC44	PA44-48U
SST	89E564RD	DIP40	
SST	89E564RD	PLCC44	PA44-48U
SST	89E564RD	WQFN40	PA40WQ40D
SST	89E58RD	DIP40	
SST	89E58RD	PLCC44	PA44-48U
SST	89E58RD	TQFP44	PA44QF44D
SST	89E58RD2	PLCC44	PA44-48U
SST	89E58RD2	TQFP44	PA44QF44D
SST	89F54	DIP40	
SST	89F54	PLCC44	PA44-48U
SST	89F58	DIP40	
SST	89F58	PLCC44	PA44-48U
SST	89V516RD	DIP40	
SST	89V516RD	PLCC44	PA44-48U
SST	89V516RD	TQFP44	PA44QF44D
SST	89V516RD2	PLCC44	PA44-48U
SST	89V516RD2	TQFP44	PA44QF44D
SST	89V52RD	DIP40	
SST	89V52RD	PLCC44	PA44-48U
SST	89V52RD	QFP44	PA44QF44D
SST	89V52RD2	PLCC44	PA44-48U
SST	89V52RD2	TQFP44	PA44QF44D
SST	89V54RD	DIP40	
SST	89V54RD	PLCC44	PA44-48U
SST	89V54RD	TQFP44	PA44QF44D
SST	89V54RD2	PLCC44	PA44-48U
SST	89V54RD2	TQFP44	PA44QF44D
SST	89V554RC	DIP40	
SST	89V554RC	PLCC44	PA44-48U
SST	89V564RD	DIP40	
SST	89V564RD	PLCC44	PA44-48U
SST	89V564RD	WQFN40	PA40WQ40D
SST	89V58RD	DIP40	
SST	89V58RD	PLCC44	PA44-48U
SST	89V58RD	TQFP44	PA44QF44D
SST	89V58RD2	PLCC44	PA44-48U
SST	89V58RD2	TQFP44	PA44QF44D
SST	PH28EE011	DIP32	
SST	SST25LF020A	SOIC8	PA16SO16D-EO-150
SST	SST25LF040A	SOIC8	PA20SO20D-EO-210
SST	SST25LF080A	SOIC8	PA20SO20D-EO-210
SST	SST25VF010	SOIC8	PA16SO16D-EO-150
SST	SST25VF010	WSON8	PA8SON8D(6x5)
SST	SST25VF010A	SOIC8	PA16SO16D-EO-150
SST	SST25VF010A	WSON8	PA8SON8D(6x5)
SST	SST25VF016B	SOIC8	PA20SO20D-EO-210
SST	SST25VF016B	WSON8	PA8SON8D(6x5)
SST	SST25VF020	SOIC8	PA16SO16D-EO-150
SST	SST25VF020	WSON8	PA8SON8D(6x5)
SST	SST25VF020B	SOP8	PA16SO16D-EO-150/PA8SO8D-150
SST	SST25VF020B	USON8	PA8SON8D(2x3)
SST	SST25VF020B	WSON8	PA8SON8D(6x5)
SST	SST25VF032B	SOIC8	PA20SO20D-EO-210
SST	SST25VF032B	SOP16	PA20SO20D-EO-210
SST	SST25VF040	SOIC8	PA20SO20D-EO-210
SST	SST25VF040	WSON8	PA8SON8D(6x5)
SST	SST25VF040B	SOIC8	PA20SO20D-EO-210
SST	SST25VF040B	WSON8	PA8SON8D(6x5)
SST	SST25VF064C	SOP16	PA28SO28D-EO-300

SST	SST25VF064C-S3AE	SOIC8	PA20SO20D-EO-210
SST	SST25VF080B	SOIC8	PA20SO20D-EO-210
SST	SST25VF080B	WSON8	PA8SON8D(6x5)
SST	SST25VF512	SOIC8	PA16SO16D-EO-150
SST	SST25VF512	WSON8	PA8SON8D(6x5)
SST	SST25VF512A	SOIC8	PA16SO16D-EO-150
SST	SST25VF512A	WSON8	PA8SON8D(6x5)
SST	SST25WF010	SOIC8	PA16SO16D-EO-150
SST	SST25WF010	WSON8	PA8SON8D(6x5)
SST	SST25WF020	SOIC8	PA16SO16D-EO-150
SST	SST25WF020	WSON8	PA8SON8D(6x5)
SST	SST25WF040	SOIC8	PA16SO16D-EO-150
SST	SST25WF040	SOIC8	PA20SO20D-EO-210
SST	SST25WF040	WSON8	PA8SON8D(6x5)
SST	SST25WF080	SOIC8	PA16SO16D-EO-150
SST	SST25WF080	SOIC8	PA20SO20D-EO-210
SST	SST25WF512	SOIC8	PA16SO16D-EO-150
SST	SST25WF512	WSON8	PA8SON8D(6x5)
SST	SST26VF016	SOIC8	PA20SO20D-EO-210
SST	SST26VF032	SOIC8	PA20SO20D-EO-210
SST	SST27SF010	DIP32	
SST	SST27SF010	PLCC32	PA32PL32D
SST	SST27SF010	TSOP32	PA32TS20/PA32TS32D-20
SST	SST27SF020	DIP32	
SST	SST27SF020	PLCC32	PA32PL32D
SST	SST27SF020	TSOP32	PA32TS20/PA32TS32D-20
SST	SST27SF256	DIP28	
SST	SST27SF512	DIP28	
SST	SST27SF512	PLCC32	PA32PL28D-YA
SST	SST27SF512	sTSOP28	PA28TS28D-EO
SST	SST27VF010	DIP32	
SST	SST27VF010	PLCC32	PA32PL32D
SST	SST27VF010	TSOP32	PA32TS20/PA32TS32D-20
SST	SST27VF020	DIP32	
SST	SST27VF020	PLCC32	PA32PL32D
SST	SST27VF020	TSOP32	PA32TS20/PA32TS32D-20
SST	SST27VF256	DIP28	
SST	SST27VF512	DIP28	
SST	SST27VF512	PLCC32	PA32PL28D-YA
SST	SST27VF512	sTSOP28	PA28TS28D-EO
SST	SST28LF040	DIP32	
SST	SST28LF040	PLCC32	PA32PL32D
SST	SST28LF040	TSOP32	PA32TS20/PA32TS32D-20
SST	SST28SF040	DIP32	
SST	SST28SF040	PLCC32	PA32PL32D
SST	SST28SF040	TSOP32	PA32TS20/PA32TS32D-20
SST	SST28SF040A	DIP32	
SST	SST28SF040A	PLCC32	PA32PL32D
SST	SST28SF040A	TSOP32	PA32TS20/PA32TS32D-20
SST	SST28VF040	DIP32	
SST	SST28VF040	PLCC32	PA32PL32D
SST	SST28VF040	TSOP32	PA32TS20/PA32TS32D-20
SST	SST28VF040A	DIP32	
SST	SST28VF040A	PLCC32	PA32PL32D
SST	SST28VF040A	TSOP32	PA32TS20/PA32TS32D-20
SST	SST29EE010	DIP32	
SST	SST29EE010	PLCC32	PA32PL32D
SST	SST29EE010	TSOP32	PA32TS32D
SST	SST29EE010A	DIP32	
SST	SST29EE010A	PLCC32	PA32PL32D
SST	SST29EE010A	TSOP32	PA32TS32D
SST	SST29EE020	DIP32	
SST	SST29EE020	PLCC32	PA32PL32D
SST	SST29EE020	TSOP32	PA32TS32D
SST	SST29EE020A	DIP32	
SST	SST29EE020A	PLCC32	PA32PL32D
SST	SST29EE020A	TSOP32	PA32TS32D
SST	SST29EE512	DIP32	
SST	SST29EE512	PLCC32	PA32PL32D
SST	SST29EE512	TSOP32	PA32TS20/PA32TS32D-20
SST	SST29EE512A	DIP32	
SST	SST29EE512A	PLCC32	PA32PL32D
SST	SST29EE512A	TSOP32	PA32TS20/PA32TS32D-20

SST	SST29LE010	DIP32	
SST	SST29LE010	PLCC32	PA32PL32D
SST	SST29LE010	TSOP32	PA32TS32D
SST	SST29LE010A	DIP32	
SST	SST29LE010A	PLCC32	PA32PL32D
SST	SST29LE010A	TSOP32	PA32TS32D
SST	SST29LE020	DIP32	
SST	SST29LE020	PLCC32	PA32PL32D
SST	SST29LE020	TSOP32	PA32TS32D
SST	SST29LE020A	DIP32	
SST	SST29LE020A	PLCC32	PA32PL32D
SST	SST29LE020A	TSOP32	PA32TS32D
SST	SST29LE512	DIP32	
SST	SST29LE512	PLCC32	PA32PL32D
SST	SST29LE512	TSOP32	PA32TS32D
SST	SST29LE512A	DIP32	
SST	SST29LE512A	PLCC32	PA32PL32D
SST	SST29LE512A	TSOP32	PA32TS32D
SST	SST29SF010	DIP32	
SST	SST29SF010	PLCC32	PA32PL32D
SST	SST29SF010	TSOP32	PA32TS32D
SST	SST29SF020	DIP32	
SST	SST29SF020	PLCC32	PA32PL32D
SST	SST29SF020	TSOP32	PA32TS32D
SST	SST29SF040	DIP32	
SST	SST29SF040	PLCC32	PA32PL32D
SST	SST29SF040	TSOP32	PA32TS32D
SST	SST29SF512	DIP32	
SST	SST29SF512	PLCC32	PA32PL32D
SST	SST29SF512	TSOP32	PA32TS32D
SST	SST29VE010	DIP32	
SST	SST29VE010	PLCC32	PA32PL32D
SST	SST29VE010	TSOP32	PA32TS32D
SST	SST29VE010A	DIP32	
SST	SST29VE010A	PLCC32	PA32PL32D
SST	SST29VE010A	TSOP32	PA32TS32D
SST	SST29VE020	DIP32	
SST	SST29VE020	PLCC32	PA32PL32D
SST	SST29VE020	TSOP32	PA32TS32D
SST	SST29VE020A	DIP32	
SST	SST29VE020A	PLCC32	PA32PL32D
SST	SST29VE020A	TSOP32	PA32TS32D
SST	SST29VE512	DIP32	
SST	SST29VE512	PLCC32	PA32PL32D
SST	SST29VE512	TSOP32	PA32TS32D
SST	SST29VE512A	DIP32	
SST	SST29VE512A	PLCC32	PA32PL32D
SST	SST29VE512A	TSOP32	PA32TS32D
SST	SST29VF010	DIP32	
SST	SST29VF010	PLCC32	PA32PL32D
SST	SST29VF010	TSOP32	PA32TS32D
SST	SST29VF020	DIP32	
SST	SST29VF020	PLCC32	PA32PL32D
SST	SST29VF020	TSOP32	PA32TS32D
SST	SST29VF040	DIP32	
SST	SST29VF040	PLCC32	PA32PL32D
SST	SST29VF040	TSOP32	PA32TS32D
SST	SST29VF512	DIP32	
SST	SST29VF512	PLCC32	PA32PL32D
SST	SST29VF512	TSOP32	PA32TS32D
SST	SST31LF021	TSOP32	PA32TS32D
SST	SST31LF021	TSOP40	PA40TS14-OT
SST	SST31LF021E	TSOP32	PA32TS32D
SST	SST31LF041	TSOP40	PA40TS14-OT
SST	SST31LF041A	TSOP32	PA32TS32D
SST	SST32HF1622C	BGA62	PA62BGA48D
SST	SST32HF1642	BGA62	PA62BGA48D
SST	SST32HF1642C	BGA62	PA62BGA48D
SST	SST32HF1682C	BGA62	PA62BGA48D
SST	SST32HF402	BGA48	PA48BG48D
SST	SST32HF402	BGA48	PA48BG48DAI
SST	SST32VF201	BGA48	PA48BGA48-SST
SST	SST34HF1621/Polling	BGA56	PA56BGA48D

SST	SST34HF1621/Single	BGA56	PA56BGA48D
SST	SST34HF1621/Toggle	BGA56	PA56BGA48D
SST	SST34HF1621A	BGA62	PA62BGA48D
SST	SST34HF1621A/Polling	BGA56	PA56BGA48D
SST	SST34HF1621A/Toggle	BGA56	PA56BGA48D
SST	SST34HF1621C/Polling	BGA56	PA56BGA48D-1
SST	SST34HF1621C/Single	BGA56	PA56BGA48D-1
SST	SST34HF1621C/Toggle	BGA56	PA56BGA48D-1
SST	SST34HF1621S/Polling	BGA56	PA56BGA48D-1
SST	SST34HF1621S/Toggle	BGA56	PA56BGA48D-1
SST	SST34HF1622	BGA56	PA56BGA48D
SST	SST34HF1622C	BGA56	PA56BGA48D
SST	SST34HF1622C	BGA62	PA62BGA48D
SST	SST34HF1622S	BGA56	PA56BGA48D
SST	SST34HF1622S	BGA62	PA62BGA48D
SST	SST34HF162G	BGA48	PA48BG48DAI
SST	SST34HF1641	BGA56	PA56BGA48D
SST	SST34HF1641	BGA62	PA62BGA48D
SST	SST34HF1641A	BGA56	PA56BGA48D
SST	SST34HF1641A	BGA62	PA62BGA48D
SST	SST34HF1641C	BGA56	PA56BGA48D
SST	SST34HF1641C	BGA62	PA62BGA48D
SST	SST34HF1641D	BGA56	PA56BGA48D
SST	SST34HF1641D	BGA62	PA62BGA48D
SST	SST34HF1641S	BGA56	PA56BGA48D
SST	SST34HF1641S	BGA62	PA62BGA48D
SST	SST34HF1642	BGA56	PA56BGA48D
SST	SST34HF1642C	BGA56	PA56BGA48D1
SST	SST34HF1642C	BGA62	PA62BGA48D1
SST	SST34HF1642D	BGA56	PA56BGA48D
SST	SST34HF1642D	BGA62	PA62BGA48D
SST	SST34HF1642S	BGA56	PA56BGA48D
SST	SST34HF1642S	BGA62	PA62BGA48D
SST	SST34HF164G	BGA48	PA48BG48DAI
SST	SST34HF1681C	BGA56	PA56BGA48D
SST	SST34HF1681C	BGA62	PA62BGA48D
SST	SST34HF1681D	BGA56	PA56BGA48D
SST	SST34HF1681D	BGA62	PA62BGA48D
SST	SST34HF1681J	BGA56	PA56BGA48D-1
SST	SST34HF1682D	BGA56	PA56BGA48D
SST	SST34HF1682D	BGA62	PA62BGA48D
SST	SST34HF3223A	BGA56	PA56BGA48D
SST	SST34HF3243A	BGA56	PA56BGA48D
SST	SST34HF3244C	BGA56	PA56BGA48D1
SST	SST34HF3244C	BGA62	PA62BGA48D1
SST	SST34HF3284	BGA56	PA56BGA48D1
SST	SST34HF3284	BGA62	PA62BGA48D1
SST	SST34HF32A4	BGA56	HA56BGA48D-2
SST	SST34VF1621	BGA56	PA56BGA48D
SST	SST34VF1622	BGA56	PA56BGA48D
SST	SST34VF1641	BGA56	PA56BGA48D
SST	SST34VF1642	BGA56	PA56BGA48D
SST	SST36VF1601	TSOP48	PA48TS48D
SST	SST36VF1601C	BGA48	PA48BG48DAI
SST	SST36VF1601C	TSOP48	PA48TS48D
SST	SST36VF1601C/PA5	BGA48	PA48BG48DAI
SST	SST36VF1601C/PA5	TSOP48	PA48TS48D
SST	SST36VF1601E	BGA48	PA48BG48DAI
SST	SST36VF1601E	TSOP48	PA48TS48D
SST	SST36VF1601G	TSOP48	PA48TS48D1
SST	SST36VF1601H	TSOP48	PA48TS48D
SST	SST36VF1602	TSOP48	PA48TS48D
SST	SST36VF1602C	TSOP48	PA48TS48D
SST	SST36VF1602E	BGA48	PA48BG48DAI
SST	SST36VF1602E	TSOP48	PA48TS48D
SST	SST36VF1602H	TSOP48	PA48TS48D
SST	SST36VF3203	BGA48	PA48BG48DAI
SST	SST36VF3203	TSOP48	PA48TS48D1
SST	SST36VF3204	BGA48	PA48BG48DAI
SST	SST36VF3204	TSOP48	PA48TS48D1
SST	SST37VF010	DIP32	
SST	SST37VF010	PLCC32	PA32PL32D
SST	SST37VF010	TSOP32	PA32TS32D

SST	SST37VF020	DIP32	
SST	SST37VF020	PLCC32	PA32PL32D
SST	SST37VF020	TSOP32	PA32TS32D
SST	SST37VF040	DIP32	
SST	SST37VF040	PLCC32	PA32PL32D
SST	SST37VF040	TSOP32	PA32TS32D
SST	SST37VF080	TSOP48	PA48TS48D
SST	SST37VF512	DIP32	
SST	SST37VF512	PLCC32	PA32PL32D
SST	SST37VF512	TSOP32	PA32TS32D
SST	SST38VF6401	BGA48	HA48BG48DAI
SST	SST38VF6401	BGA48	PA48BG48DW
SST	SST38VF6401	TSOP48	PA48TS48D1
SST	SST38VF6402	BGA48	HA48BG48DAI
SST	SST38VF6402	BGA48	PA48BG48DW
SST	SST38VF6402	TSOP48	PA48TS48D1
SST	SST38VF6403	BGA48	HA48BG48DAI
SST	SST38VF6403	BGA48	PA48BG48DW
SST	SST38VF6403	TSOP48	PA48TS48D1
SST	SST38VF6404	BGA48	HA48BG48DAI
SST	SST38VF6404	BGA48	PA48BG48DW
SST	SST38VF6404	TSOP48	PA48TS48D1
SST	SST39LF010	DIP32	
SST	SST39LF010	PLCC32	PA32PL32D
SST	SST39LF010	TSOP32	PA32TS32D
SST	SST39LF010	WFBGA34	PA48WFB32D
SST	SST39LF020	DIP32	
SST	SST39LF020	PLCC32	PA32PL32D
SST	SST39LF020	TSOP32	PA32TS32D
SST	SST39LF040	DIP32	
SST	SST39LF040	PLCC32	PA32PL32D
SST	SST39LF040	TSOP32	PA32TS32D
SST	SST39LF100	TSOP40	PA40TS14-OT
SST	SST39LF200A	TSOP48	PA48TS48D1
SST	SST39LF400A	TSOP48	PA48TS48D1
SST	SST39LF512	DIP32	
SST	SST39LF512	PLCC32	PA32PL32D
SST	SST39LF512	TSOP32	PA32TS32D
SST	SST39LF800A	BGA48	PA48BG48DAI
SST	SST39LF800A	TSOP48	PA48TS48D1
SST	SST39LF800A	WFBGA48	PA48WFB48D1
SST	SST39LH010	DIP32	
SST	SST39LH020	DIP32	
SST	SST39LH040	DIP32	
SST	SST39LH512	DIP32	
SST	SST39SF010	DIP32	
SST	SST39SF010	PLCC32	PA32PL32D
SST	SST39SF010	TSOP32	PA32TS32D
SST	SST39SF010A	DIP32	
SST	SST39SF010A	PLCC32	PA32PL32D
SST	SST39SF010A	TSOP32	PA32TS32D
SST	SST39SF020	DIP32	
SST	SST39SF020	PLCC32	PA32PL32D
SST	SST39SF020	TSOP32	PA32TS32D
SST	SST39SF020A	DIP32	
SST	SST39SF020A	PLCC32	PA32PL32D
SST	SST39SF020A	TSOP32	PA32TS32D
SST	SST39SF020P	DIP32	
SST	SST39SF020P	PLCC32	PA32PL32D
SST	SST39SF020P	TSOP32	PA32TS32D
SST	SST39SF040	DIP32	
SST	SST39SF040	PLCC32	PA32PL32D
SST	SST39SF040	TSOP32	PA32TS32D
SST	SST39SF040P	DIP32	
SST	SST39SF040P	PLCC32	PA32PL32D
SST	SST39SF040P	TSOP32	PA32TS32D
SST	SST39SF512	DIP32	
SST	SST39SF512	PLCC32	PA32PL32D
SST	SST39SF512	TSOP32	PA32TS32D
SST	SST39SF512A	DIP32	
SST	SST39SF512A	PLCC32	PA32PL32D
SST	SST39SF512A	TSOP32	PA32TS32D
SST	SST39VF010	BGA48	PA48BGA32DN-30-6X8

SST	SST39VF010	DIP32	
SST	SST39VF010	PLCC32	PA32PL32D
SST	SST39VF010	TSOP32	PA32TS32D
SST	SST39VF016	TSOP40	PA40TS40D
SST	SST39VF016Q	TSOP40	PA40TS40D
SST	SST39VF020	DIP32	
SST	SST39VF020	PLCC32	PA32PL32D
SST	SST39VF020	TSOP32	PA32TS32D
SST	SST39VF020P	BGA48	PA48BGA32DN-3O-6X8
SST	SST39VF020P	DIP32	
SST	SST39VF020P	PLCC32	PA32PL32D
SST	SST39VF020P	TSOP32	PA32TS32D
SST	SST39VF040	DIP32	
SST	SST39VF040	PLCC32	PA32PL32D
SST	SST39VF040	TSOP32	PA32TS32D
SST	SST39VF040P	BGA48	PA48BGA32DN-3O-6X8
SST	SST39VF040P	DIP32	
SST	SST39VF040P	PLCC32	PA32PL32D
SST	SST39VF040P	TSOP32	PA32TS32D
SST	SST39VF080	TSOP40	PA40TS40D
SST	SST39VF080B	TSOP48	PA48TS48D
SST	SST39VF080Q	TSOP40	PA40TS40D
SST	SST39VF088	TSOP48	PA48TS48D
SST	SST39VF100	TSOP40	PA40TS14-OT
SST	SST39VF160	TSOP48	PA48TS48D1
SST	SST39VF160(Single)	TSOP48	PA48TS48D1
SST	SST39VF1601	TSOP48	PA48TS48D1
SST	SST39VF1601	WFBGA48	PA48BG48DAI
SST	SST39VF1601C	TSOP48	PA48TS48D1
SST	SST39VF1602	TSOP48	PA48TS48D1
SST	SST39VF160Q	TSOP48	PA48TS48D1
SST	SST39VF160Q(Single)	TSOP48	PA48TS48D1
SST	SST39VF1681	TSOP48	PA48TS48D1
SST	SST39VF1682	TSOP48	PA48TS48D1
SST	SST39VF200A	BGA48	PA48BG48DAI
SST	SST39VF200A	TSOP48	PA48TS48D1
SST	SST39VF200A	WFBGA48	PA48WFB48D1
SST	SST39VF320	TSOP48	PA48TS48D1
SST	SST39VF3201	BGA48	PA48BG48DAI
SST	SST39VF3201	TSOP48	PA48TS48D1
SST	SST39VF3201B	TSOP48	PA48TS48D1
SST	SST39VF3202	BGA48	PA48BG48DAI
SST	SST39VF3202	TSOP48	PA48TS48D1
SST	SST39VF400	TSOP48	PA48TS48D1
SST	SST39VF400A	BGA48	PA48BG48DAI
SST	SST39VF400A	TSOP48	PA48TS48D1
SST	SST39VF400A	WFBGA48	PA48WFB48D1
SST	SST39VF400Q	TSOP48	PA48TS48D1
SST	SST39VF401C	TSOP48	PA48TS48D1
SST	SST39VF512	BGA48	PA48BGA32DN-3O-6X8
SST	SST39VF512	DIP32	
SST	SST39VF512	PLCC32	PA32PL32D
SST	SST39VF512	TSOP32	PA32TS32D
SST	SST39VF640	TSOP48	PA48TS48D1
SST	SST39VF6401	BGA48	HA48BG48DG1
SST	SST39VF6401	TSOP48	PA48TS48D1
SST	SST39VF6401B	BGA48	HA48BG48DG1
SST	SST39VF6401B	TSOP48	PA48TS48D1
SST	SST39VF6402	BGA48	HA48BG48DG1
SST	SST39VF6402	TSOP48	PA48TS48D1
SST	SST39VF6402B	BGA48	HA48BG48DG1
SST	SST39VF6402B	TSOP48	PA48TS48D1
SST	SST39VF800	TSOP48	PA48TS48D1
SST	SST39VF800A	BGA48	PA48BG48DAI
SST	SST39VF800A	TSOP48	PA48TS48D1
SST	SST39VF800A	WFBGA48	PA48WFB48D1
SST	SST39VF800Q	TSOP48	PA48TS48D1
SST	SST39VF801C	TSOP48	PA48TS48D1
SST	SST39WF1601	WFBGA48	HA48BG48DAI
SST	SST39WF1601	WFBGA48	PA48BG48DW
SST	SST39WF1602	WFBGA48	HA48BG48DAI
SST	SST39WF1602	WFBGA48	PA48BG48DW
SST	SST39WF400A	WFBGA48	PA48WFB48D



SST	SST39WF400B	WFBGA48	HA48BG48DAI
SST	SST39WF400B	WFBGA48	PA48BG48DW
SST	SST39WF800A	WFBGA48	PA48WFB48D1
SST	SST39WF800B	WFBGA48	PA48WFB48D1
SST	SST45LF010	SOP8	PA16SO16D-EO-150
SST	SST45VF010	SOP8	PA16SO16D-EO-150
SST	SST49LF002	PLCC32	PA32PL32D
SST	SST49LF002	TSOP32	PA32TS32D
SST	SST49LF002A	PLCC32	PA32PL32D
SST	SST49LF002A	TSOP32	PA32TS32D
SST	SST49LF002A	TSOP40	PA40TS40D
SST	SST49LF002B	PLCC32	PA32PL32D
SST	SST49LF002B	TSOP32	PA32TS32D
SST	SST49LF002B	TSOP40	PA40TS40D
SST	SST49LF003A	PLCC32	PA32PL32D
SST	SST49LF003A	TSOP32	PA32TS32D
SST	SST49LF003A	TSOP40	PA40TS40D
SST	SST49LF003B	PLCC32	PA32PL32D
SST	SST49LF003B	TSOP32	PA32TS32D
SST	SST49LF003B	TSOP40	PA40TS40D
SST	SST49LF004	PLCC32	PA32PL32D
SST	SST49LF004	TSOP32	PA32TS32D
SST	SST49LF004A	PLCC32	PA32PL32D
SST	SST49LF004A	TSOP32	PA32TS32D
SST	SST49LF004A	TSOP40	PA40TS40D
SST	SST49LF004B	PLCC32	PA32PL32D
SST	SST49LF004B	TSOP32	PA32TS32D
SST	SST49LF004B	TSOP40	PA40TS40D
SST	SST49LF004C	PLCC32	PA32PL32D
SST	SST49LF004C	TSOP32	PA32TS20/PA32TS32D-20
SST	SST49LF008	PLCC32	PA32PL32D
SST	SST49LF008	TSOP32	PA32TS32D
SST	SST49LF008A	PLCC32	PA32PL32D
SST	SST49LF008A	TSOP32	PA32TS32D
SST	SST49LF008A	TSOP40	PA40TS40D
SST	SST49LF008B	PLCC32	PA32PL32D
SST	SST49LF008B	TSOP32	PA32TS32D
SST	SST49LF008B	TSOP40	PA40TS40D
SST	SST49LF008C	PLCC32	PA32PL32D
SST	SST49LF008C	TSOP32	PA32TS20/PA32TS32D-20
SST	SST49LF016C(AAI)	PLCC32	PA32PL32D
SST	SST49LF016C(AAI)	TSOP32	PA32TS20/PA32TS32D-20
SST	SST49LF016C(AAI)	TSOP32	PA32TS32D
SST	SST49LF016C(AAI)	TSOP40	PA40TS40D
SST	SST49LF016C(FWH)	PLCC32	PA32PL32D
SST	SST49LF016C(FWH)	TSOP32	PA32TS20/PA32TS32D-20
SST	SST49LF016C(FWH)	TSOP32	PA32TS32D
SST	SST49LF016C(FWH)	TSOP40	PA40TS40D
SST	SST49LF016C(LPC)	PLCC32	PA32PL32D
SST	SST49LF016C(LPC)	TSOP32	PA32TS20/PA32TS32D-20
SST	SST49LF016C(LPC)	TSOP32	PA32TS32D
SST	SST49LF016C(LPC)	TSOP40	PA40TS40D
SST	SST49LF020	PLCC32	PA32PL32D
SST	SST49LF020	TSOP32	PA32TS32D
SST	SST49LF020A	PLCC32	PA32PL32D
SST	SST49LF020A	TSOP32	PA32TS32D
SST	SST49LF030A	PLCC32	PA32PL32D
SST	SST49LF040	PLCC32	PA32PL32D
SST	SST49LF040	TSOP32	PA32TS32D
SST	SST49LF040A	PLCC32	PA32PL32D
SST	SST49LF040A	TSOP32	PA32TS32D
SST	SST49LF040B	PLCC32	PA32PL32D
SST	SST49LF040B	TSOP32	PA32TS32D
SST	SST49LF080	PLCC32	PA32PL32D
SST	SST49LF080	TSOP32	PA32TS32D
SST	SST49LF080A	PLCC32	PA32PL32D
SST	SST49LF080A	TSOP32	PA32TS32D
SST	SST49LF160C(AAI)	PLCC32	PA32PL32D
SST	SST49LF160C(AAI)	TSOP32	PA32TS20/PA32TS32D-20
SST	SST49LF160C(AAI)	TSOP32	PA32TS32D
SST	SST49LF160C(AAI)	TSOP40	PA40TS40D
SST	SST89C58RC-NJE	PLCC44	PA44-48U
SST	SST89C58RC-TQJE	QFP44	PA44QF44D

SST	SST89E516RD2-NJE	PLCC44	PA44-48U
SST	SST89E516RD2-TQJE	TQFP44	PA44QF44D
SST	SST89E516RD-PIE	DIP40	
ST	GAL16V8	DIP20	
ST	GAL16V8	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8A	DIP20	
ST	GAL16V8A	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas10H8	DIP20	
ST	GAL16V8Aas10H8	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas10L8	DIP20	
ST	GAL16V8Aas10L8	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas10P8	DIP20	
ST	GAL16V8Aas10P8	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas12H6	DIP20	
ST	GAL16V8Aas12H6	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas12L6	DIP20	
ST	GAL16V8Aas12L6	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas12P6	DIP20	
ST	GAL16V8Aas12P6	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas14H4	DIP20	
ST	GAL16V8Aas14H4	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas14L4	DIP20	
ST	GAL16V8Aas14L4	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas14P4	DIP20	
ST	GAL16V8Aas14P4	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16H2	DIP20	
ST	GAL16V8Aas16H2	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16H8	DIP20	
ST	GAL16V8Aas16H8	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16L2	DIP20	
ST	GAL16V8Aas16L2	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16L8	DIP20	
ST	GAL16V8Aas16L8	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16P2	DIP20	
ST	GAL16V8Aas16P2	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16P8	DIP20	
ST	GAL16V8Aas16P8	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16R4	DIP20	
ST	GAL16V8Aas16R4	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16R6	DIP20	
ST	GAL16V8Aas16R6	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16R8	DIP20	
ST	GAL16V8Aas16R8	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16RP4	DIP20	
ST	GAL16V8Aas16RP4	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16RP6	DIP20	
ST	GAL16V8Aas16RP6	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8Aas16RP8	DIP20	
ST	GAL16V8Aas16RP8	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as10H8	DIP20	
ST	GAL16V8as10H8	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as10L8	DIP20	
ST	GAL16V8as10L8	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as10P8	DIP20	
ST	GAL16V8as10P8	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as12H6	DIP20	
ST	GAL16V8as12H6	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as12L6	DIP20	
ST	GAL16V8as12L6	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as12P6	DIP20	
ST	GAL16V8as12P6	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as14H4	DIP20	
ST	GAL16V8as14H4	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as14L4	DIP20	
ST	GAL16V8as14L4	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as14P4	DIP20	
ST	GAL16V8as14P4	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as16H2	DIP20	
ST	GAL16V8as16H2	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as16H8	DIP20	
ST	GAL16V8as16H8	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as16L2	DIP20	
ST	GAL16V8as16L2	PLCC20	PA20LC20D[Dead Bug]

ST	GAL16V8as16L8	DIP20	
ST	GAL16V8as16L8	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as16P2	DIP20	
ST	GAL16V8as16P2	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as16P8	DIP20	
ST	GAL16V8as16P8	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as16R4	DIP20	
ST	GAL16V8as16R4	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as16R6	DIP20	
ST	GAL16V8as16R6	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as16R8	DIP20	
ST	GAL16V8as16R8	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as16RP4	DIP20	
ST	GAL16V8as16RP4	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as16RP6	DIP20	
ST	GAL16V8as16RP6	PLCC20	PA20LC20D[Dead Bug]
ST	GAL16V8as16RP8	DIP20	
ST	GAL16V8as16RP8	PLCC20	PA20LC20D[Dead Bug]
ST	GAL20V8	DIP24	
ST	GAL20V8	PLCC28	PA28PL28D
ST	GAL20V8A	DIP24	
ST	GAL20V8A	PLCC28	PA28PL28D
ST	GAL20V8Aas14H8	DIP24	
ST	GAL20V8Aas14H8	PLCC28	PA28PL28D
ST	GAL20V8Aas14L8	DIP24	
ST	GAL20V8Aas14L8	PLCC28	PA28PL28D
ST	GAL20V8Aas14P8	DIP24	
ST	GAL20V8Aas14P8	PLCC28	PA28PL28D
ST	GAL20V8Aas16H6	DIP24	
ST	GAL20V8Aas16H6	PLCC28	PA28PL28D
ST	GAL20V8Aas16L6	DIP24	
ST	GAL20V8Aas16L6	PLCC28	PA28PL28D
ST	GAL20V8Aas16P6	DIP24	
ST	GAL20V8Aas16P6	PLCC28	PA28PL28D
ST	GAL20V8Aas18H4	DIP24	
ST	GAL20V8Aas18H4	PLCC28	PA28PL28D
ST	GAL20V8Aas18L4	DIP24	
ST	GAL20V8Aas18L4	PLCC28	PA28PL28D
ST	GAL20V8Aas18P4	DIP24	
ST	GAL20V8Aas18P4	PLCC28	PA28PL28D
ST	GAL20V8Aas20H2	DIP24	
ST	GAL20V8Aas20H2	PLCC28	PA28PL28D
ST	GAL20V8Aas20H8	DIP24	
ST	GAL20V8Aas20H8	PLCC28	PA28PL28D
ST	GAL20V8Aas20L2	DIP24	
ST	GAL20V8Aas20L2	PLCC28	PA28PL28D
ST	GAL20V8Aas20L8	DIP24	
ST	GAL20V8Aas20L8	PLCC28	PA28PL28D
ST	GAL20V8Aas20P2	DIP24	
ST	GAL20V8Aas20P2	PLCC28	PA28PL28D
ST	GAL20V8Aas20P8	DIP24	
ST	GAL20V8Aas20P8	PLCC28	PA28PL28D
ST	GAL20V8Aas20R4	DIP24	
ST	GAL20V8Aas20R4	PLCC28	PA28PL28D
ST	GAL20V8Aas20R6	DIP24	
ST	GAL20V8Aas20R6	PLCC28	PA28PL28D
ST	GAL20V8Aas20R8	DIP24	
ST	GAL20V8Aas20R8	PLCC28	PA28PL28D
ST	GAL20V8Aas20RP4	DIP24	
ST	GAL20V8Aas20RP4	PLCC28	PA28PL28D
ST	GAL20V8Aas20RP6	DIP24	
ST	GAL20V8Aas20RP6	PLCC28	PA28PL28D
ST	GAL20V8Aas20RP8	DIP24	
ST	GAL20V8Aas20RP8	PLCC28	PA28PL28D
ST	GAL20V8as14H8	DIP24	
ST	GAL20V8as14H8	PLCC28	PA28PL28D
ST	GAL20V8as14L8	DIP24	
ST	GAL20V8as14L8	PLCC28	PA28PL28D
ST	GAL20V8as14P8	DIP24	
ST	GAL20V8as14P8	PLCC28	PA28PL28D
ST	GAL20V8as16H6	DIP24	
ST	GAL20V8as16H6	PLCC28	PA28PL28D
ST	GAL20V8as16L6	DIP24	

ST	GAL20V8as16L6	PLCC28	PA28PL28D
ST	GAL20V8as16P6	DIP24	
ST	GAL20V8as16P6	PLCC28	PA28PL28D
ST	GAL20V8as18H4	DIP24	
ST	GAL20V8as18H4	PLCC28	PA28PL28D
ST	GAL20V8as18L4	DIP24	
ST	GAL20V8as18L4	PLCC28	PA28PL28D
ST	GAL20V8as18P4	DIP24	
ST	GAL20V8as18P4	PLCC28	PA28PL28D
ST	GAL20V8as20H2	DIP24	
ST	GAL20V8as20H2	PLCC28	PA28PL28D
ST	GAL20V8as20H8	DIP24	
ST	GAL20V8as20H8	PLCC28	PA28PL28D
ST	GAL20V8as20L2	DIP24	
ST	GAL20V8as20L2	PLCC28	PA28PL28D
ST	GAL20V8as20L8	DIP24	
ST	GAL20V8as20L8	PLCC28	PA28PL28D
ST	GAL20V8as20P2	DIP24	
ST	GAL20V8as20P2	PLCC28	PA28PL28D
ST	GAL20V8as20P8	DIP24	
ST	GAL20V8as20P8	PLCC28	PA28PL28D
ST	GAL20V8as20R4	DIP24	
ST	GAL20V8as20R4	PLCC28	PA28PL28D
ST	GAL20V8as20R6	DIP24	
ST	GAL20V8as20R6	PLCC28	PA28PL28D
ST	GAL20V8as20R8	DIP24	
ST	GAL20V8as20R8	PLCC28	PA28PL28D
ST	GAL20V8as20RP4	DIP24	
ST	GAL20V8as20RP4	PLCC28	PA28PL28D
ST	GAL20V8as20RP6	DIP24	
ST	GAL20V8as20RP6	PLCC28	PA28PL28D
ST	GAL20V8as20RP8	DIP24	
ST	GAL20V8as20RP8	PLCC28	PA28PL28D
ST	GAL6001	DIP24	
ST	GAL6001	PLCC28	PA28PL28D
ST	M24128	DIP8	
ST	M24128	SOIC8	PA16SO16D-EO-150
ST	M24128	TSSOP8	PA24TSS24D
ST	M24256	DIP8	
ST	M24256	SOIC8	PA16SO16D-EO-150
ST	M24512	QFN8	PA8QFN8D(2x3)
ST	M24512	SOIC8	PA16SO16D-EO-150
ST	M24512	SOIC8	PA20SO20D-EO-210
ST	M24512	TSSOP8	PA24TSS24D
ST	M24512	TSSOP8	PA8TSS8D
ST	M24C01	DIP8	
ST	M24C01	SOIC8	PA16SO16D-EO-150
ST	M24C01	TSSOP8	PA24TSS24D
ST	M24C02	DIP8	
ST	M24C02	SOIC8	PA16SO16D-EO-150
ST	M24C02	TSSOP8	PA24TSS24D
ST	M24C04	DIP8	
ST	M24C04	SOIC8	PA16SO16D-EO-150
ST	M24C04	TSSOP8	PA24TSS24D
ST	M24C08	DIP8	
ST	M24C08	MSOP8	HA8MSOP48D
ST	M24C08	SOIC8	PA16SO16D-EO-150
ST	M24C08	TSSOP8	PA24TSS24D
ST	M24C16	DIP8	
ST	M24C16	SOIC8	PA16SO16D-EO-150
ST	M24C16	TSSOP8	PA24TSS24D
ST	M24C16W	DIP8	
ST	M24C16W	SOIC8	PA16SO16D-EO-150
ST	M24C16W	TSSOP8	PA24TSS24D
ST	M24C32	DIP8	
ST	M24C32	QFN8	PA8QFN8D(2x3)
ST	M24C32	SOIC8	PA16SO16D-EO-150
ST	M24C32	TSSOP8	PA24TSS24D
ST	M24C64	DIP8	
ST	M24C64	SOIC8	PA16SO16D-EO-150
ST	M24C64	TSSOP8	PA24TSS24D
ST	M24LC21B	DIP8	
ST	M24LC21B	SOIC8	PA16SO16D-EO-150

ST	M24LC21B	TSSOP8	PA24TSS24D
ST	M24M01-DW	TSSOP8	PA8TSS8D
ST	M24M01-MN	SOIC8	PA16SO16D-EO-150
ST	M24M02-MN	SOIC8	PA16SO16D-EO-150
ST	M25P05AVDW	TSSOP8	PA28TSS28D-EO
ST	M25P05AVMN	SOIC8	PA16SO16D-EO-150
ST	M25P05AVMP	MLP8	PA8SON8D(6x5)
ST	M25P05VMN	SOIC8	PA16SO16D-EO-150
ST	M25P10AVMN	SOIC8	PA16SO16D-EO-150
ST	M25P10AVMP	MLP8	PA8SON8D(6x5)
ST	M25P10VMN	SOIC8	PA16SO16D-EO-150
ST	M25P10VMW	SOIC8	PA20SO20D-EO-210
ST	M25P128VME	MLP8	PA8SON8DA(8x6)
ST	M25P128VMF	SOP16	PA28SO28D-EO-300
ST	M25P16VME	MLP8	PA8SON8DA(8x6)
ST	M25P16VMF	SOP16	PA28SO28D-EO-300
ST	M25P16VMJ	SOP16	PA28SO28D-EO-300
ST	M25P16VMN	SOIC8	PA16SO16D-EO-150
ST	M25P16VMP	MLP8	PA8SON8D(6x5)
ST	M25P16VMW	SOIC8	PA20SO20D-EO-210
ST	M25P20VMN	SOIC8	PA16SO16D-EO-150
ST	M25P20VMP	MLP8	PA8SON8D(6x5)
ST	M25P20VMW	SOIC8	PA16SO16D-EO-150
ST	M25P32VME	MLP8	PA8SON8DA(8x6)
ST	M25P32VMF	SOP16	PA28SO28D-EO-300
ST	M25P32VMJ	SOP16	PA28SO28D-EO-300
ST	M25P32VML	MLP8	PA8SON8D(6x5)
ST	M25P32VMW	SOIC8	PA20SO20D-EO-210
ST	M25P40VMN	SOIC8	PA16SO16D-EO-150
ST	M25P40VMP	MLP8	PA8SON8D(6x5)
ST	M25P64V6P	SOP16	PA28SO28D-EO-300
ST	M25P64VME	MLP8	PA8SON20D
ST	M25P64VME	MLP8	PA8SON8DA(8x6)
ST	M25P64VMF	SOP16	PA28SO28D-EO-300
ST	M25P64VMJ	SOP16	PA28SO28D-EO-300
ST	M25P80VMF	SOP16	PA28SO28D-EO-300
ST	M25P80VMN	SOIC8	PA16SO16D-EO-150
ST	M25P80VMW	SOIC8	PA20SO20D-EO-210
ST	M25PE10VMN	SOIC8	PA16SO16D-EO-150
ST	M25PE16VMP	MLP8	PA8SON8D(6x5)
ST	M25PE16VMW	SOIC8	PA20SO20D-EO-210
ST	M25PE20VMN	SOIC8	PA16SO16D-EO-150
ST	M25PE40VMP	MLP8	PA8SON8D(6x5)
ST	M25PE40VMW	SOIC8	PA20SO20D-EO-210
ST	M25PE80VMP	MLP8	PA8SON8D(6x5)
ST	M25PE80VMW	SOIC8	PA16SO16D-EO-150
ST	M25PF32VE	SOIC8	PA20SO20D-EO-210
ST	M25PF32VMW	SOIC8	PA20SO20D-EO-210
ST	M25PX16VMN	SOIC8	PA16SO16D-EO-150
ST	M25PX64VMD	MLP8	PA8SON20D
ST	M25PX64VME	MLP8	PA8SON20D
ST	M25PX64VME	MLP8	PA8SON8DA(8x6)
ST	M25PX64VMP	SOP16	PA28SO28D-EO-300
ST	M27128A	DIP28	
ST	M2716	DIP24	
ST	M27256	DIP28	
ST	M2732A	DIP24	
ST	M27512	DIP28	
ST	M2764	DIP28	
ST	M2764A	DIP28	
ST	M27C1000	DIP32	
ST	M27C1000	PLCC32	PA32PL32D
ST	M27C1001	DIP32	
ST	M27C1001	PLCC32	PA32PL32D
ST	M27C1001	TSOP32	PA32TS20/PA32TS32D-20
ST	M27C1024	DIP40	
ST	M27C1024	PLCC44	PA44-48U
ST	M27C1024	TSOP40	PA40TS40D
ST	M27C128A	DIP28	
ST	M27C160	DIP42	
ST	M27C160	PLCC44	PA44-48U
ST	M27C160	SOP44	PA44SO44D
ST	M27C2001	DIP32	

ST	M27C2001	PLCC32	PA32PL32D
ST	M27C2001	TSOP32	PA32TS20/PA32TS32D-20
ST	M27C202	DIP40	
ST	M27C202	PLCC44	PA44-48U
ST	M27C202	TSOP40	PA40TS40D
ST	M27C256B	DIP28	
ST	M27C256B	PLCC32	PA32PL28D-YA
ST	M27C256B	TSOP28	PA28TS28D-EO
ST	M27C320	SOP44	PA44SO44D
ST	M27C320	TSOP48	PA48TS48D
ST	M27C322	DIP42	
ST	M27C400	DIP40	
ST	M27C400	PLCC44	PA44-48U
ST	M27C4001	DIP32	
ST	M27C4001	PLCC32	PA32PL32D
ST	M27C4001	TSOP32	PA32TS20/PA32TS32D-20
ST	M27C4002	DIP40	
ST	M27C4002	PLCC44	PA44-48U
ST	M27C4002	TSOP40	PA40TS40D
ST	M27C405	DIP32	
ST	M27C512	DIP28	
ST	M27C512	PLCC32	PA32PL28D-YA
ST	M27C512	TSOP28	PA28TS28D-EO
ST	M27C516	DIP40	
ST	M27C516	PLCC44	PA44-48U
ST	M27C516	TSOP40	PA40TS40D
ST	M27C64A	DIP28	
ST	M27C64A	PLCC32	PA32PL28D-YA
ST	M27C800	DIP42	
ST	M27C800	PLCC44	PA44-48U
ST	M27C800	SOP44	PA44SO44D
ST	M27C801	DIP32	
ST	M27C801	PLCC32	PA32PL32D
ST	M27C801	TSOP32	PA32TS20/PA32TS32D-20
ST	M27V101	DIP32	
ST	M27V101	PLCC32	PA32PL32D
ST	M27V101	TSOP32	PA32TS20/PA32TS32D-20
ST	M27V102	TSOP40	PA40TS40D
ST	M27V160	DIP42	
ST	M27V160	PLCC44	PA44-48U
ST	M27V160	SOP44	PA44SO44D
ST	M27V201	DIP32	
ST	M27V201	PLCC32	PA32PL32D
ST	M27V201	TSOP32	PA32TS20/PA32TS32D-20
ST	M27V256	DIP28	
ST	M27V256	PLCC32	PA32PL28D-YA
ST	M27V256	TSOP28	PA28TS28D-EO
ST	M27V322	DIP42	
ST	M27V401	DIP32	
ST	M27V401	PLCC32	PA32PL32D
ST	M27V401	TSOP32	PA32TS20/PA32TS32D-20
ST	M27V402	DIP40	
ST	M27V402	PLCC44	PA44-48U
ST	M27V402	TSOP40	PA40TS40D
ST	M27V512	DIP28	
ST	M27V512	PLCC32	PA32PL28D-YA
ST	M27V512	TSOP28	PA28TS28D-EO
ST	M27V800	DIP42	
ST	M27V800	PLCC44	PA44-48U
ST	M27V800	SOP44	PA44SO44D
ST	M27V801	DIP32	
ST	M27V801	PLCC32	PA32PL32D
ST	M27V801	TSOP32	PA32TS20/PA32TS32D-20
ST	M27W101	DIP32	
ST	M27W101	PLCC32	PA32PL32D
ST	M27W101	TSOP32	PA32TS20/PA32TS32D-20
ST	M27W102	DIP40	
ST	M27W102	PLCC44	PA44-48U
ST	M27W102	TSOP40	PA40TS40D
ST	M27W160	DIP42	
ST	M27W160	SOP44	PA44SO44D
ST	M27W201	DIP32	
ST	M27W201	PLCC32	PA32PL32D

ST	M27W201	TSOP32	PA32TS20/PA32TS32D-20
ST	M27W202	DIP40	
ST	M27W202	PLCC44	PA44-48U
ST	M27W202	TSOP40	PA40TS40D
ST	M27W256	DIP28	
ST	M27W256	PLCC32	PA32PL28D-YA
ST	M27W256	TSOP28	PA28TS28D-EO
ST	M27W256B	DIP28	
ST	M27W322	DIP42	
ST	M27W400	DIP40	
ST	M27W400	PLCC44	PA44-48U
ST	M27W401	DIP32	
ST	M27W401	PLCC32	PA32PL32D
ST	M27W401	TSOP32	PA32TS20/PA32TS32D-20
ST	M27W402	DIP40	
ST	M27W402	PLCC44	PA44-48U
ST	M27W402	TSOP40	PA40TS40D
ST	M27W512	DIP28	
ST	M27W512	PLCC32	PA32PL28D-YA
ST	M27W512	TSOP28	PA28TS28D-EO
ST	M27W800	DIP42	
ST	M27W800	PLCC44	PA44-48U
ST	M27W800	SOP44	PA44SO44D
ST	M27W801	DIP32	
ST	M27W801	PLCC32	PA32PL32D
ST	M27W801	TSOP32	PA32TS20/PA32TS32D-20
ST	M28010	DIP32	
ST	M28010	PLCC32	PA32PL32D
ST	M28010	TSOP32	PA32TS20/PA32TS32D-20
ST	M28010-xxW	DIP32	
ST	M28010-xxW	PLCC32	PA32PL32D
ST	M28010-xxW	TSOP32	PA32TS20/PA32TS32D-20
ST	M28256	DIP28	
ST	M28256	PLCC32	PA32PL28D-YA
ST	M28256	SOIC28	PA28SO28D-EO-300
ST	M28256	TSOP28	PA28TS28D-EO
ST	M28256-xxW	DIP28	
ST	M28256-xxW	PLCC32	PA32PL28D-YA
ST	M28256-xxW	SOIC28	PA28SO28D-EO-300
ST	M28256-xxW	TSOP28	PA28TS28D-EO
ST	M28C17	DIP28	
ST	M28C17	PLCC32	PA32PL28D-YA
ST	M28C17	SOIC28	PA28SO28D-EO-300
ST	M28C64	DIP28	
ST	M28C64	PLCC32	PA32PL28D-YA
ST	M28C64	SOIC28	PA28SO28D-EO-300
ST	M28C64	TSOP28	PA28TS28D-EO
ST	M28C64C	DIP28	
ST	M28C64C	PLCC32	PA32PL28D-YA
ST	M28C64C	SOIC28	PA28SO28D-EO-300
ST	M28C64C	TSOP28	PA28TS28D-EO
ST	M28C64X	DIP28	
ST	M28C64X	PLCC32	PA32PL28D-YA
ST	M28C64X	SOIC28	PA28SO28D-EO-300
ST	M28C64X	TSOP28	PA28TS28D-EO
ST	M28F101	DIP32	
ST	M28F101	PLCC32	PA32PL32D
ST	M28F101	TSOP32	PA32TS20/PA32TS32D-20
ST	M28F102	PLCC44	PA44-48U
ST	M28F201	DIP32	
ST	M28F201	PLCC32	PA32PL32D
ST	M28F201	TSOP32	PA32TS20/PA32TS32D-20
ST	M28F256	DIP32	
ST	M28F256	PLCC32	PA32PL32D
ST	M28F256A	DIP32	
ST	M28F256A	PLCC32	PA32PL32D
ST	M28F512	DIP32	
ST	M28F512	PLCC32	PA32PL32D
ST	M28W160B	TSOP48	PA48TS48D
ST	M28W160BB	TSOP48	PA48TS48D
ST	M28W160BT	TSOP48	PA48TS48D
ST	M28W160CB	TSOP48	PA48TS48D
ST	M28W160CT	TSOP48	PA48TS48D

ST	M28W160T	TSOP48	PA48TS48D
ST	M28W320BB	TSOP48	PA48TS48D
ST	M28W320BT	TSOP48	PA48TS48D
ST	M28W320CB	TSOP48	PA48TS48D
ST	M28W320CT	TSOP48	PA48TS48D
ST	M28W320FCB	TSOP48	PA48TS48D
ST	M28W320FCT	TSOP48	PA48TS48D
ST	M28W320FSB-ZA	EBGA64	PA64BGA48D/HA64BGA48D
ST	M28W320FST-ZA	EBGA64	PA64BGA48D/HA64BGA48D
ST	M28W640ECB	TSOP48	PA48TS48D
ST	M28W640ECT	TSOP48	PA48TS48D
ST	M28W640FCB	TSOP48	PA48TS48D
ST	M28W640FCT	TSOP48	PA48TS48D
ST	M28W640FSB-ZA	EBGA64	PA64BGA48D/HA64BGA48D
ST	M28W640FST-ZA	EBGA64	PA64BGA48D/HA64BGA48D
ST	M28W640FSU-ZA	EBGA64	PA64BGA48D/HA64BGA48D
ST	M28W640HCT	TSOP48	PA48TS48D
ST	M28W800CB	TSOP48	PA48TS48D
ST	M28W800CT	TSOP48	PA48TS48D
ST	M29DW128G-NF	TSOP56	PA56TS48DD
ST	M29DW256G	TSOP56	PA56TS48DC
ST	M29DW256G	TSOP56	PA56TS48DD
ST	M29DW256GH	TSOP56	PA56TS48DC
ST	M29DW323DB	TSOP48	PA48TS48D
ST	M29DW323DT	TSOP48	PA48TS48D
ST	M29DW640F	TSOP48	PA48TS48D
ST	M29F002B	DIP32	
ST	M29F002B	PLCC32	PA32PL32D
ST	M29F002B	TSOP32	PA32TS20/PA32TS32D-20
ST	M29F002BB	DIP32	
ST	M29F002BB	PLCC32	PA32PL32D
ST	M29F002BB	TSOP32	PA32TS20/PA32TS32D-20
ST	M29F002BNT	DIP32	
ST	M29F002BNT	PLCC32	PA32PL32D
ST	M29F002BNT	TSOP32	PA32TS20/PA32TS32D-20
ST	M29F002BT	DIP32	
ST	M29F002BT	PLCC32	PA32PL32D
ST	M29F002BT	TSOP32	PA32TS20/PA32TS32D-20
ST	M29F002NT	DIP32	
ST	M29F002NT	PLCC32	PA32PL32D
ST	M29F002NT	TSOP32	PA32TS20/PA32TS32D-20
ST	M29F002T	DIP32	
ST	M29F002T	PLCC32	PA32PL32D
ST	M29F002T	TSOP32	PA32TS20/PA32TS32D-20
ST	M29F010B	DIP32	
ST	M29F010B	PLCC32	PA32PL32D
ST	M29F010B	TSOP32	PA32TS20/PA32TS32D-20
ST	M29F016B	SOP44	PA44SO44D
ST	M29F016B	TSOP40	PA40TS40D
ST	M29F016D	SOP44	PA44SO44D
ST	M29F016D	TSOP40	PA40TS40D
ST	M29F032D	TSOP40	PA40TS40D
ST	M29F040	DIP32	
ST	M29F040	PLCC32	PA32PL32D
ST	M29F040	TSOP32	PA32TS20/PA32TS32D-20
ST	M29F040B	DIP32	
ST	M29F040B	PLCC32	PA32PL32D
ST	M29F040B	TSOP32	PA32TS20/PA32TS32D-20
ST	M29F080A	TSOP40	PA40TS40D
ST	M29F080D	TSOP40	PA40TS40D
ST	M29F100B	SOP44	PA44SO44D
ST	M29F100B	TSOP48	PA48TS48D
ST	M29F100BB	SOP44	PA44SO44D
ST	M29F100BB	TSOP48	PA48TS48D
ST	M29F100BT	SOP44	PA44SO44D
ST	M29F100BT	TSOP48	PA48TS48D
ST	M29F100T	SOP44	PA44SO44D
ST	M29F100T	TSOP48	PA48TS48D
ST	M29F160BB	TSOP48	PA48TS48D
ST	M29F160BT	TSOP48	PA48TS48D
ST	M29F200B	SOP44	PA44SO44D
ST	M29F200B	TSOP48	PA48TS48D
ST	M29F200BB	SOP44	PA44SO44D



ST	M29F200BB	TSOP48	PA48TS48D
ST	M29F200BT	SOP44	PA44SO44D
ST	M29F200BT	TSOP48	PA48TS48D
ST	M29F200T	SOP44	PA44SO44D
ST	M29F200T	TSOP48	PA48TS48D
ST	M29F400B	SOP44	PA44SO44D
ST	M29F400B	TSOP48	PA48TS48D
ST	M29F400BB	SOP44	PA44SO44D
ST	M29F400BB	TSOP48	PA48TS48D
ST	M29F400BT	SOP44	PA44SO44D
ST	M29F400BT	TSOP48	PA48TS48D
ST	M29F400FB	SOP44	PA44SO44D
ST	M29F400FB	TSOP48	PA48TS48D
ST	M29F400FT	SOP44	PA44SO44D
ST	M29F400FT	TSOP48	PA48TS48D
ST	M29F400T	SOP44	PA44SO44D
ST	M29F400T	TSOP48	PA48TS48D
ST	M29F512B	PLCC32	PA32PL32D
ST	M29F512B	TSOP32	PA32TS20/PA32TS32D-20
ST	M29F800AB	SOP44	PA44SO44D
ST	M29F800AB	TSOP48	PA48TS48D
ST	M29F800AT	SOP44	PA44SO44D
ST	M29F800AT	TSOP48	PA48TS48D
ST	M29F800DB	SOP44	PA44SO44D
ST	M29F800DB	TSOP48	PA48TS48D
ST	M29F800DT	SOP44	PA44SO44D
ST	M29F800DT	TSOP48	PA48TS48D
ST	M29F800FB	TSOP48	PA48TS48D
ST	M29F800FT	SOP44	PA44SO44D
ST	M29KW016E	TSOP48	PA48TS48D1
ST	M29KW032E	TSOP48	PA48TS48D1
ST	M29KW064E	TSOP48	PA48TS48D1
ST	M29W004BB	TSOP40	PA40TS40D
ST	M29W004BT	TSOP40	PA40TS40D
ST	M29W008AB	TSOP40	PA40TS40D
ST	M29W008AT	TSOP40	PA40TS40D
ST	M29W010B	DIP32	
ST	M29W010B	PLCC32	PA32PL32D
ST	M29W010B	TSOP32	PA32TS20/PA32TS32D-20
ST	M29W017D	TSOP40	PA40TS40D
ST	M29W022BB	PLCC32	PA32PL32D
ST	M29W022BB	TSOP32	PA32TS20/PA32TS32D-20
ST	M29W022BT	PLCC32	PA32PL32D
ST	M29W022BT	TSOP32	PA32TS20/PA32TS32D-20
ST	M29W040	DIP32	
ST	M29W040	PLCC32	PA32PL32D
ST	M29W040	TSOP32	PA32TS20/PA32TS32D-20
ST	M29W040	TSOP32	PA32TS32D
ST	M29W040B	DIP32	
ST	M29W040B	PLCC32	PA32PL32D
ST	M29W040B	TSOP32	PA32TS20/PA32TS32D-20
ST	M29W040B	TSOP32	PA32TS32D
ST	M29W128FH	TSOP56	PA56TS48DB
ST	M29W128FL	TSOP56	PA56TS48DB
ST	M29W128GH	TSOP56	PA56TS48DB
ST	M29W128GL	TSOP56	PA56TS48DB
ST	M29W160DB	TSOP48	PA48TS48D
ST	M29W160DT	TSOP48	PA48TS48D
ST	M29W160EB	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
ST	M29W160EB	TSOP48	PA48TS48D
ST	M29W160ET	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
ST	M29W160ET	TSOP48	PA48TS48D
ST	M29W200BB	SOP44	PA44SO44D
ST	M29W200BB	TSOP48	PA48TS48D
ST	M29W200BT	SOP44	PA44SO44D
ST	M29W200BT	TSOP48	PA48TS48D
ST	M29W256GH-ZA	BGA64	NA64BG48DT
ST	M29W256GL	TSOP56	PA56TS48DD
ST	M29W256GL-ZA	BGA64	NA64BG48DT
ST	M29W320DB	TSOP48	PA48TS48D
ST	M29W320DT	TSOP48	PA48TS48D
ST	M29W320EB	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
ST	M29W320EB	TSOP48	PA48TS48D

ST	M29W320ET	BGA64	PA64BG48DK/HA64BG48DK/NA64BG48DK
ST	M29W320ET	TSOP48	PA48TS48D
ST	M29W400B	SOP44	PA44SO44D
ST	M29W400B	TSOP48	PA48TS48D
ST	M29W400BB	SOP44	PA44SO44D
ST	M29W400BB	TSOP48	PA48TS48D
ST	M29W400BT	SOP44	PA44SO44D
ST	M29W400BT	TSOP48	PA48TS48D
ST	M29W400DB	SOP44	PA44SO44D
ST	M29W400DB	TSOP48	PA48TS48D
ST	M29W400DT	SOP44	PA44SO44D
ST	M29W400DT	TSOP48	PA48TS48D
ST	M29W400FT	TSOP48	PA48TS48D
ST	M29W400T	SOP44	PA44SO44D
ST	M29W400T	TSOP48	PA48TS48D
ST	M29W512B	PLCC32	PA32PL32D
ST	M29W512B	TSOP32	PA32TS20/PA32TS32D-20
ST	M29W640DB	TSOP48	PA48TS48D
ST	M29W640DT	TSOP48	PA48TS48D
ST	M29W640FB	TSOP48	PA48TS48D
ST	M29W640FT	TSOP48	PA48TS48D
ST	M29W640GB	TSOP48	PA48TS48D
ST	M29W640GB	TSOP56	PA56TS48DB
ST	M29W640GB-ZF	BGA64	NA64BG48DT
ST	M29W640GH	BGA48	HA48BG48DAI
ST	M29W640GH	TSOP48	PA48TS48D
ST	M29W640GH	TSOP56	PA56TS48DB
ST	M29W640GH-ZF	BGA64	NA64BG48DT
ST	M29W640GL-ZF	BGA64	NA64BG48DT
ST	M29W640GT	TSOP48	PA48TS48D
ST	M29W640GT	TSOP56	PA56TS48DB
ST	M29W640GT-ZF	BGA64	NA64BG48DT
ST	M29W641D	TSOP48	PA48TS48D
ST	M29W800AB	SOP44	PA44SO44D
ST	M29W800AB	TSOP48	PA48TS48D
ST	M29W800AT	SOP44	PA44SO44D
ST	M29W800AT	TSOP48	PA48TS48D
ST	M29W800B	SOP44	PA44SO44D
ST	M29W800B	TSOP48	PA48TS48D
ST	M29W800DB	SOP44	PA44SO44D
ST	M29W800DB	TSOP48	PA48TS48D
ST	M29W800DT	SOP44	PA44SO44D
ST	M29W800DT	TSOP48	PA48TS48D
ST	M29W800T	SOP44	PA44SO44D
ST	M29W800T	TSOP48	PA48TS48D
ST	M30LW128D	EBGA64	PA64BGA48D/HA64BGA48D
ST	M30LW128D	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
ST	M34C02LBN	DIP8	
ST	M34C02LDW	TSSOP8	PA24TSS24D
ST	M34C02LDW	TSSOP8	PA8TSS8D
ST	M34C02LMN	SOIC8	PA8SO8D-EO-150
ST	M34C02RBN	DIP8	
ST	M34C02RDW	TSSOP8	PA24TSS24D
ST	M34C02RDW	TSSOP8	PA8TSS8D
ST	M34C02RMN	SOIC8	PA8SO8D-EO-150
ST	M34C02WBN	DIP8	
ST	M34C02WDW	TSSOP8	PA24TSS24D
ST	M34C02WDW	TSSOP8	PA8TSS8D
ST	M34C02WMN	SOIC8	PA8SO8D-EO-150
ST	M36A0W5030B0	BGA66	PA66BGA48DB
ST	M36A0W5030T0	BGA66	PA66BGA48DB
ST	M36L0R8060B	BGA88	HA88BGA48DA7
ST	M36L0R8060T	BGA88	HA88BGA48DA7
ST	M36WWT6650B0	BGA88	PA88BGA48DA-YO-8X10
ST	M36WWT6650D0	BGA88	PA88BGA48DA-YO-8X10
ST	M36WWT6650T0	BGA88	PA88BGA48DA-YO-8X10
ST	M45PE10VMN	SOP8	PA16SO16D-EO-150
ST	M45PE10VMP	MLP8	PA8SON8D(6x5)
ST	M45PE16VMP	MLP8	PA8SON8D(6x5)
ST	M45PE16VMW	SOP8	PA20SO20D-EO-210
ST	M45PE20VMN	SOP8	PA16SO16D-EO-150
ST	M45PE20VMP	MLP8	PA8SON8D(6x5)
ST	M45PE40VMN	SOP8	PA20SO20D-EO-210

ST	M45PE40VMP	MLP8	PA8SON8D(6x5)
ST	M45PE80VMN	SOP8	PA20SO20D-EO-210
ST	M45PE80VMP	MLP8	PA8SON8D(6x5)
ST	M48T02	DIP24	
ST	M48T08	DIP28	
ST	M48T12	DIP24	
ST	M48T18	DIP28	
ST	M48T35AV	EDIP28	
ST	M48T35AY	EDIP28	
ST	M48T35V	EDIP28	
ST	M48T35Y	EDIP28	
ST	M48T58	EDIP28	
ST	M48T58Y	EDIP28	
ST	M48Z02	DIP24	
ST	M48Z08	DIP28	
ST	M48Z12	DIP24	
ST	M48Z128	EDIP32	
ST	M48Z128V	EDIP32	
ST	M48Z128Y	EDIP32	
ST	M48Z129	EDIP32	
ST	M48Z129V	EDIP32	
ST	M48Z129Y	EDIP32	
ST	M48Z18	DIP28	
ST	M48Z256	EDIP32	
ST	M48Z256Y	EDIP32	
ST	M48Z35	EDIP28	
ST	M48Z35Y	EDIP28	
ST	M50FLW040A	PLCC32	PA32PL32D
ST	M50FLW040A	TSOP32	PA32TS32D
ST	M50FLW040A	TSOP40	PA40TS40D
ST	M50FLW040B	PLCC32	PA32PL32D
ST	M50FLW040B	TSOP32	PA32TS32D
ST	M50FLW040B	TSOP40	PA40TS40D
ST	M50FLW080A	PLCC32	PA32PL32D
ST	M50FLW080A	TSOP32	PA32TS32D
ST	M50FLW080A	TSOP40	PA40TS40D
ST	M50FLW080B	PLCC32	PA32PL32D
ST	M50FLW080B	TSOP32	PA32TS32D
ST	M50FLW080B	TSOP40	PA40TS40D
ST	M50FW016	TSOP40	PA40TS40D
ST	M50FW020	PLCC32	PA32PL32D
ST	M50FW040	PLCC32	PA32PL32D
ST	M50FW040	TSOP40	PA40TS40D
ST	M50FW080	PLCC32	PA32PL32D
ST	M50FW080	TSOP32	PA32TS32D
ST	M50FW080	TSOP40	PA40TS40D
ST	M50LPW020	PLCC32	PA32PL32D
ST	M50LPW040	PLCC32	PA32PL32D
ST	M50LPW040	TSOP40	PA40TS40D
ST	M50LPW080	PLCC32	PA32PL32D
ST	M50LPW080	TSOP40	PA40TS40D
ST	M50LPW116	TSOP40	PA40TS40D
ST	M58LT256-B	EBGA64	HA64BG48DP
ST	M58LT256-T	EBGA64	HA64BG48DP
ST	M58LW032A	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
ST	M58LW032A-ZA	EBGA64	PA64BGA48D/HA64BGA48D
ST	M58LW032C	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
ST	M58LW032C-ZA	EBGA64	PA64BGA48D/HA64BGA48D
ST	M58LW032D	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
ST	M58LW032D-ZA	EBGA64	PA64BGA48D/HA64BGA48D
ST	M58LW064D	TSOP56	PA56TS48D-B6-YAM/CIC-56TS-48D-B6-YAM-S
ST	M58LW064D-ZA	EBGA64	PA64BGA48D/HA64BGA48D
ST	M72DW54003BB	BGA73	PA73BGA48DC-YO-8X11.6
ST	M72DW54003TB	BGA73	PA73BGA48DC-YO-8X11.6
ST	M72DW64000B	BGA73	PA73BGA48DC-YO-8X11.6
ST	M87C257	DIP28	
ST	M9306	DIP8	
ST	M9346	DIP8	
ST	M93C06	DIP8	
ST	M93C06	SOIC8	PA16SO16D-EO-150
ST	M93C06	TSSOP8	PA8TSS-OT
ST	M93C06-R	DIP8	
ST	M93C06-R	SOIC8	PA16SO16D-EO-150

ST	M93C06-R	TSSOP8	PA8TSS-OT
ST	M93C06-T	SOIC8	PA8SO8D-EO-150
ST	M93C06-W	DIP8	
ST	M93C06-W	SOIC8	PA16SO16D-EO-150
ST	M93C06-W	TSSOP8	PA8TSS-OT
ST	M93C46	DIP8	
ST	M93C46	SOIC8	PA16SO16D-EO-150
ST	M93C46	TSSOP8	PA8TSS-OT
ST	M93C46-R	DIP8	
ST	M93C46-R	SOIC8	PA16SO16D-EO-150
ST	M93C46-R	TSSOP8	PA8TSS-OT
ST	M93C46-T	SOIC8	PA8SO8D-EO-150
ST	M93C46-W	DIP8	
ST	M93C46-W	SOIC8	PA16SO16D-EO-150
ST	M93C46-W	TSSOP8	PA8TSS-OT
ST	M93C56	DIP8	
ST	M93C56	SOIC8	PA16SO16D-EO-150
ST	M93C56	TSSOP8	PA8TSS-OT
ST	M93C56-R	DIP8	
ST	M93C56-R	SOIC8	PA16SO16D-EO-150
ST	M93C56-R	TSSOP8	PA8TSS-OT
ST	M93C56-T	SOIC8	PA8SO8D-EO-150
ST	M93C56-W	DIP8	
ST	M93C56-W	SOIC8	PA16SO16D-EO-150
ST	M93C56-W	TSSOP8	PA8TSS-OT
ST	M93C66	DIP8	
ST	M93C66	SOIC8	PA16SO16D-EO-150
ST	M93C66	TSSOP8	PA8TSS-OT
ST	M93C66-R	DIP8	
ST	M93C66-R	SOIC8	PA16SO16D-EO-150
ST	M93C66-R	TSSOP8	PA8TSS-OT
ST	M93C66-T	SOIC8	PA8SO8D-EO-150
ST	M93C66-W	DIP8	
ST	M93C66-W	SOIC8	PA16SO16D-EO-150
ST	M93C66-W	TSSOP8	PA8TSS-OT
ST	M93C76	DIP8	
ST	M93C76	SOIC8	PA16SO16D-EO-150
ST	M93C76	TSSOP8	PA8TSS-OT
ST	M93C76-R	DIP8	
ST	M93C76-R	SOIC8	PA16SO16D-EO-150
ST	M93C76-R	TSSOP8	PA8TSS-OT
ST	M93C76-T	SOIC8	PA8SO8D-EO-150
ST	M93C76-W	DIP8	
ST	M93C76-W	SOIC8	PA16SO16D-EO-150
ST	M93C76-W	TSSOP8	PA8TSS-OT
ST	M93C86	DIP8	
ST	M93C86	SOIC8	PA16SO16D-EO-150
ST	M93C86	TSSOP8	PA8TSS-OT
ST	M93C86-R	DIP8	
ST	M93C86-R	SOIC8	PA16SO16D-EO-150
ST	M93C86-R	TSSOP8	PA8TSS-OT
ST	M93C86-T	SOIC8	PA8SO8D-EO-150
ST	M93C86-W	DIP8	
ST	M93C86-W	SOIC8	PA16SO16D-EO-150
ST	M93C86-W	TSSOP8	PA8TSS-OT
ST	M93S46	DIP8	
ST	M93S46	SOIC8	PA16SO16D-EO-150
ST	M93S46	TSSOP8	PA8TSS-OT
ST	M93S46-R	DIP8	
ST	M93S46-R	SOIC8	PA16SO16D-EO-150
ST	M93S46-R	TSSOP8	PA8TSS-OT
ST	M93S46-W	DIP8	
ST	M93S46-W	SOIC8	PA16SO16D-EO-150
ST	M93S46-W	TSSOP8	PA8TSS-OT
ST	M93S56	DIP8	
ST	M93S56	SOIC8	PA16SO16D-EO-150
ST	M93S56	TSSOP8	PA8TSS-OT
ST	M93S56-R	DIP8	
ST	M93S56-R	SOIC8	PA16SO16D-EO-150
ST	M93S56-R	TSSOP8	PA8TSS-OT
ST	M93S56-W	DIP8	
ST	M93S56-W	SOIC8	PA16SO16D-EO-150
ST	M93S56-W	TSSOP8	PA8TSS-OT

ST	M93S66	DIP8	
ST	M93S66	SOIC8	PA16SO16D-EO-150
ST	M93S66	TSSOP8	PA8TSS-OT
ST	M93S66-R	DIP8	
ST	M93S66-R	SOIC8	PA16SO16D-EO-150
ST	M93S66-R	TSSOP8	PA8TSS-OT
ST	M93S66-W	DIP8	
ST	M93S66-W	SOIC8	PA16SO16D-EO-150
ST	M93S66-W	TSSOP8	PA8TSS-OT
ST	M95010-R	DIP8	
ST	M95010-R	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95010-R	TSSOP8	PA8TSS8D
ST	M95010-R	USON8	PA8SON8D(2x3)
ST	M95010-W	DIP8	
ST	M95010-W	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95010-W	TSSOP8	PA8TSS8D
ST	M95010-W	USON8	PA8SON8D(2x3)
ST	M95020-R	DIP8	
ST	M95020-R	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95020-R	TSSOP8	PA8TSS8D
ST	M95020-R	USON8	PA8SON8D(2x3)
ST	M95020-W	DIP8	
ST	M95020-W	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95020-W	TSSOP8	PA8TSS8D
ST	M95020-W	USON8	PA8SON8D(2x3)
ST	M95040-DF	DIP8	
ST	M95040-DF	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95040-DF	TSSOP8	PA8TSS8D
ST	M95040-DF	USON8	PA8SON8D(2x3)
ST	M95040-R	DIP8	
ST	M95040-R	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95040-R	TSSOP8	PA8TSS8D
ST	M95040-R	USON8	PA8SON8D(2x3)
ST	M95040-W	DIP8	
ST	M95040-W	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95040-W	TSSOP8	PA8TSS8D
ST	M95040-W	USON8	PA8SON8D(2x3)
ST	M95080-DF	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95080-DF	TSSOP8	PA8TSS8D
ST	M95080-DF	USON8	PA8SON8D(2x3)
ST	M95080-R	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95080-R	TSSOP8	PA8TSS8D
ST	M95080-R	USON8	PA8SON8D(2x3)
ST	M95080-W	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95080-W	TSSOP8	PA8TSS8D
ST	M95080-W	USON8	PA8SON8D(2x3)
ST	M95128-DF	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95128-DF	TSSOP8	PA8TSS8D
ST	M95128-DF	USON8	PA8SON8D(2x3)
ST	M95128-R	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95128-R	TSSOP8	PA8TSS8D
ST	M95128-R	USON8	PA8SON8D(2x3)
ST	M95128-W	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95128-W	TSSOP8	PA8TSS8D
ST	M95128-W	USON8	PA8SON8D(2x3)
ST	M95160	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95160	TSSOP8	PA8TSS8D
ST	M95160	USON8	PA8SON8D(2x3)
ST	M95160-DF	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95160-DF	TSSOP8	PA8TSS8D
ST	M95160-DF	USON8	PA8SON8D(2x3)
ST	M95160-R	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95160-R	TSSOP8	PA8TSS8D
ST	M95160-R	USON8	PA8SON8D(2x3)
ST	M95160-W	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95160-W	TSSOP8	PA8TSS8D
ST	M95160-W	USON8	PA8SON8D(2x3)
ST	M95256-DF	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95256-DF	TSSOP8	PA8TSS8D
ST	M95256-DF	USON8	PA8SON8D(2x3)
ST	M95256-R	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95256-R	TSSOP8	PA8TSS8D
ST	M95256-R	USON8	PA8SON8D(2x3)

ST	M95256-W	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95256-W	TSSOP8	PA8TSS8D
ST	M95256-W	USON8	PA8SON8D(2x3)
ST	M95320-DF	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95320-DF	TSSOP8	PA8TSS8D
ST	M95320-DF	USON8	PA8SON8D(2x3)
ST	M95320-R	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95320-R	TSSOP8	PA8TSS8D
ST	M95320-R	USON8	PA8SON8D(2x3)
ST	M95320-W	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95320-W	TSSOP8	PA8TSS8D
ST	M95320-W	USON8	PA8SON8D(2x3)
ST	M95512-DF	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95512-DF	TSSOP8	PA8TSS8D
ST	M95512-DF	USON8	PA8SON8D(2x3)
ST	M95512-R	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95512-R	TSSOP8	PA8TSS8D
ST	M95512-R	USON8	PA8SON8D(2x3)
ST	M95512-W	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95512-W	TSSOP8	PA8TSS8D
ST	M95512-W	USON8	PA8SON8D(2x3)
ST	M95640-DF	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95640-DF	TSSOP8	PA8TSS8D
ST	M95640-DF	USON8	PA8SON8D(2x3)
ST	M95640-R	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95640-R	TSSOP8	PA8TSS8D
ST	M95640-R	USON8	PA8SON8D(2x3)
ST	M95640-W	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95640-W	TSSOP8	PA8TSS8D
ST	M95640-W	USON8	PA8SON8D(2x3)
ST	M95M01-DF	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95M01-DF	TSSOP8	PA8TSS8D
ST	M95M01-R	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95M01-R	TSSOP8	PA8TSS8D
ST	M95M02-DR	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95M04-DR	SOP8	PA16SO16D-EO-150/PA8SO8D-150
ST	M95M04-DR	TSSOP8	PA8TSS8D
ST	MK48T02	DIP24	
ST	MK48T02B	DIP24	
ST	MK48T08	DIP28	
ST	MK48T08B	DIP28	
ST	MK48T12	DIP24	
ST	MK48T18	DIP28	
ST	MK48T18B	DIP28	
ST	MK48Z02	DIP24	
ST	MK48Z02B	DIP24	
ST	MK48Z08	DIP28	
ST	MK48Z08B	DIP28	
ST	MK48Z09	EDIP28	
ST	MK48Z12	DIP24	
ST	MK48Z18	DIP28	
ST	MK48Z18B	DIP28	
ST	MK48Z19	EDIP28	
ST	NAND01GW3A	TSOP48	PA48TS48D
ST	NAND01GW3B	TSOP48	PA48TS48D
ST	NAND01GW3M2A	BGA137	HA137BGA48DI
ST	NAND02GW3B	TSOP48	PA48TS48D
ST	NAND04GW3B	TSOP48	PA48TS48D
ST	NAND08GW3B-size4G	TSOP48	PA48TS48D
ST	NAND128W3A	TSOP48	PA48TS48D
ST	NAND256W3A	TSOP48	PA48TS48D
ST	NAND512W3A	TSOP48	PA48TS48D
ST	PSD301	PLCC44	PA44-48U-PSD3xx
ST	PSD302	PLCC44	PA44-48U-PSD3xx
ST	PSD311	PLCC44	PA44-48U-PSD3xx
ST	PSD312	PLCC44	PA44-48U-PSD3xx
ST	ST24C02	DIP8	
ST	ST24C02R	DIP8	
ST	ST24W02	DIP8	
ST	ST25C02	DIP8	
ST	ST25W02	DIP8	
ST	ST27128A	DIP28	
ST	ST27256	DIP28	

ST	ST2764A	DIP28	
ST	ST27C256	DIP28	
ST	ST27C256	PLCC32	PA32PL28D-YA
ST	ST62E01C	DIP16	
ST	ST62E03C	DIP16	
ST	ST62E20	DIP20	
ST	ST62E20B	DIP20	
ST	ST62E20C	DIP20	
ST	ST62E25	DIP28	
ST	ST62E25B	DIP28	
ST	ST62E25C	DIP28	
ST	ST62E28C	DIP28	
ST	ST62E30B	DIP28	
ST	ST62E60	DIP20	
ST	ST62E60B	DIP20	
ST	ST62E60C	DIP20	
ST	ST62E65	DIP28	
ST	ST62E65B	DIP28	
ST	ST62E65C	DIP28	
ST	ST62T00C	DIP16	
ST	ST62T00C	SOIC16	PA28SO28D-EO-300
ST	ST62T00C	SSOP16	PA20SO20D-EO-210
ST	ST62T01C	DIP16	
ST	ST62T01C	SOIC16	PA28SO28D-EO-300
ST	ST62T01C	SSOP16	PA20SO20D-EO-210
ST	ST62T03C	DIP16	
ST	ST62T03C	SOIC16	PA28SO28D-EO-300
ST	ST62T03C	SSOP16	PA20SO20D-EO-210
ST	ST62T08C	DIP20	
ST	ST62T08C	SOIC20	PA28SO28D-EO-300
ST	ST62T08C	SSOP20	PA20SO20D-EO-210
ST	ST62T09C	DIP20	
ST	ST62T09C	SOIC20	PA28SO28D-EO-300
ST	ST62T09C	SSOP20	PA20SO20D-EO-210
ST	ST62T10	DIP20	
ST	ST62T10B	DIP20	
ST	ST62T10C	DIP20	
ST	ST62T10C	SOIC20	PA28SO28D-EO-300
ST	ST62T10C	SSOP20	PA20SO20D-EO-210
ST	ST62T15	DIP28	
ST	ST62T15B	DIP28	
ST	ST62T15C	DIP28	
ST	ST62T15C	SOIC28	PA28SO28D-EO-300
ST	ST62T15C	SSOP28	PA28SO28D-EO-210
ST	ST62T20	DIP20	
ST	ST62T20B	DIP20	
ST	ST62T20C	DIP20	
ST	ST62T20C	SOIC20	PA28SO28D-EO-300
ST	ST62T20C	SSOP20	PA20SO20D-EO-210
ST	ST62T25	DIP28	
ST	ST62T25B	DIP28	
ST	ST62T25C	DIP28	
ST	ST62T25C	SOIC28	PA28SO28D-EO-300
ST	ST62T25C	SSOP28	PA28SO28D-EO-210
ST	ST62T28C	DIP28	
ST	ST62T28C	SOIC28	PA28SO28D-EO-300
ST	ST62T28C	SSOP28	PA28SO28D-EO-210
ST	ST62T30B	DIP28	
ST	ST62T30B	SOIC28	PA28SO28D-EO-300
ST	ST62T53C	DIP20	
ST	ST62T53C	SOIC20	PA28SO28D-EO-300
ST	ST62T55C	DIP28	
ST	ST62T55C	SOIC28	PA28SO28D-EO-300
ST	ST62T55C	SSOP28	PA28SO28D-EO-210
ST	ST62T60	DIP20	
ST	ST62T60B	DIP20	
ST	ST62T60C	DIP20	
ST	ST62T60C	SOIC20	PA28SO28D-EO-300
ST	ST62T63C	DIP20	
ST	ST62T63C	SOIC20	PA28SO28D-EO-300
ST	ST62T65	DIP28	
ST	ST62T65B	DIP28	
ST	ST62T65C	DIP28	

ST	ST62T65C	SOIC28	PA28SO28D-EO-300
ST	ST62T65C	SSOP28	PA28SO28D-EO-210
ST	ST72F260G1B	SDIP32	PA32SD32D
ST	ST72F260G1M	SOIC28	PA28SO28D-EO-300
ST	ST72F260G2B	SDIP32	PA32SD32D
ST	ST72F260G2M	SOIC28	PA28SO28D-EO-300
ST	ST72F262G1B	SDIP32	PA32SD32D
ST	ST72F262G1M	SOIC28	PA28SO28D-EO-300
ST	ST72F262G2B	SDIP32	PA32SD32D
ST	ST72F262G2M	SOIC28	PA28SO28D-EO-300
ST	ST72F264G1B	SDIP32	PA32SD32D
ST	ST72F264G1M	SOIC28	PA28SO28D-EO-300
ST	ST72F264G2B	SDIP32	PA32SD32D
ST	ST72F264G2M	SOIC28	PA28SO28D-EO-300
ST	ST93C46A	DIP8	
ST	ST93C46A	SOIC8	PA16SO16D-EO-150
ST	ST93C46C	DIP8	
ST	ST93C46C	SOIC8	PA16SO16D-EO-150
ST	ST93C46T	SOIC8	PA16SO16D-EO-150
ST	ST93C47C	DIP8	
ST	ST93C47C	SOIC8	PA16SO16D-EO-150
ST	ST93C47T	SOIC8	PA16SO16D-EO-150
ST	ST93C56	DIP8	
ST	ST93C56	SOIC8	PA16SO16D-EO-150
ST	ST93C56C	DIP8	
ST	ST93C56C	SOIC8	PA16SO16D-EO-150
ST	ST93C57C	DIP8	
ST	ST93C57C	SOIC8	PA16SO16D-EO-150
ST	ST93C66	DIP8	
ST	ST93C66	SOIC8	PA16SO16D-EO-150
ST	ST93C67	DIP8	
ST	ST93C67	SOIC8	PA16SO16D-EO-150
ST	ST93CS46	DIP8	
ST	ST93CS46	SOIC8	PA16SO16D-EO-150
ST	ST93CS47	DIP8	
ST	ST93CS47	SOIC8	PA16SO16D-EO-150
ST	ST93CS56	DIP8	
ST	ST93CS56	SOIC8	PA16SO16D-EO-150
ST	ST93CS57	DIP8	
ST	ST93CS57	SOIC8	PA16SO16D-EO-150
ST	ST93CS66	DIP8	
ST	ST93CS66	SOIC8	PA16SO16D-EO-150
ST	ST93CS67	DIP8	
ST	ST93CS67	SOIC8	PA16SO16D-EO-150
ST	STM8L151G6U	MLF28	HA28QFN48DA
ST	STM8S103F2	TSSOP20	HA20TSS48DB
ST	STM8S103F3	TSSOP20	HA20TSS48DB
ST	STM8S103K3	LQFP32	PA32LQ48D
ST	STM8S105C4T	LQFP48	PA48LQ48DC
ST	STM8S105S4T	LQFP44	PA44LQ48D
ST	STM8S207C6	LQFP48	PA48LQ48DC
ST	STTS2004	DFN8	PA8QFN8D(2x3)
ST	TS27C256	DIP28	
ST	TS27C64	DIP28	
ST	TS27C64A	DIP28	
ST	TS27C64A	PLCC32	PA32PL28D-YA
ST	TS28C16A	DIP24	
ST	TS28C17A	DIP28	
ST	TS28C64	DIP28	
SYNCMOS	F29C51001B	DIP32	
SYNCMOS	F29C51001B	PLCC32	PA32PL32D
SYNCMOS	F29C51001B	TSOP32	PA32TS20/PA32TS32D-20
SYNCMOS	F29C51001T	DIP32	
SYNCMOS	F29C51001T	PLCC32	PA32PL32D
SYNCMOS	F29C51001T	TSOP32	PA32TS20/PA32TS32D-20
SYNCMOS	F29C51002B	DIP32	
SYNCMOS	F29C51002B	PLCC32	PA32PL32D
SYNCMOS	F29C51002B	TSOP32	PA32TS20/PA32TS32D-20
SYNCMOS	F29C51002T	DIP32	
SYNCMOS	F29C51002T	PLCC32	PA32PL32D
SYNCMOS	F29C51002T	TSOP32	PA32TS20/PA32TS32D-20
SYNCMOS	F29C51004B	DIP32	
SYNCMOS	F29C51004B	PLCC32	PA32PL32D



SYNCMOS	F29C51004B	TSOP32	PA32TS20/PA32TS32D-20
SYNCMOS	F29C51004T	DIP32	
SYNCMOS	F29C51004T	PLCC32	PA32PL32D
SYNCMOS	F29C51004T	TSOP32	PA32TS20/PA32TS32D-20
SYNCMOS	S29C31004B	DIP32	
SYNCMOS	S29C31004B	PLCC32	PA32PL32D
SYNCMOS	S29C31004B	TSOP32	PA32TS20/PA32TS32D-20
SYNCMOS	S29C31004T	DIP32	
SYNCMOS	S29C31004T	PLCC32	PA32PL32D
SYNCMOS	S29C31004T	TSOP32	PA32TS20/PA32TS32D-20
SYNCMOS	S29C51001B	DIP32	
SYNCMOS	S29C51001B	PLCC32	PA32PL32D
SYNCMOS	S29C51001B	TSOP32	PA32TS20/PA32TS32D-20
SYNCMOS	S29C51001T	DIP32	
SYNCMOS	S29C51001T	PLCC32	PA32PL32D
SYNCMOS	S29C51001T	TSOP32	PA32TS20/PA32TS32D-20
SYNCMOS	S29C51002B	DIP32	
SYNCMOS	S29C51002B	PLCC32	PA32PL32D
SYNCMOS	S29C51002B	TSOP32	PA32TS20/PA32TS32D-20
SYNCMOS	S29C51002T	DIP32	
SYNCMOS	S29C51002T	PLCC32	PA32PL32D
SYNCMOS	S29C51002T	TSOP32	PA32TS20/PA32TS32D-20
SYNCMOS	S29C51004T	DIP32	
SYNCMOS	S29C51004T	PLCC32	PA32PL32D
SYNCMOS	S29C51004T	TSOP32	PA32TS20/PA32TS32D-20
SYNCMOS	SM5964	DIP40	
SYNCMOS	SM5964	PLCC44	PA44-48U
SYNCMOS	SM5964	QFP44	PA44QF44D
SYNCMOS	SM8951	DIP40	
SYNCMOS	SM8951	PLCC44	PA44-48U
SYNCMOS	SM89516	DIP40	
SYNCMOS	SM89516	PLCC44	PA44-48U
SYNCMOS	SM89516	QFP44	PA44QF44D
SYNCMOS	SM89516A	DIP40	
SYNCMOS	SM89516A	PLCC44	PA44-48U
SYNCMOS	SM89516A	QFP44	PA44QF44D
SYNCMOS	SM8951A	DIP40	
SYNCMOS	SM8951A	PLCC44	PA44-48U
SYNCMOS	SM8951A	QFP44	PA44QF44D
SYNCMOS	SM8952	DIP40	
SYNCMOS	SM8952	PLCC44	PA44-48U
SYNCMOS	SM8952A	DIP40	
SYNCMOS	SM8952A	PLCC44	PA44-48U
SYNCMOS	SM8952A	QFP44	PA44QF44D
SYNCMOS	SM8954	DIP40	
SYNCMOS	SM8954	PLCC44	PA44-48U
SYNCMOS	SM8954A	DIP40	
SYNCMOS	SM8954A	PLCC44	PA44-48U
SYNCMOS	SM8954A	QFP44	PA44QF44D
SYNCMOS	SM8958	DIP40	
SYNCMOS	SM8958	PLCC44	PA44-48U
SYNCMOS	SM8958A	DIP40	
SYNCMOS	SM8958A	PLCC44	PA44-48U
SYNCMOS	SM8958A	QFP44	PA44QF44D
SYNERTEK	SY2716	DIP24	
TELECHIP	TCC763H309-A	BGA144	PA144BG48D
TELECHIP	TCC764H309-A	BGA144	PA144BG48D
TELECHIP	TCC766H303-A	BGA232	PA232BG48D
TELECHIP	TCC767H301-A	BGA225	PA225BG48D
TEMIC	AT89C51RE2	PLCC44	PA44PL48D
TEMIC	T87C5101	DIP24	
TEMIC	T87C5101	SOP24	PA28SO28D-EO-300
TEMIC	T87C5103	DIP16	
TEMIC	T87C5103	DIP24	
TEMIC	T87C5103	SSOP16	PA28SS-OT
TEMIC	T87C5103	SSOP24	PA28SS-OT
TEMIC	T87C5111	DIP24	
TEMIC	T87C5111	SOP24	PA28SO-08(C)
TEMIC	T87C5111	SSOP16	PA24TSS24D
TEMIC	T87C5111	SSOP24	PA24TSS24D
TEMIC	T89C5115	PLCC28	PA28PL28D
TEMIC	T89C5115	QFP32	PA32TQ32D
TEMIC	T89C5115	SOP24	PA28SO28D-EO-300

TEMIC	T89C5115	SOP28	PA28SO28D-EO-300
TEMIC	T89C51AC2	PLCC44	PA44-48U
TEMIC	T89C51CC01	PLCC44	PA44-48U
TEMIC	T89C51CC01	TQFP44	PA44TQ44D-EO
TEMIC	T89C51CC02	PLCC28	PA28PL28D
TEMIC	T89C51CC02	QFP32	PA32TQ32D-YC
TEMIC	T89C51CC02	SOP24	PA28SO28D-EO-300
TEMIC	T89C51CC02	SOP28	PA28SO28D-EO-300
TEMIC	T89C51IB2-xL_3V	PLCC44	PA44-48U
TEMIC	T89C51IB2-xL_3V	QFP44	PA44QF44D
TEMIC	T89C51IB2-xM_5V	PLCC44	PA44-48U
TEMIC	T89C51IB2-xM_5V	QFP44	PA44QF44D
TEMIC	T89C51IC2-xL_3V	PLCC44	PA44-48U
TEMIC	T89C51IC2-xL_3V	QFP44	PA44QF44D
TEMIC	T89C51IC2-xM_5V	PLCC44	PA44-48U
TEMIC	T89C51IC2-xM_5V	QFP44	PA44QF44D
TEMIC	T89C51RB2-xL_3V	DIP40	
TEMIC	T89C51RB2-xL_3V	PLCC44	PA44-48U
TEMIC	T89C51RB2-xL_3V	QFP44	PA44QF44D
TEMIC	T89C51RB2-xM_5V	DIP40	
TEMIC	T89C51RB2-xM_5V	PLCC44	PA44-48U
TEMIC	T89C51RB2-xM_5V	QFP44	PA44QF44D
TEMIC	T89C51RC2-xL_3V	DIP40	
TEMIC	T89C51RC2-xL_3V	PLCC44	PA44-48U
TEMIC	T89C51RC2-xL_3V	QFP44	PA44QF44D
TEMIC	T89C51RC2-xM_5V	DIP40	
TEMIC	T89C51RC2-xM_5V	PLCC44	PA44-48U
TEMIC	T89C51RC2-xM_5V	QFP44	PA44QF44D
TEMIC	T89C51RD2-xL_3V	DIP40	
TEMIC	T89C51RD2-xL_3V	PLCC44	PA44-48U
TEMIC	T89C51RD2-xM_5V	DIP40	
TEMIC	T89C51RD2-xM_5V	PLCC44	PA44-48U
TEMIC	TS87C51U2	DIP40	
TEMIC	TS87C51U2	PLCC44	PA44-48U
TEMIC	TS87C51U2	TQFP44	PA44VQ44D
TEMIC	TS87C58X2	DIP40	
TEMIC	TS87C58X2	PLCC44	PA44-48U
TEMIC	TSC71RBX2	DIP40	
TEMIC	TSC71RBX2	PLCC44	PA44-48U
TEMIC	TSC71RCX2	DIP40	
TEMIC	TSC71RCX2	PLCC44	PA44-48U
TEMIC	TSC71RDX2	DIP40	
TEMIC	TSC71RDX2	PLCC44	PA44-48U
TEMIC	TSC87251G1A	DIP40	
TEMIC	TSC87251G1A	PLCC44	PA44-48U
TEMIC	TSC87251G1D	DIP40	
TEMIC	TSC87251G1D	PLCC44	PA44-48U
TEMIC	TSC87251G2D	DIP40	
TEMIC	TSC87251G2D	PLCC44	PA44-48U
TEMIC	TSC87C51	DIP40	
TEMIC	TSC87C51	PLCC44	PA44-48U
TEMIC	TSC87C51RB2	DIP40	
TEMIC	TSC87C51RB2	PLCC44	PA44-48U
TEMIC	TSC87C51RC2	DIP40	
TEMIC	TSC87C51RC2	PLCC44	PA44-48U
TEMIC	TSC87C51RD2	DIP40	
TEMIC	TSC87C51RD2	PLCC44	PA44-48U
TEMIC	TSC87C52	DIP40	
TEMIC	TSC87C52	PLCC44	PA44-48U
TEMIC	TSC87C52X2	DIP40	
TEMIC	TSC87C52X2	PLCC44	PA44-48U
TEMIC	TSC87C54	DIP40	
TEMIC	TSC87C54	PLCC44	PA44-48U
TEMIC	TSC87C58	DIP40	
TEMIC	TSC87C58	PLCC44	PA44-48U
TEXAS INSTRUMENTS	SMJ2516	DIP24	
TEXAS INSTRUMENTS	SMJ2764	DIP28	
TEXAS INSTRUMENTS	SMJ27C256	DIP28	
TEXAS INSTRUMENTS	SMJ27C256	PLCC32	PA32PL28D-YA
TEXAS INSTRUMENTS	SMJ27C512	DIP28	
TEXAS INSTRUMENTS	SMJ27C512	PLCC32	PA32PL28D-YA
TEXAS INSTRUMENTS	SMJ27C64	DIP28	
TEXAS INSTRUMENTS	TBP28L22	DIP20	

TEXAS INSTRUMENTS	TICPAL16L8-55	DIP20	
TEXAS INSTRUMENTS	TICPAL16L8-55	PLCC20	PA20LC20D[Dead Bug]
TEXAS INSTRUMENTS	TICPAL16R4-55	DIP20	
TEXAS INSTRUMENTS	TICPAL16R4-55	PLCC20	PA20LC20D[Dead Bug]
TEXAS INSTRUMENTS	TICPAL16R6-55	DIP20	
TEXAS INSTRUMENTS	TICPAL16R6-55	PLCC20	PA20LC20D[Dead Bug]
TEXAS INSTRUMENTS	TICPAL16R8-55	DIP20	
TEXAS INSTRUMENTS	TICPAL16R8-55	PLCC20	PA20LC20D[Dead Bug]
TEXAS INSTRUMENTS	TICPAL22V10Z(T)	DIP24	
TEXAS INSTRUMENTS	TICPAL22V10Z(T)	PLCC28	PA28PL24D2P6-YA
TEXAS INSTRUMENTS	TICPAL22V10Z(ZP)	DIP24	
TEXAS INSTRUMENTS	TICPAL22V10Z(ZP)	PLCC28	PA28PL24D2P6-YA
TEXAS INSTRUMENTS	TMS2516JL	DIP24	
TEXAS INSTRUMENTS	TMS2532	DIP24	
TEXAS INSTRUMENTS	TMS2532A	DIP24	
TEXAS INSTRUMENTS	TMS2564	DIP28	
TEXAS INSTRUMENTS	TMS27128	DIP28	
TEXAS INSTRUMENTS	TMS2716JL	DIP24	
TEXAS INSTRUMENTS	TMS2732A	DIP24	
TEXAS INSTRUMENTS	TMS2764	DIP28	
TEXAS INSTRUMENTS	TMS27C010	DIP32	
TEXAS INSTRUMENTS	TMS27C010	PLCC32	PA32PL32D
TEXAS INSTRUMENTS	TMS27C010	TSOP32	PA32TS20/PA32TS32D-20
TEXAS INSTRUMENTS	TMS27C010A	DIP32	
TEXAS INSTRUMENTS	TMS27C010A	PLCC32	PA32PL32D
TEXAS INSTRUMENTS	TMS27C010A	TSOP32	PA32TS20/PA32TS32D-20
TEXAS INSTRUMENTS	TMS27C020	DIP32	
TEXAS INSTRUMENTS	TMS27C020	PLCC32	PA32PL32D
TEXAS INSTRUMENTS	TMS27C040	DIP32	
TEXAS INSTRUMENTS	TMS27C040	PLCC32	PA32PL32D
TEXAS INSTRUMENTS	TMS27C128	DIP28	
TEXAS INSTRUMENTS	TMS27C128	PLCC32	PA32PL28D-YA
TEXAS INSTRUMENTS	TMS27C210	DIP40	
TEXAS INSTRUMENTS	TMS27C210	PLCC44	PA44-48U
TEXAS INSTRUMENTS	TMS27C210A	DIP40	
TEXAS INSTRUMENTS	TMS27C210A	PLCC44	PA44-48U
TEXAS INSTRUMENTS	TMS27C240	DIP40	
TEXAS INSTRUMENTS	TMS27C240	PLCC44	PA44-48U
TEXAS INSTRUMENTS	TMS27C256	DIP28	
TEXAS INSTRUMENTS	TMS27C256	PLCC32	PA32PL28D-YA
TEXAS INSTRUMENTS	TMS27C32	DIP24	
TEXAS INSTRUMENTS	TMS27C512	DIP28	
TEXAS INSTRUMENTS	TMS27C512	PLCC32	PA32PL28D-YA
TEXAS INSTRUMENTS	TMS27C64	DIP28	
TEXAS INSTRUMENTS	TMS27LV010A	DIP32	
TEXAS INSTRUMENTS	TMS27LV010A	PLCC32	PA32PL32D
TEXAS INSTRUMENTS	TMS27LV010A	TSOP32	PA32TS20/PA32TS32D-20
TEXAS INSTRUMENTS	TMS27P32A	DIP24	
TEXAS INSTRUMENTS	TMS27P64	DIP28	
TEXAS INSTRUMENTS	TMS27PC010	DIP32	
TEXAS INSTRUMENTS	TMS27PC010	PLCC32	PA32PL32D
TEXAS INSTRUMENTS	TMS27PC010	TSOP32	PA32TS20/PA32TS32D-20
TEXAS INSTRUMENTS	TMS27PC010A	PLCC32	PA32PL32D
TEXAS INSTRUMENTS	TMS27PC010A	TSOP32	PA32TS20/PA32TS32D-20
TEXAS INSTRUMENTS	TMS27PC020	DIP32	
TEXAS INSTRUMENTS	TMS27PC020	PLCC32	PA32PL32D
TEXAS INSTRUMENTS	TMS27PC040	DIP32	
TEXAS INSTRUMENTS	TMS27PC040	PLCC32	PA32PL32D
TEXAS INSTRUMENTS	TMS27PC128	DIP28	
TEXAS INSTRUMENTS	TMS27PC128	PLCC32	PA32PL28D-YA
TEXAS INSTRUMENTS	TMS27PC210	DIP40	
TEXAS INSTRUMENTS	TMS27PC210	PLCC44	PA44-48U
TEXAS INSTRUMENTS	TMS27PC210A	DIP40	
TEXAS INSTRUMENTS	TMS27PC210A	PLCC44	PA44-48U
TEXAS INSTRUMENTS	TMS27PC240	DIP40	
TEXAS INSTRUMENTS	TMS27PC240	PLCC44	PA44-48U
TEXAS INSTRUMENTS	TMS27PC256	DIP28	
TEXAS INSTRUMENTS	TMS27PC256	PLCC32	PA32PL28D-YA
TEXAS INSTRUMENTS	TMS27PC32	DIP24	
TEXAS INSTRUMENTS	TMS27PC512	DIP28	
TEXAS INSTRUMENTS	TMS27PC512	PLCC32	PA32PL28D-YA
TEXAS INSTRUMENTS	TMS27PC64	DIP28	
TEXAS INSTRUMENTS	TMS28C64	DIP28	

TEXAS INSTRUMENTS	TMS28F020	DIP32	
TEXAS INSTRUMENTS	TMS28F020	PLCC32	PA32PL32D
TEXAS INSTRUMENTS	TMS28F020	TSOP32	PA32TS20/PA32TS32D-20
TEXAS INSTRUMENTS	TMS28F512A	PLCC32	PA32PL32D
TEXAS INSTRUMENTS	TMS29F010	DIP32	
TEXAS INSTRUMENTS	TMS29F040	DIP32	
TEXAS INSTRUMENTS	TMS29LF040	DIP32	
TEXAS INSTRUMENTS	TMS29VF040	DIP32	
TEXAS INSTRUMENTS	TMS320E15	DIP40	
TEXAS INSTRUMENTS	TMS320E15	PLCC44	PA44-48U
TEXAS INSTRUMENTS	TMS320P15	DIP40	
TEXAS INSTRUMENTS	TMS320P15	PLCC44	PA44-48U
TOSHIBA	TC531000CP	DIP28	
TOSHIBA	TC531001CF	SOP32	PA44SO44D
TOSHIBA	TC531001CP	DIP32	
TOSHIBA	TC541000J	DIP32	
TOSHIBA	TC541000P	DIP32	
TOSHIBA	TC541001J	DIP32	
TOSHIBA	TC541001P	DIP32	
TOSHIBA	TC54256AF	DIP28	
TOSHIBA	TC54256AP	DIP28	
TOSHIBA	TC544000P	DIP32	
TOSHIBA	TC54512AP	DIP28	
TOSHIBA	TC54H1024P	DIP40	
TOSHIBA	TC54H1024P	PLCC44	PA44-48U
TOSHIBA	TC571000AD	DIP32	
TOSHIBA	TC571000D	DIP32	
TOSHIBA	TC571001AD	DIP32	
TOSHIBA	TC571001D	DIP32	
TOSHIBA	TC571024D	DIP40	
TOSHIBA	TC571024D	PLCC44	PA44-48U
TOSHIBA	TC57256	DIP28	
TOSHIBA	TC57256AD	DIP28	
TOSHIBA	TC57256ADI	DIP28	
TOSHIBA	TC57256D	DIP28	
TOSHIBA	TC574000D	DIP32	
TOSHIBA	TC574000DI	DIP32	
TOSHIBA	TC574096D	DIP40	
TOSHIBA	TC574096D	PLCC44	PA44-48U
TOSHIBA	TC574200D	DIP40	
TOSHIBA	TC57512AD	DIP28	
TOSHIBA	TC578200D	DIP42	
TOSHIBA	TC57H1000AD	DIP32	
TOSHIBA	TC57H1001AD	DIP32	
TOSHIBA	TC57H1024AD	DIP40	
TOSHIBA	TC57H1024AD	PLCC44	PA44-48U
TOSHIBA	TC57H1024D	DIP40	
TOSHIBA	TC57H1024D	PLCC44	PA44-48U
TOSHIBA	TC57H1025AD	DIP40	
TOSHIBA	TC57H1025AD	PLCC44	PA44-48U
TOSHIBA	TC57H256D	DIP28	
TOSHIBA	TC58DVG02A1FT00	TSOP48	PA48TS48D
TOSHIBA	TC58FVB160FT	TSOP48	PA48TS48D
TOSHIBA	TC58FVB321FT	TSOP48	PA48TS48D
TOSHIBA	TC58FVB400FT	TSOP48	PA48TS48D
TOSHIBA	TC58FVB641FT	TSOP48	PA48TS48D
TOSHIBA	TC58FVB800FT	TSOP48	PA48TS48D
TOSHIBA	TC58FVM5B2A	TSOP48	PA48TS48D
TOSHIBA	TC58FVM5B3A	TSOP48	PA48TS48D
TOSHIBA	TC58FVM5T2A	TSOP48	PA48TS48D
TOSHIBA	TC58FVM5T3A	TSOP48	PA48TS48D
TOSHIBA	TC58FVM6B2AFT	TSOP48	PA48TS48D
TOSHIBA	TC58FVM6T2AFT	TSOP48	PA48TS48D
TOSHIBA	TC58FVT160FT	TSOP48	PA48TS48D
TOSHIBA	TC58FVT321FT	TSOP48	PA48TS48D
TOSHIBA	TC58FVT400FT	TSOP48	PA48TS48D
TOSHIBA	TC58FVT641FT	TSOP48	PA48TS48D
TOSHIBA	TC58FVT800FT	TSOP48	PA48TS48D
TOSHIBA	TH50VPF5584ADSB	BGA73	PA73BGA48DE-TO-7X10
TOSHIBA	TH50VPF5585ADSB	BGA73	PA73BGA48DE-TO-7X10
TOSHIBA	TH50VPF5682CDSB	BGA73	PA73BGA48DE-TO-7X10
TOSHIBA	TH50VPF5683CDSB	BGA73	PA73BGA48DE-TO-7X10
TOSHIBA	TH50VPF6782AASB	BGA69	PA69BGA48DK-TO-9X12

TOSHIBA	TH50VPF6783AASB	BGA69	PA69BGA48DK-TO-9X12
TOSHIBA	TH50VPF6784AASB	BGA69	PA69BGA48DK-TO-9X12
TOSHIBA	TH50VSF2580A	BGA69	PA69BGA48DF
TOSHIBA	TH50VSF2581A	BGA69	PA69BGA48DF
TOSHIBA	TH50VSF3680A	BGA69	PA69BGA48DF
TOSHIBA	TH50VSF3681A	BGA69	PA69BGA48DF
TOSHIBA	TH50VSF3682A	BGA69	PA69BGA48DF
TOSHIBA	TH50VSF3683A	BGA69	PA69BGA48DF
TOSHIBA	TH50VSF4682AASB	BGA69	PA69BGA48DI
TOSHIBA	TH50VSF4682BCSB	BGA69	PA69BGA48DI
TOSHIBA	TH50VSF4683AASB	BGA69	PA69BGA48DI
TOSHIBA	TH50VSF4683BCSB	BGA69	PA69BGA48DI
TOSHIBA	THPV057022BCBB	BGA69	PA69BGA48DM
TOSHIBA	THPV057023BCBB	BGA69	PA69BGA48DM
TOSHIBA	THPV067203BABD	BGA107	HA107BG48DF
TOSHIBA	THPV068022AABB	BGA73	PA73BGA48DF
TOSHIBA	THPV068023AABB	BGA73	PA73BGA48DF
TOSHIBA	THPV357022BCBB	BGA85	PA85BGA48DA-TO-7X10
TOSHIBA	THPV357023BCBB	BGA85	PA85BGA48DA-TO-7X10
TOSHIBA	TMM24128A	DIP28	
TOSHIBA	TMM24256A	DIP28	
TOSHIBA	TMM24256B	DIP28	
TOSHIBA	TMM24512	DIP28	
TOSHIBA	TMM24512A	DIP28	
TOSHIBA	TMM2464A	DIP28	
TOSHIBA	TMM27128	DIP28	
TOSHIBA	TMM27128A	DIP28	
TOSHIBA	TMM27128AD	DIP28	
TOSHIBA	TMM27128ADI	DIP28	
TOSHIBA	TMM27128D	DIP28	
TOSHIBA	TMM27128DI	DIP28	
TOSHIBA	TMM27256	DIP28	
TOSHIBA	TMM27256A	DIP28	
TOSHIBA	TMM27256AD	DIP28	
TOSHIBA	TMM27256ADI	DIP28	
TOSHIBA	TMM27256BD	DIP28	
TOSHIBA	TMM27256BDI	DIP28	
TOSHIBA	TMM27256D	DIP28	
TOSHIBA	TMM27256DI	DIP28	
TOSHIBA	TMM2732	DIP24	
TOSHIBA	TMM27512	DIP28	
TOSHIBA	TMM27512AD	DIP28	
TOSHIBA	TMM27512ADI	DIP28	
TOSHIBA	TMM27512D	DIP28	
TOSHIBA	TMM27512DI	DIP28	
TOSHIBA	TMM2764	DIP28	
TOSHIBA	TMM2764A	DIP28	
TOSHIBA	TMM2764AD	DIP28	
TOSHIBA	TMM2764ADI	DIP28	
TOSHIBA	TMM2764D	DIP28	
TOSHIBA	TMM2764DI	DIP28	
TOSHIBA	TMP86PM29AF	QFP64	BM11163
TOSHIBA	TMP87PH40	DIP28	
TOSHIBA	TMP87PH46N	DIP28	
TOSHIBA	TMP87PH808N	DIP28	
TOSHIBA	TMP87PP21FG	QFP80	BM11604
TOSHIBA	TMP88PS49F	DIP32	
TOSHIBA	TV00670002AABB	BGA73	PA73BGA48DI
TOSHIBA	TV00678003AABD	BGA107	HA107BG48DE
TOSHIBA	TV006C002SAABB	BGA73	PA7064/96-84LC
TOSHIBA	TY9000A800E0GG	BGA225	HA225BG48DA1
VANTIS	ispGAL22V10	DIP28	
VANTIS	ispGAL22V10	PLCC28	PA28PL28D
VANTIS	ispGAL22V10B	DIP28	
VANTIS	ispGAL22V10B	PLCC28	PA28PL28D
VANTIS	ispGAL22V10C	DIP28	
VANTIS	ispGAL22V10C	PLCC28	PA28PL28D
VANTIS	PALCE16V8H	DIP20	
VANTIS	PALCE16V8H	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8H	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has10H8	DIP20	
VANTIS	PALCE16V8Has10H8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has10H8	SOIC20	PA20SO20D-EO-210

VANTIS	PALCE16V8Has10L8	DIP20	
VANTIS	PALCE16V8Has10L8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has10L8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has10P8	DIP20	
VANTIS	PALCE16V8Has10P8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has10P8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has12H6	DIP20	
VANTIS	PALCE16V8Has12H6	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has12H6	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has12L6	DIP20	
VANTIS	PALCE16V8Has12L6	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has12L6	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has12P6	DIP20	
VANTIS	PALCE16V8Has12P6	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has12P6	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has14H4	DIP20	
VANTIS	PALCE16V8Has14H4	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has14H4	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has14L4	DIP20	
VANTIS	PALCE16V8Has14L4	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has14L4	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has14P4	DIP20	
VANTIS	PALCE16V8Has14P4	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has14P4	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16H2	DIP20	
VANTIS	PALCE16V8Has16H2	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16H2	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16H8	DIP20	
VANTIS	PALCE16V8Has16H8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16H8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16L2	DIP20	
VANTIS	PALCE16V8Has16L2	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16L2	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16L8	DIP20	
VANTIS	PALCE16V8Has16L8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16L8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16P2	DIP20	
VANTIS	PALCE16V8Has16P2	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16P2	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16P8	DIP20	
VANTIS	PALCE16V8Has16P8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16P8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16R4	DIP20	
VANTIS	PALCE16V8Has16R4	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16R4	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16R6	DIP20	
VANTIS	PALCE16V8Has16R6	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16R6	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16R8	DIP20	
VANTIS	PALCE16V8Has16R8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16R8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16RP4	DIP20	
VANTIS	PALCE16V8Has16RP4	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16RP4	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16RP6	DIP20	
VANTIS	PALCE16V8Has16RP6	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16RP6	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Has16RP8	DIP20	
VANTIS	PALCE16V8Has16RP8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Has16RP8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Q	DIP20	
VANTIS	PALCE16V8Q	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Q	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas10H8	DIP20	
VANTIS	PALCE16V8Qas10H8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas10H8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas10L8	DIP20	
VANTIS	PALCE16V8Qas10L8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas10L8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas10P8	DIP20	
VANTIS	PALCE16V8Qas10P8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas10P8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas12H6	DIP20	

VANTIS	PALCE16V8Qas12H6	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas12H6	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas12L6	DIP20	
VANTIS	PALCE16V8Qas12L6	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas12L6	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas12P6	DIP20	
VANTIS	PALCE16V8Qas12P6	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas12P6	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas14H4	DIP20	
VANTIS	PALCE16V8Qas14H4	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas14H4	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas14L4	DIP20	
VANTIS	PALCE16V8Qas14L4	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas14L4	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas14P4	DIP20	
VANTIS	PALCE16V8Qas14P4	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas14P4	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16H2	DIP20	
VANTIS	PALCE16V8Qas16H2	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16H2	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16H8	DIP20	
VANTIS	PALCE16V8Qas16H8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16H8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16L2	DIP20	
VANTIS	PALCE16V8Qas16L2	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16L2	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16L8	DIP20	
VANTIS	PALCE16V8Qas16L8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16L8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16P2	DIP20	
VANTIS	PALCE16V8Qas16P2	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16P2	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16P8	DIP20	
VANTIS	PALCE16V8Qas16P8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16P8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16R4	DIP20	
VANTIS	PALCE16V8Qas16R4	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16R4	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16R6	DIP20	
VANTIS	PALCE16V8Qas16R6	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16R6	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16R8	DIP20	
VANTIS	PALCE16V8Qas16R8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16R8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16RP4	DIP20	
VANTIS	PALCE16V8Qas16RP4	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16RP4	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16RP6	DIP20	
VANTIS	PALCE16V8Qas16RP6	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16RP6	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Qas16RP8	DIP20	
VANTIS	PALCE16V8Qas16RP8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Qas16RP8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Z	DIP20	
VANTIS	PALCE16V8Z	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Z	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas10H8	DIP20	
VANTIS	PALCE16V8Zas10H8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas10H8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas10L8	DIP20	
VANTIS	PALCE16V8Zas10L8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas10L8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas10P8	DIP20	
VANTIS	PALCE16V8Zas10P8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas10P8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas12H6	DIP20	
VANTIS	PALCE16V8Zas12H6	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas12H6	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas12L6	DIP20	
VANTIS	PALCE16V8Zas12L6	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas12L6	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas12P6	DIP20	
VANTIS	PALCE16V8Zas12P6	PLCC20	PA20LC20D[Dead Bug]

VANTIS	PALCE16V8Zas12P6	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas14H4	DIP20	
VANTIS	PALCE16V8Zas14H4	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas14H4	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas14L4	DIP20	
VANTIS	PALCE16V8Zas14L4	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas14L4	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas14P4	DIP20	
VANTIS	PALCE16V8Zas14P4	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas14P4	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16H2	DIP20	
VANTIS	PALCE16V8Zas16H2	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16H2	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16H8	DIP20	
VANTIS	PALCE16V8Zas16H8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16H8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16L2	DIP20	
VANTIS	PALCE16V8Zas16L2	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16L2	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16L8	DIP20	
VANTIS	PALCE16V8Zas16L8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16L8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16P2	DIP20	
VANTIS	PALCE16V8Zas16P2	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16P2	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16P8	DIP20	
VANTIS	PALCE16V8Zas16P8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16P8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16R4	DIP20	
VANTIS	PALCE16V8Zas16R4	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16R4	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16R6	DIP20	
VANTIS	PALCE16V8Zas16R6	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16R6	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16R8	DIP20	
VANTIS	PALCE16V8Zas16R8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16R8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16RP4	DIP20	
VANTIS	PALCE16V8Zas16RP4	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16RP4	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16RP6	DIP20	
VANTIS	PALCE16V8Zas16RP6	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16RP6	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE16V8Zas16RP8	DIP20	
VANTIS	PALCE16V8Zas16RP8	PLCC20	PA20LC20D[Dead Bug]
VANTIS	PALCE16V8Zas16RP8	SOIC20	PA20SO20D-EO-210
VANTIS	PALCE20RA10H	DIP24	
VANTIS	PALCE20RA10H	PLCC28	PA28PL28D
VANTIS	PALCE20RA10Q	DIP24	
VANTIS	PALCE20RA10Q	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4	DIP24	
VANTIS	PALCE20V8H-10/4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as14H8	DIP24	
VANTIS	PALCE20V8H-10/4as14H8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as14L8	DIP24	
VANTIS	PALCE20V8H-10/4as14L8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as14P8	DIP24	
VANTIS	PALCE20V8H-10/4as14P8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as16H6	DIP24	
VANTIS	PALCE20V8H-10/4as16H6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as16L6	DIP24	
VANTIS	PALCE20V8H-10/4as16L6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as16P6	DIP24	
VANTIS	PALCE20V8H-10/4as16P6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as18H4	DIP24	
VANTIS	PALCE20V8H-10/4as18H4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as18L4	DIP24	
VANTIS	PALCE20V8H-10/4as18L4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as18P4	DIP24	
VANTIS	PALCE20V8H-10/4as18P4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20H2	DIP24	
VANTIS	PALCE20V8H-10/4as20H2	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20H8	DIP24	



VANTIS	PALCE20V8H-10/4as20H8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20L2	DIP24	
VANTIS	PALCE20V8H-10/4as20L2	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20L8	DIP24	
VANTIS	PALCE20V8H-10/4as20L8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20P2	DIP24	
VANTIS	PALCE20V8H-10/4as20P2	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20P8	DIP24	
VANTIS	PALCE20V8H-10/4as20P8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20R4	DIP24	
VANTIS	PALCE20V8H-10/4as20R4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20R6	DIP24	
VANTIS	PALCE20V8H-10/4as20R6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20R8	DIP24	
VANTIS	PALCE20V8H-10/4as20R8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20RP4	DIP24	
VANTIS	PALCE20V8H-10/4as20RP4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20RP6	DIP24	
VANTIS	PALCE20V8H-10/4as20RP6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-10/4as20RP8	DIP24	
VANTIS	PALCE20V8H-10/4as20RP8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4	DIP24	
VANTIS	PALCE20V8H-15/4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as14H8	DIP24	
VANTIS	PALCE20V8H-15/4as14H8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as14L8	DIP24	
VANTIS	PALCE20V8H-15/4as14L8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as14P8	DIP24	
VANTIS	PALCE20V8H-15/4as14P8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as16H6	DIP24	
VANTIS	PALCE20V8H-15/4as16H6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as16L6	DIP24	
VANTIS	PALCE20V8H-15/4as16L6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as16P6	DIP24	
VANTIS	PALCE20V8H-15/4as16P6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as18H4	DIP24	
VANTIS	PALCE20V8H-15/4as18H4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as18L4	DIP24	
VANTIS	PALCE20V8H-15/4as18L4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as18P4	DIP24	
VANTIS	PALCE20V8H-15/4as18P4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20H2	DIP24	
VANTIS	PALCE20V8H-15/4as20H2	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20H8	DIP24	
VANTIS	PALCE20V8H-15/4as20H8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20L2	DIP24	
VANTIS	PALCE20V8H-15/4as20L2	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20L8	DIP24	
VANTIS	PALCE20V8H-15/4as20L8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20P2	DIP24	
VANTIS	PALCE20V8H-15/4as20P2	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20P8	DIP24	
VANTIS	PALCE20V8H-15/4as20P8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20R4	DIP24	
VANTIS	PALCE20V8H-15/4as20R4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20R6	DIP24	
VANTIS	PALCE20V8H-15/4as20R6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20R8	DIP24	
VANTIS	PALCE20V8H-15/4as20R8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20RP4	DIP24	
VANTIS	PALCE20V8H-15/4as20RP4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20RP6	DIP24	
VANTIS	PALCE20V8H-15/4as20RP6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-15/4as20RP8	DIP24	
VANTIS	PALCE20V8H-15/4as20RP8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4	DIP24	
VANTIS	PALCE20V8H-25/4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as14H8	DIP24	
VANTIS	PALCE20V8H-25/4as14H8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as14L8	DIP24	
VANTIS	PALCE20V8H-25/4as14L8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as14P8	DIP24	

VANTIS	PALCE20V8H-25/4as14P8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as16H6	DIP24	
VANTIS	PALCE20V8H-25/4as16H6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as16L6	DIP24	
VANTIS	PALCE20V8H-25/4as16L6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as16P6	DIP24	
VANTIS	PALCE20V8H-25/4as16P6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as18H4	DIP24	
VANTIS	PALCE20V8H-25/4as18H4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as18L4	DIP24	
VANTIS	PALCE20V8H-25/4as18L4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as18P4	DIP24	
VANTIS	PALCE20V8H-25/4as18P4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20H2	DIP24	
VANTIS	PALCE20V8H-25/4as20H2	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20H8	DIP24	
VANTIS	PALCE20V8H-25/4as20H8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20L2	DIP24	
VANTIS	PALCE20V8H-25/4as20L2	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20L8	DIP24	
VANTIS	PALCE20V8H-25/4as20L8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20P2	DIP24	
VANTIS	PALCE20V8H-25/4as20P2	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20P8	DIP24	
VANTIS	PALCE20V8H-25/4as20P8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20R4	DIP24	
VANTIS	PALCE20V8H-25/4as20R4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20R6	DIP24	
VANTIS	PALCE20V8H-25/4as20R6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20R8	DIP24	
VANTIS	PALCE20V8H-25/4as20R8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20RP4	DIP24	
VANTIS	PALCE20V8H-25/4as20RP4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20RP6	DIP24	
VANTIS	PALCE20V8H-25/4as20RP6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25/4as20RP8	DIP24	
VANTIS	PALCE20V8H-25/4as20RP8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as14H8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as14L8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as14P8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as16H6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as16L6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as16P6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as18H4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as18L4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as18P4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as20H2	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as20H8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as20L2	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as20L8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as20P2	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as20P8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as20R4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as20R6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as20R8	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as20RP4	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as20RP6	PLCC28	PA28PL28D
VANTIS	PALCE20V8H-25as20RP8	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4	DIP24	
VANTIS	PALCE20V8Q-15/4	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as14H8	DIP24	
VANTIS	PALCE20V8Q-15/4as14H8	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as14L8	DIP24	
VANTIS	PALCE20V8Q-15/4as14L8	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as14P8	DIP24	
VANTIS	PALCE20V8Q-15/4as14P8	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as16H6	DIP24	
VANTIS	PALCE20V8Q-15/4as16H6	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as16L6	DIP24	
VANTIS	PALCE20V8Q-15/4as16L6	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as16P6	DIP24	
VANTIS	PALCE20V8Q-15/4as16P6	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as18H4	DIP24	

VANTIS	PALCE20V8Q-15/4as18H4	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as18L4	DIP24	
VANTIS	PALCE20V8Q-15/4as18L4	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as18P4	DIP24	
VANTIS	PALCE20V8Q-15/4as18P4	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20H2	DIP24	
VANTIS	PALCE20V8Q-15/4as20H2	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20H8	DIP24	
VANTIS	PALCE20V8Q-15/4as20H8	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20L2	DIP24	
VANTIS	PALCE20V8Q-15/4as20L2	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20L8	DIP24	
VANTIS	PALCE20V8Q-15/4as20L8	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20P2	DIP24	
VANTIS	PALCE20V8Q-15/4as20P2	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20P8	DIP24	
VANTIS	PALCE20V8Q-15/4as20P8	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20R4	DIP24	
VANTIS	PALCE20V8Q-15/4as20R4	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20R6	DIP24	
VANTIS	PALCE20V8Q-15/4as20R6	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20R8	DIP24	
VANTIS	PALCE20V8Q-15/4as20R8	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20RP4	DIP24	
VANTIS	PALCE20V8Q-15/4as20RP4	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20RP6	DIP24	
VANTIS	PALCE20V8Q-15/4as20RP6	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-15/4as20RP8	DIP24	
VANTIS	PALCE20V8Q-15/4as20RP8	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4	DIP24	
VANTIS	PALCE20V8Q-25/4	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as14H8	DIP24	
VANTIS	PALCE20V8Q-25/4as14H8	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as14L8	DIP24	
VANTIS	PALCE20V8Q-25/4as14L8	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as14P8	DIP24	
VANTIS	PALCE20V8Q-25/4as14P8	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as16H6	DIP24	
VANTIS	PALCE20V8Q-25/4as16H6	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as16L6	DIP24	
VANTIS	PALCE20V8Q-25/4as16L6	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as16P6	DIP24	
VANTIS	PALCE20V8Q-25/4as16P6	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as18H4	DIP24	
VANTIS	PALCE20V8Q-25/4as18H4	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as18L4	DIP24	
VANTIS	PALCE20V8Q-25/4as18L4	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as18P4	DIP24	
VANTIS	PALCE20V8Q-25/4as18P4	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20H2	DIP24	
VANTIS	PALCE20V8Q-25/4as20H2	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20H8	DIP24	
VANTIS	PALCE20V8Q-25/4as20H8	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20L2	DIP24	
VANTIS	PALCE20V8Q-25/4as20L2	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20L8	DIP24	
VANTIS	PALCE20V8Q-25/4as20L8	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20P2	DIP24	
VANTIS	PALCE20V8Q-25/4as20P2	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20P8	DIP24	
VANTIS	PALCE20V8Q-25/4as20P8	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20R4	DIP24	
VANTIS	PALCE20V8Q-25/4as20R4	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20R6	DIP24	
VANTIS	PALCE20V8Q-25/4as20R6	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20R8	DIP24	
VANTIS	PALCE20V8Q-25/4as20R8	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20RP4	DIP24	
VANTIS	PALCE20V8Q-25/4as20RP4	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20RP6	DIP24	
VANTIS	PALCE20V8Q-25/4as20RP6	PLCC28	PA28PL28D
VANTIS	PALCE20V8Q-25/4as20RP8	DIP24	
VANTIS	PALCE20V8Q-25/4as20RP8	PLCC28	PA28PL28D

VANTIS	PALCE22V10H	DIP24	
VANTIS	PALCE22V10H	PLCC28	PA28PL28D
VANTIS	PALCE22V10Q	DIP24	
VANTIS	PALCE22V10Q	PLCC28	PA28PL28D
VANTIS	PALCE22V10Z	DIP24	
VANTIS	PALCE22V10Z	PLCC28	PA28PL28D
VANTIS	PALCE26V12H	DIP28	
VANTIS	PALCE26V12H	PLCC28	PA28PL28D
VANTIS	PALCE26V12H/4	DIP28	
VANTIS	PALCE26V12H/4	PLCC28	PA28PL28D
VANTIS	PALCE26V12H/4-10	DIP28	
VANTIS	PALCE26V12H/4-10	PLCC28	PA28PL28D
VANTIS	PALCE29M16H	DIP24	
VANTIS	PALCE29M16H	PLCC28	PA28PL28D
VANTIS	PALCE29MA16H	DIP24	
VANTIS	PALCE29MA16H	PLCC28	PA28PL28D
VANTIS	PALCE610H	DIP24	
VANTIS	PALCE610H	PLCC28	PA28PL28D
VANTIS	PALLV22V10	DIP24	
VANTIS	PALLV22V10	PLCC28	PA28PL28D
VANTIS	PALLV22V10Z	DIP24	
VANTIS	PALLV22V10Z	PLCC28	PA28PL28D
VLSI	VT27C256	DIP28	
VLSI	VT27C512	DIP28	
VLSI	VT27C64	DIP28	
WAFERSCALE INTEGRATIO	N PSD301	PLCC44	PA44-48U-PSD3xx
WAFERSCALE INTEGRATIO	N PSD301L	PLCC44	PA44-48U-PSD3xx
WAFERSCALE INTEGRATIO	N PSD301R	PLCC44	PA44-48U-PSD3xx
WAFERSCALE INTEGRATIO	N PSD302	PLCC44	PA44-48U-PSD3xx
WAFERSCALE INTEGRATIO	N PSD302L	PLCC44	PA44-48U-PSD3xx
WAFERSCALE INTEGRATIO	N PSD302R	PLCC44	PA44-48U-PSD3xx
WAFERSCALE INTEGRATIO	N PSD311	PLCC44	PA44-48U-PSD3xx
WAFERSCALE INTEGRATIO	N PSD311L	PLCC44	PA44-48U-PSD3xx
WAFERSCALE INTEGRATIO	N PSD311R	PLCC44	PA44-48U-PSD3xx
WAFERSCALE INTEGRATIO	N PSD312	PLCC44	PA44-48U-PSD3xx
WAFERSCALE INTEGRATIO	N PSD312L	PLCC44	PA44-48U-PSD3xx
WAFERSCALE INTEGRATIO	N PSD312R	PLCC44	PA44-48U-PSD3xx
WAFERSCALE INTEGRATIO	N WS27C010L	DIP32	
WAFERSCALE INTEGRATIO	N WS27C040L	DIP32	
WAFERSCALE INTEGRATIO	N WS27C128F	DIP28	
WAFERSCALE INTEGRATIO	N WS27C128F	PLCC32	PA32PL28D-YA
WAFERSCALE INTEGRATIO	N WS27C210L	DIP40	
WAFERSCALE INTEGRATIO	N WS27C210L	PLCC44	PA44-48U
WAFERSCALE INTEGRATIO	N WS27C256F	DIP28	
WAFERSCALE INTEGRATIO	N WS27C256F	PLCC32	PA32PL28D-YA
WAFERSCALE INTEGRATIO	N WS27C256L	DIP28	
WAFERSCALE INTEGRATIO	N WS27C512F	DIP28	
WAFERSCALE INTEGRATIO	N WS27C512F	PLCC32	PA32PL28D-YA
WAFERSCALE INTEGRATIO	N WS27C512L	DIP28	
WAFERSCALE INTEGRATIO	N WS27C512L	PLCC32	PA32PL28D-YA
WAFERSCALE INTEGRATIO	N WS27C64F	DIP28	
WAFERSCALE INTEGRATIO	N WS27C64F	PLCC32	PA32PL28D-YA
WAFERSCALE INTEGRATIO	N WS27C64L	DIP28	
WAFERSCALE INTEGRATIO	N WS27C64L	PLCC32	PA32PL28D-YA
WAFERSCALE INTEGRATIO	N WS57C128F	DIP28	
WAFERSCALE INTEGRATIO	N WS57C256F	DIP28	
WAFERSCALE INTEGRATIO	N WS57C43B	DIP24	
WAFERSCALE INTEGRATIO	N WS57C43C	DIP24	
WAFERSCALE INTEGRATIO	N WS57C51	DIP28	
WAFERSCALE INTEGRATIO	N WS57C51	PLCC28	PA28PL28D
WAFERSCALE INTEGRATIO	N WS57C512F	DIP28	
WAFERSCALE INTEGRATIO	N WS57C51C	DIP28	
WAFERSCALE INTEGRATIO	N WS57C51C	PLCC28	PA28PL28D
WAFERSCALE INTEGRATIO	N WS57C64F	DIP28	
WHITE MICROELECTRONIC	S WE128K8	DIP32	
WHITE MICROELECTRONIC	S WE256K8	DIP32	
WHITE MICROELECTRONIC	S WE512K8	DIP32	
WINBOND	W19B320AB	TSOP48	PA48TS48D
WINBOND	W19B320AT	TSOP48	PA48TS48D
WINBOND	W19B320BBT	TSOP48	PA48TS48D
WINBOND	W19B320BTT	TSOP48	PA48TS48D
WINBOND	W19L320SBBT	TSOP48	PA48TS48D
WINBOND	W19L320STT	TSOP48	PA48TS48D

WINBOND	W25D10V	DIP8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25D10V	SOIC8	PA8SON8D(6x5)
WINBOND	W25D10V	WSON8	
WINBOND	W25D20V	DIP8	
WINBOND	W25D20V	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25D20V	WSON8	PA8SON8D(6x5)
WINBOND	W25D40V	DIP8	
WINBOND	W25D40V	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25D40V	SOIC8	PA20SO20D-EO-210
WINBOND	W25D40V	WSON8	PA8SON8D(6x5)
WINBOND	W25D80V	DIP8	
WINBOND	W25D80V	SOIC8	PA20SO20D-EO-210
WINBOND	W25D80V	WSON8	PA8SON8D(6x5)
WINBOND	W25P10V	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25P16V	SOIC16	PA28SO28D-EO-300
WINBOND	W25P16V	SOIC8	PA20SO20D-EO-210
WINBOND	W25P20V	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25P32V	SOIC16	PA28SO28D-EO-300
WINBOND	W25P32V	SOIC8	PA20SO20D-EO-210
WINBOND	W25P40V	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25P80V	SOIC16	PA28SO28D-EO-300
WINBOND	W25P80V	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q01JV-IM	SOP16	PA28SO28D-EO-300
WINBOND	W25Q01JV-IM	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q01JV-IM	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q01JV-IM (Dual)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q01JV-IM (Dual)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q01JV-IM (Dual)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q01JV-IM (Quad)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q01JV-IM (Quad)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q01JV-IM (Quad)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q01JV-IQ	SOP16	PA28SO28D-EO-300
WINBOND	W25Q01JV-IQ	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q01JV-IQ	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q01JV-IQ (Dual)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q01JV-IQ (Dual)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q01JV-IQ (Dual)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q01JV-IQ (Quad)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q01JV-IQ (Quad)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q01JV-IQ (Quad)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q01NW-IM	SOP16	PA28SO28D-EO-300
WINBOND	W25Q01NW-IM	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q01NW-IM	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q01NW-IM (Quad)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q01NW-IM (Quad)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q01NW-IM (Quad)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q01NW-IQ	SOP16	PA28SO28D-EO-300
WINBOND	W25Q01NW-IQ	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q01NW-IQ	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q01NW-IQ (Quad)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q01NW-IQ (Quad)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q01NW-IQ (Quad)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q128BV	SOP16	PA28SO28D-EO-300
WINBOND	W25Q128BV	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q128BV	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q128FV	DIP8	
WINBOND	W25Q128FV	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q128FV	SOP16	PA28SO28D-EO-300
WINBOND	W25Q128FV	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q128FV	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q128FV	WSON8	PA8SON8D(6x5)
WINBOND	W25Q128FV	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q128FW-IG	SOP16	PA28SO28D-EO-300
WINBOND	W25Q128FW-IG	SOP8	PA20SO20D-EO-210
WINBOND	W25Q128FW-IG	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q128FW-IG	WSON8	PA8SON8D(6x5)
WINBOND	W25Q128FW-IG	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q128FW-IQ	SOP16	PA28SO28D-EO-300
WINBOND	W25Q128FW-IQ	SOP8	PA20SO20D-EO-210
WINBOND	W25Q128FW-IQ	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q128FW-IQ	WSON8	PA8SON8D(6x5)
WINBOND	W25Q128FW-IQ	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q128FW-IQ (Dual)	SOP16	PA28SO28D-EO-300

WINBOND	W25Q128FW-IQ (Dual)	SOP8	PA20SO20D-EO-210
WINBOND	W25Q128FW-IQ (Dual)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q128FW-IQ (Dual)	WSON8	PA8SON8D(6x5)
WINBOND	W25Q128FW-IQ (Dual)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q128FW-IQ (Quad)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q128FW-IQ (Quad)	SOP8	PA20SO20D-EO-210
WINBOND	W25Q128FW-IQ (Quad)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q128FW-IQ (Quad)	WSON8	PA8SON8D(6x5)
WINBOND	W25Q128FW-IQ (Quad)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q128JV-IM/JM	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q128JV-IM/JM	SOP16	PA28SO28D-EO-300
WINBOND	W25Q128JV-IM/JM	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q128JV-IM/JM	WSON8	PA8SON8D(6x5)
WINBOND	W25Q128JV-IM/JM	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q128JV-IM/JM (Dual)	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q128JV-IM/JM (Dual)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q128JV-IM/JM (Dual)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q128JV-IM/JM (Dual)	WSON8	PA8SON8D(6x5)
WINBOND	W25Q128JV-IM/JM (Dual)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q128JV-IM/JM (Quad)	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q128JV-IM/JM (Quad)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q128JV-IM/JM (Quad)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q128JV-IM/JM (Quad)	WSON8	PA8SON8D(6x5)
WINBOND	W25Q128JV-IM/JM (Quad)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q128JV-IQ/JQ	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q128JV-IQ/JQ	SOP16	PA28SO28D-EO-300
WINBOND	W25Q128JV-IQ/JQ	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q128JV-IQ/JQ	WSON8	PA8SON8D(6x5)
WINBOND	W25Q128JV-IQ/JQ	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q128JV-IQ/JQ (Dual)	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q128JV-IQ/JQ (Dual)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q128JV-IQ/JQ (Dual)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q128JV-IQ/JQ (Dual)	WSON8	PA8SON8D(6x5)
WINBOND	W25Q128JV-IQ/JQ (Dual)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q128JV-IQ/JQ (Quad)	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q128JV-IQ/JQ (Quad)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q128JV-IQ/JQ (Quad)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q128JV-IQ/JQ (Quad)	WSON8	PA8SON8D(6x5)
WINBOND	W25Q128JV-IQ/JQ (Quad)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q16BV	DIP8	
WINBOND	W25Q16BV	SOIC16	PA28SO28D-EO-300
WINBOND	W25Q16BV	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q16BV	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q16BV	WSON8	PA8SON8D(6x5)
WINBOND	W25Q16DV	DIP8	
WINBOND	W25Q16DV	SOIC16	PA28SO28D-EO-300
WINBOND	W25Q16DV	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q16DV	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q16DV	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q16DV	USON8	PA8SON8D(4x3)
WINBOND	W25Q16DV	WSON8	PA8SON8D(6x5)
WINBOND	W25Q16DW	SOIC16	PA28SO28D-EO-300
WINBOND	W25Q16DW	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q16DW	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q16DW	USON8	PA8SON8D(4x3)
WINBOND	W25Q16DW	WSON8	PA8SON8D(6x5)
WINBOND	W25Q16JV-IM/JM	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q16JV-IM/JM	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q16JV-IM/JM	USON8	PA8SON8D(2x3)
WINBOND	W25Q16JV-IM/JM	USON8	PA8SON8D(4x3)
WINBOND	W25Q16JV-IM/JM	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q16JV-IM/JM	WSON8	PA8SON8D(6x5)
WINBOND	W25Q16JV-IM/JM (Dual)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q16JV-IM/JM (Dual)	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q16JV-IM/JM (Dual)	USON8	PA8SON8D(2x3)
WINBOND	W25Q16JV-IM/JM (Dual)	USON8	PA8SON8D(4x3)
WINBOND	W25Q16JV-IM/JM (Dual)	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q16JV-IM/JM (Dual)	WSON8	PA8SON8D(6x5)
WINBOND	W25Q16JV-IM/JM (Quad)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q16JV-IM/JM (Quad)	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q16JV-IM/JM (Quad)	USON8	PA8SON8D(2x3)
WINBOND	W25Q16JV-IM/JM (Quad)	USON8	PA8SON8D(4x3)
WINBOND	W25Q16JV-IM/JM (Quad)	VSOP8	PA20SO20D-EO-210

WINBOND	W25Q16JV-IM/JM (Quad)	WSON8	PA8SON8D(6x5)
WINBOND	W25Q16JV-IQ/JQ	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q16JV-IQ/JQ	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q16JV-IQ/JQ	USON8	PA8SON8D(2x3)
WINBOND	W25Q16JV-IQ/JQ	USON8	PA8SON8D(4x3)
WINBOND	W25Q16JV-IQ/JQ	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q16JV-IQ/JQ	WSON8	PA8SON8D(6x5)
WINBOND	W25Q16JV-IQ/JQ (Dual)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q16JV-IQ/JQ (Dual)	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q16JV-IQ/JQ (Dual)	USON8	PA8SON8D(2x3)
WINBOND	W25Q16JV-IQ/JQ (Dual)	USON8	PA8SON8D(4x3)
WINBOND	W25Q16JV-IQ/JQ (Dual)	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q16JV-IQ/JQ (Dual)	WSON8	PA8SON8D(6x5)
WINBOND	W25Q16JV-IQ/JQ (Quad)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q16JV-IQ/JQ (Quad)	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q16JV-IQ/JQ (Quad)	USON8	PA8SON8D(2x3)
WINBOND	W25Q16JV-IQ/JQ (Quad)	USON8	PA8SON8D(4x3)
WINBOND	W25Q16JV-IQ/JQ (Quad)	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q16JV-IQ/JQ (Quad)	WSON8	PA8SON8D(6x5)
WINBOND	W25Q16JV-IQ/JQ (Quad)	WSON8	PA8SON8D(6x5)
WINBOND	W25Q256FV	SOP16	PA28SO28D-EO-300
WINBOND	W25Q256FV	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q256FV	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q256JV-IM/JM	SOP16	PA28SO28D-EO-300
WINBOND	W25Q256JV-IM/JM	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q256JV-IM/JM	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q256JV-IM/JM (Dual)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q256JV-IM/JM (Dual)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q256JV-IM/JM (Dual)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q256JV-IM/JM (Quad)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q256JV-IM/JM (Quad)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q256JV-IM/JM (Quad)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q256JV-IQ/JQ	SOP16	PA28SO28D-EO-300
WINBOND	W25Q256JV-IQ/JQ	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q256JV-IQ/JQ	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q256JV-IQ/JQ (Dual)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q256JV-IQ/JQ (Dual)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q256JV-IQ/JQ (Dual)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q256JV-IQ/JQ (Quad)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q256JV-IQ/JQ (Quad)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q256JV-IQ/JQ (Quad)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q256JV-IQ/JQ (Quad)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q256JV-IQ/JQ (Quad)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q256JV-IQ/JQ (Quad)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q256JW	SOP16	PA28SO28D-EO-300
WINBOND	W25Q256JW	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q256JW	WSON8	PA8SON8D(6x5)
WINBOND	W25Q256JW	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q32BV	DIP8	
WINBOND	W25Q32BV	SOIC16	PA28SO28D-EO-300
WINBOND	W25Q32BV	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q32BV	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q32BV	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q32BV	WSON8	PA8SON8D(6x5)
WINBOND	W25Q32BV	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q32FV	DIP8	
WINBOND	W25Q32FV	SOIC16	PA28SO28D-EO-300
WINBOND	W25Q32FV	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q32FV	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q32FV	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q32FV	WSON8	PA8SON8D(6x5)
WINBOND	W25Q32FV	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q32FW	SOIC16	PA28SO28D-EO-300
WINBOND	W25Q32FW	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q32FW	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q32FW	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q32FW	WSON8	PA8SON8D(6x5)
WINBOND	W25Q32FW	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q32JV-IM/JM	DIP8	
WINBOND	W25Q32JV-IM/JM	SOIC16	PA28SO28D-EO-300
WINBOND	W25Q32JV-IM/JM	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q32JV-IM/JM	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q32JV-IM/JM	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q32JV-IM/JM	USON8	PA8SON8D(4x3)
WINBOND	W25Q32JV-IM/JM	VSOP8	PA16SO16D-EO-150
WINBOND	W25Q32JV-IM/JM	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q32JV-IM/JM	WSON8	PA8SON8D(6x5)

WINBOND	W25Q32JV-IM/JM	WSO8	PA8SON8DA(8x6)
WINBOND	W25Q32JV-IM/JM (Dual)	DIP8	
WINBOND	W25Q32JV-IM/JM (Dual)	SOIC16	PA28SO28D-EO-300
WINBOND	W25Q32JV-IM/JM (Dual)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q32JV-IM/JM (Dual)	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q32JV-IM/JM (Dual)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q32JV-IM/JM (Dual)	USO8	PA8SON8D(4x3)
WINBOND	W25Q32JV-IM/JM (Dual)	VSOP8	PA16SO16D-EO-150
WINBOND	W25Q32JV-IM/JM (Dual)	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q32JV-IM/JM (Dual)	WSO8	PA8SON8D(6x5)
WINBOND	W25Q32JV-IM/JM (Dual)	WSO8	PA8SON8DA(8x6)
WINBOND	W25Q32JV-IM/JM (Quad)	DIP8	
WINBOND	W25Q32JV-IM/JM (Quad)	SOIC16	PA28SO28D-EO-300
WINBOND	W25Q32JV-IM/JM (Quad)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q32JV-IM/JM (Quad)	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q32JV-IM/JM (Quad)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q32JV-IM/JM (Quad)	USO8	PA8SON8D(4x3)
WINBOND	W25Q32JV-IM/JM (Quad)	VSOP8	PA16SO16D-EO-150
WINBOND	W25Q32JV-IM/JM (Quad)	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q32JV-IM/JM (Quad)	WSO8	PA8SON8D(6x5)
WINBOND	W25Q32JV-IM/JM (Quad)	WSO8	PA8SON8DA(8x6)
WINBOND	W25Q32JV-IQ/JQ	DIP8	
WINBOND	W25Q32JV-IQ/JQ	SOIC16	PA28SO28D-EO-300
WINBOND	W25Q32JV-IQ/JQ	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q32JV-IQ/JQ	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q32JV-IQ/JQ	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q32JV-IQ/JQ	USO8	PA8SON8D(4x3)
WINBOND	W25Q32JV-IQ/JQ	VSOP8	PA16SO16D-EO-150
WINBOND	W25Q32JV-IQ/JQ	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q32JV-IQ/JQ	WSO8	PA8SON8D(6x5)
WINBOND	W25Q32JV-IQ/JQ	WSO8	PA8SON8DA(8x6)
WINBOND	W25Q32JV-IQ/JQ (Dual)	DIP8	
WINBOND	W25Q32JV-IQ/JQ (Dual)	SOIC16	PA28SO28D-EO-300
WINBOND	W25Q32JV-IQ/JQ (Dual)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q32JV-IQ/JQ (Dual)	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q32JV-IQ/JQ (Dual)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q32JV-IQ/JQ (Dual)	USO8	PA8SON8D(4x3)
WINBOND	W25Q32JV-IQ/JQ (Dual)	VSOP8	PA16SO16D-EO-150
WINBOND	W25Q32JV-IQ/JQ (Dual)	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q32JV-IQ/JQ (Dual)	WSO8	PA8SON8D(6x5)
WINBOND	W25Q32JV-IQ/JQ (Dual)	WSO8	PA8SON8DA(8x6)
WINBOND	W25Q32JV-IQ/JQ (Quad)	DIP8	
WINBOND	W25Q32JV-IQ/JQ (Quad)	SOIC16	PA28SO28D-EO-300
WINBOND	W25Q32JV-IQ/JQ (Quad)	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q32JV-IQ/JQ (Quad)	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q32JV-IQ/JQ (Quad)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q32JV-IQ/JQ (Quad)	USO8	PA8SON8D(4x3)
WINBOND	W25Q32JV-IQ/JQ (Quad)	VSOP8	PA16SO16D-EO-150
WINBOND	W25Q32JV-IQ/JQ (Quad)	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q32JV-IQ/JQ (Quad)	WSO8	PA8SON8D(6x5)
WINBOND	W25Q32JV-IQ/JQ (Quad)	WSO8	PA8SON8DA(8x6)
WINBOND	W25Q40BV	DIP8	
WINBOND	W25Q40BV	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q40BV	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q40BV	USO8	PA8SON8D(2x3)
WINBOND	W25Q40BV	VSOP8	PA16SO16D-EO-150
WINBOND	W25Q40BV	WSO8	PA8SON8D(6x5)
WINBOND	W25Q40BW	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q40BW	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q40BW	USO8	PA8SON8D(2x3)
WINBOND	W25Q40BW	VSOP8	PA16SO16D-EO-150
WINBOND	W25Q40BW	WSO8	PA8SON8D(6x5)
WINBOND	W25Q40CL	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q40CL	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q40CL	USO8	PA8SON8D(2x3)
WINBOND	W25Q40EW	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q40EW	USO8	PA8SON8D(2x3)
WINBOND	W25Q40EW	VSOP8	PA16SO16D-EO-150
WINBOND	W25Q512NW-IM	SOP16	PA28SO28D-EO-300
WINBOND	W25Q512NW-IM	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q512NW-IM	WSO8	PA8SON8DA(8x6)
WINBOND	W25Q512NW-IM (Quad)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q512NW-IM (Quad)	TFBGA24	PA24BG24D(6x8mm)5x5



WINBOND	W25Q512NW-IM (Quad)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q512NW-IQ	SOP16	PA28SO28D-EO-300
WINBOND	W25Q512NW-IQ	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q512NW-IQ	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q512NW-IQ (Quad)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q512NW-IQ (Quad)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q512NW-IQ (Quad)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q64BV	DIP8	
WINBOND	W25Q64BV	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q64BV	SOP16	PA28SO28D-EO-300
WINBOND	W25Q64BV	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q64CV	DIP8	
WINBOND	W25Q64CV	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q64CV	SOP16	PA28SO28D-EO-300
WINBOND	W25Q64CV	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q64CV	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q64CV	WSON8	PA8SON8D(6x5)
WINBOND	W25Q64CV	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q64DW	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q64DW	SOP16	PA28SO28D-EO-300
WINBOND	W25Q64DW	WSON8	PA8SON8D(6x5)
WINBOND	W25Q64DW	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q64FV	DIP8	
WINBOND	W25Q64FV	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q64FV	SOP16	PA28SO28D-EO-300
WINBOND	W25Q64FV	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q64FV	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q64FV	WSON8	PA8SON8D(6x5)
WINBOND	W25Q64FV	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q64FV-IQ	DIP8	
WINBOND	W25Q64FV-IQ	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q64FV-IQ	SOP16	PA28SO28D-EO-300
WINBOND	W25Q64FV-IQ	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q64FV-IQ	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q64FV-IQ	WSON8	PA8SON8D(6x5)
WINBOND	W25Q64FV-IQ	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q64FV-IQ (Dual)	DIP8	
WINBOND	W25Q64FV-IQ (Dual)	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q64FV-IQ (Dual)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q64FV-IQ (Dual)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q64FV-IQ (Dual)	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q64FV-IQ (Dual)	WSON8	PA8SON8D(6x5)
WINBOND	W25Q64FV-IQ (Dual)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q64FV-IQ (Quad)	DIP8	
WINBOND	W25Q64FV-IQ (Quad)	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q64FV-IQ (Quad)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q64FV-IQ (Quad)	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q64FV-IQ (Quad)	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q64FV-IQ (Quad)	WSON8	PA8SON8D(6x5)
WINBOND	W25Q64FV-IQ (Quad)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q64FW	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q64FW	SOP16	PA28SO28D-EO-300
WINBOND	W25Q64FW	TFBGA24	PA24BG24D(6x8mm)5x5
WINBOND	W25Q64FW	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q64FW	WSON8	PA8SON8D(6x5)
WINBOND	W25Q64JV-IM/JM	DIP8	
WINBOND	W25Q64JV-IM/JM	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q64JV-IM/JM	SOP16	PA28SO28D-EO-300
WINBOND	W25Q64JV-IM/JM	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q64JV-IM/JM	WSON8	PA8SON8D(6x5)
WINBOND	W25Q64JV-IM/JM	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q64JV-IM/JM (Dual)	DIP8	
WINBOND	W25Q64JV-IM/JM (Dual)	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q64JV-IM/JM (Dual)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q64JV-IM/JM (Dual)	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q64JV-IM/JM (Dual)	WSON8	PA8SON8D(6x5)
WINBOND	W25Q64JV-IM/JM (Dual)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q64JV-IM/JM (Quad)	DIP8	
WINBOND	W25Q64JV-IM/JM (Quad)	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q64JV-IM/JM (Quad)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q64JV-IM/JM (Quad)	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q64JV-IM/JM (Quad)	WSON8	PA8SON8D(6x5)
WINBOND	W25Q64JV-IM/JM (Quad)	WSON8	PA8SON8DA(8x6)

WINBOND	W25Q64JV-IQ/JQ	DIP8	PA20SO20D-EO-210
WINBOND	W25Q64JV-IQ/JQ	SOIC8	PA28SO28D-EO-300
WINBOND	W25Q64JV-IQ/JQ	SOP16	PA20SO20D-EO-210
WINBOND	W25Q64JV-IQ/JQ	VSOP8	PA8SON8D(6x5)
WINBOND	W25Q64JV-IQ/JQ	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q64JV-IQ/JQ	WSON8	
WINBOND	W25Q64JV-IQ/JQ (Dual)	DIP8	
WINBOND	W25Q64JV-IQ/JQ (Dual)	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q64JV-IQ/JQ (Dual)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q64JV-IQ/JQ (Dual)	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q64JV-IQ/JQ (Dual)	WSON8	PA8SON8D(6x5)
WINBOND	W25Q64JV-IQ/JQ (Dual)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q64JV-IQ/JQ (Quad)	DIP8	
WINBOND	W25Q64JV-IQ/JQ (Quad)	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q64JV-IQ/JQ (Quad)	SOP16	PA28SO28D-EO-300
WINBOND	W25Q64JV-IQ/JQ (Quad)	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q64JV-IQ/JQ (Quad)	WSON8	PA8SON8D(6x5)
WINBOND	W25Q64JV-IQ/JQ (Quad)	WSON8	PA8SON8DA(8x6)
WINBOND	W25Q80BV	DIP8	
WINBOND	W25Q80BV	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q80BV	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q80BV	USON8	PA8SON8D(2x3)
WINBOND	W25Q80BV	WSON8	PA8SON8D(6x5)
WINBOND	W25Q80DV	DIP8	
WINBOND	W25Q80DV	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q80DV	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q80DV	USON8	PA8SON8D(2x3)
WINBOND	W25Q80DV	VSOP8	PA16SO16D-EO-150
WINBOND	W25Q80DV	WSON8	PA8SON8D(6x5)
WINBOND	W25Q80EW	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25Q80EW	SOIC8	PA20SO20D-EO-210
WINBOND	W25Q80EW	USON8	PA8SON8D(2x3)
WINBOND	W25Q80EW	USON8	PA8SON8D(4x3)
WINBOND	W25Q80EW	VSOP8	PA16SO16D-EO-150
WINBOND	W25Q80EW	VSOP8	PA20SO20D-EO-210
WINBOND	W25Q80EW	WSON8	PA8SON8D(6x5)
WINBOND	W25X05CL	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25X05CL	TSSOP8	PA8TSS8D
WINBOND	W25X05CL	USON8	PA8SON8D(2x3)
WINBOND	W25X05CL	VSOP8	PA16SO16D-EO-150
WINBOND	W25X05CL	WSON8	PA8SON8D(6x5)
WINBOND	W25X10AV	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25X10AV	WSON8	PA8SON8D(6x5)
WINBOND	W25X10BV	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25X10BV	SOIC8	PA20SO20D-EO-210
WINBOND	W25X10BV	WSON8	PA8SON8D(6x5)
WINBOND	W25X10CL	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25X10CL	USON8	PA8SON8D(2x3)
WINBOND	W25X10V	DIP8	
WINBOND	W25X10V	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25X10V	WSON8	PA8SON8D(6x5)
WINBOND	W25X16AV	DIP8	
WINBOND	W25X16AV	SOIC16	PA28SO28D-EO-300
WINBOND	W25X16AV	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25X16AV	SOIC8	PA20SO20D-EO-210
WINBOND	W25X16AV	WSON8	PA8SON8D(6x5)
WINBOND	W25X16BV	DIP8	
WINBOND	W25X16BV	SOIC16	PA28SO28D-EO-300
WINBOND	W25X16BV	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25X16BV	SOIC8	PA20SO20D-EO-210
WINBOND	W25X16BV	WSON8	PA8SON8D(6x5)
WINBOND	W25X16V	DIP8	
WINBOND	W25X16V	SOIC16	PA28SO28D-EO-300
WINBOND	W25X16V	SOIC8	PA20SO20D-EO-210
WINBOND	W25X16V	WSON8	PA8SON8D(6x5)
WINBOND	W25X20AV	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25X20AV	WSON8	PA8SON8D(6x5)
WINBOND	W25X20BV	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25X20BV	SOIC8	PA20SO20D-EO-210
WINBOND	W25X20BV	WSON8	PA8SON8D(6x5)
WINBOND	W25X20CL	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25X20CL	TSSOP8	PA8TSS8D
WINBOND	W25X20CL	USON8	PA8SON8D(2x3)

WINBOND	W25X20CL	VSOP8	PA16SO16D-EO-150
WINBOND	W25X20CL	WSON8	PA8SON8D(6x5)
WINBOND	W25X20V	DIP8	
WINBOND	W25X20V	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25X20V	WSON8	PA8SON8D(6x5)
WINBOND	W25X32AV	DIP8	
WINBOND	W25X32AV	SOIC16	PA28SO28D-EO-300
WINBOND	W25X32AV	SOIC8	PA20SO20D-EO-210
WINBOND	W25X32AV	WSON8	PA8SON8D(6x5)
WINBOND	W25X32AV	WSON8	PA8SON8DA(8x6)
WINBOND	W25X32BV	SOIC16	PA28SO28D-EO-300
WINBOND	W25X32BV	SOIC8	PA20SO20D-EO-210
WINBOND	W25X32BV	WSON8	PA8SON8D(6x5)
WINBOND	W25X32BV	WSON8	PA8SON8DA(8x6)
WINBOND	W25X32V	DIP8	
WINBOND	W25X32V	SOIC16	PA28SO28D-EO-300
WINBOND	W25X32V	SOIC8	PA20SO20D-EO-210
WINBOND	W25X32V	WSON8	PA8SON8DA(8x6)
WINBOND	W25X40AV	DIP8	
WINBOND	W25X40AV	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25X40AV	SOIC8	PA20SO20D-EO-210
WINBOND	W25X40AV	WSON8	PA8SON8D(6x5)
WINBOND	W25X40BV	DIP8	
WINBOND	W25X40BV	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25X40BV	SOIC8	PA20SO20D-EO-210
WINBOND	W25X40BV	WSON8	PA8SON8D(6x5)
WINBOND	W25X40CL	DIP8	
WINBOND	W25X40CL	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25X40CL	SOIC8	PA20SO20D-EO-210
WINBOND	W25X40CL	USON8	PA8SON8D(2x3)
WINBOND	W25X40CL	VSOP8	PA16SO16D-EO-150
WINBOND	W25X40CL	WSON8	PA8SON8D(6x5)
WINBOND	W25X40V	DIP8	
WINBOND	W25X40V	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25X40V	SOIC8	PA20SO20D-EO-210
WINBOND	W25X40V	WSON8	PA8SON8D(6x5)
WINBOND	W25X64BV	SOIC16	PA28SO28D-EO-300
WINBOND	W25X64BV	SOIC8	PA20SO20D-EO-210
WINBOND	W25X64BV	WSON8	PA8SON8DA(8x6)
WINBOND	W25X64V	DIP8	
WINBOND	W25X64V	SOIC16	PA28SO28D-EO-300
WINBOND	W25X64V	WSON8	PA8SON8DA(8x6)
WINBOND	W25X80AV	DIP8	
WINBOND	W25X80AV	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25X80AV	SOIC8	PA20SO20D-EO-210
WINBOND	W25X80AV	WSON8	PA8SON8D(6x5)
WINBOND	W25X80BV	SOIC8	PA16SO16D-EO-150/PA8SO8D-150
WINBOND	W25X80BV	SOIC8	PA20SO20D-EO-210
WINBOND	W25X80BV	WSON8	PA8SON8D(6x5)
WINBOND	W25X80V	DIP8	
WINBOND	W25X80V	SOIC8	PA20SO20D-EO-210
WINBOND	W25X80V	WSON8	PA8SON8D(6x5)
WINBOND	W27C010	DIP32	
WINBOND	W27C010	PLCC32	PA32PL32D
WINBOND	W27C010	SOP32	PA32SO32D-EO-450
WINBOND	W27C020	DIP32	
WINBOND	W27C020	PLCC32	PA32PL32D
WINBOND	W27C020M	DIP32	
WINBOND	W27C020M	PLCC32	PA32PL32D
WINBOND	W27C512	DIP28	
WINBOND	W27C512	PLCC32	PA32PL28D-YA
WINBOND	W27E010	DIP32	
WINBOND	W27E010	PLCC32	PA32PL32D
WINBOND	W27E010	SOP32	PA32SO32D-EO-450
WINBOND	W27E020	DIP32	
WINBOND	W27E020	PLCC32	PA32PL32D
WINBOND	W27E040	DIP32	
WINBOND	W27E040	PLCC32	PA32PL32D
WINBOND	W27E040	SOP32	PA32SO32D-EO-450
WINBOND	W27E040	TSOP32	PA32TS20/PA32TS32D-20
WINBOND	W27E256	DIP28	
WINBOND	W27E257	DIP28	
WINBOND	W27E4096	DIP40	

WINBOND	W27E4096	PLCC44	PA44-48U
WINBOND	W27E512	DIP28	
WINBOND	W27E512	PLCC32	PA32PL28D-YA
WINBOND	W27E512	TSOP28	PA28TS28D-EO
WINBOND	W27F010	DIP32	
WINBOND	W27F256	DIP28	
WINBOND	W27F512	DIP28	
WINBOND	W27L010	DIP32	
WINBOND	W27L010	PLCC32	PA32PL32D
WINBOND	W27L010	SOP32	PA32SO32D-EO-450
WINBOND	W27L02	DIP32	
WINBOND	W27L02P	PLCC32	PA32PL32D
WINBOND	W27L02Q	TSOP32	PA32TS20/PA32TS32D-20
WINBOND	W29C010	DIP32	
WINBOND	W29C010	PLCC32	PA32PL32D
WINBOND	W29C010	SOP32	PA32SO32D-EO-450
WINBOND	W29C011	DIP32	
WINBOND	W29C011	PLCC32	PA32PL32D
WINBOND	W29C011	SOP32	PA32SO32D-EO-450
WINBOND	W29C011A	DIP32	
WINBOND	W29C011A	PLCC32	PA32PL32D
WINBOND	W29C011A	SOP32	PA32SO32D-EO-450
WINBOND	W29C020	DIP32	
WINBOND	W29C020P	PLCC32	PA32PL32D
WINBOND	W29C020T	TSOP32	PA32TS20/PA32TS32D-20
WINBOND	W29C040	DIP32	
WINBOND	W29C040P	PLCC32	PA32PL32D
WINBOND	W29C040T	TSOP32	PA32TS20/PA32TS32D-20
WINBOND	W29C101	DIP40	
WINBOND	W29C101	PLCC44	PA44-48U
WINBOND	W29C101	TSOP40	PA40TS40D
WINBOND	W29C102	DIP40	
WINBOND	W29C102	PLCC44	PA44-48U
WINBOND	W29C102	TSOP40	PA40TS40D
WINBOND	W29EE010	DIP32	
WINBOND	W29EE010	PLCC32	PA32PL32D
WINBOND	W29EE010	SOP32	PA32SO32D-EO-450
WINBOND	W29EE010	TSOP32	PA32TS20/PA32TS32D-20
WINBOND	W29EE011	DIP32	
WINBOND	W29EE011	PLCC32	PA32PL32D
WINBOND	W29EE011	SOP32	PA32SO32D-EO-450
WINBOND	W29EE011	TSOP32	PA32TS20/PA32TS32D-20
WINBOND	W29EE012	PLCC32	PA32PL32D
WINBOND	W29EE012	TSOP32	PA32TS20/PA32TS32D-20
WINBOND	W29EE021	DIP32	
WINBOND	W29EE512	DIP32	
WINBOND	W29EE512	PLCC32	PA32PL32D
WINBOND	W29F102	PLCC44	PA44-48U
WINBOND	W29F102	TSOP40	PA40TS40D
WINBOND	W29GL032CB-S	TSOP48	PA48TS48D1
WINBOND	W29GL032CT-S	TSOP48	PA48TS48D1
WINBOND	W29GL128CH-B	BGA64	PA64BG48DR
WINBOND	W29GL128CH-C	BGA56	NA56BG48DU
WINBOND	W29GL128CH-T	TSOP56	HA56TS48DI
WINBOND	W29GL128CL-B	BGA64	PA64BG48DR
WINBOND	W29GL128CL-C	BGA56	NA56BG48DU
WINBOND	W29GL128CL-T	TSOP56	HA56TS48DI
WINBOND	W29GL256SH-B	BGA64	PA64BG48DR
WINBOND	W29GL256SH-C	BGA56	NA56BG48DU
WINBOND	W29GL256SH-T	TSOP56	HA56TS48DI
WINBOND	W29GL256SL-B	BGA64	PA64BG48DR
WINBOND	W29GL256SL-C	BGA56	NA56BG48DU
WINBOND	W29GL256SL-T	TSOP56	HA56TS48DI
WINBOND	W39L020P	PLCC32	PA32PL32D
WINBOND	W39L040AP	PLCC32	PA32PL32D
WINBOND	W39L040AQ	sTSOP32	PA32TS32D-14
WINBOND	W39L040AT	TSOP32	PA32TS20/PA32TS32D-20
WINBOND	W39L040P	PLCC32	PA32PL32D
WINBOND	W39L040Q	sTSOP32	PA32TS32D-14
WINBOND	W39L040T	TSOP32	PA32TS20/PA32TS32D-20
WINBOND	W39V040AP	PLCC32	PA32PL32D
WINBOND	W39V040APZ	PLCC32	PA32PL32D
WINBOND	W39V040BP	PLCC32	PA32PL32D

WINBOND	W39V040BPZ	PLCC32	PA32PL32D
WINBOND	W39V040CP	PLCC32	PA32PL32D
WINBOND	W39V040CPZ	PLCC32	PA32PL32D
WINBOND	W39V040FAP	PLCC32	PA32PL32D
WINBOND	W39V040FAPZ	PLCC32	PA32PL32D
WINBOND	W39V080AP	PLCC32	PA32PL32D
WINBOND	W39V080APZ	PLCC32	PA32PL32D
WINBOND	W49F002A	DIP32	
WINBOND	W49F002A	PLCC32	PA32PL32D
WINBOND	W49F002U	DIP32	
WINBOND	W49F002U	PLCC32	PA32PL32D
WINBOND	W49F002U	TSOP32	PA32TS20/PA32TS32D-20
WINBOND	W49F020	DIP32	
WINBOND	W49F020P	PLCC32	PA32PL32D
WINBOND	W49F020T	TSOP32	PA32TS20/PA32TS32D-20
WINBOND	W49F102	PLCC44	PA44-48U
WINBOND	W49F102	TSOP40	PA40TS14-OT
WINBOND	W49F201S	SOP44	PA44SO44D
WINBOND	W49F201T	TSOP48	PA48TS48D
WINBOND	W49L102	TSOP40	PA40TS14-OT
WINBOND	W49L201S	SOP44	PA44SO44D
WINBOND	W49L201T	TSOP48	PA48TS48D
WINBOND	W49L401S	SOP44	PA44SO44D
WINBOND	W49L401T	TSOP48	PA48TS48D
WINBOND	W49L401TS	SOP44	PA44SO44D
WINBOND	W49L401TT	TSOP48	PA48TS48D
WINBOND	W49V002	DIP32	
WINBOND	W49V002	PLCC32	PA32PL32D
WINBOND	W49V002AP	PLCC32	PA32PL32D
WINBOND	W49V002AQ	TSOP32	PA32TS20/PA32TS32D-20
WINBOND	W49V002FAP	PLCC32	PA32PL32D
WINBOND	W49V002FAQ	TSOP32	PA32TS20/PA32TS32D-20
WINBOND	W49V002FP	PLCC32	PA32PL32D
WINBOND	W49V002FQ	TSOP32	PA32TS20/PA32TS32D-20
WINBOND	W49V002Q	TSOP32	PA32TS20/PA32TS32D-20
WINBOND	W77E516	DIP40	
WINBOND	W77E516F	QFP44	PA44QF44D
WINBOND	W77E516P	PLCC44	PA44-48U
WINBOND	W77E532-40	DIP40	
WINBOND	W77E532A40DL	DIP40	
WINBOND	W77E532A40FL	QFP44	PA44QF44D
WINBOND	W77E532A40PL	PLCC44	PA44-48U
WINBOND	W77E532F-40	QFP44	PA44QF44D
WINBOND	W77E532P-40	PLCC44	PA44-48U
WINBOND	W77E58	DIP40	
WINBOND	W77E58F	QFP44	PA44QF44D
WINBOND	W77E58P	PLCC44	PA44-48U
WINBOND	W77LE532-25	DIP40	
WINBOND	W77LE532A25DL	DIP40	
WINBOND	W77LE532A25FL	QFP44	PA44QF44D
WINBOND	W77LE532A25PL	PLCC44	PA44-48U
WINBOND	W77LE532F-25	QFP44	PA44QF44D
WINBOND	W77LE532P-25	PLCC44	PA44-48U
WINBOND	W77LE58	DIP40	
WINBOND	W77LE58F	QFP44	PA44QF44D
WINBOND	W77LE58P	PLCC44	PA44-48U
WINBOND	W78E058B	DIP40	
WINBOND	W78E065A	PLCC44	PA44-48U
WINBOND	W78E365A	DIP40	
WINBOND	W78E365A	PLCC44	PA44-48U
WINBOND	W78E365A	QFP44	PA44QF44D
WINBOND	W78E378P	PLCC44	PA44-48U
WINBOND	W78E51	DIP40	
WINBOND	W78E516	DIP40	
WINBOND	W78E516B	DIP40	
WINBOND	W78E516BF	QFP44	PA44QF44D
WINBOND	W78E516BP	PLCC44	PA44-48U
WINBOND	W78E516F	QFP44	PA44QF44D
WINBOND	W78E516P	PLCC44	PA44-48U
WINBOND	W78E51B	DIP40	
WINBOND	W78E51BF	QFP44	PA44QF44D
WINBOND	W78E51BP	PLCC44	PA44-48U
WINBOND	W78E51C	DIP40	

WINBOND	W78E51CF	QFP44	PA44QF44D
WINBOND	W78E51CP	PLCC44	PA44-48U
WINBOND	W78E51F	QFP44	PA44QF44D
WINBOND	W78E51P	PLCC44	PA44-48U
WINBOND	W78E52	DIP40	
WINBOND	W78E52B	DIP40	
WINBOND	W78E52BF	QFP44	PA44QF44D
WINBOND	W78E52BP	PLCC44	PA44-48U
WINBOND	W78E52C	DIP40	
WINBOND	W78E52CF	QFP44	PA44QF44D
WINBOND	W78E52CP	PLCC44	PA44-48U
WINBOND	W78E52F	QFP44	PA44QF44D
WINBOND	W78E52P	PLCC44	PA44-48U
WINBOND	W78E54	DIP40	
WINBOND	W78E54B	DIP40	
WINBOND	W78E54BF	QFP44	PA44QF44D
WINBOND	W78E54BP	PLCC44	PA44-48U
WINBOND	W78E54C	DIP40	
WINBOND	W78E54CF	QFP44	PA44QF44D
WINBOND	W78E54CP	PLCC44	PA44-48U
WINBOND	W78E54F	QFP44	PA44QF44D
WINBOND	W78E54P	PLCC44	PA44-48U
WINBOND	W78E58	DIP40	
WINBOND	W78E58B	DIP40	
WINBOND	W78E58BF	QFP44	PA44QF44D
WINBOND	W78E58BP	PLCC44	PA44-48U
WINBOND	W78E58F	QFP44	PA44QF44D
WINBOND	W78E58P	PLCC44	PA44-48U
WINBOND	W78E62BF	QFP44	PA44QF44D
WINBOND	W78E62BP	PLCC44	PA44-48U
WINBOND	W78E65F	QFP44	PA44QF44D
WINBOND	W78E65P	PLCC44	PA44-48U
WINBOND	W78ERD2A40DN	DIP40	
WINBOND	W78ERD2A40FN	QFP44	PA44QF44D
WINBOND	W78ERD2A40PN	PLCC44	PA44-48U
WINBOND	W78LE51	DIP40	
WINBOND	W78LE516	DIP40	
WINBOND	W78LE516B	DIP40	
WINBOND	W78LE516BF	QFP44	PA44QF44D
WINBOND	W78LE516BP	PLCC44	PA44-48U
WINBOND	W78LE516F	QFP44	PA44QF44D
WINBOND	W78LE516P	PLCC44	PA44-48U
WINBOND	W78LE51C	DIP40	
WINBOND	W78LE51CF	QFP44	PA44QF44D
WINBOND	W78LE51CP	PLCC44	PA44-48U
WINBOND	W78LE51F	QFP44	PA44QF44D
WINBOND	W78LE51P	PLCC44	PA44-48U
WINBOND	W78LE52	DIP40	
WINBOND	W78LE52C	DIP40	
WINBOND	W78LE52CF	QFP44	PA44QF44D
WINBOND	W78LE52CP	PLCC44	PA44-48U
WINBOND	W78LE52F	QFP44	PA44QF44D
WINBOND	W78LE52P	PLCC44	PA44-48U
WINBOND	W78LE54	DIP40	
WINBOND	W78LE54C	DIP40	
WINBOND	W78LE54CF	QFP44	PA44QF44D
WINBOND	W78LE54CP	PLCC44	PA44-48U
WINBOND	W78LE54F	QFP44	PA44QF44D
WINBOND	W78LE54P	PLCC44	PA44-48U
WINBOND	W78LE58	DIP40	
WINBOND	W78LE58F	QFP44	PA44QF44D
WINBOND	W78LE58P	PLCC44	PA44-48U
WINBOND	W78LE812	DIP40	
WINBOND	W78LE812F	QFP44	PA44QF44D
WINBOND	W78LE812P	PLCC44	PA44-48U
WINBOND	W79E532A40DN	DIP40	
WINBOND	W79E532A40FN	QFP44	PA44QF44D
WINBOND	W79E532A40PN	PLCC44	PA44-48U
WINBOND	W79E632A40DN	DIP40	
WINBOND	W79E632A40FN	QFP44	PA44QF44D
WINBOND	W79E632A40PN	PLCC44	PA44-48U
WINBOND	W79L532A40DN	DIP40	
WINBOND	W79L532A40FN	QFP44	PA44QF44D

WINBOND	W79L532A40PN	PLCC44	PA44-48U
WINBOND	W79L632A40DN	DIP40	
WINBOND	W79L632A40FN	QFP44	PA44QF44D
WINBOND	W79L632A40PN	PLCC44	PA44-48U
XICOR	X2004	DIP28	
XICOR	X2016	DIP28	
XICOR	X20C04	DIP28	
XICOR	X20C04	PLCC32	PA32PL32D
XICOR	X20C16	DIP28	
XICOR	X20C16	PLCC32	PA32PL32D
XICOR	X20C16	SOIC28	PA28SO28D-EO-300
XICOR	X20C16	TSOP32	PA32TS32D
XICOR	X2210	DIP18	
XICOR	X2210A	DIP18	
XICOR	X2212	DIP18	
XICOR	X2212A	DIP18	
XICOR	X22C10	DIP18	
XICOR	X22C10	SOIC16	PA16SO16D-EO-150
XICOR	X22C12	DIP18	
XICOR	X22C12	SOIC20	PA28SO28D-EO-300
XICOR	X24001	DIP8	
XICOR	X2402	DIP8	
XICOR	X2404	DIP8	
XICOR	X24164	DIP8	
XICOR	X24320	DIP8	
XICOR	X24320	SOIC8	PA16SO16D-EO-150
XICOR	X24320	TSSOP14	PA14TSS14D
XICOR	X24325	DIP8	
XICOR	X24325	SOIC8	PA16SO16D-EO-150
XICOR	X24325	TSSOP14	PA14TSS14D
XICOR	X24645	DIP8	
XICOR	X24645	SOIC8	PA16SO16D-EO-150
XICOR	X24645	TSSOP14	PA14TSS14D
XICOR	X24645	TSSOP20	PA20TSS20D
XICOR	X24C00	DIP8	
XICOR	X24C00	SOIC8	PA16SO16D-EO-150
XICOR	X24C01	DIP8	
XICOR	X24C01A	DIP8	
XICOR	X24C02	DIP8	
XICOR	X24C04	DIP8	
XICOR	X24C08	DIP8	
XICOR	X24C16	DIP8	
XICOR	X24C44	DIP8	
XICOR	X24C44	SOIC8	PA16SO16D-EO-150
XICOR	X24F016	DIP8	
XICOR	X24F016	SOIC8	PA16SO16D-EO-150
XICOR	X24F016	TSSOP14	PA14TSS14D
XICOR	X24F032	DIP8	
XICOR	X24F032	SOIC8	PA16SO16D-EO-150
XICOR	X24F032	TSSOP14	PA14TSS14D
XICOR	X24F064	DIP8	
XICOR	X24F064	SOIC8	PA16SO16D-EO-150
XICOR	X24F064	TSSOP20	PA20TSS20D
XICOR	X24F128	DIP8	
XICOR	X24F128	SOIC16	PA16SO16D-EO-150
XICOR	X24F128	SOIC8	PA16SO16D-EO-150
XICOR	X25020	DIP8	
XICOR	X25020	SOIC8	PA16SO16D-EO-150
XICOR	X25020	TSSOP8	PA8TSS8D
XICOR	X25021	DIP8	
XICOR	X25021	SOIC8	PA16SO16D-EO-150
XICOR	X25021	TSSOP8	PA8TSS8D
XICOR	X25040	DIP8	
XICOR	X25040	SOIC8	PA16SO16D-EO-150
XICOR	X25040	TSSOP8	PA8TSS8D
XICOR	X25041	DIP8	
XICOR	X25041	SOIC8	PA16SO16D-EO-150
XICOR	X25043	DIP8	
XICOR	X25043	SOIC8	PA16SO16D-EO-150
XICOR	X25043	TSSOP14	PA14TSS14D
XICOR	X25045	DIP8	
XICOR	X25045	SOIC8	PA16SO16D-EO-150
XICOR	X25045	TSSOP14	PA14TSS14D

XICOR	X25057	DIP8	
XICOR	X25057	MSOP8	PA8MSOP8D-1
XICOR	X25057	SOIC8	PA16SO16D-EO-150
XICOR	X25057	TSSOP8	PA24TSS24D
XICOR	X25057	TSSOP8	PA8TSS8D
XICOR	X25057(1.8)	DIP8	
XICOR	X25057(1.8)	MSOP8	PA8MSOP8D-1
XICOR	X25057(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25057(1.8)	TSSOP8	PA24TSS24D
XICOR	X25057(1.8)	TSSOP8	PA8TSS8D
XICOR	X25080	DIP8	
XICOR	X25080	SOIC8	PA16SO16D-EO-150
XICOR	X25080	TSSOP14	PA14TSS14D
XICOR	X25097	DIP8	
XICOR	X25097	SOIC8	PA16SO16D-EO-150
XICOR	X25097	TSSOP8	PA24TSS24D
XICOR	X25097	TSSOP8	PA8TSS8D
XICOR	X25097(1.8)	DIP8	
XICOR	X25097(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25097(1.8)	TSSOP8	PA24TSS24D
XICOR	X25097(1.8)	TSSOP8	PA8TSS8D
XICOR	X25128	DIP8	
XICOR	X25128	SOIC14	PA16SO16D-EO-150
XICOR	X25128	SOIC16	PA16SO16D-EO-150
XICOR	X25138	DIP8	
XICOR	X25138	SOIC16	PA16SO16D-EO-150
XICOR	X25138	SOIC8	PA16SO16D-EO-150
XICOR	X25138	TSSOP8	PA24TSS24D
XICOR	X25138	TSSOP8	PA8TSS8D
XICOR	X25160	DIP8	
XICOR	X25160	SOIC14	PA16SO16D-EO-150
XICOR	X25160	SOIC8	PA16SO16D-EO-150
XICOR	X25163	DIP8	
XICOR	X25163	SOIC14	PA16SO16D-EO-150
XICOR	X25163	SOIC8	PA16SO16D-EO-150
XICOR	X25163	TSSOP14	PA14TSS14D
XICOR	X25163(1.8)	DIP8	
XICOR	X25163(1.8)	SOIC14	PA16SO16D-EO-150
XICOR	X25163(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25163(1.8)	TSSOP14	PA14TSS14D
XICOR	X25165	DIP8	
XICOR	X25165	SOIC14	PA16SO16D-EO-150
XICOR	X25165	SOIC8	PA16SO16D-EO-150
XICOR	X25165	TSSOP14	PA14TSS14D
XICOR	X25165(1.8)	DIP8	
XICOR	X25165(1.8)	SOIC14	PA16SO16D-EO-150
XICOR	X25165(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25165(1.8)	TSSOP14	PA14TSS14D
XICOR	X25168	DIP8	
XICOR	X25168	SOIC14	PA16SO16D-EO-150
XICOR	X25168	SOIC8	PA16SO16D-EO-150
XICOR	X25168	TSSOP14	PA14TSS14D
XICOR	X25168(1.8)	DIP8	
XICOR	X25168(1.8)	SOIC14	PA16SO16D-EO-150
XICOR	X25168(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25168(1.8)	TSSOP14	PA14TSS14D
XICOR	X25169	DIP8	
XICOR	X25169	SOIC14	PA16SO16D-EO-150
XICOR	X25169	SOIC8	PA16SO16D-EO-150
XICOR	X25169	TSSOP14	PA14TSS14D
XICOR	X25169(1.8)	DIP8	
XICOR	X25169(1.8)	SOIC14	PA16SO16D-EO-150
XICOR	X25169(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25169(1.8)	TSSOP14	PA14TSS14D
XICOR	X25170	DIP8	
XICOR	X25170	SOIC8	PA16SO16D-EO-150
XICOR	X25170	TSSOP14	PA14TSS14D
XICOR	X25320	DIP8	
XICOR	X25320	SOIC8	PA16SO16D-EO-150
XICOR	X25320	TSSOP14	PA14TSS14D
XICOR	X25323	DIP8	
XICOR	X25323	SOIC14	PA16SO16D-EO-150
XICOR	X25323	SOIC8	PA16SO16D-EO-150



XICOR	X25323	TSSOP14	PA14TSS14D
XICOR	X25323(1.8)	DIP8	
XICOR	X25323(1.8)	SOIC14	PA16SO16D-EO-150
XICOR	X25323(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25323(1.8)	TSSOP14	PA14TSS14D
XICOR	X25325	DIP8	
XICOR	X25325	SOIC14	PA16SO16D-EO-150
XICOR	X25325	SOIC8	PA16SO16D-EO-150
XICOR	X25325	TSSOP14	PA14TSS14D
XICOR	X25325(1.8)	DIP8	
XICOR	X25325(1.8)	SOIC14	PA16SO16D-EO-150
XICOR	X25325(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25325(1.8)	TSSOP14	PA14TSS14D
XICOR	X25328	DIP8	
XICOR	X25328	SOIC14	PA16SO16D-EO-150
XICOR	X25328	SOIC8	PA16SO16D-EO-150
XICOR	X25328	TSSOP14	PA14TSS14D
XICOR	X25328(1.8)	DIP8	
XICOR	X25328(1.8)	SOIC14	PA16SO16D-EO-150
XICOR	X25328(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25328(1.8)	TSSOP14	PA14TSS14D
XICOR	X25329	DIP8	
XICOR	X25329	SOIC14	PA16SO16D-EO-150
XICOR	X25329	SOIC8	PA16SO16D-EO-150
XICOR	X25329	TSSOP14	PA14TSS14D
XICOR	X25329(1.8)	DIP8	
XICOR	X25329(1.8)	SOIC14	PA16SO16D-EO-150
XICOR	X25329(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25329(1.8)	TSSOP14	PA14TSS14D
XICOR	X25640	DIP8	
XICOR	X25642	DIP8	
XICOR	X25642	SOIC8	PA16SO16D-EO-150
XICOR	X25643	DIP8	
XICOR	X25643	SOIC14	PA16SO16D-EO-150
XICOR	X25643	SOIC8	PA16SO16D-EO-150
XICOR	X25643	TSSOP14	PA14TSS14D
XICOR	X25643(1.8)	DIP8	
XICOR	X25643(1.8)	SOIC14	PA16SO16D-EO-150
XICOR	X25643(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25643(1.8)	TSSOP14	PA14TSS14D
XICOR	X25645	DIP8	
XICOR	X25645	SOIC14	PA16SO16D-EO-150
XICOR	X25645	SOIC8	PA16SO16D-EO-150
XICOR	X25645	TSSOP14	PA14TSS14D
XICOR	X25645(1.8)	DIP8	
XICOR	X25645(1.8)	SOIC14	PA16SO16D-EO-150
XICOR	X25645(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25645(1.8)	TSSOP14	PA14TSS14D
XICOR	X25648	DIP8	
XICOR	X25648	SOIC14	PA16SO16D-EO-150
XICOR	X25648	SOIC8	PA16SO16D-EO-150
XICOR	X25648	TSSOP14	PA14TSS14D
XICOR	X25648(1.8)	DIP8	
XICOR	X25648(1.8)	SOIC14	PA16SO16D-EO-150
XICOR	X25648(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25648(1.8)	TSSOP14	PA14TSS14D
XICOR	X25649	DIP8	
XICOR	X25649	SOIC14	PA16SO16D-EO-150
XICOR	X25649	SOIC8	PA16SO16D-EO-150
XICOR	X25649	TSSOP14	PA14TSS14D
XICOR	X25649(1.8)	DIP8	
XICOR	X25649(1.8)	SOIC14	PA16SO16D-EO-150
XICOR	X25649(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25649(1.8)	TSSOP14	PA14TSS14D
XICOR	X25C02	DIP8	
XICOR	X25C02	MSOP8	PA8MSOP8D/PA8SS8D-120
XICOR	X25C02	SOIC8	PA16SO16D-EO-150
XICOR	X25F008	DIP8	
XICOR	X25F008	SOIC8	PA16SO16D-EO-150
XICOR	X25F008	TSSOP14	PA14TSS14D
XICOR	X25F008	TSSOP20	PA20TSS20D
XICOR	X25F008(1.8)	DIP8	
XICOR	X25F008(1.8)	SOIC8	PA16SO16D-EO-150

XICOR	X25F008(1.8)	TSSOP14	PA14TSS14D
XICOR	X25F008(1.8)	TSSOP20	PA20TSS20D
XICOR	X25F016	DIP8	
XICOR	X25F016	SOIC8	PA16SO16D-EO-150
XICOR	X25F016	TSSOP14	PA14TSS14D
XICOR	X25F016	TSSOP20	PA20TSS20D
XICOR	X25F016(1.8)	DIP8	
XICOR	X25F016(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25F016(1.8)	TSSOP14	PA14TSS14D
XICOR	X25F016(1.8)	TSSOP20	PA20TSS20D
XICOR	X25F032	DIP8	
XICOR	X25F032	SOIC8	PA16SO16D-EO-150
XICOR	X25F032	TSSOP14	PA14TSS14D
XICOR	X25F032	TSSOP20	PA20TSS20D
XICOR	X25F032(1.8)	DIP8	
XICOR	X25F032(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25F032(1.8)	TSSOP14	PA14TSS14D
XICOR	X25F032(1.8)	TSSOP20	PA20TSS20D
XICOR	X25F047	DIP8	
XICOR	X25F047	MSOP8	PA8MSOP8D-1
XICOR	X25F047	SOIC8	PA16SO16D-EO-150
XICOR	X25F047	TSSOP8	PA24TSS24D
XICOR	X25F047	TSSOP8	PA8TSS8D
XICOR	X25F047(1.8)	DIP8	
XICOR	X25F047(1.8)	MSOP8	PA8MSOP8D-1
XICOR	X25F047(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25F047(1.8)	TSSOP8	PA24TSS24D
XICOR	X25F047(1.8)	TSSOP8	PA8TSS8D
XICOR	X25F064	DIP8	
XICOR	X25F064	SOIC8	PA16SO16D-EO-150
XICOR	X25F064	TSSOP14	PA14TSS14D
XICOR	X25F064	TSSOP20	PA20TSS20D
XICOR	X25F064(1.8)	DIP8	
XICOR	X25F064(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25F064(1.8)	TSSOP14	PA14TSS14D
XICOR	X25F064(1.8)	TSSOP20	PA20TSS20D
XICOR	X25F087	DIP8	
XICOR	X25F087	SOIC8	PA16SO16D-EO-150
XICOR	X25F087	TSSOP8	PA24TSS24D
XICOR	X25F087	TSSOP8	PA8TSS8D
XICOR	X25F087(1.8)	DIP8	
XICOR	X25F087(1.8)	SOIC8	PA16SO16D-EO-150
XICOR	X25F087(1.8)	TSSOP8	PA24TSS24D
XICOR	X25F087(1.8)	TSSOP8	PA8TSS8D
XICOR	X25F128	DIP8	
XICOR	X25F128	SOIC16	PA16SO16D-EO-150
XICOR	X25F128(1.8)	DIP8	
XICOR	X25F128(1.8)	SOIC16	PA16SO16D-EO-150
XICOR	X2804A	DIP24	
XICOR	X2816A	DIP24	
XICOR	X2816B	DIP24	
XICOR	X2816C	DIP24	
XICOR	X28256	DIP28	
XICOR	X2864A	DIP28	
XICOR	X2864B	DIP28	
XICOR	X2864H	DIP28	
XICOR	X28C010	DIP32	
XICOR	X28C256	DIP28	
XICOR	X28C512	DIP32	
XICOR	X28C513	PLCC32	PA32PL32D
XICOR	X28C64	DIP28	
XICOR	X28HC256	DIP28	
XICOR	X28HC256	PLCC32	PA32PL28D-YA
XICOR	X28HC64	DIP28	
XICOR	X28LC512	DIP32	
XICOR	X28LC513	PLCC32	PA32PL32D
XICOR	X5043	DIP8	
XICOR	X5043	MSOP8	PA8MSOP8D/PA8SS8D-120
XICOR	X5043	SOIC8	PA16SO16D-EO-150
XICOR	X5043	TSSOP14	PA14TSS14D
XICOR	X5045	DIP8	
XICOR	X5045	MSOP8	PA8MSOP8D/PA8SS8D-120
XICOR	X5045	SOIC8	PA16SO16D-EO-150

XICOR	X5045	TSSOP14	PA14TSS14D
XICOR	X5163	DIP8	
XICOR	X5163	SOIC8	PA16SO16D-EO-150
XICOR	X5163	TSSOP14	PA14TSS14D
XICOR	X5163AG	DIP8	
XICOR	X5163AG	SOIC8	PA16SO16D-EO-150
XICOR	X5163AG	TSSOP14	PA14TSS14D
XICOR	X5163AH	DIP8	
XICOR	X5163AH	SOIC8	PA16SO16D-EO-150
XICOR	X5163AH	TSSOP14	PA14TSS14D
XICOR	X5165	DIP8	
XICOR	X5165	SOIC8	PA16SO16D-EO-150
XICOR	X5165	TSSOP14	PA14TSS14D
XICOR	X5165AG	DIP8	
XICOR	X5165AG	SOIC8	PA16SO16D-EO-150
XICOR	X5165AG	TSSOP14	PA14TSS14D
XICOR	X5165AH	DIP8	
XICOR	X5165AH	SOIC8	PA16SO16D-EO-150
XICOR	X5165AH	TSSOP14	PA14TSS14D
XICOR	X5168	DIP8	
XICOR	X5168	SOIC8	PA16SO16D-EO-150
XICOR	X5168	TSSOP14	PA14TSS14D
XICOR	X5169	DIP8	
XICOR	X5169	SOIC8	PA16SO16D-EO-150
XICOR	X5169	TSSOP14	PA14TSS14D
XICOR	X68257	DIP28	
XICOR	X68C64	DIP24	
XICOR	X76F041A	SOIC8	PA20SO20D-EO-210
XICOR	X76F041A-3	SOIC8	PA20SO20D-EO-210
XICOR	X76F041P	DIP8	
XICOR	X76F041P-3	DIP8	
XICOR	X76F100	DIP8	
XICOR	X76F640	DIP8	
XICOR	X84041	DIP8	
XICOR	X84041	SOIC8	PA16SO16D-EO-150
XICOR	X84041	TSSOP14	PA14TSS14D
XICOR	X84129	DIP8	
XICOR	X84129	DIP8	
XICOR	X84129	SOIC8	PA16SO16D-EO-150
XICOR	X84129	TSSOP14	PA14TSS14D
XICOR	X84129	TSSOP28	PA28TSS28D-EO
XICOR	X84161	DIP8	
XICOR	X84161	DIP8	
XICOR	X84161	SOIC8	PA16SO16D-EO-150
XICOR	X84161	TSSOP8	PA8TSS-OT
XICOR	X84641	DIP8	
XICOR	X84641	DIP8	
XICOR	X84641	SOIC8	PA16SO16D-EO-150
XICOR	X84641	TSSOP20	PA20TSS20D
XICOR	X88257	DIP28	
XICOR	X88C64	DIP24	
XICOR	XM28C010	DIP32	
XILINX	XC1701	DIP8	
XILINX	XC1701	PLCC44	PA44-48U
XILINX	XC1701	SOIC20	PA28SO28D-EO-300
XILINX	XC1701L	DIP8	
XILINX	XC1701L	PLCC44	PA44-48U
XILINX	XC1701L	SOIC20	PA28SO28D-EO-300
XILINX	XC1702L	DIP8	
XILINX	XC1702L	PLCC44	PA44-48U
XILINX	XC1702L	QFP44	PA44QF44D-1
XILINX	XC1704L	DIP8	
XILINX	XC1704L	PLCC44	PA44-48U
XILINX	XC1704L	QFP44	PA44QF44D-1
XILINX	XC17128D	DIP8	
XILINX	XC17128D	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17128D	PLCC20	PA20PL8D
XILINX	XC17128D	VDFN8	PA8VO8D
XILINX	XC17128E	DIP8	
XILINX	XC17128E	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17128E	PLCC20	PA20PL8D
XILINX	XC17128E	VDFN8	PA8VO8D
XILINX	XC17128EL	DIP8	

XILINX	XC17128EL	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17128EL	PLCC20	PA20PL8D
XILINX	XC17128EL	VDFN8	PA8VO8D
XILINX	XC17128EL(X)	DIP8	
XILINX	XC17128L	DIP8	
XILINX	XC17128L	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17128L	PLCC20	PA20PL8D
XILINX	XC17128L	VDFN8	PA8VO8D
XILINX	XC17128X	DIP8	
XILINX	XC17128X	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17128X	PLCC20	PA20PL8D
XILINX	XC17128X	VDFN8	PA8VO8D
XILINX	XC1718D	DIP8	
XILINX	XC1718D	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC1718D	PLCC20	PA20PL8D
XILINX	XC1718D	SOIC8	PA28SO28D-EO-300
XILINX	XC1718D	VDFN8	PA8VO8D
XILINX	XC1718L	DIP8	
XILINX	XC1718L	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC1718L	PLCC20	PA20PL8D
XILINX	XC1718L	SOIC8	PA28SO28D-EO-300
XILINX	XC1718L	VDFN8	PA8VO8D
XILINX	XC17256D	DIP8	
XILINX	XC17256D	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17256D	PLCC20	PA20PL8D
XILINX	XC17256D	VDFN8	PA8VO8D
XILINX	XC17256E	DIP8	
XILINX	XC17256E	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17256E	VDFN8	PA8VO8D
XILINX	XC17256EL	DIP8	
XILINX	XC17256EL	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17256EL	PLCC20	PA20PL8D
XILINX	XC17256EL	VDFN8	PA8VO8D
XILINX	XC17256EL(X)	DIP8	
XILINX	XC17256L	DIP8	
XILINX	XC17256L	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17256L	PLCC20	PA20PL8D
XILINX	XC17256L	VDFN8	PA8VO8D
XILINX	XC17256X	DIP8	
XILINX	XC17256X	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17256X	PLCC20	PA20PL8D
XILINX	XC17256X	VDFN8	PA8VO8D
XILINX	XC1736D	DIP8	
XILINX	XC1736D	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC1736D	PLCC20	PA20PL8D
XILINX	XC1736D	SOIC8	PA28SO28D-EO-300
XILINX	XC1736D	VDFN8	PA8VO8D
XILINX	XC1736E	DIP8	
XILINX	XC1736E	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC1736E	SOIC8	PA28SO28D-EO-300
XILINX	XC1736E	VDFN8	PA8VO8D
XILINX	XC17512L	DIP8	
XILINX	XC17512L	PLCC44	PA44-48U
XILINX	XC17512L	SOIC20	PA28SO28D-EO-300
XILINX	XC1765D	DIP8	
XILINX	XC1765D	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC1765D	PLCC20	PA20PL8D
XILINX	XC1765D	SOIC8	PA28SO28D-EO-300
XILINX	XC1765D	VDFN8	PA8VO8D
XILINX	XC1765E	DIP8	
XILINX	XC1765E	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC1765E	PLCC20	PA20PL8D
XILINX	XC1765E	SOIC8	PA28SO28D-EO-300
XILINX	XC1765E	VDFN8	PA8VO8D
XILINX	XC1765EL	DIP8	
XILINX	XC1765EL	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC1765EL	PLCC20	PA20PL8D
XILINX	XC1765EL	SOIC8	PA28SO28D-EO-300
XILINX	XC1765EL	VDFN8	PA8VO8D
XILINX	XC1765EL(X)	DIP8	
XILINX	XC1765L	DIP8	
XILINX	XC1765L	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC1765L	PLCC20	PA20PL8D

XILINX	XC1765L	SOIC8	PA28SQ28D-EO-300
XILINX	XC1765L	VDFN8	PA8VO8D
XILINX	XC1765X	DIP8	
XILINX	XC1765X	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC1765X	PLCC20	PA20PL8D
XILINX	XC1765X	SOIC8	PA28SQ28D-EO-300
XILINX	XC1765X	VDFN8	PA8VO8D
XILINX	XC17S05	DIP8	
XILINX	XC17S05	SOIC8	PA16SO16D-EO-150
XILINX	XC17S05	VDFN8	PA8VO8D
XILINX	XC17S05L	DIP8	
XILINX	XC17S05L	SOIC8	PA16SO16D-EO-150
XILINX	XC17S05L	VDFN8	PA8VO8D
XILINX	XC17S05XL	DIP8	
XILINX	XC17S05XL	SOIC8	PA16SO16D-EO-150
XILINX	XC17S05XL	VDFN8	PA8VO8D
XILINX	XC17S10	DIP8	
XILINX	XC17S10	VDFN8	PA8VO8D
XILINX	XC17S100A	DIP8	
XILINX	XC17S100A	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17S100A	PLCC44	PA44-48U
XILINX	XC17S100A	QFP44	PA44QF44D
XILINX	XC17S100A	SOIC20	PA28SQ28D-EO-300
XILINX	XC17S100A	VDFN8	PA8VO8D
XILINX	XC17S100L	DIP8	
XILINX	XC17S100L	SOIC20	PA28SQ28D-EO-300
XILINX	XC17S100XL	DIP8	
XILINX	XC17S100XL	SOIC20	PA28SQ28D-EO-300
XILINX	XC17S10L	DIP8	
XILINX	XC17S10L	VDFN8	PA8VO8D
XILINX	XC17S10XL	DIP8	
XILINX	XC17S10XL	VDFN8	PA8VO8D
XILINX	XC17S150A	DIP8	
XILINX	XC17S150A	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17S150A	PLCC44	PA44-48U
XILINX	XC17S150A	QFP44	PA44QF44D
XILINX	XC17S150A	SOIC20	PA28SQ28D-EO-300
XILINX	XC17S150A	VDFN8	PA8VO8D
XILINX	XC17S150L	DIP8	
XILINX	XC17S150L	SOIC20	PA28SQ28D-EO-300
XILINX	XC17S150XL	DIP8	
XILINX	XC17S150XL	SOIC20	PA28SQ28D-EO-300
XILINX	XC17S15A	DIP8	
XILINX	XC17S15A	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17S15A	PLCC44	PA44-48U
XILINX	XC17S15A	QFP44	PA44QF44D
XILINX	XC17S15A	SOIC20	PA28SQ28D-EO-300
XILINX	XC17S15A	VDFN8	PA8VO8D
XILINX	XC17S20	DIP8	
XILINX	XC17S20	VDFN8	PA8VO8D
XILINX	XC17S200A	DIP8	
XILINX	XC17S200A	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17S200A	PLCC44	PA44-48U
XILINX	XC17S200A	QFP44	PA44QF44D
XILINX	XC17S200A	SOIC20	PA28SQ28D-EO-300
XILINX	XC17S200A	VDFN8	PA8VO8D
XILINX	XC17S20L	DIP8	
XILINX	XC17S20L	VDFN8	PA8VO8D
XILINX	XC17S20XL	DIP8	
XILINX	XC17S20XL	VDFN8	PA8VO8D
XILINX	XC17S30	DIP8	
XILINX	XC17S30	VDFN8	PA8VO8D
XILINX	XC17S30A	DIP8	
XILINX	XC17S30A	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17S30A	PLCC44	PA44-48U
XILINX	XC17S30A	QFP44	PA44QF44D
XILINX	XC17S30A	SOIC20	PA28SQ28D-EO-300
XILINX	XC17S30A	VDFN8	PA8VO8D
XILINX	XC17S30L	DIP8	
XILINX	XC17S30L	VDFN8	PA8VO8D
XILINX	XC17S30XL	DIP8	
XILINX	XC17S30XL	VDFN8	PA8VO8D
XILINX	XC17S40	DIP8	

XILINX	XC17S40	SOIC20	PA28SO28D-EO-300
XILINX	XC17S40L	DIP8	
XILINX	XC17S40L	SOIC20	PA28SO28D-EO-300
XILINX	XC17S40XL	DIP8	
XILINX	XC17S40XL	SOIC20	PA28SO28D-EO-300
XILINX	XC17S50	DIP8	
XILINX	XC17S50	SOIC20	PA28SO28D-EO-300
XILINX	XC17S50A	DIP8	
XILINX	XC17S50A	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17S50A	PLCC44	PA44-48U
XILINX	XC17S50A	QFP44	PA44QF44D
XILINX	XC17S50A	SOIC20	PA28SO28D-EO-300
XILINX	XC17S50A	VDFN8	PA8VO8D
XILINX	XC17S50L	DIP8	
XILINX	XC17S50L	SOIC20	PA28SO28D-EO-300
XILINX	XC17S50XL	DIP8	
XILINX	XC17S50XL	SOIC20	PA28SO28D-EO-300
XILINX	XC17V01	DIP8	
XILINX	XC17V01	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17V01	PLCC44	PA44-48U
XILINX	XC17V01	QFP44	PA44QF44D
XILINX	XC17V01	SOIC20	PA28SO28D-EO-300
XILINX	XC17V01	VDFN8	PA8VO8D
XILINX	XC17V02	DIP8	
XILINX	XC17V02	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17V02	PLCC44	PA44-48U
XILINX	XC17V02	QFP44	PA44QF44D
XILINX	XC17V02	SOIC20	PA28SO28D-EO-300
XILINX	XC17V02	VDFN8	PA8VO8D
XILINX	XC17V04	DIP8	
XILINX	XC17V04	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC17V04	PLCC44	PA44-48U
XILINX	XC17V04	QFP44	PA44QF44D
XILINX	XC17V04	SOIC20	PA28SO28D-EO-300
XILINX	XC17V04	VDFN8	PA8VO8D
XILINX	XC17V08	PLCC44	PA44-48U
XILINX	XC17V08	QFP44	PA44QF44D
XILINX	XC17V16	PLCC44	PA44-48U
XILINX	XC17V16	QFP44	PA44QF44D
XILINX	XC18V01PC20	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC18V01SO20	SOIC20	PA28SO28D-EO-300
XILINX	XC18V01VQ44	VQFP44	PA44QF44D
XILINX	XC18V02PC44	PLCC44	PA44-48U
XILINX	XC18V02VQ44	VQFP44	PA44QF44D
XILINX	XC18V04PC44	PLCC44	PA44-48U
XILINX	XC18V04VQ44	VQFP44	PA44QF44D
XILINX	XC18V256PC20	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC18V256SO20	SOIC20	PA28SO28D-EO-300
XILINX	XC18V256VQ44	VQFP44	PA44QF44D
XILINX	XC18V512PC20	PLCC20	PA20LC20D[Dead Bug]
XILINX	XC18V512SO20	SOIC20	PA28SO28D-EO-300
XILINX	XC18V512VQ44	VQFP44	PA44QF44D
XILINX	XC2C32	VQFP44	PA44QF44D
XILINX	XC2C32A	VQFP44	PA44QF44D
XILINX	XC2C64	VQFP44	PA44QF44D
XILINX	XC2C64A	VQFP44	PA44QF44D
XILINX	XC7236A	PLCC44	PA44-48U
XILINX	XC73108A	PLCC84	PA84-48B
XILINX	XC7318	PLCC44	PA44-48U
XILINX	XC7318A	PLCC44	PA44-48U
XILINX	XC7336	PLCC44	PA44-48U
XILINX	XC7336A	PLCC44	PA44-48U
XILINX	XC7336Q	PLCC44	PA44-48U
XILINX	XC7354	PLCC44	PA44-48U
XILINX	XC7354	PLCC68	PA68-48B
XILINX	XC7372	PLCC68	PA68-48C
XILINX	XC7372	PLCC84	PA84-48B
XILINX	XC95108	PLCC84	PA84-48B
XILINX	XC9536	PLCC44	PA44-48U
XILINX	XC9536	VQFP44	PA44TQ44D-EO
XILINX	XC9536XL	PLCC44	PA44-48U
XILINX	XC9536XL	VQFP44	PA44TQ44D-EO
XILINX	XC9536XL	VQFP64	PA64TQ48D

XILINX	XC9572	PLCC44	PA44-48U
XILINX	XC9572	PLCC84	PA84-48F
XILINX	XC9572	TQFP100	HA100TQ48DA
XILINX	XC9572XL	PLCC44	PA44-48U
XILINX	XC9572XL	TQFP100	PA100QF48DG
XILINX	XCF01SVO20	TSSOP20	PA24TSS24D
XILINX	XCF01SVOG20	TSSOP20	PA24TSS24D
XILINX	XCF02SVO20	TSSOP20	PA24TSS24D
XILINX	XCF02SVOG20	TSSOP20	PA24TSS24D
XILINX	XCF04SVO20	TSSOP20	PA24TSS24D
XILINX	XCF04SVOG20	TSSOP20	PA24TSS24D
XILINX	XCF08PVO48	TSOP48	PA48TS48D
XILINX	XCF16PVO48	TSOP48	PA48TS48D
XILINX	XCF32PVO48	TSOP48	PA48TS48D
XILINX	XCR3032XL	PLCC44	PA44-48U
XILINX	XCR3032XL	VQFP44	PA44VQ44D
XILINX	XCR3064XL	PLCC44	PA44-48U
XILINX	XCR3064XL	VQFP44	PA44VQ44D
XILINX	XCR3128XL	VQFP100	WA100QF48D
XILINX	XCS3032A/D	PLCC44	PA44-48U
XMC	XM25QH128A	SOP8	PA20SO20D-EO-210
XMC	XM25QH128A	WSON8	PA8SON8D(6x5)
ZILOG	Z86733	DIP28	
ZILOG	Z86743	DIP40	
ZILOG	Z86E02(1925)	DIP18	
ZILOG	Z86E0208PSC	DIP18	
ZILOG	Z86E0208PSC1866	DIP18	
ZILOG	Z86E0208PSC1903	DIP18	
ZILOG	Z86E0208SSC	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0208SSC1866	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0208SSC1903	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0308PSC	DIP18	
ZILOG	Z86E0308SSC	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0312PSC	DIP18	
ZILOG	Z86E0312SSC	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E04	DIP18	
ZILOG	Z86E04(1925)	DIP18	
ZILOG	Z86E0408PEC	DIP18	
ZILOG	Z86E0408PEC1903	DIP18	
ZILOG	Z86E0408PSC1866	DIP18	
ZILOG	Z86E0408PSC1903	DIP18	
ZILOG	Z86E0408SEC	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0408SEC1903	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0408SSC1866	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0408SSC1903	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0412PEC	DIP18	
ZILOG	Z86E0412PEC1903	DIP18	
ZILOG	Z86E0412PSC1866	DIP18	
ZILOG	Z86E0412PSC1903	DIP18	
ZILOG	Z86E0412SEC	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0412SEC1903	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0412SSC1866	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0412SSC1903	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0608PSC	DIP18	
ZILOG	Z86E0608SSC	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0612PSC	DIP18	
ZILOG	Z86E0612SSC	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E08	DIP18	
ZILOG	Z86E08(1925)	DIP18	
ZILOG	Z86E0808PEC	DIP18	
ZILOG	Z86E0808PEC1903	DIP18	
ZILOG	Z86E0808PSC1866	DIP18	
ZILOG	Z86E0808PSC1903	DIP18	
ZILOG	Z86E0808SEC	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0808SEC1903	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0808SSC1866	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0808SSC1903	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0812PEC	DIP18	
ZILOG	Z86E0812PEC1903	DIP18	
ZILOG	Z86E0812PSC1866	DIP18	
ZILOG	Z86E0812PSC1903	DIP18	
ZILOG	Z86E0812SEC	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0812SEC1903	SOIC18	PA28SO28D-EO-300

ZILOG	Z86E0812SSC1866	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E0812SSC1903	SOIC18	PA28SO28D-EO-300
ZILOG	Z86E21	DIP40	
ZILOG	Z86E30	DIP28	
ZILOG	Z86E30(1873)	DIP28	
ZILOG	Z86E31	DIP28	
ZILOG	Z86E33	DIP28	
ZILOG	Z86E34	DIP28	
ZILOG	Z86E40	DIP40	
ZILOG	Z86E40	PLCC44	PA44-48U
ZILOG	Z86E40(1873)	DIP40	
ZILOG	Z86E40(1873)	PLCC44	PA44-48U
ZILOG	Z86E43	DIP40	
ZILOG	Z86E44	DIP40	
ZILOG	Z86E61	DIP40	
ZILOG	Z86E61	PLCC44	PA44-48U
ZILOG	Z86E63	DIP40	
ZILOG	Z86E63	PLCC44	PA44-48U
ZILOG	Z8F0223SB	SOIC8	PA8SO8D-EO-150