

Rittal – The System.

Faster – better – everywhere.



PK 9516.000

Polycarbonate enclosures PK

Stan: 1/2/2023 (Źródło: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PK 9516.000 - Polycarbonate enclosures PK without knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



Cechy

Model No.	PK 9516.000
Applications	Ambient temperature range: -35 °C...+80 °C The specified temperatures may be limited by the installed equipment
Material	Enclosure: Fibreglass-reinforced polycarbonate Cover grey: Fibreglass-reinforced polycarbonate, all-round foamed-in PU seal Cover screws: Polyamide Insulating bungs: Polyethylene
Colour	RAL 7035
Supply includes	Enclosure with cover Cover screws Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08

Cechy

Dimensions	Width: 180 mm Height: 110 mm Depth: 165 mm
Cover version	grey
Operating temperature range	-35 °C...80 °C
Basic material	Polycarbonate
Packs of	2 pc(s).
Weight/pack	1.374 kg
Copper weight (kg per piece)	0
Customs tariff number	94037000
EAN	4028177139572
ETIM 7.0	EC000261
ECLASS 8.0	27180101

Aprobaty

Aprobaty	C-UL DNV-GL GOST UL
Wyjaśnienia	Declaration of conformity
