

Bourdon Tube Pressure Gauges, Stainless Steel
Type 23X.50
Item no.: 48780793

Description	
Design	EN 837-1
Nominal size	100 mm
Accuracy class	class 1.0
Scale range	-1...+24 bar
Unit of outer Scale	bar
Process connection	R 1/2-ISO7 (DIN2999)
Connector location	lower back mount
Materials	
Measuring system	stainless steel
Movement	
Dial	Aluminum, white
Pointer	aluminium, black
Case material	Stainless steel 1.4301
Window	laminated safety glass
Bezel ring	cam ring (bayonet type), stainless steel
Case filling fluid	prepared for filling
Operating conditions	
Permissible medium temperature	+ 200 °C
Permissible ambient temperature	-20 ... +60 °C
Ingress protection	IP 65
Options	
Special design features	for oxygen, oil and grease free

