

stay connected


SVS ECO LED VALVE PLUG FORM B 10 MM LED VDR 230V

2+PE field-wireable M16x1.5

Form B (10 mm) 230 V AC/DC with LED and VDR metric

Link to Product

Illustration




The information in this brochure has been compiled with the utmost care. Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 03/16

Murrelektronik GmbH | Falkenstraße 3,71570 Oppenweiler | Fon +49 (71 91) 47-0, Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com



stay connected



Height: 31 mm

Product may differ from Image

Approvals	
PG	
Form	
Form	29685
Technical Data	
Operating voltage	230 V AC/DC ±10 %
Operating current per contact	max. 1.5 A
Connection cross section	0.51.5 mm ²
Sealing range (cable Ø)	68 mm
Locking of ports	M3 (recommended torque 0.4 Nm)
Compression gland	M16 × 1.5 mm
Contact figure	Cable outlet can be turned in 180° steps
Protection	IP65 inserted and tightened
General data	
Temperature range	-40+60 °C
Commercial data	
country of origin	HU
customs tariff number	85366990
minimum order quantity	1

The information in this brochure has been compiled with the utmost care. Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 03/16

Murrelektronik GmbH | Falkenstraße 3,71570 Oppenweiler | Fon +49 (71 91) 47-0, Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com