

## Full Metal Hoods

## D45ZK+High Density D-Sub Solder Cup

### TECHNICAL SPECIFICATIONS

#### D-Sub Hood:


Material:	Zinc, Nickel Plated
Operating Temperature:	-40°C to +120°C
Cable Entry:	Side Entry
Thumbscrews:	UNC 4-40 (Standard)
Cable O.D:	Up to 11,5mm

#### High Density D-Sub Solder Cup:


Insulator:	Glass filled TP, UL94 V-0
Shell:	Steel, Tin Plated
Contact pins:	Copper Alloy Gold Flash over Ni.
Stamped & Formed Pins	Class 3, 100 inserts min.
Contact Plating:	Gold flash over Nickel
Operating Temperature:	-55°C to +85°C
Withstanding voltage:	>1000V Rms to 50 Hz for 1 minute
Current Rating:	3A
Insulator resistance:	>5000MΩ min.

#### Features:

- Available in sizes HD15-26-44-62
- 360° EMI Shielding
- Re-openable



#### Grommet Sizes DTZK:



Size D45ZK	Dim A	Dim B	Dim C
9-way	31,0	36,3	14,5
15-way	39,5	40,3	14,5
25-way	53,2	40,3	14,5
37-way	69,7	40,3	14,5

### Ordering information:

### High Density D-Sub Connector Kits

Size:	P/N - Kitted:	Description:
HD 15	L17D45ZK09+L717HDE15P	Solder Cup, 15-Male
HD 26	L17D45ZK15+L717HDA26P	Solder Cup, 26-Male
HD 44	L17D45ZK25+L717HDB44P	Solder Cup, 44-Male
HD 62	L17D45ZK37+L717HDC62P	Solder Cup, 62-Male

Size:	P/N - Kitted:	Description:
HD 15	L17D45ZK09+L77HDE15S	Solder Cup, 15-Female
HD 26	L17D45ZK15+L77HDA26S	Solder Cup, 26-Female
HD 44	L17D45ZK25+L77HDB44S	Solder Cup, 44-Female
HD 62	L17D45ZK37+L77HDC62S	Solder Cup, 62-Female