


24 2410 12

USB and IEEE 1394 connectors



USB 2.0 chassis socket type A, angular version, for printed circuit boards

1 of 3 05/2020



Materials

Insulating body PBT
Contact spring CuSn, gold-plated
Housing Steel, nickel-plated

Mechanical data

Insertion force $\leq 35 \text{ N}$ Withdrawal force $\geq 10 \text{ N}$

Electrical data (at Tamb 20 °C)

 Contact resistance
 ≤ 30 mΩ

 Rated current
 ≤ 1 A

 Rated voltage
 30 V DC

 Rated impulse voltage
 500 V

 Insulation resistance
 ≥ 1 GΩ




Counterparts


 © 2410 07
 © 2410 08
 © 2431

 © 2480
 © 2482

Accessories

☑ 2412 01





^{*}a printed circuit board layout



24 2410 12

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
2410 12	4	100	500

Packaging:

in a tray

3 of 3 05/2020