



ENGLISH

## Datasheet

Stock No: 17183016

### RS Pro Bolt Hole Swivel Braked Castor, 100mm Dia., 180kg



#### Technical Data

Wheel diameter	100 mm
Width of Tread	36 mm
Centre hole	13 mm
Offset	40 mm
Overall height	131 mm
Temperature	- 20 / + 60 °C
Swivel Radius	117 mm
Hardness of tread	Shore A 75
Load capacity	180 kg

## Product Details

Swivel castor with total lock, tail end of castor, bolt hole. Wheel centre made of Polyamide, Tread: elastic-tyre, non-marking, roller bearing

Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+