

# Rocker Switch



**Q-1304**

TYPE: **RK1-37**  
**Rocker**


## SPECIFICATIONS

Rating: 16A 250V AC  
Contact R: 100mΩ max  
Insulation R: 500V DC 100MΩ min  
Dielectric Strength: 1 Minute 1500V AC  
Operating Temperature: -25°C ~ +85°C  
Electrical Life: 10, 000 Cycles

Outline Drawing



Mounting



Circuitry

