

113.53.040 16 bar M10 x 1.0 center back mount

Pressure gauge with glycerine filling, stainless s

Item number: 48765959

Quantity: 1 pcs.

Order code: 113.53-A-BG416Z-MB-BZCZ4G-ZZZ
DIAL-IAZ1ZZZZZZZZZ1Z- 1Z1ZZ9ZZZZ

Overview: 113.53.040 16 bar M10 x 1.0 center back mount
class 2.5 case filling: glycerine
stop-pin at zero
EN 837-1 *Cl.2.5* *WIKA*

Details: Pressure gauge with glycerine filling, stainless s
teel case, Model 113.53
Movement: copper alloy
case: stainless steel
ingress protection: IP 65
Bezel ring: roll formed, stainless steel
Nominal size: 040 mm
Unit of outer Scale: bar
Measuring range: gauge pressure range
Scale range: 0...16 bar
Process connection: M10 x 1.0
Connector location: center back mount
window: polycarbon
Accuracy class: class 2.5
case filling: glycerine
Model: 113.53
Dial description:
Pressure Gauge Standard: International (standard Europe)
color for 1.scale (outside): black
dial background: White
Manufacturer logo: *WIKA*
stop pin on dial: at zero
norm-mark on dial: *EN 837-1*
accuracy class on dial: *Cl.2.5*