

Specifications	Range	UT201+	UT202+	UT202A+	UT203+	UT204+
AC current (A)	400A	±(2%+10)	±(2%+10)		±(2.5%+5)	
	600A			±(2%+10)		±(2.5%+5)
AC current frequency (Hz)	50Hz~100Hz	±(1%+5)	±(1%+5)	±(1%+5)		
DC current (A)	400A				±(2.5%+5)	
	600A					±(2.5%+5)
AC voltage (V)	600V	±(0.8%+5)	±(0.8%+5)	±(0.8%+5)	±(0.8%+5)	±(0.8%+5)
AC voltage frequency(Hz)	10Hz~10kHz	±(1%+5)	±(1%+5)	±(1%+5)		
	10Hz~60kHz				±(0.5%+2)	±(0.5%+2)
DC voltage (A)	600V	±(0.5%+2)	±(0.5%+2)	±(0.5%+2)	±(0.5%+2)	±(0.5%+2)
Resistance (Ω)	40MΩ	±(0.8%+2)	±(0.8%+2)		±(0.8%+2)	
	60MΩ			±(0.8%+2)		±(0.8%+2)
Capacitance (F)	4mF		±(4%+5)			
	40mF				±(4%+5)	
	60mF			±(4%+5)		±(4%+5)
Temperature (°C)	-40°C~1000°C		±(1.5%+5)			±(1.5%+5)
Frequency (Hz)	10Hz~10MHz			±(0.1%+4)	±(0.1%+4)	±(0.1%+4)
Features						
Display count		4000	4000	6000	4000	6000
Auto range		√	√	√	√	√
Jaw opening		28mm	28mm	28mm	28mm	28mm
True RMS		√	√	√	√	√
NCV		√	√	√	√	√
Live wire test				√		√
Continuity test		√	√	√	√	√
Diode		√	√	√	√	√
MAX/MIN		√	√	√	√	√
Relative mode			√	√	√	√
Zero mode					√	√
Data hold		√	√	√	√	√
Low battery indication		√	√	√	√	√
Auto power off		√	√	√	√	√
General Characteristics						
Power	1.5V battery (R03) x 2					
Display	37mm x 25mm					
Product color	Red and grey					

Product net weight	UT201+/UT202+/UT202A+ : 248g; UT203+/UT204+:235g
Product size	215mm x 63mm x 36mm
Standard accessories	Batteries, test leads, Themocouple (UT202+/UT204+)
Standard individual packing	Gift box, Carring bag, English manual
Standard quantity per carton	40pcs
Standard carton measurement	485mm x 295mm x 385mm
Standard carton gross weight	UT202A+: 17.8kg; UT203+: 16.8kg; UT201+/202+/204+: 17.3kg