

# Membrane Force Sensor



## 10.2mm Circle Active Area

### Application

- ✓ Fitness, Medical, Industrial and many others

### Feature

- ✓ Ultra-thin and Flexible, with better performance at high temperature, humidity and repeatability.

Order Code	Outline Drawing
MF01A-N-221-A04	

INSPECTION ITEM	SPECIFICATION
FORCE SENSITIVITY RANGE	10g~1000g (0.1N~9.8N)
FORCE RESOLUTION	Continuous(Analog)
STAND-OFF RESISTANCE (UNLOADED)	>20MΩ
FORCE REPEATABILITY (SINGLE PART)	2%
FORCE REPEATABILITY (PART TO PART)	5%
RESPONSE TIME	<1ms
LONG TERM DRIFT	<10% log10(time)
HYSTERESIS	10%
LIFE CYCLE (WITHOUT FAILURE)	>10 Million
OPERATING TEMPERATURE	-30°C to +85°C
HIGH HUMIDITY STORAGE	+70°C, 85%RH x 96hrs
HIGH TEMPERATURE STORAGE	+85°C x 120hrs
LOW TEMPERATURE STORAGE	-30°C x 120hrs

### CONNECTOR OPTIONS

Bare Tail	Female Contacts	Solder Tabs (pin)	Female Contact with Housing

Design and specifications presented here are for the standard parts only. Please kindly contact us for your special requests and ask for the current technical specifications before purchase and/or use.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha \(Taiwan\):](#)

[MF01A-N-221-A04](#)