

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0528850274](#)
Status: **Active**
Overview: SlimStack™ 0.635mm Pitch Board-to-Board Connectors
Description: 0.635mm Pitch SlimStack Receptacle, Surface Mount, Dual Row, Vertical Stacking, 6.00 to 10.00mm Stacking Heights, Embossed Tape with Cover Packaging, 20 Circuits

Documents:

[3D Model](#) [Packaging Specification SPK-52885-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification 527600000-000 \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family PCB Receptacles
Series [52885](#)
Application Board-to-Board, Signal
Comments Stacking-Type
Overview [SlimStack™ 0.635mm Pitch Board-to-Board Connectors](#)
Product Name SlimStack
UPC 822348165872

Physical

Circuits (Loaded) 20
Circuits (maximum) 20
Color - Resin Natural
Durability (mating cycles max) 50
Flammability 94V-0
Glow-Wire Capable No
Lock to Mating Part Yes
Mated Height 10.00mm, 6.00mm, 7.00mm, 8.00mm, 9.00mm
Mated Width 6.40mm
Material - Metal Copper Alloy
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Net Weight 462.001/mg
Number of Rows 2
Orientation Vertical
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Embossed Tape on Reel
Pitch - Mating Interface 0.64mm
Plating min - Mating 0.254µm
Plating min - Termination 2.032µm
Polarized to PCB Yes
Robotic Placement Pick and Place Cap
Surface Mount Compatible (SMC) N/A
Temperature Range - Operating -55° to +105°C
Termination Interface: Style Surface Mount

Electrical

Current - Maximum per Contact 0.5A
Voltage - Maximum 100V

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[52885 Series](#)

Mates With

[55091](#) , [53649](#) , [53627](#) , [53647](#) , [53625](#)

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

SPK-52885-001-001

527600000-000

SD-52885-003-001, SD-52885-004-001

This document was generated on 10/25/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION