


MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

CE **Firestop®** Technical Datasheet **RoHS₃**
tasker® C10025 CPR – 10x0,25 mm²
Braided Shielded Cable



NOTE
CATEGORY
APPLICATIONS

The picture does not represent the real number of conductors
 Braided Conductor Shielded Cable (See Data Network Catalogue)
 Data transmission and Electronics

- A:** Black **Flame Retardant PVC** sheath.
Outer cable diam. Ø 8,80 (±0,20) mm.
- B:** Braided Shielding O.F.C. Red Copper covering 85%.
- C:** Cores Insulation with **Flame Retardant PVC**.
Core color code with DIN 47100 Standards.
Diam. Ø 1,40 (±0,20) mm.
- D:** Stranded O.F.C. Red Copper formation 8x0,20 mm.
Nom. Cross section 10x0,25 mm².

MARKING

tasker® C10025 CPR 10x0,25 mm² O.F.C. - IMQ 0051-CPR-0966 – 2017 – Eca –
BRAIDED SHIELDED CABLE - Firestop® - Made Italy

Cable Properties

Conductor Resistance	75,85 Ω/Km
Capacity Core/Core	110 pF/m
Capacity Core/Shield	230 pF/m
Max Rated Voltage	49 V
Operative Temperature	-20/+70°C

USE	<input checked="" type="checkbox"/>	Indoor	Interno Edificio	INSTALLATION	<input checked="" type="checkbox"/>	Fixed	Fissa	INFORMATION	<input checked="" type="checkbox"/>	RoHS3 Compliant
Impiego	<input checked="" type="checkbox"/>	Outdoor Limited	Esterno Limitato	Posa	<input checked="" type="checkbox"/>	Restricted Mobile	Mobile Limitata	Informazioni	<input checked="" type="checkbox"/>	Ver. B / 26.05.19
		Outdoor	Esterno			Mobile	Mobile			
		Outdoor Direct Burial	Esterno Interrato			Mobile in Drag Chain	Mobile in Catena			