



UNIT	MM
------	----



**NOTE:**

1. Electrical test:

- (1). 100% open short & miss wire test;
- (2). Insulation resistance: DC 100V 0.01S 5M ohm;
- (3). Contactor resistance: 3 ohm Max;
- (4). Mac book pro + LG Monitor TEST: 3840\*2160@60Hz
- (5). Transmission rate : 40Gbps Current rate: 5A

2. RoHS and REACH Compliant

3. Support 100W MAX

**MATERIAL LIST:**

⑤	Housing	ABS Housing	2	
④	INNER MOLD	LD-PE	2	
③	E-mark	USB4 GEN3*2 40Gbps 5A	1	
②	TYPE C	USB C/M Solder Type, Black PBT Insulation, The Pin Gold Plating, the shell for Nickel Plating+Iron Shield	2	
①	CABLE	USB4 COAXL CABLE (30AWG*1C+SP+HM)*8COAX+ (34AWG*1P+HMAM)*1C +30AWG*4C+24AWG*1C+F+PAPER+B TPE JACKET BLACK OD: 4.6±0.2mm	1	
NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK

ITEM NO.	LENGTH
11.02.9080	500 ± 20mm
11.02.9081	1000 ± 30mm

DESC. ROLINE USB4 GEN3\*2 40Gbps Type CM/CM Black

CoCo	Alvan	NEW	2021.09.03	V1
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.

**SECOMP**