




<b>light source</b>	LED
<b>work equipment</b>	Energy efficiency category A/A+/A++
<b>connected load</b>	electronic ballast
<b>Power consumption</b>	220-240 V; 50/60 Hz
<b>luminous flux</b>	approx. 15 W
<b>luminous efficacy</b>	approx. 1100 lm
<b>colour temperature</b>	approx. 73 lm/W
<b>color rendering index (CRI)</b>	neutral white, approx. 5000 K
<b>glare control</b>	>= 80
<b>System of protection</b>	structured screen
<b>class of protection</b>	IP20
<b>technology</b>	I
<b>operation</b>	switchable
<b>luminaire body</b>	rocker switch
<b>lamp cover</b>	aluminium/plastic, anodised, aluminium coloured anodised
<b>weight (net)</b>	structured screen
<b>mains lead</b>	approx. 1.6 kg
	approx. 3,0 m; mains plug
	CEE 7/VI
<b>design</b>	mounted version
<b>Fastening</b>	screw down lash
<b>special features</b>	mounting left



CEE 7/VI



illuminance

luminous intensity

