

## S.LA - 1/2" long-reach metric 12-point sockets




### **Standards:**

**NF ISO 2725-1, NF ISO 1711-1,  
ISO 2725-1, ISO 1711-1, DIN  
3124, ASME B107.5**

### **Description:**

- OGV® profile: more powerful tightening, preserves fasteners.
- Long-reach sockets for long recess or thread access.
- Finish: bright chrome.

	A [mm]	Diameter [mm]	Diameter D1 [mm]	Length L [mm]	Length L1 [mm]	12-Point [mm]	Weight [g]
<b>S.12LA</b>	12.0	12.0	21.8	77.0	12.0	12.0	105.0
<b>S.12LAPB</b>	12.0	12.0	21.8	77.0	12.0	12.0	105.0
<b>S.13LA</b>	13.0	21.8	19.0	77.0	12.0	12.0	115.0
<b>S.13LAPB</b>	13.0	21.8	19.0	77.0	12.0	12.0	115.0
<b>S.14LA</b>	14.0	27.8	20.3	77.0	15.0	12.0	120.0
<b>S.15LA</b>	15.0	21.8	21.5	77.0	15.0	12.0	125.0
<b>S.16LA</b>	16.0	22.0	22.8	77.0	15.0	12.0	130.0
<b>S.17LA</b>	17.0	23.0	24.0	77.0	15.0	12.0	140.0
<b>S.17LAPB</b>	17.0	23.0	24.0	77.0	15.0	12.0	140.0
<b>S.18LA</b>	18.0	24.0	25.0	77.0	18.0	12.0	160.0
<b>S.19LA</b>	19.0	25.0	26.5	77.0	18.0	12.0	160.0
<b>S.19LAPB</b>	19.0	25.0	26.5	77.0	18.0	12.0	160.0
<b>S.21LA</b>	21.0	27.0	29.0	77.0	18.0	12.0	200.0
<b>S.21LAPB</b>	21.0	27.0	29.0	77.0	18.0	12.0	200.0
<b>S.22LA</b>	22.0	28.0	30.0	77.0	21.0	12.0	215.0
<b>S.23LA</b>	23.0	29.0	31.5	77.0	21.0	12.0	235.0
<b>S.24LA</b>	24.0	30.0	32.8	77.0	24.0	12.0	255.0
<b>S.24LAPB</b>	24.0	30.0	32.8	77.0	24.0	12.0	255.0
<b>S.26LA</b>	26.0	32.0	35.0	77.0	24.0	12.0	280.0
<b>S.27LA</b>	27.0	33.0	36.5	77.0	27.0	12.0	310.0
<b>S.27LAPB</b>	27.0	33.0	36.5	77.0	27.0	12.0	310.0
<b>S.28LA</b>	28.0	34.0	37.8	77.0	27.0	12.0	330.0
<b>S.29LA</b>	29.0	35.0	39.0	77.0	27.0	12.0	355.0
<b>S.30LA</b>	30.0	36.0	40.0	77.0	30.0	12.0	355.0
<b>S.30LAPB</b>	30.0	36.0	40.0	77.0	30.0	12.0	355.0
<b>S.32LA</b>	32.0	36.0	42.8	77.0	33.0	12.0	410.0
<b>S.32LAPB</b>	32.0	36.0	42.8	77.0	33.0	12.0	410.0