



SIRRUS **LED** Lamp, 500mm Flex Arm & Mounting Clamp

Get Light Where You Need it most?

The innovative SIRRUS LED Lamp features a flexible arm that allows you to direct light exactly where you want it. The 500mm (19.5") Flex Arm, covered with an insulated sleeve, provides vibration resistance. With its slim aluminum lamp head and one piece fabricated PC front shade, this energy efficient LED lamp provides an elegant modern design ideal for use anywhere including many office applications, assembly workstations, or quality inspection areas. You can regulate the brightness of the LED light with a convenient built-in dimmer switch on the base of the lamp. Includes metal clamp excellent for workbench mounting.

Features

- 500mm(19.5") industrial grade flexible gooseneck coated arm
- Arm stays set in any position to provide direct light where needed
- High intensity energy saving LEDs
- Cool operating temperature
- Exceptionally long LED element life (minimum 20,000 hours)
- Ideal for assembly, workshop or office applications
- Mounting Clamp allows for easy attachment to desk and bench tops

SIRRUS LED LAMP, 500MM(19.5) FLEX ARM & MOUNTING CLAMP	
LED COLOR	High intensity white LEDs
LIGHTING CONTROL	On/Off
LED LIFE	Minimum 20,000 hours
LED OUTPUT	14W
OUTPUT VOLTAGE	12V
INPUT VOLTAGE	100-260V
LENGTH OF GOOSENECK ARM	19.5" (500mm)
WEIGHT	5lbs (2.25kg)
PACKAGE CONTENTS	1 ea. SIRRUS Lamp LED, 500mm Flex Arm & Mounting Clamp

Part #	Description
26528	SIRRUS LED Lamp, 500mm(19.5") Flex Arm & Mounting Clamp
26520-MB	SIRRUS Magnetic Base optional for 26526, 26527 and 26528

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aven:](#)

[26528](#)