

MILAN S.r.l. a socio unico

**Head Office – Export department:**  
 Viale Europa, 74  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.4556-4158  
 F. +39 02 9039.4551  
 www.taskercables.com


**Ufficio Commerciale e Centro Distribuzione**  
 Viale Europa 72 Strada F12  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.0037-0059  
 F. +39 02 9039.0049  
 www.tasker.it



**Firestop® Technical Datasheet**



**tasker® C4050 CPR – 4x0,50 mm<sup>2</sup>  
 Braided Shielded Cable**



**NOTE**  
**CATEGORY**  
**APPLICATIONS**

The picture does not represent the real number of conductors  
 Braided Conductor Shielded Cable (See Data Network Catalogue)  
 Data transmission and Electronics

- A:** Black **Flame Retardant PVC** sheath.  
Outer cable diam. Ø 6,60 (±0,20) mm.
- B:** Braided Shielding O.F.C. Red Copper covering 85%.
- C:** Cores Insulation with **Flame Retardant PVC**.  
Core color code with DIN 47100 Standards.  
Diam. Ø 1,90 (±0,20) mm.
- D:** Stranded O.F.C. Red Copper formation 16x0,20 mm.  
Nom. Cross section 4x0,50 mm<sup>2</sup>.

**MARKING**

**tasker® C4050 CPR 4x0,50 mm<sup>2</sup> O.F.C. - IMQ 0051-CPR-0966 – 2017 – Eca –  
 BRAIDED SHIELDED CABLE - Firestop® - Made Italy**

**Cable Properties**

<b>Conductor Resistance</b>	38,00 Ω/Km
<b>Capacity Core/Core</b>	130 pF/mt
<b>Capacity Core/Shield</b>	220 pF/mt
<b>Max Rated Voltage</b>	49 V
<b>Operative Temperature</b>	-20/+70°C

<b>USE</b>	<b>X</b>	Indoor	Interno Edificio
<b>Impiego</b>	<b>X</b>	Outdoor Limited	Esterno Limitato
		Outdoor	Esterno
		Outdoor Direct Burial	Esterno Interrato

<b>INSTALLATION</b>	<b>X</b>	Fixed	Fissa
<b>Posa</b>	<b>X</b>	Restricted Mobile	Mobile Limitata
		Mobile	Mobile
		Mobile in Drag Chain	Mobile in Catena

<b>INFORMATION</b>	<b>X</b>	RoHS2 Compliant
<b>Informazioni</b>	<b>X</b>	Ver. A / 26.05.17